

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332459-930

Luminaire Tested: **S123RDIW-S1000D1030U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332459-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6143.5 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	53
1	99	95	91	88	92	88	85	82	75	73	71	63	62	60	53	52	51	46
2	91	84	78	73	84	78	73	68	67	63	60	56	54	51	47	45	44	39
3	83	74	67	61	77	69	63	58	59	55	51	50	47	44	42	40	38	34
4	76	66	58	52	70	61	55	50	53	48	44	45	42	38	38	35	33	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26
6	65	53	45	40	60	50	43	38	43	38	34	37	33	30	32	28	26	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	23	21	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	21	19	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13951	13951	13951	13951
5°	16630	14011	12337	14011
10°	20764	13930	11146	13930
15°	24373	13788	10165	13788
20°	27202	13575	9330	13575
25°	26766	13351	8817	13351
30°	19240	13144	8289	13144
35°	12846	12875	7947	12875
40°	9465	12552	7593	12552
45°	7939	11985	7247	11985
50°	7005	11241	6764	11241
55°	6142	10393	6101	10393
60°	5470	9580	5591	9580
65°	4806	8706	5201	8706
70°	3770	7928	4749	7928
75°	3323	6924	4338	6924
80°	2889	5883	4265	5883
85°	2322	4730	4520	4730



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.5	2.1
10°-20°	398.2	6.5
20°-30°	625.6	10.2
30°-40°	652.7	10.6
40°-50°	558.6	9.1
50°-60°	425.7	6.9
60°-70°	272.9	4.4
70°-80°	131.3	2.1
80°-90°	37.8	0.6
90°-100°	68.5	1.1
100°-110°	205.0	3.3
110°-120°	348.7	5.7
120°-130°	458.7	7.5
130°-140°	515.5	8.4
140°-150°	506.8	8.2
150°-160°	426.6	6.9
160°-170°	284.0	4.6
170°-180°	99.4	1.6
0°-30°	1151.2	18.7
0°-40°	1803.9	29.4
0°-60°	2788.2	45.4
0°-90°	3230.2	52.6
90°-120°	622.2	10.1
90°-150°	2103.2	34.2
90°-180°	2913.0	47.4
0°-180°	6143.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1296	1296	1296	1296	1296	
5°	1539	1297	1142	1297	1539	159
15°	2187	1237	912	1237	2187	620
25°	2254	1124	742	1124	2254	969
35°	978	980	605	980	978	641
45°	522	787	476	787	522	410
55°	327	554	325	554	327	296
65°	189	342	204	342	189	186
75°	80	166	104	166	80	86
85°	19	38	37	38	19	22
90°	25	1	25	1	25	13
95°	64	49	64	49	64	66
105°	197	186	197	186	197	209
115°	352	351	352	351	352	348
125°	508	514	508	514	508	454
135°	666	667	666	667	666	512
145°	809	809	809	809	809	505
155°	924	926	924	926	924	426
165°	1005	1008	1005	1008	1005	284
175°	1045	1049	1045	1049	1045	99
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1380.5	1382.2	1376.5	1375.6	1368.9	1367.1	1367.1	1357.8	1352.0	1344.5	1340.0
5°	1539.1	1548.0	1543.5	1533.6	1516.9	1513.0	1502.5	1485.9	1467.0	1443.7	1432.6
7.5°	1737.3	1749.4	1744.7	1729.3	1711.9	1697.8	1668.1	1640.5	1601.7	1567.7	1538.7
10°	1899.7	1887.0	1877.0	1862.1	1845.9	1819.8	1788.8	1746.0	1696.7	1657.8	1614.6
12.5°	2021.4	2019.3	2006.6	1991.2	1968.5	1943.7	1905.5	1853.5	1796.1	1740.0	1690.4
15°	2187.2	2190.5	2182.1	2166.1	2133.9	2090.1	2032.4	2010.8	1928.6	1867.6	1806.5
17.5°	2301.9	2301.3	2300.1	2277.9	2245.0	2213.8	2160.3	2103.4	2029.0	1943.0	1860.8
20°	2374.7	2369.2	2370.2	2345.3	2320.9	2284.8	2232.7	2150.0	2089.0	1989.7	1904.8
22.5°	2372.9	2371.8	2376.0	2367.5	2349.8	2322.1	2281.0	2211.3	2133.3	2033.1	1937.6
25°	2253.7	2249.3	2275.4	2282.6	2310.9	2315.9	2303.7	2265.4	2191.6	2088.4	1970.3
27.5°	1886.2	1883.7	1932.2	1992.8	2069.6	2129.2	2187.0	2214.8	2191.6	2117.7	1999.3
30°	1548.0	1600.2	1624.6	1712.2	1809.9	1926.4	2028.5	2125.6	2149.5	2117.3	2020.1
32.5°	1285.2	1330.7	1351.1	1426.4	1517.4	1653.8	1807.0	1944.5	2041.6	2066.2	2007.8
35°	977.6	978.2	1024.7	1058.1	1142.4	1282.8	1431.5	1615.7	1798.8	1937.5	1951.9
37.5°	780.1	782.9	811.1	844.2	907.5	981.7	1112.6	1265.8	1477.3	1690.3	1815.1
40°	673.6	678.6	699.7	732.4	777.9	833.9	936.0	1080.3	1256.7	1493.6	1687.3
42.5°	605.2	613.3	624.2	649.4	677.6	730.0	812.6	924.1	1084.5	1308.6	1531.9
45°	521.5	525.9	534.3	545.9	571.4	608.1	663.6	738.5	871.6	1052.0	1275.5
47.5°	460.1	457.7	466.5	476.0	492.9	517.9	555.1	616.2	711.2	855.9	1045.5
50°	418.3	417.8	423.9	431.1	447.2	465.5	496.0	542.1	617.5	737.4	911.0
52.5°	379.3	381.4	385.7	394.7	406.3	421.1	448.5	481.7	546.5	650.0	794.8
55°	327.3	329.1	335.1	340.1	348.5	363.4	380.6	408.4	452.7	524.9	644.2
57.5°	283.4	282.7	288.5	289.8	299.1	311.4	324.7	346.3	378.4	432.0	512.3
60°	254.1	252.4	257.5	261.3	266.4	276.3	287.4	308.5	334.0	373.4	442.2
62.5°	227.5	226.7	230.4	234.2	238.4	247.4	256.8	273.0	293.2	326.4	381.0
65°	188.7	190.3	192.0	193.6	195.8	201.4	210.3	221.4	235.2	258.5	297.9
67.5°	148.2	149.9	150.5	153.9	158.7	162.2	167.5	177.4	187.1	206.8	229.2
70°	119.8	119.3	119.8	121.5	127.6	133.7	141.0	148.1	154.3	168.1	186.9
72.5°	103.0	102.0	103.5	103.8	106.7	108.4	113.0	119.8	127.6	137.1	150.6
75°	79.9	79.9	79.9	79.9	82.1	83.2	84.9	86.6	89.4	93.8	103.8
77.5°	59.0	59.1	59.9	60.5	60.9	61.6	62.6	64.2	65.2	67.6	71.9
80°	46.6	47.1	46.6	47.1	47.1	48.3	48.8	50.5	51.0	53.8	55.5
82.5°	35.1	34.7	35.1	35.6	35.6	36.8	36.9	38.1	38.2	39.6	41.3
85°	18.8	17.8	18.8	18.3	19.4	18.3	18.8	20.0	20.0	20.5	22.7
87.5°	9.4	10.2	9.2	9.6	9.5	9.9	9.7	9.6	10.4	9.7	9.7
90°	24.8	24.4	24.1	23.6	23.3	22.7	22.0	21.3	20.5	19.8	17.4
92.5°	33.3	33.6	33.8	34.0	34.2	34.1	33.5	32.9	32.3	31.7	30.3
95°	64.4	64.4	64.4	64.4	64.4	64.1	63.3	62.6	61.9	61.1	59.7
97.5°	99.1	99.2	99.3	99.3	99.4	99.1	98.2	97.3	96.5	95.6	94.6
100°	125.6	125.1	124.8	124.4	124.1	123.6	123.1	122.5	122.0	121.4	120.5
102.5°	152.6	152.7	152.8	152.9	153.0	152.7	152.1	151.6	151.1	150.5	149.3
105°	196.6	196.2	195.8	195.5	195.1	194.9	194.9	194.9	194.9	194.9	193.3
107.5°	242.3	242.6	242.8	243.0	243.2	243.0	242.5	241.9	241.2	240.7	240.0
110°	273.4	273.8	274.1	274.5	274.8	274.7	273.9	273.2	272.5	271.7	271.4



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	306.5	306.6	306.6	306.6	306.7	306.3	305.4	304.6	303.7	302.8	302.7
115°	351.9	352.0	352.2	352.5	352.6	352.6	352.5	352.2	352.0	351.9	352.2
117.5°	397.9	398.4	399.0	399.5	400.0	400.3	400.3	400.4	400.4	400.5	400.9
120°	430.3	430.7	431.0	431.5	431.8	432.1	432.3	432.4	432.6	432.8	433.7
122.5°	461.4	461.9	462.4	462.9	463.4	464.0	464.4	464.9	465.4	465.9	466.4
125°	508.0	508.7	509.5	510.2	510.9	511.7	512.4	513.1	513.9	514.6	514.9
127.5°	554.4	555.2	556.1	556.9	557.7	558.7	559.8	560.8	561.8	562.8	563.2
130°	584.8	586.1	587.3	588.6	590.0	590.9	591.7	592.4	593.1	593.9	594.4
132.5°	616.5	617.5	618.5	619.5	620.5	621.4	622.3	623.2	624.0	624.9	625.3
135°	665.8	666.1	666.5	666.8	667.2	667.7	668.5	669.2	669.9	670.7	670.9
137.5°	709.2	709.9	710.6	711.3	712.0	712.7	713.5	714.3	715.0	715.8	715.3
140°	737.6	738.9	740.2	741.4	742.7	743.5	743.6	743.9	744.0	744.2	744.0
142.5°	766.7	767.7	768.7	769.6	770.6	771.3	771.4	771.6	771.8	772.0	771.7
145°	808.6	809.3	810.1	810.8	811.5	812.0	812.2	812.4	812.6	812.8	812.2
147.5°	846.0	847.1	848.2	849.3	850.4	850.9	850.9	850.9	850.9	850.9	850.4
150°	869.8	870.9	872.0	873.1	874.2	874.7	874.7	874.7	874.7	874.7	874.3
152.5°	892.9	893.8	894.8	895.8	896.7	897.1	896.7	896.4	896.2	895.9	895.7
155°	924.3	925.6	926.8	928.1	929.4	929.7	929.0	928.2	927.5	926.8	926.6
157.5°	952.8	953.9	955.0	955.9	957.0	957.1	956.3	955.5	954.8	954.0	953.9
160°	971.3	972.1	972.8	973.5	974.3	974.2	973.3	972.4	971.4	970.5	970.5
162.5°	985.2	986.4	987.6	988.8	989.9	990.1	989.1	988.2	987.3	986.4	986.3
165°	1005.3	1006.5	1007.8	1009.1	1010.4	1010.5	1009.3	1008.3	1007.1	1006.1	1006.1
167.5°	1022.2	1023.4	1024.5	1025.6	1026.8	1026.8	1025.6	1024.5	1023.4	1022.2	1022.1
170°	1030.9	1032.1	1033.4	1034.7	1036.0	1036.0	1034.7	1033.4	1032.1	1030.9	1030.9
172.5°	1037.5	1038.7	1040.0	1041.3	1042.6	1042.7	1041.5	1040.4	1039.3	1038.1	1038.1
175°	1044.9	1046.2	1047.4	1048.7	1050.0	1050.1	1049.0	1047.9	1046.8	1045.7	1045.7
177.5°	1048.9	1049.9	1050.9	1051.9	1053.0	1053.0	1052.1	1051.2	1050.4	1049.5	1049.5
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1338.2	1336.9	1330.7	1323.6	1314.3	1308.1	1303.2	1300.6	1292.6	1282.8	1276.1
5°	1420.9	1404.3	1386.6	1364.9	1344.9	1324.4	1311.7	1296.7	1278.3	1257.8	1243.4
7.5°	1509.5	1476.8	1441.7	1405.4	1369.5	1337.4	1309.0	1284.7	1255.5	1226.0	1205.4
10°	1577.4	1529.7	1480.3	1429.8	1383.7	1340.5	1307.2	1274.5	1239.5	1205.7	1180.1
12.5°	1639.1	1576.3	1519.4	1457.3	1398.4	1346.7	1298.8	1260.3	1218.2	1182.1	1153.1
15°	1717.2	1652.9	1584.0	1489.7	1411.5	1346.1	1287.8	1237.3	1186.3	1141.8	1113.5
17.5°	1790.2	1693.4	1600.9	1522.2	1420.6	1338.8	1267.7	1207.3	1151.3	1104.2	1069.4
20°	1820.4	1726.6	1626.2	1525.8	1426.0	1334.4	1251.7	1185.1	1126.9	1073.6	1041.5
22.5°	1838.6	1732.4	1626.7	1518.7	1412.6	1317.5	1235.7	1162.5	1099.3	1048.7	1009.0
25°	1859.8	1733.3	1616.8	1510.3	1402.1	1298.9	1201.8	1124.1	1055.9	1002.0	959.9
27.5°	1873.8	1725.0	1587.3	1468.8	1359.1	1256.4	1167.3	1085.0	1015.8	958.9	913.6
30°	1876.5	1718.3	1564.6	1436.5	1324.9	1230.6	1136.3	1057.5	984.3	923.8	881.7
32.5°	1880.0	1701.9	1534.0	1397.8	1283.7	1190.3	1104.8	1029.6	954.6	895.0	851.9
35°	1865.4	1692.8	1487.5	1331.1	1216.8	1126.3	1049.2	979.8	906.0	848.3	804.5
37.5°	1802.3	1656.8	1439.3	1255.8	1136.3	1052.6	989.7	929.3	861.5	799.3	758.0
40°	1738.9	1621.2	1402.1	1210.1	1085.2	999.2	942.6	893.3	827.9	769.6	725.2
42.5°	1644.3	1572.9	1366.6	1162.1	1027.5	944.7	896.9	850.7	793.2	734.0	692.4
45°	1470.9	1480.3	1293.9	1085.8	947.6	864.5	819.5	787.3	736.3	687.5	644.7
47.5°	1253.4	1341.6	1208.5	1004.4	863.4	785.3	746.0	718.0	683.5	635.6	596.6
50°	1111.3	1237.3	1140.2	949.9	810.7	733.0	694.1	671.3	641.4	603.6	566.5
52.5°	980.4	1115.7	1057.6	889.1	753.3	682.3	644.4	625.7	601.9	566.4	532.7
55°	799.5	936.5	923.2	797.3	667.5	603.6	574.8	553.8	537.6	511.0	484.4
57.5°	646.7	776.7	783.5	695.2	591.8	528.7	503.9	488.0	477.5	457.4	432.8
60°	550.4	669.7	693.0	626.4	537.6	482.2	457.7	445.0	436.7	420.5	401.7
62.5°	470.5	572.0	598.4	550.5	485.7	433.7	414.7	402.4	396.7	382.9	366.2
65°	360.1	444.4	469.9	443.3	409.4	367.9	352.3	341.8	336.8	329.1	316.8
67.5°	270.8	332.2	360.2	341.4	329.2	303.0	293.1	287.4	283.0	277.6	267.4
70°	217.5	263.0	291.9	286.8	276.9	263.0	255.8	251.9	247.4	243.0	234.2
72.5°	174.9	206.2	233.3	235.8	227.6	224.9	218.5	216.9	214.2	208.9	204.0
75°	115.9	137.6	156.5	163.7	167.0	169.7	167.0	166.5	165.9	161.4	158.7
77.5°	76.0	87.6	99.5	111.9	117.1	120.8	121.7	123.8	122.3	119.9	118.6
80°	58.3	61.1	69.4	79.9	88.2	91.6	93.8	94.9	94.3	93.8	91.6
82.5°	42.3	44.6	48.5	55.9	62.9	68.5	69.8	69.5	70.8	71.1	69.4
85°	22.7	23.3	24.4	25.5	29.4	35.5	37.2	38.3	39.4	39.4	36.0
87.5°	10.1	9.2	9.6	9.2	10.1	10.2	12.6	14.3	15.2	13.8	14.1
90°	15.1	12.6	10.3	8.2	6.4	4.5	2.7	0.8	2.7	4.5	6.4
92.5°	29.0	27.6	26.3	24.9	23.7	22.5	21.2	20.0	21.2	22.5	23.7
95°	58.2	56.7	55.3	53.9	52.6	51.3	50.0	48.8	50.0	51.3	52.6
97.5°	93.5	92.5	91.4	90.4	89.4	88.5	87.5	86.6	87.5	88.5	89.4
100°	119.6	118.7	117.7	116.8	115.6	114.5	113.4	112.3	113.4	114.5	115.6
102.5°	148.1	146.8	145.6	144.7	144.1	143.4	142.8	142.1	142.8	143.4	144.1
105°	191.6	190.0	188.3	187.4	186.9	186.6	186.2	185.9	186.2	186.6	186.9
107.5°	239.4	238.7	238.1	237.6	237.4	237.2	236.9	236.8	236.9	237.2	237.4
110°	271.0	270.7	270.3	269.9	269.5	269.2	268.8	268.5	268.8	269.2	269.5



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	302.6	302.6	302.5	302.4	302.1	301.9	301.7	301.5	301.7	301.9	302.1
115°	352.6	352.9	353.4	353.3	352.7	352.1	351.6	351.1	351.6	352.1	352.7
117.5°	401.4	401.9	402.4	402.4	402.0	401.7	401.3	401.0	401.3	401.7	402.0
120°	434.6	435.5	436.5	436.4	435.3	434.2	433.1	432.0	433.1	434.2	435.3
122.5°	466.8	467.3	467.7	467.6	466.8	466.0	465.2	464.4	465.2	466.0	466.8
125°	515.4	515.7	516.1	516.0	515.4	514.9	514.3	513.8	514.3	514.9	515.4
127.5°	563.6	564.0	564.4	564.0	562.9	561.7	560.5	559.4	560.5	561.7	562.9
130°	595.0	595.6	596.1	595.7	594.2	592.7	591.3	589.8	591.3	592.7	594.2
132.5°	625.7	626.1	626.6	626.1	624.6	623.1	621.6	620.1	621.6	623.1	624.6
135°	671.1	671.2	671.4	671.0	669.8	668.8	667.6	666.6	667.6	668.8	669.8
137.5°	714.9	714.4	713.9	713.2	712.2	711.3	710.5	709.6	710.5	711.3	712.2
140°	743.9	743.6	743.5	742.9	742.0	741.1	740.2	739.2	740.2	741.1	742.0
142.5°	771.3	770.9	770.6	770.1	769.1	768.2	767.3	766.4	767.3	768.2	769.1
145°	811.7	811.1	810.6	810.1	809.8	809.3	809.0	808.6	809.0	809.3	809.8
147.5°	849.9	849.4	848.9	848.3	847.7	846.9	846.3	845.6	846.3	846.9	847.7
150°	874.0	873.6	873.3	872.9	872.5	872.1	871.8	871.4	871.8	872.1	872.5
152.5°	895.4	895.2	895.0	894.6	894.1	893.6	893.1	892.6	893.1	893.6	894.1
155°	926.4	926.2	926.0	925.9	925.9	925.9	925.9	925.9	925.9	925.9	925.9
157.5°	953.7	953.6	953.4	953.5	953.7	953.9	954.1	954.4	954.1	953.9	953.7
160°	970.5	970.5	970.5	970.7	971.1	971.4	971.8	972.2	971.8	971.4	971.1
162.5°	986.1	985.9	985.8	986.0	986.5	987.0	987.6	988.1	987.6	987.0	986.5
165°	1006.1	1006.1	1006.1	1006.3	1006.9	1007.5	1008.0	1008.5	1008.0	1007.5	1006.9
167.5°	1022.0	1021.8	1021.7	1022.0	1022.7	1023.4	1024.2	1024.9	1024.2	1023.4	1022.7
170°	1030.9	1030.9	1030.9	1031.2	1031.9	1032.7	1033.4	1034.1	1033.4	1032.7	1031.9
172.5°	1038.1	1038.1	1038.1	1038.4	1039.2	1039.9	1040.6	1041.4	1040.6	1039.9	1039.2
175°	1045.7	1045.7	1045.7	1046.1	1046.8	1047.6	1048.3	1049.0	1048.3	1047.6	1046.8
177.5°	1049.5	1049.5	1049.5	1049.8	1050.4	1051.0	1051.6	1052.1	1051.6	1051.0	1050.4
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1273.9	1268.1	1264.1	1255.2	1249.5	1243.2	1237.1	1241.0	1240.6	1240.2	1240.2
5°	1231.2	1218.4	1206.8	1191.8	1182.3	1170.7	1161.8	1160.7	1162.9	1155.2	1150.7
7.5°	1188.8	1171.3	1154.9	1138.3	1120.8	1106.8	1098.0	1093.9	1088.3	1083.5	1078.5
10°	1159.0	1138.6	1122.4	1101.9	1083.0	1066.4	1055.9	1048.6	1044.7	1040.9	1033.6
12.5°	1128.5	1108.3	1087.9	1064.6	1046.7	1027.4	1019.5	1011.4	1004.0	999.6	989.7
15°	1083.6	1057.5	1035.9	1011.5	991.5	972.7	961.6	945.4	943.2	937.7	927.7
17.5°	1038.7	1010.3	980.5	962.5	939.9	920.2	903.4	898.0	882.1	876.1	867.4
20°	1003.1	977.1	954.3	930.5	897.7	879.4	866.1	858.9	846.1	838.4	832.8
22.5°	972.5	946.0	919.7	891.9	864.9	844.3	834.6	823.4	816.4	805.5	799.5
25°	928.8	899.9	868.3	838.4	819.0	803.4	787.9	777.9	767.9	762.9	751.8
27.5°	878.0	847.8	818.2	795.5	771.7	756.4	742.2	733.4	721.4	713.0	706.9
30°	850.0	814.5	789.0	768.4	737.9	723.5	713.0	701.9	693.0	684.1	678.0
32.5°	817.6	785.2	761.0	735.6	712.2	696.4	682.8	673.0	665.4	657.0	650.9
35°	766.8	739.6	714.6	689.1	671.9	655.8	639.8	631.4	624.2	616.4	610.9
37.5°	720.8	695.5	671.7	647.5	626.1	613.1	600.1	593.8	584.0	578.8	573.2
40°	692.4	667.5	642.0	618.6	596.5	586.4	574.8	565.4	556.5	552.6	546.5
42.5°	661.4	636.4	614.9	589.8	571.6	558.1	547.3	537.0	530.4	524.6	521.2
45°	615.3	593.1	572.0	547.1	529.9	518.2	506.0	496.6	490.5	486.6	480.5
47.5°	570.6	548.4	527.0	505.2	488.6	475.2	463.1	456.5	448.4	443.7	439.5
50°	538.2	518.2	495.5	475.5	458.9	445.6	435.5	427.2	420.0	413.9	411.2
52.5°	508.4	487.1	467.5	448.9	431.3	416.2	407.2	398.4	393.0	386.0	382.7
55°	459.4	438.9	422.2	403.9	386.7	374.0	362.9	355.1	349.5	341.8	337.4
57.5°	413.4	394.9	375.0	359.2	341.4	330.7	321.5	311.0	304.2	298.1	293.8
60°	382.3	361.2	344.0	329.1	313.5	299.6	291.3	283.0	275.7	269.6	265.8
62.5°	349.8	331.5	315.1	298.8	284.6	272.6	262.9	255.9	249.6	245.6	241.8
65°	300.2	285.8	269.1	255.8	242.5	233.6	225.8	219.7	215.2	212.5	209.2
67.5°	254.5	240.4	225.9	212.9	204.0	197.2	192.1	186.9	184.7	181.1	178.9
70°	224.7	210.3	197.5	187.5	178.6	173.7	170.3	166.5	164.2	159.8	157.6
72.5°	192.3	181.9	172.7	164.4	157.4	152.8	148.5	143.8	140.2	135.3	133.1
75°	151.5	142.0	134.9	129.3	124.8	118.7	112.6	107.6	106.0	104.3	103.8
77.5°	112.2	106.2	101.0	96.3	90.7	86.3	85.0	83.9	83.6	82.7	82.7
80°	88.2	82.7	78.8	73.2	69.9	69.9	69.9	68.8	69.4	69.4	69.4
82.5°	65.6	60.5	58.4	56.3	55.7	56.2	56.2	56.3	56.0	56.9	56.5
85°	33.8	34.4	35.5	35.0	35.5	35.5	36.6	36.0	36.6	35.5	36.6
87.5°	14.0	15.8	16.7	17.7	18.6	18.6	19.2	19.3	20.0	20.1	20.2
90°	8.2	10.3	12.6	15.1	17.4	19.8	20.5	21.3	22.0	22.7	23.3
92.5°	24.9	26.3	27.6	29.0	30.3	31.7	32.3	32.9	33.5	34.1	34.2
95°	53.9	55.3	56.7	58.2	59.7	61.1	61.9	62.6	63.3	64.1	64.4
97.5°	90.4	91.4	92.5	93.5	94.6	95.6	96.5	97.3	98.2	99.1	99.4
100°	116.8	117.7	118.7	119.6	120.5	121.4	122.0	122.5	123.1	123.6	124.1
102.5°	144.7	145.6	146.8	148.1	149.3	150.5	151.1	151.6	152.1	152.7	153.0
105°	187.4	188.3	190.0	191.6	193.3	194.9	194.9	194.9	194.9	194.9	195.1
107.5°	237.6	238.1	238.7	239.4	240.0	240.7	241.2	241.9	242.5	243.0	243.2
110°	269.9	270.3	270.7	271.0	271.4	271.7	272.5	273.2	273.9	274.7	274.8



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	302.4	302.5	302.6	302.6	302.7	302.8	303.7	304.6	305.4	306.3	306.7
115°	353.3	353.4	352.9	352.6	352.2	351.9	352.0	352.2	352.5	352.6	352.6
117.5°	402.4	402.4	401.9	401.4	400.9	400.5	400.4	400.4	400.3	400.3	400.0
120°	436.4	436.5	435.5	434.6	433.7	432.8	432.6	432.4	432.3	432.1	431.8
122.5°	467.6	467.7	467.3	466.8	466.4	465.9	465.4	464.9	464.4	464.0	463.4
125°	516.0	516.1	515.7	515.4	514.9	514.6	513.9	513.1	512.4	511.7	510.9
127.5°	564.0	564.4	564.0	563.6	563.2	562.8	561.8	560.8	559.8	558.7	557.7
130°	595.7	596.1	595.6	595.0	594.4	593.9	593.1	592.4	591.7	590.9	590.0
132.5°	626.1	626.6	626.1	625.7	625.3	624.9	624.0	623.2	622.3	621.4	620.5
135°	671.0	671.4	671.2	671.1	670.9	670.7	669.9	669.2	668.5	667.7	667.2
137.5°	713.2	713.9	714.4	714.9	715.3	715.8	715.0	714.3	713.5	712.7	712.0
140°	742.9	743.5	743.6	743.9	744.0	744.2	744.0	743.9	743.6	743.5	742.7
142.5°	770.1	770.6	770.9	771.3	771.7	772.0	771.8	771.6	771.4	771.3	770.6
145°	810.1	810.6	811.1	811.7	812.2	812.8	812.6	812.4	812.2	812.0	811.5
147.5°	848.3	848.9	849.4	849.9	850.4	850.9	850.9	850.9	850.9	850.9	850.4
150°	872.9	873.3	873.6	874.0	874.3	874.7	874.7	874.7	874.7	874.7	874.2
152.5°	894.6	895.0	895.2	895.4	895.7	895.9	896.2	896.4	896.7	897.1	896.7
155°	925.9	926.0	926.2	926.4	926.6	926.8	927.5	928.2	929.0	929.7	929.4
157.5°	953.5	953.4	953.6	953.7	953.9	954.0	954.8	955.5	956.3	957.1	957.0
160°	970.7	970.5	970.5	970.5	970.5	970.5	971.4	972.4	973.3	974.2	974.3
162.5°	986.0	985.8	985.9	986.1	986.3	986.4	987.3	988.2	989.1	990.1	989.9
165°	1006.3	1006.1	1006.1	1006.1	1006.1	1006.1	1007.1	1008.3	1009.3	1010.5	1010.4
167.5°	1022.0	1021.7	1021.8	1022.0	1022.1	1022.2	1023.4	1024.5	1025.6	1026.8	1026.8
170°	1031.2	1030.9	1030.9	1030.9	1030.9	1030.9	1032.1	1033.4	1034.7	1036.0	1036.0
172.5°	1038.4	1038.1	1038.1	1038.1	1038.1	1038.1	1039.3	1040.4	1041.5	1042.7	1042.6
175°	1046.1	1045.7	1045.7	1045.7	1045.7	1045.7	1046.8	1047.9	1049.0	1050.1	1050.0
177.5°	1049.8	1049.5	1049.5	1049.5	1049.5	1049.5	1050.4	1051.2	1052.1	1053.0	1053.0
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1234.9	1234.4	1234.9	1233.1	1234.9	1234.4	1234.9	1240.2	1240.2	1240.6	1241.0
5°	1149.1	1148.5	1146.9	1141.8	1146.9	1148.5	1149.1	1150.7	1155.2	1162.9	1160.7
7.5°	1074.2	1073.4	1068.5	1068.6	1068.5	1073.4	1074.2	1078.5	1083.5	1088.3	1093.9
10°	1029.8	1030.3	1023.7	1019.8	1023.7	1030.3	1029.8	1033.6	1040.9	1044.7	1048.6
12.5°	986.8	984.1	978.8	974.5	978.8	984.1	986.8	989.7	999.6	1004.0	1011.4
15°	929.9	924.4	911.0	912.2	911.0	924.4	929.9	927.7	937.7	943.2	945.4
17.5°	863.0	858.9	858.7	850.9	858.7	858.9	863.0	867.4	876.1	882.1	898.0
20°	823.9	821.2	822.2	814.5	822.2	821.2	823.9	832.8	838.4	846.1	858.9
22.5°	793.3	790.5	785.9	783.4	785.9	790.5	793.3	799.5	805.5	816.4	823.4
25°	748.4	744.0	739.6	742.4	739.6	744.0	748.4	751.8	762.9	767.9	777.9
27.5°	703.7	700.3	695.9	695.3	695.9	700.3	703.7	706.9	713.0	721.4	733.4
30°	675.2	671.9	669.7	666.9	669.7	671.9	675.2	678.0	684.1	693.0	701.9
32.5°	646.4	645.7	641.7	641.2	641.7	645.7	646.4	650.9	657.0	665.4	673.0
35°	608.6	605.4	604.2	604.8	604.2	605.4	608.6	610.9	616.4	624.2	631.4
37.5°	572.8	568.3	566.4	564.4	566.4	568.3	572.8	573.2	578.8	584.0	593.8
40°	547.1	542.7	541.5	540.4	541.5	542.7	547.1	546.5	552.6	556.5	565.4
42.5°	518.2	516.4	515.8	513.8	515.8	516.4	518.2	521.2	524.6	530.4	537.0
45°	478.8	478.3	474.9	476.1	474.9	478.3	478.8	480.5	486.6	490.5	496.6
47.5°	437.3	434.9	432.5	434.1	432.5	434.9	437.3	439.5	443.7	448.4	456.5
50°	409.0	407.8	402.8	403.9	402.8	407.8	409.0	411.2	413.9	420.0	427.2
52.5°	380.5	376.3	374.4	373.7	374.4	376.3	380.5	382.7	386.0	393.0	398.4
55°	333.5	328.5	326.3	325.1	326.3	328.5	333.5	337.4	341.8	349.5	355.1
57.5°	287.3	285.9	284.2	285.4	284.2	285.9	287.3	293.8	298.1	304.2	311.0
60°	260.2	260.2	260.2	259.7	260.2	260.2	260.2	265.8	269.6	275.7	283.0
62.5°	239.4	238.0	237.6	238.4	237.6	238.0	239.4	241.8	245.6	249.6	255.9
65°	207.5	206.9	204.7	204.2	204.7	206.9	207.5	209.2	212.5	215.2	219.7
67.5°	177.4	175.5	174.8	174.0	174.8	175.5	177.4	178.9	181.1	184.7	186.9
70°	154.8	153.7	150.3	150.9	150.3	153.7	154.8	157.6	159.8	164.2	166.5
72.5°	130.4	129.3	128.6	127.8	128.6	129.3	130.4	133.1	135.3	140.2	143.8
75°	103.2	102.6	102.1	104.3	102.1	102.6	103.2	103.8	104.3	106.0	107.6
77.5°	82.7	82.7	83.0	82.1	83.0	82.7	82.7	82.7	82.7	83.6	83.9
80°	69.4	69.4	68.8	68.8	68.8	69.4	69.4	69.4	69.4	69.4	68.8
82.5°	55.6	56.0	56.3	55.5	56.3	56.0	55.6	56.5	56.9	56.0	56.3
85°	36.6	36.0	37.2	36.6	37.2	36.0	36.6	36.6	35.5	36.6	36.0
87.5°	21.2	20.4	20.4	21.0	20.4	20.4	21.2	20.2	20.1	20.0	19.3
90°	23.6	24.1	24.4	24.8	24.4	24.1	23.6	23.3	22.7	22.0	21.3
92.5°	34.0	33.8	33.6	33.3	33.6	33.8	34.0	34.2	34.1	33.5	32.9
95°	64.4	64.4	64.4	64.4	64.4	64.4	64.4	64.4	64.1	63.3	62.6
97.5°	99.3	99.3	99.2	99.1	99.2	99.3	99.3	99.4	99.1	98.2	97.3
100°	124.4	124.8	125.1	125.6	125.1	124.8	124.4	124.1	123.6	123.1	122.5
102.5°	152.9	152.8	152.7	152.6	152.7	152.8	152.9	153.0	152.7	152.1	151.6
105°	195.5	195.8	196.2	196.6	196.2	195.8	195.5	195.1	194.9	194.9	194.9
107.5°	243.0	242.8	242.6	242.3	242.6	242.8	243.0	243.2	243.0	242.5	241.9
110°	274.5	274.1	273.8	273.4	273.8	274.1	274.5	274.8	274.7	273.9	273.2



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	306.6	306.6	306.6	306.5	306.6	306.6	306.6	306.7	306.3	305.4	304.6
115°	352.5	352.2	352.0	351.9	352.0	352.2	352.5	352.6	352.6	352.5	352.2
117.5°	399.5	399.0	398.4	397.9	398.4	399.0	399.5	400.0	400.3	400.3	400.4
120°	431.5	431.0	430.7	430.3	430.7	431.0	431.5	431.8	432.1	432.3	432.4
122.5°	462.9	462.4	461.9	461.4	461.9	462.4	462.9	463.4	464.0	464.4	464.9
125°	510.2	509.5	508.7	508.0	508.7	509.5	510.2	510.9	511.7	512.4	513.1
127.5°	556.9	556.1	555.2	554.4	555.2	556.1	556.9	557.7	558.7	559.8	560.8
130°	588.6	587.3	586.1	584.8	586.1	587.3	588.6	590.0	590.9	591.7	592.4
132.5°	619.5	618.5	617.5	616.5	617.5	618.5	619.5	620.5	621.4	622.3	623.2
135°	666.8	666.5	666.1	665.8	666.1	666.5	666.8	667.2	667.7	668.5	669.2
137.5°	711.3	710.6	709.9	709.2	709.9	710.6	711.3	712.0	712.7	713.5	714.3
140°	741.4	740.2	738.9	737.6	738.9	740.2	741.4	742.7	743.5	743.6	743.9
142.5°	769.6	768.7	767.7	766.7	767.7	768.7	769.6	770.6	771.3	771.4	771.6
145°	810.8	810.1	809.3	808.6	809.3	810.1	810.8	811.5	812.0	812.2	812.4
147.5°	849.3	848.2	847.1	846.0	847.1	848.2	849.3	850.4	850.9	850.9	850.9
150°	873.1	872.0	870.9	869.8	870.9	872.0	873.1	874.2	874.7	874.7	874.7
152.5°	895.8	894.8	893.8	892.9	893.8	894.8	895.8	896.7	897.1	896.7	896.4
155°	928.1	926.8	925.6	924.3	925.6	926.8	928.1	929.4	929.7	929.0	928.2
157.5°	955.9	955.0	953.9	952.8	953.9	955.0	955.9	957.0	957.1	956.3	955.5
160°	973.5	972.8	972.1	971.3	972.1	972.8	973.5	974.3	974.2	973.3	972.4
162.5°	988.8	987.6	986.4	985.2	986.4	987.6	988.8	989.9	990.1	989.1	988.2
165°	1009.1	1007.8	1006.5	1005.3	1006.5	1007.8	1009.1	1010.4	1010.5	1009.3	1008.3
167.5°	1025.6	1024.5	1023.4	1022.2	1023.4	1024.5	1025.6	1026.8	1026.8	1025.6	1024.5
170°	1034.7	1033.4	1032.1	1030.9	1032.1	1033.4	1034.7	1036.0	1036.0	1034.7	1033.4
172.5°	1041.3	1040.0	1038.7	1037.5	1038.7	1040.0	1041.3	1042.6	1042.7	1041.5	1040.4
175°	1048.7	1047.4	1046.2	1044.9	1046.2	1047.4	1048.7	1050.0	1050.1	1049.0	1047.9
177.5°	1051.9	1050.9	1049.9	1048.9	1049.9	1050.9	1051.9	1053.0	1053.0	1052.1	1051.2
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1237.1	1243.2	1249.5	1255.2	1264.1	1268.1	1273.9	1276.1	1282.8	1292.6	1300.6
5°	1161.8	1170.7	1182.3	1191.8	1206.8	1218.4	1231.2	1243.4	1257.8	1278.3	1296.7
7.5°	1098.0	1106.8	1120.8	1138.3	1154.9	1171.3	1188.8	1205.4	1226.0	1255.5	1284.7
10°	1055.9	1066.4	1083.0	1101.9	1122.4	1138.6	1159.0	1180.1	1205.7	1239.5	1274.5
12.5°	1019.5	1027.4	1046.7	1064.6	1087.9	1108.3	1128.5	1153.1	1182.1	1218.2	1260.3
15°	961.6	972.7	991.5	1011.5	1035.9	1057.5	1083.6	1113.5	1141.8	1186.3	1237.3
17.5°	903.4	920.2	939.9	962.5	980.5	1010.3	1038.7	1069.4	1104.2	1151.3	1207.3
20°	866.1	879.4	897.7	930.5	954.3	977.1	1003.1	1041.5	1073.6	1126.9	1185.1
22.5°	834.6	844.3	864.9	891.9	919.7	946.0	972.5	1009.0	1048.7	1099.3	1162.5
25°	787.9	803.4	819.0	838.4	868.3	899.9	928.8	959.9	1002.0	1055.9	1124.1
27.5°	742.2	756.4	771.7	795.5	818.2	847.8	878.0	913.6	958.9	1015.8	1085.0
30°	713.0	723.5	737.9	768.4	789.0	814.5	850.0	881.7	923.8	984.3	1057.5
32.5°	682.8	696.4	712.2	735.6	761.0	785.2	817.6	851.9	895.0	954.6	1029.6
35°	639.8	655.8	671.9	689.1	714.6	739.6	766.8	804.5	848.3	906.0	979.8
37.5°	600.1	613.1	626.1	647.5	671.7	695.5	720.8	758.0	799.3	861.5	929.3
40°	574.8	586.4	596.5	618.6	642.0	667.5	692.4	725.2	769.6	827.9	893.3
42.5°	547.3	558.1	571.6	589.8	614.9	636.4	661.4	692.4	734.0	793.2	850.7
45°	506.0	518.2	529.9	547.1	572.0	593.1	615.3	644.7	687.5	736.3	787.3
47.5°	463.1	475.2	488.6	505.2	527.0	548.4	570.6	596.6	635.6	683.5	718.0
50°	435.5	445.6	458.9	475.5	495.5	518.2	538.2	566.5	603.6	641.4	671.3
52.5°	407.2	416.2	431.3	448.9	467.5	487.1	508.4	532.7	566.4	601.9	625.7
55°	362.9	374.0	386.7	403.9	422.2	438.9	459.4	484.4	511.0	537.6	553.8
57.5°	321.5	330.7	341.4	359.2	375.0	394.9	413.4	432.8	457.4	477.5	488.0
60°	291.3	299.6	313.5	329.1	344.0	361.2	382.3	401.7	420.5	436.7	445.0
62.5°	262.9	272.6	284.6	298.8	315.1	331.5	349.8	366.2	382.9	396.7	402.4
65°	225.8	233.6	242.5	255.8	269.1	285.8	300.2	316.8	329.1	336.8	341.8
67.5°	192.1	197.2	204.0	212.9	225.9	240.4	254.5	267.4	277.6	283.0	287.4
70°	170.3	173.7	178.6	187.5	197.5	210.3	224.7	234.2	243.0	247.4	251.9
72.5°	148.5	152.8	157.4	164.4	172.7	181.9	192.3	204.0	208.9	214.2	216.9
75°	112.6	118.7	124.8	129.3	134.9	142.0	151.5	158.7	161.4	165.9	166.5
77.5°	85.0	86.3	90.7	96.3	101.0	106.2	112.2	118.6	119.9	122.3	123.8
80°	69.9	69.9	69.9	73.2	78.8	82.7	88.2	91.6	93.8	94.3	94.9
82.5°	56.2	56.2	55.7	56.3	58.4	60.5	65.6	69.4	71.1	70.8	69.5
85°	36.6	35.5	35.5	35.0	35.5	34.4	33.8	36.0	39.4	39.4	38.3
87.5°	19.2	18.6	18.6	17.7	16.7	15.8	14.0	14.1	13.8	15.2	14.3
90°	20.5	19.8	17.4	15.1	12.6	10.3	8.2	6.4	4.5	2.7	0.8
92.5°	32.3	31.7	30.3	29.0	27.6	26.3	24.9	23.7	22.5	21.2	20.0
95°	61.9	61.1	59.7	58.2	56.7	55.3	53.9	52.6	51.3	50.0	48.8
97.5°	96.5	95.6	94.6	93.5	92.5	91.4	90.4	89.4	88.5	87.5	86.6
100°	122.0	121.4	120.5	119.6	118.7	117.7	116.8	115.6	114.5	113.4	112.3
102.5°	151.1	150.5	149.3	148.1	146.8	145.6	144.7	144.1	143.4	142.8	142.1
105°	194.9	194.9	193.3	191.6	190.0	188.3	187.4	186.9	186.6	186.2	185.9
107.5°	241.2	240.7	240.0	239.4	238.7	238.1	237.6	237.4	237.2	236.9	236.8
110°	272.5	271.7	271.4	271.0	270.7	270.3	269.9	269.5	269.2	268.8	268.5



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	303.7	302.8	302.7	302.6	302.6	302.5	302.4	302.1	301.9	301.7	301.5
115°	352.0	351.9	352.2	352.6	352.9	353.4	353.3	352.7	352.1	351.6	351.1
117.5°	400.4	400.5	400.9	401.4	401.9	402.4	402.4	402.0	401.7	401.3	401.0
120°	432.6	432.8	433.7	434.6	435.5	436.5	436.4	435.3	434.2	433.1	432.0
122.5°	465.4	465.9	466.4	466.8	467.3	467.7	467.6	466.8	466.0	465.2	464.4
125°	513.9	514.6	514.9	515.4	515.7	516.1	516.0	515.4	514.9	514.3	513.8
127.5°	561.8	562.8	563.2	563.6	564.0	564.4	564.0	562.9	561.7	560.5	559.4
130°	593.1	593.9	594.4	595.0	595.6	596.1	595.7	594.2	592.7	591.3	589.8
132.5°	624.0	624.9	625.3	625.7	626.1	626.6	626.1	624.6	623.1	621.6	620.1
135°	669.9	670.7	670.9	671.1	671.2	671.4	671.0	669.8	668.8	667.6	666.6
137.5°	715.0	715.8	715.3	714.9	714.4	713.9	713.2	712.2	711.3	710.5	709.6
140°	744.0	744.2	744.0	743.9	743.6	743.5	742.9	742.0	741.1	740.2	739.2
142.5°	771.8	772.0	771.7	771.3	770.9	770.6	770.1	769.1	768.2	767.3	766.4
145°	812.6	812.8	812.2	811.7	811.1	810.6	810.1	809.8	809.3	809.0	808.6
147.5°	850.9	850.9	850.4	849.9	849.4	848.9	848.3	847.7	846.9	846.3	845.6
150°	874.7	874.7	874.3	874.0	873.6	873.3	872.9	872.5	872.1	871.8	871.4
152.5°	896.2	895.9	895.7	895.4	895.2	895.0	894.6	894.1	893.6	893.1	892.6
155°	927.5	926.8	926.6	926.4	926.2	926.0	925.9	925.9	925.9	925.9	925.9
157.5°	954.8	954.0	953.9	953.7	953.6	953.4	953.5	953.7	953.9	954.1	954.4
160°	971.4	970.5	970.5	970.5	970.5	970.5	970.7	971.1	971.4	971.8	972.2
162.5°	987.3	986.4	986.3	986.1	985.9	985.8	986.0	986.5	987.0	987.6	988.1
165°	1007.1	1006.1	1006.1	1006.1	1006.1	1006.1	1006.3	1006.9	1007.5	1008.0	1008.5
167.5°	1023.4	1022.2	1022.1	1022.0	1021.8	1021.7	1022.0	1022.7	1023.4	1024.2	1024.9
170°	1032.1	1030.9	1030.9	1030.9	1030.9	1030.9	1031.2	1031.9	1032.7	1033.4	1034.1
172.5°	1039.3	1038.1	1038.1	1038.1	1038.1	1038.1	1038.4	1039.2	1039.9	1040.6	1041.4
175°	1046.8	1045.7	1045.7	1045.7	1045.7	1045.7	1046.1	1046.8	1047.6	1048.3	1049.0
177.5°	1050.4	1049.5	1049.5	1049.5	1049.5	1049.5	1049.8	1050.4	1051.0	1051.6	1052.1
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1303.2	1308.1	1314.3	1323.6	1330.7	1336.9	1338.2	1340.0	1344.5	1352.0	1357.8
5°	1311.7	1324.4	1344.9	1364.9	1386.6	1404.3	1420.9	1432.6	1443.7	1467.0	1485.9
7.5°	1309.0	1337.4	1369.5	1405.4	1441.7	1476.8	1509.5	1538.7	1567.7	1601.7	1640.5
10°	1307.2	1340.5	1383.7	1429.8	1480.3	1529.7	1577.4	1614.6	1657.8	1696.7	1746.0
12.5°	1298.8	1346.7	1398.4	1457.3	1519.4	1576.3	1639.1	1690.4	1740.0	1796.1	1853.5
15°	1287.8	1346.1	1411.5	1489.7	1584.0	1652.9	1717.2	1806.5	1867.6	1928.6	2010.8
17.5°	1267.7	1338.8	1420.6	1522.2	1600.9	1693.4	1790.2	1860.8	1943.0	2029.0	2103.4
20°	1251.7	1334.4	1426.0	1525.8	1626.2	1726.6	1820.4	1904.8	1989.7	2089.0	2150.0
22.5°	1235.7	1317.5	1412.6	1518.7	1626.7	1732.4	1838.6	1937.6	2033.1	2133.3	2211.3
25°	1201.8	1298.9	1402.1	1510.3	1616.8	1733.3	1859.8	1970.3	2088.4	2191.6	2265.4
27.5°	1167.3	1256.4	1359.1	1468.8	1587.3	1725.0	1873.8	1999.3	2117.7	2191.6	2214.8
30°	1136.3	1230.6	1324.9	1436.5	1564.6	1718.3	1876.5	2020.1	2117.3	2149.5	2125.6
32.5°	1104.8	1190.3	1283.7	1397.8	1534.0	1701.9	1880.0	2007.8	2066.2	2041.6	1944.5
35°	1049.2	1126.3	1216.8	1331.1	1487.5	1692.8	1865.4	1951.9	1937.5	1798.8	1615.7
37.5°	989.7	1052.6	1136.3	1255.8	1439.3	1656.8	1802.3	1815.1	1690.3	1477.3	1265.8
40°	942.6	999.2	1085.2	1210.1	1402.1	1621.2	1738.9	1687.3	1493.6	1256.7	1080.3
42.5°	896.9	944.7	1027.5	1162.1	1366.6	1572.9	1644.3	1531.9	1308.6	1084.5	924.1
45°	819.5	864.5	947.6	1085.8	1293.9	1480.3	1470.9	1275.5	1052.0	871.6	738.5
47.5°	746.0	785.3	863.4	1004.4	1208.5	1341.6	1253.4	1045.5	855.9	711.2	616.2
50°	694.1	733.0	810.7	949.9	1140.2	1237.3	1111.3	911.0	737.4	617.5	542.1
52.5°	644.4	682.3	753.3	889.1	1057.6	1115.7	980.4	794.8	650.0	546.5	481.7
55°	574.8	603.6	667.5	797.3	923.2	936.5	799.5	644.2	524.9	452.7	408.4
57.5°	503.9	528.7	591.8	695.2	783.5	776.7	646.7	512.3	432.0	378.4	346.3
60°	457.7	482.2	537.6	626.4	693.0	669.7	550.4	442.2	373.4	334.0	308.5
62.5°	414.7	433.7	485.7	550.5	598.4	572.0	470.5	381.0	326.4	293.2	273.0
65°	352.3	367.9	409.4	443.3	469.9	444.4	360.1	297.9	258.5	235.2	221.4
67.5°	293.1	303.0	329.2	341.4	360.2	332.2	270.8	229.2	206.8	187.1	177.4
70°	255.8	263.0	276.9	286.8	291.9	263.0	217.5	186.9	168.1	154.3	148.1
72.5°	218.5	224.9	227.6	235.8	233.3	206.2	174.9	150.6	137.1	127.6	119.8
75°	167.0	169.7	167.0	163.7	156.5	137.6	115.9	103.8	93.8	89.4	86.6
77.5°	121.7	120.8	117.1	111.9	99.5	87.6	76.0	71.9	67.6	65.2	64.2
80°	93.8	91.6	88.2	79.9	69.4	61.1	58.3	55.5	53.8	51.0	50.5
82.5°	69.8	68.5	62.9	55.9	48.5	44.6	42.3	41.3	39.6	38.2	38.1
85°	37.2	35.5	29.4	25.5	24.4	23.3	22.7	22.7	20.5	20.0	20.0
87.5°	12.6	10.2	10.1	9.2	9.6	9.2	10.1	9.7	9.7	10.4	9.6
90°	2.7	4.5	6.4	8.2	10.3	12.6	15.1	17.4	19.8	20.5	21.3
92.5°	21.2	22.5	23.7	24.9	26.3	27.6	29.0	30.3	31.7	32.3	32.9
95°	50.0	51.3	52.6	53.9	55.3	56.7	58.2	59.7	61.1	61.9	62.6
97.5°	87.5	88.5	89.4	90.4	91.4	92.5	93.5	94.6	95.6	96.5	97.3
100°	113.4	114.5	115.6	116.8	117.7	118.7	119.6	120.5	121.4	122.0	122.5
102.5°	142.8	143.4	144.1	144.7	145.6	146.8	148.1	149.3	150.5	151.1	151.6
105°	186.2	186.6	186.9	187.4	188.3	190.0	191.6	193.3	194.9	194.9	194.9
107.5°	236.9	237.2	237.4	237.6	238.1	238.7	239.4	240.0	240.7	241.2	241.9
110°	268.8	269.2	269.5	269.9	270.3	270.7	271.0	271.4	271.7	272.5	273.2



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	301.7	301.9	302.1	302.4	302.5	302.6	302.6	302.7	302.8	303.7	304.6
115°	351.6	352.1	352.7	353.3	353.4	352.9	352.6	352.2	351.9	352.0	352.2
117.5°	401.3	401.7	402.0	402.4	402.4	401.9	401.4	400.9	400.5	400.4	400.4
120°	433.1	434.2	435.3	436.4	436.5	435.5	434.6	433.7	432.8	432.6	432.4
122.5°	465.2	466.0	466.8	467.6	467.7	467.3	466.8	466.4	465.9	465.4	464.9
125°	514.3	514.9	515.4	516.0	516.1	515.7	515.4	514.9	514.6	513.9	513.1
127.5°	560.5	561.7	562.9	564.0	564.4	564.0	563.6	563.2	562.8	561.8	560.8
130°	591.3	592.7	594.2	595.7	596.1	595.6	595.0	594.4	593.9	593.1	592.4
132.5°	621.6	623.1	624.6	626.1	626.6	626.1	625.7	625.3	624.9	624.0	623.2
135°	667.6	668.8	669.8	671.0	671.4	671.2	671.1	670.9	670.7	669.9	669.2
137.5°	710.5	711.3	712.2	713.2	713.9	714.4	714.9	715.3	715.8	715.0	714.3
140°	740.2	741.1	742.0	742.9	743.5	743.6	743.9	744.0	744.2	744.0	743.9
142.5°	767.3	768.2	769.1	770.1	770.6	770.9	771.3	771.7	772.0	771.8	771.6
145°	809.0	809.3	809.8	810.1	810.6	811.1	811.7	812.2	812.8	812.6	812.4
147.5°	846.3	846.9	847.7	848.3	848.9	849.4	849.9	850.4	850.9	850.9	850.9
150°	871.8	872.1	872.5	872.9	873.3	873.6	874.0	874.3	874.7	874.7	874.7
152.5°	893.1	893.6	894.1	894.6	895.0	895.2	895.4	895.7	895.9	896.2	896.4
155°	925.9	925.9	925.9	925.9	926.0	926.2	926.4	926.6	926.8	927.5	928.2
157.5°	954.1	953.9	953.7	953.5	953.4	953.6	953.7	953.9	954.0	954.8	955.5
160°	971.8	971.4	971.1	970.7	970.5	970.5	970.5	970.5	970.5	971.4	972.4
162.5°	987.6	987.0	986.5	986.0	985.8	985.9	986.1	986.3	986.4	987.3	988.2
165°	1008.0	1007.5	1006.9	1006.3	1006.1	1006.1	1006.1	1006.1	1006.1	1007.1	1008.3
167.5°	1024.2	1023.4	1022.7	1022.0	1021.7	1021.8	1022.0	1022.1	1022.2	1023.4	1024.5
170°	1033.4	1032.7	1031.9	1031.2	1030.9	1030.9	1030.9	1030.9	1030.9	1032.1	1033.4
172.5°	1040.6	1039.9	1039.2	1038.4	1038.1	1038.1	1038.1	1038.1	1038.1	1039.3	1040.4
175°	1048.3	1047.6	1046.8	1046.1	1045.7	1045.7	1045.7	1045.7	1045.7	1046.8	1047.9
177.5°	1051.6	1051.0	1050.4	1049.8	1049.5	1049.5	1049.5	1049.5	1049.5	1050.4	1051.2
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1	1296.1
2.5°	1367.1	1367.1	1368.9	1375.6	1376.5	1382.2	1380.5
5°	1502.5	1513.0	1516.9	1533.6	1543.5	1548.0	1539.1
7.5°	1668.1	1697.8	1711.9	1729.3	1744.7	1749.4	1737.3
10°	1788.8	1819.8	1845.9	1862.1	1877.0	1887.0	1899.7
12.5°	1905.5	1943.7	1968.5	1991.2	2006.6	2019.3	2021.4
15°	2032.4	2090.1	2133.9	2166.1	2182.1	2190.5	2187.2
17.5°	2160.3	2213.8	2245.0	2277.9	2300.1	2301.3	2301.9
20°	2232.7	2284.8	2320.9	2345.3	2370.2	2369.2	2374.7
22.5°	2281.0	2322.1	2349.8	2367.5	2376.0	2371.8	2372.9
25°	2303.7	2315.9	2310.9	2282.6	2275.4	2249.3	2253.7
27.5°	2187.0	2129.2	2069.6	1992.8	1932.2	1883.7	1886.2
30°	2028.5	1926.4	1809.9	1712.2	1624.6	1600.2	1548.0
32.5°	1807.0	1653.8	1517.4	1426.4	1351.1	1330.7	1285.2
35°	1431.5	1282.8	1142.4	1058.1	1024.7	978.2	977.6
37.5°	1112.6	981.7	907.5	844.2	811.1	782.9	780.1
40°	936.0	833.9	777.9	732.4	699.7	678.6	673.6
42.5°	812.6	730.0	677.6	649.4	624.2	613.3	605.2
45°	663.6	608.1	571.4	545.9	534.3	525.9	521.5
47.5°	555.1	517.9	492.9	476.0	466.5	457.7	460.1
50°	496.0	465.5	447.2	431.1	423.9	417.8	418.3
52.5°	448.5	421.1	406.3	394.7	385.7	381.4	379.3
55°	380.6	363.4	348.5	340.1	335.1	329.1	327.3
57.5°	324.7	311.4	299.1	289.8	288.5	282.7	283.4
60°	287.4	276.3	266.4	261.3	257.5	252.4	254.1
62.5°	256.8	247.4	238.4	234.2	230.4	226.7	227.5
65°	210.3	201.4	195.8	193.6	192.0	190.3	188.7
67.5°	167.5	162.2	158.7	153.9	150.5	149.9	148.2
70°	141.0	133.7	127.6	121.5	119.8	119.3	119.8
72.5°	113.0	108.4	106.7	103.8	103.5	102.0	103.0
75°	84.9	83.2	82.1	79.9	79.9	79.9	79.9
77.5°	62.6	61.6	60.9	60.5	59.9	59.1	59.0
80°	48.8	48.3	47.1	47.1	46.6	47.1	46.6
82.5°	36.9	36.8	35.6	35.6	35.1	34.7	35.1
85°	18.8	18.3	19.4	18.3	18.8	17.8	18.8
87.5°	9.7	9.9	9.5	9.6	9.2	10.2	9.4
90°	22.0	22.7	23.3	23.6	24.1	24.4	24.8
92.5°	33.5	34.1	34.2	34.0	33.8	33.6	33.3
95°	63.3	64.1	64.4	64.4	64.4	64.4	64.4
97.5°	98.2	99.1	99.4	99.3	99.3	99.2	99.1
100°	123.1	123.6	124.1	124.4	124.8	125.1	125.6
102.5°	152.1	152.7	153.0	152.9	152.8	152.7	152.6
105°	194.9	194.9	195.1	195.5	195.8	196.2	196.6
107.5°	242.5	243.0	243.2	243.0	242.8	242.6	242.3
110°	273.9	274.7	274.8	274.5	274.1	273.8	273.4



TEST NUMBER: P332459-930

CATALOG NUMBER: S123RDIW-S1000D1030U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	305.4	306.3	306.7	306.6	306.6	306.6	306.5
115°	352.5	352.6	352.6	352.5	352.2	352.0	351.9
117.5°	400.3	400.3	400.0	399.5	399.0	398.4	397.9
120°	432.3	432.1	431.8	431.5	431.0	430.7	430.3
122.5°	464.4	464.0	463.4	462.9	462.4	461.9	461.4
125°	512.4	511.7	510.9	510.2	509.5	508.7	508.0
127.5°	559.8	558.7	557.7	556.9	556.1	555.2	554.4
130°	591.7	590.9	590.0	588.6	587.3	586.1	584.8
132.5°	622.3	621.4	620.5	619.5	618.5	617.5	616.5
135°	668.5	667.7	667.2	666.8	666.5	666.1	665.8
137.5°	713.5	712.7	712.0	711.3	710.6	709.9	709.2
140°	743.6	743.5	742.7	741.4	740.2	738.9	737.6
142.5°	771.4	771.3	770.6	769.6	768.7	767.7	766.7
145°	812.2	812.0	811.5	810.8	810.1	809.3	808.6
147.5°	850.9	850.9	850.4	849.3	848.2	847.1	846.0
150°	874.7	874.7	874.2	873.1	872.0	870.9	869.8
152.5°	896.7	897.1	896.7	895.8	894.8	893.8	892.9
155°	929.0	929.7	929.4	928.1	926.8	925.6	924.3
157.5°	956.3	957.1	957.0	955.9	955.0	953.9	952.8
160°	973.3	974.2	974.3	973.5	972.8	972.1	971.3
162.5°	989.1	990.1	989.9	988.8	987.6	986.4	985.2
165°	1009.3	1010.5	1010.4	1009.1	1007.8	1006.5	1005.3
167.5°	1025.6	1026.8	1026.8	1025.6	1024.5	1023.4	1022.2
170°	1034.7	1036.0	1036.0	1034.7	1033.4	1032.1	1030.9
172.5°	1041.5	1042.7	1042.6	1041.3	1040.0	1038.7	1037.5
175°	1049.0	1050.1	1050.0	1048.7	1047.4	1046.2	1044.9
177.5°	1052.1	1053.0	1053.0	1051.9	1050.9	1049.9	1048.9
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5

(END OF REPORT)