

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331818-940

Luminaire Tested: **S122RDIW-S675D1240U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331818-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1240U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6100.6 lumens
Efficiency: N/A
Efficacy: 99.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37								
1	95	91	88	85	86	83	80	77	68	65	64	53	52	51	40	39	38	32								
2	87	81	75	70	79	73	69	64	60	56	54	47	45	43	36	35	33	28								
3	80	71	64	59	73	65	59	55	53	49	46	43	40	37	32	31	29	25								
4	74	63	56	50	67	58	52	47	48	43	40	38	35	32	29	27	26	22								
5	68	57	49	44	61	52	45	41	43	38	34	35	31	29	27	25	23	19								
6	63	51	44	38	57	47	40	36	39	34	30	32	28	25	25	22	20	17								
7	58	46	39	34	53	43	36	31	36	31	27	29	25	23	23	20	18	16								
8	54	42	35	30	49	39	32	28	33	28	24	27	23	20	21	19	17	14								
9	50	39	32	27	46	36	29	25	30	25	22	25	21	19	20	17	15	13								
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14	12								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21151	21151	21151	21151
5°	23622	21284	18870	21284
10°	26209	21135	16357	21135
15°	27497	20824	12889	20824
20°	23838	20366	11153	20366
25°	15634	19737	9957	19737
30°	10524	18975	9012	18975
35°	8523	18015	8129	18015
40°	7579	16971	7522	16971
45°	6859	15746	6715	15746
50°	6242	14531	6219	14531
55°	5869	13185	5790	13185
60°	4908	11951	4850	11951
65°	4138	10850	4695	10850
70°	3829	9692	4428	9692
75°	3575	8434	4086	8434
80°	3301	6936	3636	6936
85°	3038	5483	3205	5483



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	2.0
10°-20°	346.0	5.7
20°-30°	445.9	7.3
30°-40°	423.7	6.9
40°-50°	363.0	6.0
50°-60°	276.4	4.5
60°-70°	174.7	2.9
70°-80°	87.3	1.4
80°-90°	28.2	0.5
90°-100°	86.8	1.4
100°-110°	269.6	4.4
110°-120°	460.9	7.6
120°-130°	606.1	9.9
130°-140°	680.3	11.2
140°-150°	667.1	10.9
150°-160°	559.5	9.2
160°-170°	371.1	6.1
170°-180°	129.7	2.1
0°-30°	916.1	15.0
0°-40°	1339.8	22.0
0°-60°	1979.2	32.4
0°-90°	2269.4	37.2
90°-120°	817.4	13.4
90°-150°	2770.9	45.4
90°-180°	3831.0	62.8
0°-180°	6100.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1310	1310	1310	1310	1310	
5°	1458	1313	1164	1313	1458	144
15°	1645	1246	771	1246	1645	444
25°	878	1108	559	1108	878	416
35°	432	914	412	914	432	277
45°	300	690	294	690	300	232
55°	208	468	206	468	208	183
65°	108	284	123	284	108	110
75°	57	135	66	135	57	61
85°	16	30	17	30	16	19
90°	39	1	39	1	39	18
95°	72	60	72	60	72	80
105°	257	249	257	249	257	270
115°	462	462	462	462	462	457
125°	675	673	675	673	675	602
135°	881	871	881	871	881	678
145°	1068	1057	1068	1057	1068	667
155°	1218	1208	1218	1208	1218	560
165°	1316	1315	1316	1315	1316	371
175°	1363	1368	1363	1368	1363	130
180°	1370	1370	1370	1370	1370	



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1363.2	1364.2	1365.4	1362.8	1362.8	1360.6	1355.8	1352.3	1342.0	1340.6	1340.6
5°	1457.5	1456.5	1458.4	1452.5	1444.3	1442.4	1433.8	1422.5	1410.6	1397.4	1394.6
7.5°	1551.2	1549.9	1546.2	1545.2	1538.9	1525.2	1511.3	1496.5	1476.8	1457.6	1448.0
10°	1598.6	1613.6	1604.5	1588.6	1591.8	1570.4	1559.0	1539.4	1523.0	1494.3	1488.0
12.5°	1645.2	1651.1	1648.2	1639.1	1635.0	1620.2	1604.9	1587.9	1557.6	1531.9	1509.5
15°	1645.0	1653.7	1655.9	1653.2	1655.5	1654.6	1646.4	1632.3	1605.9	1577.6	1553.1
17.5°	1523.6	1529.6	1544.5	1554.6	1567.4	1594.3	1607.6	1612.7	1608.8	1592.8	1575.5
20°	1387.4	1377.3	1419.2	1440.6	1458.8	1504.3	1543.5	1558.5	1582.6	1582.2	1577.6
22.5°	1194.4	1196.8	1236.4	1261.9	1315.0	1360.5	1405.2	1461.7	1508.3	1539.2	1557.3
25°	877.6	894.9	934.5	969.1	1028.2	1112.9	1189.8	1279.1	1363.2	1429.7	1493.0
27.5°	659.1	660.4	691.8	723.7	758.8	828.2	925.1	1031.6	1151.6	1250.7	1364.7
30°	564.5	561.7	574.9	594.5	624.5	678.2	751.0	855.8	975.4	1124.7	1257.7
32.5°	497.4	497.6	507.6	522.0	547.0	583.2	633.0	718.1	831.3	978.0	1133.8
35°	432.4	431.9	439.3	449.7	460.2	483.4	517.5	562.1	640.0	776.9	936.3
37.5°	385.8	387.8	391.4	397.9	409.5	422.4	442.9	472.9	528.2	609.3	743.2
40°	359.6	360.5	365.5	371.0	377.8	387.8	404.7	428.7	469.3	534.0	631.8
42.5°	335.6	336.4	340.0	345.1	350.4	360.5	374.4	395.3	428.1	478.6	559.3
45°	300.4	300.4	303.6	305.9	311.8	320.9	332.3	349.6	372.4	409.7	463.3
47.5°	267.4	267.5	269.7	273.6	277.3	284.4	295.6	309.7	326.3	355.2	401.0
50°	248.5	249.0	250.3	253.5	255.8	262.2	270.8	283.1	300.4	322.7	361.0
52.5°	233.3	232.9	234.7	236.0	237.6	242.2	248.6	259.5	274.9	294.4	326.0
55°	208.5	206.6	209.4	211.7	213.0	214.8	218.5	225.3	238.5	254.9	278.6
57.5°	177.5	176.8	178.7	180.8	185.1	190.0	193.1	197.4	204.3	216.1	239.5
60°	152.0	152.0	156.1	157.5	162.5	168.9	175.2	178.9	185.7	193.4	210.7
62.5°	129.5	129.8	131.7	133.1	135.9	143.7	152.7	160.7	167.1	174.5	186.0
65°	108.3	109.2	109.2	110.1	112.0	113.8	117.4	123.8	135.2	145.6	154.3
67.5°	91.9	92.2	92.5	93.4	93.9	95.9	97.3	100.1	102.8	112.7	123.4
70°	81.1	82.4	81.9	82.8	83.3	84.2	86.1	87.4	91.5	93.8	100.1
72.5°	70.8	71.8	71.7	72.3	73.5	73.7	75.1	76.5	79.1	81.1	84.4
75°	57.3	56.9	57.3	58.2	58.7	59.2	59.2	61.0	62.3	64.2	66.4
77.5°	44.2	44.7	44.6	44.7	44.8	45.6	45.5	46.4	47.7	48.6	49.7
80°	35.5	35.9	35.5	35.9	36.4	36.8	36.4	36.8	38.3	39.1	39.1
82.5°	27.5	27.6	27.8	27.9	28.0	28.1	28.8	28.9	29.9	29.7	30.1
85°	16.4	16.0	16.0	16.0	16.4	16.9	16.4	16.4	16.9	16.9	16.9
87.5°	13.7	14.0	13.9	13.9	13.8	13.9	14.0	14.4	14.2	14.6	13.2
90°	39.3	39.1	38.8	38.5	38.3	38.4	39.0	39.4	39.9	40.5	34.8
92.5°	37.5	37.5	37.4	37.3	37.3	37.2	37.1	37.0	36.8	36.7	35.4
95°	71.7	72.2	72.7	73.2	73.7	74.0	74.0	74.0	74.0	74.0	73.5
97.5°	124.2	124.2	124.3	124.3	124.4	124.4	124.4	124.4	124.4	124.4	123.4
100°	158.4	158.6	158.9	159.2	159.4	159.5	159.5	159.5	159.5	159.5	158.8
102.5°	197.2	197.5	197.8	198.0	198.3	198.3	198.1	197.9	197.7	197.5	196.5
105°	256.7	256.7	256.7	256.7	256.7	256.5	255.9	255.4	254.9	254.4	253.9
107.5°	312.6	313.8	315.0	316.2	317.4	317.9	317.6	317.4	317.3	317.0	317.0
110°	356.1	356.9	357.7	358.5	359.2	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	397.7	398.3	398.9	399.4	400.0	400.6	401.2	401.8	402.4	403.1	403.2
115°	462.5	463.2	464.0	464.8	465.6	466.1	466.4	466.6	466.9	467.1	467.6
117.5°	524.2	525.0	525.8	526.6	527.4	528.0	528.6	529.2	529.9	530.5	531.9
120°	567.8	568.5	569.3	570.0	570.8	571.1	571.1	571.1	571.1	571.1	573.2
122.5°	610.3	610.8	611.4	612.0	612.5	613.1	613.8	614.4	614.9	615.5	617.0
125°	675.2	675.5	675.7	676.0	676.3	676.8	677.5	678.3	679.1	679.8	680.6
127.5°	734.4	735.3	736.1	736.9	737.7	738.6	739.5	740.5	741.4	742.3	743.2
130°	776.9	778.0	779.1	780.1	781.1	781.9	782.4	782.9	783.4	783.9	784.4
132.5°	817.7	818.5	819.3	820.2	821.0	822.0	823.0	824.2	825.4	826.4	826.3
135°	881.0	881.8	882.6	883.3	884.1	884.7	884.9	885.2	885.4	885.6	885.2
137.5°	938.4	939.4	940.5	941.5	942.5	943.2	943.3	943.5	943.8	944.0	943.3
140°	978.2	979.2	980.3	981.2	982.3	982.8	982.8	982.8	982.8	982.8	981.5
142.5°	1014.2	1015.3	1016.3	1017.4	1018.3	1018.8	1018.6	1018.3	1018.2	1018.0	1017.1
145°	1068.4	1069.4	1070.4	1071.5	1072.5	1072.8	1072.6	1072.4	1072.1	1071.8	1070.3
147.5°	1116.7	1117.7	1118.7	1119.6	1120.6	1120.8	1120.3	1119.6	1119.1	1118.6	1117.5
150°	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2	1147.1
152.5°	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8	1176.5
155°	1217.5	1218.3	1219.1	1219.9	1220.6	1220.3	1219.1	1217.8	1216.5	1215.2	1214.4
157.5°	1251.7	1252.9	1254.2	1255.4	1256.7	1256.4	1254.6	1252.9	1251.2	1249.5	1248.9
160°	1273.0	1274.1	1275.1	1276.1	1277.1	1276.8	1275.3	1273.8	1272.2	1270.7	1270.4
162.5°	1291.6	1292.7	1294.0	1295.2	1296.5	1296.2	1294.4	1292.7	1290.9	1289.2	1289.0
165°	1315.8	1317.1	1318.4	1319.6	1320.9	1320.7	1318.8	1317.1	1315.3	1313.5	1313.5
167.5°	1335.7	1337.0	1338.4	1339.7	1341.0	1340.8	1339.0	1337.2	1335.4	1333.6	1333.6
170°	1345.9	1347.4	1349.0	1350.5	1352.0	1351.9	1350.1	1348.3	1346.5	1344.7	1345.0
172.5°	1354.2	1355.8	1357.3	1358.8	1360.3	1360.2	1358.4	1356.6	1354.9	1353.0	1353.3
175°	1363.2	1364.8	1366.3	1367.8	1369.4	1369.2	1367.4	1365.7	1363.9	1362.0	1362.5
177.5°	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3	1367.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1341.3	1338.4	1335.9	1329.3	1326.1	1318.8	1317.7	1317.3	1307.8	1298.7	1296.2
5°	1387.4	1380.1	1369.1	1356.4	1343.2	1329.5	1320.4	1313.2	1294.9	1277.6	1267.7
7.5°	1433.8	1418.2	1399.3	1375.2	1355.0	1332.5	1315.7	1300.7	1274.9	1250.1	1233.4
10°	1468.4	1442.9	1417.9	1384.6	1358.7	1333.2	1309.6	1289.1	1259.9	1227.2	1203.9
12.5°	1489.9	1461.9	1427.4	1394.8	1361.3	1328.8	1297.2	1270.9	1236.6	1202.7	1175.2
15°	1518.9	1488.9	1447.0	1400.6	1357.4	1315.0	1278.6	1245.8	1201.2	1160.7	1127.0
17.5°	1542.7	1501.4	1456.3	1402.7	1352.6	1298.8	1251.9	1210.1	1160.4	1111.5	1071.8
20°	1550.3	1509.4	1457.5	1403.7	1344.6	1281.3	1230.8	1185.3	1132.0	1078.8	1033.2
22.5°	1545.6	1513.8	1456.0	1391.8	1331.1	1264.9	1207.8	1155.0	1096.0	1041.6	988.8
25°	1513.5	1502.5	1448.0	1377.8	1308.7	1231.7	1165.7	1107.9	1040.5	982.3	924.9
27.5°	1438.5	1462.1	1428.3	1353.6	1276.7	1194.2	1120.0	1054.2	984.3	918.7	861.6
30°	1366.5	1420.6	1406.0	1336.9	1250.8	1169.8	1086.5	1017.8	943.2	875.7	819.3
32.5°	1267.7	1357.3	1371.5	1313.6	1224.6	1135.6	1048.3	979.9	902.0	831.0	776.0
35°	1110.6	1244.5	1305.9	1269.0	1179.8	1083.8	993.6	914.0	835.7	765.6	711.0
37.5°	923.2	1105.5	1207.8	1210.5	1128.5	1028.7	930.6	851.5	771.3	702.5	643.5
40°	801.6	999.1	1132.5	1162.1	1092.9	985.0	885.7	805.2	726.9	659.5	591.7
42.5°	692.3	889.1	1053.1	1104.6	1049.5	942.4	842.8	758.6	682.5	618.8	549.5
45°	559.9	731.9	912.7	1004.6	974.1	874.9	769.7	689.6	618.1	563.0	496.6
47.5°	472.3	593.5	768.4	892.8	892.2	801.6	698.2	621.5	555.3	503.6	449.8
50°	422.4	528.0	675.9	817.1	828.8	752.9	654.5	578.5	516.7	462.4	419.2
52.5°	377.6	464.7	597.6	732.9	766.6	700.8	605.4	535.2	475.1	425.3	388.3
55°	319.1	386.5	487.5	614.0	665.0	618.6	534.0	468.4	419.6	377.8	345.9
57.5°	269.9	320.5	401.5	503.5	562.8	533.6	463.7	410.5	368.8	330.9	305.8
60°	239.0	280.4	349.1	434.3	499.8	479.3	419.6	370.1	334.6	301.8	278.1
62.5°	209.8	245.4	304.3	373.4	433.5	425.1	376.3	334.7	303.6	273.8	253.7
65°	168.9	194.8	240.8	295.0	343.2	347.3	312.3	284.0	256.3	232.6	214.8
67.5°	134.5	151.4	183.8	229.4	265.6	278.5	257.1	235.5	213.5	195.2	179.8
70°	113.3	127.0	150.7	187.5	220.8	234.4	222.1	205.3	186.2	171.1	157.9
72.5°	91.8	105.1	122.6	149.6	178.2	192.9	188.6	176.6	161.0	148.6	136.1
75°	69.2	73.3	85.2	103.3	125.6	138.4	141.6	135.2	122.9	113.3	106.0
77.5°	51.2	53.6	59.3	68.8	83.4	94.8	99.4	98.7	90.2	84.6	77.8
80°	40.9	42.4	45.0	49.1	60.1	71.4	74.6	74.6	68.8	66.4	59.7
82.5°	31.1	32.1	33.8	36.0	41.1	51.1	54.7	55.4	51.6	48.6	43.2
85°	17.7	17.3	18.2	19.5	20.5	23.2	28.7	29.6	28.7	25.1	23.6
87.5°	12.0	11.2	10.2	8.9	8.6	8.4	9.6	10.8	10.0	9.5	9.4
90°	29.2	23.5	17.8	13.5	10.4	7.3	4.3	1.2	4.3	7.3	10.4
92.5°	34.1	32.7	31.4	29.6	27.4	25.1	22.8	20.6	22.8	25.1	27.4
95°	72.9	72.5	72.0	70.4	67.9	65.3	62.7	60.1	62.7	65.3	67.9
97.5°	122.4	121.5	120.5	118.9	116.6	114.4	112.1	109.9	112.1	114.4	116.6
100°	158.0	157.2	156.5	155.1	153.0	151.0	148.9	146.9	148.9	151.0	153.0
102.5°	195.6	194.6	193.6	192.3	190.6	189.0	187.3	185.7	187.3	189.0	190.6
105°	253.3	252.8	252.4	251.6	250.9	250.1	249.3	248.6	249.3	250.1	250.9
107.5°	317.0	317.0	317.0	316.5	315.3	314.2	313.1	311.9	313.1	314.2	315.3
110°	359.6	359.6	359.6	358.8	357.3	355.7	354.2	352.7	354.2	355.7	357.3



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	403.5	403.7	403.9	403.2	401.7	400.1	398.6	397.1	398.6	400.1	401.7
115°	468.1	468.7	469.1	468.7	467.1	465.6	464.0	462.5	464.0	465.6	467.1
117.5°	533.3	534.8	536.3	535.9	533.9	531.8	529.8	527.7	529.8	531.8	533.9
120°	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	573.2	575.3	577.4
122.5°	618.5	619.9	621.3	620.8	618.3	615.9	613.4	610.9	613.4	615.9	618.3
125°	681.4	682.2	683.0	682.2	679.8	677.5	675.2	672.9	675.2	677.5	679.8
127.5°	744.1	745.1	746.0	745.0	742.1	739.1	736.2	733.3	736.2	739.1	742.1
130°	785.0	785.5	786.0	784.5	781.2	777.9	774.5	771.2	774.5	777.9	781.2
132.5°	826.3	826.2	826.1	824.7	821.9	819.2	816.5	813.8	816.5	819.2	821.9
135°	884.7	884.1	883.6	882.0	879.1	876.3	873.4	870.7	873.4	876.3	879.1
137.5°	942.6	941.9	941.3	939.8	937.5	935.1	932.8	930.5	932.8	935.1	937.5
140°	980.3	978.9	977.7	975.9	973.6	971.3	968.9	966.6	968.9	971.3	973.6
142.5°	1016.2	1015.3	1014.4	1012.9	1010.6	1008.3	1005.9	1003.6	1005.9	1008.3	1010.6
145°	1068.7	1067.2	1065.7	1064.0	1062.2	1060.4	1058.6	1056.8	1058.6	1060.4	1062.2
147.5°	1116.5	1115.4	1114.5	1112.9	1110.7	1108.5	1106.3	1104.2	1106.3	1108.5	1110.7
150°	1146.1	1145.0	1144.1	1142.7	1141.2	1139.7	1138.1	1136.6	1138.1	1139.7	1141.2
152.5°	1175.3	1174.0	1172.8	1171.4	1169.8	1168.3	1166.8	1165.3	1166.8	1168.3	1169.8
155°	1213.6	1212.9	1212.1	1211.4	1210.6	1209.8	1209.1	1208.3	1209.1	1209.8	1210.6
157.5°	1248.5	1248.0	1247.6	1247.1	1246.6	1246.1	1245.5	1245.0	1245.5	1246.1	1246.6
160°	1270.2	1269.9	1269.7	1269.3	1268.8	1268.3	1267.7	1267.2	1267.7	1268.3	1268.8
162.5°	1288.7	1288.4	1288.2	1288.0	1287.9	1287.8	1287.7	1287.5	1287.7	1287.8	1287.9
165°	1313.5	1313.5	1313.5	1313.6	1313.8	1314.1	1314.4	1314.6	1314.4	1314.1	1313.8
167.5°	1333.7	1333.7	1333.8	1334.2	1335.0	1335.8	1336.5	1337.3	1336.5	1335.8	1335.0
170°	1345.2	1345.5	1345.8	1346.2	1347.0	1347.8	1348.5	1349.3	1348.5	1347.8	1347.0
172.5°	1353.5	1353.8	1354.1	1354.6	1355.3	1356.1	1356.9	1357.6	1356.9	1356.1	1355.3
175°	1363.1	1363.6	1364.1	1364.8	1365.5	1366.3	1367.1	1367.8	1367.1	1366.3	1365.5
177.5°	1368.2	1368.6	1369.0	1369.5	1370.1	1370.7	1371.4	1372.0	1371.4	1370.7	1370.1
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1291.5	1288.9	1284.2	1276.8	1272.5	1264.8	1259.7	1262.7	1263.4	1262.7	1261.9
5°	1256.8	1247.1	1233.9	1221.2	1209.4	1196.7	1189.4	1186.2	1179.8	1176.2	1174.4
7.5°	1214.8	1198.3	1179.6	1157.4	1138.5	1118.8	1108.8	1103.7	1090.7	1083.6	1077.4
10°	1183.5	1157.5	1138.9	1109.7	1092.0	1066.0	1048.3	1048.7	1031.0	1020.9	1013.7
12.5°	1148.9	1120.3	1089.3	1063.1	1038.4	1017.6	996.2	987.6	968.7	959.0	939.4
15°	1091.5	1058.3	1025.6	990.0	965.0	932.6	901.7	863.9	833.4	807.0	799.8
17.5°	1028.9	987.7	954.8	913.2	870.3	815.9	780.1	758.1	739.8	725.9	715.4
20°	985.9	944.1	909.0	846.1	788.4	751.5	725.1	708.3	689.1	674.1	665.9
22.5°	940.8	897.1	849.3	779.2	734.1	704.5	681.0	661.6	648.7	636.9	629.5
25°	876.6	828.8	750.1	701.9	665.5	634.5	618.1	606.3	592.6	576.7	569.4
27.5°	809.0	732.9	676.4	640.5	605.7	585.6	570.9	553.2	541.0	533.9	526.3
30°	758.3	682.3	638.2	599.1	574.4	552.1	534.8	524.9	513.0	500.7	495.7
32.5°	701.9	641.1	598.9	566.2	541.3	522.3	508.6	492.4	483.8	476.3	465.8
35°	631.8	585.9	547.2	520.8	497.0	481.6	465.7	456.1	440.6	434.3	430.2
37.5°	572.4	532.5	503.7	475.8	457.1	440.0	430.3	415.0	408.3	399.5	390.8
40°	539.0	499.8	472.0	449.2	428.3	415.5	403.3	391.0	380.9	376.9	366.4
42.5°	504.7	472.9	445.1	420.1	406.1	392.6	377.1	368.1	357.7	351.1	344.6
45°	457.4	429.3	405.6	385.0	369.6	355.5	345.4	330.5	324.6	311.3	305.9
47.5°	416.0	389.7	367.1	347.7	332.5	323.3	308.7	296.9	287.5	279.4	272.4
50°	386.5	364.6	342.8	325.5	311.8	298.6	283.6	277.7	263.1	259.0	254.9
52.5°	359.5	338.8	318.7	301.8	288.1	275.3	262.1	254.3	244.5	240.4	237.5
55°	321.8	301.8	282.7	267.6	254.0	240.8	232.6	223.0	218.5	215.3	211.7
57.5°	283.9	265.9	251.3	236.0	222.3	211.9	202.3	196.6	191.9	187.7	183.3
60°	259.9	242.6	229.4	215.3	201.2	192.5	185.3	178.4	173.0	166.6	164.8
62.5°	234.4	219.3	207.2	193.4	181.2	173.3	166.3	159.9	153.3	144.0	141.4
65°	199.4	187.5	174.8	163.5	152.5	144.7	134.7	127.4	124.8	123.8	123.3
67.5°	167.7	156.5	145.5	133.9	123.9	116.8	111.7	110.6	108.7	108.2	106.9
70°	146.6	136.1	125.2	114.2	104.7	103.3	101.5	99.7	97.4	96.5	95.6
72.5°	127.6	116.8	105.8	97.1	93.0	91.3	89.5	87.7	86.1	85.2	84.6
75°	97.8	87.8	80.6	77.4	75.1	73.7	71.0	69.6	68.8	67.3	66.9
77.5°	70.4	64.8	61.4	59.5	57.1	55.6	54.0	52.7	51.7	51.5	50.7
80°	53.7	51.0	48.7	46.0	45.0	43.2	42.8	41.5	41.9	40.5	40.5
82.5°	41.7	38.3	36.3	35.0	34.2	32.7	32.2	31.6	31.7	30.7	30.7
85°	21.4	20.5	19.5	18.6	18.6	17.3	17.7	17.3	17.3	16.4	16.0
87.5°	9.6	10.2	10.5	11.7	12.8	13.6	13.5	13.0	12.8	12.8	12.4
90°	13.5	17.8	23.5	29.2	34.8	40.5	39.9	39.4	39.0	38.4	38.3
92.5°	29.6	31.4	32.7	34.1	35.4	36.7	36.8	37.0	37.1	37.2	37.3
95°	70.4	72.0	72.5	72.9	73.5	74.0	74.0	74.0	74.0	74.0	73.7
97.5°	118.9	120.5	121.5	122.4	123.4	124.4	124.4	124.4	124.4	124.4	124.4
100°	155.1	156.5	157.2	158.0	158.8	159.5	159.5	159.5	159.5	159.5	159.4
102.5°	192.3	193.6	194.6	195.6	196.5	197.5	197.7	197.9	198.1	198.3	198.3
105°	251.6	252.4	252.8	253.3	253.9	254.4	254.9	255.4	255.9	256.5	256.7
107.5°	316.5	317.0	317.0	317.0	317.0	317.0	317.3	317.4	317.6	317.9	317.4
110°	358.8	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.6	359.2



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	403.2	403.9	403.7	403.5	403.2	403.1	402.4	401.8	401.2	400.6	400.0
115°	468.7	469.1	468.7	468.1	467.6	467.1	466.9	466.6	466.4	466.1	465.6
117.5°	535.9	536.3	534.8	533.3	531.9	530.5	529.9	529.2	528.6	528.0	527.4
120°	579.4	579.4	577.4	575.3	573.2	571.1	571.1	571.1	571.1	571.1	570.8
122.5°	620.8	621.3	619.9	618.5	617.0	615.5	614.9	614.4	613.8	613.1	612.5
125°	682.2	683.0	682.2	681.4	680.6	679.8	679.1	678.3	677.5	676.8	676.3
127.5°	745.0	746.0	745.1	744.1	743.2	742.3	741.4	740.5	739.5	738.6	737.7
130°	784.5	786.0	785.5	785.0	784.4	783.9	783.4	782.9	782.4	781.9	781.1
132.5°	824.7	826.1	826.2	826.3	826.3	826.4	825.4	824.2	823.0	822.0	821.0
135°	882.0	883.6	884.1	884.7	885.2	885.6	885.4	885.2	884.9	884.7	884.1
137.5°	939.8	941.3	941.9	942.6	943.3	944.0	943.8	943.5	943.3	943.2	942.5
140°	975.9	977.7	978.9	980.3	981.5	982.8	982.8	982.8	982.8	982.8	982.3
142.5°	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2	1018.3	1018.6	1018.8	1018.3
145°	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1	1072.4	1072.6	1072.8	1072.5
147.5°	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1	1119.6	1120.3	1120.8	1120.6
150°	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2
152.5°	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6
155°	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5	1217.8	1219.1	1220.3	1220.6
157.5°	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2	1252.9	1254.6	1256.4	1256.7
160°	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2	1273.8	1275.3	1276.8	1277.1
162.5°	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9	1292.7	1294.4	1296.2	1296.5
165°	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3	1317.1	1318.8	1320.7	1320.9
167.5°	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4	1337.2	1339.0	1340.8	1341.0
170°	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5	1348.3	1350.1	1351.9	1352.0
172.5°	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9	1356.6	1358.4	1360.2	1360.3
175°	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9	1365.7	1367.4	1369.2	1369.4
177.5°	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1257.9	1258.6	1257.6	1258.3	1257.6	1258.6	1257.9	1261.9	1262.7	1263.4	1262.7
5°	1172.1	1166.6	1165.7	1164.3	1165.7	1166.6	1172.1	1174.4	1176.2	1179.8	1186.2
7.5°	1069.6	1068.7	1066.5	1063.3	1066.5	1068.7	1069.6	1077.4	1083.6	1090.7	1103.7
10°	1003.6	1001.4	1000.9	997.7	1000.9	1001.4	1003.6	1013.7	1020.9	1031.0	1048.7
12.5°	926.5	911.8	910.3	902.3	910.3	911.8	926.5	939.4	959.0	968.7	987.6
15°	788.8	786.1	776.9	771.1	776.9	786.1	788.8	799.8	807.0	833.4	863.9
17.5°	710.2	701.2	698.4	697.1	698.4	701.2	710.2	715.4	725.9	739.8	758.1
20°	659.5	651.4	650.0	649.1	650.0	651.4	659.5	665.9	674.1	689.1	708.3
22.5°	624.6	616.0	612.5	609.8	612.5	616.0	624.6	629.5	636.9	648.7	661.6
25°	564.9	561.7	559.9	558.9	559.9	561.7	564.9	569.4	576.7	592.6	606.3
27.5°	518.2	511.1	509.8	507.5	509.8	511.1	518.2	526.3	533.9	541.0	553.2
30°	491.6	489.3	486.2	483.4	486.2	489.3	491.6	495.7	500.7	513.0	524.9
32.5°	460.3	458.3	455.6	454.2	455.6	458.3	460.3	465.8	476.3	483.8	492.4
35°	425.6	419.2	416.5	412.4	416.5	419.2	425.6	430.2	434.3	440.6	456.1
37.5°	388.9	385.6	381.7	383.1	381.7	385.6	388.9	390.8	399.5	408.3	415.0
40°	360.5	358.2	357.3	356.9	357.3	358.2	360.5	366.4	376.9	380.9	391.0
42.5°	338.0	331.6	329.3	329.2	329.3	331.6	338.0	344.6	351.1	357.7	368.1
45°	303.6	297.7	293.6	294.1	293.6	297.7	303.6	305.9	311.3	324.6	330.5
47.5°	268.5	268.3	265.7	266.5	265.7	268.3	268.5	272.4	279.4	287.5	296.9
50°	251.7	249.0	247.2	247.6	247.2	249.0	251.7	254.9	259.0	263.1	277.7
52.5°	235.7	233.4	231.8	233.8	231.8	233.4	235.7	237.5	240.4	244.5	254.3
55°	209.4	206.6	206.2	205.7	206.2	206.6	209.4	211.7	215.3	218.5	223.0
57.5°	179.9	178.2	175.4	174.2	175.4	178.2	179.9	183.3	187.7	191.9	196.6
60°	158.8	155.2	150.7	150.2	150.7	155.2	158.8	164.8	166.6	173.0	178.4
62.5°	139.6	138.8	137.9	137.9	137.9	138.8	139.6	141.4	144.0	153.3	159.9
65°	122.4	122.0	122.4	122.9	122.4	122.0	122.4	123.3	123.8	124.8	127.4
67.5°	106.7	105.8	105.0	105.4	105.0	105.8	106.7	106.9	108.2	108.7	110.6
70°	94.7	94.3	93.8	93.8	93.8	94.3	94.7	95.6	96.5	97.4	99.7
72.5°	83.0	82.9	82.5	82.1	82.5	82.9	83.0	84.6	85.2	86.1	87.7
75°	66.4	65.5	65.5	65.5	65.5	65.5	66.4	66.9	67.3	68.8	69.6
77.5°	50.6	50.2	49.7	49.3	49.7	50.2	50.6	50.7	51.5	51.7	52.7
80°	40.0	39.6	39.1	39.1	39.1	39.6	40.0	40.5	40.5	41.9	41.5
82.5°	30.6	30.1	30.1	29.7	30.1	30.1	30.6	30.7	30.7	31.7	31.6
85°	16.4	16.9	16.4	17.3	16.4	16.9	16.4	16.0	16.4	17.3	17.3
87.5°	12.5	12.1	12.6	12.2	12.6	12.1	12.5	12.4	12.8	12.8	13.0
90°	38.5	38.8	39.1	39.3	39.1	38.8	38.5	38.3	38.4	39.0	39.4
92.5°	37.3	37.4	37.5	37.5	37.5	37.4	37.3	37.3	37.2	37.1	37.0
95°	73.2	72.7	72.2	71.7	72.2	72.7	73.2	73.7	74.0	74.0	74.0
97.5°	124.3	124.3	124.2	124.2	124.2	124.3	124.3	124.4	124.4	124.4	124.4
100°	159.2	158.9	158.6	158.4	158.6	158.9	159.2	159.4	159.5	159.5	159.5
102.5°	198.0	197.8	197.5	197.2	197.5	197.8	198.0	198.3	198.3	198.1	197.9
105°	256.7	256.7	256.7	256.7	256.7	256.7	256.7	256.7	256.5	255.9	255.4
107.5°	316.2	315.0	313.8	312.6	313.8	315.0	316.2	317.4	317.9	317.6	317.4
110°	358.5	357.7	356.9	356.1	356.9	357.7	358.5	359.2	359.6	359.6	359.6



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	399.4	398.9	398.3	397.7	398.3	398.9	399.4	400.0	400.6	401.2	401.8
115°	464.8	464.0	463.2	462.5	463.2	464.0	464.8	465.6	466.1	466.4	466.6
117.5°	526.6	525.8	525.0	524.2	525.0	525.8	526.6	527.4	528.0	528.6	529.2
120°	570.0	569.3	568.5	567.8	568.5	569.3	570.0	570.8	571.1	571.1	571.1
122.5°	612.0	611.4	610.8	610.3	610.8	611.4	612.0	612.5	613.1	613.8	614.4
125°	676.0	675.7	675.5	675.2	675.5	675.7	676.0	676.3	676.8	677.5	678.3
127.5°	736.9	736.1	735.3	734.4	735.3	736.1	736.9	737.7	738.6	739.5	740.5
130°	780.1	779.1	778.0	776.9	778.0	779.1	780.1	781.1	781.9	782.4	782.9
132.5°	820.2	819.3	818.5	817.7	818.5	819.3	820.2	821.0	822.0	823.0	824.2
135°	883.3	882.6	881.8	881.0	881.8	882.6	883.3	884.1	884.7	884.9	885.2
137.5°	941.5	940.5	939.4	938.4	939.4	940.5	941.5	942.5	943.2	943.3	943.5
140°	981.2	980.3	979.2	978.2	979.2	980.3	981.2	982.3	982.8	982.8	982.8
142.5°	1017.4	1016.3	1015.3	1014.2	1015.3	1016.3	1017.4	1018.3	1018.8	1018.6	1018.3
145°	1071.5	1070.4	1069.4	1068.4	1069.4	1070.4	1071.5	1072.5	1072.8	1072.6	1072.4
147.5°	1119.6	1118.7	1117.7	1116.7	1117.7	1118.7	1119.6	1120.6	1120.8	1120.3	1119.6
150°	1150.5	1149.7	1148.9	1148.2	1148.9	1149.7	1150.5	1151.2	1151.2	1150.5	1149.7
152.5°	1180.6	1179.7	1178.8	1177.8	1178.8	1179.7	1180.6	1181.6	1181.6	1180.6	1179.7
155°	1219.9	1219.1	1218.3	1217.5	1218.3	1219.1	1219.9	1220.6	1220.3	1219.1	1217.8
157.5°	1255.4	1254.2	1252.9	1251.7	1252.9	1254.2	1255.4	1256.7	1256.4	1254.6	1252.9
160°	1276.1	1275.1	1274.1	1273.0	1274.1	1275.1	1276.1	1277.1	1276.8	1275.3	1273.8
162.5°	1295.2	1294.0	1292.7	1291.6	1292.7	1294.0	1295.2	1296.5	1296.2	1294.4	1292.7
165°	1319.6	1318.4	1317.1	1315.8	1317.1	1318.4	1319.6	1320.9	1320.7	1318.8	1317.1
167.5°	1339.7	1338.4	1337.0	1335.7	1337.0	1338.4	1339.7	1341.0	1340.8	1339.0	1337.2
170°	1350.5	1349.0	1347.4	1345.9	1347.4	1349.0	1350.5	1352.0	1351.9	1350.1	1348.3
172.5°	1358.8	1357.3	1355.8	1354.2	1355.8	1357.3	1358.8	1360.3	1360.2	1358.4	1356.6
175°	1367.8	1366.3	1364.8	1363.2	1364.8	1366.3	1367.8	1369.4	1369.2	1367.4	1365.7
177.5°	1371.1	1369.8	1368.6	1367.3	1368.6	1369.8	1371.1	1372.3	1372.3	1371.1	1369.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1259.7	1264.8	1272.5	1276.8	1284.2	1288.9	1291.5	1296.2	1298.7	1307.8	1317.3
5°	1189.4	1196.7	1209.4	1221.2	1233.9	1247.1	1256.8	1267.7	1277.6	1294.9	1313.2
7.5°	1108.8	1118.8	1138.5	1157.4	1179.6	1198.3	1214.8	1233.4	1250.1	1274.9	1300.7
10°	1048.3	1066.0	1092.0	1109.7	1138.9	1157.5	1183.5	1203.9	1227.2	1259.9	1289.1
12.5°	996.2	1017.6	1038.4	1063.1	1089.3	1120.3	1148.9	1175.2	1202.7	1236.6	1270.9
15°	901.7	932.6	965.0	990.0	1025.6	1058.3	1091.5	1127.0	1160.7	1201.2	1245.8
17.5°	780.1	815.9	870.3	913.2	954.8	987.7	1028.9	1071.8	1111.5	1160.4	1210.1
20°	725.1	751.5	788.4	846.1	909.0	944.1	985.9	1033.2	1078.8	1132.0	1185.3
22.5°	681.0	704.5	734.1	779.2	849.3	897.1	940.8	988.8	1041.6	1096.0	1155.0
25°	618.1	634.5	665.5	701.9	750.1	828.8	876.6	924.9	982.3	1040.5	1107.9
27.5°	570.9	585.6	605.7	640.5	676.4	732.9	809.0	861.6	918.7	984.3	1054.2
30°	534.8	552.1	574.4	599.1	638.2	682.3	758.3	819.3	875.7	943.2	1017.8
32.5°	508.6	522.3	541.3	566.2	598.9	641.1	701.9	776.0	831.0	902.0	979.9
35°	465.7	481.6	497.0	520.8	547.2	585.9	631.8	711.0	765.6	835.7	914.0
37.5°	430.3	440.0	457.1	475.8	503.7	532.5	572.4	643.5	702.5	771.3	851.5
40°	403.3	415.5	428.3	449.2	472.0	499.8	539.0	591.7	659.5	726.9	805.2
42.5°	377.1	392.6	406.1	420.1	445.1	472.9	504.7	549.5	618.8	682.5	758.6
45°	345.4	355.5	369.6	385.0	405.6	429.3	457.4	496.6	563.0	618.1	689.6
47.5°	308.7	323.3	332.5	347.7	367.1	389.7	416.0	449.8	503.6	555.3	621.5
50°	283.6	298.6	311.8	325.5	342.8	364.6	386.5	419.2	462.4	516.7	578.5
52.5°	262.1	275.3	288.1	301.8	318.7	338.8	359.5	388.3	425.3	475.1	535.2
55°	232.6	240.8	254.0	267.6	282.7	301.8	321.8	345.9	377.8	419.6	468.4
57.5°	202.3	211.9	222.3	236.0	251.3	265.9	283.9	305.8	330.9	368.8	410.5
60°	185.3	192.5	201.2	215.3	229.4	242.6	259.9	278.1	301.8	334.6	370.1
62.5°	166.3	173.3	181.2	193.4	207.2	219.3	234.4	253.7	273.8	303.6	334.7
65°	134.7	144.7	152.5	163.5	174.8	187.5	199.4	214.8	232.6	256.3	284.0
67.5°	111.7	116.8	123.9	133.9	145.5	156.5	167.7	179.8	195.2	213.5	235.5
70°	101.5	103.3	104.7	114.2	125.2	136.1	146.6	157.9	171.1	186.2	205.3
72.5°	89.5	91.3	93.0	97.1	105.8	116.8	127.6	136.1	148.6	161.0	176.6
75°	71.0	73.7	75.1	77.4	80.6	87.8	97.8	106.0	113.3	122.9	135.2
77.5°	54.0	55.6	57.1	59.5	61.4	64.8	70.4	77.8	84.6	90.2	98.7
80°	42.8	43.2	45.0	46.0	48.7	51.0	53.7	59.7	66.4	68.8	74.6
82.5°	32.2	32.7	34.2	35.0	36.3	38.3	41.7	43.2	48.6	51.6	55.4
85°	17.7	17.3	18.6	18.6	19.5	20.5	21.4	23.6	25.1	28.7	29.6
87.5°	13.5	13.6	12.8	11.7	10.5	10.2	9.6	9.4	9.5	10.0	10.8
90°	39.9	40.5	34.8	29.2	23.5	17.8	13.5	10.4	7.3	4.3	1.2
92.5°	36.8	36.7	35.4	34.1	32.7	31.4	29.6	27.4	25.1	22.8	20.6
95°	74.0	74.0	73.5	72.9	72.5	72.0	70.4	67.9	65.3	62.7	60.1
97.5°	124.4	124.4	123.4	122.4	121.5	120.5	118.9	116.6	114.4	112.1	109.9
100°	159.5	159.5	158.8	158.0	157.2	156.5	155.1	153.0	151.0	148.9	146.9
102.5°	197.7	197.5	196.5	195.6	194.6	193.6	192.3	190.6	189.0	187.3	185.7
105°	254.9	254.4	253.9	253.3	252.8	252.4	251.6	250.9	250.1	249.3	248.6
107.5°	317.3	317.0	317.0	317.0	317.0	317.0	316.5	315.3	314.2	313.1	311.9
110°	359.6	359.6	359.6	359.6	359.6	359.6	358.8	357.3	355.7	354.2	352.7



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	402.4	403.1	403.2	403.5	403.7	403.9	403.2	401.7	400.1	398.6	397.1
115°	466.9	467.1	467.6	468.1	468.7	469.1	468.7	467.1	465.6	464.0	462.5
117.5°	529.9	530.5	531.9	533.3	534.8	536.3	535.9	533.9	531.8	529.8	527.7
120°	571.1	571.1	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1
122.5°	614.9	615.5	617.0	618.5	619.9	621.3	620.8	618.3	615.9	613.4	610.9
125°	679.1	679.8	680.6	681.4	682.2	683.0	682.2	679.8	677.5	675.2	672.9
127.5°	741.4	742.3	743.2	744.1	745.1	746.0	745.0	742.1	739.1	736.2	733.3
130°	783.4	783.9	784.4	785.0	785.5	786.0	784.5	781.2	777.9	774.5	771.2
132.5°	825.4	826.4	826.3	826.3	826.2	826.1	824.7	821.9	819.2	816.5	813.8
135°	885.4	885.6	885.2	884.7	884.1	883.6	882.0	879.1	876.3	873.4	870.7
137.5°	943.8	944.0	943.3	942.6	941.9	941.3	939.8	937.5	935.1	932.8	930.5
140°	982.8	982.8	981.5	980.3	978.9	977.7	975.9	973.6	971.3	968.9	966.6
142.5°	1018.2	1018.0	1017.1	1016.2	1015.3	1014.4	1012.9	1010.6	1008.3	1005.9	1003.6
145°	1072.1	1071.8	1070.3	1068.7	1067.2	1065.7	1064.0	1062.2	1060.4	1058.6	1056.8
147.5°	1119.1	1118.6	1117.5	1116.5	1115.4	1114.5	1112.9	1110.7	1108.5	1106.3	1104.2
150°	1148.9	1148.2	1147.1	1146.1	1145.0	1144.1	1142.7	1141.2	1139.7	1138.1	1136.6
152.5°	1178.8	1177.8	1176.5	1175.3	1174.0	1172.8	1171.4	1169.8	1168.3	1166.8	1165.3
155°	1216.5	1215.2	1214.4	1213.6	1212.9	1212.1	1211.4	1210.6	1209.8	1209.1	1208.3
157.5°	1251.2	1249.5	1248.9	1248.5	1248.0	1247.6	1247.1	1246.6	1246.1	1245.5	1245.0
160°	1272.2	1270.7	1270.4	1270.2	1269.9	1269.7	1269.3	1268.8	1268.3	1267.7	1267.2
162.5°	1290.9	1289.2	1289.0	1288.7	1288.4	1288.2	1288.0	1287.9	1287.8	1287.7	1287.5
165°	1315.3	1313.5	1313.5	1313.5	1313.5	1313.5	1313.6	1313.8	1314.1	1314.4	1314.6
167.5°	1335.4	1333.6	1333.6	1333.7	1333.7	1333.8	1334.2	1335.0	1335.8	1336.5	1337.3
170°	1346.5	1344.7	1345.0	1345.2	1345.5	1345.8	1346.2	1347.0	1347.8	1348.5	1349.3
172.5°	1354.9	1353.0	1353.3	1353.5	1353.8	1354.1	1354.6	1355.3	1356.1	1356.9	1357.6
175°	1363.9	1362.0	1362.5	1363.1	1363.6	1364.1	1364.8	1365.5	1366.3	1367.1	1367.8
177.5°	1368.6	1367.3	1367.8	1368.2	1368.6	1369.0	1369.5	1370.1	1370.7	1371.4	1372.0
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1317.7	1318.8	1326.1	1329.3	1335.9	1338.4	1341.3	1340.6	1340.6	1342.0	1352.3
5°	1320.4	1329.5	1343.2	1356.4	1369.1	1380.1	1387.4	1394.6	1397.4	1410.6	1422.5
7.5°	1315.7	1332.5	1355.0	1375.2	1399.3	1418.2	1433.8	1448.0	1457.6	1476.8	1496.5
10°	1309.6	1333.2	1358.7	1384.6	1417.9	1442.9	1468.4	1488.0	1494.3	1523.0	1539.4
12.5°	1297.2	1328.8	1361.3	1394.8	1427.4	1461.9	1489.9	1509.5	1531.9	1557.6	1587.9
15°	1278.6	1315.0	1357.4	1400.6	1447.0	1488.9	1518.9	1553.1	1577.6	1605.9	1632.3
17.5°	1251.9	1298.8	1352.6	1402.7	1456.3	1501.4	1542.7	1575.5	1592.8	1608.8	1612.7
20°	1230.8	1281.3	1344.6	1403.7	1457.5	1509.4	1550.3	1577.6	1582.2	1582.6	1558.5
22.5°	1207.8	1264.9	1331.1	1391.8	1456.0	1513.8	1545.6	1557.3	1539.2	1508.3	1461.7
25°	1165.7	1231.7	1308.7	1377.8	1448.0	1502.5	1513.5	1493.0	1429.7	1363.2	1279.1
27.5°	1120.0	1194.2	1276.7	1353.6	1428.3	1462.1	1438.5	1364.7	1250.7	1151.6	1031.6
30°	1086.5	1169.8	1250.8	1336.9	1406.0	1420.6	1366.5	1257.7	1124.7	975.4	855.8
32.5°	1048.3	1135.6	1224.6	1313.6	1371.5	1357.3	1267.7	1133.8	978.0	831.3	718.1
35°	993.6	1083.8	1179.8	1269.0	1305.9	1244.5	1110.6	936.3	776.9	640.0	562.1
37.5°	930.6	1028.7	1128.5	1210.5	1207.8	1105.5	923.2	743.2	609.3	528.2	472.9
40°	885.7	985.0	1092.9	1162.1	1132.5	999.1	801.6	631.8	534.0	469.3	428.7
42.5°	842.8	942.4	1049.5	1104.6	1053.1	889.1	692.3	559.3	478.6	428.1	395.3
45°	769.7	874.9	974.1	1004.6	912.7	731.9	559.9	463.3	409.7	372.4	349.6
47.5°	698.2	801.6	892.2	892.8	768.4	593.5	472.3	401.0	355.2	326.3	309.7
50°	654.5	752.9	828.8	817.1	675.9	528.0	422.4	361.0	322.7	300.4	283.1
52.5°	605.4	700.8	766.6	732.9	597.6	464.7	377.6	326.0	294.4	274.9	259.5
55°	534.0	618.6	665.0	614.0	487.5	386.5	319.1	278.6	254.9	238.5	225.3
57.5°	463.7	533.6	562.8	503.5	401.5	320.5	269.9	239.5	216.1	204.3	197.4
60°	419.6	479.3	499.8	434.3	349.1	280.4	239.0	210.7	193.4	185.7	178.9
62.5°	376.3	425.1	433.5	373.4	304.3	245.4	209.8	186.0	174.5	167.1	160.7
65°	312.3	347.3	343.2	295.0	240.8	194.8	168.9	154.3	145.6	135.2	123.8
67.5°	257.1	278.5	265.6	229.4	183.8	151.4	134.5	123.4	112.7	102.8	100.1
70°	222.1	234.4	220.8	187.5	150.7	127.0	113.3	100.1	93.8	91.5	87.4
72.5°	188.6	192.9	178.2	149.6	122.6	105.1	91.8	84.4	81.1	79.1	76.5
75°	141.6	138.4	125.6	103.3	85.2	73.3	69.2	66.4	64.2	62.3	61.0
77.5°	99.4	94.8	83.4	68.8	59.3	53.6	51.2	49.7	48.6	47.7	46.4
80°	74.6	71.4	60.1	49.1	45.0	42.4	40.9	39.1	39.1	38.3	36.8
82.5°	54.7	51.1	41.1	36.0	33.8	32.1	31.1	30.1	29.7	29.9	28.9
85°	28.7	23.2	20.5	19.5	18.2	17.3	17.7	16.9	16.9	16.9	16.4
87.5°	9.6	8.4	8.6	8.9	10.2	11.2	12.0	13.2	14.6	14.2	14.4
90°	4.3	7.3	10.4	13.5	17.8	23.5	29.2	34.8	40.5	39.9	39.4
92.5°	22.8	25.1	27.4	29.6	31.4	32.7	34.1	35.4	36.7	36.8	37.0
95°	62.7	65.3	67.9	70.4	72.0	72.5	72.9	73.5	74.0	74.0	74.0
97.5°	112.1	114.4	116.6	118.9	120.5	121.5	122.4	123.4	124.4	124.4	124.4
100°	148.9	151.0	153.0	155.1	156.5	157.2	158.0	158.8	159.5	159.5	159.5
102.5°	187.3	189.0	190.6	192.3	193.6	194.6	195.6	196.5	197.5	197.7	197.9
105°	249.3	250.1	250.9	251.6	252.4	252.8	253.3	253.9	254.4	254.9	255.4
107.5°	313.1	314.2	315.3	316.5	317.0	317.0	317.0	317.0	317.0	317.3	317.4
110°	354.2	355.7	357.3	358.8	359.6	359.6	359.6	359.6	359.6	359.6	359.6



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	398.6	400.1	401.7	403.2	403.9	403.7	403.5	403.2	403.1	402.4	401.8
115°	464.0	465.6	467.1	468.7	469.1	468.7	468.1	467.6	467.1	466.9	466.6
117.5°	529.8	531.8	533.9	535.9	536.3	534.8	533.3	531.9	530.5	529.9	529.2
120°	573.2	575.3	577.4	579.4	579.4	577.4	575.3	573.2	571.1	571.1	571.1
122.5°	613.4	615.9	618.3	620.8	621.3	619.9	618.5	617.0	615.5	614.9	614.4
125°	675.2	677.5	679.8	682.2	683.0	682.2	681.4	680.6	679.8	679.1	678.3
127.5°	736.2	739.1	742.1	745.0	746.0	745.1	744.1	743.2	742.3	741.4	740.5
130°	774.5	777.9	781.2	784.5	786.0	785.5	785.0	784.4	783.9	783.4	782.9
132.5°	816.5	819.2	821.9	824.7	826.1	826.2	826.3	826.3	826.4	825.4	824.2
135°	873.4	876.3	879.1	882.0	883.6	884.1	884.7	885.2	885.6	885.4	885.2
137.5°	932.8	935.1	937.5	939.8	941.3	941.9	942.6	943.3	944.0	943.8	943.5
140°	968.9	971.3	973.6	975.9	977.7	978.9	980.3	981.5	982.8	982.8	982.8
142.5°	1005.9	1008.3	1010.6	1012.9	1014.4	1015.3	1016.2	1017.1	1018.0	1018.2	1018.3
145°	1058.6	1060.4	1062.2	1064.0	1065.7	1067.2	1068.7	1070.3	1071.8	1072.1	1072.4
147.5°	1106.3	1108.5	1110.7	1112.9	1114.5	1115.4	1116.5	1117.5	1118.6	1119.1	1119.6
150°	1138.1	1139.7	1141.2	1142.7	1144.1	1145.0	1146.1	1147.1	1148.2	1148.9	1149.7
152.5°	1166.8	1168.3	1169.8	1171.4	1172.8	1174.0	1175.3	1176.5	1177.8	1178.8	1179.7
155°	1209.1	1209.8	1210.6	1211.4	1212.1	1212.9	1213.6	1214.4	1215.2	1216.5	1217.8
157.5°	1245.5	1246.1	1246.6	1247.1	1247.6	1248.0	1248.5	1248.9	1249.5	1251.2	1252.9
160°	1267.7	1268.3	1268.8	1269.3	1269.7	1269.9	1270.2	1270.4	1270.7	1272.2	1273.8
162.5°	1287.7	1287.8	1287.9	1288.0	1288.2	1288.4	1288.7	1289.0	1289.2	1290.9	1292.7
165°	1314.4	1314.1	1313.8	1313.6	1313.5	1313.5	1313.5	1313.5	1313.5	1315.3	1317.1
167.5°	1336.5	1335.8	1335.0	1334.2	1333.8	1333.7	1333.7	1333.6	1333.6	1335.4	1337.2
170°	1348.5	1347.8	1347.0	1346.2	1345.8	1345.5	1345.2	1345.0	1344.7	1346.5	1348.3
172.5°	1356.9	1356.1	1355.3	1354.6	1354.1	1353.8	1353.5	1353.3	1353.0	1354.9	1356.6
175°	1367.1	1366.3	1365.5	1364.8	1364.1	1363.6	1363.1	1362.5	1362.0	1363.9	1365.7
177.5°	1371.4	1370.7	1370.1	1369.5	1369.0	1368.6	1368.2	1367.8	1367.3	1368.6	1369.8
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1355.8	1360.6	1362.8	1362.8	1365.4	1364.2	1363.2
5°	1433.8	1442.4	1444.3	1452.5	1458.4	1456.5	1457.5
7.5°	1511.3	1525.2	1538.9	1545.2	1546.2	1549.9	1551.2
10°	1559.0	1570.4	1591.8	1588.6	1604.5	1613.6	1598.6
12.5°	1604.9	1620.2	1635.0	1639.1	1648.2	1651.1	1645.2
15°	1646.4	1654.6	1655.5	1653.2	1655.9	1653.7	1645.0
17.5°	1607.6	1594.3	1567.4	1554.6	1544.5	1529.6	1523.6
20°	1543.5	1504.3	1458.8	1440.6	1419.2	1377.3	1387.4
22.5°	1405.2	1360.5	1315.0	1261.9	1236.4	1196.8	1194.4
25°	1189.8	1112.9	1028.2	969.1	934.5	894.9	877.6
27.5°	925.1	828.2	758.8	723.7	691.8	660.4	659.1
30°	751.0	678.2	624.5	594.5	574.9	561.7	564.5
32.5°	633.0	583.2	547.0	522.0	507.6	497.6	497.4
35°	517.5	483.4	460.2	449.7	439.3	431.9	432.4
37.5°	442.9	422.4	409.5	397.9	391.4	387.8	385.8
40°	404.7	387.8	377.8	371.0	365.5	360.5	359.6
42.5°	374.4	360.5	350.4	345.1	340.0	336.4	335.6
45°	332.3	320.9	311.8	305.9	303.6	300.4	300.4
47.5°	295.6	284.4	277.3	273.6	269.7	267.5	267.4
50°	270.8	262.2	255.8	253.5	250.3	249.0	248.5
52.5°	248.6	242.2	237.6	236.0	234.7	232.9	233.3
55°	218.5	214.8	213.0	211.7	209.4	206.6	208.5
57.5°	193.1	190.0	185.1	180.8	178.7	176.8	177.5
60°	175.2	168.9	162.5	157.5	156.1	152.0	152.0
62.5°	152.7	143.7	135.9	133.1	131.7	129.8	129.5
65°	117.4	113.8	112.0	110.1	109.2	109.2	108.3
67.5°	97.3	95.9	93.9	93.4	92.5	92.2	91.9
70°	86.1	84.2	83.3	82.8	81.9	82.4	81.1
72.5°	75.1	73.7	73.5	72.3	71.7	71.8	70.8
75°	59.2	59.2	58.7	58.2	57.3	56.9	57.3
77.5°	45.5	45.6	44.8	44.7	44.6	44.7	44.2
80°	36.4	36.8	36.4	35.9	35.5	35.9	35.5
82.5°	28.8	28.1	28.0	27.9	27.8	27.6	27.5
85°	16.4	16.9	16.4	16.0	16.0	16.0	16.4
87.5°	14.0	13.9	13.8	13.9	13.9	14.0	13.7
90°	39.0	38.4	38.3	38.5	38.8	39.1	39.3
92.5°	37.1	37.2	37.3	37.3	37.4	37.5	37.5
95°	74.0	74.0	73.7	73.2	72.7	72.2	71.7
97.5°	124.4	124.4	124.4	124.3	124.3	124.2	124.2
100°	159.5	159.5	159.4	159.2	158.9	158.6	158.4
102.5°	198.1	198.3	198.3	198.0	197.8	197.5	197.2
105°	255.9	256.5	256.7	256.7	256.7	256.7	256.7
107.5°	317.6	317.9	317.4	316.2	315.0	313.8	312.6
110°	359.6	359.6	359.2	358.5	357.7	356.9	356.1



TEST NUMBER: P331818-940

CATALOG NUMBER: S122RDIW-S675D1240U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	401.2	400.6	400.0	399.4	398.9	398.3	397.7
115°	466.4	466.1	465.6	464.8	464.0	463.2	462.5
117.5°	528.6	528.0	527.4	526.6	525.8	525.0	524.2
120°	571.1	571.1	570.8	570.0	569.3	568.5	567.8
122.5°	613.8	613.1	612.5	612.0	611.4	610.8	610.3
125°	677.5	676.8	676.3	676.0	675.7	675.5	675.2
127.5°	739.5	738.6	737.7	736.9	736.1	735.3	734.4
130°	782.4	781.9	781.1	780.1	779.1	778.0	776.9
132.5°	823.0	822.0	821.0	820.2	819.3	818.5	817.7
135°	884.9	884.7	884.1	883.3	882.6	881.8	881.0
137.5°	943.3	943.2	942.5	941.5	940.5	939.4	938.4
140°	982.8	982.8	982.3	981.2	980.3	979.2	978.2
142.5°	1018.6	1018.8	1018.3	1017.4	1016.3	1015.3	1014.2
145°	1072.6	1072.8	1072.5	1071.5	1070.4	1069.4	1068.4
147.5°	1120.3	1120.8	1120.6	1119.6	1118.7	1117.7	1116.7
150°	1150.5	1151.2	1151.2	1150.5	1149.7	1148.9	1148.2
152.5°	1180.6	1181.6	1181.6	1180.6	1179.7	1178.8	1177.8
155°	1219.1	1220.3	1220.6	1219.9	1219.1	1218.3	1217.5
157.5°	1254.6	1256.4	1256.7	1255.4	1254.2	1252.9	1251.7
160°	1275.3	1276.8	1277.1	1276.1	1275.1	1274.1	1273.0
162.5°	1294.4	1296.2	1296.5	1295.2	1294.0	1292.7	1291.6
165°	1318.8	1320.7	1320.9	1319.6	1318.4	1317.1	1315.8
167.5°	1339.0	1340.8	1341.0	1339.7	1338.4	1337.0	1335.7
170°	1350.1	1351.9	1352.0	1350.5	1349.0	1347.4	1345.9
172.5°	1358.4	1360.2	1360.3	1358.8	1357.3	1355.8	1354.2
175°	1367.4	1369.2	1369.4	1367.8	1366.3	1364.8	1363.2
177.5°	1371.1	1372.3	1372.3	1371.1	1369.8	1368.6	1367.3
180°	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1	1370.1

(END OF REPORT)