

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331808-940

Luminaire Tested: **S122RDIW-S675D435U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331808-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D435U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3409.4 lumens
Efficiency: N/A
Efficacy: 90.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331808-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331808-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	93	89	94	91	87	84	79	77	75	69	67	65	59	58	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	75	68	62	79	71	64	59	62	57	53	55	51	48	47	45	42	39
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	43	40	37	34
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33	30
6	66	54	46	41	62	51	44	39	46	40	35	40	36	32	35	32	29	26
7	61	49	41	36	57	47	39	34	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	53	43	36	31	38	32	28	34	29	26	30	26	23	21
9	53	41	34	29	50	39	32	28	35	29	26	31	27	23	28	24	21	19
10	50	38	31	26	47	36	29	25	32	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16239	16239	16239
5°	16302	16037	16126
10°	16179	15775	15641
15°	15992	15308	14867
20°	15735	14639	13904
25°	15471	13881	12975
30°	15105	13103	11779
35°	14747	12254	10730
40°	14389	11377	9516
45°	13967	10392	8416
50°	13536	9399	7340
55°	13095	8329	6303
60°	12581	7201	5231
65°	12000	6052	4768
70°	11301	4985	4381
75°	10449	4548	4086
80°	9224	4063	3719
85°	7243	3205	3205



TEST NUMBER: P331808-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.2	2.8
10°-20°	258.5	7.6
20°-30°	363.0	10.6
30°-40°	395.9	11.6
40°-50°	364.0	10.7
50°-60°	285.9	8.4
60°-70°	186.4	5.5
70°-80°	96.1	2.8
80°-90°	26.8	0.8
90°-100°	30.3	0.9
100°-110°	94.2	2.8
110°-120°	161.0	4.7
120°-130°	211.8	6.2
130°-140°	237.7	7.0
140°-150°	233.1	6.8
150°-160°	195.5	5.7
160°-170°	129.7	3.8
170°-180°	45.3	1.3
0°-30°	715.7	21.0
0°-40°	1111.6	32.6
0°-60°	1761.4	51.7
0°-90°	2070.8	60.7
90°-120°	285.6	8.4
90°-150°	968.1	28.4
90°-180°	1339.0	39.3
0°-180°	3409.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1006	1001	990	997	995	95
15°	957	946	916	899	889	269
25°	868	838	779	743	728	399
35°	748	700	622	566	544	468
45°	612	549	455	393	369	472
55°	465	393	296	243	224	416
65°	314	240	158	129	125	311
75°	168	106	73	67	66	177
85°	39	21	17	17	17	46
90°	0	5	14	13	14	3
95°	21	25	26	26	25	24
105°	87	88	89	90	90	92
115°	162	164	163	163	162	160
125°	235	238	238	236	236	210
135°	304	308	309	309	308	235
145°	369	372	374	375	373	231
155°	422	423	425	426	425	194
165°	459	459	459	462	460	129
175°	478	477	476	478	476	45
180°	479	479	479	479	479	



TEST NUMBER: P331808-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1009.5	1008.7	1007.9	1007.1	1006.3	1005.0	1003.2	1001.4	999.7	997.9	999.5
5°	1005.8	1004.9	1003.9	1002.8	1001.8	1000.1	997.4	994.8	992.1	989.5	991.3
7.5°	995.5	994.3	993.0	991.8	990.5	988.3	985.3	982.2	979.1	976.1	976.5
10°	986.8	985.3	983.9	982.5	981.1	978.4	974.3	970.3	966.3	962.2	961.6
12.5°	975.8	974.1	972.3	970.6	968.8	965.5	960.3	955.1	949.9	944.7	943.6
15°	956.7	954.5	952.3	950.0	947.8	943.3	936.4	929.5	922.7	915.8	912.0
17.5°	933.3	929.9	926.5	923.0	919.6	913.6	904.7	895.9	887.1	878.2	873.7
20°	915.8	911.7	907.7	903.7	899.6	892.5	882.3	872.3	862.2	852.0	846.9
22.5°	896.8	892.3	887.8	883.2	878.7	870.8	859.3	847.9	836.5	825.1	818.6
25°	868.4	861.9	855.5	849.0	842.6	832.6	819.3	805.9	792.6	779.2	770.9
27.5°	834.2	827.2	820.1	813.1	806.0	795.0	780.0	764.9	749.8	734.8	725.1
30°	810.2	802.5	794.8	787.1	779.4	767.5	751.3	735.1	718.9	702.8	692.4
32.5°	786.8	777.8	768.9	759.9	750.9	738.2	721.7	705.2	688.7	672.2	660.4
35°	748.2	738.0	727.6	717.3	707.0	692.9	675.1	657.4	639.5	621.7	608.9
37.5°	709.7	698.3	687.0	675.6	664.3	649.2	630.3	611.3	592.3	573.3	559.3
40°	682.7	670.6	658.4	646.3	634.2	618.3	598.7	579.1	559.5	539.8	525.5
42.5°	655.1	642.3	629.5	616.7	604.0	587.4	567.1	546.9	526.6	506.3	491.4
45°	611.7	598.2	584.6	571.1	557.5	540.1	518.9	497.7	476.4	455.1	440.8
47.5°	569.4	555.1	540.7	526.4	512.0	493.9	472.0	450.0	428.1	406.2	391.9
50°	538.9	524.5	510.1	495.8	481.4	463.2	440.9	418.7	396.4	374.2	360.2
52.5°	509.1	494.0	479.0	464.0	449.0	430.6	408.8	387.1	365.3	343.6	330.1
55°	465.2	449.4	433.6	417.9	402.1	383.3	361.4	339.6	317.7	295.9	283.7
57.5°	420.2	404.0	387.8	371.7	355.4	336.9	315.8	294.9	273.8	252.9	241.7
60°	389.6	373.4	357.2	341.1	324.9	306.4	285.5	264.7	243.9	223.0	212.7
62.5°	359.7	343.6	327.3	311.2	295.0	277.0	257.2	237.3	217.4	197.5	187.7
65°	314.1	297.7	281.2	264.9	248.5	231.2	213.0	194.8	176.6	158.4	151.5
67.5°	270.0	253.7	237.5	221.2	204.9	188.6	172.2	155.9	139.5	123.1	119.9
70°	239.4	223.6	207.9	192.1	176.3	161.4	147.5	133.5	119.6	105.6	103.5
72.5°	210.3	195.1	180.0	164.9	149.7	136.6	125.4	114.1	103.0	91.8	90.1
75°	167.5	153.4	139.2	125.0	110.8	100.3	93.5	86.6	79.7	72.9	71.4
77.5°	125.5	113.0	100.6	88.2	75.8	67.9	64.6	61.3	58.0	54.7	53.8
80°	99.2	88.9	78.6	68.3	58.0	51.8	49.8	47.7	45.7	43.7	42.9
82.5°	75.2	67.1	59.1	51.0	43.0	38.3	36.9	35.5	34.2	32.8	32.3
85°	39.1	34.9	30.7	26.4	22.1	19.7	19.1	18.5	17.9	17.3	17.3
87.5°	11.8	10.6	9.5	8.5	7.4	7.0	7.5	7.8	8.3	8.6	8.5
90°	0.4	1.5	2.6	3.7	4.7	6.2	8.2	10.2	12.1	14.2	14.0
92.5°	7.2	8.0	8.7	9.5	10.3	11.0	11.4	11.9	12.4	12.8	12.8
95°	21.0	21.9	22.8	23.7	24.6	25.1	25.3	25.5	25.7	25.9	25.9
97.5°	38.3	39.1	39.9	40.8	41.6	42.1	42.4	42.8	43.2	43.4	43.4
100°	51.3	52.0	52.7	53.5	54.2	54.7	54.9	55.2	55.5	55.7	55.7
102.5°	64.9	65.5	66.0	66.6	67.1	67.7	67.9	68.3	68.7	69.0	69.1
105°	86.9	87.1	87.4	87.7	87.9	88.2	88.4	88.5	88.7	88.9	89.1
107.5°	109.0	109.4	109.8	110.2	110.6	110.8	110.8	110.8	110.8	110.8	110.8
110°	123.2	123.8	124.3	124.8	125.4	125.6	125.6	125.6	125.6	125.6	125.6



TEST NUMBER: P331808-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.8	139.3	139.8	140.4	140.9	141.2	141.1	141.0	140.9	140.8	140.6
115°	161.6	162.1	162.6	163.2	163.7	163.9	163.7	163.5	163.4	163.2	163.1
117.5°	184.4	185.1	185.8	186.5	187.3	187.3	186.9	186.4	185.8	185.4	185.1
120°	199.6	200.3	201.0	201.7	202.4	202.4	201.7	201.0	200.3	199.6	199.6
122.5°	213.5	214.4	215.2	216.1	217.0	217.1	216.6	216.1	215.6	215.1	214.9
125°	235.1	235.9	236.7	237.6	238.4	238.6	238.4	238.1	237.8	237.6	237.3
127.5°	256.2	257.3	258.2	259.3	260.3	260.6	260.4	260.0	259.7	259.4	259.0
130°	269.5	270.6	271.8	273.0	274.1	274.6	274.5	274.3	274.1	273.9	273.8
132.5°	284.4	285.3	286.2	287.2	288.1	288.6	288.6	288.7	288.7	288.7	288.4
135°	304.3	305.2	306.2	307.2	308.2	308.7	308.9	309.1	309.2	309.4	309.3
137.5°	325.1	325.9	326.7	327.5	328.3	328.9	329.1	329.4	329.6	329.8	329.8
140°	337.8	338.6	339.4	340.2	341.0	341.6	342.1	342.5	343.0	343.4	343.4
142.5°	350.7	351.5	352.3	353.1	353.9	354.5	354.7	355.1	355.3	355.7	355.8
145°	369.3	369.9	370.5	371.1	371.8	372.4	372.9	373.4	374.0	374.5	374.6
147.5°	385.8	386.6	387.4	388.1	388.9	389.4	389.8	390.1	390.5	390.8	391.0
150°	397.2	397.7	398.2	398.8	399.3	399.8	400.1	400.5	400.8	401.2	401.4
152.5°	407.2	407.7	408.2	408.8	409.3	409.8	410.2	410.6	411.1	411.5	411.9
155°	422.1	422.4	422.7	423.0	423.3	423.6	423.8	424.1	424.4	424.6	425.1
157.5°	435.1	435.2	435.4	435.6	435.8	435.9	436.0	436.2	436.4	436.6	437.2
160°	442.8	443.0	443.2	443.4	443.5	443.6	443.7	443.8	443.9	444.0	444.5
162.5°	449.9	450.0	450.0	450.0	450.0	450.1	450.2	450.3	450.4	450.5	451.0
165°	459.3	459.2	459.1	459.1	459.0	459.0	459.0	459.0	459.0	459.0	459.6
167.5°	467.3	467.0	466.7	466.5	466.2	466.0	466.0	466.0	466.0	466.0	466.6
170°	471.4	471.2	470.9	470.6	470.4	470.2	470.1	470.0	469.9	469.8	470.5
172.5°	474.4	474.1	473.9	473.6	473.3	473.1	473.1	473.0	472.9	472.8	473.4
175°	478.0	477.7	477.4	477.2	476.9	476.6	476.4	476.3	476.1	475.9	476.5
177.5°	479.4	479.2	478.9	478.8	478.5	478.3	478.2	478.0	477.9	477.8	478.2
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8



TEST NUMBER: P331808-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8	1005.8
2.5°	1001.1	1002.7	1004.3	1005.0	1004.7	1004.3	1004.1	1003.7
5°	993.1	995.0	996.8	997.4	996.8	996.1	995.6	995.0
7.5°	977.0	977.6	978.1	977.9	976.8	975.8	974.7	973.7
10°	961.0	960.4	959.7	958.9	957.6	956.4	955.2	954.0
12.5°	942.5	941.5	940.3	938.8	936.7	934.8	932.7	930.7
15°	908.1	904.2	900.4	897.4	895.5	893.4	891.4	889.4
17.5°	869.2	864.5	860.0	856.0	852.5	849.0	845.5	842.0
20°	842.0	836.9	831.8	827.1	822.6	818.1	813.7	809.2
22.5°	812.1	805.6	799.1	794.2	790.8	787.5	784.2	780.9
25°	762.6	754.3	746.0	740.4	737.4	734.3	731.3	728.3
27.5°	715.4	705.8	696.2	688.8	684.0	679.2	674.4	669.6
30°	682.2	671.8	661.5	653.6	648.1	642.7	637.2	631.8
32.5°	648.6	636.9	625.1	616.6	611.4	606.4	601.2	596.1
35°	596.3	583.5	570.8	562.1	557.7	553.2	548.8	544.4
37.5°	545.2	531.2	517.2	507.6	502.5	497.4	492.3	487.2
40°	511.0	496.7	482.3	472.5	467.3	462.0	456.7	451.5
42.5°	476.6	461.7	446.9	436.9	431.9	426.8	421.7	416.5
45°	426.4	412.1	397.7	388.1	383.3	378.4	373.5	368.6
47.5°	377.6	363.4	349.0	339.7	335.3	330.9	326.5	322.1
50°	346.3	332.3	318.3	309.2	305.0	300.7	296.5	292.2
52.5°	316.6	303.1	289.6	281.0	277.1	273.1	269.2	265.3
55°	271.6	259.4	247.3	239.3	235.5	231.6	227.7	223.9
57.5°	230.6	219.5	208.4	201.2	198.0	194.7	191.5	188.2
60°	202.4	192.1	181.7	175.0	171.7	168.5	165.2	162.0
62.5°	177.9	168.0	158.2	152.3	150.3	148.5	146.5	144.5
65°	144.6	137.8	130.9	127.2	126.5	125.9	125.3	124.8
67.5°	116.7	113.6	110.5	108.5	107.9	107.3	106.6	105.9
70°	101.6	99.5	97.5	96.1	95.2	94.4	93.6	92.8
72.5°	88.4	86.7	85.0	83.9	83.4	82.9	82.4	81.9
75°	70.0	68.6	67.1	66.3	66.2	66.0	65.7	65.5
77.5°	53.0	52.2	51.4	50.8	50.5	50.2	49.8	49.5
80°	42.1	41.3	40.5	40.0	40.0	40.0	40.0	40.0
82.5°	31.8	31.3	30.9	30.6	30.6	30.6	30.6	30.6
85°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	8.3	8.0	7.8	7.8	7.8	7.8	7.8	7.8
90°	13.8	13.6	13.5	13.4	13.5	13.6	13.6	13.7
92.5°	12.9	12.9	13.0	13.0	13.0	13.0	13.1	13.1
95°	25.9	25.9	25.9	25.8	25.6	25.4	25.2	25.1
97.5°	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4
100°	55.7	55.7	55.7	55.7	55.6	55.6	55.5	55.4
102.5°	69.1	69.2	69.3	69.3	69.2	69.1	69.0	68.9
105°	89.3	89.4	89.6	89.7	89.7	89.7	89.7	89.7
107.5°	110.9	111.0	111.1	110.9	110.5	110.0	109.7	109.2
110°	125.6	125.6	125.6	125.5	125.2	124.9	124.7	124.4



TEST NUMBER: P331808-940

CATALOG NUMBER: S122RDIW-S675D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	140.4	140.2	140.0	139.7	139.6	139.4	139.2	139.0
115°	163.0	162.9	162.8	162.6	162.4	162.1	161.8	161.6
117.5°	184.9	184.7	184.5	184.2	184.0	183.7	183.4	183.2
120°	199.6	199.6	199.6	199.5	199.2	198.9	198.7	198.4
122.5°	214.6	214.5	214.2	214.0	213.8	213.7	213.4	213.2
125°	237.0	236.7	236.5	236.3	236.2	236.1	236.0	235.9
127.5°	258.7	258.4	258.1	257.8	257.4	257.2	256.9	256.6
130°	273.6	273.4	273.2	273.0	272.6	272.2	271.9	271.5
132.5°	288.0	287.6	287.2	286.9	286.6	286.2	286.0	285.7
135°	309.2	309.2	309.1	308.9	308.6	308.4	308.1	307.8
137.5°	329.7	329.6	329.6	329.3	329.0	328.6	328.2	327.9
140°	343.4	343.4	343.4	343.2	342.9	342.5	342.1	341.8
142.5°	355.8	355.9	356.0	355.8	355.4	355.1	354.7	354.4
145°	374.7	374.8	374.9	374.7	374.3	374.0	373.6	373.3
147.5°	391.2	391.5	391.6	391.6	391.2	390.8	390.5	390.2
150°	401.7	402.0	402.3	402.3	402.0	401.7	401.4	401.2
152.5°	412.1	412.5	412.9	412.9	412.5	412.1	411.9	411.5
155°	425.5	426.0	426.4	426.5	426.2	426.0	425.7	425.4
157.5°	437.7	438.4	439.0	439.1	438.6	438.2	437.8	437.4
160°	445.1	445.6	446.1	446.2	445.9	445.5	445.1	444.8
162.5°	451.7	452.3	452.9	453.0	452.5	452.1	451.7	451.3
165°	460.2	460.8	461.5	461.5	461.1	460.7	460.2	459.8
167.5°	467.3	467.9	468.5	468.6	468.1	467.6	467.2	466.7
170°	471.1	471.7	472.3	472.4	471.9	471.4	470.8	470.3
172.5°	474.0	474.7	475.3	475.3	474.7	474.2	473.7	473.1
175°	477.2	477.8	478.4	478.5	478.0	477.4	476.9	476.4
177.5°	478.7	479.0	479.5	479.5	479.0	478.7	478.2	477.8
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8

(END OF REPORT)