

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332452-930

Luminaire Tested: **S123RDIW-S1000D460U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332452-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D460U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4595.8 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332452-930

CATALOG NUMBER: S123RDIW-S1000D460U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332452-930

CATALOG NUMBER: S123RDIW-S1000D460U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	62	58
2	93	86	80	75	88	81	76	71	73	68	65	65	61	59	57	55	53	49
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	68	60	54	74	64	57	51	58	52	47	52	47	43	46	42	39	36
5	72	61	52	46	68	58	50	45	52	46	41	46	42	38	42	38	35	32
6	67	55	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31	28
7	62	49	41	36	58	47	40	35	43	37	32	39	34	30	35	31	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	25	22	20
10	50	38	31	26	48	36	30	25	33	28	24	30	25	22	27	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14727	14727	14727
5°	14783	14579	14664
10°	14700	14397	14348
15°	14542	14060	13912
20°	14325	13639	13321
25°	14101	13166	12744
30°	13806	12621	11931
35°	13502	12073	11184
40°	13222	11428	10260
45°	12855	10794	9426
50°	12450	10071	8492
55°	12037	9246	7621
60°	11657	8361	6665
65°	11163	7404	5708
70°	10546	6216	4611
75°	9649	4891	4338
80°	8598	4333	3986
85°	7262	3841	3569



TEST NUMBER: P332452-930

CATALOG NUMBER: S123RDIW-S1000D460U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	2.8
10°-20°	357.5	7.8
20°-30°	514.7	11.2
30°-40°	579.8	12.6
40°-50°	554.7	12.1
50°-60°	454.2	9.9
60°-70°	306.5	6.7
70°-80°	154.2	3.4
80°-90°	42.2	0.9
90°-100°	17.9	0.4
100°-110°	85.4	1.9
110°-120°	205.2	4.5
120°-130°	261.3	5.7
130°-140°	279.2	6.1
140°-150°	261.1	5.7
150°-160°	210.6	4.6
160°-170°	135.9	3.0
170°-180°	46.8	1.0
0°-30°	1000.7	21.8
0°-40°	1580.5	34.4
0°-60°	2589.5	56.3
0°-90°	3092.3	67.3
90°-120°	308.6	6.7
90°-150°	1110.2	24.2
90°-180°	1504.0	32.7
0°-180°	4595.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1368	1368	1368	1368	1368	
5°	1368	1362	1349	1359	1357	130
15°	1305	1292	1262	1256	1248	367
25°	1187	1158	1109	1086	1073	546
35°	1028	986	919	873	851	643
45°	844	793	709	648	619	651
55°	641	585	493	431	406	575
65°	438	376	291	239	224	434
75°	232	178	118	107	104	247
85°	59	36	31	29	29	66
90°	0	4	9	10	11	4
95°	22	8	11	14	14	28
105°	109	111	80	19	16	116
115°	205	207	210	214	215	202
125°	289	291	293	294	294	258
135°	359	362	363	364	363	277
145°	415	417	418	419	419	259
155°	457	456	456	458	456	210
165°	482	481	480	483	481	136
175°	493	491	492	494	491	47
180°	493	493	493	493	493	



TEST NUMBER: P332452-930

CATALOG NUMBER: S123RDIW-S1000D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1372.6	1371.8	1371.1	1370.3	1369.5	1367.9	1365.5	1363.2	1360.8	1358.5	1360.6
5°	1368.2	1366.9	1365.7	1364.5	1363.3	1361.1	1358.2	1355.3	1352.3	1349.3	1351.5
7.5°	1355.5	1354.2	1352.9	1351.5	1350.2	1347.6	1343.8	1339.9	1336.1	1332.3	1333.5
10°	1344.9	1343.2	1341.4	1339.7	1338.0	1334.9	1330.5	1326.0	1321.6	1317.2	1317.4
12.5°	1329.8	1327.9	1326.0	1324.0	1322.1	1318.4	1313.0	1307.6	1302.2	1296.7	1296.6
15°	1305.0	1302.3	1299.5	1296.8	1294.1	1289.3	1282.4	1275.5	1268.6	1261.7	1260.5
17.5°	1273.7	1270.5	1267.4	1264.2	1261.0	1255.1	1246.3	1237.5	1228.7	1219.9	1217.3
20°	1250.6	1246.7	1242.7	1238.8	1234.8	1228.2	1218.8	1209.4	1200.0	1190.7	1187.5
22.5°	1224.8	1220.3	1215.8	1211.2	1206.7	1199.5	1189.4	1179.5	1169.5	1159.6	1155.6
25°	1187.3	1181.2	1175.0	1168.8	1162.7	1153.9	1142.6	1131.2	1119.9	1108.6	1103.3
27.5°	1141.8	1135.1	1128.2	1121.4	1114.6	1104.9	1092.3	1079.6	1067.0	1054.4	1047.2
30°	1110.8	1103.3	1096.0	1088.6	1081.2	1070.6	1056.8	1042.9	1029.2	1015.4	1007.0
32.5°	1079.7	1071.3	1062.9	1054.5	1046.2	1034.7	1020.1	1005.5	990.8	976.2	967.1
35°	1027.5	1018.6	1009.7	1000.9	992.1	979.9	964.7	949.3	934.1	918.8	908.2
37.5°	974.7	964.8	955.0	945.1	935.2	922.2	905.9	889.5	873.2	856.9	844.8
40°	941.0	930.2	919.2	908.4	897.6	883.4	865.9	848.4	830.9	813.3	800.5
42.5°	902.8	891.9	881.1	870.3	859.4	845.0	826.9	808.8	790.7	772.6	758.6
45°	844.5	833.3	822.2	811.1	800.1	785.1	766.1	747.1	728.1	709.1	695.0
47.5°	786.1	773.9	761.7	749.5	737.4	721.8	702.8	683.8	664.8	645.8	630.6
50°	743.5	731.9	720.3	708.7	697.1	681.3	661.4	641.4	621.4	601.4	586.1
52.5°	705.3	692.8	680.1	667.6	655.0	638.8	619.1	599.2	579.5	559.7	543.8
55°	641.4	629.3	617.2	605.1	593.0	576.5	555.5	534.6	513.6	492.7	478.4
57.5°	582.4	569.2	556.0	542.8	529.7	512.6	491.5	470.4	449.4	428.4	414.8
60°	541.5	528.0	514.4	500.8	487.2	470.3	449.8	429.3	408.9	388.4	375.0
62.5°	500.7	487.1	473.5	460.0	446.5	429.4	409.0	388.5	368.0	347.6	335.0
65°	438.3	424.8	411.2	397.6	384.1	367.7	348.5	329.2	310.0	290.7	278.7
67.5°	375.9	362.2	348.5	334.8	321.1	305.0	286.6	268.2	249.7	231.2	222.3
70°	335.1	321.8	308.5	295.1	281.8	266.6	249.3	232.0	214.7	197.5	188.9
72.5°	294.2	281.2	268.1	254.9	241.8	227.4	211.7	196.1	180.3	164.7	157.6
75°	232.0	220.0	208.2	196.4	184.6	171.9	158.3	144.7	131.2	117.6	115.1
77.5°	175.1	164.4	153.7	143.0	132.3	122.5	113.8	105.1	96.4	87.6	86.3
80°	138.7	128.6	118.5	108.4	98.2	90.7	85.4	80.2	75.1	69.9	69.1
82.5°	104.1	95.4	86.7	77.9	69.1	63.6	61.1	58.8	56.3	53.9	53.2
85°	58.8	53.4	47.9	42.6	37.1	34.0	33.3	32.5	31.8	31.1	30.6
87.5°	21.4	19.4	17.4	15.3	13.4	12.5	12.6	12.9	13.1	13.3	13.1
90°	0.3	1.1	2.0	2.8	3.6	4.6	5.6	6.7	7.7	8.8	9.1
92.5°	6.8	6.6	6.4	6.1	5.9	6.2	7.0	7.7	8.6	9.4	9.9
95°	22.3	19.0	15.7	12.3	9.0	7.7	8.6	9.5	10.4	11.3	11.9
97.5°	44.9	43.4	41.9	40.4	38.9	35.2	29.4	23.5	17.7	11.8	12.5
100°	61.9	63.5	65.1	66.8	68.4	62.9	50.2	37.5	24.8	12.1	12.7
102.5°	81.2	82.4	83.6	84.8	85.9	79.6	65.7	51.9	38.0	24.1	22.1
105°	109.2	110.1	111.0	111.9	112.8	109.5	102.2	94.9	87.6	80.2	65.8
107.5°	138.6	139.3	140.1	140.7	141.5	142.4	143.6	144.7	145.9	147.0	136.5
110°	158.2	158.9	159.6	160.2	160.9	161.6	162.5	163.4	164.3	165.2	162.5



TEST NUMBER: P332452-930

CATALOG NUMBER: S123RDIW-S1000D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	177.0	177.6	178.1	178.7	179.4	180.1	181.0	181.9	182.8	183.7	183.7
115°	204.7	205.2	205.7	206.2	206.7	207.3	208.1	208.8	209.5	210.3	211.1
117.5°	231.6	232.3	232.8	233.4	234.1	234.6	234.9	235.3	235.7	236.0	236.7
120°	248.3	249.1	249.8	250.5	251.3	251.8	252.0	252.3	252.5	252.7	253.4
122.5°	265.4	266.0	266.5	267.2	267.7	268.2	268.6	268.8	269.1	269.5	269.9
125°	288.6	289.3	289.9	290.6	291.2	291.7	292.0	292.4	292.7	293.0	293.2
127.5°	311.2	311.9	312.5	313.2	313.8	314.3	314.7	315.1	315.5	315.9	316.2
130°	325.3	326.0	326.6	327.3	327.9	328.4	328.7	329.1	329.4	329.6	330.0
132.5°	338.8	339.4	340.1	340.7	341.4	341.8	342.1	342.3	342.6	342.8	343.2
135°	359.3	359.8	360.3	360.8	361.3	361.7	362.0	362.3	362.6	363.0	363.2
137.5°	376.9	377.6	378.1	378.8	379.4	379.8	380.0	380.2	380.3	380.5	380.9
140°	388.7	389.1	389.6	390.1	390.6	390.9	391.2	391.4	391.7	391.9	392.2
142.5°	399.5	400.0	400.5	401.0	401.5	401.8	402.0	402.3	402.5	402.8	403.0
145°	414.7	415.2	415.8	416.4	416.9	417.3	417.4	417.6	417.8	417.9	418.1
147.5°	428.9	429.3	429.7	430.1	430.4	430.7	430.9	431.0	431.2	431.4	431.5
150°	437.7	438.0	438.2	438.5	438.7	438.9	439.0	439.2	439.4	439.5	439.7
152.5°	445.6	445.7	445.9	446.0	446.1	446.2	446.3	446.4	446.5	446.6	446.9
155°	456.7	456.6	456.4	456.3	456.2	456.1	456.2	456.2	456.3	456.4	456.8
157.5°	465.5	465.4	465.4	465.4	465.4	465.3	465.2	465.1	465.0	465.0	465.5
160°	470.7	470.6	470.5	470.4	470.3	470.3	470.2	470.1	470.0	469.9	470.4
162.5°	475.6	475.5	475.2	475.1	474.8	474.7	474.6	474.5	474.4	474.3	474.9
165°	481.7	481.4	481.2	480.9	480.7	480.5	480.5	480.4	480.3	480.2	480.9
167.5°	486.4	486.1	485.8	485.4	485.1	484.9	484.9	484.9	484.9	484.9	485.6
170°	489.0	488.7	488.4	488.0	487.7	487.5	487.5	487.5	487.5	487.5	488.2
172.5°	490.7	490.4	490.0	489.6	489.2	489.0	489.1	489.2	489.3	489.3	489.9
175°	493.0	492.6	492.2	491.8	491.4	491.2	491.3	491.4	491.5	491.5	492.1
177.5°	493.6	493.3	492.9	492.6	492.3	492.2	492.3	492.3	492.4	492.4	492.9
180°	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0



TEST NUMBER: P332452-930

CATALOG NUMBER: S123RDIW-S1000D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2	1368.2
2.5°	1362.8	1365.0	1367.1	1368.0	1367.6	1367.3	1366.8	1366.4
5°	1353.8	1356.0	1358.2	1359.1	1358.6	1358.1	1357.6	1357.1
7.5°	1334.7	1335.9	1337.2	1337.4	1336.5	1335.7	1334.9	1334.0
10°	1317.7	1317.9	1318.2	1317.7	1316.4	1315.2	1313.9	1312.7
12.5°	1296.4	1296.3	1296.2	1295.3	1294.0	1292.5	1291.1	1289.6
15°	1259.2	1258.0	1256.8	1255.2	1253.5	1251.8	1250.1	1248.4
17.5°	1214.7	1212.1	1209.5	1206.9	1204.4	1201.8	1199.2	1196.6
20°	1184.2	1181.0	1177.9	1174.8	1171.8	1168.8	1165.9	1162.9
22.5°	1151.6	1147.6	1143.6	1140.2	1137.5	1134.7	1132.0	1129.2
25°	1098.2	1093.0	1087.9	1083.9	1081.2	1078.5	1075.8	1073.0
27.5°	1040.0	1032.8	1025.6	1019.9	1015.8	1011.6	1007.5	1003.4
30°	998.6	990.2	981.8	975.7	971.7	967.8	963.8	959.9
32.5°	957.9	948.8	939.6	932.9	928.8	924.6	920.5	916.3
35°	897.6	887.0	876.4	868.9	864.5	860.0	855.6	851.1
37.5°	832.8	820.8	808.8	800.0	794.5	789.0	783.6	778.1
40°	787.7	774.9	762.1	752.8	747.1	741.5	735.8	730.2
42.5°	744.5	730.5	716.5	706.9	701.9	696.8	691.7	686.6
45°	680.9	666.9	652.8	642.9	636.9	631.0	625.1	619.2
47.5°	615.2	600.0	584.7	574.4	569.1	563.9	558.6	553.3
50°	570.9	555.5	540.3	529.8	524.2	518.4	512.8	507.1
52.5°	528.0	512.1	496.2	485.7	480.6	475.6	470.5	465.4
55°	464.1	449.8	435.5	425.8	420.9	416.0	411.1	406.1
57.5°	401.3	387.8	374.3	365.4	361.3	357.0	352.9	348.6
60°	361.7	348.5	335.1	326.4	322.2	318.0	313.8	309.6
62.5°	322.5	310.0	297.4	288.9	284.6	280.2	275.8	271.4
65°	266.6	254.5	242.4	235.0	232.3	229.6	226.9	224.1
67.5°	213.2	204.2	195.2	189.1	186.3	183.4	180.4	177.6
70°	180.3	171.6	163.0	157.4	154.6	151.9	149.2	146.5
72.5°	150.6	143.5	136.5	132.4	131.3	130.1	129.0	127.8
75°	112.7	110.2	107.8	106.3	105.8	105.3	104.8	104.3
77.5°	85.0	83.6	82.3	81.4	81.0	80.5	80.0	79.5
80°	68.4	67.7	66.9	66.4	65.9	65.4	64.8	64.3
82.5°	52.4	51.7	51.0	50.5	50.5	50.4	50.2	50.1
85°	30.1	29.6	29.1	28.9	28.9	28.9	28.9	28.9
87.5°	13.0	12.9	12.8	12.6	12.5	12.3	12.1	12.0
90°	9.5	9.8	10.1	10.4	10.5	10.7	10.8	11.0
92.5°	10.4	10.9	11.5	11.7	11.9	12.0	12.1	12.1
95°	12.5	13.0	13.6	13.9	13.9	13.9	13.9	13.9
97.5°	13.1	13.8	14.4	14.8	14.8	14.9	15.0	15.1
100°	13.4	14.0	14.7	15.1	15.2	15.2	15.3	15.4
102.5°	20.1	18.0	16.1	15.1	15.2	15.4	15.5	15.7
105°	51.4	37.0	22.6	15.5	15.7	15.8	16.0	16.1
107.5°	125.9	115.4	104.8	94.1	83.2	72.3	61.5	50.6
110°	159.8	157.1	154.4	147.3	135.7	124.0	112.3	100.8



TEST NUMBER: P332452-930

CATALOG NUMBER: S123RDIW-S1000D460U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	183.8	183.8	183.8	182.6	180.2	177.7	175.3	172.8
115°	211.9	212.7	213.5	214.1	214.4	214.7	215.1	215.4
117.5°	237.3	238.0	238.6	239.0	239.0	239.1	239.2	239.3
120°	254.0	254.7	255.4	255.7	255.7	255.7	255.7	255.7
122.5°	270.4	270.8	271.3	271.5	271.6	271.7	271.7	271.8
125°	293.3	293.5	293.7	293.8	294.0	294.2	294.3	294.5
127.5°	316.4	316.7	316.9	317.0	316.8	316.7	316.5	316.3
130°	330.3	330.6	330.9	331.0	330.8	330.7	330.5	330.4
132.5°	343.5	343.8	344.1	344.2	344.0	343.7	343.5	343.3
135°	363.5	363.7	363.9	363.9	363.7	363.5	363.2	363.0
137.5°	381.3	381.6	382.0	382.2	382.0	381.9	381.7	381.6
140°	392.6	392.9	393.2	393.3	393.1	393.0	392.8	392.6
142.5°	403.3	403.6	403.8	403.8	403.6	403.4	403.2	402.9
145°	418.2	418.4	418.6	418.7	418.7	418.7	418.7	418.7
147.5°	431.7	431.9	432.0	431.9	431.5	431.1	430.8	430.4
150°	439.9	440.0	440.2	440.2	439.9	439.7	439.4	439.2
152.5°	447.2	447.4	447.8	447.7	447.4	446.9	446.6	446.2
155°	457.2	457.6	458.0	458.0	457.5	457.0	456.5	456.1
157.5°	465.9	466.4	466.9	466.8	466.2	465.6	465.0	464.3
160°	470.9	471.4	471.9	471.9	471.3	470.8	470.2	469.6
162.5°	475.5	476.1	476.5	476.6	476.1	475.6	475.1	474.6
165°	481.5	482.2	482.8	482.8	482.2	481.8	481.2	480.6
167.5°	486.2	486.8	487.5	487.5	486.8	486.2	485.6	484.9
170°	488.9	489.5	490.2	490.2	489.5	488.9	488.2	487.5
172.5°	490.6	491.2	491.9	491.9	491.1	490.4	489.8	489.0
175°	492.7	493.3	493.8	493.8	493.2	492.5	491.9	491.2
177.5°	493.5	494.0	494.6	494.5	493.8	493.2	492.5	491.9
180°	493.0	493.0	493.0	493.0	493.0	493.0	493.0	493.0

(END OF REPORT)