

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331813-940

Luminaire Tested: **S122RDIW-S675D970U940-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331813-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S675D970U940-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5717.7 lumens  
Efficiency: N/A  
Efficacy: 108.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	40	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	36	35	30
3	81	72	65	60	73	66	60	55	54	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	23	22	19
7	58	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	39	33	28	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	25	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21151	21151	21151	21151
5°	23622	21284	18870	21284
10°	26209	21135	16357	21135
15°	27497	20824	12889	20824
20°	23838	20366	11153	20366
25°	15634	19737	9957	19737
30°	10524	18975	9012	18975
35°	8523	18015	8129	18015
40°	7579	16971	7522	16971
45°	6859	15746	6715	15746
50°	6242	14531	6219	14531
55°	5869	13185	5790	13185
60°	4908	11951	4850	11951
65°	4138	10850	4695	10850
70°	3829	9692	4428	9692
75°	3575	8434	4086	8434
80°	3301	6936	3636	6936
85°	3038	5483	3205	5483



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	124.2	2.2
10°-20°	346.0	6.1
20°-30°	445.9	7.8
30°-40°	423.7	7.4
40°-50°	363.0	6.3
50°-60°	276.4	4.8
60°-70°	174.7	3.1
70°-80°	87.3	1.5
80°-90°	25.6	0.4
90°-100°	39.3	0.7
100°-110°	144.0	2.5
110°-120°	385.0	6.7
120°-130°	635.6	11.1
130°-140°	675.9	11.8
140°-150°	628.3	11.0
150°-160°	505.1	8.8
160°-170°	325.5	5.7
170°-180°	112.0	2.0
0°-30°	916.1	16.0
0°-40°	1339.8	23.4
0°-60°	1979.2	34.6
0°-90°	2266.9	39.6
90°-120°	568.4	9.9
90°-150°	2508.2	43.9
90°-180°	3451.0	60.4
0°-180°	5717.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1310	1310	1310	1310	1310	
5°	1458	1313	1164	1313	1458	144
15°	1645	1246	771	1246	1645	444
25°	878	1108	559	1108	878	416
35°	432	914	412	914	432	277
45°	300	690	294	690	300	232
55°	208	468	206	468	208	183
65°	108	284	123	284	108	110
75°	57	135	66	135	57	61
85°	16	30	17	30	16	18
90°	23	1	23	1	23	11
95°	37	55	37	55	37	34
105°	65	259	65	259	65	67
115°	70	490	70	490	70	175
125°	728	693	728	693	728	630
135°	885	857	885	857	885	682
145°	1010	994	1010	994	1010	631
155°	1096	1095	1096	1095	1096	506
165°	1151	1154	1151	1154	1151	325
175°	1173	1180	1173	1180	1173	112
180°	1178	1178	1178	1178	1178	



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1363.2	1364.2	1365.4	1362.8	1362.8	1360.6	1355.8	1352.3	1342.0	1340.6	1340.6
5°	1457.5	1456.5	1458.4	1452.5	1444.3	1442.4	1433.8	1422.5	1410.6	1397.4	1394.6
7.5°	1551.2	1549.9	1546.2	1545.2	1538.9	1525.2	1511.3	1496.5	1476.8	1457.6	1448.0
10°	1598.6	1613.6	1604.5	1588.6	1591.8	1570.4	1559.0	1539.4	1523.0	1494.3	1488.0
12.5°	1645.2	1651.1	1648.2	1639.1	1635.0	1620.2	1604.9	1587.9	1557.6	1531.9	1509.5
15°	1645.0	1653.7	1655.9	1653.2	1655.5	1654.6	1646.4	1632.3	1605.9	1577.6	1553.1
17.5°	1523.6	1529.6	1544.5	1554.6	1567.4	1594.3	1607.6	1612.7	1608.8	1592.8	1575.5
20°	1387.4	1377.3	1419.2	1440.6	1458.8	1504.3	1543.5	1558.5	1582.6	1582.2	1577.6
22.5°	1194.4	1196.8	1236.4	1261.9	1315.0	1360.5	1405.2	1461.7	1508.3	1539.2	1557.3
25°	877.6	894.9	934.5	969.1	1028.2	1112.9	1189.8	1279.1	1363.2	1429.7	1493.0
27.5°	659.1	660.4	691.8	723.7	758.8	828.2	925.1	1031.6	1151.6	1250.7	1364.7
30°	564.5	561.7	574.9	594.5	624.5	678.2	751.0	855.8	975.4	1124.7	1257.7
32.5°	497.4	497.6	507.6	522.0	547.0	583.2	633.0	718.1	831.3	978.0	1133.8
35°	432.4	431.9	439.3	449.7	460.2	483.4	517.5	562.1	640.0	776.9	936.3
37.5°	385.8	387.8	391.4	397.9	409.5	422.4	442.9	472.9	528.2	609.3	743.2
40°	359.6	360.5	365.5	371.0	377.8	387.8	404.7	428.7	469.3	534.0	631.8
42.5°	335.6	336.4	340.0	345.1	350.4	360.5	374.4	395.3	428.1	478.6	559.3
45°	300.4	300.4	303.6	305.9	311.8	320.9	332.3	349.6	372.4	409.7	463.3
47.5°	267.4	267.5	269.7	273.6	277.3	284.4	295.6	309.7	326.3	355.2	401.0
50°	248.5	249.0	250.3	253.5	255.8	262.2	270.8	283.1	300.4	322.7	361.0
52.5°	233.3	232.9	234.7	236.0	237.6	242.2	248.6	259.5	274.9	294.4	326.0
55°	208.5	206.6	209.4	211.7	213.0	214.8	218.5	225.3	238.5	254.9	278.6
57.5°	177.5	176.8	178.7	180.8	185.1	190.0	193.1	197.4	204.3	216.1	239.5
60°	152.0	152.0	156.1	157.5	162.5	168.9	175.2	178.9	185.7	193.4	210.7
62.5°	129.5	129.8	131.7	133.1	135.9	143.7	152.7	160.7	167.1	174.5	186.0
65°	108.3	109.2	109.2	110.1	112.0	113.8	117.4	123.8	135.2	145.6	154.3
67.5°	91.9	92.2	92.5	93.4	93.9	95.9	97.3	100.1	102.8	112.7	123.4
70°	81.1	82.4	81.9	82.8	83.3	84.2	86.1	87.4	91.5	93.8	100.1
72.5°	70.8	71.8	71.7	72.3	73.5	73.7	75.1	76.5	79.1	81.1	84.4
75°	57.3	56.9	57.3	58.2	58.7	59.2	59.2	61.0	62.3	64.2	66.4
77.5°	44.2	44.7	44.6	44.7	44.8	45.6	45.5	46.4	47.7	48.6	49.7
80°	35.5	35.9	35.5	35.9	36.4	36.8	36.4	36.8	38.3	39.1	39.1
82.5°	27.5	27.6	27.8	27.9	28.0	28.1	28.8	28.9	29.9	29.7	30.1
85°	16.4	16.0	16.0	16.0	16.4	16.9	16.4	16.4	16.9	16.9	16.9
87.5°	10.4	10.7	10.6	10.5	10.5	10.3	10.2	10.3	9.8	10.0	9.3
90°	23.0	22.6	22.2	21.8	21.5	20.9	19.9	18.9	18.0	17.0	15.5
92.5°	23.0	22.7	22.6	22.3	22.1	21.8	21.2	20.8	20.2	19.8	19.0
95°	36.6	36.8	37.0	37.2	37.4	37.0	36.1	35.1	34.2	33.3	31.9
97.5°	48.9	48.7	48.4	48.2	48.0	47.5	46.7	46.0	45.2	44.5	41.4
100°	57.1	56.7	56.4	55.9	55.6	54.7	53.1	51.6	50.1	48.6	45.4
102.5°	61.2	60.6	60.1	59.6	59.0	57.8	55.8	53.9	51.9	49.9	46.9
105°	64.7	64.0	63.2	62.5	61.7	60.3	58.2	56.2	54.0	52.0	49.7
107.5°	66.6	65.9	65.1	64.4	63.6	64.3	66.4	68.5	70.6	72.8	76.9
110°	67.3	66.5	65.8	65.0	64.3	73.4	92.3	111.2	130.2	149.1	203.8



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	68.0	67.4	66.8	66.2	65.5	99.8	168.9	237.9	307.0	376.1	389.6
115°	69.9	83.5	97.1	110.8	124.4	175.0	262.7	350.4	438.0	525.8	521.0
117.5°	285.3	330.1	374.9	419.6	464.5	497.5	518.7	539.8	561.1	582.3	579.1
120°	519.8	545.3	570.9	596.5	622.0	633.6	631.3	629.1	626.9	624.6	621.2
122.5°	648.6	653.5	658.5	663.4	668.4	670.2	668.9	667.5	666.1	664.8	661.0
125°	728.5	727.9	727.4	726.8	726.2	725.3	724.0	722.6	721.3	720.0	716.4
127.5°	778.9	778.8	778.7	778.6	778.5	777.5	775.5	773.6	771.7	769.7	767.0
130°	810.3	810.5	810.7	810.8	811.1	810.1	808.1	805.9	803.9	801.8	799.7
132.5°	841.0	841.2	841.3	841.5	841.8	841.0	839.2	837.4	835.6	833.8	831.7
135°	885.3	885.6	886.0	886.4	886.8	886.0	884.1	882.3	880.4	878.5	876.7
137.5°	925.7	926.3	926.9	927.6	928.3	927.6	925.8	923.9	922.1	920.2	918.3
140°	950.9	951.8	952.8	953.8	954.7	954.3	952.6	950.9	949.2	947.5	945.4
142.5°	975.4	976.4	977.3	978.3	979.2	978.9	977.4	975.8	974.3	972.7	970.4
145°	1009.7	1010.7	1011.6	1012.5	1013.5	1013.3	1012.0	1010.7	1009.3	1008.0	1004.8
147.5°	1039.8	1040.6	1041.4	1042.2	1043.0	1042.9	1042.0	1041.0	1040.0	1039.0	1035.8
150°	1058.3	1059.2	1060.2	1061.1	1062.0	1061.9	1060.8	1059.7	1058.5	1057.4	1054.4
152.5°	1074.0	1075.2	1076.5	1077.7	1079.0	1079.0	1077.8	1076.7	1075.6	1074.4	1071.6
155°	1095.7	1097.3	1098.8	1100.3	1101.8	1102.0	1100.8	1099.7	1098.6	1097.4	1095.2
157.5°	1115.7	1117.1	1118.7	1120.1	1121.6	1121.7	1120.4	1119.1	1117.8	1116.5	1114.9
160°	1127.3	1128.6	1129.9	1131.2	1132.6	1132.7	1131.5	1130.4	1129.3	1128.1	1127.0
162.5°	1136.8	1138.4	1140.1	1141.7	1143.4	1143.5	1142.2	1140.9	1139.6	1138.4	1137.4
165°	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1	1150.6
167.5°	1160.2	1161.9	1163.6	1165.3	1167.0	1167.2	1165.8	1164.5	1163.1	1161.9	1161.4
170°	1165.6	1167.3	1169.0	1170.7	1172.4	1172.6	1171.3	1170.0	1168.7	1167.3	1167.0
172.5°	1169.7	1171.4	1173.1	1174.8	1176.5	1176.7	1175.4	1174.0	1172.8	1171.4	1171.0
175°	1173.3	1175.2	1177.1	1178.9	1180.9	1181.2	1179.8	1178.5	1177.1	1175.8	1175.5
177.5°	1175.5	1176.9	1178.2	1179.6	1181.0	1181.1	1180.0	1179.0	1177.9	1176.9	1176.7
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1341.3	1338.4	1335.9	1329.3	1326.1	1318.8	1317.7	1317.3	1307.8	1298.7	1296.2
5°	1387.4	1380.1	1369.1	1356.4	1343.2	1329.5	1320.4	1313.2	1294.9	1277.6	1267.7
7.5°	1433.8	1418.2	1399.3	1375.2	1355.0	1332.5	1315.7	1300.7	1274.9	1250.1	1233.4
10°	1468.4	1442.9	1417.9	1384.6	1358.7	1333.2	1309.6	1289.1	1259.9	1227.2	1203.9
12.5°	1489.9	1461.9	1427.4	1394.8	1361.3	1328.8	1297.2	1270.9	1236.6	1202.7	1175.2
15°	1518.9	1488.9	1447.0	1400.6	1357.4	1315.0	1278.6	1245.8	1201.2	1160.7	1127.0
17.5°	1542.7	1501.4	1456.3	1402.7	1352.6	1298.8	1251.9	1210.1	1160.4	1111.5	1071.8
20°	1550.3	1509.4	1457.5	1403.7	1344.6	1281.3	1230.8	1185.3	1132.0	1078.8	1033.2
22.5°	1545.6	1513.8	1456.0	1391.8	1331.1	1264.9	1207.8	1155.0	1096.0	1041.6	988.8
25°	1513.5	1502.5	1448.0	1377.8	1308.7	1231.7	1165.7	1107.9	1040.5	982.3	924.9
27.5°	1438.5	1462.1	1428.3	1353.6	1276.7	1194.2	1120.0	1054.2	984.3	918.7	861.6
30°	1366.5	1420.6	1406.0	1336.9	1250.8	1169.8	1086.5	1017.8	943.2	875.7	819.3
32.5°	1267.7	1357.3	1371.5	1313.6	1224.6	1135.6	1048.3	979.9	902.0	831.0	776.0
35°	1110.6	1244.5	1305.9	1269.0	1179.8	1083.8	993.6	914.0	835.7	765.6	711.0
37.5°	923.2	1105.5	1207.8	1210.5	1128.5	1028.7	930.6	851.5	771.3	702.5	643.5
40°	801.6	999.1	1132.5	1162.1	1092.9	985.0	885.7	805.2	726.9	659.5	591.7
42.5°	692.3	889.1	1053.1	1104.6	1049.5	942.4	842.8	758.6	682.5	618.8	549.5
45°	559.9	731.9	912.7	1004.6	974.1	874.9	769.7	689.6	618.1	563.0	496.6
47.5°	472.3	593.5	768.4	892.8	892.2	801.6	698.2	621.5	555.3	503.6	449.8
50°	422.4	528.0	675.9	817.1	828.8	752.9	654.5	578.5	516.7	462.4	419.2
52.5°	377.6	464.7	597.6	732.9	766.6	700.8	605.4	535.2	475.1	425.3	388.3
55°	319.1	386.5	487.5	614.0	665.0	618.6	534.0	468.4	419.6	377.8	345.9
57.5°	269.9	320.5	401.5	503.5	562.8	533.6	463.7	410.5	368.8	330.9	305.8
60°	239.0	280.4	349.1	434.3	499.8	479.3	419.6	370.1	334.6	301.8	278.1
62.5°	209.8	245.4	304.3	373.4	433.5	425.1	376.3	334.7	303.6	273.8	253.7
65°	168.9	194.8	240.8	295.0	343.2	347.3	312.3	284.0	256.3	232.6	214.8
67.5°	134.5	151.4	183.8	229.4	265.6	278.5	257.1	235.5	213.5	195.2	179.8
70°	113.3	127.0	150.7	187.5	220.8	234.4	222.1	205.3	186.2	171.1	157.9
72.5°	91.8	105.1	122.6	149.6	178.2	192.9	188.6	176.6	161.0	148.6	136.1
75°	69.2	73.3	85.2	103.3	125.6	138.4	141.6	135.2	122.9	113.3	106.0
77.5°	51.2	53.6	59.3	68.8	83.4	94.8	99.4	98.7	90.2	84.6	77.8
80°	40.9	42.4	45.0	49.1	60.1	71.4	74.6	74.6	68.8	66.4	59.7
82.5°	31.1	32.1	33.8	36.0	41.1	51.1	54.7	55.4	51.6	48.6	43.2
85°	17.7	17.3	18.2	19.5	20.5	23.2	28.7	29.6	28.7	25.1	23.6
87.5°	9.0	9.1	8.7	8.0	7.9	7.9	9.4	10.7	9.7	9.0	8.7
90°	14.0	12.5	11.0	9.2	7.1	5.0	2.9	0.9	2.9	5.0	7.1
92.5°	18.3	17.5	16.8	16.5	16.7	16.9	17.0	17.2	17.0	16.9	16.7
95°	30.6	29.2	27.9	30.4	36.6	42.9	49.1	55.4	49.1	42.9	36.6
97.5°	38.3	35.3	32.2	39.5	57.1	74.7	92.3	109.9	92.3	74.7	57.1
100°	42.1	38.9	35.7	47.1	73.0	98.9	124.8	150.8	124.8	98.9	73.0
102.5°	103.8	130.7	157.7	173.8	179.3	184.9	190.3	195.8	190.3	184.9	179.3
105°	155.3	207.1	258.8	281.8	276.1	270.4	264.7	259.0	264.7	270.4	276.1
107.5°	196.7	258.8	320.7	349.5	344.8	340.3	335.7	331.1	335.7	340.3	344.8
110°	258.6	313.3	368.0	393.3	389.4	385.4	381.5	377.5	381.5	385.4	389.4





TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	403.1	416.7	430.2	435.2	431.7	428.1	424.6	421.1	424.6	428.1	431.7
115°	516.2	511.5	506.8	502.8	499.6	496.4	493.1	489.9	493.1	496.4	499.6
117.5°	575.8	572.6	569.3	565.9	562.2	558.7	555.1	551.4	555.1	558.7	562.2
120°	617.8	614.3	610.9	607.8	604.9	602.1	599.3	596.5	599.3	602.1	604.9
122.5°	657.4	653.6	650.0	646.6	643.5	640.6	637.6	634.6	637.6	640.6	643.5
125°	712.8	709.2	705.6	702.6	700.1	697.7	695.2	692.7	695.2	697.7	700.1
127.5°	764.4	761.7	759.0	756.3	753.6	750.8	748.1	745.4	748.1	750.8	753.6
130°	797.6	795.5	793.4	790.9	787.8	784.9	781.9	778.8	781.9	784.9	787.8
132.5°	829.6	827.6	825.5	823.1	820.6	818.1	815.5	812.9	815.5	818.1	820.6
135°	875.0	873.3	871.6	869.3	866.3	863.3	860.2	857.2	860.2	863.3	866.3
137.5°	916.3	914.4	912.5	910.4	908.4	906.2	904.1	902.0	904.1	906.2	908.4
140°	943.3	941.2	939.1	937.4	935.9	934.3	932.8	931.3	932.8	934.3	935.9
142.5°	968.0	965.5	963.1	961.3	959.9	958.6	957.2	955.8	957.2	958.6	959.9
145°	1001.6	998.4	995.1	993.6	993.8	994.0	994.2	994.3	994.2	994.0	993.8
147.5°	1032.6	1029.5	1026.3	1025.0	1025.7	1026.4	1027.2	1028.0	1027.2	1026.4	1025.7
150°	1051.3	1048.3	1045.3	1044.5	1045.8	1047.0	1048.4	1049.7	1048.4	1047.0	1045.8
152.5°	1068.7	1065.8	1062.9	1062.2	1063.7	1065.1	1066.7	1068.2	1066.7	1065.1	1063.7
155°	1092.9	1090.7	1088.3	1088.1	1089.8	1091.5	1093.1	1094.9	1093.1	1091.5	1089.8
157.5°	1113.4	1111.8	1110.2	1110.1	1111.5	1112.9	1114.5	1115.9	1114.5	1112.9	1111.5
160°	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1127.0	1125.9	1124.7
162.5°	1136.4	1135.4	1134.4	1134.5	1135.6	1136.8	1137.9	1139.1	1137.9	1136.8	1135.6
165°	1150.0	1149.4	1148.9	1149.1	1150.3	1151.4	1152.5	1153.7	1152.5	1151.4	1150.3
167.5°	1160.8	1160.3	1159.8	1160.0	1161.2	1162.3	1163.4	1164.6	1163.4	1162.3	1161.2
170°	1166.5	1166.2	1165.8	1166.2	1167.3	1168.5	1169.6	1170.7	1169.6	1168.5	1167.3
172.5°	1170.6	1170.3	1169.9	1170.3	1171.4	1172.5	1173.7	1174.8	1173.7	1172.5	1171.4
175°	1175.1	1174.7	1174.3	1174.8	1176.2	1177.4	1178.8	1180.1	1178.8	1177.4	1176.2
177.5°	1176.5	1176.4	1176.3	1176.7	1177.8	1178.8	1179.9	1181.0	1179.9	1178.8	1177.8
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1291.5	1288.9	1284.2	1276.8	1272.5	1264.8	1259.7	1262.7	1263.4	1262.7	1261.9
5°	1256.8	1247.1	1233.9	1221.2	1209.4	1196.7	1189.4	1186.2	1179.8	1176.2	1174.4
7.5°	1214.8	1198.3	1179.6	1157.4	1138.5	1118.8	1108.8	1103.7	1090.7	1083.6	1077.4
10°	1183.5	1157.5	1138.9	1109.7	1092.0	1066.0	1048.3	1048.7	1031.0	1020.9	1013.7
12.5°	1148.9	1120.3	1089.3	1063.1	1038.4	1017.6	996.2	987.6	968.7	959.0	939.4
15°	1091.5	1058.3	1025.6	990.0	965.0	932.6	901.7	863.9	833.4	807.0	799.8
17.5°	1028.9	987.7	954.8	913.2	870.3	815.9	780.1	758.1	739.8	725.9	715.4
20°	985.9	944.1	909.0	846.1	788.4	751.5	725.1	708.3	689.1	674.1	665.9
22.5°	940.8	897.1	849.3	779.2	734.1	704.5	681.0	661.6	648.7	636.9	629.5
25°	876.6	828.8	750.1	701.9	665.5	634.5	618.1	606.3	592.6	576.7	569.4
27.5°	809.0	732.9	676.4	640.5	605.7	585.6	570.9	553.2	541.0	533.9	526.3
30°	758.3	682.3	638.2	599.1	574.4	552.1	534.8	524.9	513.0	500.7	495.7
32.5°	701.9	641.1	598.9	566.2	541.3	522.3	508.6	492.4	483.8	476.3	465.8
35°	631.8	585.9	547.2	520.8	497.0	481.6	465.7	456.1	440.6	434.3	430.2
37.5°	572.4	532.5	503.7	475.8	457.1	440.0	430.3	415.0	408.3	399.5	390.8
40°	539.0	499.8	472.0	449.2	428.3	415.5	403.3	391.0	380.9	376.9	366.4
42.5°	504.7	472.9	445.1	420.1	406.1	392.6	377.1	368.1	357.7	351.1	344.6
45°	457.4	429.3	405.6	385.0	369.6	355.5	345.4	330.5	324.6	311.3	305.9
47.5°	416.0	389.7	367.1	347.7	332.5	323.3	308.7	296.9	287.5	279.4	272.4
50°	386.5	364.6	342.8	325.5	311.8	298.6	283.6	277.7	263.1	259.0	254.9
52.5°	359.5	338.8	318.7	301.8	288.1	275.3	262.1	254.3	244.5	240.4	237.5
55°	321.8	301.8	282.7	267.6	254.0	240.8	232.6	223.0	218.5	215.3	211.7
57.5°	283.9	265.9	251.3	236.0	222.3	211.9	202.3	196.6	191.9	187.7	183.3
60°	259.9	242.6	229.4	215.3	201.2	192.5	185.3	178.4	173.0	166.6	164.8
62.5°	234.4	219.3	207.2	193.4	181.2	173.3	166.3	159.9	153.3	144.0	141.4
65°	199.4	187.5	174.8	163.5	152.5	144.7	134.7	127.4	124.8	123.8	123.3
67.5°	167.7	156.5	145.5	133.9	123.9	116.8	111.7	110.6	108.7	108.2	106.9
70°	146.6	136.1	125.2	114.2	104.7	103.3	101.5	99.7	97.4	96.5	95.6
72.5°	127.6	116.8	105.8	97.1	93.0	91.3	89.5	87.7	86.1	85.2	84.6
75°	97.8	87.8	80.6	77.4	75.1	73.7	71.0	69.6	68.8	67.3	66.9
77.5°	70.4	64.8	61.4	59.5	57.1	55.6	54.0	52.7	51.7	51.5	50.7
80°	53.7	51.0	48.7	46.0	45.0	43.2	42.8	41.5	41.9	40.5	40.5
82.5°	41.7	38.3	36.3	35.0	34.2	32.7	32.2	31.6	31.7	30.7	30.7
85°	21.4	20.5	19.5	18.6	18.6	17.3	17.7	17.3	17.3	16.4	16.0
87.5°	8.7	8.7	8.3	8.6	8.9	8.8	9.1	8.9	9.1	9.3	9.0
90°	9.2	11.0	12.5	14.0	15.5	17.0	18.0	18.9	19.9	20.9	21.5
92.5°	16.5	16.8	17.5	18.3	19.0	19.8	20.2	20.8	21.2	21.8	22.1
95°	30.4	27.9	29.2	30.6	31.9	33.3	34.2	35.1	36.1	37.0	37.4
97.5°	39.5	32.2	35.3	38.3	41.4	44.5	45.2	46.0	46.7	47.5	48.0
100°	47.1	35.7	38.9	42.1	45.4	48.6	50.1	51.6	53.1	54.7	55.6
102.5°	173.8	157.7	130.7	103.8	76.9	49.9	51.9	53.9	55.8	57.8	59.0
105°	281.8	258.8	207.1	155.3	103.7	52.0	54.0	56.2	58.2	60.3	61.7
107.5°	349.5	320.7	258.8	196.7	134.7	72.8	70.6	68.5	66.4	64.3	63.6
110°	393.3	368.0	313.3	258.6	203.8	149.1	130.2	111.2	92.3	73.4	64.3



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	435.2	430.2	416.7	403.1	389.6	376.1	307.0	237.9	168.9	99.8	65.5
115°	502.8	506.8	511.5	516.2	521.0	525.8	438.0	350.4	262.7	175.0	124.4
117.5°	565.9	569.3	572.6	575.8	579.1	582.3	561.1	539.8	518.7	497.5	464.5
120°	607.8	610.9	614.3	617.8	621.2	624.6	626.9	629.1	631.3	633.6	622.0
122.5°	646.6	650.0	653.6	657.4	661.0	664.8	666.1	667.5	668.9	670.2	668.4
125°	702.6	705.6	709.2	712.8	716.4	720.0	721.3	722.6	724.0	725.3	726.2
127.5°	756.3	759.0	761.7	764.4	767.0	769.7	771.7	773.6	775.5	777.5	778.5
130°	790.9	793.4	795.5	797.6	799.7	801.8	803.9	805.9	808.1	810.1	811.1
132.5°	823.1	825.5	827.6	829.6	831.7	833.8	835.6	837.4	839.2	841.0	841.8
135°	869.3	871.6	873.3	875.0	876.7	878.5	880.4	882.3	884.1	886.0	886.8
137.5°	910.4	912.5	914.4	916.3	918.3	920.2	922.1	923.9	925.8	927.6	928.3
140°	937.4	939.1	941.2	943.3	945.4	947.5	949.2	950.9	952.6	954.3	954.7
142.5°	961.3	963.1	965.5	968.0	970.4	972.7	974.3	975.8	977.4	978.9	979.2
145°	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3	1010.7	1012.0	1013.3	1013.5
147.5°	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0	1041.0	1042.0	1042.9	1043.0
150°	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5	1059.7	1060.8	1061.9	1062.0
152.5°	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6	1076.7	1077.8	1079.0	1079.0
155°	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6	1099.7	1100.8	1102.0	1101.8
157.5°	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8	1119.1	1120.4	1121.7	1121.6
160°	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3	1130.4	1131.5	1132.7	1132.6
162.5°	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6	1140.9	1142.2	1143.5	1143.4
165°	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5
167.5°	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1	1164.5	1165.8	1167.2	1167.0
170°	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7	1170.0	1171.3	1172.6	1172.4
172.5°	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8	1174.0	1175.4	1176.7	1176.5
175°	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1	1178.5	1179.8	1181.2	1180.9
177.5°	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9	1179.0	1180.0	1181.1	1181.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1257.9	1258.6	1257.6	1258.3	1257.6	1258.6	1257.9	1261.9	1262.7	1263.4	1262.7
5°	1172.1	1166.6	1165.7	1164.3	1165.7	1166.6	1172.1	1174.4	1176.2	1179.8	1186.2
7.5°	1069.6	1068.7	1066.5	1063.3	1066.5	1068.7	1069.6	1077.4	1083.6	1090.7	1103.7
10°	1003.6	1001.4	1000.9	997.7	1000.9	1001.4	1003.6	1013.7	1020.9	1031.0	1048.7
12.5°	926.5	911.8	910.3	902.3	910.3	911.8	926.5	939.4	959.0	968.7	987.6
15°	788.8	786.1	776.9	771.1	776.9	786.1	788.8	799.8	807.0	833.4	863.9
17.5°	710.2	701.2	698.4	697.1	698.4	701.2	710.2	715.4	725.9	739.8	758.1
20°	659.5	651.4	650.0	649.1	650.0	651.4	659.5	665.9	674.1	689.1	708.3
22.5°	624.6	616.0	612.5	609.8	612.5	616.0	624.6	629.5	636.9	648.7	661.6
25°	564.9	561.7	559.9	558.9	559.9	561.7	564.9	569.4	576.7	592.6	606.3
27.5°	518.2	511.1	509.8	507.5	509.8	511.1	518.2	526.3	533.9	541.0	553.2
30°	491.6	489.3	486.2	483.4	486.2	489.3	491.6	495.7	500.7	513.0	524.9
32.5°	460.3	458.3	455.6	454.2	455.6	458.3	460.3	465.8	476.3	483.8	492.4
35°	425.6	419.2	416.5	412.4	416.5	419.2	425.6	430.2	434.3	440.6	456.1
37.5°	388.9	385.6	381.7	383.1	381.7	385.6	388.9	390.8	399.5	408.3	415.0
40°	360.5	358.2	357.3	356.9	357.3	358.2	360.5	366.4	376.9	380.9	391.0
42.5°	338.0	331.6	329.3	329.2	329.3	331.6	338.0	344.6	351.1	357.7	368.1
45°	303.6	297.7	293.6	294.1	293.6	297.7	303.6	305.9	311.3	324.6	330.5
47.5°	268.5	268.3	265.7	266.5	265.7	268.3	268.5	272.4	279.4	287.5	296.9
50°	251.7	249.0	247.2	247.6	247.2	249.0	251.7	254.9	259.0	263.1	277.7
52.5°	235.7	233.4	231.8	233.8	231.8	233.4	235.7	237.5	240.4	244.5	254.3
55°	209.4	206.6	206.2	205.7	206.2	206.6	209.4	211.7	215.3	218.5	223.0
57.5°	179.9	178.2	175.4	174.2	175.4	178.2	179.9	183.3	187.7	191.9	196.6
60°	158.8	155.2	150.7	150.2	150.7	155.2	158.8	164.8	166.6	173.0	178.4
62.5°	139.6	138.8	137.9	137.9	137.9	138.8	139.6	141.4	144.0	153.3	159.9
65°	122.4	122.0	122.4	122.9	122.4	122.0	122.4	123.3	123.8	124.8	127.4
67.5°	106.7	105.8	105.0	105.4	105.0	105.8	106.7	106.9	108.2	108.7	110.6
70°	94.7	94.3	93.8	93.8	93.8	94.3	94.7	95.6	96.5	97.4	99.7
72.5°	83.0	82.9	82.5	82.1	82.5	82.9	83.0	84.6	85.2	86.1	87.7
75°	66.4	65.5	65.5	65.5	65.5	65.5	66.4	66.9	67.3	68.8	69.6
77.5°	50.6	50.2	49.7	49.3	49.7	50.2	50.6	50.7	51.5	51.7	52.7
80°	40.0	39.6	39.1	39.1	39.1	39.6	40.0	40.5	40.5	41.9	41.5
82.5°	30.6	30.1	30.1	29.7	30.1	30.1	30.6	30.7	30.7	31.7	31.6
85°	16.4	16.9	16.4	17.3	16.4	16.9	16.4	16.0	16.4	17.3	17.3
87.5°	9.1	8.8	9.3	9.0	9.3	8.8	9.1	9.0	9.3	9.1	8.9
90°	21.8	22.2	22.6	23.0	22.6	22.2	21.8	21.5	20.9	19.9	18.9
92.5°	22.3	22.6	22.7	23.0	22.7	22.6	22.3	22.1	21.8	21.2	20.8
95°	37.2	37.0	36.8	36.6	36.8	37.0	37.2	37.4	37.0	36.1	35.1
97.5°	48.2	48.4	48.7	48.9	48.7	48.4	48.2	48.0	47.5	46.7	46.0
100°	55.9	56.4	56.7	57.1	56.7	56.4	55.9	55.6	54.7	53.1	51.6
102.5°	59.6	60.1	60.6	61.2	60.6	60.1	59.6	59.0	57.8	55.8	53.9
105°	62.5	63.2	64.0	64.7	64.0	63.2	62.5	61.7	60.3	58.2	56.2
107.5°	64.4	65.1	65.9	66.6	65.9	65.1	64.4	63.6	64.3	66.4	68.5
110°	65.0	65.8	66.5	67.3	66.5	65.8	65.0	64.3	73.4	92.3	111.2



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	66.2	66.8	67.4	68.0	67.4	66.8	66.2	65.5	99.8	168.9	237.9
115°	110.8	97.1	83.5	69.9	83.5	97.1	110.8	124.4	175.0	262.7	350.4
117.5°	419.6	374.9	330.1	285.3	330.1	374.9	419.6	464.5	497.5	518.7	539.8
120°	596.5	570.9	545.3	519.8	545.3	570.9	596.5	622.0	633.6	631.3	629.1
122.5°	663.4	658.5	653.5	648.6	653.5	658.5	663.4	668.4	670.2	668.9	667.5
125°	726.8	727.4	727.9	728.5	727.9	727.4	726.8	726.2	725.3	724.0	722.6
127.5°	778.6	778.7	778.8	778.9	778.8	778.7	778.6	778.5	777.5	775.5	773.6
130°	810.8	810.7	810.5	810.3	810.5	810.7	810.8	811.1	810.1	808.1	805.9
132.5°	841.5	841.3	841.2	841.0	841.2	841.3	841.5	841.8	841.0	839.2	837.4
135°	886.4	886.0	885.6	885.3	885.6	886.0	886.4	886.8	886.0	884.1	882.3
137.5°	927.6	926.9	926.3	925.7	926.3	926.9	927.6	928.3	927.6	925.8	923.9
140°	953.8	952.8	951.8	950.9	951.8	952.8	953.8	954.7	954.3	952.6	950.9
142.5°	978.3	977.3	976.4	975.4	976.4	977.3	978.3	979.2	978.9	977.4	975.8
145°	1012.5	1011.6	1010.7	1009.7	1010.7	1011.6	1012.5	1013.5	1013.3	1012.0	1010.7
147.5°	1042.2	1041.4	1040.6	1039.8	1040.6	1041.4	1042.2	1043.0	1042.9	1042.0	1041.0
150°	1061.1	1060.2	1059.2	1058.3	1059.2	1060.2	1061.1	1062.0	1061.9	1060.8	1059.7
152.5°	1077.7	1076.5	1075.2	1074.0	1075.2	1076.5	1077.7	1079.0	1079.0	1077.8	1076.7
155°	1100.3	1098.8	1097.3	1095.7	1097.3	1098.8	1100.3	1101.8	1102.0	1100.8	1099.7
157.5°	1120.1	1118.7	1117.1	1115.7	1117.1	1118.7	1120.1	1121.6	1121.7	1120.4	1119.1
160°	1131.2	1129.9	1128.6	1127.3	1128.6	1129.9	1131.2	1132.6	1132.7	1131.5	1130.4
162.5°	1141.7	1140.1	1138.4	1136.8	1138.4	1140.1	1141.7	1143.4	1143.5	1142.2	1140.9
165°	1155.1	1153.8	1152.4	1151.1	1152.4	1153.8	1155.1	1156.5	1156.5	1155.1	1153.8
167.5°	1165.3	1163.6	1161.9	1160.2	1161.9	1163.6	1165.3	1167.0	1167.2	1165.8	1164.5
170°	1170.7	1169.0	1167.3	1165.6	1167.3	1169.0	1170.7	1172.4	1172.6	1171.3	1170.0
172.5°	1174.8	1173.1	1171.4	1169.7	1171.4	1173.1	1174.8	1176.5	1176.7	1175.4	1174.0
175°	1178.9	1177.1	1175.2	1173.3	1175.2	1177.1	1178.9	1180.9	1181.2	1179.8	1178.5
177.5°	1179.6	1178.2	1176.9	1175.5	1176.9	1178.2	1179.6	1181.0	1181.1	1180.0	1179.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1259.7	1264.8	1272.5	1276.8	1284.2	1288.9	1291.5	1296.2	1298.7	1307.8	1317.3
5°	1189.4	1196.7	1209.4	1221.2	1233.9	1247.1	1256.8	1267.7	1277.6	1294.9	1313.2
7.5°	1108.8	1118.8	1138.5	1157.4	1179.6	1198.3	1214.8	1233.4	1250.1	1274.9	1300.7
10°	1048.3	1066.0	1092.0	1109.7	1138.9	1157.5	1183.5	1203.9	1227.2	1259.9	1289.1
12.5°	996.2	1017.6	1038.4	1063.1	1089.3	1120.3	1148.9	1175.2	1202.7	1236.6	1270.9
15°	901.7	932.6	965.0	990.0	1025.6	1058.3	1091.5	1127.0	1160.7	1201.2	1245.8
17.5°	780.1	815.9	870.3	913.2	954.8	987.7	1028.9	1071.8	1111.5	1160.4	1210.1
20°	725.1	751.5	788.4	846.1	909.0	944.1	985.9	1033.2	1078.8	1132.0	1185.3
22.5°	681.0	704.5	734.1	779.2	849.3	897.1	940.8	988.8	1041.6	1096.0	1155.0
25°	618.1	634.5	665.5	701.9	750.1	828.8	876.6	924.9	982.3	1040.5	1107.9
27.5°	570.9	585.6	605.7	640.5	676.4	732.9	809.0	861.6	918.7	984.3	1054.2
30°	534.8	552.1	574.4	599.1	638.2	682.3	758.3	819.3	875.7	943.2	1017.8
32.5°	508.6	522.3	541.3	566.2	598.9	641.1	701.9	776.0	831.0	902.0	979.9
35°	465.7	481.6	497.0	520.8	547.2	585.9	631.8	711.0	765.6	835.7	914.0
37.5°	430.3	440.0	457.1	475.8	503.7	532.5	572.4	643.5	702.5	771.3	851.5
40°	403.3	415.5	428.3	449.2	472.0	499.8	539.0	591.7	659.5	726.9	805.2
42.5°	377.1	392.6	406.1	420.1	445.1	472.9	504.7	549.5	618.8	682.5	758.6
45°	345.4	355.5	369.6	385.0	405.6	429.3	457.4	496.6	563.0	618.1	689.6
47.5°	308.7	323.3	332.5	347.7	367.1	389.7	416.0	449.8	503.6	555.3	621.5
50°	283.6	298.6	311.8	325.5	342.8	364.6	386.5	419.2	462.4	516.7	578.5
52.5°	262.1	275.3	288.1	301.8	318.7	338.8	359.5	388.3	425.3	475.1	535.2
55°	232.6	240.8	254.0	267.6	282.7	301.8	321.8	345.9	377.8	419.6	468.4
57.5°	202.3	211.9	222.3	236.0	251.3	265.9	283.9	305.8	330.9	368.8	410.5
60°	185.3	192.5	201.2	215.3	229.4	242.6	259.9	278.1	301.8	334.6	370.1
62.5°	166.3	173.3	181.2	193.4	207.2	219.3	234.4	253.7	273.8	303.6	334.7
65°	134.7	144.7	152.5	163.5	174.8	187.5	199.4	214.8	232.6	256.3	284.0
67.5°	111.7	116.8	123.9	133.9	145.5	156.5	167.7	179.8	195.2	213.5	235.5
70°	101.5	103.3	104.7	114.2	125.2	136.1	146.6	157.9	171.1	186.2	205.3
72.5°	89.5	91.3	93.0	97.1	105.8	116.8	127.6	136.1	148.6	161.0	176.6
75°	71.0	73.7	75.1	77.4	80.6	87.8	97.8	106.0	113.3	122.9	135.2
77.5°	54.0	55.6	57.1	59.5	61.4	64.8	70.4	77.8	84.6	90.2	98.7
80°	42.8	43.2	45.0	46.0	48.7	51.0	53.7	59.7	66.4	68.8	74.6
82.5°	32.2	32.7	34.2	35.0	36.3	38.3	41.7	43.2	48.6	51.6	55.4
85°	17.7	17.3	18.6	18.6	19.5	20.5	21.4	23.6	25.1	28.7	29.6
87.5°	9.1	8.8	8.9	8.6	8.3	8.7	8.7	8.7	9.0	9.7	10.7
90°	18.0	17.0	15.5	14.0	12.5	11.0	9.2	7.1	5.0	2.9	0.9
92.5°	20.2	19.8	19.0	18.3	17.5	16.8	16.5	16.7	16.9	17.0	17.2
95°	34.2	33.3	31.9	30.6	29.2	27.9	30.4	36.6	42.9	49.1	55.4
97.5°	45.2	44.5	41.4	38.3	35.3	32.2	39.5	57.1	74.7	92.3	109.9
100°	50.1	48.6	45.4	42.1	38.9	35.7	47.1	73.0	98.9	124.8	150.8
102.5°	51.9	49.9	76.9	103.8	130.7	157.7	173.8	179.3	184.9	190.3	195.8
105°	54.0	52.0	103.7	155.3	207.1	258.8	281.8	276.1	270.4	264.7	259.0
107.5°	70.6	72.8	134.7	196.7	258.8	320.7	349.5	344.8	340.3	335.7	331.1
110°	130.2	149.1	203.8	258.6	313.3	368.0	393.3	389.4	385.4	381.5	377.5



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	307.0	376.1	389.6	403.1	416.7	430.2	435.2	431.7	428.1	424.6	421.1
115°	438.0	525.8	521.0	516.2	511.5	506.8	502.8	499.6	496.4	493.1	489.9
117.5°	561.1	582.3	579.1	575.8	572.6	569.3	565.9	562.2	558.7	555.1	551.4
120°	626.9	624.6	621.2	617.8	614.3	610.9	607.8	604.9	602.1	599.3	596.5
122.5°	666.1	664.8	661.0	657.4	653.6	650.0	646.6	643.5	640.6	637.6	634.6
125°	721.3	720.0	716.4	712.8	709.2	705.6	702.6	700.1	697.7	695.2	692.7
127.5°	771.7	769.7	767.0	764.4	761.7	759.0	756.3	753.6	750.8	748.1	745.4
130°	803.9	801.8	799.7	797.6	795.5	793.4	790.9	787.8	784.9	781.9	778.8
132.5°	835.6	833.8	831.7	829.6	827.6	825.5	823.1	820.6	818.1	815.5	812.9
135°	880.4	878.5	876.7	875.0	873.3	871.6	869.3	866.3	863.3	860.2	857.2
137.5°	922.1	920.2	918.3	916.3	914.4	912.5	910.4	908.4	906.2	904.1	902.0
140°	949.2	947.5	945.4	943.3	941.2	939.1	937.4	935.9	934.3	932.8	931.3
142.5°	974.3	972.7	970.4	968.0	965.5	963.1	961.3	959.9	958.6	957.2	955.8
145°	1009.3	1008.0	1004.8	1001.6	998.4	995.1	993.6	993.8	994.0	994.2	994.3
147.5°	1040.0	1039.0	1035.8	1032.6	1029.5	1026.3	1025.0	1025.7	1026.4	1027.2	1028.0
150°	1058.5	1057.4	1054.4	1051.3	1048.3	1045.3	1044.5	1045.8	1047.0	1048.4	1049.7
152.5°	1075.6	1074.4	1071.6	1068.7	1065.8	1062.9	1062.2	1063.7	1065.1	1066.7	1068.2
155°	1098.6	1097.4	1095.2	1092.9	1090.7	1088.3	1088.1	1089.8	1091.5	1093.1	1094.9
157.5°	1117.8	1116.5	1114.9	1113.4	1111.8	1110.2	1110.1	1111.5	1112.9	1114.5	1115.9
160°	1129.3	1128.1	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1
162.5°	1139.6	1138.4	1137.4	1136.4	1135.4	1134.4	1134.5	1135.6	1136.8	1137.9	1139.1
165°	1152.4	1151.1	1150.6	1150.0	1149.4	1148.9	1149.1	1150.3	1151.4	1152.5	1153.7
167.5°	1163.1	1161.9	1161.4	1160.8	1160.3	1159.8	1160.0	1161.2	1162.3	1163.4	1164.6
170°	1168.7	1167.3	1167.0	1166.5	1166.2	1165.8	1166.2	1167.3	1168.5	1169.6	1170.7
172.5°	1172.8	1171.4	1171.0	1170.6	1170.3	1169.9	1170.3	1171.4	1172.5	1173.7	1174.8
175°	1177.1	1175.8	1175.5	1175.1	1174.7	1174.3	1174.8	1176.2	1177.4	1178.8	1180.1
177.5°	1177.9	1176.9	1176.7	1176.5	1176.4	1176.3	1176.7	1177.8	1178.8	1179.9	1181.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1317.7	1318.8	1326.1	1329.3	1335.9	1338.4	1341.3	1340.6	1340.6	1342.0	1352.3
5°	1320.4	1329.5	1343.2	1356.4	1369.1	1380.1	1387.4	1394.6	1397.4	1410.6	1422.5
7.5°	1315.7	1332.5	1355.0	1375.2	1399.3	1418.2	1433.8	1448.0	1457.6	1476.8	1496.5
10°	1309.6	1333.2	1358.7	1384.6	1417.9	1442.9	1468.4	1488.0	1494.3	1523.0	1539.4
12.5°	1297.2	1328.8	1361.3	1394.8	1427.4	1461.9	1489.9	1509.5	1531.9	1557.6	1587.9
15°	1278.6	1315.0	1357.4	1400.6	1447.0	1488.9	1518.9	1553.1	1577.6	1605.9	1632.3
17.5°	1251.9	1298.8	1352.6	1402.7	1456.3	1501.4	1542.7	1575.5	1592.8	1608.8	1612.7
20°	1230.8	1281.3	1344.6	1403.7	1457.5	1509.4	1550.3	1577.6	1582.2	1582.6	1558.5
22.5°	1207.8	1264.9	1331.1	1391.8	1456.0	1513.8	1545.6	1557.3	1539.2	1508.3	1461.7
25°	1165.7	1231.7	1308.7	1377.8	1448.0	1502.5	1513.5	1493.0	1429.7	1363.2	1279.1
27.5°	1120.0	1194.2	1276.7	1353.6	1428.3	1462.1	1438.5	1364.7	1250.7	1151.6	1031.6
30°	1086.5	1169.8	1250.8	1336.9	1406.0	1420.6	1366.5	1257.7	1124.7	975.4	855.8
32.5°	1048.3	1135.6	1224.6	1313.6	1371.5	1357.3	1267.7	1133.8	978.0	831.3	718.1
35°	993.6	1083.8	1179.8	1269.0	1305.9	1244.5	1110.6	936.3	776.9	640.0	562.1
37.5°	930.6	1028.7	1128.5	1210.5	1207.8	1105.5	923.2	743.2	609.3	528.2	472.9
40°	885.7	985.0	1092.9	1162.1	1132.5	999.1	801.6	631.8	534.0	469.3	428.7
42.5°	842.8	942.4	1049.5	1104.6	1053.1	889.1	692.3	559.3	478.6	428.1	395.3
45°	769.7	874.9	974.1	1004.6	912.7	731.9	559.9	463.3	409.7	372.4	349.6
47.5°	698.2	801.6	892.2	892.8	768.4	593.5	472.3	401.0	355.2	326.3	309.7
50°	654.5	752.9	828.8	817.1	675.9	528.0	422.4	361.0	322.7	300.4	283.1
52.5°	605.4	700.8	766.6	732.9	597.6	464.7	377.6	326.0	294.4	274.9	259.5
55°	534.0	618.6	665.0	614.0	487.5	386.5	319.1	278.6	254.9	238.5	225.3
57.5°	463.7	533.6	562.8	503.5	401.5	320.5	269.9	239.5	216.1	204.3	197.4
60°	419.6	479.3	499.8	434.3	349.1	280.4	239.0	210.7	193.4	185.7	178.9
62.5°	376.3	425.1	433.5	373.4	304.3	245.4	209.8	186.0	174.5	167.1	160.7
65°	312.3	347.3	343.2	295.0	240.8	194.8	168.9	154.3	145.6	135.2	123.8
67.5°	257.1	278.5	265.6	229.4	183.8	151.4	134.5	123.4	112.7	102.8	100.1
70°	222.1	234.4	220.8	187.5	150.7	127.0	113.3	100.1	93.8	91.5	87.4
72.5°	188.6	192.9	178.2	149.6	122.6	105.1	91.8	84.4	81.1	79.1	76.5
75°	141.6	138.4	125.6	103.3	85.2	73.3	69.2	66.4	64.2	62.3	61.0
77.5°	99.4	94.8	83.4	68.8	59.3	53.6	51.2	49.7	48.6	47.7	46.4
80°	74.6	71.4	60.1	49.1	45.0	42.4	40.9	39.1	39.1	38.3	36.8
82.5°	54.7	51.1	41.1	36.0	33.8	32.1	31.1	30.1	29.7	29.9	28.9
85°	28.7	23.2	20.5	19.5	18.2	17.3	17.7	16.9	16.9	16.9	16.4
87.5°	9.4	7.9	7.9	8.0	8.7	9.1	9.0	9.3	10.0	9.8	10.3
90°	2.9	5.0	7.1	9.2	11.0	12.5	14.0	15.5	17.0	18.0	18.9
92.5°	17.0	16.9	16.7	16.5	16.8	17.5	18.3	19.0	19.8	20.2	20.8
95°	49.1	42.9	36.6	30.4	27.9	29.2	30.6	31.9	33.3	34.2	35.1
97.5°	92.3	74.7	57.1	39.5	32.2	35.3	38.3	41.4	44.5	45.2	46.0
100°	124.8	98.9	73.0	47.1	35.7	38.9	42.1	45.4	48.6	50.1	51.6
102.5°	190.3	184.9	179.3	173.8	157.7	130.7	103.8	76.9	49.9	51.9	53.9
105°	264.7	270.4	276.1	281.8	258.8	207.1	155.3	103.7	52.0	54.0	56.2
107.5°	335.7	340.3	344.8	349.5	320.7	258.8	196.7	134.7	72.8	70.6	68.5
110°	381.5	385.4	389.4	393.3	368.0	313.3	258.6	203.8	149.1	130.2	111.2





TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	424.6	428.1	431.7	435.2	430.2	416.7	403.1	389.6	376.1	307.0	237.9
115°	493.1	496.4	499.6	502.8	506.8	511.5	516.2	521.0	525.8	438.0	350.4
117.5°	555.1	558.7	562.2	565.9	569.3	572.6	575.8	579.1	582.3	561.1	539.8
120°	599.3	602.1	604.9	607.8	610.9	614.3	617.8	621.2	624.6	626.9	629.1
122.5°	637.6	640.6	643.5	646.6	650.0	653.6	657.4	661.0	664.8	666.1	667.5
125°	695.2	697.7	700.1	702.6	705.6	709.2	712.8	716.4	720.0	721.3	722.6
127.5°	748.1	750.8	753.6	756.3	759.0	761.7	764.4	767.0	769.7	771.7	773.6
130°	781.9	784.9	787.8	790.9	793.4	795.5	797.6	799.7	801.8	803.9	805.9
132.5°	815.5	818.1	820.6	823.1	825.5	827.6	829.6	831.7	833.8	835.6	837.4
135°	860.2	863.3	866.3	869.3	871.6	873.3	875.0	876.7	878.5	880.4	882.3
137.5°	904.1	906.2	908.4	910.4	912.5	914.4	916.3	918.3	920.2	922.1	923.9
140°	932.8	934.3	935.9	937.4	939.1	941.2	943.3	945.4	947.5	949.2	950.9
142.5°	957.2	958.6	959.9	961.3	963.1	965.5	968.0	970.4	972.7	974.3	975.8
145°	994.2	994.0	993.8	993.6	995.1	998.4	1001.6	1004.8	1008.0	1009.3	1010.7
147.5°	1027.2	1026.4	1025.7	1025.0	1026.3	1029.5	1032.6	1035.8	1039.0	1040.0	1041.0
150°	1048.4	1047.0	1045.8	1044.5	1045.3	1048.3	1051.3	1054.4	1057.4	1058.5	1059.7
152.5°	1066.7	1065.1	1063.7	1062.2	1062.9	1065.8	1068.7	1071.6	1074.4	1075.6	1076.7
155°	1093.1	1091.5	1089.8	1088.1	1088.3	1090.7	1092.9	1095.2	1097.4	1098.6	1099.7
157.5°	1114.5	1112.9	1111.5	1110.1	1110.2	1111.8	1113.4	1114.9	1116.5	1117.8	1119.1
160°	1127.0	1125.9	1124.7	1123.6	1123.6	1124.7	1125.9	1127.0	1128.1	1129.3	1130.4
162.5°	1137.9	1136.8	1135.6	1134.5	1134.4	1135.4	1136.4	1137.4	1138.4	1139.6	1140.9
165°	1152.5	1151.4	1150.3	1149.1	1148.9	1149.4	1150.0	1150.6	1151.1	1152.4	1153.8
167.5°	1163.4	1162.3	1161.2	1160.0	1159.8	1160.3	1160.8	1161.4	1161.9	1163.1	1164.5
170°	1169.6	1168.5	1167.3	1166.2	1165.8	1166.2	1166.5	1167.0	1167.3	1168.7	1170.0
172.5°	1173.7	1172.5	1171.4	1170.3	1169.9	1170.3	1170.6	1171.0	1171.4	1172.8	1174.0
175°	1178.8	1177.4	1176.2	1174.8	1174.3	1174.7	1175.1	1175.5	1175.8	1177.1	1178.5
177.5°	1179.9	1178.8	1177.8	1176.7	1176.3	1176.4	1176.5	1176.7	1176.9	1177.9	1179.0
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0	1310.0
2.5°	1355.8	1360.6	1362.8	1362.8	1365.4	1364.2	1363.2
5°	1433.8	1442.4	1444.3	1452.5	1458.4	1456.5	1457.5
7.5°	1511.3	1525.2	1538.9	1545.2	1546.2	1549.9	1551.2
10°	1559.0	1570.4	1591.8	1588.6	1604.5	1613.6	1598.6
12.5°	1604.9	1620.2	1635.0	1639.1	1648.2	1651.1	1645.2
15°	1646.4	1654.6	1655.5	1653.2	1655.9	1653.7	1645.0
17.5°	1607.6	1594.3	1567.4	1554.6	1544.5	1529.6	1523.6
20°	1543.5	1504.3	1458.8	1440.6	1419.2	1377.3	1387.4
22.5°	1405.2	1360.5	1315.0	1261.9	1236.4	1196.8	1194.4
25°	1189.8	1112.9	1028.2	969.1	934.5	894.9	877.6
27.5°	925.1	828.2	758.8	723.7	691.8	660.4	659.1
30°	751.0	678.2	624.5	594.5	574.9	561.7	564.5
32.5°	633.0	583.2	547.0	522.0	507.6	497.6	497.4
35°	517.5	483.4	460.2	449.7	439.3	431.9	432.4
37.5°	442.9	422.4	409.5	397.9	391.4	387.8	385.8
40°	404.7	387.8	377.8	371.0	365.5	360.5	359.6
42.5°	374.4	360.5	350.4	345.1	340.0	336.4	335.6
45°	332.3	320.9	311.8	305.9	303.6	300.4	300.4
47.5°	295.6	284.4	277.3	273.6	269.7	267.5	267.4
50°	270.8	262.2	255.8	253.5	250.3	249.0	248.5
52.5°	248.6	242.2	237.6	236.0	234.7	232.9	233.3
55°	218.5	214.8	213.0	211.7	209.4	206.6	208.5
57.5°	193.1	190.0	185.1	180.8	178.7	176.8	177.5
60°	175.2	168.9	162.5	157.5	156.1	152.0	152.0
62.5°	152.7	143.7	135.9	133.1	131.7	129.8	129.5
65°	117.4	113.8	112.0	110.1	109.2	109.2	108.3
67.5°	97.3	95.9	93.9	93.4	92.5	92.2	91.9
70°	86.1	84.2	83.3	82.8	81.9	82.4	81.1
72.5°	75.1	73.7	73.5	72.3	71.7	71.8	70.8
75°	59.2	59.2	58.7	58.2	57.3	56.9	57.3
77.5°	45.5	45.6	44.8	44.7	44.6	44.7	44.2
80°	36.4	36.8	36.4	35.9	35.5	35.9	35.5
82.5°	28.8	28.1	28.0	27.9	27.8	27.6	27.5
85°	16.4	16.9	16.4	16.0	16.0	16.0	16.4
87.5°	10.2	10.3	10.5	10.5	10.6	10.7	10.4
90°	19.9	20.9	21.5	21.8	22.2	22.6	23.0
92.5°	21.2	21.8	22.1	22.3	22.6	22.7	23.0
95°	36.1	37.0	37.4	37.2	37.0	36.8	36.6
97.5°	46.7	47.5	48.0	48.2	48.4	48.7	48.9
100°	53.1	54.7	55.6	55.9	56.4	56.7	57.1
102.5°	55.8	57.8	59.0	59.6	60.1	60.6	61.2
105°	58.2	60.3	61.7	62.5	63.2	64.0	64.7
107.5°	66.4	64.3	63.6	64.4	65.1	65.9	66.6
110°	92.3	73.4	64.3	65.0	65.8	66.5	67.3



TEST NUMBER: P331813-940

CATALOG NUMBER: S122RDIW-S675D970U940-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	168.9	99.8	65.5	66.2	66.8	67.4	68.0
115°	262.7	175.0	124.4	110.8	97.1	83.5	69.9
117.5°	518.7	497.5	464.5	419.6	374.9	330.1	285.3
120°	631.3	633.6	622.0	596.5	570.9	545.3	519.8
122.5°	668.9	670.2	668.4	663.4	658.5	653.5	648.6
125°	724.0	725.3	726.2	726.8	727.4	727.9	728.5
127.5°	775.5	777.5	778.5	778.6	778.7	778.8	778.9
130°	808.1	810.1	811.1	810.8	810.7	810.5	810.3
132.5°	839.2	841.0	841.8	841.5	841.3	841.2	841.0
135°	884.1	886.0	886.8	886.4	886.0	885.6	885.3
137.5°	925.8	927.6	928.3	927.6	926.9	926.3	925.7
140°	952.6	954.3	954.7	953.8	952.8	951.8	950.9
142.5°	977.4	978.9	979.2	978.3	977.3	976.4	975.4
145°	1012.0	1013.3	1013.5	1012.5	1011.6	1010.7	1009.7
147.5°	1042.0	1042.9	1043.0	1042.2	1041.4	1040.6	1039.8
150°	1060.8	1061.9	1062.0	1061.1	1060.2	1059.2	1058.3
152.5°	1077.8	1079.0	1079.0	1077.7	1076.5	1075.2	1074.0
155°	1100.8	1102.0	1101.8	1100.3	1098.8	1097.3	1095.7
157.5°	1120.4	1121.7	1121.6	1120.1	1118.7	1117.1	1115.7
160°	1131.5	1132.7	1132.6	1131.2	1129.9	1128.6	1127.3
162.5°	1142.2	1143.5	1143.4	1141.7	1140.1	1138.4	1136.8
165°	1155.1	1156.5	1156.5	1155.1	1153.8	1152.4	1151.1
167.5°	1165.8	1167.2	1167.0	1165.3	1163.6	1161.9	1160.2
170°	1171.3	1172.6	1172.4	1170.7	1169.0	1167.3	1165.6
172.5°	1175.4	1176.7	1176.5	1174.8	1173.1	1171.4	1169.7
175°	1179.8	1181.2	1180.9	1178.9	1177.1	1175.2	1173.3
177.5°	1180.0	1181.1	1181.0	1179.6	1178.2	1176.9	1175.5
180°	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5	1177.5

(END OF REPORT)