

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331842-940

Luminaire Tested: **S122RDIW-S865D1440U940-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331842-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D1440U940-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7403.5 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	41	41	35
2	88	81	75	71	80	74	69	65	61	58	55	49	47	45	38	37	35	30
3	81	72	65	60	73	66	60	55	55	50	47	44	41	39	34	32	31	26
4	74	64	57	51	67	59	52	47	49	44	40	40	36	34	31	29	27	23
5	68	57	50	44	62	53	46	41	44	39	35	36	32	30	28	26	24	21
6	63	52	44	39	57	48	41	36	40	35	31	33	29	26	26	24	22	19
7	59	47	39	34	53	43	37	32	36	31	28	30	26	24	24	21	19	17
8	54	43	35	30	50	40	33	29	33	28	25	28	24	21	22	20	18	15
9	51	39	32	27	46	36	30	26	31	26	22	26	22	19	21	18	16	14
10	47	36	29	25	43	33	27	23	28	24	20	24	20	18	19	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27493	27493	27493	27493
5°	30705	27665	24530	27665
10°	34067	27471	21263	27471
15°	35741	27067	16754	27067
20°	30986	26472	14496	26472
25°	20322	25655	12944	25655
30°	13679	24664	11714	24664
35°	11077	23416	10565	23416
40°	9851	22059	9778	22059
45°	8917	20466	8727	20466
50°	8116	18889	8083	18889
55°	7628	17140	7527	17140
60°	6381	15532	6307	15532
65°	5379	14105	6101	14105
70°	4971	12595	5755	12595
75°	4648	10967	5315	10967
80°	4296	9019	4733	9019
85°	3946	7114	4168	7114



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.4	2.2
10°-20°	449.8	6.1
20°-30°	579.6	7.8
30°-40°	550.8	7.4
40°-50°	471.8	6.4
50°-60°	359.3	4.9
60°-70°	227.1	3.1
70°-80°	113.4	1.5
80°-90°	35.9	0.5
90°-100°	100.9	1.4
100°-110°	313.5	4.2
110°-120°	535.9	7.2
120°-130°	704.7	9.5
130°-140°	791.0	10.7
140°-150°	775.6	10.5
150°-160°	650.5	8.8
160°-170°	431.5	5.8
170°-180°	150.8	2.0
0°-30°	1190.8	16.1
0°-40°	1741.6	23.5
0°-60°	2572.7	34.7
0°-90°	2949.2	39.8
90°-120°	950.3	12.8
90°-150°	3221.6	43.5
90°-180°	4454.0	60.2
0°-180°	7403.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1703	1703	1703	1703	1703	
5°	1894	1707	1514	1707	1894	187
15°	2138	1619	1002	1619	2138	577
25°	1141	1440	727	1440	1141	541
35°	562	1188	536	1188	562	360
45°	390	896	382	896	390	302
55°	271	609	267	609	271	238
65°	141	369	160	369	141	143
75°	74	176	85	176	74	79
85°	21	38	22	38	21	24
90°	46	1	46	1	46	21
95°	83	70	83	70	83	93
105°	298	289	298	289	298	314
115°	538	538	538	538	538	531
125°	785	782	785	782	785	700
135°	1024	1012	1024	1012	1024	789
145°	1242	1229	1242	1229	1242	776
155°	1416	1405	1416	1405	1416	651
165°	1530	1528	1530	1528	1530	431
175°	1585	1590	1585	1590	1585	151
180°	1593	1593	1593	1593	1593	



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1771.9	1773.3	1774.8	1771.4	1771.4	1768.6	1762.5	1757.7	1744.5	1742.6	1742.6
5°	1894.5	1893.3	1895.7	1888.0	1877.3	1875.0	1863.8	1849.0	1833.5	1816.4	1812.8
7.5°	2016.3	2014.6	2009.8	2008.6	2000.4	1982.5	1964.4	1945.2	1919.6	1894.6	1882.0
10°	2077.9	2097.4	2085.6	2064.8	2069.0	2041.2	2026.4	2001.0	1979.7	1942.4	1934.1
12.5°	2138.5	2146.2	2142.4	2130.7	2125.4	2106.0	2086.1	2064.0	2024.6	1991.2	1962.0
15°	2138.2	2149.5	2152.4	2148.9	2151.9	2150.7	2140.0	2121.6	2087.4	2050.7	2018.7
17.5°	1980.4	1988.2	2007.6	2020.7	2037.3	2072.3	2089.6	2096.3	2091.2	2070.3	2047.8
20°	1803.4	1790.4	1844.8	1872.6	1896.2	1955.4	2006.3	2025.9	2057.2	2056.6	2050.7
22.5°	1552.5	1555.6	1607.2	1640.2	1709.3	1768.4	1826.5	1900.0	1960.6	2000.7	2024.2
25°	1140.7	1163.2	1214.7	1259.6	1336.6	1446.6	1546.6	1662.6	1772.0	1858.4	1940.6
27.5°	856.8	858.4	899.2	940.8	986.4	1076.6	1202.5	1341.0	1497.0	1625.8	1773.9
30°	733.7	730.1	747.3	772.7	811.7	881.5	976.2	1112.3	1267.9	1462.0	1634.8
32.5°	646.6	646.8	659.7	678.5	711.0	758.0	822.9	933.4	1080.5	1271.2	1473.8
35°	562.0	561.5	571.0	584.5	598.2	628.3	672.7	730.7	831.9	1010.0	1217.0
37.5°	501.5	504.1	508.7	517.2	532.3	549.0	575.7	614.7	686.7	792.0	966.1
40°	467.4	468.6	475.1	482.2	491.1	504.1	526.0	557.3	610.0	694.0	821.2
42.5°	436.1	437.4	441.9	448.6	455.6	468.6	486.7	513.8	556.5	622.1	727.0
45°	390.5	390.5	394.7	397.6	405.3	417.1	431.9	454.4	483.9	532.5	602.4
47.5°	347.7	347.8	350.5	355.6	360.4	369.7	384.2	402.6	424.1	461.6	521.3
50°	323.1	323.6	325.4	329.6	332.5	340.8	352.0	368.0	390.5	419.5	469.2
52.5°	303.2	302.8	305.1	306.8	308.9	314.8	323.2	337.2	357.4	382.5	423.7
55°	271.0	268.6	272.2	275.1	276.9	279.3	284.0	292.8	310.0	331.4	362.1
57.5°	230.8	229.8	232.3	235.0	240.6	246.9	251.0	256.6	265.6	280.8	311.3
60°	197.6	197.6	203.0	204.7	211.2	219.5	227.8	232.6	241.4	251.5	273.9
62.5°	168.3	168.7	171.2	173.0	176.6	186.8	198.4	208.8	217.2	226.9	241.7
65°	140.8	142.0	142.0	143.2	145.5	147.9	152.7	161.0	175.8	189.3	200.5
67.5°	119.5	119.8	120.2	121.5	122.0	124.6	126.5	130.2	133.6	146.5	160.4
70°	105.3	107.1	106.5	107.7	108.3	109.4	111.8	113.6	119.0	121.9	130.2
72.5°	92.0	93.4	93.3	94.0	95.5	95.8	97.6	99.4	102.8	105.3	109.8
75°	74.5	73.9	74.5	75.7	76.3	77.0	77.0	79.3	81.1	83.5	86.4
77.5°	57.5	58.1	58.0	58.1	58.2	59.3	59.2	60.2	62.0	63.2	64.6
80°	46.2	46.7	46.2	46.7	47.3	47.9	47.3	47.9	49.7	50.9	50.9
82.5°	35.8	35.8	36.2	36.3	36.5	36.6	37.4	37.5	38.8	38.6	39.1
85°	21.3	20.7	20.7	20.7	21.3	21.8	21.3	21.3	21.8	21.8	21.8
87.5°	16.7	17.1	17.0	17.0	16.9	16.9	17.1	17.7	17.3	17.9	16.1
90°	45.7	45.4	45.1	44.9	44.5	44.7	45.3	45.8	46.5	47.1	40.5
92.5°	43.5	43.5	43.4	43.3	43.3	43.2	43.1	43.0	42.9	42.7	41.2
95°	83.4	83.9	84.5	85.2	85.7	86.1	86.1	86.1	86.1	86.1	85.4
97.5°	144.4	144.5	144.5	144.5	144.6	144.6	144.6	144.6	144.6	144.6	143.5
100°	184.1	184.5	184.8	185.0	185.4	185.5	185.5	185.5	185.5	185.5	184.6
102.5°	229.3	229.6	230.0	230.2	230.5	230.6	230.3	230.1	229.9	229.6	228.5
105°	298.5	298.5	298.5	298.5	298.5	298.1	297.6	296.9	296.3	295.8	295.2
107.5°	363.5	364.9	366.2	367.7	369.0	369.5	369.3	369.1	368.8	368.6	368.6
110°	414.0	414.9	415.8	416.7	417.6	418.1	418.1	418.1	418.1	418.1	418.1



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	462.4	463.1	463.8	464.4	465.0	465.7	466.5	467.2	467.9	468.6	468.9
115°	537.7	538.6	539.5	540.4	541.3	541.9	542.2	542.5	542.8	543.1	543.7
117.5°	609.5	610.4	611.3	612.2	613.1	613.9	614.7	615.4	616.1	616.8	618.4
120°	660.0	660.9	661.8	662.7	663.6	664.1	664.1	664.1	664.1	664.1	666.5
122.5°	709.5	710.2	710.9	711.5	712.1	712.8	713.5	714.3	715.0	715.7	717.4
125°	785.1	785.4	785.7	786.0	786.3	786.8	787.7	788.6	789.5	790.4	791.4
127.5°	853.9	854.9	855.8	856.8	857.7	858.7	859.8	860.9	861.9	863.1	864.2
130°	903.4	904.6	905.8	907.0	908.1	909.0	909.6	910.3	910.9	911.4	912.0
132.5°	950.7	951.6	952.6	953.6	954.5	955.6	957.0	958.3	959.6	960.9	960.8
135°	1024.4	1025.3	1026.2	1027.1	1028.0	1028.6	1028.9	1029.1	1029.5	1029.7	1029.1
137.5°	1091.0	1092.3	1093.4	1094.7	1095.8	1096.5	1096.8	1097.0	1097.3	1097.5	1096.7
140°	1137.3	1138.4	1139.7	1140.9	1142.1	1142.6	1142.6	1142.6	1142.6	1142.6	1141.2
142.5°	1179.2	1180.4	1181.6	1182.9	1184.0	1184.5	1184.3	1184.0	1183.7	1183.6	1182.5
145°	1242.2	1243.3	1244.6	1245.7	1246.9	1247.3	1247.1	1246.8	1246.4	1246.2	1244.4
147.5°	1298.3	1299.5	1300.6	1301.7	1302.9	1303.1	1302.4	1301.8	1301.2	1300.5	1299.3
150°	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5	1337.6	1336.7	1335.8	1334.9	1333.7
152.5°	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9	1372.7	1371.5	1370.5	1369.3	1367.9
155°	1415.6	1416.5	1417.4	1418.3	1419.2	1418.8	1417.4	1415.9	1414.3	1412.8	1411.9
157.5°	1455.4	1456.8	1458.2	1459.6	1461.1	1460.8	1458.7	1456.7	1454.6	1452.7	1452.2
160°	1480.1	1481.3	1482.5	1483.6	1484.9	1484.5	1482.7	1481.0	1479.2	1477.4	1477.1
162.5°	1501.6	1503.1	1504.5	1505.9	1507.3	1507.0	1505.0	1503.0	1500.9	1498.9	1498.6
165°	1529.8	1531.3	1532.9	1534.3	1535.8	1535.5	1533.4	1531.3	1529.2	1527.1	1527.1
167.5°	1552.9	1554.5	1556.0	1557.6	1559.2	1558.9	1556.8	1554.7	1552.6	1550.5	1550.6
170°	1564.8	1566.6	1568.3	1570.1	1571.9	1571.8	1569.7	1567.6	1565.5	1563.4	1563.7
172.5°	1574.5	1576.3	1578.1	1579.8	1581.6	1581.4	1579.4	1577.3	1575.2	1573.1	1573.4
175°	1584.9	1586.7	1588.5	1590.3	1592.1	1592.0	1589.8	1587.8	1585.7	1583.6	1584.2
177.5°	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5	1594.1	1592.7	1591.2	1589.7	1590.3
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1743.5	1739.7	1736.4	1727.9	1723.6	1714.1	1712.7	1712.3	1700.0	1688.1	1684.8
5°	1803.4	1793.9	1779.7	1763.2	1746.0	1728.2	1716.4	1706.9	1683.3	1660.8	1647.8
7.5°	1863.8	1843.3	1818.9	1787.5	1761.4	1732.1	1710.2	1690.7	1657.2	1625.0	1603.3
10°	1908.7	1875.5	1843.0	1799.8	1766.1	1733.0	1702.2	1675.6	1637.7	1595.1	1565.0
12.5°	1936.6	1900.1	1855.3	1813.1	1769.4	1727.2	1686.1	1651.9	1607.4	1563.4	1527.5
15°	1974.3	1935.3	1880.9	1820.5	1764.3	1709.3	1662.0	1619.3	1561.4	1508.7	1464.9
17.5°	2005.3	1951.5	1893.1	1823.3	1758.2	1688.3	1627.3	1572.9	1508.3	1444.8	1393.2
20°	2015.2	1961.9	1894.5	1824.7	1747.8	1665.5	1599.8	1540.7	1471.4	1402.2	1343.1
22.5°	2009.0	1967.6	1892.6	1809.0	1730.3	1644.2	1570.0	1501.4	1424.6	1354.0	1285.3
25°	1967.3	1953.0	1882.0	1790.9	1701.0	1601.1	1515.2	1440.1	1352.5	1276.8	1202.2
27.5°	1869.9	1900.5	1856.5	1759.4	1659.5	1552.3	1455.8	1370.3	1279.4	1194.2	1119.9
30°	1776.2	1846.6	1827.7	1737.7	1625.9	1520.5	1412.3	1322.9	1225.9	1138.4	1065.0
32.5°	1647.9	1764.2	1782.7	1707.4	1591.8	1476.0	1362.6	1273.7	1172.4	1080.1	1008.6
35°	1443.7	1617.6	1697.5	1649.6	1533.6	1408.7	1291.6	1188.0	1086.3	995.1	924.2
37.5°	1200.0	1436.9	1570.0	1573.4	1467.0	1337.1	1209.6	1106.8	1002.6	913.2	836.3
40°	1041.9	1298.7	1472.0	1510.5	1420.6	1280.3	1151.4	1046.6	944.9	857.3	769.2
42.5°	899.9	1155.7	1368.9	1435.7	1364.2	1224.9	1095.6	986.1	887.2	804.3	714.3
45°	727.7	951.4	1186.2	1305.8	1266.1	1137.2	1000.5	896.3	803.4	731.9	645.5
47.5°	613.9	771.5	998.8	1160.5	1159.8	1042.1	907.6	807.9	721.7	654.6	584.7
50°	549.0	686.3	878.6	1062.0	1077.4	978.6	850.8	752.0	671.5	601.1	544.9
52.5°	490.8	604.0	776.9	952.7	996.5	910.9	786.9	695.7	617.6	552.9	504.7
55°	414.7	502.3	633.6	798.2	864.4	804.1	694.0	608.9	545.5	491.1	449.7
57.5°	350.9	416.5	521.9	654.3	731.6	693.6	602.8	533.6	479.4	430.2	397.4
60°	310.6	364.4	453.8	564.5	649.6	623.0	545.5	481.0	434.9	392.3	361.5
62.5°	272.8	319.1	395.6	485.4	563.5	552.5	489.2	435.1	394.7	355.8	329.8
65°	219.5	253.2	313.0	383.4	446.1	451.5	405.9	369.2	333.1	302.4	279.3
67.5°	174.8	196.8	238.9	298.2	345.2	361.9	334.1	306.1	277.5	253.7	233.7
70°	147.3	165.1	195.8	243.8	287.0	304.7	288.7	266.8	242.0	222.5	205.3
72.5°	119.4	136.7	159.3	194.6	231.6	250.7	245.2	229.4	209.3	193.1	176.9
75°	90.0	95.2	110.7	134.3	163.3	179.9	184.0	175.8	159.7	147.3	137.9
77.5°	66.5	69.7	77.0	89.4	108.4	123.1	129.2	128.2	117.3	110.0	101.2
80°	53.2	55.0	58.6	63.9	78.1	92.9	97.0	97.0	89.3	86.4	77.5
82.5°	40.5	41.7	43.9	46.8	53.5	66.3	71.0	72.0	67.1	63.2	56.2
85°	23.1	22.5	23.6	25.4	26.7	30.1	37.3	38.4	37.3	32.5	30.8
87.5°	14.8	14.0	12.7	11.1	11.0	10.7	12.3	14.0	12.8	12.1	11.9
90°	33.9	27.4	20.8	15.7	12.1	8.5	4.9	1.3	4.9	8.5	12.1
92.5°	39.7	38.1	36.6	34.4	31.8	29.2	26.6	23.9	26.6	29.2	31.8
95°	84.8	84.3	83.6	81.9	78.8	75.9	72.9	69.9	72.9	75.9	78.8
97.5°	142.4	141.2	140.1	138.2	135.6	133.0	130.4	127.7	130.4	133.0	135.6
100°	183.7	182.8	181.9	180.3	177.9	175.5	173.1	170.8	173.1	175.5	177.9
102.5°	227.3	226.2	225.1	223.6	221.6	219.7	217.8	215.9	217.8	219.7	221.6
105°	294.5	294.0	293.4	292.6	291.7	290.8	289.9	289.0	289.9	290.8	291.7
107.5°	368.6	368.6	368.6	367.9	366.7	365.3	364.0	362.7	364.0	365.3	366.7
110°	418.1	418.1	418.1	417.1	415.4	413.6	411.8	410.0	411.8	413.6	415.4



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	469.1	469.3	469.6	468.8	467.0	465.2	463.4	461.6	463.4	465.2	467.0
115°	544.3	544.9	545.5	544.9	543.1	541.3	539.5	537.7	539.5	541.3	543.1
117.5°	620.1	621.8	623.5	623.1	620.7	618.3	615.9	613.6	615.9	618.3	620.7
120°	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1	666.5	668.9	671.3
122.5°	719.1	720.8	722.4	721.8	718.9	716.0	713.2	710.3	713.2	716.0	718.9
125°	792.3	793.2	794.1	793.2	790.4	787.7	785.1	782.4	785.1	787.7	790.4
127.5°	865.2	866.3	867.4	866.2	862.8	859.3	856.0	852.6	856.0	859.3	862.8
130°	912.7	913.2	913.8	912.2	908.3	904.5	900.5	896.6	900.5	904.5	908.3
132.5°	960.6	960.6	960.5	958.8	955.6	952.4	949.3	946.1	949.3	952.4	955.6
135°	1028.6	1028.0	1027.3	1025.4	1022.1	1018.9	1015.6	1012.3	1015.6	1018.9	1022.1
137.5°	1095.9	1095.2	1094.4	1092.6	1089.9	1087.3	1084.6	1081.9	1084.6	1087.3	1089.9
140°	1139.7	1138.2	1136.7	1134.6	1131.9	1129.3	1126.5	1123.8	1126.5	1129.3	1131.9
142.5°	1181.5	1180.4	1179.5	1177.6	1174.9	1172.2	1169.6	1166.9	1169.6	1172.2	1174.9
145°	1242.6	1240.8	1239.0	1237.1	1234.9	1232.9	1230.8	1228.7	1230.8	1232.9	1234.9
147.5°	1298.1	1296.9	1295.7	1293.9	1291.4	1288.8	1286.3	1283.8	1286.3	1288.8	1291.4
150°	1332.5	1331.3	1330.1	1328.6	1326.9	1325.1	1323.2	1321.4	1323.2	1325.1	1326.9
152.5°	1366.5	1365.0	1363.6	1362.0	1360.1	1358.3	1356.6	1354.8	1356.6	1358.3	1360.1
155°	1411.0	1410.2	1409.3	1408.4	1407.5	1406.6	1405.7	1404.8	1405.7	1406.6	1407.5
157.5°	1451.6	1451.1	1450.5	1449.9	1449.4	1448.8	1448.1	1447.5	1448.1	1448.8	1449.4
160°	1476.8	1476.5	1476.2	1475.8	1475.2	1474.5	1474.0	1473.4	1474.0	1474.5	1475.2
162.5°	1498.3	1498.0	1497.7	1497.5	1497.4	1497.3	1497.2	1497.0	1497.2	1497.3	1497.4
165°	1527.1	1527.1	1527.1	1527.3	1527.6	1527.9	1528.2	1528.5	1528.2	1527.9	1527.6
167.5°	1550.7	1550.7	1550.8	1551.2	1552.1	1553.0	1553.9	1554.8	1553.9	1553.0	1552.1
170°	1564.1	1564.3	1564.6	1565.2	1566.1	1567.0	1567.9	1568.8	1567.9	1567.0	1566.1
172.5°	1573.7	1574.0	1574.3	1574.9	1575.8	1576.7	1577.6	1578.5	1577.6	1576.7	1575.8
175°	1584.7	1585.4	1586.0	1586.7	1587.6	1588.5	1589.4	1590.3	1589.4	1588.5	1587.6
177.5°	1590.7	1591.2	1591.7	1592.3	1593.0	1593.8	1594.5	1595.2	1594.5	1593.8	1593.0
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1678.6	1675.3	1669.2	1659.7	1654.0	1644.1	1637.4	1641.3	1642.2	1641.3	1640.3
5°	1633.5	1621.1	1604.0	1587.4	1572.0	1555.5	1546.0	1541.9	1533.6	1528.8	1526.5
7.5°	1579.0	1557.6	1533.3	1504.5	1480.0	1454.3	1441.2	1434.7	1417.7	1408.5	1400.4
10°	1538.3	1504.6	1480.3	1442.4	1419.4	1385.6	1362.6	1363.2	1340.1	1327.0	1317.6
12.5°	1493.3	1456.3	1415.9	1381.9	1349.8	1322.7	1294.9	1283.6	1259.2	1246.6	1221.0
15°	1418.8	1375.6	1333.0	1286.8	1254.3	1212.3	1172.1	1122.9	1083.3	1049.0	1039.6
17.5°	1337.4	1283.9	1241.2	1187.0	1131.2	1060.6	1014.0	985.4	961.5	943.4	930.0
20°	1281.6	1227.1	1181.5	1099.9	1024.8	976.9	942.5	920.6	895.8	876.3	865.6
22.5°	1222.8	1166.0	1103.9	1012.8	954.2	915.8	885.2	860.1	843.2	828.0	818.2
25°	1139.5	1077.4	975.1	912.3	865.0	824.7	803.4	788.1	770.3	749.7	740.1
27.5°	1051.5	952.7	879.2	832.6	787.4	761.3	742.1	719.1	703.2	693.9	684.0
30°	985.7	886.9	829.5	778.6	746.6	717.6	695.2	682.2	666.8	650.9	644.4
32.5°	912.3	833.4	778.4	736.0	703.6	678.9	661.1	640.1	628.9	619.1	605.5
35°	821.2	761.4	711.1	676.9	646.1	626.0	605.3	592.8	572.7	564.5	559.1
37.5°	744.0	692.2	654.7	618.5	594.1	571.9	559.2	539.5	530.7	519.2	508.0
40°	700.5	649.6	613.6	584.0	556.8	540.2	524.2	508.3	495.3	489.9	476.3
42.5°	656.0	614.7	578.5	546.1	527.9	510.3	490.2	478.4	464.9	456.3	447.9
45°	594.6	557.9	527.2	500.5	480.5	462.1	449.1	429.5	421.9	404.7	397.6
47.5°	540.6	506.6	477.2	451.9	432.3	420.4	401.3	386.0	373.7	363.2	354.0
50°	502.3	473.9	445.5	423.0	405.3	388.2	368.6	360.9	342.0	336.6	331.4
52.5°	467.3	440.3	414.3	392.3	374.5	357.8	340.6	330.6	317.8	312.5	308.6
55°	418.3	392.3	367.4	347.9	330.1	313.0	302.4	289.9	284.0	279.8	275.1
57.5°	369.1	345.6	326.6	306.8	289.0	275.4	263.1	255.6	249.4	244.0	238.4
60°	337.9	315.3	298.2	279.8	261.5	250.3	240.8	231.9	224.8	216.5	214.2
62.5°	304.7	285.1	269.3	251.5	235.5	225.2	216.2	207.8	199.3	187.2	183.9
65°	259.1	243.8	227.2	212.4	198.2	188.2	175.1	165.7	162.1	161.0	160.3
67.5°	217.9	203.4	189.2	174.1	161.1	151.9	145.2	143.7	141.2	140.5	138.9
70°	190.5	176.9	162.7	148.5	136.1	134.3	132.0	129.6	126.6	125.5	124.2
72.5°	165.9	151.9	137.6	126.3	120.9	118.7	116.3	114.0	111.9	110.8	110.0
75°	127.2	114.2	104.7	100.6	97.6	95.9	92.3	90.5	89.3	87.6	86.9
77.5°	91.6	84.3	79.9	77.3	74.2	72.3	70.3	68.5	67.2	66.9	65.9
80°	69.8	66.3	63.3	59.7	58.6	56.2	55.6	53.9	54.4	52.7	52.7
82.5°	54.2	49.7	47.2	45.6	44.4	42.4	41.9	41.0	41.2	39.9	39.9
85°	27.8	26.7	25.4	24.3	24.3	22.5	23.1	22.5	22.5	21.3	20.7
87.5°	12.1	12.7	13.0	14.4	15.7	16.5	16.4	15.8	15.7	15.5	15.1
90°	15.7	20.8	27.4	33.9	40.5	47.1	46.5	45.8	45.3	44.7	44.5
92.5°	34.4	36.6	38.1	39.7	41.2	42.7	42.9	43.0	43.1	43.2	43.3
95°	81.9	83.6	84.3	84.8	85.4	86.1	86.1	86.1	86.1	86.1	85.7
97.5°	138.2	140.1	141.2	142.4	143.5	144.6	144.6	144.6	144.6	144.6	144.6
100°	180.3	181.9	182.8	183.7	184.6	185.5	185.5	185.5	185.5	185.5	185.4
102.5°	223.6	225.1	226.2	227.3	228.5	229.6	229.9	230.1	230.3	230.6	230.5
105°	292.6	293.4	294.0	294.5	295.2	295.8	296.3	296.9	297.6	298.1	298.5
107.5°	367.9	368.6	368.6	368.6	368.6	368.6	368.8	369.1	369.3	369.5	369.0
110°	417.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1	417.6



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	468.8	469.6	469.3	469.1	468.9	468.6	467.9	467.2	466.5	465.7	465.0
115°	544.9	545.5	544.9	544.3	543.7	543.1	542.8	542.5	542.2	541.9	541.3
117.5°	623.1	623.5	621.8	620.1	618.4	616.8	616.1	615.4	614.7	613.9	613.1
120°	673.7	673.7	671.3	668.9	666.5	664.1	664.1	664.1	664.1	664.1	663.6
122.5°	721.8	722.4	720.8	719.1	717.4	715.7	715.0	714.3	713.5	712.8	712.1
125°	793.2	794.1	793.2	792.3	791.4	790.4	789.5	788.6	787.7	786.8	786.3
127.5°	866.2	867.4	866.3	865.2	864.2	863.1	861.9	860.9	859.8	858.7	857.7
130°	912.2	913.8	913.2	912.7	912.0	911.4	910.9	910.3	909.6	909.0	908.1
132.5°	958.8	960.5	960.6	960.6	960.8	960.9	959.6	958.3	957.0	955.6	954.5
135°	1025.4	1027.3	1028.0	1028.6	1029.1	1029.7	1029.5	1029.1	1028.9	1028.6	1028.0
137.5°	1092.6	1094.4	1095.2	1095.9	1096.7	1097.5	1097.3	1097.0	1096.8	1096.5	1095.8
140°	1134.6	1136.7	1138.2	1139.7	1141.2	1142.6	1142.6	1142.6	1142.6	1142.6	1142.1
142.5°	1177.6	1179.5	1180.4	1181.5	1182.5	1183.6	1183.7	1184.0	1184.3	1184.5	1184.0
145°	1237.1	1239.0	1240.8	1242.6	1244.4	1246.2	1246.4	1246.8	1247.1	1247.3	1246.9
147.5°	1293.9	1295.7	1296.9	1298.1	1299.3	1300.5	1301.2	1301.8	1302.4	1303.1	1302.9
150°	1328.6	1330.1	1331.3	1332.5	1333.7	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5
152.5°	1362.0	1363.6	1365.0	1366.5	1367.9	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9
155°	1408.4	1409.3	1410.2	1411.0	1411.9	1412.8	1414.3	1415.9	1417.4	1418.8	1419.2
157.5°	1449.9	1450.5	1451.1	1451.6	1452.2	1452.7	1454.6	1456.7	1458.7	1460.8	1461.1
160°	1475.8	1476.2	1476.5	1476.8	1477.1	1477.4	1479.2	1481.0	1482.7	1484.5	1484.9
162.5°	1497.5	1497.7	1498.0	1498.3	1498.6	1498.9	1500.9	1503.0	1505.0	1507.0	1507.3
165°	1527.3	1527.1	1527.1	1527.1	1527.1	1527.1	1529.2	1531.3	1533.4	1535.5	1535.8
167.5°	1551.2	1550.8	1550.7	1550.7	1550.6	1550.5	1552.6	1554.7	1556.8	1558.9	1559.2
170°	1565.2	1564.6	1564.3	1564.1	1563.7	1563.4	1565.5	1567.6	1569.7	1571.8	1571.9
172.5°	1574.9	1574.3	1574.0	1573.7	1573.4	1573.1	1575.2	1577.3	1579.4	1581.4	1581.6
175°	1586.7	1586.0	1585.4	1584.7	1584.2	1583.6	1585.7	1587.8	1589.8	1592.0	1592.1
177.5°	1592.3	1591.7	1591.2	1590.7	1590.3	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1635.1	1636.0	1634.6	1635.6	1634.6	1636.0	1635.1	1640.3	1641.3	1642.2	1641.3
5°	1523.5	1516.4	1515.2	1513.5	1515.2	1516.4	1523.5	1526.5	1528.8	1533.6	1541.9
7.5°	1390.3	1389.2	1386.3	1382.2	1386.3	1389.2	1390.3	1400.4	1408.5	1417.7	1434.7
10°	1304.6	1301.6	1301.1	1296.9	1301.1	1301.6	1304.6	1317.6	1327.0	1340.1	1363.2
12.5°	1204.3	1185.2	1183.2	1172.9	1183.2	1185.2	1204.3	1221.0	1246.6	1259.2	1283.6
15°	1025.4	1021.8	1010.0	1002.3	1010.0	1021.8	1025.4	1039.6	1049.0	1083.3	1122.9
17.5°	923.1	911.5	907.9	906.2	907.9	911.5	923.1	930.0	943.4	961.5	985.4
20°	857.3	846.7	844.9	843.7	844.9	846.7	857.3	865.6	876.3	895.8	920.6
22.5°	811.9	800.8	796.1	792.6	796.1	800.8	811.9	818.2	828.0	843.2	860.1
25°	734.2	730.1	727.7	726.6	727.7	730.1	734.2	740.1	749.7	770.3	788.1
27.5°	673.5	664.4	662.6	659.6	662.6	664.4	673.5	684.0	693.9	703.2	719.1
30°	639.0	636.1	631.9	628.3	631.9	636.1	639.0	644.4	650.9	666.8	682.2
32.5°	598.2	595.8	592.1	590.5	592.1	595.8	598.2	605.5	619.1	628.9	640.1
35°	553.2	544.9	541.4	536.0	541.4	544.9	553.2	559.1	564.5	572.7	592.8
37.5°	505.5	501.1	496.1	497.9	496.1	501.1	505.5	508.0	519.2	530.7	539.5
40°	468.6	465.7	464.5	463.9	464.5	465.7	468.6	476.3	489.9	495.3	508.3
42.5°	439.3	431.1	428.0	427.8	428.0	431.1	439.3	447.9	456.3	464.9	478.4
45°	394.7	386.9	381.7	382.2	381.7	386.9	394.7	397.6	404.7	421.9	429.5
47.5°	348.9	348.7	345.4	346.5	345.4	348.7	348.9	354.0	363.2	373.7	386.0
50°	327.2	323.6	321.3	321.8	321.3	323.6	327.2	331.4	336.6	342.0	360.9
52.5°	306.4	303.3	301.4	303.9	301.4	303.3	306.4	308.6	312.5	317.8	330.6
55°	272.2	268.6	268.0	267.4	268.0	268.6	272.2	275.1	279.8	284.0	289.9
57.5°	234.0	231.6	228.0	226.5	228.0	231.6	234.0	238.4	244.0	249.4	255.6
60°	206.5	201.8	195.8	195.3	195.8	201.8	206.5	214.2	216.5	224.8	231.9
62.5°	181.4	180.5	179.2	179.1	179.2	180.5	181.4	183.9	187.2	199.3	207.8
65°	159.2	158.5	159.2	159.7	159.2	158.5	159.2	160.3	161.0	162.1	165.7
67.5°	138.7	137.6	136.5	137.1	136.5	137.6	138.7	138.9	140.5	141.2	143.7
70°	123.1	122.4	121.9	121.9	121.9	122.4	123.1	124.2	125.5	126.6	129.6
72.5°	107.9	107.8	107.2	106.7	107.2	107.8	107.9	110.0	110.8	111.9	114.0
75°	86.4	85.2	85.2	85.2	85.2	85.2	86.4	86.9	87.6	89.3	90.5
77.5°	65.8	65.2	64.6	64.1	64.6	65.2	65.8	65.9	66.9	67.2	68.5
80°	52.1	51.5	50.9	50.9	50.9	51.5	52.1	52.7	52.7	54.4	53.9
82.5°	39.8	39.1	39.1	38.6	39.1	39.1	39.8	39.9	39.9	41.2	41.0
85°	21.3	21.8	21.3	22.5	21.3	21.8	21.3	20.7	21.3	22.5	22.5
87.5°	15.2	14.7	15.2	14.8	15.2	14.7	15.2	15.1	15.5	15.7	15.8
90°	44.9	45.1	45.4	45.7	45.4	45.1	44.9	44.5	44.7	45.3	45.8
92.5°	43.3	43.4	43.5	43.5	43.5	43.4	43.3	43.3	43.2	43.1	43.0
95°	85.2	84.5	83.9	83.4	83.9	84.5	85.2	85.7	86.1	86.1	86.1
97.5°	144.5	144.5	144.5	144.4	144.5	144.5	144.5	144.6	144.6	144.6	144.6
100°	185.0	184.8	184.5	184.1	184.5	184.8	185.0	185.4	185.5	185.5	185.5
102.5°	230.2	230.0	229.6	229.3	229.6	230.0	230.2	230.5	230.6	230.3	230.1
105°	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.5	298.1	297.6	296.9
107.5°	367.7	366.2	364.9	363.5	364.9	366.2	367.7	369.0	369.5	369.3	369.1
110°	416.7	415.8	414.9	414.0	414.9	415.8	416.7	417.6	418.1	418.1	418.1



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	464.4	463.8	463.1	462.4	463.1	463.8	464.4	465.0	465.7	466.5	467.2
115°	540.4	539.5	538.6	537.7	538.6	539.5	540.4	541.3	541.9	542.2	542.5
117.5°	612.2	611.3	610.4	609.5	610.4	611.3	612.2	613.1	613.9	614.7	615.4
120°	662.7	661.8	660.9	660.0	660.9	661.8	662.7	663.6	664.1	664.1	664.1
122.5°	711.5	710.9	710.2	709.5	710.2	710.9	711.5	712.1	712.8	713.5	714.3
125°	786.0	785.7	785.4	785.1	785.4	785.7	786.0	786.3	786.8	787.7	788.6
127.5°	856.8	855.8	854.9	853.9	854.9	855.8	856.8	857.7	858.7	859.8	860.9
130°	907.0	905.8	904.6	903.4	904.6	905.8	907.0	908.1	909.0	909.6	910.3
132.5°	953.6	952.6	951.6	950.7	951.6	952.6	953.6	954.5	955.6	957.0	958.3
135°	1027.1	1026.2	1025.3	1024.4	1025.3	1026.2	1027.1	1028.0	1028.6	1028.9	1029.1
137.5°	1094.7	1093.4	1092.3	1091.0	1092.3	1093.4	1094.7	1095.8	1096.5	1096.8	1097.0
140°	1140.9	1139.7	1138.4	1137.3	1138.4	1139.7	1140.9	1142.1	1142.6	1142.6	1142.6
142.5°	1182.9	1181.6	1180.4	1179.2	1180.4	1181.6	1182.9	1184.0	1184.5	1184.3	1184.0
145°	1245.7	1244.6	1243.3	1242.2	1243.3	1244.6	1245.7	1246.9	1247.3	1247.1	1246.8
147.5°	1301.7	1300.6	1299.5	1298.3	1299.5	1300.6	1301.7	1302.9	1303.1	1302.4	1301.8
150°	1337.6	1336.7	1335.8	1334.9	1335.8	1336.7	1337.6	1338.5	1338.5	1337.6	1336.7
152.5°	1372.7	1371.5	1370.5	1369.3	1370.5	1371.5	1372.7	1373.9	1373.9	1372.7	1371.5
155°	1418.3	1417.4	1416.5	1415.6	1416.5	1417.4	1418.3	1419.2	1418.8	1417.4	1415.9
157.5°	1459.6	1458.2	1456.8	1455.4	1456.8	1458.2	1459.6	1461.1	1460.8	1458.7	1456.7
160°	1483.6	1482.5	1481.3	1480.1	1481.3	1482.5	1483.6	1484.9	1484.5	1482.7	1481.0
162.5°	1505.9	1504.5	1503.1	1501.6	1503.1	1504.5	1505.9	1507.3	1507.0	1505.0	1503.0
165°	1534.3	1532.9	1531.3	1529.8	1531.3	1532.9	1534.3	1535.8	1535.5	1533.4	1531.3
167.5°	1557.6	1556.0	1554.5	1552.9	1554.5	1556.0	1557.6	1559.2	1558.9	1556.8	1554.7
170°	1570.1	1568.3	1566.6	1564.8	1566.6	1568.3	1570.1	1571.9	1571.8	1569.7	1567.6
172.5°	1579.8	1578.1	1576.3	1574.5	1576.3	1578.1	1579.8	1581.6	1581.4	1579.4	1577.3
175°	1590.3	1588.5	1586.7	1584.9	1586.7	1588.5	1590.3	1592.1	1592.0	1589.8	1587.8
177.5°	1594.1	1592.7	1591.2	1589.7	1591.2	1592.7	1594.1	1595.5	1595.5	1594.1	1592.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1637.4	1644.1	1654.0	1659.7	1669.2	1675.3	1678.6	1684.8	1688.1	1700.0	1712.3
5°	1546.0	1555.5	1572.0	1587.4	1604.0	1621.1	1633.5	1647.8	1660.8	1683.3	1706.9
7.5°	1441.2	1454.3	1480.0	1504.5	1533.3	1557.6	1579.0	1603.3	1625.0	1657.2	1690.7
10°	1362.6	1385.6	1419.4	1442.4	1480.3	1504.6	1538.3	1565.0	1595.1	1637.7	1675.6
12.5°	1294.9	1322.7	1349.8	1381.9	1415.9	1456.3	1493.3	1527.5	1563.4	1607.4	1651.9
15°	1172.1	1212.3	1254.3	1286.8	1333.0	1375.6	1418.8	1464.9	1508.7	1561.4	1619.3
17.5°	1014.0	1060.6	1131.2	1187.0	1241.2	1283.9	1337.4	1393.2	1444.8	1508.3	1572.9
20°	942.5	976.9	1024.8	1099.9	1181.5	1227.1	1281.6	1343.1	1402.2	1471.4	1540.7
22.5°	885.2	915.8	954.2	1012.8	1103.9	1166.0	1222.8	1285.3	1354.0	1424.6	1501.4
25°	803.4	824.7	865.0	912.3	975.1	1077.4	1139.5	1202.2	1276.8	1352.5	1440.1
27.5°	742.1	761.3	787.4	832.6	879.2	952.7	1051.5	1119.9	1194.2	1279.4	1370.3
30°	695.2	717.6	746.6	778.6	829.5	886.9	985.7	1065.0	1138.4	1225.9	1322.9
32.5°	661.1	678.9	703.6	736.0	778.4	833.4	912.3	1008.6	1080.1	1172.4	1273.7
35°	605.3	626.0	646.1	676.9	711.1	761.4	821.2	924.2	995.1	1086.3	1188.0
37.5°	559.2	571.9	594.1	618.5	654.7	692.2	744.0	836.3	913.2	1002.6	1106.8
40°	524.2	540.2	556.8	584.0	613.6	649.6	700.5	769.2	857.3	944.9	1046.6
42.5°	490.2	510.3	527.9	546.1	578.5	614.7	656.0	714.3	804.3	887.2	986.1
45°	449.1	462.1	480.5	500.5	527.2	557.9	594.6	645.5	731.9	803.4	896.3
47.5°	401.3	420.4	432.3	451.9	477.2	506.6	540.6	584.7	654.6	721.7	807.9
50°	368.6	388.2	405.3	423.0	445.5	473.9	502.3	544.9	601.1	671.5	752.0
52.5°	340.6	357.8	374.5	392.3	414.3	440.3	467.3	504.7	552.9	617.6	695.7
55°	302.4	313.0	330.1	347.9	367.4	392.3	418.3	449.7	491.1	545.5	608.9
57.5°	263.1	275.4	289.0	306.8	326.6	345.6	369.1	397.4	430.2	479.4	533.6
60°	240.8	250.3	261.5	279.8	298.2	315.3	337.9	361.5	392.3	434.9	481.0
62.5°	216.2	225.2	235.5	251.5	269.3	285.1	304.7	329.8	355.8	394.7	435.1
65°	175.1	188.2	198.2	212.4	227.2	243.8	259.1	279.3	302.4	333.1	369.2
67.5°	145.2	151.9	161.1	174.1	189.2	203.4	217.9	233.7	253.7	277.5	306.1
70°	132.0	134.3	136.1	148.5	162.7	176.9	190.5	205.3	222.5	242.0	266.8
72.5°	116.3	118.7	120.9	126.3	137.6	151.9	165.9	176.9	193.1	209.3	229.4
75°	92.3	95.9	97.6	100.6	104.7	114.2	127.2	137.9	147.3	159.7	175.8
77.5°	70.3	72.3	74.2	77.3	79.9	84.3	91.6	101.2	110.0	117.3	128.2
80°	55.6	56.2	58.6	59.7	63.3	66.3	69.8	77.5	86.4	89.3	97.0
82.5°	41.9	42.4	44.4	45.6	47.2	49.7	54.2	56.2	63.2	67.1	72.0
85°	23.1	22.5	24.3	24.3	25.4	26.7	27.8	30.8	32.5	37.3	38.4
87.5°	16.4	16.5	15.7	14.4	13.0	12.7	12.1	11.9	12.1	12.8	14.0
90°	46.5	47.1	40.5	33.9	27.4	20.8	15.7	12.1	8.5	4.9	1.3
92.5°	42.9	42.7	41.2	39.7	38.1	36.6	34.4	31.8	29.2	26.6	23.9
95°	86.1	86.1	85.4	84.8	84.3	83.6	81.9	78.8	75.9	72.9	69.9
97.5°	144.6	144.6	143.5	142.4	141.2	140.1	138.2	135.6	133.0	130.4	127.7
100°	185.5	185.5	184.6	183.7	182.8	181.9	180.3	177.9	175.5	173.1	170.8
102.5°	229.9	229.6	228.5	227.3	226.2	225.1	223.6	221.6	219.7	217.8	215.9
105°	296.3	295.8	295.2	294.5	294.0	293.4	292.6	291.7	290.8	289.9	289.0
107.5°	368.8	368.6	368.6	368.6	368.6	368.6	367.9	366.7	365.3	364.0	362.7
110°	418.1	418.1	418.1	418.1	418.1	418.1	417.1	415.4	413.6	411.8	410.0



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	467.9	468.6	468.9	469.1	469.3	469.6	468.8	467.0	465.2	463.4	461.6
115°	542.8	543.1	543.7	544.3	544.9	545.5	544.9	543.1	541.3	539.5	537.7
117.5°	616.1	616.8	618.4	620.1	621.8	623.5	623.1	620.7	618.3	615.9	613.6
120°	664.1	664.1	666.5	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1
122.5°	715.0	715.7	717.4	719.1	720.8	722.4	721.8	718.9	716.0	713.2	710.3
125°	789.5	790.4	791.4	792.3	793.2	794.1	793.2	790.4	787.7	785.1	782.4
127.5°	861.9	863.1	864.2	865.2	866.3	867.4	866.2	862.8	859.3	856.0	852.6
130°	910.9	911.4	912.0	912.7	913.2	913.8	912.2	908.3	904.5	900.5	896.6
132.5°	959.6	960.9	960.8	960.6	960.6	960.5	958.8	955.6	952.4	949.3	946.1
135°	1029.5	1029.7	1029.1	1028.6	1028.0	1027.3	1025.4	1022.1	1018.9	1015.6	1012.3
137.5°	1097.3	1097.5	1096.7	1095.9	1095.2	1094.4	1092.6	1089.9	1087.3	1084.6	1081.9
140°	1142.6	1142.6	1141.2	1139.7	1138.2	1136.7	1134.6	1131.9	1129.3	1126.5	1123.8
142.5°	1183.7	1183.6	1182.5	1181.5	1180.4	1179.5	1177.6	1174.9	1172.2	1169.6	1166.9
145°	1246.4	1246.2	1244.4	1242.6	1240.8	1239.0	1237.1	1234.9	1232.9	1230.8	1228.7
147.5°	1301.2	1300.5	1299.3	1298.1	1296.9	1295.7	1293.9	1291.4	1288.8	1286.3	1283.8
150°	1335.8	1334.9	1333.7	1332.5	1331.3	1330.1	1328.6	1326.9	1325.1	1323.2	1321.4
152.5°	1370.5	1369.3	1367.9	1366.5	1365.0	1363.6	1362.0	1360.1	1358.3	1356.6	1354.8
155°	1414.3	1412.8	1411.9	1411.0	1410.2	1409.3	1408.4	1407.5	1406.6	1405.7	1404.8
157.5°	1454.6	1452.7	1452.2	1451.6	1451.1	1450.5	1449.9	1449.4	1448.8	1448.1	1447.5
160°	1479.2	1477.4	1477.1	1476.8	1476.5	1476.2	1475.8	1475.2	1474.5	1474.0	1473.4
162.5°	1500.9	1498.9	1498.6	1498.3	1498.0	1497.7	1497.5	1497.4	1497.3	1497.2	1497.0
165°	1529.2	1527.1	1527.1	1527.1	1527.1	1527.1	1527.3	1527.6	1527.9	1528.2	1528.5
167.5°	1552.6	1550.5	1550.6	1550.7	1550.7	1550.8	1551.2	1552.1	1553.0	1553.9	1554.8
170°	1565.5	1563.4	1563.7	1564.1	1564.3	1564.6	1565.2	1566.1	1567.0	1567.9	1568.8
172.5°	1575.2	1573.1	1573.4	1573.7	1574.0	1574.3	1574.9	1575.8	1576.7	1577.6	1578.5
175°	1585.7	1583.6	1584.2	1584.7	1585.4	1586.0	1586.7	1587.6	1588.5	1589.4	1590.3
177.5°	1591.2	1589.7	1590.3	1590.7	1591.2	1591.7	1592.3	1593.0	1593.8	1594.5	1595.2
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1712.7	1714.1	1723.6	1727.9	1736.4	1739.7	1743.5	1742.6	1742.6	1744.5	1757.7
5°	1716.4	1728.2	1746.0	1763.2	1779.7	1793.9	1803.4	1812.8	1816.4	1833.5	1849.0
7.5°	1710.2	1732.1	1761.4	1787.5	1818.9	1843.3	1863.8	1882.0	1894.6	1919.6	1945.2
10°	1702.2	1733.0	1766.1	1799.8	1843.0	1875.5	1908.7	1934.1	1942.4	1979.7	2001.0
12.5°	1686.1	1727.2	1769.4	1813.1	1855.3	1900.1	1936.6	1962.0	1991.2	2024.6	2064.0
15°	1662.0	1709.3	1764.3	1820.5	1880.9	1935.3	1974.3	2018.7	2050.7	2087.4	2121.6
17.5°	1627.3	1688.3	1758.2	1823.3	1893.1	1951.5	2005.3	2047.8	2070.3	2091.2	2096.3
20°	1599.8	1665.5	1747.8	1824.7	1894.5	1961.9	2015.2	2050.7	2056.6	2057.2	2025.9
22.5°	1570.0	1644.2	1730.3	1809.0	1892.6	1967.6	2009.0	2024.2	2000.7	1960.6	1900.0
25°	1515.2	1601.1	1701.0	1790.9	1882.0	1953.0	1967.3	1940.6	1858.4	1772.0	1662.6
27.5°	1455.8	1552.3	1659.5	1759.4	1856.5	1900.5	1869.9	1773.9	1625.8	1497.0	1341.0
30°	1412.3	1520.5	1625.9	1737.7	1827.7	1846.6	1776.2	1634.8	1462.0	1267.9	1112.3
32.5°	1362.6	1476.0	1591.8	1707.4	1782.7	1764.2	1647.9	1473.8	1271.2	1080.5	933.4
35°	1291.6	1408.7	1533.6	1649.6	1697.5	1617.6	1443.7	1217.0	1010.0	831.9	730.7
37.5°	1209.6	1337.1	1467.0	1573.4	1570.0	1436.9	1200.0	966.1	792.0	686.7	614.7
40°	1151.4	1280.3	1420.6	1510.5	1472.0	1298.7	1041.9	821.2	694.0	610.0	557.3
42.5°	1095.6	1224.9	1364.2	1435.7	1368.9	1155.7	899.9	727.0	622.1	556.5	513.8
45°	1000.5	1137.2	1266.1	1305.8	1186.2	951.4	727.7	602.4	532.5	483.9	454.4
47.5°	907.6	1042.1	1159.8	1160.5	998.8	771.5	613.9	521.3	461.6	424.1	402.6
50°	850.8	978.6	1077.4	1062.0	878.6	686.3	549.0	469.2	419.5	390.5	368.0
52.5°	786.9	910.9	996.5	952.7	776.9	604.0	490.8	423.7	382.5	357.4	337.2
55°	694.0	804.1	864.4	798.2	633.6	502.3	414.7	362.1	331.4	310.0	292.8
57.5°	602.8	693.6	731.6	654.3	521.9	416.5	350.9	311.3	280.8	265.6	256.6
60°	545.5	623.0	649.6	564.5	453.8	364.4	310.6	273.9	251.5	241.4	232.6
62.5°	489.2	552.5	563.5	485.4	395.6	319.1	272.8	241.7	226.9	217.2	208.8
65°	405.9	451.5	446.1	383.4	313.0	253.2	219.5	200.5	189.3	175.8	161.0
67.5°	334.1	361.9	345.2	298.2	238.9	196.8	174.8	160.4	146.5	133.6	130.2
70°	288.7	304.7	287.0	243.8	195.8	165.1	147.3	130.2	121.9	119.0	113.6
72.5°	245.2	250.7	231.6	194.6	159.3	136.7	119.4	109.8	105.3	102.8	99.4
75°	184.0	179.9	163.3	134.3	110.7	95.2	90.0	86.4	83.5	81.1	79.3
77.5°	129.2	123.1	108.4	89.4	77.0	69.7	66.5	64.6	63.2	62.0	60.2
80°	97.0	92.9	78.1	63.9	58.6	55.0	53.2	50.9	50.9	49.7	47.9
82.5°	71.0	66.3	53.5	46.8	43.9	41.7	40.5	39.1	38.6	38.8	37.5
85°	37.3	30.1	26.7	25.4	23.6	22.5	23.1	21.8	21.8	21.8	21.3
87.5°	12.3	10.7	11.0	11.1	12.7	14.0	14.8	16.1	17.9	17.3	17.7
90°	4.9	8.5	12.1	15.7	20.8	27.4	33.9	40.5	47.1	46.5	45.8
92.5°	26.6	29.2	31.8	34.4	36.6	38.1	39.7	41.2	42.7	42.9	43.0
95°	72.9	75.9	78.8	81.9	83.6	84.3	84.8	85.4	86.1	86.1	86.1
97.5°	130.4	133.0	135.6	138.2	140.1	141.2	142.4	143.5	144.6	144.6	144.6
100°	173.1	175.5	177.9	180.3	181.9	182.8	183.7	184.6	185.5	185.5	185.5
102.5°	217.8	219.7	221.6	223.6	225.1	226.2	227.3	228.5	229.6	229.9	230.1
105°	289.9	290.8	291.7	292.6	293.4	294.0	294.5	295.2	295.8	296.3	296.9
107.5°	364.0	365.3	366.7	367.9	368.6	368.6	368.6	368.6	368.6	368.8	369.1
110°	411.8	413.6	415.4	417.1	418.1	418.1	418.1	418.1	418.1	418.1	418.1



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	463.4	465.2	467.0	468.8	469.6	469.3	469.1	468.9	468.6	467.9	467.2
115°	539.5	541.3	543.1	544.9	545.5	544.9	544.3	543.7	543.1	542.8	542.5
117.5°	615.9	618.3	620.7	623.1	623.5	621.8	620.1	618.4	616.8	616.1	615.4
120°	666.5	668.9	671.3	673.7	673.7	671.3	668.9	666.5	664.1	664.1	664.1
122.5°	713.2	716.0	718.9	721.8	722.4	720.8	719.1	717.4	715.7	715.0	714.3
125°	785.1	787.7	790.4	793.2	794.1	793.2	792.3	791.4	790.4	789.5	788.6
127.5°	856.0	859.3	862.8	866.2	867.4	866.3	865.2	864.2	863.1	861.9	860.9
130°	900.5	904.5	908.3	912.2	913.8	913.2	912.7	912.0	911.4	910.9	910.3
132.5°	949.3	952.4	955.6	958.8	960.5	960.6	960.6	960.8	960.9	959.6	958.3
135°	1015.6	1018.9	1022.1	1025.4	1027.3	1028.0	1028.6	1029.1	1029.7	1029.5	1029.1
137.5°	1084.6	1087.3	1089.9	1092.6	1094.4	1095.2	1095.9	1096.7	1097.5	1097.3	1097.0
140°	1126.5	1129.3	1131.9	1134.6	1136.7	1138.2	1139.7	1141.2	1142.6	1142.6	1142.6
142.5°	1169.6	1172.2	1174.9	1177.6	1179.5	1180.4	1181.5	1182.5	1183.6	1183.7	1184.0
145°	1230.8	1232.9	1234.9	1237.1	1239.0	1240.8	1242.6	1244.4	1246.2	1246.4	1246.8
147.5°	1286.3	1288.8	1291.4	1293.9	1295.7	1296.9	1298.1	1299.3	1300.5	1301.2	1301.8
150°	1323.2	1325.1	1326.9	1328.6	1330.1	1331.3	1332.5	1333.7	1334.9	1335.8	1336.7
152.5°	1356.6	1358.3	1360.1	1362.0	1363.6	1365.0	1366.5	1367.9	1369.3	1370.5	1371.5
155°	1405.7	1406.6	1407.5	1408.4	1409.3	1410.2	1411.0	1411.9	1412.8	1414.3	1415.9
157.5°	1448.1	1448.8	1449.4	1449.9	1450.5	1451.1	1451.6	1452.2	1452.7	1454.6	1456.7
160°	1474.0	1474.5	1475.2	1475.8	1476.2	1476.5	1476.8	1477.1	1477.4	1479.2	1481.0
162.5°	1497.2	1497.3	1497.4	1497.5	1497.7	1498.0	1498.3	1498.6	1498.9	1500.9	1503.0
165°	1528.2	1527.9	1527.6	1527.3	1527.1	1527.1	1527.1	1527.1	1527.1	1529.2	1531.3
167.5°	1553.9	1553.0	1552.1	1551.2	1550.8	1550.7	1550.7	1550.6	1550.5	1552.6	1554.7
170°	1567.9	1567.0	1566.1	1565.2	1564.6	1564.3	1564.1	1563.7	1563.4	1565.5	1567.6
172.5°	1577.6	1576.7	1575.8	1574.9	1574.3	1574.0	1573.7	1573.4	1573.1	1575.2	1577.3
175°	1589.4	1588.5	1587.6	1586.7	1586.0	1585.4	1584.7	1584.2	1583.6	1585.7	1587.8
177.5°	1594.5	1593.8	1593.0	1592.3	1591.7	1591.2	1590.7	1590.3	1589.7	1591.2	1592.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8	1702.8
2.5°	1762.5	1768.6	1771.4	1771.4	1774.8	1773.3	1771.9
5°	1863.8	1875.0	1877.3	1888.0	1895.7	1893.3	1894.5
7.5°	1964.4	1982.5	2000.4	2008.6	2009.8	2014.6	2016.3
10°	2026.4	2041.2	2069.0	2064.8	2085.6	2097.4	2077.9
12.5°	2086.1	2106.0	2125.4	2130.7	2142.4	2146.2	2138.5
15°	2140.0	2150.7	2151.9	2148.9	2152.4	2149.5	2138.2
17.5°	2089.6	2072.3	2037.3	2020.7	2007.6	1988.2	1980.4
20°	2006.3	1955.4	1896.2	1872.6	1844.8	1790.4	1803.4
22.5°	1826.5	1768.4	1709.3	1640.2	1607.2	1555.6	1552.5
25°	1546.6	1446.6	1336.6	1259.6	1214.7	1163.2	1140.7
27.5°	1202.5	1076.6	986.4	940.8	899.2	858.4	856.8
30°	976.2	881.5	811.7	772.7	747.3	730.1	733.7
32.5°	822.9	758.0	711.0	678.5	659.7	646.8	646.6
35°	672.7	628.3	598.2	584.5	571.0	561.5	562.0
37.5°	575.7	549.0	532.3	517.2	508.7	504.1	501.5
40°	526.0	504.1	491.1	482.2	475.1	468.6	467.4
42.5°	486.7	468.6	455.6	448.6	441.9	437.4	436.1
45°	431.9	417.1	405.3	397.6	394.7	390.5	390.5
47.5°	384.2	369.7	360.4	355.6	350.5	347.8	347.7
50°	352.0	340.8	332.5	329.6	325.4	323.6	323.1
52.5°	323.2	314.8	308.9	306.8	305.1	302.8	303.2
55°	284.0	279.3	276.9	275.1	272.2	268.6	271.0
57.5°	251.0	246.9	240.6	235.0	232.3	229.8	230.8
60°	227.8	219.5	211.2	204.7	203.0	197.6	197.6
62.5°	198.4	186.8	176.6	173.0	171.2	168.7	168.3
65°	152.7	147.9	145.5	143.2	142.0	142.0	140.8
67.5°	126.5	124.6	122.0	121.5	120.2	119.8	119.5
70°	111.8	109.4	108.3	107.7	106.5	107.1	105.3
72.5°	97.6	95.8	95.5	94.0	93.3	93.4	92.0
75°	77.0	77.0	76.3	75.7	74.5	73.9	74.5
77.5°	59.2	59.3	58.2	58.1	58.0	58.1	57.5
80°	47.3	47.9	47.3	46.7	46.2	46.7	46.2
82.5°	37.4	36.6	36.5	36.3	36.2	35.8	35.8
85°	21.3	21.8	21.3	20.7	20.7	20.7	21.3
87.5°	17.1	16.9	16.9	17.0	17.0	17.1	16.7
90°	45.3	44.7	44.5	44.9	45.1	45.4	45.7
92.5°	43.1	43.2	43.3	43.3	43.4	43.5	43.5
95°	86.1	86.1	85.7	85.2	84.5	83.9	83.4
97.5°	144.6	144.6	144.6	144.5	144.5	144.5	144.4
100°	185.5	185.5	185.4	185.0	184.8	184.5	184.1
102.5°	230.3	230.6	230.5	230.2	230.0	229.6	229.3
105°	297.6	298.1	298.5	298.5	298.5	298.5	298.5
107.5°	369.3	369.5	369.0	367.7	366.2	364.9	363.5
110°	418.1	418.1	417.6	416.7	415.8	414.9	414.0



TEST NUMBER: P331842-940

CATALOG NUMBER: S122RDIW-S865D1440U940-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	466.5	465.7	465.0	464.4	463.8	463.1	462.4
115°	542.2	541.9	541.3	540.4	539.5	538.6	537.7
117.5°	614.7	613.9	613.1	612.2	611.3	610.4	609.5
120°	664.1	664.1	663.6	662.7	661.8	660.9	660.0
122.5°	713.5	712.8	712.1	711.5	710.9	710.2	709.5
125°	787.7	786.8	786.3	786.0	785.7	785.4	785.1
127.5°	859.8	858.7	857.7	856.8	855.8	854.9	853.9
130°	909.6	909.0	908.1	907.0	905.8	904.6	903.4
132.5°	957.0	955.6	954.5	953.6	952.6	951.6	950.7
135°	1028.9	1028.6	1028.0	1027.1	1026.2	1025.3	1024.4
137.5°	1096.8	1096.5	1095.8	1094.7	1093.4	1092.3	1091.0
140°	1142.6	1142.6	1142.1	1140.9	1139.7	1138.4	1137.3
142.5°	1184.3	1184.5	1184.0	1182.9	1181.6	1180.4	1179.2
145°	1247.1	1247.3	1246.9	1245.7	1244.6	1243.3	1242.2
147.5°	1302.4	1303.1	1302.9	1301.7	1300.6	1299.5	1298.3
150°	1337.6	1338.5	1338.5	1337.6	1336.7	1335.8	1334.9
152.5°	1372.7	1373.9	1373.9	1372.7	1371.5	1370.5	1369.3
155°	1417.4	1418.8	1419.2	1418.3	1417.4	1416.5	1415.6
157.5°	1458.7	1460.8	1461.1	1459.6	1458.2	1456.8	1455.4
160°	1482.7	1484.5	1484.9	1483.6	1482.5	1481.3	1480.1
162.5°	1505.0	1507.0	1507.3	1505.9	1504.5	1503.1	1501.6
165°	1533.4	1535.5	1535.8	1534.3	1532.9	1531.3	1529.8
167.5°	1556.8	1558.9	1559.2	1557.6	1556.0	1554.5	1552.9
170°	1569.7	1571.8	1571.9	1570.1	1568.3	1566.6	1564.8
172.5°	1579.4	1581.4	1581.6	1579.8	1578.1	1576.3	1574.5
175°	1589.8	1592.0	1592.1	1590.3	1588.5	1586.7	1584.9
177.5°	1594.1	1595.5	1595.5	1594.1	1592.7	1591.2	1589.7
180°	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0	1593.0

(END OF REPORT)