

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332489-930

Luminaire Tested: **S123RDIW-S1165D1535U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332489-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1535U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7910.7 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332489-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332489-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	81	75	70	81	75	70	65	63	59	56	51	49	46	41	39	38	33				
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	37	34	32	28				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24				
5	68	57	49	43	62	52	46	40	44	39	35	37	33	30	30	27	25	21				
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17				
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15				
9	50	38	31	26	46	36	29	24	30	25	22	26	22	19	21	18	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17009	17009	17009
5°	17074	16839	16935
10°	16978	16628	16571
15°	16796	16238	16067
20°	16544	15753	15385
25°	16286	15206	14719
30°	15945	14574	13779
35°	15594	13943	12917
40°	15271	13200	11849
45°	14846	12466	10886
50°	14380	11632	9808
55°	13902	10678	8801
60°	13464	9657	7698
65°	12893	8550	6594
70°	12180	7179	5325
75°	11137	5648	5011
80°	9930	5002	4612
85°	8386	4434	4113



TEST NUMBER: P332489-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.4	1.9
10°-20°	412.9	5.2
20°-30°	594.5	7.5
30°-40°	669.6	8.5
40°-50°	640.6	8.1
50°-60°	524.6	6.6
60°-70°	354.0	4.5
70°-80°	178.1	2.3
80°-90°	51.7	0.7
90°-100°	102.0	1.3
100°-110°	305.2	3.9
110°-120°	519.0	6.6
120°-130°	682.7	8.6
130°-140°	767.4	9.7
140°-150°	754.3	9.5
150°-160°	635.0	8.0
160°-170°	422.7	5.3
170°-180°	148.0	1.9
0°-30°	1155.7	14.6
0°-40°	1825.4	23.1
0°-60°	2990.6	37.8
0°-90°	3574.4	45.2
90°-120°	926.2	11.7
90°-150°	3130.5	39.6
90°-180°	4336.0	54.8
0°-180°	7910.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1580	1573	1558	1569	1567	150
15°	1507	1492	1457	1451	1442	424
25°	1371	1338	1280	1254	1239	630
35°	1187	1139	1061	1008	983	742
45°	975	915	819	748	715	752
55°	741	675	569	497	469	664
65°	506	434	336	276	259	501
75°	268	206	136	124	120	286
85°	68	41	36	33	33	76
90°	1	14	30	34	37	8
95°	73	81	91	96	96	82
105°	277	280	290	290	293	296
115°	522	526	524	525	524	517
125°	765	768	766	761	756	682
135°	992	999	998	994	991	764
145°	1204	1206	1210	1208	1204	752
155°	1378	1378	1379	1384	1376	634
165°	1501	1498	1498	1504	1496	423
175°	1561	1557	1556	1563	1555	148
180°	1565	1565	1565	1565	1565	



TEST NUMBER: P332489-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1585.3	1584.4	1583.5	1582.6	1581.7	1579.8	1577.1	1574.3	1571.7	1568.9	1571.4
5°	1580.2	1578.7	1577.4	1575.9	1574.5	1572.1	1568.6	1565.2	1561.8	1558.4	1561.0
7.5°	1565.5	1564.1	1562.5	1561.0	1559.4	1556.4	1552.0	1547.5	1543.1	1538.6	1540.1
10°	1553.3	1551.3	1549.3	1547.3	1545.3	1541.7	1536.6	1531.5	1526.3	1521.3	1521.5
12.5°	1535.9	1533.7	1531.4	1529.2	1527.0	1522.7	1516.5	1510.2	1503.9	1497.6	1497.5
15°	1507.2	1504.0	1500.9	1497.7	1494.6	1489.1	1481.1	1473.1	1465.1	1457.2	1455.7
17.5°	1471.0	1467.4	1463.7	1460.0	1456.5	1449.5	1439.4	1429.2	1419.1	1409.0	1406.0
20°	1444.3	1439.8	1435.3	1430.7	1426.1	1418.5	1407.6	1396.8	1385.9	1375.2	1371.4
22.5°	1414.6	1409.3	1404.1	1398.9	1393.7	1385.3	1373.8	1362.3	1350.8	1339.2	1334.6
25°	1371.3	1364.2	1357.1	1349.9	1342.8	1332.7	1319.6	1306.5	1293.4	1280.3	1274.3
27.5°	1318.7	1310.9	1303.0	1295.2	1287.3	1276.1	1261.5	1246.9	1232.3	1217.7	1209.4
30°	1282.9	1274.3	1265.8	1257.2	1248.7	1236.4	1220.5	1204.5	1188.6	1172.6	1162.9
32.5°	1247.0	1237.3	1227.6	1217.9	1208.3	1195.0	1178.1	1161.2	1144.4	1127.6	1117.0
35°	1186.7	1176.5	1166.2	1156.0	1145.7	1131.8	1114.1	1096.5	1078.8	1061.1	1048.9
37.5°	1125.8	1114.4	1102.9	1091.5	1080.2	1065.0	1046.2	1027.4	1008.5	989.6	975.8
40°	1086.8	1074.2	1061.7	1049.2	1036.7	1020.3	1000.0	979.8	959.6	939.4	924.5
42.5°	1042.7	1030.1	1017.7	1005.1	992.5	975.8	955.0	934.0	913.1	892.3	876.0
45°	975.3	962.5	949.7	936.9	924.0	906.6	884.7	862.7	840.8	818.9	802.7
47.5°	907.8	893.8	879.7	865.7	851.6	833.6	811.6	789.7	767.8	745.9	728.2
50°	858.7	845.3	831.8	818.5	805.1	786.9	763.9	740.8	717.7	694.6	676.9
52.5°	814.6	800.1	785.5	771.0	756.4	737.8	714.9	692.1	669.3	646.5	628.1
55°	740.8	726.8	712.8	698.9	684.9	665.9	641.6	617.4	593.2	569.0	552.5
57.5°	672.5	657.4	642.1	627.0	611.7	592.0	567.7	543.3	519.0	494.7	479.1
60°	625.4	609.8	594.1	578.5	562.7	543.1	519.4	495.9	472.2	448.6	433.2
62.5°	578.2	562.6	546.9	531.2	515.6	495.9	472.3	448.7	425.0	401.4	386.9
65°	506.2	490.6	474.9	459.3	443.6	424.6	402.4	380.2	358.0	335.7	321.8
67.5°	434.2	418.3	402.5	386.7	370.9	352.3	331.0	309.7	288.4	267.1	256.7
70°	387.0	371.7	356.3	340.9	325.5	307.9	288.0	268.0	248.1	228.1	218.2
72.5°	339.9	324.7	309.6	294.4	279.2	262.6	244.5	226.4	208.3	190.2	182.1
75°	267.8	254.2	240.5	226.8	213.2	198.5	182.9	167.1	151.5	135.8	133.0
77.5°	202.2	189.9	177.5	165.2	152.8	141.5	131.5	121.4	111.3	101.3	99.7
80°	160.2	148.5	136.8	125.1	113.5	104.7	98.7	92.7	86.7	80.7	79.9
82.5°	120.2	110.1	100.0	89.9	79.9	73.5	70.7	67.8	65.1	62.3	61.4
85°	67.9	61.6	55.4	49.2	42.9	39.3	38.5	37.6	36.8	35.9	35.3
87.5°	24.9	22.9	21.0	19.0	17.0	16.4	17.1	17.8	18.5	19.2	19.2
90°	1.2	4.0	6.7	9.5	12.1	15.3	18.8	22.4	25.9	29.5	30.6
92.5°	29.8	31.6	33.4	35.3	37.2	39.1	41.2	43.1	45.2	47.2	48.1
95°	72.6	74.4	76.4	78.3	80.2	82.3	84.4	86.6	88.8	91.0	92.0
97.5°	128.8	130.3	131.7	133.1	134.5	136.0	137.6	139.2	140.8	142.4	143.7
100°	167.2	168.8	170.5	172.1	173.7	175.3	176.6	178.0	179.4	180.8	181.6
102.5°	211.5	212.5	213.4	214.4	215.4	216.8	218.6	220.4	222.2	224.0	224.9
105°	276.6	277.2	277.7	278.3	278.8	280.3	282.7	285.2	287.7	290.2	290.2
107.5°	352.4	352.7	353.0	353.4	353.7	354.3	355.3	356.3	357.3	358.2	359.1
110°	399.6	400.1	400.6	401.2	401.8	402.3	402.8	403.4	403.9	404.5	405.6



TEST NUMBER: P332489-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	448.7	449.1	449.4	449.7	450.0	450.3	450.4	450.5	450.6	450.7	452.0
115°	522.5	523.3	524.2	525.0	525.8	525.9	525.4	524.8	524.3	523.7	524.0
117.5°	596.8	597.3	597.9	598.4	598.9	598.8	598.2	597.5	596.7	596.1	596.0
120°	643.0	644.7	646.3	647.9	649.5	649.7	648.3	646.9	645.6	644.2	643.9
122.5°	691.2	692.4	693.6	694.8	696.0	696.3	695.5	694.8	694.1	693.4	692.7
125°	764.7	765.5	766.4	767.2	768.0	768.1	767.6	767.0	766.5	766.0	764.8
127.5°	832.6	834.3	836.1	837.8	839.6	840.2	839.5	838.9	838.4	837.7	836.2
130°	877.8	880.0	882.2	884.4	886.6	887.2	886.4	885.6	884.8	883.9	882.9
132.5°	923.1	925.2	927.4	929.6	931.8	932.6	932.0	931.4	930.7	930.2	928.9
135°	992.1	993.8	995.4	997.0	998.7	999.4	999.1	998.8	998.6	998.3	997.2
137.5°	1056.1	1057.4	1058.8	1060.2	1061.5	1062.6	1063.3	1064.0	1064.7	1065.4	1064.3
140°	1100.3	1101.7	1103.1	1104.4	1105.8	1106.6	1106.9	1107.2	1107.4	1107.7	1107.4
142.5°	1140.7	1142.0	1143.4	1144.8	1146.1	1147.0	1147.5	1148.0	1148.5	1149.0	1148.8
145°	1203.6	1204.2	1204.7	1205.3	1205.8	1206.5	1207.3	1208.1	1208.9	1209.7	1209.5
147.5°	1258.7	1259.6	1260.6	1261.7	1262.7	1263.5	1264.3	1265.0	1265.8	1266.6	1266.6
150°	1297.1	1297.6	1298.1	1298.7	1299.3	1299.8	1300.3	1300.9	1301.4	1302.0	1302.0
152.5°	1328.5	1329.3	1330.1	1330.8	1331.5	1332.1	1332.4	1332.8	1333.1	1333.4	1333.9
155°	1378.2	1378.2	1378.2	1378.2	1378.2	1378.3	1378.6	1378.8	1379.2	1379.4	1380.5
157.5°	1420.5	1420.2	1419.8	1419.5	1419.2	1419.1	1419.4	1419.5	1419.8	1420.0	1421.1
160°	1447.1	1446.5	1445.9	1445.4	1444.9	1444.5	1444.5	1444.5	1444.5	1444.5	1445.9
162.5°	1470.6	1469.9	1469.1	1468.4	1467.6	1467.3	1467.5	1467.8	1467.9	1468.2	1469.6
165°	1501.1	1500.3	1499.5	1498.7	1497.9	1497.5	1497.5	1497.5	1497.5	1497.5	1499.1
167.5°	1525.5	1524.4	1523.3	1522.2	1521.1	1520.7	1520.9	1521.1	1521.3	1521.5	1523.2
170°	1539.2	1538.1	1537.1	1535.9	1534.9	1534.3	1534.3	1534.3	1534.3	1534.3	1536.3
172.5°	1550.0	1549.0	1547.8	1546.8	1545.7	1545.2	1545.2	1545.2	1545.2	1545.2	1546.9
175°	1561.4	1560.3	1559.2	1558.1	1557.0	1556.5	1556.5	1556.5	1556.5	1556.5	1558.1
177.5°	1566.0	1565.2	1564.3	1563.4	1562.5	1562.1	1562.1	1562.1	1562.1	1562.1	1563.4
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0



TEST NUMBER: P332489-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2	1580.2
2.5°	1573.9	1576.5	1578.9	1580.0	1579.5	1579.1	1578.6	1578.1
5°	1563.5	1566.1	1568.6	1569.6	1569.0	1568.5	1567.9	1567.3
7.5°	1541.5	1543.0	1544.3	1544.6	1543.6	1542.6	1541.6	1540.7
10°	1521.8	1522.1	1522.4	1521.8	1520.4	1519.0	1517.5	1516.1
12.5°	1497.3	1497.1	1497.0	1496.1	1494.4	1492.7	1491.1	1489.5
15°	1454.3	1452.9	1451.5	1449.8	1447.7	1445.8	1443.7	1441.8
17.5°	1403.0	1399.9	1396.9	1393.9	1390.9	1388.0	1385.0	1382.0
20°	1367.7	1364.0	1360.3	1356.7	1353.3	1349.9	1346.5	1343.1
22.5°	1330.0	1325.4	1320.8	1316.9	1313.7	1310.5	1307.3	1304.2
25°	1268.4	1262.3	1256.4	1251.8	1248.7	1245.5	1242.4	1239.3
27.5°	1201.1	1192.8	1184.5	1177.9	1173.1	1168.4	1163.6	1158.8
30°	1153.2	1143.6	1133.9	1126.8	1122.3	1117.7	1113.1	1108.6
32.5°	1106.4	1095.8	1085.2	1077.5	1072.7	1067.9	1063.2	1058.3
35°	1036.7	1024.4	1012.2	1003.5	998.3	993.2	988.1	983.0
37.5°	961.8	947.9	934.0	923.9	917.6	911.3	905.0	898.6
40°	909.8	895.0	880.2	869.5	862.9	856.4	849.9	843.3
42.5°	859.9	843.7	827.5	816.5	810.7	804.8	798.9	793.0
45°	786.4	770.2	754.0	742.5	735.6	728.8	721.9	715.1
47.5°	710.5	692.9	675.2	663.4	657.3	651.2	645.1	639.0
50°	659.3	641.6	623.9	611.9	605.4	598.8	592.2	585.7
52.5°	609.8	591.4	573.1	560.9	555.1	549.3	543.4	537.5
55°	536.0	519.4	503.0	491.9	486.2	480.5	474.7	469.0
57.5°	463.5	447.8	432.3	422.0	417.2	412.4	407.5	402.7
60°	417.8	402.4	387.0	376.9	372.1	367.2	362.4	357.6
62.5°	372.4	358.0	343.5	333.8	328.6	323.6	318.5	313.5
65°	307.9	293.9	280.0	271.4	268.3	265.1	262.0	258.9
67.5°	246.2	235.8	225.3	218.5	215.2	211.7	208.4	205.0
70°	208.1	198.2	188.3	181.7	178.6	175.5	172.3	169.2
72.5°	173.9	165.8	157.6	152.9	151.6	150.3	149.0	147.7
75°	130.1	127.3	124.4	122.8	122.2	121.6	121.1	120.5
77.5°	98.2	96.6	95.1	94.0	93.4	92.9	92.3	91.7
80°	79.0	78.2	77.3	76.6	76.1	75.5	74.9	74.4
82.5°	60.6	59.8	58.9	58.4	58.3	58.1	58.0	58.0
85°	34.7	34.2	33.6	33.3	33.3	33.3	33.3	33.3
87.5°	19.2	19.2	19.2	19.2	19.0	18.9	18.8	18.7
90°	31.7	32.8	33.9	34.7	35.2	35.8	36.4	36.9
92.5°	48.9	49.8	50.7	51.0	50.6	50.3	50.0	49.7
95°	93.2	94.2	95.3	95.9	95.9	95.9	95.9	95.9
97.5°	144.9	146.1	147.4	148.0	147.9	147.7	147.7	147.6
100°	182.4	183.2	184.0	184.7	185.2	185.8	186.3	186.9
102.5°	225.7	226.5	227.3	227.6	227.6	227.4	227.3	227.2
105°	290.2	290.2	290.2	290.4	291.0	291.6	292.0	292.6
107.5°	360.0	360.9	361.7	362.0	361.7	361.3	361.0	360.7
110°	406.7	407.7	408.9	409.1	408.5	408.1	407.5	406.9



TEST NUMBER: P332489-930

CATALOG NUMBER: S123RDIW-S1165D1535U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	453.3	454.6	455.9	456.6	456.5	456.3	456.2	456.1
115°	524.3	524.6	524.8	524.8	524.6	524.3	524.0	523.7
117.5°	595.9	595.9	595.8	595.4	594.6	593.9	593.1	592.3
120°	643.7	643.4	643.1	642.7	642.2	641.6	641.1	640.5
122.5°	691.9	691.3	690.6	689.8	689.1	688.3	687.5	686.7
125°	763.8	762.6	761.6	760.4	759.4	758.3	757.2	756.1
127.5°	834.7	833.2	831.6	830.2	829.0	827.7	826.5	825.2
130°	881.7	880.7	879.6	878.1	876.2	874.2	872.4	870.4
132.5°	927.6	926.3	925.0	923.6	922.1	920.6	919.1	917.6
135°	996.1	995.0	993.9	993.1	992.5	992.0	991.5	990.9
137.5°	1063.2	1062.0	1060.9	1059.7	1058.7	1057.7	1056.6	1055.6
140°	1107.2	1106.9	1106.6	1105.5	1103.6	1101.7	1099.8	1097.9
142.5°	1148.5	1148.2	1147.9	1147.0	1145.6	1144.1	1142.6	1141.2
145°	1209.2	1208.9	1208.7	1207.9	1206.9	1205.8	1204.7	1203.6
147.5°	1266.6	1266.6	1266.6	1265.8	1264.1	1262.5	1260.8	1259.1
150°	1302.0	1302.0	1302.0	1301.1	1299.5	1297.9	1296.2	1294.6
152.5°	1334.3	1334.7	1335.2	1334.7	1333.3	1331.9	1330.4	1329.0
155°	1381.6	1382.7	1383.8	1383.4	1381.4	1379.6	1377.6	1375.7
157.5°	1422.3	1423.4	1424.6	1424.4	1422.9	1421.3	1419.8	1418.3
160°	1447.3	1448.7	1450.0	1450.2	1449.1	1448.0	1446.9	1445.8
162.5°	1470.9	1472.3	1473.7	1473.5	1471.7	1470.0	1468.2	1466.5
165°	1500.7	1502.4	1504.0	1503.9	1501.9	1500.1	1498.1	1496.2
167.5°	1524.9	1526.6	1528.3	1528.3	1526.6	1524.9	1523.2	1521.5
170°	1538.1	1540.1	1542.0	1542.0	1540.1	1538.1	1536.3	1534.3
172.5°	1548.5	1550.2	1551.9	1551.8	1549.9	1548.0	1546.1	1544.2
175°	1559.7	1561.4	1563.0	1562.8	1561.0	1559.0	1557.1	1555.3
177.5°	1564.7	1566.0	1567.3	1567.2	1565.7	1564.2	1562.7	1561.1
180°	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0	1565.0

(END OF REPORT)