

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331828-940

Luminaire Tested: **S122RDIW-S865D435U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331828-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S865D435U940-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4029.7 lumens
Efficiency: N/A
Efficacy: 87.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331828-940

CATALOG NUMBER: S122RDIW-S865D435U940-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331828-940

CATALOG NUMBER: S122RDIW-S865D435U940-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62	58
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49
3	86	77	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40	37
5	73	61	53	47	68	58	51	45	52	47	42	47	42	39	42	38	35	33
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	38	35	31	29
7	62	50	42	37	59	48	41	35	43	37	33	39	34	31	35	31	28	26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	23
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23	21
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21111	21111	21111
5°	21191	20846	20960
10°	21028	20505	20330
15°	20787	19896	19323
20°	20452	19029	18076
25°	20110	18045	16864
30°	19634	17031	15310
35°	19170	15930	13947
40°	18704	14790	12370
45°	18155	13511	10942
50°	17595	12215	9540
55°	17022	10826	8194
60°	16353	9361	6801
65°	15595	7866	6193
70°	14691	6477	5693
75°	13587	5908	5315
80°	11985	5281	4844
85°	9429	4168	4168



TEST NUMBER: P331828-940

CATALOG NUMBER: S122RDIW-S865D435U940-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.4	3.0
10°-20°	336.0	8.3
20°-30°	471.9	11.7
30°-40°	514.6	12.8
40°-50°	473.1	11.7
50°-60°	371.6	9.2
60°-70°	242.3	6.0
70°-80°	124.9	3.1
80°-90°	34.3	0.9
90°-100°	30.3	0.8
100°-110°	94.2	2.3
110°-120°	161.0	4.0
120°-130°	211.8	5.3
130°-140°	237.7	5.9
140°-150°	233.1	5.8
150°-160°	195.5	4.9
160°-170°	129.7	3.2
170°-180°	45.3	1.1
0°-30°	930.3	23.1
0°-40°	1444.9	35.9
0°-60°	2289.6	56.8
0°-90°	2691.1	66.8
90°-120°	285.6	7.1
90°-150°	968.1	24.0
90°-180°	1339.0	33.2
0°-180°	4029.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1308	1308	1308	1308	1308	
5°	1308	1301	1286	1296	1293	124
15°	1244	1229	1190	1168	1156	350
25°	1129	1089	1013	966	947	519
35°	973	910	808	736	708	608
45°	795	713	592	511	479	614
55°	605	510	385	316	291	540
65°	408	312	206	168	162	405
75°	218	137	95	87	85	230
85°	51	27	22	22	22	60
90°	0	5	14	13	14	3
95°	21	25	26	26	25	24
105°	87	88	89	90	90	92
115°	162	164	163	163	162	160
125°	235	238	238	236	236	210
135°	304	308	309	309	308	235
145°	369	372	374	375	373	231
155°	422	423	425	426	425	194
165°	459	459	459	462	460	129
175°	478	477	476	478	476	45
180°	479	479	479	479	479	



TEST NUMBER: P331828-940

CATALOG NUMBER: S122RDIW-S865D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1312.2	1311.2	1310.1	1309.0	1308.1	1306.4	1304.0	1301.7	1299.4	1297.1	1299.2
5°	1307.5	1306.2	1304.8	1303.5	1302.3	1299.8	1296.5	1293.1	1289.6	1286.2	1288.5
7.5°	1294.0	1292.4	1290.8	1289.1	1287.5	1284.7	1280.7	1276.7	1272.6	1268.6	1269.4
10°	1282.6	1280.8	1279.0	1277.1	1275.2	1271.8	1266.5	1261.2	1256.0	1250.7	1249.9
12.5°	1268.5	1266.1	1263.9	1261.7	1259.4	1254.9	1248.1	1241.4	1234.7	1228.0	1226.5
15°	1243.6	1240.7	1237.8	1234.9	1232.0	1226.1	1217.2	1208.3	1199.3	1190.3	1185.4
17.5°	1213.1	1208.6	1204.3	1199.8	1195.4	1187.5	1176.0	1164.5	1153.1	1141.6	1135.7
20°	1190.3	1185.1	1179.8	1174.6	1169.3	1160.1	1146.9	1133.8	1120.7	1107.5	1100.9
22.5°	1165.7	1159.8	1154.0	1148.1	1142.2	1131.8	1117.0	1102.2	1087.4	1072.5	1064.0
25°	1128.8	1120.4	1112.0	1103.6	1095.2	1082.3	1064.9	1047.6	1030.2	1012.9	1002.1
27.5°	1084.3	1075.1	1066.0	1056.9	1047.8	1033.4	1013.8	994.3	974.6	955.1	942.5
30°	1053.1	1043.1	1033.1	1023.1	1013.2	997.6	976.6	955.6	934.5	913.5	900.1
32.5°	1022.8	1011.1	999.4	987.7	976.1	959.6	938.1	916.6	895.2	873.7	858.4
35°	972.6	959.2	945.8	932.4	919.0	900.7	877.5	854.4	831.3	808.2	791.6
37.5°	922.5	907.8	893.0	878.2	863.5	843.8	819.2	794.5	769.9	745.2	726.9
40°	887.4	871.6	855.9	840.1	824.3	803.7	778.2	752.7	727.2	701.7	683.0
42.5°	851.5	834.8	818.2	801.6	785.0	763.5	737.2	710.8	684.5	658.1	638.8
45°	795.1	777.5	759.9	742.3	724.7	702.0	674.5	646.8	619.2	591.7	572.9
47.5°	740.2	721.6	702.9	684.2	665.6	641.9	613.5	585.0	556.4	528.0	509.4
50°	700.5	681.8	663.2	644.4	625.8	602.0	573.1	544.1	515.2	486.3	468.1
52.5°	661.6	642.1	622.7	603.2	583.6	559.7	531.5	503.1	474.8	446.6	429.0
55°	604.7	584.2	563.7	543.1	522.6	498.1	469.8	441.3	413.0	384.6	368.8
57.5°	546.2	525.1	504.1	483.0	462.1	437.9	410.5	383.3	356.0	328.7	314.2
60°	506.4	485.4	464.4	443.4	422.3	398.2	371.1	344.0	317.0	289.9	276.5
62.5°	467.6	446.6	425.5	404.5	383.4	360.1	334.2	308.4	282.6	256.7	244.0
65°	408.2	386.9	365.6	344.3	323.1	300.5	276.9	253.2	229.5	205.9	197.0
67.5°	351.0	329.8	308.7	287.5	266.4	245.1	223.9	202.6	181.3	160.0	155.9
70°	311.2	290.7	270.2	249.7	229.2	209.8	191.7	173.5	155.4	137.2	134.6
72.5°	273.3	253.7	234.0	214.4	194.7	177.5	163.0	148.4	133.8	119.3	117.1
75°	217.8	199.3	180.9	162.5	144.1	130.5	121.5	112.5	103.6	94.7	92.8
77.5°	163.1	146.9	130.7	114.6	98.4	88.3	83.9	79.6	75.3	71.0	69.9
80°	128.9	115.6	102.2	88.7	75.3	67.3	64.6	62.1	59.4	56.8	55.7
82.5°	97.7	87.3	76.8	66.3	55.9	49.8	48.0	46.2	44.4	42.6	42.0
85°	50.9	45.4	39.9	34.3	28.8	25.7	24.9	24.1	23.3	22.5	22.5
87.5°	15.2	13.7	12.3	10.8	9.4	8.8	9.2	9.6	10.0	10.4	10.2
90°	0.4	1.5	2.6	3.7	4.7	6.2	8.2	10.2	12.1	14.2	14.0
92.5°	7.2	8.0	8.7	9.5	10.3	11.0	11.4	11.9	12.4	12.8	12.8
95°	21.0	21.9	22.8	23.7	24.6	25.1	25.3	25.5	25.7	25.9	25.9
97.5°	38.3	39.1	39.9	40.8	41.6	42.1	42.4	42.8	43.2	43.4	43.4
100°	51.3	52.0	52.7	53.5	54.2	54.7	54.9	55.2	55.5	55.7	55.7
102.5°	64.9	65.5	66.0	66.6	67.1	67.7	67.9	68.3	68.7	69.0	69.1
105°	86.9	87.1	87.4	87.7	87.9	88.2	88.4	88.5	88.7	88.9	89.1
107.5°	109.0	109.4	109.8	110.2	110.6	110.8	110.8	110.8	110.8	110.8	110.8
110°	123.2	123.8	124.3	124.8	125.4	125.6	125.6	125.6	125.6	125.6	125.6



TEST NUMBER: P331828-940

CATALOG NUMBER: S122RDIW-S865D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.8	139.3	139.8	140.4	140.9	141.2	141.1	141.0	140.9	140.8	140.6
115°	161.6	162.1	162.6	163.2	163.7	163.9	163.7	163.5	163.4	163.2	163.1
117.5°	184.4	185.1	185.8	186.5	187.3	187.3	186.9	186.4	185.8	185.4	185.1
120°	199.6	200.3	201.0	201.7	202.4	202.4	201.7	201.0	200.3	199.6	199.6
122.5°	213.5	214.4	215.2	216.1	217.0	217.1	216.6	216.1	215.6	215.1	214.9
125°	235.1	235.9	236.7	237.6	238.4	238.6	238.4	238.1	237.8	237.6	237.3
127.5°	256.2	257.3	258.2	259.3	260.3	260.6	260.4	260.0	259.7	259.4	259.0
130°	269.5	270.6	271.8	273.0	274.1	274.6	274.5	274.3	274.1	273.9	273.8
132.5°	284.4	285.3	286.2	287.2	288.1	288.6	288.6	288.7	288.7	288.7	288.4
135°	304.3	305.2	306.2	307.2	308.2	308.7	308.9	309.1	309.2	309.4	309.3
137.5°	325.1	325.9	326.7	327.5	328.3	328.9	329.1	329.4	329.6	329.8	329.8
140°	337.8	338.6	339.4	340.2	341.0	341.6	342.1	342.5	343.0	343.4	343.4
142.5°	350.7	351.5	352.3	353.1	353.9	354.5	354.7	355.1	355.3	355.7	355.8
145°	369.3	369.9	370.5	371.1	371.8	372.4	372.9	373.4	374.0	374.5	374.6
147.5°	385.8	386.6	387.4	388.1	388.9	389.4	389.8	390.1	390.5	390.8	391.0
150°	397.2	397.7	398.2	398.8	399.3	399.8	400.1	400.5	400.8	401.2	401.4
152.5°	407.2	407.7	408.2	408.8	409.3	409.8	410.2	410.6	411.1	411.5	411.9
155°	422.1	422.4	422.7	423.0	423.3	423.6	423.8	424.1	424.4	424.6	425.1
157.5°	435.1	435.2	435.4	435.6	435.8	435.9	436.0	436.2	436.4	436.6	437.2
160°	442.8	443.0	443.2	443.4	443.5	443.6	443.7	443.8	443.9	444.0	444.5
162.5°	449.9	450.0	450.0	450.0	450.0	450.1	450.2	450.3	450.4	450.5	451.0
165°	459.3	459.2	459.1	459.1	459.0	459.0	459.0	459.0	459.0	459.0	459.6
167.5°	467.3	467.0	466.7	466.5	466.2	466.0	466.0	466.0	466.0	466.0	466.6
170°	471.4	471.2	470.9	470.6	470.4	470.2	470.1	470.0	469.9	469.8	470.5
172.5°	474.4	474.1	473.9	473.6	473.3	473.1	473.1	473.0	472.9	472.8	473.4
175°	478.0	477.7	477.4	477.2	476.9	476.6	476.4	476.3	476.1	475.9	476.5
177.5°	479.4	479.2	478.9	478.8	478.5	478.3	478.2	478.0	477.9	477.8	478.2
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8



TEST NUMBER: P331828-940

CATALOG NUMBER: S122RDIW-S865D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5	1307.5
2.5°	1301.3	1303.4	1305.5	1306.4	1305.9	1305.5	1305.1	1304.7
5°	1290.9	1293.2	1295.7	1296.5	1295.7	1294.9	1294.1	1293.2
7.5°	1270.1	1270.7	1271.4	1271.0	1269.7	1268.4	1266.9	1265.6
10°	1249.1	1248.3	1247.5	1246.3	1244.7	1243.2	1241.6	1240.0
12.5°	1225.1	1223.7	1222.3	1220.3	1217.6	1215.0	1212.4	1209.8
15°	1180.4	1175.4	1170.4	1166.5	1164.0	1161.3	1158.7	1156.0
17.5°	1129.7	1123.7	1117.8	1112.6	1108.0	1103.6	1099.0	1094.5
20°	1094.4	1087.8	1081.2	1075.0	1069.3	1063.5	1057.7	1052.0
22.5°	1055.6	1047.1	1038.7	1032.2	1028.0	1023.6	1019.3	1015.0
25°	991.3	980.5	969.7	962.3	958.4	954.5	950.6	946.6
27.5°	930.0	917.4	904.8	895.5	889.2	882.9	876.6	870.4
30°	886.6	873.3	859.8	849.5	842.5	835.4	828.3	821.2
32.5°	843.1	827.8	812.5	801.5	794.9	788.2	781.5	774.8
35°	775.0	758.5	741.9	730.8	725.0	719.2	713.4	707.6
37.5°	708.7	690.5	672.3	659.8	653.2	646.5	639.9	633.3
40°	664.3	645.7	627.0	614.2	607.4	600.6	593.7	586.9
42.5°	619.6	600.2	580.9	567.9	561.3	554.7	548.0	541.4
45°	554.3	535.7	516.9	504.4	498.1	491.9	485.5	479.2
47.5°	490.8	472.3	453.7	441.6	435.9	430.1	424.4	418.7
50°	450.0	431.9	413.8	401.9	396.4	390.8	385.3	379.8
52.5°	411.5	394.0	376.5	365.2	360.1	355.0	349.9	344.8
55°	353.0	337.2	321.5	311.0	306.0	301.0	296.0	291.1
57.5°	299.8	285.3	270.9	261.5	257.3	253.1	248.9	244.7
60°	263.1	249.7	236.2	227.5	223.2	219.0	214.8	210.6
62.5°	231.2	218.5	205.6	198.0	195.5	193.0	190.4	187.9
65°	188.0	179.1	170.1	165.2	164.4	163.7	162.9	162.1
67.5°	151.8	147.7	143.6	141.1	140.3	139.4	138.6	137.8
70°	132.0	129.4	126.7	124.9	123.9	122.8	121.7	120.6
72.5°	114.9	112.6	110.4	109.1	108.3	107.7	107.1	106.5
75°	91.0	89.2	87.3	86.2	86.0	85.7	85.4	85.2
77.5°	68.9	67.9	66.8	66.1	65.6	65.2	64.8	64.4
80°	54.7	53.7	52.6	52.1	52.1	52.1	52.1	52.1
82.5°	41.4	40.7	40.0	39.8	39.8	39.8	39.8	39.8
85°	22.5	22.5	22.5	22.5	22.5	22.5	22.5	22.5
87.5°	9.9	9.6	9.5	9.3	9.4	9.4	9.4	9.4
90°	13.8	13.6	13.5	13.4	13.5	13.6	13.6	13.7
92.5°	12.9	12.9	13.0	13.0	13.0	13.0	13.1	13.1
95°	25.9	25.9	25.9	25.8	25.6	25.4	25.2	25.1
97.5°	43.4	43.4	43.4	43.4	43.4	43.4	43.4	43.4
100°	55.7	55.7	55.7	55.7	55.6	55.6	55.5	55.4
102.5°	69.1	69.2	69.3	69.3	69.2	69.1	69.0	68.9
105°	89.3	89.4	89.6	89.7	89.7	89.7	89.7	89.7
107.5°	110.9	111.0	111.1	110.9	110.5	110.0	109.7	109.2
110°	125.6	125.6	125.6	125.5	125.2	124.9	124.7	124.4



TEST NUMBER: P331828-940

CATALOG NUMBER: S122RDIW-S865D435U940-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	140.4	140.2	140.0	139.7	139.6	139.4	139.2	139.0
115°	163.0	162.9	162.8	162.6	162.4	162.1	161.8	161.6
117.5°	184.9	184.7	184.5	184.2	184.0	183.7	183.4	183.2
120°	199.6	199.6	199.6	199.5	199.2	198.9	198.7	198.4
122.5°	214.6	214.5	214.2	214.0	213.8	213.7	213.4	213.2
125°	237.0	236.7	236.5	236.3	236.2	236.1	236.0	235.9
127.5°	258.7	258.4	258.1	257.8	257.4	257.2	256.9	256.6
130°	273.6	273.4	273.2	273.0	272.6	272.2	271.9	271.5
132.5°	288.0	287.6	287.2	286.9	286.6	286.2	286.0	285.7
135°	309.2	309.2	309.1	308.9	308.6	308.4	308.1	307.8
137.5°	329.7	329.6	329.6	329.3	329.0	328.6	328.2	327.9
140°	343.4	343.4	343.4	343.2	342.9	342.5	342.1	341.8
142.5°	355.8	355.9	356.0	355.8	355.4	355.1	354.7	354.4
145°	374.7	374.8	374.9	374.7	374.3	374.0	373.6	373.3
147.5°	391.2	391.5	391.6	391.6	391.2	390.8	390.5	390.2
150°	401.7	402.0	402.3	402.3	402.0	401.7	401.4	401.2
152.5°	412.1	412.5	412.9	412.9	412.5	412.1	411.9	411.5
155°	425.5	426.0	426.4	426.5	426.2	426.0	425.7	425.4
157.5°	437.7	438.4	439.0	439.1	438.6	438.2	437.8	437.4
160°	445.1	445.6	446.1	446.2	445.9	445.5	445.1	444.8
162.5°	451.7	452.3	452.9	453.0	452.5	452.1	451.7	451.3
165°	460.2	460.8	461.5	461.5	461.1	460.7	460.2	459.8
167.5°	467.3	467.9	468.5	468.6	468.1	467.6	467.2	466.7
170°	471.1	471.7	472.3	472.4	471.9	471.4	470.8	470.3
172.5°	474.0	474.7	475.3	475.3	474.7	474.2	473.7	473.1
175°	477.2	477.8	478.4	478.5	478.0	477.4	476.9	476.4
177.5°	478.7	479.0	479.5	479.5	479.0	478.7	478.2	477.8
180°	478.8	478.8	478.8	478.8	478.8	478.8	478.8	478.8

(END OF REPORT)