

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332401-930

Luminaire Tested: **S123RDIW-S340D1030U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332401-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1030U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3974.6 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332401-930

CATALOG NUMBER: S123RDIW-S340D1030U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332401-930

CATALOG NUMBER: S123RDIW-S340D1030U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	30	23
2	85	78	72	67	75	69	65	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	24	23	22	17
4	71	60	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19	14
5	65	54	46	40	58	48	42	37	38	33	30	29	25	23	20	18	16	13
6	60	48	40	35	53	43	37	32	34	29	26	26	23	20	18	16	14	11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11	9
9	47	36	28	24	42	32	26	22	26	21	18	20	16	14	14	12	10	8
10	44	33	26	21	39	30	23	19	24	19	16	18	15	13	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5042	5042	5042
5°	5061	4991	5020
10°	5032	4928	4912
15°	4979	4813	4763
20°	4904	4669	4560
25°	4828	4507	4363
30°	4727	4320	4084
35°	4623	4133	3829
40°	4526	3912	3513
45°	4401	3694	3227
50°	4262	3448	2907
55°	4121	3166	2609
60°	3991	2863	2282
65°	3823	2534	1954
70°	3610	2127	1577
75°	3302	1676	1485
80°	2944	1488	1364
85°	2482	1309	1223



TEST NUMBER: P332401-930

CATALOG NUMBER: S123RDIW-S340D1030U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.1
10°-20°	122.4	3.1
20°-30°	176.2	4.4
30°-40°	198.5	5.0
40°-50°	189.9	4.8
50°-60°	155.5	3.9
60°-70°	104.9	2.6
70°-80°	52.8	1.3
80°-90°	17.1	0.4
90°-100°	68.5	1.7
100°-110°	205.0	5.2
110°-120°	348.7	8.8
120°-130°	458.7	11.5
130°-140°	515.5	13.0
140°-150°	506.8	12.8
150°-160°	426.6	10.7
160°-170°	284.0	7.1
170°-180°	99.4	2.5
0°-30°	342.6	8.6
0°-40°	541.1	13.6
0°-60°	886.5	22.3
0°-90°	1061.3	26.7
90°-120°	622.2	15.7
90°-150°	2103.2	52.9
90°-180°	2913.0	73.3
0°-180°	3974.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	465	465	44
15°	447	442	432	430	427	126
25°	406	396	380	372	367	187
35°	352	338	314	299	291	220
45°	289	271	243	222	212	223
55°	220	200	169	147	139	197
65°	150	129	100	82	77	148
75°	79	61	40	37	36	85
85°	20	12	11	10	10	23
90°	1	9	20	23	25	4
95°	49	55	61	64	64	55
105°	186	188	195	195	197	199
115°	351	353	352	353	352	347
125°	514	516	515	511	508	458
135°	667	671	671	667	666	513
145°	809	810	813	812	809	505
155°	926	926	927	930	924	426
165°	1008	1006	1006	1010	1005	284
175°	1049	1046	1046	1050	1045	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P332401-930

CATALOG NUMBER: S123RDIW-S340D1030U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	469.9	469.6	469.4	469.1	468.9	468.3	467.5	466.7	465.9	465.0	465.8
5°	468.4	468.0	467.6	467.2	466.7	466.0	465.0	464.0	462.9	461.9	462.7
7.5°	464.1	463.6	463.2	462.7	462.3	461.4	460.1	458.8	457.4	456.1	456.5
10°	460.4	459.8	459.3	458.7	458.0	457.0	455.5	454.0	452.4	450.9	451.0
12.5°	455.3	454.6	454.0	453.3	452.7	451.3	449.5	447.7	445.8	443.9	443.8
15°	446.8	445.8	444.9	443.9	443.0	441.4	439.0	436.7	434.3	431.9	431.5
17.5°	436.0	435.0	433.9	432.8	431.7	429.7	426.6	423.6	420.7	417.7	416.8
20°	428.1	426.8	425.4	424.1	422.7	420.4	417.3	414.0	410.8	407.6	406.5
22.5°	419.3	417.8	416.2	414.7	413.1	410.7	407.2	403.8	400.4	397.0	395.6
25°	406.5	404.4	402.3	400.1	398.0	395.0	391.2	387.3	383.4	379.5	377.7
27.5°	390.9	388.6	386.2	383.9	381.6	378.3	374.0	369.6	365.3	360.9	358.5
30°	380.3	377.7	375.2	372.7	370.1	366.5	361.7	357.0	352.3	347.6	344.7
32.5°	369.7	366.7	363.9	361.0	358.2	354.2	349.2	344.2	339.2	334.2	331.1
35°	351.8	348.7	345.7	342.7	339.7	335.5	330.3	325.0	319.8	314.5	311.0
37.5°	333.7	330.3	326.9	323.6	320.2	315.7	310.1	304.5	299.0	293.3	289.3
40°	322.1	318.5	314.7	311.0	307.3	302.4	296.4	290.4	284.5	278.4	274.1
42.5°	309.1	305.3	301.7	297.9	294.2	289.3	283.1	276.9	270.7	264.5	259.7
45°	289.1	285.3	281.5	277.7	273.9	268.7	262.3	255.8	249.2	242.7	237.9
47.5°	269.1	265.0	260.7	256.6	252.4	247.1	240.6	234.1	227.6	221.1	215.9
50°	254.5	250.5	246.6	242.6	238.6	233.3	226.4	219.6	212.7	205.9	200.6
52.5°	241.5	237.2	232.8	228.5	224.2	218.7	211.9	205.1	198.4	191.6	186.2
55°	219.6	215.4	211.3	207.2	203.0	197.4	190.2	183.0	175.9	168.7	163.8
57.5°	199.3	194.9	190.4	185.8	181.3	175.5	168.3	161.0	153.8	146.7	142.0
60°	185.4	180.8	176.1	171.5	166.8	161.0	154.0	147.0	140.0	133.0	128.4
62.5°	171.4	166.7	162.1	157.5	152.9	147.0	140.0	133.0	126.0	119.0	114.7
65°	150.1	145.4	140.8	136.2	131.5	125.9	119.3	112.7	106.2	99.5	95.4
67.5°	128.7	124.0	119.3	114.6	109.9	104.4	98.1	91.8	85.4	79.2	76.1
70°	114.7	110.1	105.6	101.0	96.5	91.2	85.4	79.4	73.5	67.6	64.7
72.5°	100.8	96.3	91.8	87.2	82.8	77.9	72.5	67.1	61.7	56.3	54.0
75°	79.4	75.3	71.3	67.3	63.2	58.9	54.2	49.6	44.9	40.3	39.5
77.5°	59.9	56.3	52.6	48.9	45.3	42.0	39.0	36.0	33.0	30.0	29.6
80°	47.5	44.0	40.6	37.1	33.7	31.1	29.3	27.5	25.7	24.0	23.6
82.5°	35.6	32.6	29.7	26.7	23.6	21.8	21.0	20.1	19.3	18.4	18.2
85°	20.1	18.3	16.4	14.6	12.7	11.7	11.4	11.2	10.9	10.6	10.4
87.5°	7.4	7.1	6.7	6.4	6.0	6.0	6.5	6.9	7.4	7.9	8.0
90°	0.8	2.7	4.5	6.4	8.2	10.3	12.6	15.1	17.4	19.8	20.5
92.5°	20.0	21.2	22.5	23.7	24.9	26.3	27.6	29.0	30.3	31.7	32.3
95°	48.8	50.0	51.3	52.6	53.9	55.3	56.7	58.2	59.7	61.1	61.9
97.5°	86.6	87.5	88.5	89.4	90.4	91.4	92.5	93.5	94.6	95.6	96.5
100°	112.3	113.4	114.5	115.6	116.8	117.7	118.7	119.6	120.5	121.4	122.0
102.5°	142.1	142.8	143.4	144.1	144.7	145.6	146.8	148.1	149.3	150.5	151.1
105°	185.9	186.2	186.6	186.9	187.4	188.3	190.0	191.6	193.3	194.9	194.9
107.5°	236.8	236.9	237.2	237.4	237.6	238.1	238.7	239.4	240.0	240.7	241.2
110°	268.5	268.8	269.2	269.5	269.9	270.3	270.7	271.0	271.4	271.7	272.5



TEST NUMBER: P332401-930

CATALOG NUMBER: S123RDIW-S340D1030U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	301.5	301.7	301.9	302.1	302.4	302.5	302.6	302.6	302.7	302.8	303.7
115°	351.1	351.6	352.1	352.7	353.3	353.4	352.9	352.6	352.2	351.9	352.0
117.5°	401.0	401.3	401.7	402.0	402.4	402.4	401.9	401.4	400.9	400.5	400.4
120°	432.0	433.1	434.2	435.3	436.4	436.5	435.5	434.6	433.7	432.8	432.6
122.5°	464.4	465.2	466.0	466.8	467.6	467.7	467.3	466.8	466.4	465.9	465.4
125°	513.8	514.3	514.9	515.4	516.0	516.1	515.7	515.4	514.9	514.6	513.9
127.5°	559.4	560.5	561.7	562.9	564.0	564.4	564.0	563.6	563.2	562.8	561.8
130°	589.8	591.3	592.7	594.2	595.7	596.1	595.6	595.0	594.4	593.9	593.1
132.5°	620.1	621.6	623.1	624.6	626.1	626.6	626.1	625.7	625.3	624.9	624.0
135°	666.6	667.6	668.8	669.8	671.0	671.4	671.2	671.1	670.9	670.7	669.9
137.5°	709.6	710.5	711.3	712.2	713.2	713.9	714.4	714.9	715.3	715.8	715.0
140°	739.2	740.2	741.1	742.0	742.9	743.5	743.6	743.9	744.0	744.2	744.0
142.5°	766.4	767.3	768.2	769.1	770.1	770.6	770.9	771.3	771.7	772.0	771.8
145°	808.6	809.0	809.3	809.8	810.1	810.6	811.1	811.7	812.2	812.8	812.6
147.5°	845.6	846.3	846.9	847.7	848.3	848.9	849.4	849.9	850.4	850.9	850.9
150°	871.4	871.8	872.1	872.5	872.9	873.3	873.6	874.0	874.3	874.7	874.7
152.5°	892.6	893.1	893.6	894.1	894.6	895.0	895.2	895.4	895.7	895.9	896.2
155°	925.9	925.9	925.9	925.9	925.9	926.0	926.2	926.4	926.6	926.8	927.5
157.5°	954.4	954.1	953.9	953.7	953.5	953.4	953.6	953.7	953.9	954.0	954.8
160°	972.2	971.8	971.4	971.1	970.7	970.5	970.5	970.5	970.5	970.5	971.4
162.5°	988.1	987.6	987.0	986.5	986.0	985.8	985.9	986.1	986.3	986.4	987.3
165°	1008.5	1008.0	1007.5	1006.9	1006.3	1006.1	1006.1	1006.1	1006.1	1006.1	1007.1
167.5°	1024.9	1024.2	1023.4	1022.7	1022.0	1021.7	1021.8	1022.0	1022.1	1022.2	1023.4
170°	1034.1	1033.4	1032.7	1031.9	1031.2	1030.9	1030.9	1030.9	1030.9	1030.9	1032.1
172.5°	1041.4	1040.6	1039.9	1039.2	1038.4	1038.1	1038.1	1038.1	1038.1	1038.1	1039.3
175°	1049.0	1048.3	1047.6	1046.8	1046.1	1045.7	1045.7	1045.7	1045.7	1045.7	1046.8
177.5°	1052.1	1051.6	1051.0	1050.4	1049.8	1049.5	1049.5	1049.5	1049.5	1049.5	1050.4
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5



TEST NUMBER: P332401-930

CATALOG NUMBER: S123RDIW-S340D1030U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.5	467.2	468.1	468.3	468.2	468.1	467.9	467.8
5°	463.5	464.2	465.0	465.3	465.1	465.0	464.8	464.6
7.5°	457.0	457.4	457.8	457.9	457.5	457.3	457.0	456.7
10°	451.1	451.2	451.3	451.1	450.7	450.3	449.8	449.4
12.5°	443.8	443.8	443.8	443.4	443.0	442.5	442.0	441.5
15°	431.0	430.6	430.2	429.7	429.2	428.5	428.0	427.4
17.5°	415.9	415.0	414.1	413.2	412.3	411.4	410.6	409.7
20°	405.4	404.3	403.2	402.2	401.1	400.1	399.2	398.1
22.5°	394.3	392.9	391.5	390.4	389.4	388.5	387.5	386.6
25°	375.9	374.2	372.4	371.0	370.1	369.2	368.3	367.4
27.5°	356.0	353.6	351.1	349.2	347.7	346.3	345.0	343.5
30°	341.9	339.0	336.1	334.0	332.6	331.3	330.0	328.6
32.5°	327.9	324.8	321.6	319.4	318.0	316.6	315.1	313.7
35°	307.3	303.6	300.0	297.4	296.0	294.4	292.9	291.4
37.5°	285.1	281.0	276.9	273.9	272.0	270.1	268.2	266.4
40°	269.7	265.3	260.9	257.7	255.8	253.9	251.9	250.0
42.5°	254.9	250.1	245.3	242.1	240.3	238.6	236.8	235.1
45°	233.1	228.3	223.5	220.0	218.1	216.1	214.0	212.0
47.5°	210.6	205.4	200.2	196.7	194.9	193.1	191.2	189.4
50°	195.4	190.2	185.0	181.4	179.4	177.5	175.5	173.6
52.5°	180.8	175.3	169.9	166.3	164.5	162.8	161.1	159.3
55°	158.9	154.0	149.1	145.8	144.1	142.4	140.7	139.0
57.5°	137.4	132.7	128.2	125.1	123.7	122.2	120.8	119.4
60°	123.8	119.3	114.7	111.7	110.3	108.8	107.5	106.0
62.5°	110.4	106.2	101.8	98.9	97.4	96.0	94.4	92.9
65°	91.2	87.2	83.0	80.5	79.5	78.6	77.7	76.7
67.5°	73.0	69.9	66.8	64.7	63.8	62.8	61.8	60.8
70°	61.7	58.8	55.8	53.9	52.9	52.0	51.0	50.1
72.5°	51.5	49.2	46.7	45.3	44.9	44.5	44.2	43.8
75°	38.6	37.7	36.9	36.4	36.2	36.0	35.9	35.7
77.5°	29.1	28.6	28.2	27.9	27.7	27.6	27.4	27.2
80°	23.4	23.2	22.9	22.7	22.5	22.3	22.2	22.0
82.5°	17.9	17.7	17.4	17.3	17.3	17.2	17.2	17.2
85°	10.3	10.1	9.9	9.9	9.9	9.9	9.9	9.9
87.5°	8.1	8.2	8.2	8.3	8.3	8.3	8.3	8.3
90°	21.3	22.0	22.7	23.3	23.6	24.1	24.4	24.8
92.5°	32.9	33.5	34.1	34.2	34.0	33.8	33.6	33.3
95°	62.6	63.3	64.1	64.4	64.4	64.4	64.4	64.4
97.5°	97.3	98.2	99.1	99.4	99.3	99.3	99.2	99.1
100°	122.5	123.1	123.6	124.1	124.4	124.8	125.1	125.6
102.5°	151.6	152.1	152.7	153.0	152.9	152.8	152.7	152.6
105°	194.9	194.9	194.9	195.1	195.5	195.8	196.2	196.6
107.5°	241.9	242.5	243.0	243.2	243.0	242.8	242.6	242.3
110°	273.2	273.9	274.7	274.8	274.5	274.1	273.8	273.4



TEST NUMBER: P332401-930

CATALOG NUMBER: S123RDIW-S340D1030U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	304.6	305.4	306.3	306.7	306.6	306.6	306.6	306.5
115°	352.2	352.5	352.6	352.6	352.5	352.2	352.0	351.9
117.5°	400.4	400.3	400.3	400.0	399.5	399.0	398.4	397.9
120°	432.4	432.3	432.1	431.8	431.5	431.0	430.7	430.3
122.5°	464.9	464.4	464.0	463.4	462.9	462.4	461.9	461.4
125°	513.1	512.4	511.7	510.9	510.2	509.5	508.7	508.0
127.5°	560.8	559.8	558.7	557.7	556.9	556.1	555.2	554.4
130°	592.4	591.7	590.9	590.0	588.6	587.3	586.1	584.8
132.5°	623.2	622.3	621.4	620.5	619.5	618.5	617.5	616.5
135°	669.2	668.5	667.7	667.2	666.8	666.5	666.1	665.8
137.5°	714.3	713.5	712.7	712.0	711.3	710.6	709.9	709.2
140°	743.9	743.6	743.5	742.7	741.4	740.2	738.9	737.6
142.5°	771.6	771.4	771.3	770.6	769.6	768.7	767.7	766.7
145°	812.4	812.2	812.0	811.5	810.8	810.1	809.3	808.6
147.5°	850.9	850.9	850.9	850.4	849.3	848.2	847.1	846.0
150°	874.7	874.7	874.7	874.2	873.1	872.0	870.9	869.8
152.5°	896.4	896.7	897.1	896.7	895.8	894.8	893.8	892.9
155°	928.2	929.0	929.7	929.4	928.1	926.8	925.6	924.3
157.5°	955.5	956.3	957.1	957.0	955.9	955.0	953.9	952.8
160°	972.4	973.3	974.2	974.3	973.5	972.8	972.1	971.3
162.5°	988.2	989.1	990.1	989.9	988.8	987.6	986.4	985.2
165°	1008.3	1009.3	1010.5	1010.4	1009.1	1007.8	1006.5	1005.3
167.5°	1024.5	1025.6	1026.8	1026.8	1025.6	1024.5	1023.4	1022.2
170°	1033.4	1034.7	1036.0	1036.0	1034.7	1033.4	1032.1	1030.9
172.5°	1040.4	1041.5	1042.7	1042.6	1041.3	1040.0	1038.7	1037.5
175°	1047.9	1049.0	1050.1	1050.0	1048.7	1047.4	1046.2	1044.9
177.5°	1051.2	1052.1	1053.0	1053.0	1051.9	1050.9	1049.9	1048.9
180°	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5	1051.5

(END OF REPORT)