

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332405-930

Luminaire Tested: **S123RDIW-S340D1320U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332405-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1320U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4791.7 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332405-930

CATALOG NUMBER: S123RDIW-S340D1320U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332405-930

CATALOG NUMBER: S123RDIW-S340D1320U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	48	48	48	31	31	31	22
1	92	88	84	81	81	78	75	72	59	58	56	43	41	40	27	27	26	19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	16
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	21	20	19	14
4	70	60	52	46	62	53	47	42	41	37	33	30	27	25	19	18	16	12
5	64	53	45	40	56	47	41	36	37	32	29	27	24	21	17	16	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	13	11	8
8	50	38	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	23	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5042	5042	5042
5°	5061	4991	5020
10°	5032	4928	4912
15°	4979	4813	4763
20°	4904	4669	4560
25°	4828	4507	4363
30°	4727	4320	4084
35°	4623	4133	3829
40°	4526	3912	3513
45°	4401	3694	3227
50°	4262	3448	2907
55°	4121	3166	2609
60°	3991	2863	2282
65°	3823	2534	1954
70°	3610	2127	1577
75°	3302	1676	1485
80°	2944	1488	1364
85°	2482	1309	1223



TEST NUMBER: P332405-930

CATALOG NUMBER: S123RDIW-S340D1320U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	0.9
10°-20°	122.4	2.6
20°-30°	176.2	3.7
30°-40°	198.5	4.1
40°-50°	189.9	4.0
50°-60°	155.5	3.2
60°-70°	104.9	2.2
70°-80°	52.8	1.1
80°-90°	17.9	0.4
90°-100°	87.7	1.8
100°-110°	262.5	5.5
110°-120°	446.4	9.3
120°-130°	587.2	12.3
130°-140°	660.0	13.8
140°-150°	648.8	13.5
150°-160°	546.2	11.4
160°-170°	363.6	7.6
170°-180°	127.3	2.7
0°-30°	342.6	7.1
0°-40°	541.1	11.3
0°-60°	886.5	18.5
0°-90°	1062.1	22.2
90°-120°	796.6	16.6
90°-150°	2692.5	56.2
90°-180°	3730.0	77.8
0°-180°	4791.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	465	465	44
15°	447	442	432	430	427	126
25°	406	396	380	372	367	187
35°	352	338	314	299	291	220
45°	289	271	243	222	212	223
55°	220	200	169	147	139	197
65°	150	129	100	82	77	148
75°	79	61	40	37	36	85
85°	20	12	11	10	10	23
90°	1	12	25	29	32	5
95°	62	70	78	82	82	70
105°	238	240	250	250	252	255
115°	449	452	450	451	450	444
125°	658	661	659	655	650	586
135°	853	859	859	854	852	657
145°	1035	1037	1040	1039	1035	646
155°	1185	1185	1186	1190	1183	545
165°	1291	1288	1288	1294	1287	364
175°	1343	1339	1339	1344	1338	128
180°	1346	1346	1346	1346	1346	



TEST NUMBER: P332405-930

CATALOG NUMBER: S123RDIW-S340D1320U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	469.9	469.6	469.4	469.1	468.9	468.3	467.5	466.7	465.9	465.0	465.8
5°	468.4	468.0	467.6	467.2	466.7	466.0	465.0	464.0	462.9	461.9	462.7
7.5°	464.1	463.6	463.2	462.7	462.3	461.4	460.1	458.8	457.4	456.1	456.5
10°	460.4	459.8	459.3	458.7	458.0	457.0	455.5	454.0	452.4	450.9	451.0
12.5°	455.3	454.6	454.0	453.3	452.7	451.3	449.5	447.7	445.8	443.9	443.8
15°	446.8	445.8	444.9	443.9	443.0	441.4	439.0	436.7	434.3	431.9	431.5
17.5°	436.0	435.0	433.9	432.8	431.7	429.7	426.6	423.6	420.7	417.7	416.8
20°	428.1	426.8	425.4	424.1	422.7	420.4	417.3	414.0	410.8	407.6	406.5
22.5°	419.3	417.8	416.2	414.7	413.1	410.7	407.2	403.8	400.4	397.0	395.6
25°	406.5	404.4	402.3	400.1	398.0	395.0	391.2	387.3	383.4	379.5	377.7
27.5°	390.9	388.6	386.2	383.9	381.6	378.3	374.0	369.6	365.3	360.9	358.5
30°	380.3	377.7	375.2	372.7	370.1	366.5	361.7	357.0	352.3	347.6	344.7
32.5°	369.7	366.7	363.9	361.0	358.2	354.2	349.2	344.2	339.2	334.2	331.1
35°	351.8	348.7	345.7	342.7	339.7	335.5	330.3	325.0	319.8	314.5	311.0
37.5°	333.7	330.3	326.9	323.6	320.2	315.7	310.1	304.5	299.0	293.3	289.3
40°	322.1	318.5	314.7	311.0	307.3	302.4	296.4	290.4	284.5	278.4	274.1
42.5°	309.1	305.3	301.7	297.9	294.2	289.3	283.1	276.9	270.7	264.5	259.7
45°	289.1	285.3	281.5	277.7	273.9	268.7	262.3	255.8	249.2	242.7	237.9
47.5°	269.1	265.0	260.7	256.6	252.4	247.1	240.6	234.1	227.6	221.1	215.9
50°	254.5	250.5	246.6	242.6	238.6	233.3	226.4	219.6	212.7	205.9	200.6
52.5°	241.5	237.2	232.8	228.5	224.2	218.7	211.9	205.1	198.4	191.6	186.2
55°	219.6	215.4	211.3	207.2	203.0	197.4	190.2	183.0	175.9	168.7	163.8
57.5°	199.3	194.9	190.4	185.8	181.3	175.5	168.3	161.0	153.8	146.7	142.0
60°	185.4	180.8	176.1	171.5	166.8	161.0	154.0	147.0	140.0	133.0	128.4
62.5°	171.4	166.7	162.1	157.5	152.9	147.0	140.0	133.0	126.0	119.0	114.7
65°	150.1	145.4	140.8	136.2	131.5	125.9	119.3	112.7	106.2	99.5	95.4
67.5°	128.7	124.0	119.3	114.6	109.9	104.4	98.1	91.8	85.4	79.2	76.1
70°	114.7	110.1	105.6	101.0	96.5	91.2	85.4	79.4	73.5	67.6	64.7
72.5°	100.8	96.3	91.8	87.2	82.8	77.9	72.5	67.1	61.7	56.3	54.0
75°	79.4	75.3	71.3	67.3	63.2	58.9	54.2	49.6	44.9	40.3	39.5
77.5°	59.9	56.3	52.6	48.9	45.3	42.0	39.0	36.0	33.0	30.0	29.6
80°	47.5	44.0	40.6	37.1	33.7	31.1	29.3	27.5	25.7	24.0	23.6
82.5°	35.6	32.6	29.7	26.7	23.6	21.8	21.0	20.1	19.3	18.4	18.2
85°	20.1	18.3	16.4	14.6	12.7	11.7	11.4	11.2	10.9	10.6	10.4
87.5°	7.5	7.3	6.9	6.7	6.4	6.6	7.2	7.8	8.4	9.0	9.1
90°	1.1	3.4	5.8	8.1	10.4	13.1	16.2	19.2	22.3	25.4	26.3
92.5°	25.6	27.1	28.8	30.4	32.0	33.7	35.4	37.1	38.9	40.6	41.3
95°	62.4	64.0	65.7	67.3	69.0	70.8	72.6	74.5	76.4	78.3	79.2
97.5°	110.8	112.0	113.2	114.5	115.7	117.0	118.4	119.7	121.1	122.5	123.5
100°	143.8	145.2	146.6	148.1	149.4	150.7	151.9	153.1	154.3	155.5	156.1
102.5°	181.9	182.7	183.6	184.4	185.2	186.5	188.0	189.6	191.1	192.7	193.4
105°	237.9	238.4	238.9	239.3	239.8	241.1	243.2	245.3	247.4	249.6	249.6
107.5°	303.0	303.4	303.6	303.9	304.2	304.8	305.6	306.5	307.3	308.1	308.9
110°	343.6	344.1	344.6	345.0	345.5	346.0	346.5	347.0	347.4	347.9	348.9



TEST NUMBER: P332405-930

CATALOG NUMBER: S123RDIW-S340D1320U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	386.0	386.2	386.5	386.8	387.1	387.3	387.3	387.4	387.6	387.7	388.8
115°	449.4	450.1	450.8	451.5	452.2	452.3	451.8	451.4	450.9	450.5	450.7
117.5°	513.3	513.7	514.2	514.7	515.2	515.1	514.5	513.9	513.2	512.7	512.6
120°	553.0	554.4	555.9	557.3	558.6	558.8	557.6	556.4	555.3	554.1	553.8
122.5°	594.5	595.5	596.6	597.6	598.6	598.8	598.2	597.6	597.0	596.4	595.7
125°	657.7	658.4	659.1	659.8	660.6	660.6	660.1	659.7	659.3	658.8	657.9
127.5°	716.1	717.6	719.1	720.6	722.1	722.6	722.1	721.5	721.1	720.6	719.2
130°	755.0	756.8	758.8	760.7	762.5	763.1	762.4	761.7	761.0	760.3	759.4
132.5°	793.9	795.8	797.7	799.6	801.4	802.1	801.6	801.1	800.5	800.1	798.9
135°	853.4	854.8	856.1	857.5	859.0	859.6	859.3	859.1	858.8	858.6	857.7
137.5°	908.3	909.5	910.7	911.8	913.1	914.0	914.5	915.2	915.7	916.4	915.3
140°	946.4	947.5	948.8	949.9	951.1	951.8	952.0	952.3	952.5	952.8	952.5
142.5°	981.0	982.3	983.4	984.6	985.8	986.6	987.0	987.4	987.8	988.3	988.1
145°	1035.2	1035.7	1036.2	1036.7	1037.1	1037.7	1038.4	1039.1	1039.8	1040.5	1040.2
147.5°	1082.6	1083.5	1084.3	1085.2	1086.0	1086.7	1087.4	1088.0	1088.7	1089.3	1089.3
150°	1115.6	1116.1	1116.6	1117.0	1117.4	1117.9	1118.4	1118.8	1119.3	1119.8	1119.8
152.5°	1142.6	1143.3	1143.9	1144.6	1145.3	1145.7	1146.1	1146.3	1146.6	1146.9	1147.3
155°	1185.4	1185.4	1185.4	1185.4	1185.4	1185.5	1185.7	1185.9	1186.2	1186.4	1187.4
157.5°	1221.7	1221.5	1221.2	1220.9	1220.6	1220.6	1220.7	1220.9	1221.2	1221.3	1222.3
160°	1244.6	1244.1	1243.7	1243.2	1242.7	1242.4	1242.4	1242.4	1242.4	1242.4	1243.7
162.5°	1264.9	1264.2	1263.6	1262.9	1262.2	1262.0	1262.2	1262.4	1262.6	1262.7	1264.0
165°	1291.1	1290.4	1289.7	1289.0	1288.3	1287.9	1287.9	1287.9	1287.9	1287.9	1289.3
167.5°	1312.1	1311.1	1310.2	1309.2	1308.3	1307.9	1308.1	1308.3	1308.5	1308.6	1310.1
170°	1323.9	1323.0	1322.0	1321.1	1320.1	1319.6	1319.6	1319.6	1319.6	1319.6	1321.3
172.5°	1333.2	1332.3	1331.3	1330.4	1329.4	1328.9	1328.9	1328.9	1328.9	1328.9	1330.4
175°	1343.0	1342.0	1341.1	1340.1	1339.1	1338.7	1338.7	1338.7	1338.7	1338.7	1340.1
177.5°	1347.0	1346.2	1345.4	1344.7	1343.9	1343.5	1343.5	1343.5	1343.5	1343.5	1344.7
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1



TEST NUMBER: P332405-930

CATALOG NUMBER: S123RDIW-S340D1320U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.5	467.2	468.1	468.3	468.2	468.1	467.9	467.8
5°	463.5	464.2	465.0	465.3	465.1	465.0	464.8	464.6
7.5°	457.0	457.4	457.8	457.9	457.5	457.3	457.0	456.7
10°	451.1	451.2	451.3	451.1	450.7	450.3	449.8	449.4
12.5°	443.8	443.8	443.8	443.4	443.0	442.5	442.0	441.5
15°	431.0	430.6	430.2	429.7	429.2	428.5	428.0	427.4
17.5°	415.9	415.0	414.1	413.2	412.3	411.4	410.6	409.7
20°	405.4	404.3	403.2	402.2	401.1	400.1	399.2	398.1
22.5°	394.3	392.9	391.5	390.4	389.4	388.5	387.5	386.6
25°	375.9	374.2	372.4	371.0	370.1	369.2	368.3	367.4
27.5°	356.0	353.6	351.1	349.2	347.7	346.3	345.0	343.5
30°	341.9	339.0	336.1	334.0	332.6	331.3	330.0	328.6
32.5°	327.9	324.8	321.6	319.4	318.0	316.6	315.1	313.7
35°	307.3	303.6	300.0	297.4	296.0	294.4	292.9	291.4
37.5°	285.1	281.0	276.9	273.9	272.0	270.1	268.2	266.4
40°	269.7	265.3	260.9	257.7	255.8	253.9	251.9	250.0
42.5°	254.9	250.1	245.3	242.1	240.3	238.6	236.8	235.1
45°	233.1	228.3	223.5	220.0	218.1	216.1	214.0	212.0
47.5°	210.6	205.4	200.2	196.7	194.9	193.1	191.2	189.4
50°	195.4	190.2	185.0	181.4	179.4	177.5	175.5	173.6
52.5°	180.8	175.3	169.9	166.3	164.5	162.8	161.1	159.3
55°	158.9	154.0	149.1	145.8	144.1	142.4	140.7	139.0
57.5°	137.4	132.7	128.2	125.1	123.7	122.2	120.8	119.4
60°	123.8	119.3	114.7	111.7	110.3	108.8	107.5	106.0
62.5°	110.4	106.2	101.8	98.9	97.4	96.0	94.4	92.9
65°	91.2	87.2	83.0	80.5	79.5	78.6	77.7	76.7
67.5°	73.0	69.9	66.8	64.7	63.8	62.8	61.8	60.8
70°	61.7	58.8	55.8	53.9	52.9	52.0	51.0	50.1
72.5°	51.5	49.2	46.7	45.3	44.9	44.5	44.2	43.8
75°	38.6	37.7	36.9	36.4	36.2	36.0	35.9	35.7
77.5°	29.1	28.6	28.2	27.9	27.7	27.6	27.4	27.2
80°	23.4	23.2	22.9	22.7	22.5	22.3	22.2	22.0
82.5°	17.9	17.7	17.4	17.3	17.3	17.2	17.2	17.2
85°	10.3	10.1	9.9	9.9	9.9	9.9	9.9	9.9
87.5°	9.3	9.4	9.5	9.6	9.6	9.6	9.6	9.7
90°	27.2	28.2	29.1	29.8	30.3	30.8	31.2	31.7
92.5°	42.1	42.9	43.6	43.9	43.5	43.3	43.0	42.7
95°	80.1	81.0	82.0	82.5	82.5	82.5	82.5	82.5
97.5°	124.6	125.7	126.8	127.3	127.2	127.1	127.0	126.9
100°	156.9	157.5	158.2	158.8	159.3	159.8	160.3	160.7
102.5°	194.0	194.8	195.5	195.8	195.7	195.6	195.5	195.4
105°	249.6	249.6	249.6	249.8	250.3	250.7	251.2	251.7
107.5°	309.7	310.4	311.1	311.4	311.1	310.8	310.5	310.2
110°	349.8	350.7	351.6	351.9	351.4	351.0	350.5	350.0



TEST NUMBER: P332405-930

CATALOG NUMBER: S123RDIW-S340D1320U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	389.9	391.0	392.2	392.6	392.6	392.5	392.4	392.3
115°	450.9	451.2	451.4	451.4	451.2	450.9	450.7	450.5
117.5°	512.6	512.5	512.4	512.1	511.4	510.8	510.1	509.5
120°	553.6	553.4	553.2	552.8	552.4	551.9	551.4	550.9
122.5°	595.2	594.5	593.9	593.3	592.6	592.0	591.3	590.7
125°	656.9	656.0	655.0	654.1	653.1	652.2	651.3	650.3
127.5°	717.9	716.6	715.3	714.0	713.0	711.9	710.9	709.7
130°	758.4	757.5	756.5	755.2	753.6	752.0	750.3	748.7
132.5°	797.8	796.6	795.6	794.3	793.0	791.8	790.5	789.3
135°	856.7	855.8	854.8	854.2	853.7	853.2	852.7	852.3
137.5°	914.4	913.4	912.4	911.5	910.6	909.7	908.8	907.9
140°	952.3	952.0	951.8	950.9	949.3	947.5	945.9	944.3
142.5°	987.8	987.6	987.3	986.6	985.3	984.1	982.8	981.5
145°	1040.0	1039.8	1039.6	1039.0	1038.0	1037.1	1036.2	1035.2
147.5°	1089.3	1089.3	1089.3	1088.7	1087.3	1085.8	1084.4	1083.0
150°	1119.8	1119.8	1119.8	1119.1	1117.7	1116.3	1114.8	1113.5
152.5°	1147.6	1148.0	1148.3	1147.9	1146.7	1145.5	1144.3	1143.0
155°	1188.3	1189.3	1190.2	1189.8	1188.2	1186.6	1184.9	1183.2
157.5°	1223.3	1224.3	1225.3	1225.1	1223.8	1222.5	1221.2	1219.9
160°	1244.8	1246.0	1247.2	1247.3	1246.3	1245.5	1244.5	1243.5
162.5°	1265.1	1266.3	1267.5	1267.3	1265.8	1264.3	1262.8	1261.3
165°	1290.8	1292.2	1293.6	1293.5	1291.8	1290.2	1288.5	1286.9
167.5°	1311.6	1313.0	1314.5	1314.5	1313.0	1311.6	1310.1	1308.6
170°	1323.0	1324.6	1326.2	1326.2	1324.6	1323.0	1321.3	1319.6
172.5°	1331.9	1333.3	1334.8	1334.7	1333.1	1331.4	1329.8	1328.1
175°	1341.5	1343.0	1344.3	1344.2	1342.6	1340.9	1339.3	1337.7
177.5°	1345.8	1347.0	1348.1	1348.0	1346.6	1345.3	1344.0	1342.7
180°	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1	1346.1

(END OF REPORT)