

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332393-930

Luminaire Tested: **S123RDIW-S340D460U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332393-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D460U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2362.7 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332393-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332393-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38
2	88	81	75	70	81	75	70	65	62	59	56	51	49	46	41	39	37	33
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	29	27	24	21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5042	5042	5042
5°	5061	4991	5020
10°	5032	4928	4912
15°	4979	4813	4763
20°	4904	4669	4560
25°	4828	4507	4363
30°	4727	4320	4084
35°	4623	4133	3829
40°	4526	3912	3513
45°	4401	3694	3227
50°	4262	3448	2907
55°	4121	3166	2609
60°	3991	2863	2282
65°	3823	2534	1954
70°	3610	2127	1577
75°	3302	1676	1485
80°	2944	1488	1364
85°	2482	1309	1223



TEST NUMBER: P332393-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.9
10°-20°	122.4	5.2
20°-30°	176.2	7.5
30°-40°	198.5	8.4
40°-50°	189.9	8.0
50°-60°	155.5	6.6
60°-70°	104.9	4.4
70°-80°	52.8	2.2
80°-90°	15.4	0.6
90°-100°	30.6	1.3
100°-110°	91.7	3.9
110°-120°	156.0	6.6
120°-130°	205.2	8.7
130°-140°	230.6	9.8
140°-150°	226.7	9.6
150°-160°	190.8	8.1
160°-170°	127.0	5.4
170°-180°	44.5	1.9
0°-30°	342.6	14.5
0°-40°	541.1	22.9
0°-60°	886.5	37.5
0°-90°	1059.6	44.8
90°-120°	278.3	11.8
90°-150°	940.8	39.8
90°-180°	1303.0	55.1
0°-180°	2362.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	465	465	44
15°	447	442	432	430	427	126
25°	406	396	380	372	367	187
35°	352	338	314	299	291	220
45°	289	271	243	222	212	223
55°	220	200	169	147	139	197
65°	150	129	100	82	77	148
75°	79	61	40	37	36	85
85°	20	12	11	10	10	23
90°	0	4	9	10	11	2
95°	22	24	27	29	29	24
105°	83	84	87	87	88	89
115°	157	158	157	158	157	155
125°	230	231	230	229	227	205
135°	298	300	300	299	298	230
145°	362	362	364	363	362	226
155°	414	414	415	416	413	191
165°	451	450	450	452	450	127
175°	469	468	468	470	467	45
180°	470	470	470	470	470	



TEST NUMBER: P332393-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	469.9	469.6	469.4	469.1	468.9	468.3	467.5	466.7	465.9	465.0	465.8
5°	468.4	468.0	467.6	467.2	466.7	466.0	465.0	464.0	462.9	461.9	462.7
7.5°	464.1	463.6	463.2	462.7	462.3	461.4	460.1	458.8	457.4	456.1	456.5
10°	460.4	459.8	459.3	458.7	458.0	457.0	455.5	454.0	452.4	450.9	451.0
12.5°	455.3	454.6	454.0	453.3	452.7	451.3	449.5	447.7	445.8	443.9	443.8
15°	446.8	445.8	444.9	443.9	443.0	441.4	439.0	436.7	434.3	431.9	431.5
17.5°	436.0	435.0	433.9	432.8	431.7	429.7	426.6	423.6	420.7	417.7	416.8
20°	428.1	426.8	425.4	424.1	422.7	420.4	417.3	414.0	410.8	407.6	406.5
22.5°	419.3	417.8	416.2	414.7	413.1	410.7	407.2	403.8	400.4	397.0	395.6
25°	406.5	404.4	402.3	400.1	398.0	395.0	391.2	387.3	383.4	379.5	377.7
27.5°	390.9	388.6	386.2	383.9	381.6	378.3	374.0	369.6	365.3	360.9	358.5
30°	380.3	377.7	375.2	372.7	370.1	366.5	361.7	357.0	352.3	347.6	344.7
32.5°	369.7	366.7	363.9	361.0	358.2	354.2	349.2	344.2	339.2	334.2	331.1
35°	351.8	348.7	345.7	342.7	339.7	335.5	330.3	325.0	319.8	314.5	311.0
37.5°	333.7	330.3	326.9	323.6	320.2	315.7	310.1	304.5	299.0	293.3	289.3
40°	322.1	318.5	314.7	311.0	307.3	302.4	296.4	290.4	284.5	278.4	274.1
42.5°	309.1	305.3	301.7	297.9	294.2	289.3	283.1	276.9	270.7	264.5	259.7
45°	289.1	285.3	281.5	277.7	273.9	268.7	262.3	255.8	249.2	242.7	237.9
47.5°	269.1	265.0	260.7	256.6	252.4	247.1	240.6	234.1	227.6	221.1	215.9
50°	254.5	250.5	246.6	242.6	238.6	233.3	226.4	219.6	212.7	205.9	200.6
52.5°	241.5	237.2	232.8	228.5	224.2	218.7	211.9	205.1	198.4	191.6	186.2
55°	219.6	215.4	211.3	207.2	203.0	197.4	190.2	183.0	175.9	168.7	163.8
57.5°	199.3	194.9	190.4	185.8	181.3	175.5	168.3	161.0	153.8	146.7	142.0
60°	185.4	180.8	176.1	171.5	166.8	161.0	154.0	147.0	140.0	133.0	128.4
62.5°	171.4	166.7	162.1	157.5	152.9	147.0	140.0	133.0	126.0	119.0	114.7
65°	150.1	145.4	140.8	136.2	131.5	125.9	119.3	112.7	106.2	99.5	95.4
67.5°	128.7	124.0	119.3	114.6	109.9	104.4	98.1	91.8	85.4	79.2	76.1
70°	114.7	110.1	105.6	101.0	96.5	91.2	85.4	79.4	73.5	67.6	64.7
72.5°	100.8	96.3	91.8	87.2	82.8	77.9	72.5	67.1	61.7	56.3	54.0
75°	79.4	75.3	71.3	67.3	63.2	58.9	54.2	49.6	44.9	40.3	39.5
77.5°	59.9	56.3	52.6	48.9	45.3	42.0	39.0	36.0	33.0	30.0	29.6
80°	47.5	44.0	40.6	37.1	33.7	31.1	29.3	27.5	25.7	24.0	23.6
82.5°	35.6	32.6	29.7	26.7	23.6	21.8	21.0	20.1	19.3	18.4	18.2
85°	20.1	18.3	16.4	14.6	12.7	11.7	11.4	11.2	10.9	10.6	10.4
87.5°	7.3	6.8	6.2	5.6	5.1	4.9	5.1	5.3	5.5	5.7	5.7
90°	0.4	1.2	2.0	2.9	3.7	4.6	5.6	6.8	7.8	8.9	9.2
92.5°	9.0	9.5	10.0	10.6	11.2	11.7	12.4	13.0	13.6	14.2	14.4
95°	21.8	22.3	22.9	23.6	24.1	24.7	25.4	26.0	26.7	27.3	27.6
97.5°	38.7	39.1	39.5	40.0	40.4	40.8	41.3	41.8	42.3	42.8	43.1
100°	50.2	50.7	51.2	51.7	52.2	52.7	53.1	53.5	53.9	54.3	54.5
102.5°	63.5	63.8	64.2	64.4	64.7	65.1	65.7	66.2	66.8	67.3	67.6
105°	83.2	83.3	83.5	83.6	83.8	84.2	85.0	85.7	86.4	87.2	87.2
107.5°	105.9	106.0	106.1	106.2	106.3	106.5	106.8	107.0	107.4	107.7	107.9
110°	120.1	120.3	120.4	120.6	120.7	120.9	121.1	121.2	121.4	121.6	121.9



TEST NUMBER: P332393-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.9	134.9	135.1	135.2	135.3	135.3	135.3	135.4	135.4	135.4	135.8
115°	157.0	157.3	157.5	157.8	158.0	158.1	157.9	157.8	157.6	157.4	157.5
117.5°	179.4	179.5	179.7	179.9	180.0	179.9	179.8	179.5	179.4	179.1	179.1
120°	193.2	193.7	194.2	194.7	195.2	195.3	194.9	194.4	194.0	193.6	193.6
122.5°	207.7	208.1	208.5	208.8	209.1	209.2	209.0	208.8	208.6	208.4	208.1
125°	229.8	230.1	230.3	230.6	230.8	230.8	230.6	230.5	230.3	230.2	229.8
127.5°	250.2	250.7	251.3	251.8	252.3	252.5	252.3	252.1	251.9	251.8	251.3
130°	263.8	264.5	265.1	265.8	266.4	266.6	266.4	266.1	265.9	265.6	265.3
132.5°	277.4	278.0	278.8	279.4	280.1	280.3	280.1	279.9	279.7	279.6	279.2
135°	298.2	298.6	299.1	299.6	300.1	300.4	300.3	300.2	300.1	300.0	299.7
137.5°	317.4	317.8	318.2	318.6	319.0	319.4	319.5	319.8	320.0	320.2	319.8
140°	330.7	331.1	331.5	331.9	332.3	332.6	332.6	332.7	332.8	332.9	332.8
142.5°	342.8	343.2	343.6	344.1	344.5	344.7	344.9	345.0	345.2	345.3	345.2
145°	361.7	361.9	362.1	362.2	362.4	362.6	362.8	363.1	363.3	363.5	363.5
147.5°	378.3	378.5	378.9	379.1	379.4	379.7	379.9	380.2	380.4	380.7	380.7
150°	389.8	390.0	390.1	390.3	390.4	390.6	390.8	390.9	391.1	391.3	391.3
152.5°	399.3	399.5	399.7	399.9	400.1	400.3	400.4	400.6	400.6	400.7	400.9
155°	414.2	414.2	414.2	414.2	414.2	414.3	414.3	414.4	414.5	414.6	414.9
157.5°	426.9	426.8	426.7	426.6	426.5	426.5	426.6	426.6	426.6	426.7	427.1
160°	434.9	434.7	434.6	434.4	434.2	434.1	434.1	434.1	434.1	434.1	434.6
162.5°	442.0	441.7	441.5	441.2	441.1	441.0	441.0	441.1	441.2	441.2	441.6
165°	451.1	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.5
167.5°	458.4	458.1	457.8	457.5	457.1	457.0	457.1	457.1	457.2	457.2	457.8
170°	462.6	462.3	461.9	461.6	461.3	461.1	461.1	461.1	461.1	461.1	461.7
172.5°	465.9	465.5	465.2	464.9	464.5	464.3	464.3	464.3	464.3	464.3	464.9
175°	469.2	468.9	468.6	468.2	467.9	467.7	467.7	467.7	467.7	467.7	468.2
177.5°	470.7	470.3	470.1	469.9	469.6	469.4	469.4	469.4	469.4	469.4	469.9
180°	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3



TEST NUMBER: P332393-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.5	467.2	468.1	468.3	468.2	468.1	467.9	467.8
5°	463.5	464.2	465.0	465.3	465.1	465.0	464.8	464.6
7.5°	457.0	457.4	457.8	457.9	457.5	457.3	457.0	456.7
10°	451.1	451.2	451.3	451.1	450.7	450.3	449.8	449.4
12.5°	443.8	443.8	443.8	443.4	443.0	442.5	442.0	441.5
15°	431.0	430.6	430.2	429.7	429.2	428.5	428.0	427.4
17.5°	415.9	415.0	414.1	413.2	412.3	411.4	410.6	409.7
20°	405.4	404.3	403.2	402.2	401.1	400.1	399.2	398.1
22.5°	394.3	392.9	391.5	390.4	389.4	388.5	387.5	386.6
25°	375.9	374.2	372.4	371.0	370.1	369.2	368.3	367.4
27.5°	356.0	353.6	351.1	349.2	347.7	346.3	345.0	343.5
30°	341.9	339.0	336.1	334.0	332.6	331.3	330.0	328.6
32.5°	327.9	324.8	321.6	319.4	318.0	316.6	315.1	313.7
35°	307.3	303.6	300.0	297.4	296.0	294.4	292.9	291.4
37.5°	285.1	281.0	276.9	273.9	272.0	270.1	268.2	266.4
40°	269.7	265.3	260.9	257.7	255.8	253.9	251.9	250.0
42.5°	254.9	250.1	245.3	242.1	240.3	238.6	236.8	235.1
45°	233.1	228.3	223.5	220.0	218.1	216.1	214.0	212.0
47.5°	210.6	205.4	200.2	196.7	194.9	193.1	191.2	189.4
50°	195.4	190.2	185.0	181.4	179.4	177.5	175.5	173.6
52.5°	180.8	175.3	169.9	166.3	164.5	162.8	161.1	159.3
55°	158.9	154.0	149.1	145.8	144.1	142.4	140.7	139.0
57.5°	137.4	132.7	128.2	125.1	123.7	122.2	120.8	119.4
60°	123.8	119.3	114.7	111.7	110.3	108.8	107.5	106.0
62.5°	110.4	106.2	101.8	98.9	97.4	96.0	94.4	92.9
65°	91.2	87.2	83.0	80.5	79.5	78.6	77.7	76.7
67.5°	73.0	69.9	66.8	64.7	63.8	62.8	61.8	60.8
70°	61.7	58.8	55.8	53.9	52.9	52.0	51.0	50.1
72.5°	51.5	49.2	46.7	45.3	44.9	44.5	44.2	43.8
75°	38.6	37.7	36.9	36.4	36.2	36.0	35.9	35.7
77.5°	29.1	28.6	28.2	27.9	27.7	27.6	27.4	27.2
80°	23.4	23.2	22.9	22.7	22.5	22.3	22.2	22.0
82.5°	17.9	17.7	17.4	17.3	17.3	17.2	17.2	17.2
85°	10.3	10.1	9.9	9.9	9.9	9.9	9.9	9.9
87.5°	5.7	5.7	5.7	5.7	5.6	5.6	5.6	5.5
90°	9.5	9.9	10.2	10.4	10.6	10.8	10.9	11.1
92.5°	14.7	15.0	15.2	15.3	15.2	15.1	15.0	14.9
95°	28.0	28.3	28.6	28.8	28.8	28.8	28.8	28.8
97.5°	43.5	43.9	44.3	44.4	44.4	44.4	44.4	44.4
100°	54.8	55.0	55.3	55.5	55.7	55.8	56.0	56.2
102.5°	67.8	68.1	68.3	68.4	68.4	68.3	68.3	68.2
105°	87.2	87.2	87.2	87.2	87.5	87.6	87.8	88.0
107.5°	108.2	108.4	108.7	108.8	108.7	108.6	108.5	108.4
110°	122.2	122.5	122.9	122.9	122.8	122.6	122.5	122.3



TEST NUMBER: P332393-930

CATALOG NUMBER: S123RDIW-S340D460U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	136.2	136.6	137.1	137.2	137.1	137.1	137.1	137.1
115°	157.6	157.7	157.8	157.8	157.7	157.6	157.5	157.4
117.5°	179.1	179.0	179.0	179.0	178.7	178.5	178.2	178.0
120°	193.5	193.4	193.3	193.1	193.0	192.8	192.7	192.5
122.5°	208.0	207.7	207.5	207.3	207.1	206.8	206.6	206.4
125°	229.5	229.2	228.9	228.5	228.2	227.9	227.6	227.2
127.5°	250.9	250.4	249.9	249.5	249.2	248.7	248.3	248.0
130°	265.0	264.6	264.3	263.9	263.3	262.8	262.2	261.5
132.5°	278.8	278.3	277.9	277.5	277.1	276.6	276.2	275.7
135°	299.4	299.1	298.7	298.5	298.3	298.2	298.0	297.8
137.5°	319.5	319.2	318.8	318.5	318.1	317.9	317.6	317.2
140°	332.7	332.6	332.6	332.2	331.7	331.1	330.5	330.0
142.5°	345.1	345.0	345.0	344.7	344.3	343.8	343.4	342.9
145°	363.4	363.3	363.2	363.1	362.7	362.4	362.1	361.7
147.5°	380.7	380.7	380.7	380.4	379.9	379.4	378.9	378.4
150°	391.3	391.3	391.3	391.0	390.5	390.0	389.6	389.1
152.5°	401.0	401.1	401.3	401.1	400.7	400.2	399.8	399.4
155°	415.2	415.6	415.9	415.7	415.2	414.6	414.0	413.4
157.5°	427.5	427.8	428.1	428.0	427.6	427.1	426.6	426.2
160°	435.0	435.4	435.8	435.8	435.5	435.1	434.8	434.5
162.5°	442.1	442.5	442.9	442.8	442.3	441.7	441.2	440.7
165°	451.0	451.5	452.0	451.9	451.3	450.8	450.2	449.6
167.5°	458.3	458.8	459.3	459.3	458.8	458.3	457.8	457.2
170°	462.3	462.8	463.4	463.4	462.8	462.3	461.7	461.1
172.5°	465.4	465.9	466.4	466.4	465.8	465.2	464.6	464.1
175°	468.7	469.2	469.7	469.7	469.1	468.6	468.0	467.4
177.5°	470.3	470.7	471.0	471.0	470.5	470.1	469.6	469.1
180°	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3

(END OF REPORT)