

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332396-930

Luminaire Tested: **S123RDIW-S340D755U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332396-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D755U930-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3523.0 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332396-930

CATALOG NUMBER: S123RDIW-S340D755U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332396-930

CATALOG NUMBER: S123RDIW-S340D755U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	89	86	82	84	80	77	74	63	61	60	48	47	45	34	33	32	26
2	85	78	72	68	76	70	66	61	56	52	50	42	40	38	30	29	27	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5042	5042	5042
5°	5061	4991	5020
10°	5032	4928	4912
15°	4979	4813	4763
20°	4904	4669	4560
25°	4828	4507	4363
30°	4727	4320	4084
35°	4623	4133	3829
40°	4526	3912	3513
45°	4401	3694	3227
50°	4262	3448	2907
55°	4121	3166	2609
60°	3991	2863	2282
65°	3823	2534	1954
70°	3610	2127	1577
75°	3302	1676	1485
80°	2944	1488	1364
85°	2482	1309	1223



TEST NUMBER: P332396-930

CATALOG NUMBER: S123RDIW-S340D755U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	1.2
10°-20°	122.4	3.5
20°-30°	176.2	5.0
30°-40°	198.5	5.6
40°-50°	189.9	5.4
50°-60°	155.5	4.4
60°-70°	104.9	3.0
70°-80°	52.8	1.5
80°-90°	16.2	0.5
90°-100°	29.4	0.8
100°-110°	139.9	4.0
110°-120°	336.1	9.5
120°-130°	428.0	12.1
130°-140°	457.3	13.0
140°-150°	427.6	12.1
150°-160°	344.9	9.8
160°-170°	222.6	6.3
170°-180°	76.7	2.2
0°-30°	342.6	9.7
0°-40°	541.1	15.4
0°-60°	886.5	25.2
0°-90°	1060.4	30.1
90°-120°	505.4	14.3
90°-150°	1818.3	51.6
90°-180°	2463.0	69.9
0°-180°	3523.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	468	468	468	468	468	
5°	468	466	462	465	465	44
15°	447	442	432	430	427	126
25°	406	396	380	372	367	187
35°	352	338	314	299	291	220
45°	289	271	243	222	212	223
55°	220	200	169	147	139	197
65°	150	129	100	82	77	148
75°	79	61	40	37	36	85
85°	20	12	11	10	10	23
90°	1	7	14	17	18	3
95°	37	14	19	23	23	45
105°	179	182	131	31	26	190
115°	335	339	344	350	353	331
125°	473	477	480	481	482	422
135°	589	592	594	596	594	453
145°	679	683	684	686	686	425
155°	748	747	748	750	747	345
165°	789	787	786	791	787	223
175°	808	805	805	809	804	77
180°	808	808	808	808	808	



TEST NUMBER: P332396-930

CATALOG NUMBER: S123RDIW-S340D755U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	469.9	469.6	469.4	469.1	468.9	468.3	467.5	466.7	465.9	465.0	465.8
5°	468.4	468.0	467.6	467.2	466.7	466.0	465.0	464.0	462.9	461.9	462.7
7.5°	464.1	463.6	463.2	462.7	462.3	461.4	460.1	458.8	457.4	456.1	456.5
10°	460.4	459.8	459.3	458.7	458.0	457.0	455.5	454.0	452.4	450.9	451.0
12.5°	455.3	454.6	454.0	453.3	452.7	451.3	449.5	447.7	445.8	443.9	443.8
15°	446.8	445.8	444.9	443.9	443.0	441.4	439.0	436.7	434.3	431.9	431.5
17.5°	436.0	435.0	433.9	432.8	431.7	429.7	426.6	423.6	420.7	417.7	416.8
20°	428.1	426.8	425.4	424.1	422.7	420.4	417.3	414.0	410.8	407.6	406.5
22.5°	419.3	417.8	416.2	414.7	413.1	410.7	407.2	403.8	400.4	397.0	395.6
25°	406.5	404.4	402.3	400.1	398.0	395.0	391.2	387.3	383.4	379.5	377.7
27.5°	390.9	388.6	386.2	383.9	381.6	378.3	374.0	369.6	365.3	360.9	358.5
30°	380.3	377.7	375.2	372.7	370.1	366.5	361.7	357.0	352.3	347.6	344.7
32.5°	369.7	366.7	363.9	361.0	358.2	354.2	349.2	344.2	339.2	334.2	331.1
35°	351.8	348.7	345.7	342.7	339.7	335.5	330.3	325.0	319.8	314.5	311.0
37.5°	333.7	330.3	326.9	323.6	320.2	315.7	310.1	304.5	299.0	293.3	289.3
40°	322.1	318.5	314.7	311.0	307.3	302.4	296.4	290.4	284.5	278.4	274.1
42.5°	309.1	305.3	301.7	297.9	294.2	289.3	283.1	276.9	270.7	264.5	259.7
45°	289.1	285.3	281.5	277.7	273.9	268.7	262.3	255.8	249.2	242.7	237.9
47.5°	269.1	265.0	260.7	256.6	252.4	247.1	240.6	234.1	227.6	221.1	215.9
50°	254.5	250.5	246.6	242.6	238.6	233.3	226.4	219.6	212.7	205.9	200.6
52.5°	241.5	237.2	232.8	228.5	224.2	218.7	211.9	205.1	198.4	191.6	186.2
55°	219.6	215.4	211.3	207.2	203.0	197.4	190.2	183.0	175.9	168.7	163.8
57.5°	199.3	194.9	190.4	185.8	181.3	175.5	168.3	161.0	153.8	146.7	142.0
60°	185.4	180.8	176.1	171.5	166.8	161.0	154.0	147.0	140.0	133.0	128.4
62.5°	171.4	166.7	162.1	157.5	152.9	147.0	140.0	133.0	126.0	119.0	114.7
65°	150.1	145.4	140.8	136.2	131.5	125.9	119.3	112.7	106.2	99.5	95.4
67.5°	128.7	124.0	119.3	114.6	109.9	104.4	98.1	91.8	85.4	79.2	76.1
70°	114.7	110.1	105.6	101.0	96.5	91.2	85.4	79.4	73.5	67.6	64.7
72.5°	100.8	96.3	91.8	87.2	82.8	77.9	72.5	67.1	61.7	56.3	54.0
75°	79.4	75.3	71.3	67.3	63.2	58.9	54.2	49.6	44.9	40.3	39.5
77.5°	59.9	56.3	52.6	48.9	45.3	42.0	39.0	36.0	33.0	30.0	29.6
80°	47.5	44.0	40.6	37.1	33.7	31.1	29.3	27.5	25.7	24.0	23.6
82.5°	35.6	32.6	29.7	26.7	23.6	21.8	21.0	20.1	19.3	18.4	18.2
85°	20.1	18.3	16.4	14.6	12.7	11.7	11.4	11.2	10.9	10.6	10.4
87.5°	7.4	6.9	6.4	6.0	5.5	5.5	5.8	6.1	6.5	6.8	6.8
90°	0.6	2.0	3.3	4.6	6.0	7.5	9.2	10.9	12.6	14.4	14.9
92.5°	11.2	10.8	10.4	10.0	9.7	10.1	11.4	12.7	14.0	15.3	16.2
95°	36.6	31.1	25.7	20.2	14.8	12.7	14.2	15.7	17.1	18.6	19.6
97.5°	73.5	71.1	68.6	66.2	63.8	57.7	48.1	38.5	28.9	19.3	20.4
100°	101.4	104.0	106.7	109.4	112.0	103.0	82.2	61.4	40.6	19.8	20.9
102.5°	133.1	135.0	136.9	138.8	140.7	130.4	107.6	84.9	62.2	39.5	36.2
105°	178.8	180.3	181.7	183.2	184.7	179.4	167.4	155.4	143.4	131.4	107.8
107.5°	227.0	228.2	229.3	230.6	231.7	233.3	235.1	237.0	239.0	240.8	223.5
110°	259.2	260.2	261.3	262.4	263.4	264.7	266.2	267.7	269.1	270.6	266.2



TEST NUMBER: P332396-930

CATALOG NUMBER: S123RDIW-S340D755U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	289.9	290.8	291.8	292.8	293.8	295.0	296.4	297.9	299.4	300.8	300.9
115°	335.3	336.1	337.0	337.8	338.6	339.6	340.8	341.9	343.2	344.4	345.7
117.5°	379.4	380.4	381.4	382.4	383.4	384.2	384.7	385.4	386.0	386.6	387.7
120°	406.8	408.0	409.2	410.3	411.6	412.4	412.8	413.2	413.6	413.9	415.1
122.5°	434.6	435.6	436.6	437.6	438.5	439.3	439.8	440.3	440.8	441.3	442.1
125°	472.8	473.9	474.9	476.0	477.0	477.8	478.3	478.9	479.4	480.0	480.2
127.5°	509.7	510.8	511.8	512.9	514.0	514.9	515.5	516.1	516.7	517.4	517.8
130°	532.7	533.9	534.9	536.0	537.0	537.9	538.3	538.9	539.4	540.0	540.5
132.5°	554.8	555.9	556.9	558.0	559.1	559.9	560.3	560.7	561.1	561.6	562.1
135°	588.6	589.4	590.1	590.9	591.7	592.4	593.0	593.5	594.0	594.5	594.9
137.5°	617.3	618.3	619.4	620.4	621.4	622.1	622.3	622.6	623.0	623.2	623.9
140°	636.5	637.3	638.1	639.0	639.8	640.3	640.7	641.2	641.6	642.0	642.5
142.5°	654.3	655.1	655.9	656.7	657.5	658.1	658.5	658.9	659.3	659.7	660.1
145°	679.1	680.0	681.0	681.9	682.9	683.5	683.7	684.0	684.3	684.5	684.8
147.5°	702.5	703.1	703.8	704.3	705.0	705.4	705.7	706.0	706.2	706.5	706.8
150°	717.0	717.3	717.7	718.1	718.5	718.8	719.2	719.4	719.7	719.9	720.2
152.5°	729.9	730.1	730.3	730.4	730.7	730.8	731.0	731.2	731.3	731.5	731.9
155°	748.1	747.9	747.6	747.3	747.1	747.0	747.1	747.3	747.4	747.5	748.2
157.5°	762.3	762.3	762.2	762.2	762.2	762.1	762.0	761.8	761.7	761.6	762.4
160°	770.9	770.8	770.7	770.5	770.4	770.3	770.1	770.0	769.9	769.7	770.5
162.5°	779.1	778.8	778.4	778.0	777.7	777.5	777.3	777.2	777.1	776.9	777.9
165°	789.0	788.6	788.1	787.7	787.3	787.1	786.9	786.8	786.7	786.5	787.6
167.5°	796.6	796.1	795.6	795.0	794.5	794.2	794.2	794.2	794.2	794.2	795.2
170°	801.0	800.4	799.9	799.3	798.8	798.5	798.5	798.5	798.5	798.5	799.6
172.5°	803.8	803.2	802.5	801.9	801.3	801.0	801.1	801.2	801.3	801.4	802.5
175°	807.6	806.8	806.2	805.5	804.9	804.6	804.7	804.9	805.0	805.1	806.1
177.5°	808.5	808.0	807.4	806.9	806.3	806.2	806.2	806.3	806.5	806.6	807.4
180°	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6



TEST NUMBER: P332396-930

CATALOG NUMBER: S123RDIW-S340D755U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	468.4	468.4	468.4	468.4	468.4	468.4	468.4	468.4
2.5°	466.5	467.2	468.1	468.3	468.2	468.1	467.9	467.8
5°	463.5	464.2	465.0	465.3	465.1	465.0	464.8	464.6
7.5°	457.0	457.4	457.8	457.9	457.5	457.3	457.0	456.7
10°	451.1	451.2	451.3	451.1	450.7	450.3	449.8	449.4
12.5°	443.8	443.8	443.8	443.4	443.0	442.5	442.0	441.5
15°	431.0	430.6	430.2	429.7	429.2	428.5	428.0	427.4
17.5°	415.9	415.0	414.1	413.2	412.3	411.4	410.6	409.7
20°	405.4	404.3	403.2	402.2	401.1	400.1	399.2	398.1
22.5°	394.3	392.9	391.5	390.4	389.4	388.5	387.5	386.6
25°	375.9	374.2	372.4	371.0	370.1	369.2	368.3	367.4
27.5°	356.0	353.6	351.1	349.2	347.7	346.3	345.0	343.5
30°	341.9	339.0	336.1	334.0	332.6	331.3	330.0	328.6
32.5°	327.9	324.8	321.6	319.4	318.0	316.6	315.1	313.7
35°	307.3	303.6	300.0	297.4	296.0	294.4	292.9	291.4
37.5°	285.1	281.0	276.9	273.9	272.0	270.1	268.2	266.4
40°	269.7	265.3	260.9	257.7	255.8	253.9	251.9	250.0
42.5°	254.9	250.1	245.3	242.1	240.3	238.6	236.8	235.1
45°	233.1	228.3	223.5	220.0	218.1	216.1	214.0	212.0
47.5°	210.6	205.4	200.2	196.7	194.9	193.1	191.2	189.4
50°	195.4	190.2	185.0	181.4	179.4	177.5	175.5	173.6
52.5°	180.8	175.3	169.9	166.3	164.5	162.8	161.1	159.3
55°	158.9	154.0	149.1	145.8	144.1	142.4	140.7	139.0
57.5°	137.4	132.7	128.2	125.1	123.7	122.2	120.8	119.4
60°	123.8	119.3	114.7	111.7	110.3	108.8	107.5	106.0
62.5°	110.4	106.2	101.8	98.9	97.4	96.0	94.4	92.9
65°	91.2	87.2	83.0	80.5	79.5	78.6	77.7	76.7
67.5°	73.0	69.9	66.8	64.7	63.8	62.8	61.8	60.8
70°	61.7	58.8	55.8	53.9	52.9	52.0	51.0	50.1
72.5°	51.5	49.2	46.7	45.3	44.9	44.5	44.2	43.8
75°	38.6	37.7	36.9	36.4	36.2	36.0	35.9	35.7
77.5°	29.1	28.6	28.2	27.9	27.7	27.6	27.4	27.2
80°	23.4	23.2	22.9	22.7	22.5	22.3	22.2	22.0
82.5°	17.9	17.7	17.4	17.3	17.3	17.2	17.2	17.2
85°	10.3	10.1	9.9	9.9	9.9	9.9	9.9	9.9
87.5°	6.9	6.9	7.0	7.0	7.0	7.0	6.9	6.9
90°	15.5	16.0	16.6	17.0	17.2	17.4	17.7	18.0
92.5°	17.0	17.9	18.8	19.2	19.4	19.6	19.7	19.9
95°	20.5	21.4	22.3	22.8	22.8	22.8	22.8	22.8
97.5°	21.4	22.5	23.6	24.2	24.3	24.5	24.6	24.7
100°	21.9	23.0	24.1	24.7	24.8	24.9	25.0	25.2
102.5°	32.9	29.6	26.3	24.7	24.9	25.2	25.4	25.7
105°	84.2	60.6	37.0	25.4	25.6	25.8	26.2	26.4
107.5°	206.2	188.9	171.6	154.1	136.2	118.5	100.7	82.9
110°	261.8	257.4	253.0	241.2	222.2	203.1	184.0	165.0



TEST NUMBER: P332396-930

CATALOG NUMBER: S123RDIW-S340D755U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	301.0	301.1	301.2	299.1	295.1	291.1	287.1	283.1
115°	347.1	348.4	349.7	350.7	351.1	351.7	352.2	352.8
117.5°	388.7	389.8	390.9	391.4	391.6	391.7	391.8	391.9
120°	416.1	417.2	418.2	418.7	418.7	418.7	418.7	418.7
122.5°	442.8	443.5	444.3	444.7	444.8	444.9	445.1	445.2
125°	480.5	480.8	481.0	481.3	481.6	481.8	482.1	482.3
127.5°	518.3	518.7	519.1	519.2	518.9	518.6	518.4	518.1
130°	541.0	541.5	542.1	542.3	541.9	541.7	541.4	541.1
132.5°	562.6	563.1	563.7	563.8	563.4	563.0	562.6	562.2
135°	595.3	595.7	596.1	596.1	595.7	595.3	594.9	594.5
137.5°	624.5	625.2	625.8	626.0	625.7	625.4	625.2	624.9
140°	643.0	643.5	644.1	644.2	643.9	643.7	643.4	643.1
142.5°	660.6	661.0	661.4	661.5	661.0	660.7	660.3	659.9
145°	685.1	685.3	685.6	685.7	685.7	685.7	685.7	685.7
147.5°	707.0	707.3	707.6	707.4	706.8	706.1	705.6	704.9
150°	720.5	720.7	721.0	721.0	720.6	720.2	719.7	719.3
152.5°	732.4	732.9	733.4	733.3	732.7	732.1	731.5	730.8
155°	748.9	749.5	750.2	750.2	749.3	748.5	747.7	746.9
157.5°	763.2	763.9	764.8	764.7	763.6	762.5	761.6	760.5
160°	771.4	772.2	772.9	772.9	771.9	771.0	770.1	769.2
162.5°	778.8	779.7	780.6	780.6	779.8	778.9	778.1	777.3
165°	788.6	789.7	790.8	790.8	789.9	789.0	788.1	787.1
167.5°	796.3	797.4	798.5	798.5	797.4	796.3	795.2	794.2
170°	800.6	801.8	802.8	802.8	801.8	800.6	799.6	798.5
172.5°	803.6	804.6	805.7	805.6	804.5	803.3	802.1	801.0
175°	807.0	808.0	808.9	808.8	807.7	806.7	805.6	804.5
177.5°	808.3	809.1	810.0	809.8	808.8	807.7	806.7	805.6
180°	807.6	807.6	807.6	807.6	807.6	807.6	807.6	807.6

(END OF REPORT)