

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332413-930

Luminaire Tested: **S123RDIW-S560D460U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332413-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S560D460U930-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3044.2 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332413-930

CATALOG NUMBER: S123RDIW-S560D460U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332413-930

CATALOG NUMBER: S123RDIW-S560D460U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	92	88	93	89	86	83	77	75	73	66	64	63	56	55	54	49
2	91	84	78	73	85	78	73	69	68	64	61	59	56	53	50	48	46	42
3	83	74	67	61	77	69	63	58	60	55	51	52	48	45	44	42	39	36
4	76	66	58	52	71	62	55	49	54	48	44	47	42	39	40	37	34	31
5	70	59	51	45	65	55	48	43	48	43	38	42	38	34	36	33	30	27
6	65	53	45	39	60	50	43	37	44	38	34	38	34	30	33	29	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	44	36	31	52	41	34	29	36	31	27	32	27	24	28	24	21	19
9	52	40	32	27	49	38	31	26	33	28	24	29	25	22	26	22	19	17
10	49	37	30	25	46	35	28	24	31	25	22	27	23	20	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8289	8289	8289
5°	8321	8206	8253
10°	8273	8103	8075
15°	8184	7913	7830
20°	8062	7676	7497
25°	7936	7410	7172
30°	7771	7102	6714
35°	7599	6795	6294
40°	7442	6433	5774
45°	7234	6075	5305
50°	7006	5668	4779
55°	6775	5204	4290
60°	6562	4706	3750
65°	6283	4167	3212
70°	5936	3500	2593
75°	5427	2753	2441
80°	4841	2442	2244
85°	4088	2149	2001



TEST NUMBER: P332413-930

CATALOG NUMBER: S123RDIW-S560D460U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.3	2.4
10°-20°	201.2	6.6
20°-30°	289.7	9.5
30°-40°	326.3	10.7
40°-50°	312.2	10.3
50°-60°	255.7	8.4
60°-70°	172.5	5.7
70°-80°	86.8	2.9
80°-90°	24.4	0.8
90°-100°	30.6	1.0
100°-110°	91.7	3.0
110°-120°	156.0	5.1
120°-130°	205.2	6.7
130°-140°	230.6	7.6
140°-150°	226.7	7.4
150°-160°	190.8	6.3
160°-170°	127.0	4.2
170°-180°	44.5	1.5
0°-30°	563.2	18.5
0°-40°	889.5	29.2
0°-60°	1457.4	47.9
0°-90°	1741.0	57.2
90°-120°	278.3	9.1
90°-150°	940.8	30.9
90°-180°	1303.0	42.8
0°-180°	3044.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	770	770	770	770	770	
5°	770	767	760	765	764	73
15°	734	727	710	707	703	207
25°	668	652	624	611	604	307
35°	578	555	517	491	479	362
45°	475	446	399	365	348	367
55°	361	329	277	242	229	324
65°	247	212	164	134	126	244
75°	130	100	66	60	59	139
85°	33	20	17	16	16	37
90°	0	4	9	10	11	3
95°	22	24	27	29	29	24
105°	83	84	87	87	88	89
115°	157	158	157	158	157	155
125°	230	231	230	229	227	205
135°	298	300	300	299	298	230
145°	362	362	364	363	362	226
155°	414	414	415	416	413	191
165°	451	450	450	452	450	127
175°	469	468	468	470	467	45
180°	470	470	470	470	470	



TEST NUMBER: P332413-930

CATALOG NUMBER: S123RDIW-S560D460U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	772.6	772.1	771.7	771.2	770.8	769.9	768.6	767.2	765.9	764.6	765.8
5°	770.1	769.4	768.7	768.0	767.3	766.1	764.4	762.8	761.1	759.5	760.7
7.5°	763.0	762.2	761.4	760.7	759.9	758.5	756.4	754.2	752.0	749.8	750.5
10°	756.9	755.9	755.0	754.0	753.1	751.3	748.9	746.3	743.8	741.4	741.4
12.5°	748.4	747.4	746.2	745.2	744.1	742.1	739.0	736.0	732.9	729.9	729.8
15°	734.4	733.0	731.4	729.9	728.4	725.6	721.8	717.9	714.0	710.1	709.4
17.5°	716.8	715.1	713.3	711.5	709.7	706.4	701.4	696.5	691.5	686.6	685.2
20°	703.8	701.6	699.4	697.2	695.0	691.2	685.9	680.7	675.4	670.1	668.3
22.5°	689.3	686.8	684.3	681.7	679.1	675.1	669.4	663.8	658.3	652.6	650.4
25°	668.2	664.8	661.3	657.9	654.4	649.5	643.0	636.7	630.3	623.9	621.0
27.5°	642.6	638.8	635.0	631.1	627.3	621.8	614.7	607.6	600.5	593.5	589.4
30°	625.2	621.0	616.9	612.7	608.5	602.5	594.8	587.0	579.2	571.4	566.7
32.5°	607.6	603.0	598.3	593.5	588.8	582.4	574.1	565.9	557.7	549.4	544.3
35°	578.3	573.3	568.3	563.4	558.3	551.5	542.9	534.3	525.7	517.1	511.1
37.5°	548.6	543.1	537.5	531.9	526.4	519.0	509.8	500.7	491.5	482.2	475.5
40°	529.6	523.5	517.4	511.3	505.2	497.2	487.4	477.5	467.7	457.8	450.5
42.5°	508.1	502.0	495.9	489.8	483.7	475.6	465.4	455.2	445.0	434.8	426.9
45°	475.2	469.0	462.8	456.6	450.3	441.8	431.1	420.4	409.8	399.1	391.2
47.5°	442.4	435.5	428.7	421.8	415.0	406.3	395.5	384.8	374.1	363.5	354.9
50°	418.4	411.9	405.4	398.8	392.3	383.4	372.2	361.0	349.8	338.5	329.9
52.5°	397.0	389.9	382.8	375.7	368.7	359.5	348.4	337.3	326.1	315.0	306.1
55°	361.0	354.2	347.4	340.6	333.8	324.5	312.7	300.9	289.1	277.3	269.2
57.5°	327.8	320.3	312.9	305.5	298.1	288.5	276.6	264.8	252.9	241.1	233.5
60°	304.8	297.2	289.5	281.8	274.3	264.6	253.2	241.7	230.1	218.6	211.1
62.5°	281.8	274.2	266.5	258.9	251.3	241.7	230.2	218.7	207.1	195.6	188.6
65°	246.7	239.0	231.5	223.8	216.1	206.9	196.1	185.3	174.5	163.6	156.9
67.5°	211.6	203.9	196.2	188.4	180.8	171.7	161.3	150.9	140.6	130.1	125.1
70°	188.6	181.1	173.7	166.2	158.7	150.0	140.3	130.6	120.9	111.2	106.3
72.5°	165.6	158.2	150.8	143.5	136.1	128.0	119.2	110.3	101.5	92.7	88.7
75°	130.5	123.8	117.2	110.6	103.9	96.7	89.1	81.4	73.9	66.2	64.8
77.5°	98.6	92.5	86.5	80.5	74.4	69.0	64.1	59.2	54.2	49.3	48.6
80°	78.1	72.4	66.7	61.0	55.3	51.0	48.1	45.2	42.2	39.4	38.9
82.5°	58.6	53.6	48.8	43.9	38.9	35.8	34.4	33.1	31.7	30.3	29.9
85°	33.1	30.1	27.0	24.0	20.9	19.2	18.8	18.3	17.9	17.4	17.2
87.5°	12.1	11.0	9.9	8.9	7.8	7.4	7.7	7.8	8.1	8.2	8.2
90°	0.4	1.2	2.0	2.9	3.7	4.6	5.6	6.8	7.8	8.9	9.2
92.5°	9.0	9.5	10.0	10.6	11.2	11.7	12.4	13.0	13.6	14.2	14.4
95°	21.8	22.3	22.9	23.6	24.1	24.7	25.4	26.0	26.7	27.3	27.6
97.5°	38.7	39.1	39.5	40.0	40.4	40.8	41.3	41.8	42.3	42.8	43.1
100°	50.2	50.7	51.2	51.7	52.2	52.7	53.1	53.5	53.9	54.3	54.5
102.5°	63.5	63.8	64.2	64.4	64.7	65.1	65.7	66.2	66.8	67.3	67.6
105°	83.2	83.3	83.5	83.6	83.8	84.2	85.0	85.7	86.4	87.2	87.2
107.5°	105.9	106.0	106.1	106.2	106.3	106.5	106.8	107.0	107.4	107.7	107.9
110°	120.1	120.3	120.4	120.6	120.7	120.9	121.1	121.2	121.4	121.6	121.9



TEST NUMBER: P332413-930

CATALOG NUMBER: S123RDIW-S560D460U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.9	134.9	135.1	135.2	135.3	135.3	135.3	135.4	135.4	135.4	135.8
115°	157.0	157.3	157.5	157.8	158.0	158.1	157.9	157.8	157.6	157.4	157.5
117.5°	179.4	179.5	179.7	179.9	180.0	179.9	179.8	179.5	179.4	179.1	179.1
120°	193.2	193.7	194.2	194.7	195.2	195.3	194.9	194.4	194.0	193.6	193.6
122.5°	207.7	208.1	208.5	208.8	209.1	209.2	209.0	208.8	208.6	208.4	208.1
125°	229.8	230.1	230.3	230.6	230.8	230.8	230.6	230.5	230.3	230.2	229.8
127.5°	250.2	250.7	251.3	251.8	252.3	252.5	252.3	252.1	251.9	251.8	251.3
130°	263.8	264.5	265.1	265.8	266.4	266.6	266.4	266.1	265.9	265.6	265.3
132.5°	277.4	278.0	278.8	279.4	280.1	280.3	280.1	279.9	279.7	279.6	279.2
135°	298.2	298.6	299.1	299.6	300.1	300.4	300.3	300.2	300.1	300.0	299.7
137.5°	317.4	317.8	318.2	318.6	319.0	319.4	319.5	319.8	320.0	320.2	319.8
140°	330.7	331.1	331.5	331.9	332.3	332.6	332.6	332.7	332.8	332.9	332.8
142.5°	342.8	343.2	343.6	344.1	344.5	344.7	344.9	345.0	345.2	345.3	345.2
145°	361.7	361.9	362.1	362.2	362.4	362.6	362.8	363.1	363.3	363.5	363.5
147.5°	378.3	378.5	378.9	379.1	379.4	379.7	379.9	380.2	380.4	380.7	380.7
150°	389.8	390.0	390.1	390.3	390.4	390.6	390.8	390.9	391.1	391.3	391.3
152.5°	399.3	399.5	399.7	399.9	400.1	400.3	400.4	400.6	400.6	400.7	400.9
155°	414.2	414.2	414.2	414.2	414.2	414.3	414.3	414.4	414.5	414.6	414.9
157.5°	426.9	426.8	426.7	426.6	426.5	426.5	426.6	426.6	426.6	426.7	427.1
160°	434.9	434.7	434.6	434.4	434.2	434.1	434.1	434.1	434.1	434.1	434.6
162.5°	442.0	441.7	441.5	441.2	441.1	441.0	441.0	441.1	441.2	441.2	441.6
165°	451.1	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.5
167.5°	458.4	458.1	457.8	457.5	457.1	457.0	457.1	457.1	457.2	457.2	457.8
170°	462.6	462.3	461.9	461.6	461.3	461.1	461.1	461.1	461.1	461.1	461.7
172.5°	465.9	465.5	465.2	464.9	464.5	464.3	464.3	464.3	464.3	464.3	464.9
175°	469.2	468.9	468.6	468.2	467.9	467.7	467.7	467.7	467.7	467.7	468.2
177.5°	470.7	470.3	470.1	469.9	469.6	469.4	469.4	469.4	469.4	469.4	469.9
180°	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3



TEST NUMBER: P332413-930

CATALOG NUMBER: S123RDIW-S560D460U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	770.1	770.1	770.1	770.1	770.1	770.1	770.1	770.1
2.5°	767.0	768.3	769.5	770.0	769.7	769.5	769.3	769.1
5°	761.9	763.2	764.4	764.9	764.7	764.3	764.1	763.8
7.5°	751.2	751.9	752.6	752.7	752.2	751.8	751.3	750.8
10°	741.6	741.8	741.8	741.6	740.9	740.2	739.6	738.8
12.5°	729.7	729.6	729.5	729.0	728.2	727.4	726.7	725.9
15°	708.7	708.0	707.4	706.5	705.5	704.6	703.6	702.6
17.5°	683.7	682.2	680.7	679.3	677.8	676.4	674.9	673.5
20°	666.5	664.7	662.9	661.2	659.5	657.9	656.2	654.5
22.5°	648.2	645.9	643.7	641.7	640.2	638.6	637.1	635.5
25°	618.1	615.1	612.3	610.0	608.5	607.0	605.4	603.9
27.5°	585.3	581.3	577.2	574.1	571.7	569.4	567.0	564.7
30°	562.0	557.3	552.6	549.1	546.9	544.7	542.4	540.2
32.5°	539.2	533.9	528.8	525.1	522.8	520.4	518.0	515.8
35°	505.2	499.2	493.3	489.0	486.5	484.0	481.5	479.0
37.5°	468.7	461.9	455.2	450.3	447.2	444.1	441.0	437.9
40°	443.4	436.1	428.9	423.7	420.5	417.4	414.2	410.9
42.5°	419.1	411.2	403.2	397.9	395.0	392.2	389.3	386.5
45°	383.3	375.4	367.5	361.8	358.5	355.1	351.8	348.5
47.5°	346.3	337.7	329.1	323.3	320.3	317.3	314.4	311.4
50°	321.3	312.7	304.1	298.2	295.0	291.8	288.6	285.4
52.5°	297.2	288.2	279.2	273.4	270.5	267.7	264.8	262.0
55°	261.2	253.2	245.1	239.7	236.9	234.2	231.4	228.6
57.5°	225.8	218.3	210.7	205.7	203.3	201.0	198.6	196.2
60°	203.6	196.1	188.6	183.7	181.3	179.0	176.6	174.2
62.5°	181.5	174.5	167.4	162.7	160.2	157.7	155.2	152.8
65°	150.0	143.2	136.4	132.2	130.8	129.2	127.7	126.1
67.5°	120.0	114.9	109.8	106.5	104.8	103.2	101.6	100.0
70°	101.4	96.6	91.7	88.5	87.0	85.5	84.0	82.4
72.5°	84.7	80.8	76.8	74.5	73.9	73.2	72.6	71.9
75°	63.4	62.0	60.7	59.8	59.5	59.3	58.9	58.7
77.5°	47.9	47.1	46.3	45.8	45.6	45.2	45.0	44.7
80°	38.5	38.1	37.7	37.3	37.1	36.8	36.5	36.2
82.5°	29.5	29.1	28.7	28.5	28.4	28.4	28.3	28.2
85°	17.0	16.6	16.4	16.2	16.2	16.2	16.2	16.2
87.5°	8.2	8.2	8.1	8.0	7.9	7.9	7.8	7.7
90°	9.5	9.9	10.2	10.4	10.6	10.8	10.9	11.1
92.5°	14.7	15.0	15.2	15.3	15.2	15.1	15.0	14.9
95°	28.0	28.3	28.6	28.8	28.8	28.8	28.8	28.8
97.5°	43.5	43.9	44.3	44.4	44.4	44.4	44.4	44.4
100°	54.8	55.0	55.3	55.5	55.7	55.8	56.0	56.2
102.5°	67.8	68.1	68.3	68.4	68.4	68.3	68.3	68.2
105°	87.2	87.2	87.2	87.2	87.5	87.6	87.8	88.0
107.5°	108.2	108.4	108.7	108.8	108.7	108.6	108.5	108.4
110°	122.2	122.5	122.9	122.9	122.8	122.6	122.5	122.3



TEST NUMBER: P332413-930

CATALOG NUMBER: S123RDIW-S560D460U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	136.2	136.6	137.1	137.2	137.1	137.1	137.1	137.1
115°	157.6	157.7	157.8	157.8	157.7	157.6	157.5	157.4
117.5°	179.1	179.0	179.0	179.0	178.7	178.5	178.2	178.0
120°	193.5	193.4	193.3	193.1	193.0	192.8	192.7	192.5
122.5°	208.0	207.7	207.5	207.3	207.1	206.8	206.6	206.4
125°	229.5	229.2	228.9	228.5	228.2	227.9	227.6	227.2
127.5°	250.9	250.4	249.9	249.5	249.2	248.7	248.3	248.0
130°	265.0	264.6	264.3	263.9	263.3	262.8	262.2	261.5
132.5°	278.8	278.3	277.9	277.5	277.1	276.6	276.2	275.7
135°	299.4	299.1	298.7	298.5	298.3	298.2	298.0	297.8
137.5°	319.5	319.2	318.8	318.5	318.1	317.9	317.6	317.2
140°	332.7	332.6	332.6	332.2	331.7	331.1	330.5	330.0
142.5°	345.1	345.0	345.0	344.7	344.3	343.8	343.4	342.9
145°	363.4	363.3	363.2	363.1	362.7	362.4	362.1	361.7
147.5°	380.7	380.7	380.7	380.4	379.9	379.4	378.9	378.4
150°	391.3	391.3	391.3	391.0	390.5	390.0	389.6	389.1
152.5°	401.0	401.1	401.3	401.1	400.7	400.2	399.8	399.4
155°	415.2	415.6	415.9	415.7	415.2	414.6	414.0	413.4
157.5°	427.5	427.8	428.1	428.0	427.6	427.1	426.6	426.2
160°	435.0	435.4	435.8	435.8	435.5	435.1	434.8	434.5
162.5°	442.1	442.5	442.9	442.8	442.3	441.7	441.2	440.7
165°	451.0	451.5	452.0	451.9	451.3	450.8	450.2	449.6
167.5°	458.3	458.8	459.3	459.3	458.8	458.3	457.8	457.2
170°	462.3	462.8	463.4	463.4	462.8	462.3	461.7	461.1
172.5°	465.4	465.9	466.4	466.4	465.8	465.2	464.6	464.1
175°	468.7	469.2	469.7	469.7	469.1	468.6	468.0	467.4
177.5°	470.3	470.7	471.0	471.0	470.5	470.1	469.6	469.1
180°	470.3	470.3	470.3	470.3	470.3	470.3	470.3	470.3

(END OF REPORT)