

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332208

Luminaire Tested: **S123DIW-S1000D1535U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332208  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1000D1535U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1535 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 10260.9 lumens  
Efficiency: N/A  
Efficacy: 134.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332208

CATALOG NUMBER: S123DIW-S1000D1535U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332208

CATALOG NUMBER: S123DIW-S1000D1535U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	34
2	87	80	74	68	79	73	67	63	60	56	53	48	45	43	37	35	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	24
4	72	62	54	48	66	57	50	45	47	42	38	37	34	31	29	26	24	20
5	66	55	47	41	60	50	43	38	42	36	32	34	30	27	26	23	21	18
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	24	21	19	16
7	56	44	37	31	51	41	34	29	34	29	25	28	24	21	21	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	16	18	15	13	11
10	45	34	26	22	41	31	25	20	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17038	17038	17038
5°	17117	16883	17001
10°	17004	16736	16840
15°	16805	16547	16577
20°	16573	16276	16292
25°	16262	15954	15922
30°	15918	15597	15478
35°	15559	15219	15023
40°	15185	14802	14573
45°	14772	14420	14067
50°	14359	13949	13561
55°	13818	13461	13052
60°	13272	12893	12482
65°	12791	12271	11889
70°	12079	11566	11050
75°	11038	10643	10189
80°	9955	9534	9447
85°	8744	8410	8065



TEST NUMBER: P332208

CATALOG NUMBER: S123DIW-S1000D1535U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	149.1	1.5
10°-20°	421.0	4.1
20°-30°	621.9	6.1
30°-40°	726.5	7.1
40°-50°	730.4	7.1
50°-60°	641.5	6.3
60°-70°	478.0	4.7
70°-80°	272.3	2.7
80°-90°	83.8	0.8
90°-100°	73.2	0.7
100°-110°	348.7	3.4
110°-120°	837.5	8.2
120°-130°	1066.5	10.4
130°-140°	1139.5	11.1
140°-150°	1065.6	10.4
150°-160°	859.5	8.4
160°-170°	554.7	5.4
170°-180°	191.2	1.9
0°-30°	1192.0	11.6
0°-40°	1918.5	18.7
0°-60°	3290.4	32.1
0°-90°	4124.4	40.2
90°-120°	1259.4	12.3
90°-150°	4531.0	44.2
90°-180°	6136.0	59.8
0°-180°	10260.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1583	1583	1583	1583	1583	
5°	1584	1577	1562	1575	1573	150
15°	1508	1502	1485	1495	1488	425
25°	1369	1360	1343	1344	1341	630
35°	1184	1175	1158	1150	1143	740
45°	970	964	947	932	924	749
55°	736	734	717	703	696	659
65°	502	495	482	471	467	495
75°	265	260	256	249	245	284
85°	71	68	68	65	65	78
90°	2	17	36	42	45	8
95°	91	34	46	56	57	113
105°	446	454	327	78	66	472
115°	836	845	858	873	879	825
125°	1178	1190	1196	1199	1202	1052
135°	1467	1475	1482	1486	1482	1129
145°	1692	1702	1706	1709	1709	1059
155°	1864	1862	1863	1869	1861	859
165°	1966	1962	1960	1971	1961	555
175°	2012	2005	2006	2016	2005	191
180°	2012	2012	2012	2012	2012	



TEST NUMBER: P332208

CATALOG NUMBER: S123DIW-S1000D1535U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1588.3	1587.4	1586.4	1585.4	1584.5	1582.6	1580.0	1577.3	1574.7	1572.0	1574.4
5°	1584.2	1582.7	1581.2	1579.7	1578.2	1575.8	1572.5	1569.1	1565.8	1562.5	1565.5
7.5°	1568.7	1567.2	1565.7	1564.2	1562.7	1560.2	1556.8	1553.3	1549.9	1546.4	1549.1
10°	1555.7	1554.2	1552.6	1551.1	1549.6	1546.9	1543.0	1539.0	1535.1	1531.2	1533.9
12.5°	1538.2	1537.0	1535.7	1534.4	1533.2	1530.7	1527.0	1523.3	1519.6	1515.9	1517.9
15°	1508.0	1506.8	1505.6	1504.4	1503.2	1500.6	1496.7	1492.8	1488.8	1484.9	1487.3
17.5°	1472.9	1471.3	1469.8	1468.2	1466.6	1463.9	1459.9	1456.0	1452.1	1448.1	1449.8
20°	1446.8	1445.0	1443.2	1441.3	1439.5	1436.6	1432.7	1428.8	1424.9	1420.9	1422.1
22.5°	1417.4	1415.6	1413.8	1411.9	1410.1	1407.3	1403.3	1399.4	1395.5	1391.5	1392.5
25°	1369.2	1367.4	1365.6	1363.8	1361.9	1359.1	1355.1	1351.2	1347.3	1343.3	1343.6
27.5°	1317.8	1316.0	1314.2	1312.5	1310.7	1307.7	1303.5	1299.3	1295.0	1290.8	1291.0
30°	1280.7	1279.2	1277.7	1276.2	1274.7	1271.8	1267.6	1263.3	1259.1	1254.9	1254.9
32.5°	1243.7	1241.7	1239.7	1237.7	1235.7	1233.1	1229.8	1226.6	1223.3	1220.0	1218.3
35°	1184.1	1182.3	1180.5	1178.7	1176.8	1174.0	1170.0	1166.1	1162.2	1158.2	1156.4
37.5°	1123.1	1120.8	1118.5	1116.2	1113.9	1110.8	1106.8	1102.8	1098.8	1094.8	1092.6
40°	1080.7	1078.8	1077.0	1075.2	1073.4	1070.4	1066.1	1061.9	1057.7	1053.4	1051.0
42.5°	1038.2	1036.1	1034.1	1032.0	1030.0	1026.8	1022.6	1018.4	1014.1	1009.9	1007.5
45°	970.4	969.2	968.0	966.8	965.6	963.0	959.1	955.1	951.2	947.3	943.7
47.5°	903.2	901.4	899.7	897.9	896.2	893.4	889.8	886.1	882.4	878.7	875.1
50°	857.5	855.9	854.4	852.9	851.4	848.7	844.7	840.8	836.9	833.0	829.6
52.5°	809.5	808.5	807.5	806.5	805.4	802.8	798.7	794.5	790.3	786.1	783.3
55°	736.3	736.0	735.7	735.4	735.1	733.0	729.1	725.1	721.2	717.3	713.9
57.5°	666.6	665.6	664.6	663.6	662.5	660.4	657.3	654.1	651.0	647.9	644.9
60°	616.5	616.2	615.9	615.6	615.3	613.4	609.7	606.1	602.5	598.9	596.1
62.5°	571.9	571.1	570.3	569.5	568.8	566.6	562.9	559.3	555.7	552.0	549.3
65°	502.2	500.7	499.2	497.7	496.2	493.9	490.9	487.9	484.8	481.8	479.4
67.5°	428.5	427.1	425.8	424.5	423.1	421.3	419.0	416.7	414.4	412.1	410.0
70°	383.8	382.0	380.2	378.4	376.6	374.7	372.9	371.1	369.3	367.5	365.4
72.5°	337.0	335.7	334.3	333.0	331.7	330.0	327.9	325.9	323.8	321.7	319.9
75°	265.4	264.2	263.0	261.8	260.6	259.5	258.6	257.7	256.8	255.9	254.4
77.5°	202.0	201.3	200.6	200.0	199.3	198.4	197.4	196.3	195.2	194.1	193.1
80°	160.6	159.7	158.8	157.9	157.0	156.2	155.6	155.0	154.4	153.8	153.5
82.5°	120.3	120.1	120.0	119.8	119.6	119.4	119.3	119.2	119.1	119.0	118.4
85°	70.8	70.2	69.6	69.0	68.4	68.1	68.1	68.1	68.1	68.1	67.4
87.5°	28.6	28.5	28.5	28.4	28.4	28.6	29.3	29.9	30.5	31.1	31.2
90°	1.5	4.8	8.1	11.5	14.8	18.6	22.9	27.2	31.6	35.9	37.2
92.5°	27.8	26.9	25.9	25.0	24.1	25.2	28.5	31.8	35.0	38.3	40.4
95°	91.2	77.6	64.0	50.3	36.7	31.7	35.4	39.0	42.7	46.3	48.7
97.5°	183.3	177.2	171.1	164.9	158.8	143.8	119.9	96.0	72.1	48.1	50.8
100°	252.7	259.3	265.9	272.6	279.2	256.6	204.8	153.0	101.2	49.3	52.0
102.5°	331.6	336.4	341.2	345.9	350.7	324.8	268.2	211.6	155.0	98.4	90.1
105°	445.5	449.2	452.8	456.5	460.1	447.0	417.1	387.2	357.3	327.4	268.6
107.5°	565.7	568.6	571.5	574.5	577.4	581.2	585.9	590.7	595.4	600.1	557.0
110°	645.8	648.5	651.1	653.8	656.5	659.6	663.3	666.9	670.6	674.2	663.3



TEST NUMBER: P332208

CATALOG NUMBER: S123DIW-S1000D1535U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	722.4	724.8	727.2	729.6	731.9	735.0	738.6	742.3	745.9	749.6	749.8
115°	835.7	837.7	839.7	841.7	843.7	846.2	849.2	852.1	855.1	858.1	861.4
117.5°	945.4	947.9	950.3	952.8	955.3	957.3	958.8	960.3	961.8	963.4	966.0
120°	1013.6	1016.6	1019.6	1022.6	1025.6	1027.6	1028.5	1029.5	1030.5	1031.5	1034.2
122.5°	1083.0	1085.4	1087.9	1090.3	1092.8	1094.7	1095.9	1097.2	1098.4	1099.7	1101.6
125°	1178.0	1180.7	1183.4	1186.0	1188.7	1190.7	1192.0	1193.3	1194.7	1196.0	1196.7
127.5°	1270.1	1272.8	1275.5	1278.1	1280.8	1282.9	1284.5	1286.1	1287.7	1289.3	1290.3
130°	1327.5	1330.2	1332.9	1335.5	1338.2	1340.2	1341.5	1342.8	1344.2	1345.5	1346.8
132.5°	1382.6	1385.2	1387.9	1390.5	1393.2	1395.1	1396.1	1397.2	1398.2	1399.3	1400.6
135°	1466.6	1468.6	1470.6	1472.6	1474.6	1476.2	1477.5	1478.9	1480.2	1481.5	1482.5
137.5°	1538.3	1540.9	1543.4	1545.9	1548.4	1550.1	1550.8	1551.5	1552.3	1553.0	1554.6
140°	1586.2	1588.2	1590.2	1592.2	1594.2	1595.6	1596.6	1597.6	1598.6	1599.6	1601.0
142.5°	1630.4	1632.4	1634.4	1636.4	1638.4	1639.9	1640.9	1641.9	1642.9	1643.9	1644.9
145°	1692.3	1694.6	1697.0	1699.3	1701.6	1703.1	1703.8	1704.4	1705.1	1705.8	1706.4
147.5°	1750.6	1752.2	1753.7	1755.2	1756.7	1757.8	1758.5	1759.2	1759.8	1760.5	1761.2
150°	1786.5	1787.5	1788.5	1789.5	1790.5	1791.3	1792.0	1792.7	1793.3	1794.0	1794.6
152.5°	1818.8	1819.3	1819.7	1820.2	1820.7	1821.1	1821.5	1821.9	1822.3	1822.7	1823.9
155°	1864.2	1863.6	1862.9	1862.3	1861.6	1861.4	1861.8	1862.1	1862.4	1862.7	1864.4
157.5°	1899.5	1899.5	1899.4	1899.3	1899.3	1899.1	1898.7	1898.4	1898.1	1897.7	1899.7
160°	1921.1	1920.7	1920.4	1920.1	1919.7	1919.4	1919.1	1918.7	1918.4	1918.1	1920.1
162.5°	1941.4	1940.5	1939.7	1938.8	1937.9	1937.3	1937.0	1936.7	1936.3	1936.0	1938.3
165°	1965.9	1964.9	1963.9	1962.9	1961.9	1961.3	1960.9	1960.6	1960.3	1959.9	1962.6
167.5°	1985.0	1983.7	1982.4	1981.1	1979.7	1979.1	1979.1	1979.1	1979.1	1979.1	1981.7
170°	1995.8	1994.5	1993.1	1991.8	1990.5	1989.8	1989.8	1989.8	1989.8	1989.8	1992.5
172.5°	2003.0	2001.4	1999.8	1998.2	1996.6	1995.9	1996.2	1996.5	1996.7	1997.0	1999.7
175°	2012.2	2010.6	2008.9	2007.3	2005.6	2004.9	2005.3	2005.6	2005.9	2006.3	2008.6
177.5°	2014.6	2013.3	2012.0	2010.7	2009.3	2008.8	2009.1	2009.3	2009.6	2009.9	2012.0
180°	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2



TEST NUMBER: P332208

CATALOG NUMBER: S123DIW-S1000D1535U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9	1582.9
2.5°	1576.8	1579.3	1581.7	1582.8	1582.5	1582.3	1582.0	1581.8
5°	1568.5	1571.5	1574.6	1575.8	1575.2	1574.6	1574.0	1573.4
7.5°	1551.9	1554.6	1557.3	1558.5	1558.1	1557.8	1557.4	1557.0
10°	1536.6	1539.3	1542.1	1543.1	1542.5	1541.9	1541.3	1540.7
12.5°	1519.9	1521.9	1523.9	1524.7	1524.4	1524.0	1523.6	1523.3
15°	1489.7	1492.1	1494.6	1494.9	1493.1	1491.2	1489.4	1487.6
17.5°	1451.5	1453.2	1454.9	1455.4	1454.8	1454.1	1453.4	1452.8
20°	1423.3	1424.6	1425.8	1425.9	1425.0	1424.1	1423.2	1422.3
22.5°	1393.5	1394.4	1395.4	1395.3	1394.2	1393.0	1391.9	1390.7
25°	1343.9	1344.3	1344.6	1344.3	1343.3	1342.4	1341.5	1340.6
27.5°	1291.3	1291.5	1291.8	1291.3	1290.2	1289.0	1287.9	1286.7
30°	1254.9	1254.9	1254.9	1253.8	1251.7	1249.6	1247.5	1245.3
32.5°	1216.6	1215.0	1213.3	1211.8	1210.7	1209.5	1208.4	1207.2
35°	1154.6	1152.8	1151.0	1149.3	1147.8	1146.3	1144.8	1143.3
37.5°	1090.5	1088.3	1086.1	1084.5	1083.6	1082.6	1081.6	1080.7
40°	1048.6	1046.2	1043.8	1041.9	1040.7	1039.5	1038.3	1037.1
42.5°	1005.0	1002.6	1000.2	998.4	997.2	996.0	994.8	993.6
45°	940.0	936.4	932.8	930.2	928.7	927.2	925.7	924.1
47.5°	871.5	868.0	864.4	862.0	860.6	859.3	858.0	856.6
50°	826.3	823.0	819.6	817.1	815.3	813.4	811.6	809.8
52.5°	780.4	777.6	774.8	772.4	770.6	768.8	767.0	765.2
55°	710.6	707.3	704.0	701.5	700.0	698.5	697.0	695.5
57.5°	641.9	639.0	636.0	633.6	631.9	630.1	628.4	626.6
60°	593.4	590.7	588.0	585.9	584.3	582.8	581.3	579.8
62.5°	546.6	543.9	541.1	539.3	538.2	537.2	536.2	535.2
65°	477.0	474.5	472.1	470.5	469.6	468.7	467.7	466.8
67.5°	407.9	405.8	403.7	402.0	400.7	399.4	398.1	396.9
70°	363.2	361.1	359.0	357.2	355.7	354.2	352.7	351.1
72.5°	318.0	316.1	314.2	312.9	312.1	311.3	310.6	309.8
75°	252.9	251.3	249.8	248.6	247.7	246.8	245.9	245.0
77.5°	192.0	191.0	190.0	189.5	189.5	189.5	189.5	189.5
80°	153.2	152.9	152.6	152.4	152.4	152.4	152.4	152.4
82.5°	117.9	117.3	116.8	116.4	116.1	115.9	115.7	115.4
85°	66.8	66.2	65.6	65.3	65.3	65.3	65.3	65.3
87.5°	31.2	31.2	31.2	31.3	31.4	31.6	31.7	31.8
90°	38.5	39.9	41.2	42.2	42.9	43.5	44.2	44.8
92.5°	42.5	44.7	46.8	48.0	48.4	48.8	49.2	49.6
95°	51.0	53.3	55.6	56.8	56.8	56.8	56.8	56.8
97.5°	53.5	56.1	58.8	60.3	60.6	60.9	61.3	61.6
100°	54.6	57.3	60.0	61.5	61.8	62.1	62.5	62.8
102.5°	81.9	73.7	65.4	61.6	62.2	62.8	63.4	64.0
105°	209.8	151.0	92.2	63.1	63.8	64.5	65.1	65.8
107.5°	513.8	470.7	427.6	383.9	339.6	295.2	250.9	206.6
110°	652.3	641.3	630.4	601.1	553.6	506.1	458.6	411.1





TEST NUMBER: P332208

CATALOG NUMBER: S123DIW-S1000D1535U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	750.0	750.2	750.4	745.5	735.4	725.4	715.4	705.3
115°	864.8	868.1	871.4	873.7	875.1	876.4	877.7	879.1
117.5°	968.7	971.3	974.0	975.5	975.7	976.0	976.3	976.5
120°	1036.9	1039.5	1042.2	1043.5	1043.5	1043.5	1043.5	1043.5
122.5°	1103.4	1105.3	1107.2	1108.2	1108.5	1108.7	1109.0	1109.3
125°	1197.3	1198.0	1198.6	1199.3	1200.0	1200.6	1201.3	1202.0
127.5°	1291.4	1292.5	1293.5	1293.7	1293.1	1292.4	1291.7	1291.1
130°	1348.1	1349.5	1350.8	1351.1	1350.5	1349.8	1349.1	1348.5
132.5°	1402.0	1403.3	1404.6	1404.8	1403.9	1403.0	1402.0	1401.1
135°	1483.5	1484.5	1485.5	1485.5	1484.5	1483.5	1482.5	1481.5
137.5°	1556.2	1557.8	1559.4	1559.8	1559.2	1558.5	1557.8	1557.2
140°	1602.3	1603.6	1604.9	1605.3	1604.6	1604.0	1603.3	1602.6
142.5°	1646.0	1647.1	1648.1	1648.2	1647.3	1646.3	1645.4	1644.5
145°	1707.1	1707.8	1708.4	1708.8	1708.8	1708.8	1708.8	1708.8
147.5°	1761.8	1762.5	1763.2	1762.7	1761.2	1759.7	1758.1	1756.6
150°	1795.3	1796.0	1796.6	1796.5	1795.5	1794.5	1793.5	1792.5
152.5°	1825.1	1826.3	1827.5	1827.3	1825.8	1824.2	1822.7	1821.2
155°	1866.1	1867.7	1869.4	1869.2	1867.2	1865.2	1863.2	1861.3
157.5°	1901.7	1903.7	1905.7	1905.4	1902.8	1900.2	1897.6	1895.0
160°	1922.1	1924.0	1926.0	1925.9	1923.5	1921.2	1918.9	1916.6
162.5°	1940.5	1942.8	1945.0	1945.1	1943.1	1941.0	1939.0	1936.9
165°	1965.2	1967.9	1970.6	1970.7	1968.4	1966.1	1963.7	1961.4
167.5°	1984.4	1987.0	1989.7	1989.7	1987.0	1984.4	1981.7	1979.1
170°	1995.1	1997.8	2000.5	2000.5	1997.8	1995.1	1992.5	1989.8
172.5°	2002.3	2005.0	2007.6	2007.5	2004.6	2001.7	1998.7	1995.8
175°	2010.9	2013.2	2015.6	2015.4	2012.7	2010.1	2007.4	2004.8
177.5°	2014.1	2016.2	2018.4	2018.1	2015.4	2012.8	2010.1	2007.5
180°	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2

(END OF REPORT)