

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332186

Luminaire Tested: **S123DIW-S1000D755U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332186
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D755U835-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7262.4 lumens
Efficiency: N/A
Efficacy: 135.5 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332186
CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58
1	100	96	92	88	93	89	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	68	64	61	59	56	54	50	48	46	42
3	83	74	67	61	78	69	63	58	61	56	52	53	49	46	45	42	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	40	37	35	31
5	70	59	51	45	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15118	15118	15118	15118
5°	18029	15183	13456	15183
10°	22566	15106	12153	15106
15°	27679	14985	11314	14985
20°	32972	14795	10772	14795
25°	35011	14563	10652	14563
30°	30009	14395	10708	14395
35°	20871	14155	10820	14155
40°	15719	13874	10786	13874
45°	13052	13457	10648	13457
50°	11692	12603	10551	12603
55°	10931	11684	10421	11684
60°	10254	10723	10314	10723
65°	9638	9775	9984	9775
70°	9039	8696	9508	8696
75°	8093	7615	8717	7615
80°	7085	6242	7507	6242
85°	5545	4533	5039	4533



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.4	1.9
10°-20°	443.6	6.1
20°-30°	744.6	10.3
30°-40°	843.1	11.6
40°-50°	756.1	10.4
50°-60°	610.1	8.4
60°-70°	425.2	5.9
70°-80°	223.5	3.1
80°-90°	57.4	0.8
90°-100°	36.0	0.5
100°-110°	171.6	2.4
110°-120°	412.3	5.7
120°-130°	525.0	7.2
130°-140°	560.9	7.7
140°-150°	524.5	7.2
150°-160°	423.1	5.8
160°-170°	273.1	3.8
170°-180°	94.1	1.3
0°-30°	1326.6	18.3
0°-40°	2169.7	29.9
0°-60°	3535.9	48.7
0°-90°	4241.9	58.4
90°-120°	619.9	8.5
90°-150°	2230.2	30.7
90°-180°	3020.0	41.6
0°-180°	7262.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1404	1404	1404	1404	1404	
5°	1669	1405	1245	1405	1669	173
15°	2484	1345	1015	1345	2484	717
25°	2948	1226	897	1226	2948	1293
35°	1588	1077	823	1077	1588	1032
45°	857	884	700	884	857	678
55°	582	623	555	623	582	523
65°	378	384	392	384	378	377
75°	195	183	210	183	195	208
85°	45	37	41	37	45	54
90°	22	1	22	1	22	12
95°	28	45	28	45	28	23
105°	32	219	32	219	32	74
115°	433	411	433	411	433	400
125°	592	580	592	580	592	528
135°	729	722	729	722	729	562
145°	841	833	841	833	841	525
155°	916	918	916	918	916	422
165°	965	968	965	968	965	273
175°	987	990	987	990	987	94
180°	990	990	990	990	990	



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1490.5	1489.5	1486.7	1488.9	1484.6	1478.6	1478.0	1472.6	1456.8	1455.7	1451.4
5°	1668.6	1663.1	1662.4	1661.8	1652.2	1639.3	1614.8	1612.8	1580.1	1563.8	1544.0
7.5°	1899.1	1902.0	1892.0	1883.3	1854.2	1835.0	1808.7	1775.1	1735.0	1694.3	1667.2
10°	2064.6	2087.1	2059.2	2040.1	2022.4	1989.1	1950.3	1902.0	1853.7	1797.2	1754.3
12.5°	2242.1	2253.1	2247.5	2229.6	2202.1	2151.3	2082.6	2029.4	1984.9	1890.8	1852.8
15°	2483.8	2525.3	2498.8	2437.5	2438.9	2390.6	2300.7	2202.1	2149.7	2067.3	1955.1
17.5°	2741.3	2746.5	2735.2	2684.1	2650.1	2583.7	2500.8	2406.2	2300.1	2200.4	2081.4
20°	2878.5	2874.4	2850.6	2824.0	2765.5	2713.8	2623.3	2517.8	2381.7	2283.7	2153.8
22.5°	2954.7	2947.9	2936.6	2914.4	2865.7	2810.2	2728.9	2613.6	2484.1	2349.1	2198.9
25°	2947.9	2956.7	2958.1	2952.0	2935.0	2901.6	2837.6	2745.8	2616.5	2443.0	2286.5
27.5°	2681.1	2693.7	2730.0	2762.3	2798.3	2835.1	2830.2	2784.6	2688.9	2539.0	2347.7
30°	2414.4	2387.2	2454.5	2539.6	2597.4	2699.5	2756.7	2760.1	2706.3	2577.7	2391.2
32.5°	2044.2	2074.1	2103.9	2208.6	2335.0	2449.6	2563.4	2655.0	2665.5	2579.9	2416.8
35°	1588.3	1625.7	1680.1	1734.6	1870.7	1987.7	2187.8	2362.0	2500.8	2519.2	2419.1
37.5°	1279.9	1298.4	1332.8	1387.4	1476.4	1615.2	1770.0	1990.2	2191.3	2340.9	2347.4
40°	1118.7	1124.2	1163.0	1204.5	1276.6	1390.9	1530.4	1725.0	1965.9	2174.9	2262.0
42.5°	997.9	1009.8	1026.3	1066.2	1123.6	1209.6	1339.3	1500.2	1721.0	1961.4	2131.8
45°	857.4	871.0	881.2	907.8	948.6	1006.4	1097.0	1243.9	1412.0	1660.4	1889.7
47.5°	764.6	765.7	773.3	793.3	821.1	864.5	928.5	1022.9	1177.2	1378.7	1614.1
50°	698.2	709.1	711.8	727.4	749.2	781.2	834.3	914.6	1041.2	1218.1	1434.5
52.5°	651.4	654.6	662.3	673.6	692.6	717.5	763.5	826.4	925.7	1076.5	1275.5
55°	582.5	582.5	590.0	598.8	609.7	632.2	662.8	709.1	784.6	901.7	1066.3
57.5°	518.8	522.2	527.5	530.2	539.5	554.3	579.9	615.0	671.4	761.5	892.4
60°	476.3	482.5	481.8	487.2	495.4	507.0	528.7	557.3	607.7	679.8	790.1
62.5°	439.3	438.9	438.8	445.3	453.5	464.5	478.7	503.4	546.2	610.1	704.0
65°	378.4	377.0	381.8	385.8	388.6	396.7	407.6	429.4	458.0	505.6	578.4
67.5°	324.2	320.2	322.8	324.2	328.8	335.2	345.4	358.9	381.6	419.9	474.7
70°	287.2	283.8	283.1	284.4	288.5	293.3	300.8	313.7	334.8	365.4	405.6
72.5°	249.1	246.7	246.6	249.6	251.5	254.6	259.9	271.8	288.5	311.5	349.0
75°	194.6	194.6	194.6	195.3	197.3	200.1	204.1	210.3	223.2	239.5	264.7
77.5°	145.9	145.8	144.9	144.8	147.8	149.0	150.0	155.7	162.9	173.9	192.3
80°	114.3	110.9	112.3	114.3	115.7	116.4	118.4	119.8	125.9	132.0	144.9
82.5°	84.9	82.1	82.3	85.5	85.7	86.4	88.5	90.4	92.7	98.3	105.2
85°	44.9	44.9	45.6	45.6	46.3	45.6	47.6	48.3	48.3	51.7	55.8
87.5°	20.7	19.6	20.1	20.6	19.9	20.4	20.8	21.2	21.6	22.0	22.2
90°	22.1	21.7	21.4	21.1	20.8	20.3	19.6	19.0	18.3	17.7	15.5
92.5°	24.4	24.2	24.0	23.8	23.6	23.0	22.0	20.9	19.9	18.8	17.2
95°	28.0	28.0	28.0	28.0	28.0	27.4	26.2	25.1	24.0	22.8	21.0
97.5°	30.3	30.2	30.0	29.8	29.7	28.9	27.6	26.3	25.0	23.7	35.5
100°	30.9	30.7	30.6	30.4	30.3	29.5	28.2	26.9	25.6	24.3	49.8
102.5°	31.5	31.2	30.9	30.6	30.3	32.2	36.3	40.3	44.4	48.4	76.3
105°	32.4	32.1	31.7	31.4	31.1	45.4	74.3	103.3	132.2	161.2	175.9
107.5°	101.7	123.5	145.3	167.1	189.0	210.5	231.7	252.9	274.1	295.4	293.1
110°	202.4	225.7	249.1	272.5	295.9	310.3	315.7	321.1	326.5	331.9	330.1



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	347.2	352.1	357.1	362.0	366.9	369.4	369.3	369.2	369.1	369.0	367.2
115°	432.7	432.0	431.4	430.7	430.1	428.9	427.3	425.7	424.0	422.4	420.9
117.5°	480.7	480.5	480.4	480.3	480.1	479.4	478.1	476.8	475.5	474.2	473.4
120°	513.6	513.6	513.6	513.6	513.6	513.0	511.7	510.4	509.1	507.7	507.3
122.5°	546.0	545.9	545.7	545.6	545.5	545.0	544.0	543.1	542.2	541.3	540.7
125°	591.6	591.3	591.0	590.7	590.3	590.0	589.7	589.3	589.0	588.7	588.0
127.5°	635.5	635.8	636.1	636.5	636.8	636.7	636.2	635.7	635.1	634.6	633.8
130°	663.7	664.1	664.4	664.7	665.1	664.9	664.2	663.6	662.9	662.3	661.6
132.5°	689.6	690.1	690.6	691.0	691.5	691.4	690.7	690.1	689.4	688.8	688.2
135°	729.2	729.7	730.2	730.7	731.2	731.2	730.7	730.2	729.7	729.2	728.6
137.5°	766.5	766.8	767.1	767.5	767.8	767.6	766.8	766.0	765.2	764.4	764.1
140°	788.8	789.2	789.5	789.8	790.2	790.0	789.3	788.7	788.0	787.4	786.9
142.5°	809.4	809.9	810.4	810.8	811.3	811.2	810.7	810.2	809.7	809.2	808.7
145°	841.1	841.1	841.1	841.1	841.1	840.9	840.6	840.3	839.9	839.6	839.3
147.5°	864.6	865.4	866.1	866.9	867.6	867.9	867.5	867.2	866.9	866.5	866.2
150°	882.3	882.8	883.3	883.8	884.3	884.3	884.0	883.7	883.4	883.0	882.7
152.5°	896.4	897.2	897.9	898.7	899.4	899.5	898.9	898.3	897.7	897.2	897.0
155°	916.1	917.1	918.1	919.1	920.1	920.2	919.3	918.5	917.7	916.9	916.7
157.5°	932.8	934.1	935.3	936.6	937.9	938.0	937.0	936.1	935.1	934.1	934.3
160°	943.4	944.5	945.7	946.8	948.0	948.0	947.1	946.1	945.1	944.1	944.3
162.5°	953.4	954.4	955.4	956.4	957.4	957.4	956.3	955.2	954.1	952.9	953.1
165°	965.4	966.6	967.7	968.9	970.0	969.9	968.6	967.3	966.0	964.7	964.9
167.5°	974.1	975.4	976.7	978.1	979.4	979.4	978.1	976.7	975.4	974.1	974.1
170°	979.4	980.7	982.0	983.4	984.7	984.7	983.4	982.0	980.7	979.4	979.4
172.5°	982.4	983.8	985.3	986.7	988.1	988.2	986.9	985.6	984.3	983.0	982.8
175°	986.8	988.1	989.4	990.7	992.0	992.1	991.0	989.8	988.7	987.5	987.4
177.5°	988.1	989.4	990.7	992.0	993.3	993.5	992.4	991.4	990.3	989.3	989.2
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1448.1	1443.7	1439.4	1431.8	1425.2	1416.0	1413.2	1410.0	1400.2	1391.5	1384.9
5°	1536.5	1520.2	1496.4	1474.6	1456.9	1433.1	1419.5	1405.2	1384.8	1366.4	1351.5
7.5°	1629.1	1597.0	1560.0	1519.9	1482.7	1446.7	1417.7	1391.9	1363.3	1336.2	1315.1
10°	1702.6	1656.3	1604.6	1548.8	1501.2	1454.9	1416.1	1382.1	1345.3	1313.3	1286.8
12.5°	1786.4	1717.8	1646.5	1578.7	1522.4	1458.2	1411.2	1367.9	1326.3	1287.8	1258.0
15°	1885.6	1798.5	1714.2	1620.9	1535.2	1454.9	1399.1	1344.7	1296.3	1256.9	1218.8
17.5°	1976.0	1877.3	1766.1	1652.8	1549.3	1454.1	1376.0	1314.4	1254.0	1205.7	1167.7
20°	2027.2	1914.9	1789.0	1671.3	1557.0	1450.8	1365.1	1291.6	1226.2	1175.2	1132.3
22.5°	2071.3	1939.9	1809.7	1683.8	1556.4	1442.1	1344.9	1269.3	1198.5	1148.5	1102.9
25°	2117.0	1959.8	1829.2	1681.5	1539.3	1420.9	1312.0	1226.2	1155.5	1097.0	1050.0
27.5°	2156.2	1958.5	1803.4	1644.6	1512.3	1393.6	1277.4	1185.4	1110.3	1046.7	999.1
30°	2182.3	1961.2	1776.8	1619.6	1486.2	1363.7	1250.7	1158.2	1079.3	1014.6	969.7
32.5°	2198.7	1959.5	1752.3	1584.7	1444.8	1336.5	1221.9	1126.1	1045.0	981.4	938.1
35°	2208.2	1947.6	1710.1	1512.7	1378.0	1272.5	1176.6	1077.2	992.2	933.0	884.0
37.5°	2189.1	1922.4	1661.1	1443.3	1295.8	1191.9	1111.2	1026.6	945.2	880.0	837.8
40°	2159.2	1906.1	1623.0	1394.3	1239.2	1139.1	1070.4	987.4	907.1	845.2	805.7
42.5°	2102.0	1872.8	1581.1	1339.9	1180.4	1080.3	1017.1	947.7	871.7	813.6	774.1
45°	1962.5	1800.6	1518.2	1258.2	1093.5	990.1	934.3	884.0	815.2	758.7	724.7
47.5°	1769.0	1691.8	1427.3	1172.1	1002.9	903.4	845.4	804.9	754.7	709.1	676.4
50°	1634.5	1602.6	1365.7	1113.3	942.5	845.2	789.4	752.6	716.6	671.0	641.0
52.5°	1479.4	1499.1	1293.9	1052.3	881.0	785.3	732.8	703.6	670.8	633.4	607.3
55°	1261.0	1332.4	1169.8	950.0	789.4	698.2	648.5	622.6	603.6	575.7	553.2
57.5°	1056.4	1147.3	1035.6	844.5	699.4	620.7	573.1	544.9	532.7	518.1	500.4
60°	935.0	1024.8	939.8	773.7	639.0	564.1	521.9	498.1	485.9	475.7	460.7
62.5°	826.7	917.6	846.1	701.9	579.6	510.2	473.5	450.2	440.7	435.4	422.6
65°	677.8	756.0	708.4	590.0	494.7	433.5	400.1	383.8	375.0	372.9	364.7
67.5°	551.6	611.2	576.5	489.4	414.4	361.5	333.2	319.3	312.5	311.8	305.7
70°	468.9	524.7	498.1	419.2	354.5	313.0	288.5	276.3	272.2	271.5	268.1
72.5°	404.6	443.5	422.4	356.6	306.6	268.9	251.0	238.2	233.5	234.5	232.2
75°	299.4	328.7	316.4	270.8	230.7	206.2	191.2	183.1	179.0	181.0	178.3
77.5°	215.4	234.0	222.9	191.4	166.6	148.9	137.9	132.8	129.2	129.0	127.8
80°	162.6	173.5	167.4	148.3	127.9	113.0	104.1	100.7	98.7	98.0	97.3
82.5°	115.8	125.1	117.9	104.8	90.9	81.9	76.9	72.4	70.9	71.3	70.6
85°	58.5	61.9	59.2	51.0	45.6	41.5	38.8	36.7	35.4	36.1	34.7
87.5°	22.8	22.9	20.9	18.3	16.9	15.0	14.6	13.2	12.5	12.8	12.6
90°	13.4	11.3	9.2	7.3	5.6	4.0	2.4	0.7	2.4	4.0	5.6
92.5°	15.6	14.0	12.4	11.9	12.3	12.8	13.2	13.7	13.2	12.8	12.3
95°	19.2	17.4	15.6	18.1	24.8	31.5	38.2	44.9	38.2	31.5	24.8
97.5°	47.2	59.0	70.8	78.2	81.2	84.2	87.2	90.2	87.2	84.2	81.2
100°	75.3	100.8	126.3	137.4	134.2	130.9	127.6	124.4	127.6	130.9	134.2
102.5°	104.1	132.0	159.9	172.6	170.3	167.9	165.6	163.2	165.6	167.9	170.3
105°	190.6	205.3	220.0	226.5	224.7	222.9	221.1	219.3	221.1	222.9	224.7
107.5°	290.7	288.4	286.1	284.2	282.8	281.3	279.9	278.4	279.9	281.3	282.8
110°	328.3	326.5	324.7	323.1	321.8	320.5	319.2	317.9	319.2	320.5	321.8



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	365.4	363.6	361.8	360.3	359.1	357.9	356.7	355.6	356.7	357.9	359.1
115°	419.4	418.0	416.5	415.3	414.3	413.3	412.3	411.3	412.3	413.3	414.3
117.5°	472.7	471.9	471.2	470.2	469.0	467.8	466.6	465.4	466.6	467.8	469.0
120°	506.8	506.3	505.8	504.8	503.3	501.9	500.4	498.9	500.4	501.9	503.3
122.5°	540.1	539.4	538.8	537.9	536.7	535.5	534.3	533.1	534.3	535.5	536.7
125°	587.4	586.7	586.1	585.1	583.8	582.5	581.2	579.9	581.2	582.5	583.8
127.5°	633.0	632.3	631.5	630.4	629.1	627.8	626.5	625.2	626.5	627.8	629.1
130°	661.0	660.3	659.7	658.7	657.4	656.1	654.8	653.4	654.8	656.1	657.4
132.5°	687.7	687.2	686.7	685.8	684.4	683.1	681.8	680.5	681.8	683.1	684.4
135°	727.9	727.3	726.6	725.8	724.8	723.8	722.9	721.9	722.9	723.8	724.8
137.5°	763.7	763.3	763.0	762.2	760.9	759.7	758.4	757.2	758.4	759.7	760.9
140°	786.4	785.9	785.4	784.7	783.7	782.7	781.7	780.7	781.7	782.7	783.7
142.5°	808.2	807.7	807.2	806.5	805.5	804.5	803.5	802.5	803.5	804.5	805.5
145°	839.0	838.6	838.3	837.6	836.4	835.3	834.1	833.0	834.1	835.3	836.4
147.5°	865.9	865.6	865.2	864.7	863.9	863.2	862.4	861.7	862.4	863.2	863.9
150°	882.4	882.1	881.7	881.3	880.8	880.3	879.8	879.4	879.8	880.3	880.8
152.5°	896.8	896.6	896.4	896.2	895.9	895.7	895.5	895.2	895.5	895.7	895.9
155°	916.6	916.4	916.2	916.3	916.6	917.0	917.3	917.6	917.3	917.0	916.6
157.5°	934.4	934.6	934.8	934.9	934.9	934.9	935.0	935.0	935.0	934.9	934.9
160°	944.4	944.6	944.8	944.9	945.1	945.3	945.4	945.6	945.4	945.3	945.1
162.5°	953.3	953.4	953.6	953.9	954.3	954.7	955.2	955.6	955.2	954.7	954.3
165°	965.0	965.2	965.4	965.7	966.2	966.7	967.2	967.7	967.2	966.7	966.2
167.5°	974.1	974.1	974.1	974.5	975.1	975.8	976.4	977.1	976.4	975.8	975.1
170°	979.4	979.4	979.4	979.8	980.4	981.1	981.7	982.4	981.7	981.1	980.4
172.5°	982.7	982.6	982.4	982.8	983.6	984.3	985.1	985.9	985.1	984.3	983.6
175°	987.2	987.0	986.9	987.2	988.0	988.8	989.6	990.5	989.6	988.8	988.0
177.5°	989.0	988.9	988.8	989.0	989.7	990.3	991.0	991.6	991.0	990.3	989.7
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1381.1	1377.3	1371.9	1363.7	1357.2	1346.8	1346.8	1348.5	1348.5	1347.9	1346.8
5°	1339.2	1329.0	1316.8	1302.5	1287.5	1272.5	1269.8	1264.4	1260.3	1257.5	1254.1
7.5°	1295.0	1276.9	1259.0	1239.0	1220.8	1205.7	1195.2	1186.5	1180.9	1174.9	1170.6
10°	1265.0	1242.6	1221.5	1200.4	1177.2	1158.9	1147.3	1139.1	1133.0	1127.6	1124.9
12.5°	1229.6	1203.9	1180.7	1160.6	1135.3	1116.4	1105.4	1101.6	1094.4	1082.9	1076.9
15°	1177.9	1154.1	1126.2	1095.6	1083.3	1060.2	1047.3	1041.2	1037.1	1028.2	1025.5
17.5°	1133.7	1102.5	1071.2	1048.4	1025.6	1006.9	999.6	992.0	986.6	979.4	977.2
20°	1098.3	1070.4	1041.8	1017.3	993.5	973.1	967.0	961.5	956.1	952.7	950.0
22.5°	1062.4	1034.5	1010.8	987.9	962.5	949.1	942.5	936.5	932.7	930.4	927.6
25°	1011.9	987.4	960.9	940.4	920.0	911.2	907.1	903.7	901.0	897.6	896.9
27.5°	966.7	940.0	918.5	899.5	884.8	877.4	873.5	871.8	872.4	873.6	874.4
30°	933.0	908.5	890.8	874.4	860.8	854.0	853.3	853.3	856.1	856.7	858.1
32.5°	901.9	881.8	864.1	848.3	838.0	833.3	835.9	835.9	838.1	839.9	842.3
35°	856.7	839.0	825.4	811.8	803.0	805.0	806.4	807.7	811.1	815.2	818.0
37.5°	813.6	798.2	784.1	773.4	769.4	773.0	776.3	779.2	783.1	786.2	789.0
40°	782.6	771.0	757.4	747.9	749.2	751.3	754.0	757.4	760.8	762.8	765.6
42.5°	753.7	741.6	731.3	723.4	725.3	727.9	729.5	731.3	735.2	738.9	740.5
45°	709.8	700.2	690.7	685.9	687.3	688.7	690.0	692.1	695.5	698.2	698.9
47.5°	660.3	653.7	647.3	642.7	644.8	644.3	646.1	650.4	651.5	653.1	656.9
50°	628.8	622.6	615.2	613.8	613.8	613.8	614.5	619.9	619.9	622.6	625.4
52.5°	593.9	590.0	585.2	582.8	581.7	581.7	584.5	587.3	588.4	592.2	594.9
55°	542.4	538.3	534.2	532.1	530.8	532.1	537.6	538.9	542.4	544.4	546.4
57.5°	488.6	485.5	482.2	481.1	480.8	482.6	485.6	489.7	490.5	496.8	499.9
60°	453.2	448.4	445.7	445.7	444.4	450.5	449.1	455.9	457.3	461.4	466.1
62.5°	416.7	410.3	409.2	409.2	411.2	412.9	414.8	417.8	421.4	426.5	430.2
65°	357.9	354.5	359.3	358.6	357.3	361.3	361.3	364.7	368.8	373.6	381.1
67.5°	302.3	300.5	300.9	300.9	303.0	305.3	307.2	310.2	315.1	320.1	325.0
70°	264.7	266.8	263.4	266.1	268.1	268.8	270.2	274.2	279.7	283.1	288.5
72.5°	228.2	228.1	228.5	229.6	231.6	232.9	234.2	238.9	244.8	247.7	252.1
75°	175.6	174.9	176.9	176.9	180.3	181.7	183.1	185.1	190.5	194.6	198.0
77.5°	128.2	129.0	128.6	130.9	130.0	130.2	134.5	136.5	137.1	145.1	146.9
80°	96.6	98.0	98.7	99.4	100.0	98.7	103.4	105.5	105.5	110.2	113.6
82.5°	69.4	70.2	72.0	72.7	72.8	74.2	74.6	76.1	77.7	79.8	84.2
85°	34.7	36.7	37.4	36.7	37.4	36.1	38.1	38.8	39.5	39.5	39.5
87.5°	12.3	13.3	13.1	14.1	14.0	15.0	15.1	14.1	14.3	16.0	14.0
90°	7.3	9.2	11.3	13.4	15.5	17.7	18.3	19.0	19.6	20.3	20.8
92.5°	11.9	12.4	14.0	15.6	17.2	18.8	19.9	20.9	22.0	23.0	23.6
95°	18.1	15.6	17.4	19.2	21.0	22.8	24.0	25.1	26.2	27.4	28.0
97.5°	78.2	70.8	59.0	47.2	35.5	23.7	25.0	26.3	27.6	28.9	29.7
100°	137.4	126.3	100.8	75.3	49.8	24.3	25.6	26.9	28.2	29.5	30.3
102.5°	172.6	159.9	132.0	104.1	76.3	48.4	44.4	40.3	36.3	32.2	30.3
105°	226.5	220.0	205.3	190.6	175.9	161.2	132.2	103.3	74.3	45.4	31.1
107.5°	284.2	286.1	288.4	290.7	293.1	295.4	274.1	252.9	231.7	210.5	189.0
110°	323.1	324.7	326.5	328.3	330.1	331.9	326.5	321.1	315.7	310.3	295.9



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	360.3	361.8	363.6	365.4	367.2	369.0	369.1	369.2	369.3	369.4	366.9
115°	415.3	416.5	418.0	419.4	420.9	422.4	424.0	425.7	427.3	428.9	430.1
117.5°	470.2	471.2	471.9	472.7	473.4	474.2	475.5	476.8	478.1	479.4	480.1
120°	504.8	505.8	506.3	506.8	507.3	507.7	509.1	510.4	511.7	513.0	513.6
122.5°	537.9	538.8	539.4	540.1	540.7	541.3	542.2	543.1	544.0	545.0	545.5
125°	585.1	586.1	586.7	587.4	588.0	588.7	589.0	589.3	589.7	590.0	590.3
127.5°	630.4	631.5	632.3	633.0	633.8	634.6	635.1	635.7	636.2	636.7	636.8
130°	658.7	659.7	660.3	661.0	661.6	662.3	662.9	663.6	664.2	664.9	665.1
132.5°	685.8	686.7	687.2	687.7	688.2	688.8	689.4	690.1	690.7	691.4	691.5
135°	725.8	726.6	727.3	727.9	728.6	729.2	729.7	730.2	730.7	731.2	731.2
137.5°	762.2	763.0	763.3	763.7	764.1	764.4	765.2	766.0	766.8	767.6	767.8
140°	784.7	785.4	785.9	786.4	786.9	787.4	788.0	788.7	789.3	790.0	790.2
142.5°	806.5	807.2	807.7	808.2	808.7	809.2	809.7	810.2	810.7	811.2	811.3
145°	837.6	838.3	838.6	839.0	839.3	839.6	839.9	840.3	840.6	840.9	841.1
147.5°	864.7	865.2	865.6	865.9	866.2	866.5	866.9	867.2	867.5	867.9	867.6
150°	881.3	881.7	882.1	882.4	882.7	883.0	883.4	883.7	884.0	884.3	884.3
152.5°	896.2	896.4	896.6	896.8	897.0	897.2	897.7	898.3	898.9	899.5	899.4
155°	916.3	916.2	916.4	916.6	916.7	916.9	917.7	918.5	919.3	920.2	920.1
157.5°	934.9	934.8	934.6	934.4	934.3	934.1	935.1	936.1	937.0	938.0	937.9
160°	944.9	944.8	944.6	944.4	944.3	944.1	945.1	946.1	947.1	948.0	948.0
162.5°	953.9	953.6	953.4	953.3	953.1	952.9	954.1	955.2	956.3	957.4	957.4
165°	965.7	965.4	965.2	965.0	964.9	964.7	966.0	967.3	968.6	969.9	970.0
167.5°	974.5	974.1	974.1	974.1	974.1	974.1	975.4	976.7	978.1	979.4	979.4
170°	979.8	979.4	979.4	979.4	979.4	979.4	980.7	982.0	983.4	984.7	984.7
172.5°	982.8	982.4	982.6	982.7	982.8	983.0	984.3	985.6	986.9	988.2	988.1
175°	987.2	986.9	987.0	987.2	987.4	987.5	988.7	989.8	991.0	992.1	992.0
177.5°	989.0	988.8	988.9	989.0	989.2	989.3	990.3	991.4	992.4	993.5	993.3
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1343.0	1342.5	1346.3	1343.6	1346.3	1342.5	1343.0	1346.8	1347.9	1348.5	1348.5
5°	1250.1	1252.1	1245.3	1245.3	1245.3	1252.1	1250.1	1254.1	1257.5	1260.3	1264.4
7.5°	1167.3	1164.3	1164.6	1160.9	1164.6	1164.3	1167.3	1170.6	1174.9	1180.9	1186.5
10°	1116.7	1112.6	1111.2	1111.9	1111.2	1112.6	1116.7	1124.9	1127.6	1133.0	1139.1
12.5°	1074.8	1074.0	1065.0	1065.1	1065.0	1074.0	1074.8	1076.9	1082.9	1094.4	1101.6
15°	1025.5	1012.6	1011.2	1015.3	1011.2	1012.6	1025.5	1025.5	1028.2	1037.1	1041.2
17.5°	976.1	969.3	969.7	967.7	969.7	969.3	976.1	977.2	979.4	986.6	992.0
20°	950.0	945.9	945.2	940.4	945.2	945.9	950.0	950.0	952.7	956.1	961.5
22.5°	926.0	924.7	925.1	919.8	925.1	924.7	926.0	927.6	930.4	932.7	936.5
25°	896.2	899.6	896.9	896.9	896.9	899.6	896.2	896.9	897.6	901.0	903.7
27.5°	876.1	875.9	874.6	874.6	874.6	875.9	876.1	874.4	873.6	872.4	871.8
30°	860.8	860.1	861.5	861.5	861.5	860.1	860.8	858.1	856.7	856.1	853.3
32.5°	845.6	846.5	846.8	847.3	846.8	846.5	845.6	842.3	839.9	838.1	835.9
35°	822.0	822.7	824.8	823.4	824.8	822.7	822.0	818.0	815.2	811.1	807.7
37.5°	790.2	793.3	792.6	793.7	792.6	793.3	790.2	789.0	786.2	783.1	779.2
40°	766.2	768.3	767.6	767.6	767.6	768.3	766.2	765.6	762.8	760.8	757.4
42.5°	741.7	743.2	741.5	740.4	741.5	743.2	741.7	740.5	738.9	735.2	731.3
45°	701.6	700.2	702.3	699.5	702.3	700.2	701.6	698.9	698.2	695.5	692.1
47.5°	656.7	658.0	658.6	660.6	658.6	658.0	656.7	656.9	653.1	651.5	650.4
50°	626.7	630.8	630.8	630.1	630.8	630.8	626.7	625.4	622.6	619.9	619.9
52.5°	597.3	599.2	602.0	601.8	602.0	599.2	597.3	594.9	592.2	588.4	587.3
55°	551.9	553.2	554.6	555.3	554.6	553.2	551.9	546.4	544.4	542.4	538.9
57.5°	504.8	504.2	507.5	508.5	507.5	504.2	504.8	499.9	496.8	490.5	489.7
60°	471.6	471.6	477.0	479.1	477.0	471.6	471.6	466.1	461.4	457.3	455.9
62.5°	436.2	438.4	443.8	441.0	443.8	438.4	436.2	430.2	426.5	421.4	417.8
65°	384.5	389.9	389.2	392.0	389.2	389.9	384.5	381.1	373.6	368.8	364.7
67.5°	330.4	333.8	338.7	339.2	338.7	333.8	330.4	325.0	320.1	315.1	310.2
70°	294.0	297.4	300.1	302.1	300.1	297.4	294.0	288.5	283.1	279.7	274.2
72.5°	258.6	260.4	266.9	264.0	266.9	260.4	258.6	252.1	247.7	244.8	238.9
75°	202.8	207.5	211.6	209.6	211.6	207.5	202.8	198.0	194.6	190.5	185.1
77.5°	150.0	154.7	156.6	154.9	156.6	154.7	150.0	146.9	145.1	137.1	136.5
80°	118.4	117.7	121.8	121.1	121.8	117.7	118.4	113.6	110.2	105.5	105.5
82.5°	86.8	86.2	88.1	88.5	88.1	86.2	86.8	84.2	79.8	77.7	76.1
85°	42.2	44.2	41.5	40.8	41.5	44.2	42.2	39.5	39.5	39.5	38.8
87.5°	14.0	14.1	13.6	13.1	13.6	14.1	14.0	14.0	16.0	14.3	14.1
90°	21.1	21.4	21.7	22.1	21.7	21.4	21.1	20.8	20.3	19.6	19.0
92.5°	23.8	24.0	24.2	24.4	24.2	24.0	23.8	23.6	23.0	22.0	20.9
95°	28.0	28.0	28.0	28.0	28.0	28.0	28.0	28.0	27.4	26.2	25.1
97.5°	29.8	30.0	30.2	30.3	30.2	30.0	29.8	29.7	28.9	27.6	26.3
100°	30.4	30.6	30.7	30.9	30.7	30.6	30.4	30.3	29.5	28.2	26.9
102.5°	30.6	30.9	31.2	31.5	31.2	30.9	30.6	30.3	32.2	36.3	40.3
105°	31.4	31.7	32.1	32.4	32.1	31.7	31.4	31.1	45.4	74.3	103.3
107.5°	167.1	145.3	123.5	101.7	123.5	145.3	167.1	189.0	210.5	231.7	252.9
110°	272.5	249.1	225.7	202.4	225.7	249.1	272.5	295.9	310.3	315.7	321.1



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	362.0	357.1	352.1	347.2	352.1	357.1	362.0	366.9	369.4	369.3	369.2
115°	430.7	431.4	432.0	432.7	432.0	431.4	430.7	430.1	428.9	427.3	425.7
117.5°	480.3	480.4	480.5	480.7	480.5	480.4	480.3	480.1	479.4	478.1	476.8
120°	513.6	513.6	513.6	513.6	513.6	513.6	513.6	513.6	513.0	511.7	510.4
122.5°	545.6	545.7	545.9	546.0	545.9	545.7	545.6	545.5	545.0	544.0	543.1
125°	590.7	591.0	591.3	591.6	591.3	591.0	590.7	590.3	590.0	589.7	589.3
127.5°	636.5	636.1	635.8	635.5	635.8	636.1	636.5	636.8	636.7	636.2	635.7
130°	664.7	664.4	664.1	663.7	664.1	664.4	664.7	665.1	664.9	664.2	663.6
132.5°	691.0	690.6	690.1	689.6	690.1	690.6	691.0	691.5	691.4	690.7	690.1
135°	730.7	730.2	729.7	729.2	729.7	730.2	730.7	731.2	731.2	730.7	730.2
137.5°	767.5	767.1	766.8	766.5	766.8	767.1	767.5	767.8	767.6	766.8	766.0
140°	789.8	789.5	789.2	788.8	789.2	789.5	789.8	790.2	790.0	789.3	788.7
142.5°	810.8	810.4	809.9	809.4	809.9	810.4	810.8	811.3	811.2	810.7	810.2
145°	841.1	841.1	841.1	841.1	841.1	841.1	841.1	841.1	840.9	840.6	840.3
147.5°	866.9	866.1	865.4	864.6	865.4	866.1	866.9	867.6	867.9	867.5	867.2
150°	883.8	883.3	882.8	882.3	882.8	883.3	883.8	884.3	884.3	884.0	883.7
152.5°	898.7	897.9	897.2	896.4	897.2	897.9	898.7	899.4	899.5	898.9	898.3
155°	919.1	918.1	917.1	916.1	917.1	918.1	919.1	920.1	920.2	919.3	918.5
157.5°	936.6	935.3	934.1	932.8	934.1	935.3	936.6	937.9	938.0	937.0	936.1
160°	946.8	945.7	944.5	943.4	944.5	945.7	946.8	948.0	948.0	947.1	946.1
162.5°	956.4	955.4	954.4	953.4	954.4	955.4	956.4	957.4	957.4	956.3	955.2
165°	968.9	967.7	966.6	965.4	966.6	967.7	968.9	970.0	969.9	968.6	967.3
167.5°	978.1	976.7	975.4	974.1	975.4	976.7	978.1	979.4	979.4	978.1	976.7
170°	983.4	982.0	980.7	979.4	980.7	982.0	983.4	984.7	984.7	983.4	982.0
172.5°	986.7	985.3	983.8	982.4	983.8	985.3	986.7	988.1	988.2	986.9	985.6
175°	990.7	989.4	988.1	986.8	988.1	989.4	990.7	992.0	992.1	991.0	989.8
177.5°	992.0	990.7	989.4	988.1	989.4	990.7	992.0	993.3	993.5	992.4	991.4
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1346.8	1346.8	1357.2	1363.7	1371.9	1377.3	1381.1	1384.9	1391.5	1400.2	1410.0
5°	1269.8	1272.5	1287.5	1302.5	1316.8	1329.0	1339.2	1351.5	1366.4	1384.8	1405.2
7.5°	1195.2	1205.7	1220.8	1239.0	1259.0	1276.9	1295.0	1315.1	1336.2	1363.3	1391.9
10°	1147.3	1158.9	1177.2	1200.4	1221.5	1242.6	1265.0	1286.8	1313.3	1345.3	1382.1
12.5°	1105.4	1116.4	1135.3	1160.6	1180.7	1203.9	1229.6	1258.0	1287.8	1326.3	1367.9
15°	1047.3	1060.2	1083.3	1095.6	1126.2	1154.1	1177.9	1218.8	1256.9	1296.3	1344.7
17.5°	999.6	1006.9	1025.6	1048.4	1071.2	1102.5	1133.7	1167.7	1205.7	1254.0	1314.4
20°	967.0	973.1	993.5	1017.3	1041.8	1070.4	1098.3	1132.3	1175.2	1226.2	1291.6
22.5°	942.5	949.1	962.5	987.9	1010.8	1034.5	1062.4	1102.9	1148.5	1198.5	1269.3
25°	907.1	911.2	920.0	940.4	960.9	987.4	1011.9	1050.0	1097.0	1155.5	1226.2
27.5°	873.5	877.4	884.8	899.5	918.5	940.0	966.7	999.1	1046.7	1110.3	1185.4
30°	853.3	854.0	860.8	874.4	890.8	908.5	933.0	969.7	1014.6	1079.3	1158.2
32.5°	835.9	833.3	838.0	848.3	864.1	881.8	901.9	938.1	981.4	1045.0	1126.1
35°	806.4	805.0	803.0	811.8	825.4	839.0	856.7	884.0	933.0	992.2	1077.2
37.5°	776.3	773.0	769.4	773.4	784.1	798.2	813.6	837.8	880.0	945.2	1026.6
40°	754.0	751.3	749.2	747.9	757.4	771.0	782.6	805.7	845.2	907.1	987.4
42.5°	729.5	727.9	725.3	723.4	731.3	741.6	753.7	774.1	813.6	871.7	947.7
45°	690.0	688.7	687.3	685.9	690.7	700.2	709.8	724.7	758.7	815.2	884.0
47.5°	646.1	644.3	644.8	642.7	647.3	653.7	660.3	676.4	709.1	754.7	804.9
50°	614.5	613.8	613.8	613.8	615.2	622.6	628.8	641.0	671.0	716.6	752.6
52.5°	584.5	581.7	581.7	582.8	585.2	590.0	593.9	607.3	633.4	670.8	703.6
55°	537.6	532.1	530.8	532.1	534.2	538.3	542.4	553.2	575.7	603.6	622.6
57.5°	485.6	482.6	480.8	481.1	482.2	485.5	488.6	500.4	518.1	532.7	544.9
60°	449.1	450.5	444.4	445.7	445.7	448.4	453.2	460.7	475.7	485.9	498.1
62.5°	414.8	412.9	411.2	409.2	409.2	410.3	416.7	422.6	435.4	440.7	450.2
65°	361.3	361.3	357.3	358.6	359.3	354.5	357.9	364.7	372.9	375.0	383.8
67.5°	307.2	305.3	303.0	300.9	300.9	300.5	302.3	305.7	311.8	312.5	319.3
70°	270.2	268.8	268.1	266.1	263.4	266.8	264.7	268.1	271.5	272.2	276.3
72.5°	234.2	232.9	231.6	229.6	228.5	228.1	228.2	232.2	234.5	233.5	238.2
75°	183.1	181.7	180.3	176.9	176.9	174.9	175.6	178.3	181.0	179.0	183.1
77.5°	134.5	130.2	130.0	130.9	128.6	129.0	128.2	127.8	129.0	129.2	132.8
80°	103.4	98.7	100.0	99.4	98.7	98.0	96.6	97.3	98.0	98.7	100.7
82.5°	74.6	74.2	72.8	72.7	72.0	70.2	69.4	70.6	71.3	70.9	72.4
85°	38.1	36.1	37.4	36.7	37.4	36.7	34.7	34.7	36.1	35.4	36.7
87.5°	15.1	15.0	14.0	14.1	13.1	13.3	12.3	12.6	12.8	12.5	13.2
90°	18.3	17.7	15.5	13.4	11.3	9.2	7.3	5.6	4.0	2.4	0.7
92.5°	19.9	18.8	17.2	15.6	14.0	12.4	11.9	12.3	12.8	13.2	13.7
95°	24.0	22.8	21.0	19.2	17.4	15.6	18.1	24.8	31.5	38.2	44.9
97.5°	25.0	23.7	35.5	47.2	59.0	70.8	78.2	81.2	84.2	87.2	90.2
100°	25.6	24.3	49.8	75.3	100.8	126.3	137.4	134.2	130.9	127.6	124.4
102.5°	44.4	48.4	76.3	104.1	132.0	159.9	172.6	170.3	167.9	165.6	163.2
105°	132.2	161.2	175.9	190.6	205.3	220.0	226.5	224.7	222.9	221.1	219.3
107.5°	274.1	295.4	293.1	290.7	288.4	286.1	284.2	282.8	281.3	279.9	278.4
110°	326.5	331.9	330.1	328.3	326.5	324.7	323.1	321.8	320.5	319.2	317.9



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	369.1	369.0	367.2	365.4	363.6	361.8	360.3	359.1	357.9	356.7	355.6
115°	424.0	422.4	420.9	419.4	418.0	416.5	415.3	414.3	413.3	412.3	411.3
117.5°	475.5	474.2	473.4	472.7	471.9	471.2	470.2	469.0	467.8	466.6	465.4
120°	509.1	507.7	507.3	506.8	506.3	505.8	504.8	503.3	501.9	500.4	498.9
122.5°	542.2	541.3	540.7	540.1	539.4	538.8	537.9	536.7	535.5	534.3	533.1
125°	589.0	588.7	588.0	587.4	586.7	586.1	585.1	583.8	582.5	581.2	579.9
127.5°	635.1	634.6	633.8	633.0	632.3	631.5	630.4	629.1	627.8	626.5	625.2
130°	662.9	662.3	661.6	661.0	660.3	659.7	658.7	657.4	656.1	654.8	653.4
132.5°	689.4	688.8	688.2	687.7	687.2	686.7	685.8	684.4	683.1	681.8	680.5
135°	729.7	729.2	728.6	727.9	727.3	726.6	725.8	724.8	723.8	722.9	721.9
137.5°	765.2	764.4	764.1	763.7	763.3	763.0	762.2	760.9	759.7	758.4	757.2
140°	788.0	787.4	786.9	786.4	785.9	785.4	784.7	783.7	782.7	781.7	780.7
142.5°	809.7	809.2	808.7	808.2	807.7	807.2	806.5	805.5	804.5	803.5	802.5
145°	839.9	839.6	839.3	839.0	838.6	838.3	837.6	836.4	835.3	834.1	833.0
147.5°	866.9	866.5	866.2	865.9	865.6	865.2	864.7	863.9	863.2	862.4	861.7
150°	883.4	883.0	882.7	882.4	882.1	881.7	881.3	880.8	880.3	879.8	879.4
152.5°	897.7	897.2	897.0	896.8	896.6	896.4	896.2	895.9	895.7	895.5	895.2
155°	917.7	916.9	916.7	916.6	916.4	916.2	916.3	916.6	917.0	917.3	917.6
157.5°	935.1	934.1	934.3	934.4	934.6	934.8	934.9	934.9	934.9	935.0	935.0
160°	945.1	944.1	944.3	944.4	944.6	944.8	944.9	945.1	945.3	945.4	945.6
162.5°	954.1	952.9	953.1	953.3	953.4	953.6	953.9	954.3	954.7	955.2	955.6
165°	966.0	964.7	964.9	965.0	965.2	965.4	965.7	966.2	966.7	967.2	967.7
167.5°	975.4	974.1	974.1	974.1	974.1	974.1	974.5	975.1	975.8	976.4	977.1
170°	980.7	979.4	979.4	979.4	979.4	979.4	979.8	980.4	981.1	981.7	982.4
172.5°	984.3	983.0	982.8	982.7	982.6	982.4	982.8	983.6	984.3	985.1	985.9
175°	988.7	987.5	987.4	987.2	987.0	986.9	987.2	988.0	988.8	989.6	990.5
177.5°	990.3	989.3	989.2	989.0	988.9	988.8	989.0	989.7	990.3	991.0	991.6
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1413.2	1416.0	1425.2	1431.8	1439.4	1443.7	1448.1	1451.4	1455.7	1456.8	1472.6
5°	1419.5	1433.1	1456.9	1474.6	1496.4	1520.2	1536.5	1544.0	1563.8	1580.1	1612.8
7.5°	1417.7	1446.7	1482.7	1519.9	1560.0	1597.0	1629.1	1667.2	1694.3	1735.0	1775.1
10°	1416.1	1454.9	1501.2	1548.8	1604.6	1656.3	1702.6	1754.3	1797.2	1853.7	1902.0
12.5°	1411.2	1458.2	1522.4	1578.7	1646.5	1717.8	1786.4	1852.8	1890.8	1984.9	2029.4
15°	1399.1	1454.9	1535.2	1620.9	1714.2	1798.5	1885.6	1955.1	2067.3	2149.7	2202.1
17.5°	1376.0	1454.1	1549.3	1652.8	1766.1	1877.3	1976.0	2081.4	2200.4	2300.1	2406.2
20°	1365.1	1450.8	1557.0	1671.3	1789.0	1914.9	2027.2	2153.8	2283.7	2381.7	2517.8
22.5°	1344.9	1442.1	1556.4	1683.8	1809.7	1939.9	2071.3	2198.9	2349.1	2484.1	2613.6
25°	1312.0	1420.9	1539.3	1681.5	1829.2	1959.8	2117.0	2286.5	2443.0	2616.5	2745.8
27.5°	1277.4	1393.6	1512.3	1644.6	1803.4	1958.5	2156.2	2347.7	2539.0	2688.9	2784.6
30°	1250.7	1363.7	1486.2	1619.6	1776.8	1961.2	2182.3	2391.2	2577.7	2706.3	2760.1
32.5°	1221.9	1336.5	1444.8	1584.7	1752.3	1959.5	2198.7	2416.8	2579.9	2665.5	2655.0
35°	1176.6	1272.5	1378.0	1512.7	1710.1	1947.6	2208.2	2419.1	2519.2	2500.8	2362.0
37.5°	1111.2	1191.9	1295.8	1443.3	1661.1	1922.4	2189.1	2347.4	2340.9	2191.3	1990.2
40°	1070.4	1139.1	1239.2	1394.3	1623.0	1906.1	2159.2	2262.0	2174.9	1965.9	1725.0
42.5°	1017.1	1080.3	1180.4	1339.9	1581.1	1872.8	2102.0	2131.8	1961.4	1721.0	1500.2
45°	934.3	990.1	1093.5	1258.2	1518.2	1800.6	1962.5	1889.7	1660.4	1412.0	1243.9
47.5°	845.4	903.4	1002.9	1172.1	1427.3	1691.8	1769.0	1614.1	1378.7	1177.2	1022.9
50°	789.4	845.2	942.5	1113.3	1365.7	1602.6	1634.5	1434.5	1218.1	1041.2	914.6
52.5°	732.8	785.3	881.0	1052.3	1293.9	1499.1	1479.4	1275.5	1076.5	925.7	826.4
55°	648.5	698.2	789.4	950.0	1169.8	1332.4	1261.0	1066.3	901.7	784.6	709.1
57.5°	573.1	620.7	699.4	844.5	1035.6	1147.3	1056.4	892.4	761.5	671.4	615.0
60°	521.9	564.1	639.0	773.7	939.8	1024.8	935.0	790.1	679.8	607.7	557.3
62.5°	473.5	510.2	579.6	701.9	846.1	917.6	826.7	704.0	610.1	546.2	503.4
65°	400.1	433.5	494.7	590.0	708.4	756.0	677.8	578.4	505.6	458.0	429.4
67.5°	333.2	361.5	414.4	489.4	576.5	611.2	551.6	474.7	419.9	381.6	358.9
70°	288.5	313.0	354.5	419.2	498.1	524.7	468.9	405.6	365.4	334.8	313.7
72.5°	251.0	268.9	306.6	356.6	422.4	443.5	404.6	349.0	311.5	288.5	271.8
75°	191.2	206.2	230.7	270.8	316.4	328.7	299.4	264.7	239.5	223.2	210.3
77.5°	137.9	148.9	166.6	191.4	222.9	234.0	215.4	192.3	173.9	162.9	155.7
80°	104.1	113.0	127.9	148.3	167.4	173.5	162.6	144.9	132.0	125.9	119.8
82.5°	76.9	81.9	90.9	104.8	117.9	125.1	115.8	105.2	98.3	92.7	90.4
85°	38.8	41.5	45.6	51.0	59.2	61.9	58.5	55.8	51.7	48.3	48.3
87.5°	14.6	15.0	16.9	18.3	20.9	22.9	22.8	22.2	22.0	21.6	21.2
90°	2.4	4.0	5.6	7.3	9.2	11.3	13.4	15.5	17.7	18.3	19.0
92.5°	13.2	12.8	12.3	11.9	12.4	14.0	15.6	17.2	18.8	19.9	20.9
95°	38.2	31.5	24.8	18.1	15.6	17.4	19.2	21.0	22.8	24.0	25.1
97.5°	87.2	84.2	81.2	78.2	70.8	59.0	47.2	35.5	23.7	25.0	26.3
100°	127.6	130.9	134.2	137.4	126.3	100.8	75.3	49.8	24.3	25.6	26.9
102.5°	165.6	167.9	170.3	172.6	159.9	132.0	104.1	76.3	48.4	44.4	40.3
105°	221.1	222.9	224.7	226.5	220.0	205.3	190.6	175.9	161.2	132.2	103.3
107.5°	279.9	281.3	282.8	284.2	286.1	288.4	290.7	293.1	295.4	274.1	252.9
110°	319.2	320.5	321.8	323.1	324.7	326.5	328.3	330.1	331.9	326.5	321.1



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	356.7	357.9	359.1	360.3	361.8	363.6	365.4	367.2	369.0	369.1	369.2
115°	412.3	413.3	414.3	415.3	416.5	418.0	419.4	420.9	422.4	424.0	425.7
117.5°	466.6	467.8	469.0	470.2	471.2	471.9	472.7	473.4	474.2	475.5	476.8
120°	500.4	501.9	503.3	504.8	505.8	506.3	506.8	507.3	507.7	509.1	510.4
122.5°	534.3	535.5	536.7	537.9	538.8	539.4	540.1	540.7	541.3	542.2	543.1
125°	581.2	582.5	583.8	585.1	586.1	586.7	587.4	588.0	588.7	589.0	589.3
127.5°	626.5	627.8	629.1	630.4	631.5	632.3	633.0	633.8	634.6	635.1	635.7
130°	654.8	656.1	657.4	658.7	659.7	660.3	661.0	661.6	662.3	662.9	663.6
132.5°	681.8	683.1	684.4	685.8	686.7	687.2	687.7	688.2	688.8	689.4	690.1
135°	722.9	723.8	724.8	725.8	726.6	727.3	727.9	728.6	729.2	729.7	730.2
137.5°	758.4	759.7	760.9	762.2	763.0	763.3	763.7	764.1	764.4	765.2	766.0
140°	781.7	782.7	783.7	784.7	785.4	785.9	786.4	786.9	787.4	788.0	788.7
142.5°	803.5	804.5	805.5	806.5	807.2	807.7	808.2	808.7	809.2	809.7	810.2
145°	834.1	835.3	836.4	837.6	838.3	838.6	839.0	839.3	839.6	839.9	840.3
147.5°	862.4	863.2	863.9	864.7	865.2	865.6	865.9	866.2	866.5	866.9	867.2
150°	879.8	880.3	880.8	881.3	881.7	882.1	882.4	882.7	883.0	883.4	883.7
152.5°	895.5	895.7	895.9	896.2	896.4	896.6	896.8	897.0	897.2	897.7	898.3
155°	917.3	917.0	916.6	916.3	916.2	916.4	916.6	916.7	916.9	917.7	918.5
157.5°	935.0	934.9	934.9	934.9	934.8	934.6	934.4	934.3	934.1	935.1	936.1
160°	945.4	945.3	945.1	944.9	944.8	944.6	944.4	944.3	944.1	945.1	946.1
162.5°	955.2	954.7	954.3	953.9	953.6	953.4	953.3	953.1	952.9	954.1	955.2
165°	967.2	966.7	966.2	965.7	965.4	965.2	965.0	964.9	964.7	966.0	967.3
167.5°	976.4	975.8	975.1	974.5	974.1	974.1	974.1	974.1	974.1	975.4	976.7
170°	981.7	981.1	980.4	979.8	979.4	979.4	979.4	979.4	979.4	980.7	982.0
172.5°	985.1	984.3	983.6	982.8	982.4	982.6	982.7	982.8	983.0	984.3	985.6
175°	989.6	988.8	988.0	987.2	986.9	987.0	987.2	987.4	987.5	988.7	989.8
177.5°	991.0	990.3	989.7	989.0	988.8	988.9	989.0	989.2	989.3	990.3	991.4
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5	1404.5
2.5°	1478.0	1478.6	1484.6	1488.9	1486.7	1489.5	1490.5
5°	1614.8	1639.3	1652.2	1661.8	1662.4	1663.1	1668.6
7.5°	1808.7	1835.0	1854.2	1883.3	1892.0	1902.0	1899.1
10°	1950.3	1989.1	2022.4	2040.1	2059.2	2087.1	2064.6
12.5°	2082.6	2151.3	2202.1	2229.6	2247.5	2253.1	2242.1
15°	2300.7	2390.6	2438.9	2437.5	2498.8	2525.3	2483.8
17.5°	2500.8	2583.7	2650.1	2684.1	2735.2	2746.5	2741.3
20°	2623.3	2713.8	2765.5	2824.0	2850.6	2874.4	2878.5
22.5°	2728.9	2810.2	2865.7	2914.4	2936.6	2947.9	2954.7
25°	2837.6	2901.6	2935.0	2952.0	2958.1	2956.7	2947.9
27.5°	2830.2	2835.1	2798.3	2762.3	2730.0	2693.7	2681.1
30°	2756.7	2699.5	2597.4	2539.6	2454.5	2387.2	2414.4
32.5°	2563.4	2449.6	2335.0	2208.6	2103.9	2074.1	2044.2
35°	2187.8	1987.7	1870.7	1734.6	1680.1	1625.7	1588.3
37.5°	1770.0	1615.2	1476.4	1387.4	1332.8	1298.4	1279.9
40°	1530.4	1390.9	1276.6	1204.5	1163.0	1124.2	1118.7
42.5°	1339.3	1209.6	1123.6	1066.2	1026.3	1009.8	997.9
45°	1097.0	1006.4	948.6	907.8	881.2	871.0	857.4
47.5°	928.5	864.5	821.1	793.3	773.3	765.7	764.6
50°	834.3	781.2	749.2	727.4	711.8	709.1	698.2
52.5°	763.5	717.5	692.6	673.6	662.3	654.6	651.4
55°	662.8	632.2	609.7	598.8	590.0	582.5	582.5
57.5°	579.9	554.3	539.5	530.2	527.5	522.2	518.8
60°	528.7	507.0	495.4	487.2	481.8	482.5	476.3
62.5°	478.7	464.5	453.5	445.3	438.8	438.9	439.3
65°	407.6	396.7	388.6	385.8	381.8	377.0	378.4
67.5°	345.4	335.2	328.8	324.2	322.8	320.2	324.2
70°	300.8	293.3	288.5	284.4	283.1	283.8	287.2
72.5°	259.9	254.6	251.5	249.6	246.6	246.7	249.1
75°	204.1	200.1	197.3	195.3	194.6	194.6	194.6
77.5°	150.0	149.0	147.8	144.8	144.9	145.8	145.9
80°	118.4	116.4	115.7	114.3	112.3	110.9	114.3
82.5°	88.5	86.4	85.7	85.5	82.3	82.1	84.9
85°	47.6	45.6	46.3	45.6	45.6	44.9	44.9
87.5°	20.8	20.4	19.9	20.6	20.1	19.6	20.7
90°	19.6	20.3	20.8	21.1	21.4	21.7	22.1
92.5°	22.0	23.0	23.6	23.8	24.0	24.2	24.4
95°	26.2	27.4	28.0	28.0	28.0	28.0	28.0
97.5°	27.6	28.9	29.7	29.8	30.0	30.2	30.3
100°	28.2	29.5	30.3	30.4	30.6	30.7	30.9
102.5°	36.3	32.2	30.3	30.6	30.9	31.2	31.5
105°	74.3	45.4	31.1	31.4	31.7	32.1	32.4
107.5°	231.7	210.5	189.0	167.1	145.3	123.5	101.7
110°	315.7	310.3	295.9	272.5	249.1	225.7	202.4



TEST NUMBER: P332186

CATALOG NUMBER: S123DIW-S1000D755U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	369.3	369.4	366.9	362.0	357.1	352.1	347.2
115°	427.3	428.9	430.1	430.7	431.4	432.0	432.7
117.5°	478.1	479.4	480.1	480.3	480.4	480.5	480.7
120°	511.7	513.0	513.6	513.6	513.6	513.6	513.6
122.5°	544.0	545.0	545.5	545.6	545.7	545.9	546.0
125°	589.7	590.0	590.3	590.7	591.0	591.3	591.6
127.5°	636.2	636.7	636.8	636.5	636.1	635.8	635.5
130°	664.2	664.9	665.1	664.7	664.4	664.1	663.7
132.5°	690.7	691.4	691.5	691.0	690.6	690.1	689.6
135°	730.7	731.2	731.2	730.7	730.2	729.7	729.2
137.5°	766.8	767.6	767.8	767.5	767.1	766.8	766.5
140°	789.3	790.0	790.2	789.8	789.5	789.2	788.8
142.5°	810.7	811.2	811.3	810.8	810.4	809.9	809.4
145°	840.6	840.9	841.1	841.1	841.1	841.1	841.1
147.5°	867.5	867.9	867.6	866.9	866.1	865.4	864.6
150°	884.0	884.3	884.3	883.8	883.3	882.8	882.3
152.5°	898.9	899.5	899.4	898.7	897.9	897.2	896.4
155°	919.3	920.2	920.1	919.1	918.1	917.1	916.1
157.5°	937.0	938.0	937.9	936.6	935.3	934.1	932.8
160°	947.1	948.0	948.0	946.8	945.7	944.5	943.4
162.5°	956.3	957.4	957.4	956.4	955.4	954.4	953.4
165°	968.6	969.9	970.0	968.9	967.7	966.6	965.4
167.5°	978.1	979.4	979.4	978.1	976.7	975.4	974.1
170°	983.4	984.7	984.7	983.4	982.0	980.7	979.4
172.5°	986.9	988.2	988.1	986.7	985.3	983.8	982.4
175°	991.0	992.1	992.0	990.7	989.4	988.1	986.8
177.5°	992.4	993.5	993.3	992.0	990.7	989.4	988.1
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5

(END OF REPORT)