

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332203-927

Luminaire Tested: **S123DIW-S1000D1320U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332203-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1320U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6890.5 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332203-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332203-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45				40	
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38				33	
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32				28	
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28				24	
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24				21	
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21				18	
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19				16	
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17				15	
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15				13	
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14				12	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13497	13497	13497
5°	13560	13374	13467
10°	13470	13258	13340
15°	13312	13108	13133
20°	13128	12893	12906
25°	12883	12638	12613
30°	12609	12356	12261
35°	12326	12056	11901
40°	12029	11726	11545
45°	11702	11423	11144
50°	11375	11050	10742
55°	10946	10663	10340
60°	10514	10213	9888
65°	10132	9722	9419
70°	9567	9161	8752
75°	8742	8430	8072
80°	7885	7550	7482
85°	6928	6657	6385



TEST NUMBER: P332203-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.1	1.7
10°-20°	333.5	4.8
20°-30°	492.7	7.1
30°-40°	575.5	8.4
40°-50°	578.6	8.4
50°-60°	508.2	7.4
60°-70°	378.6	5.5
70°-80°	215.7	3.1
80°-90°	65.8	1.0
90°-100°	85.2	1.2
100°-110°	255.0	3.7
110°-120°	433.8	6.3
120°-130°	570.5	8.3
130°-140°	641.3	9.3
140°-150°	630.4	9.1
150°-160°	530.7	7.7
160°-170°	353.3	5.1
170°-180°	123.7	1.8
0°-30°	944.3	13.7
0°-40°	1519.8	22.1
0°-60°	2606.6	37.8
0°-90°	3266.7	47.4
90°-120°	774.0	11.2
90°-150°	2616.2	38.0
90°-180°	3624.0	52.6
0°-180°	6890.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1254	1254	1254	1254	1254	
5°	1255	1249	1238	1248	1246	119
15°	1195	1190	1176	1184	1178	337
25°	1085	1078	1064	1065	1062	499
35°	938	931	918	911	906	587
45°	769	764	750	738	732	593
55°	583	582	568	557	551	522
65°	398	392	382	373	370	392
75°	210	206	203	197	194	225
85°	56	54	54	52	52	62
90°	1	11	25	29	31	7
95°	61	68	76	80	80	68
105°	231	234	242	243	244	248
115°	437	439	438	439	438	432
125°	639	642	640	636	632	570
135°	829	835	834	830	828	639
145°	1006	1008	1011	1010	1006	628
155°	1152	1152	1153	1156	1150	530
165°	1254	1252	1251	1257	1250	354
175°	1305	1301	1301	1306	1300	124
180°	1308	1308	1308	1308	1308	



TEST NUMBER: P332203-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1258.2	1257.5	1256.7	1255.9	1255.2	1253.7	1251.6	1249.5	1247.4	1245.3	1247.2
5°	1255.0	1253.8	1252.6	1251.4	1250.2	1248.3	1245.7	1243.0	1240.4	1237.8	1240.2
7.5°	1242.7	1241.5	1240.3	1239.1	1237.9	1236.0	1233.3	1230.5	1227.8	1225.0	1227.2
10°	1232.4	1231.2	1229.9	1228.8	1227.6	1225.4	1222.3	1219.2	1216.1	1213.0	1215.1
12.5°	1218.5	1217.6	1216.6	1215.5	1214.6	1212.6	1209.7	1206.7	1203.8	1200.9	1202.5
15°	1194.6	1193.7	1192.7	1191.8	1190.8	1188.7	1185.7	1182.6	1179.4	1176.3	1178.2
17.5°	1166.8	1165.5	1164.3	1163.1	1161.8	1159.7	1156.5	1153.4	1150.3	1147.2	1148.5
20°	1146.1	1144.7	1143.3	1141.8	1140.3	1138.0	1135.0	1131.9	1128.8	1125.6	1126.6
22.5°	1122.8	1121.4	1120.0	1118.5	1117.1	1114.8	1111.7	1108.6	1105.5	1102.3	1103.1
25°	1084.7	1083.2	1081.8	1080.4	1078.9	1076.7	1073.5	1070.4	1067.3	1064.1	1064.4
27.5°	1043.9	1042.5	1041.1	1039.7	1038.3	1035.9	1032.6	1029.3	1025.9	1022.5	1022.7
30°	1014.5	1013.4	1012.2	1011.0	1009.8	1007.5	1004.2	1000.8	997.4	994.1	994.1
32.5°	985.2	983.7	982.1	980.5	978.9	976.8	974.2	971.7	969.1	966.5	965.1
35°	938.0	936.6	935.2	933.7	932.2	930.0	926.9	923.8	920.7	917.5	916.1
37.5°	889.7	887.9	886.1	884.2	882.4	880.0	876.8	873.6	870.4	867.3	865.5
40°	856.1	854.6	853.2	851.8	850.3	848.0	844.5	841.2	837.9	834.5	832.6
42.5°	822.4	820.8	819.2	817.5	815.9	813.4	810.1	806.8	803.4	800.0	798.1
45°	768.7	767.8	766.8	765.9	764.9	762.9	759.8	756.6	753.5	750.4	747.6
47.5°	715.5	714.1	712.7	711.3	710.0	707.7	704.9	702.0	699.0	696.1	693.2
50°	679.3	678.0	676.8	675.7	674.5	672.3	669.2	666.1	663.0	659.9	657.2
52.5°	641.3	640.5	639.7	638.9	638.0	636.0	632.7	629.4	626.1	622.7	620.5
55°	583.3	583.0	582.8	582.6	582.3	580.7	577.6	574.4	571.3	568.2	565.5
57.5°	528.1	527.3	526.5	525.7	524.8	523.2	520.7	518.2	515.7	513.3	510.9
60°	488.4	488.1	487.9	487.7	487.4	485.9	483.0	480.1	477.3	474.4	472.2
62.5°	453.0	452.4	451.8	451.1	450.6	448.9	445.9	443.1	440.2	437.3	435.1
65°	397.8	396.6	395.5	394.3	393.1	391.3	388.9	386.5	384.0	381.7	379.8
67.5°	339.5	338.3	337.3	336.3	335.2	333.7	331.9	330.1	328.3	326.5	324.8
70°	304.0	302.6	301.2	299.8	298.3	296.8	295.4	294.0	292.6	291.1	289.5
72.5°	267.0	265.9	264.8	263.8	262.8	261.4	259.8	258.2	256.5	254.8	253.4
75°	210.2	209.3	208.3	207.4	206.4	205.6	204.9	204.1	203.4	202.7	201.5
77.5°	160.0	159.5	158.9	158.4	157.9	157.2	156.4	155.5	154.6	153.8	153.0
80°	127.2	126.5	125.8	125.1	124.4	123.7	123.3	122.8	122.3	121.8	121.6
82.5°	95.3	95.1	95.1	94.9	94.7	94.6	94.5	94.4	94.3	94.3	93.8
85°	56.1	55.6	55.1	54.7	54.2	53.9	53.9	53.9	53.9	53.9	53.4
87.5°	22.7	22.5	22.4	22.3	22.2	22.3	22.7	23.1	23.5	23.9	23.9
90°	1.0	3.3	5.6	7.8	10.1	12.8	15.8	18.7	21.7	24.6	25.6
92.5°	24.9	26.4	28.0	29.5	31.1	32.7	34.4	36.0	37.8	39.5	40.2
95°	60.6	62.2	63.8	65.4	67.0	68.8	70.6	72.4	74.2	76.0	76.9
97.5°	107.7	108.8	110.0	111.2	112.4	113.7	115.0	116.3	117.6	119.0	120.0
100°	139.7	141.1	142.4	143.9	145.2	146.5	147.6	148.8	149.9	151.1	151.7
102.5°	176.7	177.5	178.4	179.2	180.0	181.2	182.7	184.2	185.7	187.2	187.9
105°	231.2	231.6	232.1	232.5	233.0	234.2	236.3	238.4	240.4	242.5	242.5
107.5°	294.5	294.8	295.0	295.3	295.6	296.1	296.9	297.8	298.6	299.4	300.2
110°	333.9	334.4	334.9	335.3	335.7	336.2	336.7	337.2	337.5	338.0	339.0



TEST NUMBER: P332203-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.0	375.3	375.6	375.8	376.1	376.3	376.4	376.4	376.6	376.7	377.8
115°	436.7	437.4	438.0	438.7	439.4	439.5	439.0	438.6	438.2	437.7	437.9
117.5°	498.8	499.2	499.6	500.1	500.6	500.5	499.9	499.3	498.7	498.1	498.0
120°	537.3	538.7	540.1	541.5	542.8	543.0	541.8	540.7	539.6	538.4	538.1
122.5°	577.7	578.6	579.6	580.7	581.6	581.9	581.2	580.7	580.0	579.5	578.8
125°	639.1	639.8	640.4	641.1	641.8	641.9	641.4	641.0	640.6	640.1	639.2
127.5°	695.8	697.3	698.7	700.1	701.6	702.1	701.6	701.1	700.6	700.1	698.8
130°	733.6	735.4	737.3	739.1	740.9	741.5	740.8	740.1	739.4	738.7	737.8
132.5°	771.4	773.2	775.1	776.9	778.7	779.3	778.9	778.4	777.8	777.4	776.3
135°	829.2	830.5	831.9	833.2	834.6	835.2	835.0	834.7	834.5	834.2	833.4
137.5°	882.6	883.7	884.9	886.0	887.2	888.0	888.6	889.2	889.8	890.4	889.4
140°	919.6	920.7	921.9	923.0	924.2	924.8	925.0	925.3	925.5	925.7	925.5
142.5°	953.2	954.4	955.5	956.7	957.8	958.6	959.0	959.4	959.8	960.3	960.0
145°	1005.8	1006.3	1006.8	1007.3	1007.7	1008.3	1008.9	1009.6	1010.3	1011.0	1010.7
147.5°	1051.9	1052.7	1053.5	1054.4	1055.2	1055.9	1056.5	1057.2	1057.8	1058.4	1058.4
150°	1083.9	1084.4	1084.9	1085.3	1085.8	1086.2	1086.7	1087.1	1087.6	1088.1	1088.1
152.5°	1110.2	1110.9	1111.5	1112.1	1112.8	1113.3	1113.6	1113.8	1114.1	1114.4	1114.8
155°	1151.8	1151.8	1151.8	1151.8	1151.8	1151.9	1152.1	1152.3	1152.5	1152.8	1153.7
157.5°	1187.1	1186.8	1186.5	1186.3	1186.0	1186.0	1186.1	1186.3	1186.5	1186.7	1187.6
160°	1209.3	1208.9	1208.4	1207.9	1207.4	1207.2	1207.2	1207.2	1207.2	1207.2	1208.4
162.5°	1229.0	1228.4	1227.7	1227.1	1226.5	1226.2	1226.5	1226.6	1226.8	1226.9	1228.1
165°	1254.5	1253.8	1253.2	1252.4	1251.8	1251.4	1251.4	1251.4	1251.4	1251.4	1252.8
167.5°	1274.9	1273.9	1273.0	1272.1	1271.2	1270.8	1271.0	1271.2	1271.4	1271.5	1273.0
170°	1286.3	1285.5	1284.5	1283.7	1282.7	1282.2	1282.2	1282.2	1282.2	1282.2	1283.8
172.5°	1295.4	1294.5	1293.6	1292.7	1291.7	1291.3	1291.3	1291.3	1291.3	1291.3	1292.7
175°	1304.9	1303.9	1303.1	1302.1	1301.2	1300.8	1300.8	1300.8	1300.8	1300.8	1302.1
177.5°	1308.8	1308.1	1307.3	1306.5	1305.8	1305.4	1305.4	1305.4	1305.4	1305.4	1306.5
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332203-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9	1253.9
2.5°	1249.1	1251.1	1253.0	1253.9	1253.6	1253.5	1253.2	1253.1
5°	1242.5	1244.9	1247.4	1248.3	1247.8	1247.4	1246.9	1246.4
7.5°	1229.4	1231.5	1233.7	1234.6	1234.3	1234.1	1233.7	1233.4
10°	1217.3	1219.4	1221.6	1222.4	1221.9	1221.5	1221.0	1220.5
12.5°	1204.0	1205.6	1207.2	1207.8	1207.6	1207.3	1207.0	1206.7
15°	1180.1	1182.0	1184.0	1184.2	1182.8	1181.3	1179.9	1178.5
17.5°	1149.9	1151.2	1152.5	1152.9	1152.5	1151.9	1151.4	1150.9
20°	1127.5	1128.5	1129.5	1129.6	1128.9	1128.1	1127.4	1126.7
22.5°	1103.9	1104.6	1105.4	1105.3	1104.5	1103.5	1102.6	1101.7
25°	1064.6	1064.9	1065.2	1064.9	1064.1	1063.4	1062.7	1062.0
27.5°	1022.9	1023.1	1023.3	1022.9	1022.1	1021.1	1020.3	1019.3
30°	994.1	994.1	994.1	993.2	991.6	989.9	988.2	986.5
32.5°	963.8	962.5	961.2	960.0	959.1	958.1	957.3	956.3
35°	914.7	913.2	911.8	910.5	909.3	908.1	906.9	905.7
37.5°	863.9	862.1	860.4	859.1	858.4	857.6	856.8	856.1
40°	830.7	828.8	826.9	825.4	824.4	823.5	822.5	821.6
42.5°	796.1	794.2	792.3	790.9	790.0	789.0	788.1	787.1
45°	744.7	741.8	738.9	736.9	735.7	734.5	733.3	732.1
47.5°	690.4	687.6	684.8	682.9	681.8	680.7	679.7	678.6
50°	654.6	652.0	649.3	647.3	645.9	644.4	642.9	641.5
52.5°	618.2	616.0	613.8	611.9	610.5	609.0	607.6	606.2
55°	562.9	560.3	557.7	555.7	554.5	553.3	552.2	551.0
57.5°	508.5	506.2	503.8	501.9	500.6	499.2	497.8	496.4
60°	470.1	467.9	465.8	464.1	462.9	461.7	460.5	459.3
62.5°	433.0	430.9	428.6	427.2	426.4	425.6	424.8	424.0
65°	377.9	375.9	374.0	372.7	372.0	371.3	370.5	369.8
67.5°	323.1	321.5	319.8	318.5	317.4	316.4	315.4	314.4
70°	287.7	286.1	284.4	283.0	281.8	280.6	279.4	278.1
72.5°	251.9	250.4	248.9	247.9	247.2	246.6	246.1	245.4
75°	200.3	199.1	197.9	196.9	196.2	195.5	194.8	194.1
77.5°	152.1	151.3	150.5	150.1	150.1	150.1	150.1	150.1
80°	121.4	121.1	120.9	120.7	120.7	120.7	120.7	120.7
82.5°	93.4	92.9	92.5	92.2	92.0	91.8	91.7	91.4
85°	52.9	52.4	52.0	51.7	51.7	51.7	51.7	51.7
87.5°	23.9	23.8	23.8	23.9	24.0	24.1	24.2	24.2
90°	26.5	27.4	28.3	29.0	29.5	29.9	30.3	30.8
92.5°	40.9	41.7	42.4	42.6	42.3	42.1	41.7	41.5
95°	77.9	78.7	79.7	80.2	80.2	80.2	80.2	80.2
97.5°	121.0	122.2	123.2	123.7	123.6	123.5	123.4	123.3
100°	152.4	153.0	153.8	154.3	154.8	155.3	155.7	156.1
102.5°	188.5	189.3	190.0	190.2	190.1	190.0	190.0	189.9
105°	242.5	242.5	242.5	242.7	243.2	243.6	244.1	244.5
107.5°	300.9	301.6	302.3	302.5	302.3	302.0	301.7	301.4
110°	339.8	340.8	341.7	341.9	341.4	341.0	340.6	340.1



TEST NUMBER: P332203-927

CATALOG NUMBER: S123DIW-S1000D1320U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.8	379.9	381.0	381.5	381.4	381.4	381.3	381.2
115°	438.2	438.4	438.6	438.6	438.4	438.2	437.9	437.7
117.5°	498.0	498.0	497.9	497.6	496.9	496.3	495.7	495.0
120°	537.9	537.7	537.5	537.1	536.7	536.2	535.8	535.3
122.5°	578.3	577.7	577.1	576.5	575.8	575.2	574.6	573.9
125°	638.3	637.4	636.4	635.6	634.6	633.7	632.8	631.8
127.5°	697.5	696.2	695.0	693.8	692.8	691.7	690.7	689.6
130°	736.9	736.0	735.1	733.8	732.2	730.6	729.0	727.5
132.5°	775.2	774.0	773.0	771.8	770.6	769.4	768.1	766.9
135°	832.4	831.6	830.6	830.0	829.5	829.0	828.5	828.1
137.5°	888.4	887.5	886.5	885.7	884.8	883.9	883.0	882.2
140°	925.3	925.0	924.8	923.9	922.3	920.7	919.1	917.5
142.5°	959.8	959.6	959.3	958.6	957.4	956.2	954.9	953.7
145°	1010.5	1010.3	1010.1	1009.6	1008.6	1007.7	1006.8	1005.8
147.5°	1058.4	1058.4	1058.4	1057.8	1056.5	1055.0	1053.7	1052.3
150°	1088.1	1088.1	1088.1	1087.3	1086.0	1084.7	1083.2	1081.9
152.5°	1115.1	1115.5	1115.8	1115.4	1114.2	1113.0	1111.8	1110.6
155°	1154.6	1155.6	1156.4	1156.1	1154.5	1152.9	1151.3	1149.7
157.5°	1188.6	1189.5	1190.6	1190.3	1189.1	1187.8	1186.5	1185.3
160°	1209.5	1210.7	1211.8	1212.0	1211.0	1210.1	1209.2	1208.2
162.5°	1229.2	1230.4	1231.5	1231.4	1229.9	1228.4	1227.0	1225.5
165°	1254.2	1255.5	1256.9	1256.8	1255.2	1253.6	1252.0	1250.4
167.5°	1274.4	1275.8	1277.2	1277.2	1275.8	1274.4	1273.0	1271.5
170°	1285.5	1287.1	1288.6	1288.6	1287.1	1285.5	1283.8	1282.2
172.5°	1294.1	1295.5	1297.0	1296.9	1295.3	1293.6	1292.0	1290.5
175°	1303.5	1304.9	1306.2	1306.1	1304.5	1302.9	1301.3	1299.7
177.5°	1307.7	1308.8	1309.9	1309.8	1308.4	1307.2	1305.9	1304.6
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0

(END OF REPORT)