

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332226

Luminaire Tested: **S123DIW-S1165D1030U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332226  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1165D1030U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8883.5 lumens  
Efficiency: N/A  
Efficacy: 131.8 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332226

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332226

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32
4	75	64	56	50	69	60	52	47	51	46	41	44	39	36	36	33	31	27
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27	24
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21
7	59	46	38	32	54	43	36	31	37	32	27	32	28	24	27	24	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	16
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	19678	19678	19678
5°	19770	19498	19634
10°	19638	19329	19449
15°	19409	19110	19146
20°	19140	18798	18816
25°	18781	18427	18389
30°	18385	18013	17877
35°	17971	17578	17350
40°	17537	17096	16831
45°	17061	16653	16247
50°	16583	16109	15662
55°	15959	15546	15073
60°	15330	14889	14415
65°	14772	14174	13733
70°	13951	13357	12765
75°	12747	12289	11765
80°	11499	11009	10916
85°	10090	9707	9324



TEST NUMBER: P332226

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.2	1.9
10°-20°	486.2	5.5
20°-30°	718.3	8.1
30°-40°	839.0	9.4
40°-50°	843.5	9.5
50°-60°	740.9	8.3
60°-70°	552.0	6.2
70°-80°	314.5	3.5
80°-90°	94.1	1.1
90°-100°	49.2	0.6
100°-110°	234.3	2.6
110°-120°	562.7	6.3
120°-130°	716.5	8.1
130°-140°	765.6	8.6
140°-150°	715.9	8.1
150°-160°	577.5	6.5
160°-170°	372.7	4.2
170°-180°	128.4	1.4
0°-30°	1376.7	15.5
0°-40°	2215.7	24.9
0°-60°	3800.2	42.8
0°-90°	4760.7	53.6
90°-120°	846.1	9.5
90°-150°	3044.1	34.3
90°-180°	4123.0	46.4
0°-180°	8883.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1828	1828	1828	1828	1828	
5°	1830	1821	1804	1819	1817	173
15°	1742	1735	1715	1726	1718	491
25°	1581	1571	1552	1553	1548	728
35°	1368	1358	1338	1328	1320	855
45°	1121	1114	1094	1076	1067	865
55°	850	848	828	812	803	761
65°	580	572	556	544	539	572
75°	306	300	296	288	283	328
85°	82	79	79	76	76	90
90°	1	11	24	28	30	7
95°	61	23	31	38	38	76
105°	299	305	220	52	44	317
115°	562	568	576	586	591	554
125°	792	799	804	806	808	707
135°	985	991	995	998	995	758
145°	1137	1144	1146	1148	1148	711
155°	1252	1251	1252	1256	1250	577
165°	1321	1318	1317	1324	1318	373
175°	1352	1347	1348	1354	1347	129
180°	1352	1352	1352	1352	1352	



TEST NUMBER: P332226

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1834.4	1833.3	1832.2	1831.1	1829.9	1827.8	1824.8	1821.7	1818.6	1815.5	1818.3
5°	1829.7	1828.0	1826.2	1824.5	1822.7	1819.9	1816.1	1812.2	1808.4	1804.5	1808.0
7.5°	1811.8	1810.0	1808.3	1806.5	1804.8	1801.9	1797.9	1794.0	1790.0	1786.0	1789.1
10°	1796.7	1794.9	1793.2	1791.4	1789.7	1786.6	1782.0	1777.5	1772.9	1768.4	1771.5
12.5°	1776.6	1775.1	1773.6	1772.2	1770.7	1767.8	1763.6	1759.3	1755.0	1750.8	1753.1
15°	1741.7	1740.3	1738.9	1737.5	1736.1	1733.1	1728.6	1724.0	1719.5	1714.9	1717.7
17.5°	1701.1	1699.3	1697.5	1695.7	1693.8	1690.7	1686.1	1681.6	1677.0	1672.5	1674.5
20°	1670.9	1668.8	1666.7	1664.6	1662.6	1659.2	1654.7	1650.2	1645.6	1641.1	1642.5
22.5°	1637.0	1634.9	1632.8	1630.7	1628.6	1625.3	1620.7	1616.2	1611.7	1607.1	1608.2
25°	1581.3	1579.2	1577.1	1575.0	1573.0	1569.6	1565.1	1560.6	1556.0	1551.5	1551.8
27.5°	1521.9	1519.9	1517.9	1515.8	1513.8	1510.4	1505.5	1500.6	1495.7	1490.8	1491.1
30°	1479.2	1477.4	1475.7	1473.9	1472.2	1468.9	1464.0	1459.1	1454.2	1449.3	1449.3
32.5°	1436.4	1434.1	1431.8	1429.5	1427.2	1424.1	1420.4	1416.6	1412.8	1409.1	1407.1
35°	1367.6	1365.5	1363.4	1361.3	1359.2	1355.9	1351.3	1346.8	1342.2	1337.7	1335.6
37.5°	1297.1	1294.5	1291.8	1289.2	1286.5	1282.9	1278.3	1273.7	1269.1	1264.4	1261.9
40°	1248.1	1246.0	1243.9	1241.8	1239.7	1236.2	1231.3	1226.4	1221.5	1216.7	1213.9
42.5°	1199.0	1196.7	1194.3	1191.9	1189.5	1185.9	1181.0	1176.1	1171.2	1166.4	1163.6
45°	1120.8	1119.4	1118.0	1116.6	1115.2	1112.2	1107.7	1103.1	1098.6	1094.0	1089.9
47.5°	1043.1	1041.1	1039.1	1037.0	1035.0	1031.9	1027.6	1023.3	1019.1	1014.8	1010.7
50°	990.3	988.6	986.8	985.1	983.3	980.2	975.6	971.1	966.5	962.0	958.2
52.5°	935.0	933.8	932.6	931.4	930.2	927.2	922.4	917.6	912.8	907.9	904.6
55°	850.4	850.1	849.7	849.4	849.0	846.6	842.0	837.5	832.9	828.4	824.6
57.5°	769.9	768.7	767.5	766.4	765.2	762.8	759.1	755.5	751.9	748.2	744.8
60°	712.1	711.7	711.4	711.0	710.7	708.4	704.2	700.0	695.8	691.6	688.5
62.5°	660.5	659.6	658.7	657.8	656.9	654.3	650.1	645.9	641.8	637.6	634.4
65°	580.0	578.3	576.5	574.8	573.0	570.4	566.9	563.4	559.9	556.5	553.7
67.5°	494.8	493.3	491.8	490.2	488.7	486.6	483.9	481.3	478.6	476.0	473.5
70°	443.3	441.2	439.1	437.0	434.9	432.8	430.7	428.6	426.5	424.4	422.0
72.5°	389.2	387.7	386.1	384.6	383.1	381.1	378.7	376.3	374.0	371.6	369.4
75°	306.5	305.1	303.7	302.3	300.9	299.7	298.7	297.6	296.6	295.5	293.8
77.5°	233.3	232.5	231.7	231.0	230.2	229.2	227.9	226.7	225.4	224.2	223.0
80°	185.5	184.4	183.4	182.3	181.3	180.4	179.7	179.0	178.3	177.6	177.3
82.5°	139.0	138.7	138.5	138.3	138.1	137.9	137.8	137.7	137.5	137.4	136.8
85°	81.7	81.0	80.3	79.6	78.9	78.6	78.6	78.6	78.6	78.6	77.9
87.5°	32.9	32.5	32.1	31.7	31.3	31.3	31.6	31.9	32.2	32.5	32.4
90°	1.0	3.2	5.5	7.7	9.9	12.5	15.4	18.3	21.2	24.1	25.0
92.5°	18.7	18.1	17.4	16.8	16.2	17.0	19.2	21.3	23.5	25.7	27.1
95°	61.3	52.1	43.0	33.8	24.7	21.3	23.8	26.2	28.7	31.1	32.7
97.5°	123.1	119.0	114.9	110.8	106.7	96.6	80.6	64.5	48.4	32.3	34.1
100°	169.7	174.2	178.7	183.1	187.6	172.4	137.6	102.8	68.0	33.1	34.9
102.5°	222.8	226.0	229.2	232.4	235.6	218.2	180.2	142.2	104.1	66.1	60.6
105°	299.3	301.8	304.2	306.7	309.1	300.3	280.2	260.1	240.1	220.0	180.5
107.5°	380.1	382.0	384.0	386.0	387.9	390.5	393.7	396.8	400.0	403.2	374.2
110°	433.9	435.7	437.5	439.3	441.0	443.2	445.6	448.1	450.5	453.0	445.6



TEST NUMBER: P332226

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.3	486.9	488.5	490.2	491.8	493.8	496.2	498.7	501.2	503.6	503.7
115°	561.5	562.8	564.1	565.5	566.8	568.5	570.5	572.5	574.5	576.5	578.8
117.5°	635.2	636.8	638.5	640.1	641.8	643.1	644.2	645.2	646.2	647.2	649.0
120°	681.0	683.0	685.0	687.0	689.0	690.4	691.0	691.7	692.4	693.0	694.8
122.5°	727.6	729.2	730.9	732.5	734.2	735.4	736.3	737.1	738.0	738.8	740.1
125°	791.5	793.3	795.0	796.8	798.6	800.0	800.8	801.7	802.6	803.5	804.0
127.5°	853.3	855.1	856.9	858.7	860.5	861.9	863.0	864.1	865.1	866.2	866.9
130°	891.9	893.7	895.5	897.3	899.1	900.4	901.3	902.2	903.1	904.0	904.9
132.5°	928.9	930.7	932.4	934.2	936.0	937.3	938.0	938.7	939.4	940.1	941.0
135°	985.3	986.7	988.0	989.3	990.7	991.8	992.7	993.6	994.5	995.4	996.0
137.5°	1033.5	1035.2	1036.9	1038.6	1040.3	1041.4	1041.9	1042.4	1042.9	1043.4	1044.4
140°	1065.7	1067.0	1068.4	1069.7	1071.0	1072.0	1072.7	1073.4	1074.0	1074.7	1075.6
142.5°	1095.4	1096.7	1098.1	1099.4	1100.8	1101.8	1102.4	1103.1	1103.8	1104.4	1105.2
145°	1137.0	1138.5	1140.1	1141.7	1143.2	1144.2	1144.7	1145.1	1145.6	1146.0	1146.5
147.5°	1176.2	1177.2	1178.2	1179.2	1180.3	1181.0	1181.4	1181.9	1182.3	1182.8	1183.2
150°	1200.3	1200.9	1201.6	1202.3	1202.9	1203.5	1203.9	1204.4	1204.8	1205.3	1205.7
152.5°	1222.0	1222.3	1222.6	1222.9	1223.2	1223.5	1223.8	1224.0	1224.3	1224.6	1225.4
155°	1252.5	1252.0	1251.6	1251.2	1250.7	1250.6	1250.8	1251.0	1251.3	1251.5	1252.6
157.5°	1276.2	1276.2	1276.1	1276.1	1276.0	1275.9	1275.7	1275.4	1275.2	1275.0	1276.3
160°	1290.7	1290.4	1290.2	1290.0	1289.8	1289.5	1289.3	1289.1	1288.9	1288.7	1290.0
162.5°	1304.3	1303.7	1303.2	1302.6	1302.0	1301.6	1301.4	1301.2	1300.9	1300.7	1302.2
165°	1320.8	1320.1	1319.5	1318.8	1318.1	1317.7	1317.4	1317.2	1317.0	1316.8	1318.6
167.5°	1333.6	1332.8	1331.9	1331.0	1330.1	1329.6	1329.6	1329.6	1329.6	1329.6	1331.4
170°	1340.9	1340.0	1339.1	1338.2	1337.3	1336.9	1336.9	1336.9	1336.9	1336.9	1338.6
172.5°	1345.7	1344.6	1343.6	1342.5	1341.4	1341.0	1341.1	1341.3	1341.5	1341.7	1343.5
175°	1351.9	1350.8	1349.7	1348.6	1347.5	1347.0	1347.2	1347.5	1347.7	1347.9	1349.5
177.5°	1353.5	1352.6	1351.8	1350.9	1350.0	1349.6	1349.8	1350.0	1350.1	1350.3	1351.8
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332226

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1821.1	1823.9	1826.7	1828.0	1827.7	1827.4	1827.1	1826.9
5°	1811.5	1815.0	1818.5	1819.9	1819.2	1818.5	1817.8	1817.1
7.5°	1792.3	1795.4	1798.6	1799.9	1799.5	1799.1	1798.7	1798.3
10°	1774.7	1777.8	1781.0	1782.2	1781.5	1780.8	1780.1	1779.4
12.5°	1755.4	1757.7	1760.0	1761.0	1760.5	1760.1	1759.7	1759.3
15°	1720.5	1723.3	1726.1	1726.5	1724.4	1722.3	1720.2	1718.1
17.5°	1676.4	1678.4	1680.3	1680.9	1680.2	1679.4	1678.6	1677.9
20°	1643.9	1645.3	1646.7	1646.8	1645.8	1644.7	1643.7	1642.6
22.5°	1609.4	1610.5	1611.6	1611.5	1610.2	1608.8	1607.5	1606.2
25°	1552.2	1552.5	1552.9	1552.5	1551.5	1550.4	1549.4	1548.3
27.5°	1491.4	1491.6	1491.9	1491.4	1490.1	1488.7	1487.4	1486.1
30°	1449.3	1449.3	1449.3	1448.1	1445.6	1443.2	1440.7	1438.3
32.5°	1405.1	1403.2	1401.2	1399.6	1398.3	1396.9	1395.6	1394.3
35°	1333.5	1331.4	1329.3	1327.4	1325.6	1323.9	1322.1	1320.4
37.5°	1259.4	1256.9	1254.4	1252.6	1251.4	1250.3	1249.2	1248.1
40°	1211.1	1208.3	1205.5	1203.4	1202.0	1200.6	1199.2	1197.8
42.5°	1160.8	1158.0	1155.2	1153.1	1151.7	1150.3	1148.9	1147.5
45°	1085.7	1081.5	1077.3	1074.3	1072.6	1070.8	1069.1	1067.3
47.5°	1006.6	1002.5	998.3	995.5	994.0	992.4	990.9	989.4
50°	954.3	950.5	946.6	943.7	941.6	939.5	937.4	935.3
52.5°	901.4	898.1	894.8	892.1	890.0	887.9	885.8	883.7
55°	820.7	816.9	813.0	810.2	808.5	806.7	805.0	803.2
57.5°	741.4	738.0	734.5	731.8	729.8	727.8	725.7	723.7
60°	685.4	682.2	679.1	676.6	674.9	673.1	671.4	669.6
62.5°	631.3	628.1	625.0	622.8	621.6	620.4	619.3	618.1
65°	550.9	548.1	545.3	543.4	542.3	541.3	540.2	539.2
67.5°	471.1	468.6	466.2	464.2	462.8	461.3	459.8	458.4
70°	419.5	417.1	414.6	412.5	410.8	409.0	407.3	405.6
72.5°	367.3	365.1	362.9	361.4	360.5	359.6	358.7	357.8
75°	292.0	290.3	288.5	287.1	286.1	285.0	284.0	282.9
77.5°	221.8	220.6	219.4	218.8	218.8	218.8	218.8	218.8
80°	176.9	176.6	176.2	176.1	176.1	176.1	176.1	176.1
82.5°	136.1	135.5	134.9	134.4	134.1	133.9	133.6	133.3
85°	77.2	76.5	75.8	75.5	75.5	75.5	75.5	75.5
87.5°	32.3	32.2	32.1	32.1	32.2	32.3	32.3	32.4
90°	25.9	26.8	27.7	28.3	28.8	29.2	29.7	30.1
92.5°	28.6	30.0	31.4	32.3	32.5	32.8	33.1	33.3
95°	34.3	35.8	37.4	38.2	38.2	38.2	38.2	38.2
97.5°	35.9	37.7	39.5	40.5	40.7	40.9	41.2	41.4
100°	36.7	38.5	40.3	41.3	41.5	41.7	42.0	42.2
102.5°	55.0	49.5	43.9	41.4	41.8	42.2	42.6	43.0
105°	141.0	101.4	61.9	42.4	42.9	43.3	43.7	44.2
107.5°	345.2	316.3	287.3	257.9	228.1	198.4	168.6	138.8
110°	438.3	430.9	423.5	403.9	372.0	340.0	308.1	276.2





TEST NUMBER: P332226

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	503.9	504.0	504.1	500.8	494.1	487.4	480.6	473.9
115°	581.0	583.2	585.5	587.0	587.9	588.8	589.7	590.6
117.5°	650.8	652.6	654.4	655.4	655.5	655.7	655.9	656.1
120°	696.6	698.4	700.2	701.1	701.1	701.1	701.1	701.1
122.5°	741.3	742.6	743.8	744.6	744.7	744.9	745.1	745.3
125°	804.4	804.9	805.3	805.8	806.2	806.6	807.1	807.5
127.5°	867.6	868.3	869.1	869.2	868.7	868.3	867.9	867.4
130°	905.8	906.6	907.5	907.8	907.3	906.9	906.4	906.0
132.5°	941.9	942.8	943.7	943.8	943.2	942.6	942.0	941.3
135°	996.7	997.4	998.0	998.0	997.4	996.7	996.0	995.4
137.5°	1045.5	1046.6	1047.7	1048.0	1047.5	1047.1	1046.6	1046.2
140°	1076.5	1077.4	1078.3	1078.5	1078.1	1077.6	1077.2	1076.7
142.5°	1105.9	1106.6	1107.3	1107.3	1106.7	1106.1	1105.5	1104.8
145°	1146.9	1147.4	1147.8	1148.0	1148.0	1148.0	1148.0	1148.0
147.5°	1183.7	1184.1	1184.6	1184.3	1183.3	1182.2	1181.2	1180.2
150°	1206.2	1206.6	1207.1	1207.0	1206.3	1205.6	1205.0	1204.3
152.5°	1226.2	1227.0	1227.8	1227.7	1226.6	1225.6	1224.6	1223.6
155°	1253.7	1254.8	1256.0	1255.8	1254.5	1253.2	1251.8	1250.5
157.5°	1277.7	1279.0	1280.3	1280.1	1278.4	1276.7	1274.9	1273.2
160°	1291.3	1292.7	1294.0	1293.9	1292.3	1290.8	1289.2	1287.6
162.5°	1303.7	1305.3	1306.8	1306.8	1305.5	1304.1	1302.7	1301.3
165°	1320.3	1322.1	1323.9	1324.0	1322.5	1320.9	1319.3	1317.8
167.5°	1333.2	1335.0	1336.8	1336.8	1335.0	1333.2	1331.4	1329.6
170°	1340.4	1342.2	1344.0	1344.0	1342.2	1340.4	1338.6	1336.9
172.5°	1345.3	1347.0	1348.8	1348.7	1346.8	1344.8	1342.8	1340.9
175°	1351.0	1352.6	1354.2	1354.1	1352.3	1350.5	1348.7	1346.9
177.5°	1353.2	1354.6	1356.0	1355.9	1354.1	1352.3	1350.5	1348.7
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9

(END OF REPORT)