

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332227

Luminaire Tested: **S123DIW-S1165D1030U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332227
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1030U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8334.1 lumens
Efficiency: N/A
Efficacy: 123.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332227

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332227

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57
1	99	95	91	87	92	88	85	82	76	74	72	65	64	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40
3	82	73	65	59	76	68	61	56	59	54	50	51	47	44	43	40	38	34
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	33	29
5	69	57	49	43	64	54	46	41	47	41	37	41	36	32	35	31	28	25
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	36	31	38	33	28	33	29	25	29	25	22	20
8	55	42	34	29	51	40	33	28	35	29	25	31	26	22	26	23	20	18
9	51	39	31	26	48	36	30	25	32	26	22	28	24	20	24	21	18	16
10	48	36	28	23	44	34	27	22	30	24	20	26	21	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19678	19678	19678
5°	19770	19498	19634
10°	19638	19329	19449
15°	19409	19110	19146
20°	19140	18798	18816
25°	18781	18427	18389
30°	18385	18013	17877
35°	17971	17578	17350
40°	17537	17096	16831
45°	17061	16653	16247
50°	16583	16109	15662
55°	15959	15546	15073
60°	15330	14889	14415
65°	14772	14174	13733
70°	13951	13357	12765
75°	12747	12289	11765
80°	11499	11009	10916
85°	10090	9707	9324



TEST NUMBER: P332227

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.2	2.1
10°-20°	486.2	5.8
20°-30°	718.3	8.6
30°-40°	839.0	10.1
40°-50°	843.5	10.1
50°-60°	740.9	8.9
60°-70°	552.0	6.6
70°-80°	314.5	3.8
80°-90°	94.1	1.1
90°-100°	84.0	1.0
100°-110°	251.5	3.0
110°-120°	427.7	5.1
120°-130°	562.6	6.8
130°-140°	632.3	7.6
140°-150°	621.6	7.5
150°-160°	523.3	6.3
160°-170°	348.3	4.2
170°-180°	122.0	1.5
0°-30°	1376.7	16.5
0°-40°	2215.7	26.6
0°-60°	3800.2	45.6
0°-90°	4760.8	57.1
90°-120°	763.2	9.2
90°-150°	2579.7	31.0
90°-180°	3573.0	42.9
0°-180°	8334.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1828	1828	1828	1828	1828	
5°	1830	1821	1804	1819	1817	173
15°	1742	1735	1715	1726	1718	491
25°	1581	1571	1552	1553	1548	728
35°	1368	1358	1338	1328	1320	855
45°	1121	1114	1094	1076	1067	865
55°	850	848	828	812	803	761
65°	580	572	556	544	539	572
75°	306	300	296	288	283	328
85°	82	79	79	76	76	90
90°	1	11	24	28	30	8
95°	60	67	75	79	79	67
105°	228	230	239	239	241	244
115°	431	433	432	432	432	426
125°	630	633	631	627	623	562
135°	818	823	823	819	817	630
145°	992	994	997	996	992	619
155°	1136	1136	1137	1140	1134	523
165°	1237	1234	1234	1239	1233	349
175°	1287	1283	1283	1288	1282	122
180°	1290	1290	1290	1290	1290	



TEST NUMBER: P332227

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1834.4	1833.3	1832.2	1831.1	1829.9	1827.8	1824.8	1821.7	1818.6	1815.5	1818.3
5°	1829.7	1828.0	1826.2	1824.5	1822.7	1819.9	1816.1	1812.2	1808.4	1804.5	1808.0
7.5°	1811.8	1810.0	1808.3	1806.5	1804.8	1801.9	1797.9	1794.0	1790.0	1786.0	1789.1
10°	1796.7	1794.9	1793.2	1791.4	1789.7	1786.6	1782.0	1777.5	1772.9	1768.4	1771.5
12.5°	1776.6	1775.1	1773.6	1772.2	1770.7	1767.8	1763.6	1759.3	1755.0	1750.8	1753.1
15°	1741.7	1740.3	1738.9	1737.5	1736.1	1733.1	1728.6	1724.0	1719.5	1714.9	1717.7
17.5°	1701.1	1699.3	1697.5	1695.7	1693.8	1690.7	1686.1	1681.6	1677.0	1672.5	1674.5
20°	1670.9	1668.8	1666.7	1664.6	1662.6	1659.2	1654.7	1650.2	1645.6	1641.1	1642.5
22.5°	1637.0	1634.9	1632.8	1630.7	1628.6	1625.3	1620.7	1616.2	1611.7	1607.1	1608.2
25°	1581.3	1579.2	1577.1	1575.0	1573.0	1569.6	1565.1	1560.6	1556.0	1551.5	1551.8
27.5°	1521.9	1519.9	1517.9	1515.8	1513.8	1510.4	1505.5	1500.6	1495.7	1490.8	1491.1
30°	1479.2	1477.4	1475.7	1473.9	1472.2	1468.9	1464.0	1459.1	1454.2	1449.3	1449.3
32.5°	1436.4	1434.1	1431.8	1429.5	1427.2	1424.1	1420.4	1416.6	1412.8	1409.1	1407.1
35°	1367.6	1365.5	1363.4	1361.3	1359.2	1355.9	1351.3	1346.8	1342.2	1337.7	1335.6
37.5°	1297.1	1294.5	1291.8	1289.2	1286.5	1282.9	1278.3	1273.7	1269.1	1264.4	1261.9
40°	1248.1	1246.0	1243.9	1241.8	1239.7	1236.2	1231.3	1226.4	1221.5	1216.7	1213.9
42.5°	1199.0	1196.7	1194.3	1191.9	1189.5	1185.9	1181.0	1176.1	1171.2	1166.4	1163.6
45°	1120.8	1119.4	1118.0	1116.6	1115.2	1112.2	1107.7	1103.1	1098.6	1094.0	1089.9
47.5°	1043.1	1041.1	1039.1	1037.0	1035.0	1031.9	1027.6	1023.3	1019.1	1014.8	1010.7
50°	990.3	988.6	986.8	985.1	983.3	980.2	975.6	971.1	966.5	962.0	958.2
52.5°	935.0	933.8	932.6	931.4	930.2	927.2	922.4	917.6	912.8	907.9	904.6
55°	850.4	850.1	849.7	849.4	849.0	846.6	842.0	837.5	832.9	828.4	824.6
57.5°	769.9	768.7	767.5	766.4	765.2	762.8	759.1	755.5	751.9	748.2	744.8
60°	712.1	711.7	711.4	711.0	710.7	708.4	704.2	700.0	695.8	691.6	688.5
62.5°	660.5	659.6	658.7	657.8	656.9	654.3	650.1	645.9	641.8	637.6	634.4
65°	580.0	578.3	576.5	574.8	573.0	570.4	566.9	563.4	559.9	556.5	553.7
67.5°	494.8	493.3	491.8	490.2	488.7	486.6	483.9	481.3	478.6	476.0	473.5
70°	443.3	441.2	439.1	437.0	434.9	432.8	430.7	428.6	426.5	424.4	422.0
72.5°	389.2	387.7	386.1	384.6	383.1	381.1	378.7	376.3	374.0	371.6	369.4
75°	306.5	305.1	303.7	302.3	300.9	299.7	298.7	297.6	296.6	295.5	293.8
77.5°	233.3	232.5	231.7	231.0	230.2	229.2	227.9	226.7	225.4	224.2	223.0
80°	185.5	184.4	183.4	182.3	181.3	180.4	179.7	179.0	178.3	177.6	177.3
82.5°	139.0	138.7	138.5	138.3	138.1	137.9	137.8	137.7	137.5	137.4	136.8
85°	81.7	81.0	80.3	79.6	78.9	78.6	78.6	78.6	78.6	78.6	77.9
87.5°	32.9	32.5	32.1	31.7	31.3	31.3	31.6	31.9	32.2	32.5	32.4
90°	1.0	3.3	5.5	7.8	10.0	12.6	15.5	18.5	21.4	24.3	25.2
92.5°	24.5	26.0	27.6	29.1	30.6	32.2	33.9	35.6	37.2	38.9	39.6
95°	59.8	61.3	62.9	64.5	66.1	67.8	69.6	71.4	73.2	75.0	75.9
97.5°	106.2	107.3	108.5	109.7	110.9	112.1	113.4	114.7	116.0	117.3	118.4
100°	137.8	139.1	140.5	141.8	143.2	144.4	145.6	146.7	147.8	148.9	149.6
102.5°	174.3	175.1	175.9	176.7	177.5	178.6	180.1	181.6	183.1	184.6	185.3
105°	228.0	228.4	228.9	229.3	229.8	231.0	233.0	235.0	237.1	239.1	239.1
107.5°	290.4	290.6	290.9	291.2	291.4	292.0	292.8	293.6	294.4	295.2	295.9
110°	329.3	329.7	330.2	330.6	331.1	331.5	332.0	332.4	332.9	333.3	334.2



TEST NUMBER: P332227

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	369.8	370.1	370.3	370.6	370.9	371.0	371.1	371.2	371.3	371.4	372.5
115°	430.6	431.2	431.9	432.6	433.3	433.4	432.9	432.5	432.0	431.6	431.8
117.5°	491.8	492.2	492.7	493.1	493.6	493.5	492.9	492.3	491.7	491.2	491.1
120°	529.9	531.2	532.6	533.9	535.3	535.4	534.2	533.1	532.0	530.9	530.6
122.5°	569.6	570.6	571.6	572.5	573.5	573.7	573.2	572.6	572.0	571.4	570.8
125°	630.2	630.8	631.5	632.2	632.9	633.0	632.5	632.1	631.6	631.2	630.3
127.5°	686.1	687.5	689.0	690.4	691.8	692.3	691.8	691.3	690.8	690.3	689.1
130°	723.4	725.2	727.0	728.8	730.6	731.1	730.5	729.8	729.1	728.4	727.5
132.5°	760.6	762.4	764.2	766.1	767.9	768.5	768.0	767.5	767.0	766.5	765.4
135°	817.6	818.9	820.3	821.6	823.0	823.5	823.3	823.1	822.9	822.6	821.7
137.5°	870.3	871.4	872.5	873.6	874.8	875.6	876.2	876.8	877.4	878.0	877.0
140°	906.7	907.9	909.0	910.1	911.2	911.9	912.1	912.4	912.6	912.8	912.6
142.5°	940.0	941.1	942.2	943.3	944.5	945.2	945.6	946.0	946.5	946.9	946.6
145°	991.8	992.3	992.7	993.2	993.6	994.2	994.9	995.6	996.2	996.9	996.7
147.5°	1037.2	1038.0	1038.8	1039.7	1040.5	1041.2	1041.8	1042.5	1043.1	1043.7	1043.7
150°	1068.8	1069.3	1069.7	1070.2	1070.6	1071.1	1071.5	1072.0	1072.4	1072.9	1072.9
152.5°	1094.8	1095.4	1096.0	1096.7	1097.3	1097.7	1098.0	1098.3	1098.6	1098.8	1099.2
155°	1135.7	1135.7	1135.7	1135.7	1135.7	1135.8	1136.0	1136.3	1136.5	1136.7	1137.6
157.5°	1170.6	1170.3	1170.0	1169.7	1169.5	1169.4	1169.6	1169.8	1170.0	1170.1	1171.1
160°	1192.4	1192.0	1191.5	1191.1	1190.6	1190.4	1190.4	1190.4	1190.4	1190.4	1191.5
162.5°	1211.9	1211.3	1210.6	1210.0	1209.4	1209.1	1209.3	1209.5	1209.7	1209.9	1211.0
165°	1237.0	1236.3	1235.7	1235.0	1234.3	1234.0	1234.0	1234.0	1234.0	1234.0	1235.3
167.5°	1257.1	1256.2	1255.3	1254.4	1253.5	1253.1	1253.3	1253.5	1253.7	1253.8	1255.2
170°	1268.4	1267.5	1266.6	1265.7	1264.8	1264.4	1264.4	1264.4	1264.4	1264.4	1265.9
172.5°	1277.3	1276.4	1275.5	1274.6	1273.7	1273.3	1273.3	1273.3	1273.3	1273.3	1274.7
175°	1286.7	1285.8	1284.9	1284.0	1283.1	1282.6	1282.6	1282.6	1282.6	1282.6	1284.0
177.5°	1290.5	1289.8	1289.1	1288.3	1287.6	1287.3	1287.3	1287.3	1287.3	1287.3	1288.3
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7



TEST NUMBER: P332227

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1	1828.1
2.5°	1821.1	1823.9	1826.7	1828.0	1827.7	1827.4	1827.1	1826.9
5°	1811.5	1815.0	1818.5	1819.9	1819.2	1818.5	1817.8	1817.1
7.5°	1792.3	1795.4	1798.6	1799.9	1799.5	1799.1	1798.7	1798.3
10°	1774.7	1777.8	1781.0	1782.2	1781.5	1780.8	1780.1	1779.4
12.5°	1755.4	1757.7	1760.0	1761.0	1760.5	1760.1	1759.7	1759.3
15°	1720.5	1723.3	1726.1	1726.5	1724.4	1722.3	1720.2	1718.1
17.5°	1676.4	1678.4	1680.3	1680.9	1680.2	1679.4	1678.6	1677.9
20°	1643.9	1645.3	1646.7	1646.8	1645.8	1644.7	1643.7	1642.6
22.5°	1609.4	1610.5	1611.6	1611.5	1610.2	1608.8	1607.5	1606.2
25°	1552.2	1552.5	1552.9	1552.5	1551.5	1550.4	1549.4	1548.3
27.5°	1491.4	1491.6	1491.9	1491.4	1490.1	1488.7	1487.4	1486.1
30°	1449.3	1449.3	1449.3	1448.1	1445.6	1443.2	1440.7	1438.3
32.5°	1405.1	1403.2	1401.2	1399.6	1398.3	1396.9	1395.6	1394.3
35°	1333.5	1331.4	1329.3	1327.4	1325.6	1323.9	1322.1	1320.4
37.5°	1259.4	1256.9	1254.4	1252.6	1251.4	1250.3	1249.2	1248.1
40°	1211.1	1208.3	1205.5	1203.4	1202.0	1200.6	1199.2	1197.8
42.5°	1160.8	1158.0	1155.2	1153.1	1151.7	1150.3	1148.9	1147.5
45°	1085.7	1081.5	1077.3	1074.3	1072.6	1070.8	1069.1	1067.3
47.5°	1006.6	1002.5	998.3	995.5	994.0	992.4	990.9	989.4
50°	954.3	950.5	946.6	943.7	941.6	939.5	937.4	935.3
52.5°	901.4	898.1	894.8	892.1	890.0	887.9	885.8	883.7
55°	820.7	816.9	813.0	810.2	808.5	806.7	805.0	803.2
57.5°	741.4	738.0	734.5	731.8	729.8	727.8	725.7	723.7
60°	685.4	682.2	679.1	676.6	674.9	673.1	671.4	669.6
62.5°	631.3	628.1	625.0	622.8	621.6	620.4	619.3	618.1
65°	550.9	548.1	545.3	543.4	542.3	541.3	540.2	539.2
67.5°	471.1	468.6	466.2	464.2	462.8	461.3	459.8	458.4
70°	419.5	417.1	414.6	412.5	410.8	409.0	407.3	405.6
72.5°	367.3	365.1	362.9	361.4	360.5	359.6	358.7	357.8
75°	292.0	290.3	288.5	287.1	286.1	285.0	284.0	282.9
77.5°	221.8	220.6	219.4	218.8	218.8	218.8	218.8	218.8
80°	176.9	176.6	176.2	176.1	176.1	176.1	176.1	176.1
82.5°	136.1	135.5	134.9	134.4	134.1	133.9	133.6	133.3
85°	77.2	76.5	75.8	75.5	75.5	75.5	75.5	75.5
87.5°	32.3	32.2	32.1	32.1	32.2	32.3	32.4	32.5
90°	26.1	27.0	27.9	28.6	29.0	29.5	29.9	30.4
92.5°	40.3	41.1	41.8	42.0	41.7	41.5	41.2	40.9
95°	76.8	77.7	78.6	79.0	79.0	79.0	79.0	79.0
97.5°	119.4	120.4	121.5	121.9	121.8	121.8	121.7	121.6
100°	150.3	151.0	151.6	152.2	152.6	153.1	153.5	154.0
102.5°	185.9	186.6	187.3	187.6	187.5	187.4	187.3	187.2
105°	239.1	239.1	239.1	239.3	239.8	240.2	240.7	241.1
107.5°	296.7	297.4	298.1	298.3	298.1	297.8	297.5	297.2
110°	335.1	336.0	336.9	337.1	336.7	336.2	335.8	335.3



TEST NUMBER: P332227

CATALOG NUMBER: S123DIW-S1165D1030U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	373.6	374.6	375.7	376.2	376.1	376.0	376.0	375.9
115°	432.0	432.3	432.5	432.5	432.3	432.0	431.8	431.6
117.5°	491.1	491.0	491.0	490.6	490.0	489.4	488.7	488.1
120°	530.4	530.2	530.0	529.6	529.2	528.7	528.3	527.8
122.5°	570.2	569.6	569.1	568.4	567.8	567.2	566.6	565.9
125°	629.4	628.5	627.6	626.7	625.8	624.9	624.0	623.1
127.5°	687.8	686.6	685.3	684.1	683.1	682.1	681.0	680.0
130°	726.6	725.7	724.8	723.6	722.0	720.4	718.9	717.3
132.5°	764.4	763.3	762.2	761.1	759.8	758.6	757.4	756.2
135°	820.8	819.9	819.0	818.4	817.9	817.5	817.0	816.6
137.5°	876.1	875.1	874.2	873.3	872.4	871.6	870.7	869.9
140°	912.4	912.1	911.9	911.0	909.4	907.9	906.3	904.7
142.5°	946.4	946.2	946.0	945.2	944.0	942.8	941.6	940.4
145°	996.5	996.2	996.0	995.4	994.5	993.6	992.7	991.8
147.5°	1043.7	1043.7	1043.7	1043.0	1041.7	1040.3	1039.0	1037.6
150°	1072.9	1072.9	1072.9	1072.2	1070.9	1069.5	1068.2	1066.8
152.5°	1099.5	1099.9	1100.3	1099.9	1098.7	1097.5	1096.3	1095.2
155°	1138.5	1139.4	1140.3	1140.0	1138.4	1136.8	1135.3	1133.7
157.5°	1172.0	1173.0	1173.9	1173.8	1172.5	1171.3	1170.0	1168.7
160°	1192.7	1193.8	1194.9	1195.0	1194.1	1193.2	1192.3	1191.4
162.5°	1212.1	1213.2	1214.4	1214.2	1212.8	1211.3	1209.9	1208.4
165°	1236.7	1238.0	1239.4	1239.3	1237.7	1236.1	1234.5	1233.0
167.5°	1256.6	1258.0	1259.4	1259.4	1258.0	1256.6	1255.2	1253.8
170°	1267.5	1269.1	1270.7	1270.7	1269.1	1267.5	1265.9	1264.4
172.5°	1276.1	1277.5	1278.9	1278.8	1277.2	1275.6	1274.0	1272.5
175°	1285.3	1286.7	1288.0	1287.9	1286.3	1284.7	1283.2	1281.6
177.5°	1289.4	1290.5	1291.6	1291.5	1290.2	1289.0	1287.7	1286.5
180°	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7	1289.7

(END OF REPORT)