

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332205-927

Luminaire Tested: **S123DIW-S1000D1535U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332205-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1000D1535U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7576.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				
1	97	93	89	85	88	85	82	79	71	68	66	58	56	55	45	44	43	38				
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37	32				
3	81	71	64	59	74	66	60	55	55	50	47	45	42	39	36	34	32	27				
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	27	24				
5	68	56	48	43	62	52	45	40	44	39	34	36	32	29	29	26	24	21				
6	62	51	43	37	57	47	40	35	39	34	30	33	29	26	26	23	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	24	27	23	20	22	19	17	14				
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13				
10	47	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11976	11976	11976	11976
5°	14282	12028	10659	12028
10°	17876	11967	9627	11967
15°	21926	11870	8963	11870
20°	26120	11720	8534	11720
25°	27736	11537	8438	11537
30°	23772	11404	8483	11404
35°	16533	11213	8571	11213
40°	12452	10991	8545	10991
45°	10339	10660	8435	10660
50°	9262	9984	8359	9984
55°	8659	9256	8255	9256
60°	8122	8495	8170	8495
65°	7636	7743	7908	7743
70°	7160	6889	7531	6889
75°	6413	6030	6904	6030
80°	5610	4947	5945	4947
85°	4397	3594	3989	3594



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.6	1.4
10°-20°	351.5	4.6
20°-30°	589.8	7.8
30°-40°	667.9	8.8
40°-50°	598.9	7.9
50°-60°	483.3	6.4
60°-70°	336.8	4.4
70°-80°	177.0	2.3
80°-90°	47.8	0.6
90°-100°	99.1	1.3
100°-110°	296.5	3.9
110°-120°	504.3	6.7
120°-130°	663.4	8.8
130°-140°	745.6	9.8
140°-150°	732.9	9.7
150°-160°	617.0	8.1
160°-170°	410.7	5.4
170°-180°	143.8	1.9
0°-30°	1050.9	13.9
0°-40°	1718.8	22.7
0°-60°	2801.1	37.0
0°-90°	3362.7	44.4
90°-120°	899.9	11.9
90°-150°	3041.8	40.1
90°-180°	4213.0	55.6
0°-180°	7576.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1113	1113	1113	1113	1113	
5°	1322	1113	986	1113	1322	137
15°	1968	1065	804	1065	1968	568
25°	2335	971	710	971	2335	1024
35°	1258	853	652	853	1258	817
45°	679	700	554	700	679	537
55°	461	493	440	493	461	414
65°	300	304	310	304	300	298
75°	154	145	166	145	154	165
85°	36	29	32	29	36	43
90°	36	1	36	1	36	19
95°	93	70	93	70	93	96
105°	284	269	284	269	284	302
115°	509	508	509	508	509	504
125°	735	743	735	743	735	657
135°	963	964	963	964	963	740
145°	1170	1170	1170	1170	1170	730
155°	1337	1339	1337	1339	1337	615
165°	1454	1459	1454	1459	1454	410
175°	1511	1517	1511	1517	1511	144
180°	1521	1521	1521	1521	1521	



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1180.7	1180.0	1177.7	1179.5	1176.1	1171.3	1170.8	1166.6	1154.1	1153.2	1149.8
5°	1321.8	1317.5	1316.9	1316.4	1308.8	1298.6	1279.2	1277.6	1251.7	1238.8	1223.1
7.5°	1504.4	1506.7	1498.8	1491.9	1468.9	1453.7	1432.8	1406.2	1374.4	1342.2	1320.7
10°	1635.5	1653.4	1631.3	1616.1	1602.1	1575.7	1545.0	1506.7	1468.5	1423.7	1389.7
12.5°	1776.2	1784.9	1780.4	1766.2	1744.5	1704.2	1649.8	1607.7	1572.4	1497.9	1467.8
15°	1967.6	2000.5	1979.5	1930.9	1932.1	1893.8	1822.6	1744.5	1703.0	1637.7	1548.8
17.5°	2171.6	2175.7	2166.8	2126.3	2099.4	2046.8	1981.1	1906.1	1822.1	1743.1	1648.8
20°	2280.3	2277.0	2258.2	2237.1	2190.8	2149.8	2078.1	1994.6	1886.7	1809.1	1706.2
22.5°	2340.7	2335.3	2326.3	2308.7	2270.2	2226.2	2161.8	2070.4	1967.9	1860.9	1741.9
25°	2335.3	2342.2	2343.4	2338.5	2325.1	2298.6	2247.9	2175.2	2072.7	1935.3	1811.3
27.5°	2123.9	2133.9	2162.7	2188.2	2216.8	2245.9	2242.0	2205.9	2130.1	2011.4	1859.8
30°	1912.6	1891.1	1944.4	2011.8	2057.6	2138.5	2183.8	2186.5	2143.9	2042.0	1894.3
32.5°	1619.4	1643.1	1666.7	1749.6	1849.7	1940.5	2030.7	2103.2	2111.6	2043.8	1914.5
35°	1258.2	1287.9	1330.9	1374.1	1481.9	1574.6	1733.1	1871.1	1981.1	1995.7	1916.4
37.5°	1013.9	1028.6	1055.8	1099.1	1169.6	1279.5	1402.2	1576.6	1735.9	1854.4	1859.6
40°	886.2	890.6	921.3	954.2	1011.3	1101.8	1212.4	1366.5	1557.4	1722.9	1791.9
42.5°	790.5	799.9	813.0	844.6	890.1	958.2	1061.0	1188.4	1363.3	1553.8	1688.8
45°	679.2	690.0	698.1	719.1	751.5	797.3	869.0	985.4	1118.6	1315.3	1497.0
47.5°	605.7	606.6	612.6	628.4	650.5	684.8	735.5	810.3	932.6	1092.2	1278.7
50°	553.1	561.7	563.9	576.2	593.5	618.9	660.9	724.5	824.8	965.0	1136.4
52.5°	516.0	518.6	524.7	533.6	548.7	568.4	604.8	654.7	733.3	852.8	1010.4
55°	461.4	461.4	467.4	474.4	483.0	500.8	525.1	561.7	621.5	714.3	844.7
57.5°	411.0	413.7	417.9	420.0	427.4	439.1	459.4	487.2	531.9	603.2	706.9
60°	377.3	382.2	381.7	386.0	392.4	401.6	418.8	441.5	481.4	538.5	625.9
62.5°	348.0	347.7	347.6	352.8	359.3	368.0	379.2	398.8	432.7	483.3	557.7
65°	299.8	298.7	302.5	305.6	307.8	314.3	322.9	340.2	362.8	400.5	458.2
67.5°	256.8	253.7	255.7	256.8	260.5	265.5	273.6	284.3	302.3	332.6	376.0
70°	227.5	224.8	224.3	225.3	228.5	232.3	238.3	248.5	265.2	289.5	321.3
72.5°	197.3	195.4	195.4	197.7	199.2	201.7	205.9	215.3	228.5	246.8	276.5
75°	154.2	154.2	154.2	154.7	156.3	158.5	161.7	166.6	176.8	189.7	209.7
77.5°	115.6	115.5	114.8	114.7	117.1	118.0	118.8	123.3	129.0	137.8	152.3
80°	90.5	87.9	89.0	90.5	91.7	92.2	93.8	94.9	99.7	104.6	114.8
82.5°	67.3	65.0	65.2	67.7	67.9	68.4	70.1	71.6	73.4	77.9	83.3
85°	35.6	35.6	36.1	36.1	36.7	36.1	37.7	38.3	38.3	41.0	44.2
87.5°	20.1	19.2	19.5	19.8	19.3	19.5	19.7	20.0	20.2	20.4	20.1
90°	35.8	35.3	34.8	34.2	33.7	33.0	31.8	30.8	29.7	28.7	25.2
92.5°	48.2	48.6	48.9	49.2	49.5	49.3	48.4	47.5	46.7	45.9	43.9
95°	93.2	93.2	93.2	93.2	93.2	92.6	91.6	90.5	89.4	88.4	86.3
97.5°	143.4	143.5	143.5	143.7	143.8	143.2	142.0	140.8	139.6	138.3	136.8
100°	181.6	181.0	180.5	180.0	179.4	178.8	178.0	177.2	176.4	175.6	174.3
102.5°	220.8	220.9	220.9	221.1	221.2	220.9	220.1	219.3	218.5	217.6	215.9
105°	284.3	283.8	283.3	282.7	282.2	281.9	281.9	281.9	281.9	281.9	279.6
107.5°	350.5	350.8	351.1	351.4	351.7	351.5	350.6	349.8	349.0	348.1	347.1
110°	395.4	395.9	396.5	397.0	397.5	397.3	396.2	395.1	394.1	393.0	392.4



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	443.1	443.3	443.4	443.5	443.6	443.0	441.7	440.5	439.2	437.9	437.8
115°	508.9	509.1	509.5	509.7	509.9	509.9	509.7	509.5	509.1	508.9	509.5
117.5°	575.5	576.3	577.0	577.7	578.5	578.9	579.0	579.0	579.1	579.2	579.8
120°	622.3	622.9	623.4	624.0	624.5	624.9	625.2	625.4	625.7	626.0	627.2
122.5°	667.3	668.0	668.8	669.6	670.3	671.0	671.7	672.3	673.0	673.8	674.5
125°	734.7	735.7	736.8	737.8	738.9	740.0	741.0	742.1	743.1	744.3	744.7
127.5°	801.8	803.0	804.2	805.5	806.7	808.0	809.5	811.0	812.5	814.0	814.6
130°	845.7	847.6	849.5	851.4	853.2	854.7	855.7	856.7	857.9	858.9	859.7
132.5°	891.6	893.0	894.5	896.0	897.4	898.7	900.0	901.3	902.5	903.8	904.4
135°	962.8	963.4	963.8	964.4	965.0	965.7	966.8	967.9	968.9	970.0	970.3
137.5°	1025.6	1026.7	1027.7	1028.6	1029.7	1030.8	1031.9	1033.0	1034.1	1035.2	1034.5
140°	1066.8	1068.6	1070.5	1072.3	1074.2	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0
142.5°	1108.8	1110.2	1111.7	1113.1	1114.5	1115.4	1115.6	1115.9	1116.2	1116.4	1115.9
145°	1169.5	1170.5	1171.6	1172.7	1173.7	1174.4	1174.6	1174.9	1175.2	1175.4	1174.6
147.5°	1223.4	1225.0	1226.7	1228.3	1229.9	1230.7	1230.7	1230.7	1230.7	1230.7	1229.9
150°	1257.9	1259.5	1261.1	1262.7	1264.2	1265.0	1265.0	1265.0	1265.0	1265.0	1264.5
152.5°	1291.3	1292.7	1294.1	1295.5	1296.9	1297.4	1296.9	1296.5	1296.1	1295.6	1295.3
155°	1336.7	1338.6	1340.5	1342.3	1344.2	1344.6	1343.5	1342.4	1341.4	1340.3	1340.1
157.5°	1378.1	1379.5	1381.0	1382.5	1384.0	1384.2	1383.1	1382.0	1380.9	1379.7	1379.5
160°	1404.8	1405.9	1406.9	1408.0	1409.1	1408.9	1407.6	1406.3	1404.9	1403.6	1403.6
162.5°	1424.9	1426.6	1428.3	1430.0	1431.7	1431.9	1430.5	1429.2	1427.9	1426.6	1426.3
165°	1453.8	1455.6	1457.5	1459.4	1461.3	1461.3	1459.8	1458.2	1456.6	1455.0	1455.0
167.5°	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4	1478.2
170°	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8	1490.8
172.5°	1500.4	1502.2	1504.1	1505.9	1507.8	1507.9	1506.3	1504.6	1503.0	1501.3	1501.3
175°	1511.2	1513.0	1514.8	1516.7	1518.5	1518.7	1517.1	1515.5	1513.9	1512.4	1512.4
177.5°	1516.9	1518.4	1519.8	1521.3	1522.8	1522.9	1521.6	1520.4	1519.1	1517.8	1517.8
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1147.2	1143.7	1140.3	1134.2	1129.0	1121.7	1119.5	1117.0	1109.2	1102.3	1097.1
5°	1217.2	1204.3	1185.4	1168.2	1154.1	1135.3	1124.5	1113.2	1097.0	1082.4	1070.6
7.5°	1290.5	1265.1	1235.8	1204.0	1174.6	1146.1	1123.1	1102.6	1080.0	1058.5	1041.8
10°	1348.8	1312.1	1271.1	1226.9	1189.2	1152.5	1121.8	1094.9	1065.7	1040.4	1019.4
12.5°	1415.2	1360.8	1304.3	1250.6	1206.0	1155.2	1117.9	1083.6	1050.7	1020.2	996.6
15°	1493.7	1424.7	1358.0	1284.0	1216.2	1152.5	1108.3	1065.2	1026.9	995.7	965.5
17.5°	1565.4	1487.2	1399.1	1309.3	1227.3	1151.9	1090.0	1041.2	993.4	955.1	925.0
20°	1605.9	1516.9	1417.2	1324.0	1233.4	1149.3	1081.4	1023.2	971.4	931.0	897.0
22.5°	1640.8	1536.8	1433.6	1333.9	1233.0	1142.4	1065.4	1005.5	949.4	909.8	873.7
25°	1677.0	1552.5	1449.1	1332.1	1219.4	1125.6	1039.3	971.4	915.4	869.0	831.8
27.5°	1708.1	1551.5	1428.6	1302.8	1198.0	1104.0	1011.9	939.1	879.6	829.2	791.5
30°	1728.8	1553.6	1407.5	1283.0	1177.3	1080.3	990.8	917.5	855.0	803.7	768.2
32.5°	1741.8	1552.3	1388.1	1255.4	1144.5	1058.8	968.0	892.1	827.8	777.4	743.1
35°	1749.3	1542.9	1354.7	1198.3	1091.6	1008.1	932.1	853.3	786.0	739.1	700.3
37.5°	1734.2	1522.9	1315.9	1143.4	1026.5	944.2	880.3	813.3	748.8	697.1	663.7
40°	1710.5	1510.0	1285.7	1104.5	981.7	902.4	848.0	782.2	718.6	669.6	638.3
42.5°	1665.2	1483.6	1252.5	1061.4	935.1	855.8	805.7	750.8	690.5	644.5	613.2
45°	1554.7	1426.4	1202.7	996.7	866.3	784.3	740.1	700.3	645.8	601.0	574.1
47.5°	1401.4	1340.2	1130.7	928.5	794.5	715.7	669.7	637.6	597.9	561.7	535.8
50°	1294.8	1269.6	1081.9	881.9	746.6	669.6	625.3	596.2	567.7	531.6	507.8
52.5°	1172.0	1187.6	1025.0	833.6	697.9	622.1	580.5	557.4	531.4	501.8	481.1
55°	998.9	1055.5	926.7	752.6	625.3	553.1	513.7	493.2	478.2	456.1	438.2
57.5°	836.9	908.9	820.4	669.0	554.1	491.7	454.0	431.7	422.0	410.4	396.4
60°	740.7	811.8	744.5	612.9	506.2	446.9	413.4	394.6	384.9	376.8	365.0
62.5°	654.9	726.9	670.3	556.0	459.1	404.2	375.1	356.6	349.1	344.9	334.8
65°	536.9	598.9	561.2	467.4	391.9	343.4	317.0	304.0	297.1	295.4	288.9
67.5°	437.0	484.2	456.7	387.7	328.3	286.4	264.0	252.9	247.6	247.0	242.2
70°	371.5	415.7	394.6	332.1	280.8	248.0	228.5	218.9	215.6	215.1	212.4
72.5°	320.5	351.3	334.6	282.5	242.9	213.0	198.8	188.7	185.0	185.8	183.9
75°	237.2	260.4	250.6	214.5	182.8	163.3	151.5	145.0	141.8	143.4	141.2
77.5°	170.6	185.4	176.6	151.6	132.0	118.0	109.2	105.2	102.3	102.2	101.2
80°	128.8	137.4	132.6	117.5	101.3	89.5	82.5	79.8	78.2	77.6	77.1
82.5°	91.7	99.1	93.4	83.0	72.0	64.9	60.9	57.4	56.2	56.5	55.9
85°	46.3	49.0	46.9	40.4	36.1	32.9	30.7	29.1	28.0	28.6	27.5
87.5°	20.3	20.0	18.1	15.8	14.3	12.5	12.0	10.6	10.2	10.8	10.9
90°	21.8	18.3	14.9	11.8	9.2	6.5	3.9	1.2	3.9	6.5	9.2
92.5°	41.9	40.0	38.0	36.1	34.3	32.5	30.7	28.9	30.7	32.5	34.3
95°	84.1	82.0	79.9	78.0	76.0	74.2	72.3	70.5	72.3	74.2	76.0
97.5°	135.2	133.7	132.1	130.7	129.4	127.9	126.6	125.2	126.6	127.9	129.4
100°	172.9	171.6	170.3	168.8	167.2	165.6	164.1	162.5	164.1	165.6	167.2
102.5°	214.1	212.4	210.6	209.3	208.3	207.4	206.4	205.5	206.4	207.4	208.3
105°	277.1	274.7	272.4	270.9	270.4	269.8	269.3	268.8	269.3	269.8	270.4
107.5°	346.2	345.2	344.3	343.6	343.3	343.0	342.7	342.4	342.7	343.0	343.3
110°	392.0	391.4	390.9	390.4	389.8	389.3	388.8	388.2	388.8	389.3	389.8



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	437.7	437.6	437.5	437.3	437.0	436.7	436.3	436.0	436.3	436.7	437.0
115°	509.9	510.5	511.0	510.9	510.1	509.3	508.5	507.7	508.5	509.3	510.1
117.5°	580.5	581.2	581.9	581.9	581.5	580.9	580.4	579.9	580.4	580.9	581.5
120°	628.6	629.9	631.3	631.1	629.5	628.0	626.4	624.8	626.4	628.0	629.5
122.5°	675.1	675.8	676.5	676.3	675.1	673.9	672.7	671.6	672.7	673.9	675.1
125°	745.3	745.8	746.3	746.2	745.4	744.7	743.8	743.0	743.8	744.7	745.4
127.5°	815.2	815.7	816.3	815.8	814.0	812.4	810.6	809.0	810.6	812.4	814.0
130°	860.5	861.3	862.1	861.4	859.3	857.1	855.1	852.9	855.1	857.1	859.3
132.5°	905.0	905.5	906.2	905.4	903.2	901.1	899.0	896.9	899.0	901.1	903.2
135°	970.5	970.8	971.1	970.4	968.8	967.2	965.6	964.0	965.6	967.2	968.8
137.5°	1033.8	1033.2	1032.5	1031.4	1030.2	1028.8	1027.5	1026.1	1027.5	1028.8	1030.2
140°	1075.8	1075.5	1075.2	1074.4	1073.1	1071.8	1070.5	1069.1	1070.5	1071.8	1073.1
142.5°	1115.5	1115.0	1114.5	1113.6	1112.3	1111.0	1109.6	1108.3	1109.6	1111.0	1112.3
145°	1173.9	1173.1	1172.3	1171.6	1171.1	1170.5	1170.1	1169.5	1170.1	1170.5	1171.1
147.5°	1229.2	1228.4	1227.6	1226.9	1225.9	1224.9	1223.9	1223.0	1223.9	1224.9	1225.9
150°	1264.0	1263.5	1262.9	1262.4	1261.9	1261.3	1260.8	1260.3	1260.8	1261.3	1261.9
152.5°	1295.0	1294.7	1294.3	1293.8	1293.1	1292.4	1291.6	1290.9	1291.6	1292.4	1293.1
155°	1339.7	1339.5	1339.3	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1
157.5°	1379.3	1379.1	1378.9	1379.0	1379.3	1379.6	1379.9	1380.2	1379.9	1379.6	1379.3
160°	1403.6	1403.6	1403.6	1403.9	1404.4	1404.9	1405.5	1406.0	1405.5	1404.9	1404.4
162.5°	1426.2	1425.9	1425.7	1426.0	1426.7	1427.4	1428.2	1428.9	1428.2	1427.4	1426.7
165°	1455.0	1455.0	1455.0	1455.4	1456.2	1457.0	1457.8	1458.6	1457.8	1457.0	1456.2
167.5°	1478.0	1477.7	1477.6	1478.0	1479.0	1480.1	1481.1	1482.3	1481.1	1480.1	1479.0
170°	1490.8	1490.8	1490.8	1491.4	1492.4	1493.5	1494.5	1495.6	1494.5	1493.5	1492.4
172.5°	1501.3	1501.3	1501.3	1501.9	1502.9	1504.0	1505.1	1506.1	1505.1	1504.0	1502.9
175°	1512.4	1512.4	1512.4	1512.8	1513.9	1515.0	1516.1	1517.1	1516.1	1515.0	1513.9
177.5°	1517.8	1517.8	1517.8	1518.2	1519.1	1520.0	1520.8	1521.6	1520.8	1520.0	1519.1
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1094.1	1091.1	1086.8	1080.3	1075.1	1066.9	1066.9	1068.3	1068.3	1067.8	1066.9
5°	1060.9	1052.8	1043.1	1031.8	1019.9	1008.1	1005.9	1001.6	998.4	996.2	993.5
7.5°	1025.9	1011.5	997.4	981.5	967.1	955.1	946.8	939.9	935.5	930.7	927.3
10°	1002.1	984.4	967.7	950.9	932.6	918.1	908.9	902.4	897.5	893.3	891.1
12.5°	974.1	953.7	935.3	919.4	899.4	884.4	875.7	872.7	867.0	857.9	853.1
15°	933.1	914.3	892.2	867.9	858.2	839.9	829.7	824.8	821.6	814.5	812.4
17.5°	898.1	873.4	848.6	830.5	812.5	797.6	791.9	785.8	781.6	775.9	774.1
20°	870.1	848.0	825.3	805.9	787.0	770.9	766.0	761.7	757.4	754.7	752.6
22.5°	841.6	819.5	800.7	782.6	762.5	751.9	746.6	741.9	738.9	737.0	734.8
25°	801.6	782.2	761.2	745.0	728.8	721.8	718.6	715.9	713.8	711.1	710.5
27.5°	765.8	744.7	727.6	712.6	700.9	695.1	692.0	690.6	691.1	692.1	692.7
30°	739.1	719.7	705.7	692.7	681.9	676.5	676.0	676.0	678.2	678.7	679.8
32.5°	714.5	698.5	684.5	672.0	663.8	660.1	662.2	662.2	663.9	665.4	667.3
35°	678.7	664.6	653.9	643.1	636.1	637.7	638.8	639.8	642.5	645.8	648.0
37.5°	644.5	632.3	621.2	612.7	609.5	612.4	615.0	617.3	620.4	622.8	625.0
40°	620.0	610.8	600.0	592.5	593.5	595.2	597.3	600.0	602.7	604.3	606.5
42.5°	597.1	587.5	579.3	573.1	574.6	576.6	577.9	579.3	582.4	585.3	586.6
45°	562.3	554.7	547.2	543.4	544.5	545.6	546.6	548.3	551.0	553.1	553.7
47.5°	523.1	517.8	512.8	509.1	510.8	510.4	511.8	515.2	516.1	517.4	520.4
50°	498.1	493.2	487.4	486.2	486.2	486.2	486.8	491.1	491.1	493.2	495.4
52.5°	470.5	467.4	463.6	461.7	460.8	460.8	463.0	465.2	466.1	469.1	471.3
55°	429.7	426.4	423.2	421.5	420.5	421.5	425.9	426.9	429.7	431.3	432.8
57.5°	387.1	384.6	382.0	381.1	380.9	382.3	384.7	387.9	388.6	393.6	396.0
60°	359.0	355.2	353.1	353.1	352.0	356.9	355.8	361.2	362.3	365.5	369.2
62.5°	330.1	325.0	324.2	324.2	325.7	327.1	328.6	331.0	333.8	337.9	340.8
65°	283.5	280.8	284.6	284.1	283.0	286.2	286.2	288.9	292.2	296.0	301.9
67.5°	239.5	238.1	238.4	238.4	240.0	241.9	243.4	245.7	249.6	253.6	257.5
70°	209.7	211.4	208.7	210.8	212.4	212.9	214.0	217.2	221.6	224.3	228.5
72.5°	180.8	180.7	181.0	181.9	183.5	184.5	185.5	189.3	193.9	196.2	199.7
75°	139.1	138.6	140.1	140.1	142.8	143.9	145.0	146.6	150.9	154.2	156.9
77.5°	101.6	102.2	101.9	103.7	103.0	103.1	106.5	108.1	108.6	114.9	116.4
80°	76.5	77.6	78.2	78.7	79.2	78.2	81.9	83.6	83.6	87.3	90.0
82.5°	55.0	55.6	57.0	57.6	57.7	58.8	59.1	60.3	61.6	63.2	66.7
85°	27.5	29.1	29.6	29.1	29.6	28.6	30.2	30.7	31.3	31.3	31.3
87.5°	11.0	12.0	12.3	13.4	13.7	14.8	15.0	14.3	14.6	16.1	14.5
90°	11.8	14.9	18.3	21.8	25.2	28.7	29.7	30.8	31.8	33.0	33.7
92.5°	36.1	38.0	40.0	41.9	43.9	45.9	46.7	47.5	48.4	49.3	49.5
95°	78.0	79.9	82.0	84.1	86.3	88.4	89.4	90.5	91.6	92.6	93.2
97.5°	130.7	132.1	133.7	135.2	136.8	138.3	139.6	140.8	142.0	143.2	143.8
100°	168.8	170.3	171.6	172.9	174.3	175.6	176.4	177.2	178.0	178.8	179.4
102.5°	209.3	210.6	212.4	214.1	215.9	217.6	218.5	219.3	220.1	220.9	221.2
105°	270.9	272.4	274.7	277.1	279.6	281.9	281.9	281.9	281.9	281.9	282.2
107.5°	343.6	344.3	345.2	346.2	347.1	348.1	349.0	349.8	350.6	351.5	351.7
110°	390.4	390.9	391.4	392.0	392.4	393.0	394.1	395.1	396.2	397.3	397.5



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	437.3	437.5	437.6	437.7	437.8	437.9	439.2	440.5	441.7	443.0	443.6
115°	510.9	511.0	510.5	509.9	509.5	508.9	509.1	509.5	509.7	509.9	509.9
117.5°	581.9	581.9	581.2	580.5	579.8	579.2	579.1	579.0	579.0	578.9	578.5
120°	631.1	631.3	629.9	628.6	627.2	626.0	625.7	625.4	625.2	624.9	624.5
122.5°	676.3	676.5	675.8	675.1	674.5	673.8	673.0	672.3	671.7	671.0	670.3
125°	746.2	746.3	745.8	745.3	744.7	744.3	743.1	742.1	741.0	740.0	738.9
127.5°	815.8	816.3	815.7	815.2	814.6	814.0	812.5	811.0	809.5	808.0	806.7
130°	861.4	862.1	861.3	860.5	859.7	858.9	857.9	856.7	855.7	854.7	853.2
132.5°	905.4	906.2	905.5	905.0	904.4	903.8	902.5	901.3	900.0	898.7	897.4
135°	970.4	971.1	970.8	970.5	970.3	970.0	968.9	967.9	966.8	965.7	965.0
137.5°	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1	1033.0	1031.9	1030.8	1029.7
140°	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0	1075.8	1075.5	1075.2	1074.2
142.5°	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2	1115.9	1115.6	1115.4	1114.5
145°	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2	1174.9	1174.6	1174.4	1173.7
147.5°	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7	1230.7	1230.7	1230.7	1229.9
150°	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0	1265.0	1265.0	1265.0	1264.2
152.5°	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1	1296.5	1296.9	1297.4	1296.9
155°	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4	1342.4	1343.5	1344.6	1344.2
157.5°	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9	1382.0	1383.1	1384.2	1384.0
160°	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9	1406.3	1407.6	1408.9	1409.1
162.5°	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9	1429.2	1430.5	1431.9	1431.7
165°	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6	1458.2	1459.8	1461.3	1461.3
167.5°	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9
170°	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3
172.5°	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0	1504.6	1506.3	1507.9	1507.8
175°	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9	1515.5	1517.1	1518.7	1518.5
177.5°	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1	1520.4	1521.6	1522.9	1522.8
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1063.9	1063.5	1066.5	1064.4	1066.5	1063.5	1063.9	1066.9	1067.8	1068.3	1068.3
5°	990.3	991.9	986.5	986.5	986.5	991.9	990.3	993.5	996.2	998.4	1001.6
7.5°	924.7	922.3	922.6	919.6	922.6	922.3	924.7	927.3	930.7	935.5	939.9
10°	884.6	881.4	880.3	880.8	880.3	881.4	884.6	891.1	893.3	897.5	902.4
12.5°	851.4	850.8	843.7	843.8	843.7	850.8	851.4	853.1	857.9	867.0	872.7
15°	812.4	802.2	801.1	804.3	801.1	802.2	812.4	812.4	814.5	821.6	824.8
17.5°	773.2	767.9	768.2	766.6	768.2	767.9	773.2	774.1	775.9	781.6	785.8
20°	752.6	749.3	748.8	745.0	748.8	749.3	752.6	752.6	754.7	757.4	761.7
22.5°	733.6	732.5	732.8	728.6	732.8	732.5	733.6	734.8	737.0	738.9	741.9
25°	710.0	712.6	710.5	710.5	710.5	712.6	710.0	710.5	711.1	713.8	715.9
27.5°	694.0	693.9	692.8	692.8	692.8	693.9	694.0	692.7	692.1	691.1	690.6
30°	681.9	681.4	682.5	682.5	682.5	681.4	681.9	679.8	678.7	678.2	676.0
32.5°	669.9	670.6	670.8	671.2	670.8	670.6	669.9	667.3	665.4	663.9	662.2
35°	651.2	651.7	653.4	652.3	653.4	651.7	651.2	648.0	645.8	642.5	639.8
37.5°	626.0	628.4	627.9	628.8	627.9	628.4	626.0	625.0	622.8	620.4	617.3
40°	607.0	608.6	608.1	608.1	608.1	608.6	607.0	606.5	604.3	602.7	600.0
42.5°	587.6	588.7	587.4	586.5	587.4	588.7	587.6	586.6	585.3	582.4	579.3
45°	555.8	554.7	556.3	554.1	556.3	554.7	555.8	553.7	553.1	551.0	548.3
47.5°	520.2	521.3	521.7	523.3	521.7	521.3	520.2	520.4	517.4	516.1	515.2
50°	496.5	499.7	499.7	499.2	499.7	499.7	496.5	495.4	493.2	491.1	491.1
52.5°	473.2	474.7	476.9	476.7	476.9	474.7	473.2	471.3	469.1	466.1	465.2
55°	437.2	438.2	439.3	439.9	439.3	438.2	437.2	432.8	431.3	429.7	426.9
57.5°	399.9	399.4	402.0	402.8	402.0	399.4	399.9	396.0	393.6	388.6	387.9
60°	373.6	373.6	377.9	379.5	377.9	373.6	373.6	369.2	365.5	362.3	361.2
62.5°	345.5	347.3	351.6	349.4	351.6	347.3	345.5	340.8	337.9	333.8	331.0
65°	304.6	308.9	308.3	310.5	308.3	308.9	304.6	301.9	296.0	292.2	288.9
67.5°	261.7	264.4	268.3	268.7	268.3	264.4	261.7	257.5	253.6	249.6	245.7
70°	232.9	235.6	237.7	239.3	237.7	235.6	232.9	228.5	224.3	221.6	217.2
72.5°	204.9	206.3	211.4	209.1	211.4	206.3	204.9	199.7	196.2	193.9	189.3
75°	160.7	164.4	167.6	166.0	167.6	164.4	160.7	156.9	154.2	150.9	146.6
77.5°	118.8	122.6	124.1	122.7	124.1	122.6	118.8	116.4	114.9	108.6	108.1
80°	93.8	93.2	96.5	95.9	96.5	93.2	93.8	90.0	87.3	83.6	83.6
82.5°	68.8	68.3	69.8	70.1	69.8	68.3	68.8	66.7	63.2	61.6	60.3
85°	33.4	35.0	32.9	32.3	32.9	35.0	33.4	31.3	31.3	31.3	30.7
87.5°	14.6	14.7	14.4	14.1	14.4	14.7	14.6	14.5	16.1	14.6	14.3
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	33.0	31.8	30.8
92.5°	49.2	48.9	48.6	48.2	48.6	48.9	49.2	49.5	49.3	48.4	47.5
95°	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2	92.6	91.6	90.5
97.5°	143.7	143.5	143.5	143.4	143.5	143.5	143.7	143.8	143.2	142.0	140.8
100°	180.0	180.5	181.0	181.6	181.0	180.5	180.0	179.4	178.8	178.0	177.2
102.5°	221.1	220.9	220.9	220.8	220.9	220.9	221.1	221.2	220.9	220.1	219.3
105°	282.7	283.3	283.8	284.3	283.8	283.3	282.7	282.2	281.9	281.9	281.9
107.5°	351.4	351.1	350.8	350.5	350.8	351.1	351.4	351.7	351.5	350.6	349.8
110°	397.0	396.5	395.9	395.4	395.9	396.5	397.0	397.5	397.3	396.2	395.1



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	443.5	443.4	443.3	443.1	443.3	443.4	443.5	443.6	443.0	441.7	440.5
115°	509.7	509.5	509.1	508.9	509.1	509.5	509.7	509.9	509.9	509.7	509.5
117.5°	577.7	577.0	576.3	575.5	576.3	577.0	577.7	578.5	578.9	579.0	579.0
120°	624.0	623.4	622.9	622.3	622.9	623.4	624.0	624.5	624.9	625.2	625.4
122.5°	669.6	668.8	668.0	667.3	668.0	668.8	669.6	670.3	671.0	671.7	672.3
125°	737.8	736.8	735.7	734.7	735.7	736.8	737.8	738.9	740.0	741.0	742.1
127.5°	805.5	804.2	803.0	801.8	803.0	804.2	805.5	806.7	808.0	809.5	811.0
130°	851.4	849.5	847.6	845.7	847.6	849.5	851.4	853.2	854.7	855.7	856.7
132.5°	896.0	894.5	893.0	891.6	893.0	894.5	896.0	897.4	898.7	900.0	901.3
135°	964.4	963.8	963.4	962.8	963.4	963.8	964.4	965.0	965.7	966.8	967.9
137.5°	1028.6	1027.7	1026.7	1025.6	1026.7	1027.7	1028.6	1029.7	1030.8	1031.9	1033.0
140°	1072.3	1070.5	1068.6	1066.8	1068.6	1070.5	1072.3	1074.2	1075.2	1075.5	1075.8
142.5°	1113.1	1111.7	1110.2	1108.8	1110.2	1111.7	1113.1	1114.5	1115.4	1115.6	1115.9
145°	1172.7	1171.6	1170.5	1169.5	1170.5	1171.6	1172.7	1173.7	1174.4	1174.6	1174.9
147.5°	1228.3	1226.7	1225.0	1223.4	1225.0	1226.7	1228.3	1229.9	1230.7	1230.7	1230.7
150°	1262.7	1261.1	1259.5	1257.9	1259.5	1261.1	1262.7	1264.2	1265.0	1265.0	1265.0
152.5°	1295.5	1294.1	1292.7	1291.3	1292.7	1294.1	1295.5	1296.9	1297.4	1296.9	1296.5
155°	1342.3	1340.5	1338.6	1336.7	1338.6	1340.5	1342.3	1344.2	1344.6	1343.5	1342.4
157.5°	1382.5	1381.0	1379.5	1378.1	1379.5	1381.0	1382.5	1384.0	1384.2	1383.1	1382.0
160°	1408.0	1406.9	1405.9	1404.8	1405.9	1406.9	1408.0	1409.1	1408.9	1407.6	1406.3
162.5°	1430.0	1428.3	1426.6	1424.9	1426.6	1428.3	1430.0	1431.7	1431.9	1430.5	1429.2
165°	1459.4	1457.5	1455.6	1453.8	1455.6	1457.5	1459.4	1461.3	1461.3	1459.8	1458.2
167.5°	1483.4	1481.7	1480.0	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7
170°	1496.4	1494.5	1492.7	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5
172.5°	1505.9	1504.1	1502.2	1500.4	1502.2	1504.1	1505.9	1507.8	1507.9	1506.3	1504.6
175°	1516.7	1514.8	1513.0	1511.2	1513.0	1514.8	1516.7	1518.5	1518.7	1517.1	1515.5
177.5°	1521.3	1519.8	1518.4	1516.9	1518.4	1519.8	1521.3	1522.8	1522.9	1521.6	1520.4
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1066.9	1066.9	1075.1	1080.3	1086.8	1091.1	1094.1	1097.1	1102.3	1109.2	1117.0
5°	1005.9	1008.1	1019.9	1031.8	1043.1	1052.8	1060.9	1070.6	1082.4	1097.0	1113.2
7.5°	946.8	955.1	967.1	981.5	997.4	1011.5	1025.9	1041.8	1058.5	1080.0	1102.6
10°	908.9	918.1	932.6	950.9	967.7	984.4	1002.1	1019.4	1040.4	1065.7	1094.9
12.5°	875.7	884.4	899.4	919.4	935.3	953.7	974.1	996.6	1020.2	1050.7	1083.6
15°	829.7	839.9	858.2	867.9	892.2	914.3	933.1	965.5	995.7	1026.9	1065.2
17.5°	791.9	797.6	812.5	830.5	848.6	873.4	898.1	925.0	955.1	993.4	1041.2
20°	766.0	770.9	787.0	805.9	825.3	848.0	870.1	897.0	931.0	971.4	1023.2
22.5°	746.6	751.9	762.5	782.6	800.7	819.5	841.6	873.7	909.8	949.4	1005.5
25°	718.6	721.8	728.8	745.0	761.2	782.2	801.6	831.8	869.0	915.4	971.4
27.5°	692.0	695.1	700.9	712.6	727.6	744.7	765.8	791.5	829.2	879.6	939.1
30°	676.0	676.5	681.9	692.7	705.7	719.7	739.1	768.2	803.7	855.0	917.5
32.5°	662.2	660.1	663.8	672.0	684.5	698.5	714.5	743.1	777.4	827.8	892.1
35°	638.8	637.7	636.1	643.1	653.9	664.6	678.7	700.3	739.1	786.0	853.3
37.5°	615.0	612.4	609.5	612.7	621.2	632.3	644.5	663.7	697.1	748.8	813.3
40°	597.3	595.2	593.5	592.5	600.0	610.8	620.0	638.3	669.6	718.6	782.2
42.5°	577.9	576.6	574.6	573.1	579.3	587.5	597.1	613.2	644.5	690.5	750.8
45°	546.6	545.6	544.5	543.4	547.2	554.7	562.3	574.1	601.0	645.8	700.3
47.5°	511.8	510.4	510.8	509.1	512.8	517.8	523.1	535.8	561.7	597.9	637.6
50°	486.8	486.2	486.2	486.2	487.4	493.2	498.1	507.8	531.6	567.7	596.2
52.5°	463.0	460.8	460.8	461.7	463.6	467.4	470.5	481.1	501.8	531.4	557.4
55°	425.9	421.5	420.5	421.5	423.2	426.4	429.7	438.2	456.1	478.2	493.2
57.5°	384.7	382.3	380.9	381.1	382.0	384.6	387.1	396.4	410.4	422.0	431.7
60°	355.8	356.9	352.0	353.1	353.1	355.2	359.0	365.0	376.8	384.9	394.6
62.5°	328.6	327.1	325.7	324.2	324.2	325.0	330.1	334.8	344.9	349.1	356.6
65°	286.2	286.2	283.0	284.1	284.6	280.8	283.5	288.9	295.4	297.1	304.0
67.5°	243.4	241.9	240.0	238.4	238.4	238.1	239.5	242.2	247.0	247.6	252.9
70°	214.0	212.9	212.4	210.8	208.7	211.4	209.7	212.4	215.1	215.6	218.9
72.5°	185.5	184.5	183.5	181.9	181.0	180.7	180.8	183.9	185.8	185.0	188.7
75°	145.0	143.9	142.8	140.1	140.1	138.6	139.1	141.2	143.4	141.8	145.0
77.5°	106.5	103.1	103.0	103.7	101.9	102.2	101.6	101.2	102.2	102.3	105.2
80°	81.9	78.2	79.2	78.7	78.2	77.6	76.5	77.1	77.6	78.2	79.8
82.5°	59.1	58.8	57.7	57.6	57.0	55.6	55.0	55.9	56.5	56.2	57.4
85°	30.2	28.6	29.6	29.1	29.6	29.1	27.5	27.5	28.6	28.0	29.1
87.5°	15.0	14.8	13.7	13.4	12.3	12.0	11.0	10.9	10.8	10.2	10.6
90°	29.7	28.7	25.2	21.8	18.3	14.9	11.8	9.2	6.5	3.9	1.2
92.5°	46.7	45.9	43.9	41.9	40.0	38.0	36.1	34.3	32.5	30.7	28.9
95°	89.4	88.4	86.3	84.1	82.0	79.9	78.0	76.0	74.2	72.3	70.5
97.5°	139.6	138.3	136.8	135.2	133.7	132.1	130.7	129.4	127.9	126.6	125.2
100°	176.4	175.6	174.3	172.9	171.6	170.3	168.8	167.2	165.6	164.1	162.5
102.5°	218.5	217.6	215.9	214.1	212.4	210.6	209.3	208.3	207.4	206.4	205.5
105°	281.9	281.9	279.6	277.1	274.7	272.4	270.9	270.4	269.8	269.3	268.8
107.5°	349.0	348.1	347.1	346.2	345.2	344.3	343.6	343.3	343.0	342.7	342.4
110°	394.1	393.0	392.4	392.0	391.4	390.9	390.4	389.8	389.3	388.8	388.2



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	439.2	437.9	437.8	437.7	437.6	437.5	437.3	437.0	436.7	436.3	436.0
115°	509.1	508.9	509.5	509.9	510.5	511.0	510.9	510.1	509.3	508.5	507.7
117.5°	579.1	579.2	579.8	580.5	581.2	581.9	581.9	581.5	580.9	580.4	579.9
120°	625.7	626.0	627.2	628.6	629.9	631.3	631.1	629.5	628.0	626.4	624.8
122.5°	673.0	673.8	674.5	675.1	675.8	676.5	676.3	675.1	673.9	672.7	671.6
125°	743.1	744.3	744.7	745.3	745.8	746.3	746.2	745.4	744.7	743.8	743.0
127.5°	812.5	814.0	814.6	815.2	815.7	816.3	815.8	814.0	812.4	810.6	809.0
130°	857.9	858.9	859.7	860.5	861.3	862.1	861.4	859.3	857.1	855.1	852.9
132.5°	902.5	903.8	904.4	905.0	905.5	906.2	905.4	903.2	901.1	899.0	896.9
135°	968.9	970.0	970.3	970.5	970.8	971.1	970.4	968.8	967.2	965.6	964.0
137.5°	1034.1	1035.2	1034.5	1033.8	1033.2	1032.5	1031.4	1030.2	1028.8	1027.5	1026.1
140°	1076.0	1076.3	1076.0	1075.8	1075.5	1075.2	1074.4	1073.1	1071.8	1070.5	1069.1
142.5°	1116.2	1116.4	1115.9	1115.5	1115.0	1114.5	1113.6	1112.3	1111.0	1109.6	1108.3
145°	1175.2	1175.4	1174.6	1173.9	1173.1	1172.3	1171.6	1171.1	1170.5	1170.1	1169.5
147.5°	1230.7	1230.7	1229.9	1229.2	1228.4	1227.6	1226.9	1225.9	1224.9	1223.9	1223.0
150°	1265.0	1265.0	1264.5	1264.0	1263.5	1262.9	1262.4	1261.9	1261.3	1260.8	1260.3
152.5°	1296.1	1295.6	1295.3	1295.0	1294.7	1294.3	1293.8	1293.1	1292.4	1291.6	1290.9
155°	1341.4	1340.3	1340.1	1339.7	1339.5	1339.3	1339.1	1339.1	1339.1	1339.1	1339.1
157.5°	1380.9	1379.7	1379.5	1379.3	1379.1	1378.9	1379.0	1379.3	1379.6	1379.9	1380.2
160°	1404.9	1403.6	1403.6	1403.6	1403.6	1403.6	1403.9	1404.4	1404.9	1405.5	1406.0
162.5°	1427.9	1426.6	1426.3	1426.2	1425.9	1425.7	1426.0	1426.7	1427.4	1428.2	1428.9
165°	1456.6	1455.0	1455.0	1455.0	1455.0	1455.0	1455.4	1456.2	1457.0	1457.8	1458.6
167.5°	1480.0	1478.4	1478.2	1478.0	1477.7	1477.6	1478.0	1479.0	1480.1	1481.1	1482.3
170°	1492.7	1490.8	1490.8	1490.8	1490.8	1490.8	1491.4	1492.4	1493.5	1494.5	1495.6
172.5°	1503.0	1501.3	1501.3	1501.3	1501.3	1501.3	1501.9	1502.9	1504.0	1505.1	1506.1
175°	1513.9	1512.4	1512.4	1512.4	1512.4	1512.4	1512.8	1513.9	1515.0	1516.1	1517.1
177.5°	1519.1	1517.8	1517.8	1517.8	1517.8	1517.8	1518.2	1519.1	1520.0	1520.8	1521.6
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1119.5	1121.7	1129.0	1134.2	1140.3	1143.7	1147.2	1149.8	1153.2	1154.1	1166.6
5°	1124.5	1135.3	1154.1	1168.2	1185.4	1204.3	1217.2	1223.1	1238.8	1251.7	1277.6
7.5°	1123.1	1146.1	1174.6	1204.0	1235.8	1265.1	1290.5	1320.7	1342.2	1374.4	1406.2
10°	1121.8	1152.5	1189.2	1226.9	1271.1	1312.1	1348.8	1389.7	1423.7	1468.5	1506.7
12.5°	1117.9	1155.2	1206.0	1250.6	1304.3	1360.8	1415.2	1467.8	1497.9	1572.4	1607.7
15°	1108.3	1152.5	1216.2	1284.0	1358.0	1424.7	1493.7	1548.8	1637.7	1703.0	1744.5
17.5°	1090.0	1151.9	1227.3	1309.3	1399.1	1487.2	1565.4	1648.8	1743.1	1822.1	1906.1
20°	1081.4	1149.3	1233.4	1324.0	1417.2	1516.9	1605.9	1706.2	1809.1	1886.7	1994.6
22.5°	1065.4	1142.4	1233.0	1333.9	1433.6	1536.8	1640.8	1741.9	1860.9	1967.9	2070.4
25°	1039.3	1125.6	1219.4	1332.1	1449.1	1552.5	1677.0	1811.3	1935.3	2072.7	2175.2
27.5°	1011.9	1104.0	1198.0	1302.8	1428.6	1551.5	1708.1	1859.8	2011.4	2130.1	2205.9
30°	990.8	1080.3	1177.3	1283.0	1407.5	1553.6	1728.8	1894.3	2042.0	2143.9	2186.5
32.5°	968.0	1058.8	1144.5	1255.4	1388.1	1552.3	1741.8	1914.5	2043.8	2111.6	2103.2
35°	932.1	1008.1	1091.6	1198.3	1354.7	1542.9	1749.3	1916.4	1995.7	1981.1	1871.1
37.5°	880.3	944.2	1026.5	1143.4	1315.9	1522.9	1734.2	1859.6	1854.4	1735.9	1576.6
40°	848.0	902.4	981.7	1104.5	1285.7	1510.0	1710.5	1791.9	1722.9	1557.4	1366.5
42.5°	805.7	855.8	935.1	1061.4	1252.5	1483.6	1665.2	1688.8	1553.8	1363.3	1188.4
45°	740.1	784.3	866.3	996.7	1202.7	1426.4	1554.7	1497.0	1315.3	1118.6	985.4
47.5°	669.7	715.7	794.5	928.5	1130.7	1340.2	1401.4	1278.7	1092.2	932.6	810.3
50°	625.3	669.6	746.6	881.9	1081.9	1269.6	1294.8	1136.4	965.0	824.8	724.5
52.5°	580.5	622.1	697.9	833.6	1025.0	1187.6	1172.0	1010.4	852.8	733.3	654.7
55°	513.7	553.1	625.3	752.6	926.7	1055.5	998.9	844.7	714.3	621.5	561.7
57.5°	454.0	491.7	554.1	669.0	820.4	908.9	836.9	706.9	603.2	531.9	487.2
60°	413.4	446.9	506.2	612.9	744.5	811.8	740.7	625.9	538.5	481.4	441.5
62.5°	375.1	404.2	459.1	556.0	670.3	726.9	654.9	557.7	483.3	432.7	398.8
65°	317.0	343.4	391.9	467.4	561.2	598.9	536.9	458.2	400.5	362.8	340.2
67.5°	264.0	286.4	328.3	387.7	456.7	484.2	437.0	376.0	332.6	302.3	284.3
70°	228.5	248.0	280.8	332.1	394.6	415.7	371.5	321.3	289.5	265.2	248.5
72.5°	198.8	213.0	242.9	282.5	334.6	351.3	320.5	276.5	246.8	228.5	215.3
75°	151.5	163.3	182.8	214.5	250.6	260.4	237.2	209.7	189.7	176.8	166.6
77.5°	109.2	118.0	132.0	151.6	176.6	185.4	170.6	152.3	137.8	129.0	123.3
80°	82.5	89.5	101.3	117.5	132.6	137.4	128.8	114.8	104.6	99.7	94.9
82.5°	60.9	64.9	72.0	83.0	93.4	99.1	91.7	83.3	77.9	73.4	71.6
85°	30.7	32.9	36.1	40.4	46.9	49.0	46.3	44.2	41.0	38.3	38.3
87.5°	12.0	12.5	14.3	15.8	18.1	20.0	20.3	20.1	20.4	20.2	20.0
90°	3.9	6.5	9.2	11.8	14.9	18.3	21.8	25.2	28.7	29.7	30.8
92.5°	30.7	32.5	34.3	36.1	38.0	40.0	41.9	43.9	45.9	46.7	47.5
95°	72.3	74.2	76.0	78.0	79.9	82.0	84.1	86.3	88.4	89.4	90.5
97.5°	126.6	127.9	129.4	130.7	132.1	133.7	135.2	136.8	138.3	139.6	140.8
100°	164.1	165.6	167.2	168.8	170.3	171.6	172.9	174.3	175.6	176.4	177.2
102.5°	206.4	207.4	208.3	209.3	210.6	212.4	214.1	215.9	217.6	218.5	219.3
105°	269.3	269.8	270.4	270.9	272.4	274.7	277.1	279.6	281.9	281.9	281.9
107.5°	342.7	343.0	343.3	343.6	344.3	345.2	346.2	347.1	348.1	349.0	349.8
110°	388.8	389.3	389.8	390.4	390.9	391.4	392.0	392.4	393.0	394.1	395.1



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	436.3	436.7	437.0	437.3	437.5	437.6	437.7	437.8	437.9	439.2	440.5
115°	508.5	509.3	510.1	510.9	511.0	510.5	509.9	509.5	508.9	509.1	509.5
117.5°	580.4	580.9	581.5	581.9	581.9	581.2	580.5	579.8	579.2	579.1	579.0
120°	626.4	628.0	629.5	631.1	631.3	629.9	628.6	627.2	626.0	625.7	625.4
122.5°	672.7	673.9	675.1	676.3	676.5	675.8	675.1	674.5	673.8	673.0	672.3
125°	743.8	744.7	745.4	746.2	746.3	745.8	745.3	744.7	744.3	743.1	742.1
127.5°	810.6	812.4	814.0	815.8	816.3	815.7	815.2	814.6	814.0	812.5	811.0
130°	855.1	857.1	859.3	861.4	862.1	861.3	860.5	859.7	858.9	857.9	856.7
132.5°	899.0	901.1	903.2	905.4	906.2	905.5	905.0	904.4	903.8	902.5	901.3
135°	965.6	967.2	968.8	970.4	971.1	970.8	970.5	970.3	970.0	968.9	967.9
137.5°	1027.5	1028.8	1030.2	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1	1033.0
140°	1070.5	1071.8	1073.1	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0	1075.8
142.5°	1109.6	1111.0	1112.3	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2	1115.9
145°	1170.1	1170.5	1171.1	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2	1174.9
147.5°	1223.9	1224.9	1225.9	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7	1230.7
150°	1260.8	1261.3	1261.9	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0	1265.0
152.5°	1291.6	1292.4	1293.1	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1	1296.5
155°	1339.1	1339.1	1339.1	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4	1342.4
157.5°	1379.9	1379.6	1379.3	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9	1382.0
160°	1405.5	1404.9	1404.4	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9	1406.3
162.5°	1428.2	1427.4	1426.7	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9	1429.2
165°	1457.8	1457.0	1456.2	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6	1458.2
167.5°	1481.1	1480.1	1479.0	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0	1481.7
170°	1494.5	1493.5	1492.4	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7	1494.5
172.5°	1505.1	1504.0	1502.9	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0	1504.6
175°	1516.1	1515.0	1513.9	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9	1515.5
177.5°	1520.8	1520.0	1519.1	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1	1520.4
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6	1112.6
2.5°	1170.8	1171.3	1176.1	1179.5	1177.7	1180.0	1180.7
5°	1279.2	1298.6	1308.8	1316.4	1316.9	1317.5	1321.8
7.5°	1432.8	1453.7	1468.9	1491.9	1498.8	1506.7	1504.4
10°	1545.0	1575.7	1602.1	1616.1	1631.3	1653.4	1635.5
12.5°	1649.8	1704.2	1744.5	1766.2	1780.4	1784.9	1776.2
15°	1822.6	1893.8	1932.1	1930.9	1979.5	2000.5	1967.6
17.5°	1981.1	2046.8	2099.4	2126.3	2166.8	2175.7	2171.6
20°	2078.1	2149.8	2190.8	2237.1	2258.2	2277.0	2280.3
22.5°	2161.8	2226.2	2270.2	2308.7	2326.3	2335.3	2340.7
25°	2247.9	2298.6	2325.1	2338.5	2343.4	2342.2	2335.3
27.5°	2242.0	2245.9	2216.8	2188.2	2162.7	2133.9	2123.9
30°	2183.8	2138.5	2057.6	2011.8	1944.4	1891.1	1912.6
32.5°	2030.7	1940.5	1849.7	1749.6	1666.7	1643.1	1619.4
35°	1733.1	1574.6	1481.9	1374.1	1330.9	1287.9	1258.2
37.5°	1402.2	1279.5	1169.6	1099.1	1055.8	1028.6	1013.9
40°	1212.4	1101.8	1011.3	954.2	921.3	890.6	886.2
42.5°	1061.0	958.2	890.1	844.6	813.0	799.9	790.5
45°	869.0	797.3	751.5	719.1	698.1	690.0	679.2
47.5°	735.5	684.8	650.5	628.4	612.6	606.6	605.7
50°	660.9	618.9	593.5	576.2	563.9	561.7	553.1
52.5°	604.8	568.4	548.7	533.6	524.7	518.6	516.0
55°	525.1	500.8	483.0	474.4	467.4	461.4	461.4
57.5°	459.4	439.1	427.4	420.0	417.9	413.7	411.0
60°	418.8	401.6	392.4	386.0	381.7	382.2	377.3
62.5°	379.2	368.0	359.3	352.8	347.6	347.7	348.0
65°	322.9	314.3	307.8	305.6	302.5	298.7	299.8
67.5°	273.6	265.5	260.5	256.8	255.7	253.7	256.8
70°	238.3	232.3	228.5	225.3	224.3	224.8	227.5
72.5°	205.9	201.7	199.2	197.7	195.4	195.4	197.3
75°	161.7	158.5	156.3	154.7	154.2	154.2	154.2
77.5°	118.8	118.0	117.1	114.7	114.8	115.5	115.6
80°	93.8	92.2	91.7	90.5	89.0	87.9	90.5
82.5°	70.1	68.4	67.9	67.7	65.2	65.0	67.3
85°	37.7	36.1	36.7	36.1	36.1	35.6	35.6
87.5°	19.7	19.5	19.3	19.8	19.5	19.2	20.1
90°	31.8	33.0	33.7	34.2	34.8	35.3	35.8
92.5°	48.4	49.3	49.5	49.2	48.9	48.6	48.2
95°	91.6	92.6	93.2	93.2	93.2	93.2	93.2
97.5°	142.0	143.2	143.8	143.7	143.5	143.5	143.4
100°	178.0	178.8	179.4	180.0	180.5	181.0	181.6
102.5°	220.1	220.9	221.2	221.1	220.9	220.9	220.8
105°	281.9	281.9	282.2	282.7	283.3	283.8	284.3
107.5°	350.6	351.5	351.7	351.4	351.1	350.8	350.5
110°	396.2	397.3	397.5	397.0	396.5	395.9	395.4



TEST NUMBER: P332205-927

CATALOG NUMBER: S123DIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	441.7	443.0	443.6	443.5	443.4	443.3	443.1
115°	509.7	509.9	509.9	509.7	509.5	509.1	508.9
117.5°	579.0	578.9	578.5	577.7	577.0	576.3	575.5
120°	625.2	624.9	624.5	624.0	623.4	622.9	622.3
122.5°	671.7	671.0	670.3	669.6	668.8	668.0	667.3
125°	741.0	740.0	738.9	737.8	736.8	735.7	734.7
127.5°	809.5	808.0	806.7	805.5	804.2	803.0	801.8
130°	855.7	854.7	853.2	851.4	849.5	847.6	845.7
132.5°	900.0	898.7	897.4	896.0	894.5	893.0	891.6
135°	966.8	965.7	965.0	964.4	963.8	963.4	962.8
137.5°	1031.9	1030.8	1029.7	1028.6	1027.7	1026.7	1025.6
140°	1075.5	1075.2	1074.2	1072.3	1070.5	1068.6	1066.8
142.5°	1115.6	1115.4	1114.5	1113.1	1111.7	1110.2	1108.8
145°	1174.6	1174.4	1173.7	1172.7	1171.6	1170.5	1169.5
147.5°	1230.7	1230.7	1229.9	1228.3	1226.7	1225.0	1223.4
150°	1265.0	1265.0	1264.2	1262.7	1261.1	1259.5	1257.9
152.5°	1296.9	1297.4	1296.9	1295.5	1294.1	1292.7	1291.3
155°	1343.5	1344.6	1344.2	1342.3	1340.5	1338.6	1336.7
157.5°	1383.1	1384.2	1384.0	1382.5	1381.0	1379.5	1378.1
160°	1407.6	1408.9	1409.1	1408.0	1406.9	1405.9	1404.8
162.5°	1430.5	1431.9	1431.7	1430.0	1428.3	1426.6	1424.9
165°	1459.8	1461.3	1461.3	1459.4	1457.5	1455.6	1453.8
167.5°	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4
170°	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8
172.5°	1506.3	1507.9	1507.8	1505.9	1504.1	1502.2	1500.4
175°	1517.1	1518.7	1518.5	1516.7	1514.8	1513.0	1511.2
177.5°	1521.6	1522.9	1522.8	1521.3	1519.8	1518.4	1516.9
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7

(END OF REPORT)