

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332232-927

Luminaire Tested: **S123DIW-S1165D1320U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332232-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1320U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7953.3 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332232-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332232-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45	40
2	88	81	75	70	81	75	69	65	63	59	55	52	49	47	42	40	38	33
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32	28
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24	21
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21	18
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19	16
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15588	15588	15588
5°	15662	15446	15554
10°	15557	15312	15407
15°	15375	15139	15166
20°	15163	14892	14905
25°	14878	14598	14567
30°	14564	14270	14162
35°	14236	13925	13745
40°	13893	13543	13333
45°	13516	13192	12871
50°	13137	12762	12407
55°	12643	12314	11941
60°	12144	11795	11418
65°	11703	11227	10878
70°	11053	10581	10112
75°	10098	9736	9320
80°	9106	8722	8647
85°	7991	7694	7385



TEST NUMBER: P332232-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.4	1.7
10°-20°	385.2	4.8
20°-30°	569.0	7.2
30°-40°	664.6	8.4
40°-50°	668.2	8.4
50°-60°	587.0	7.4
60°-70°	437.3	5.5
70°-80°	249.1	3.1
80°-90°	75.3	0.9
90°-100°	49.8	0.6
100°-110°	237.6	3.0
110°-120°	570.6	7.2
120°-130°	726.7	9.1
130°-140°	776.4	9.8
140°-150°	726.0	9.1
150°-160°	585.6	7.4
160°-170°	378.0	4.8
170°-180°	130.3	1.6
0°-30°	1090.6	13.7
0°-40°	1755.3	22.1
0°-60°	3010.4	37.9
0°-90°	3772.2	47.4
90°-120°	858.1	10.8
90°-150°	3087.2	38.8
90°-180°	4181.0	52.6
0°-180°	7953.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1448	1448	1448	1448	1448	
5°	1450	1443	1430	1441	1440	137
15°	1380	1374	1358	1368	1361	389
25°	1253	1245	1229	1230	1226	577
35°	1083	1075	1060	1052	1046	677
45°	888	882	867	852	846	685
55°	674	672	656	643	636	603
65°	460	453	441	431	427	453
75°	243	238	234	228	224	260
85°	65	62	62	60	60	71
90°	1	11	24	28	31	6
95°	62	23	32	38	39	77
105°	304	309	223	53	45	322
115°	569	576	585	594	599	562
125°	803	811	815	817	819	717
135°	999	1005	1010	1012	1010	769
145°	1153	1160	1162	1164	1164	722
155°	1270	1268	1269	1274	1268	585
165°	1340	1336	1335	1343	1336	378
175°	1371	1366	1367	1373	1366	130
180°	1371	1371	1371	1371	1371	



TEST NUMBER: P332232-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1453.2	1452.3	1451.4	1450.6	1449.6	1448.0	1445.6	1443.1	1440.7	1438.2	1440.4
5°	1449.5	1448.1	1446.7	1445.3	1443.9	1441.7	1438.7	1435.6	1432.6	1429.5	1432.3
7.5°	1435.3	1433.8	1432.5	1431.1	1429.7	1427.4	1424.3	1421.2	1418.0	1414.8	1417.3
10°	1423.3	1421.9	1420.5	1419.1	1417.8	1415.3	1411.7	1408.1	1404.5	1400.9	1403.4
12.5°	1407.4	1406.2	1405.0	1403.9	1402.7	1400.4	1397.1	1393.7	1390.3	1387.0	1388.8
15°	1379.7	1378.6	1377.5	1376.4	1375.3	1372.9	1369.4	1365.7	1362.2	1358.5	1360.7
17.5°	1347.6	1346.2	1344.7	1343.3	1341.8	1339.3	1335.7	1332.1	1328.5	1324.9	1326.5
20°	1323.7	1322.0	1320.3	1318.7	1317.1	1314.4	1310.8	1307.3	1303.6	1300.1	1301.2
22.5°	1296.8	1295.1	1293.5	1291.8	1290.1	1287.5	1283.9	1280.3	1276.8	1273.1	1274.0
25°	1252.7	1251.0	1249.4	1247.7	1246.1	1243.4	1239.8	1236.3	1232.6	1229.1	1229.3
27.5°	1205.6	1204.0	1202.5	1200.8	1199.2	1196.5	1192.6	1188.7	1184.9	1181.0	1181.2
30°	1171.8	1170.4	1169.0	1167.6	1166.3	1163.6	1159.8	1155.9	1152.0	1148.1	1148.1
32.5°	1137.9	1136.1	1134.2	1132.4	1130.6	1128.1	1125.2	1122.2	1119.2	1116.3	1114.7
35°	1083.4	1081.7	1080.1	1078.4	1076.7	1074.1	1070.5	1066.9	1063.3	1059.7	1058.0
37.5°	1027.5	1025.5	1023.3	1021.3	1019.1	1016.3	1012.6	1009.0	1005.4	1001.6	999.7
40°	988.7	987.1	985.4	983.7	982.1	979.3	975.4	971.5	967.7	963.8	961.6
42.5°	949.8	948.0	946.1	944.2	942.3	939.4	935.6	931.7	927.8	924.0	921.8
45°	887.9	886.8	885.7	884.6	883.4	881.1	877.5	873.9	870.3	866.6	863.4
47.5°	826.3	824.7	823.2	821.5	819.9	817.5	814.0	810.6	807.3	803.9	800.7
50°	784.5	783.2	781.7	780.4	779.0	776.5	772.9	769.3	765.6	762.1	759.1
52.5°	740.7	739.7	738.8	737.8	736.9	734.5	730.7	726.9	723.1	719.2	716.6
55°	673.7	673.4	673.1	672.9	672.6	670.7	667.0	663.5	659.8	656.2	653.2
57.5°	609.9	609.0	608.0	607.1	606.2	604.3	601.3	598.5	595.6	592.7	590.0
60°	564.1	563.8	563.6	563.2	563.0	561.2	557.9	554.5	551.2	547.9	545.4
62.5°	523.2	522.5	521.8	521.1	520.4	518.3	515.0	511.7	508.4	505.1	502.6
65°	459.5	458.1	456.7	455.3	453.9	451.9	449.1	446.3	443.5	440.8	438.6
67.5°	392.0	390.8	389.6	388.3	387.1	385.5	383.3	381.3	379.1	377.1	375.1
70°	351.2	349.5	347.8	346.2	344.5	342.9	341.2	339.5	337.9	336.2	334.3
72.5°	308.3	307.1	305.9	304.7	303.5	301.9	300.0	298.1	296.3	294.4	292.6
75°	242.8	241.7	240.6	239.5	238.4	237.4	236.6	235.8	235.0	234.1	232.7
77.5°	184.8	184.2	183.5	183.0	182.4	181.6	180.5	179.6	178.6	177.6	176.7
80°	146.9	146.1	145.3	144.4	143.6	142.9	142.4	141.8	141.2	140.7	140.5
82.5°	110.1	109.9	109.7	109.6	109.4	109.2	109.2	109.1	108.9	108.8	108.4
85°	64.7	64.2	63.6	63.1	62.5	62.3	62.3	62.3	62.3	62.3	61.7
87.5°	26.1	25.9	25.7	25.5	25.3	25.3	25.7	26.1	26.5	26.8	26.8
90°	1.0	3.2	5.5	7.8	10.1	12.7	15.6	18.5	21.5	24.5	25.3
92.5°	18.9	18.3	17.7	17.0	16.4	17.2	19.4	21.6	23.8	26.1	27.5
95°	62.1	52.8	43.6	34.3	25.0	21.6	24.1	26.6	29.1	31.6	33.2
97.5°	124.8	120.7	116.5	112.4	108.2	98.0	81.7	65.4	49.1	32.8	34.6
100°	172.1	176.7	181.2	185.7	190.3	174.8	139.6	104.3	68.9	33.6	35.4
102.5°	225.9	229.2	232.4	235.7	239.0	221.3	182.8	144.2	105.6	67.0	61.4
105°	303.6	306.0	308.6	311.0	313.5	304.6	284.2	263.8	243.4	223.1	183.0
107.5°	385.5	387.5	389.4	391.4	393.4	396.0	399.3	402.4	405.7	408.8	379.5
110°	440.1	441.9	443.6	445.4	447.3	449.4	451.9	454.4	456.9	459.4	451.9



TEST NUMBER: P332232-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.2	493.8	495.4	497.1	498.7	500.7	503.3	505.7	508.3	510.7	510.9
115°	569.4	570.8	572.1	573.5	574.8	576.6	578.5	580.6	582.7	584.7	586.9
117.5°	644.2	645.9	647.5	649.2	650.9	652.2	653.2	654.3	655.4	656.4	658.2
120°	690.6	692.7	694.7	696.7	698.8	700.1	700.8	701.5	702.2	702.8	704.6
122.5°	737.9	739.6	741.2	742.9	744.6	745.8	746.7	747.6	748.5	749.3	750.6
125°	802.6	804.5	806.3	808.1	809.9	811.3	812.1	813.1	814.0	814.9	815.3
127.5°	865.4	867.2	869.0	870.8	872.7	874.1	875.2	876.3	877.3	878.5	879.2
130°	904.5	906.3	908.2	910.0	911.8	913.1	914.0	915.0	915.8	916.7	917.7
132.5°	942.0	943.8	945.6	947.5	949.3	950.5	951.3	952.0	952.7	953.4	954.3
135°	999.3	1000.6	1002.0	1003.3	1004.7	1005.8	1006.7	1007.7	1008.5	1009.5	1010.1
137.5°	1048.1	1049.9	1051.6	1053.3	1055.0	1056.1	1056.6	1057.2	1057.6	1058.1	1059.2
140°	1080.8	1082.1	1083.5	1084.8	1086.2	1087.2	1087.9	1088.5	1089.3	1089.9	1090.8
142.5°	1110.9	1112.2	1113.6	1115.0	1116.3	1117.4	1118.0	1118.7	1119.4	1120.1	1120.8
145°	1153.1	1154.7	1156.3	1157.9	1159.4	1160.4	1160.9	1161.3	1161.8	1162.2	1162.7
147.5°	1192.8	1193.8	1194.8	1195.9	1197.0	1197.7	1198.2	1198.6	1199.0	1199.5	1200.0
150°	1217.3	1217.9	1218.6	1219.2	1220.0	1220.5	1221.0	1221.4	1221.9	1222.3	1222.8
152.5°	1239.2	1239.5	1239.8	1240.2	1240.5	1240.8	1241.1	1241.3	1241.6	1241.9	1242.7
155°	1270.2	1269.8	1269.3	1268.8	1268.4	1268.3	1268.5	1268.8	1269.0	1269.2	1270.3
157.5°	1294.3	1294.2	1294.2	1294.1	1294.0	1294.0	1293.7	1293.5	1293.2	1293.0	1294.3
160°	1308.9	1308.7	1308.4	1308.2	1308.0	1307.8	1307.6	1307.3	1307.1	1306.9	1308.2
162.5°	1322.8	1322.2	1321.6	1321.0	1320.4	1320.0	1319.8	1319.5	1319.3	1319.1	1320.6
165°	1339.5	1338.8	1338.1	1337.4	1336.7	1336.3	1336.1	1335.9	1335.6	1335.4	1337.2
167.5°	1352.5	1351.6	1350.7	1349.8	1348.8	1348.5	1348.5	1348.5	1348.5	1348.5	1350.3
170°	1359.9	1358.9	1358.0	1357.2	1356.2	1355.7	1355.7	1355.7	1355.7	1355.7	1357.6
172.5°	1364.8	1363.7	1362.6	1361.4	1360.4	1359.9	1360.1	1360.3	1360.5	1360.7	1362.5
175°	1371.0	1369.9	1368.8	1367.6	1366.5	1366.0	1366.3	1366.5	1366.8	1367.0	1368.6
177.5°	1372.7	1371.7	1370.9	1370.0	1369.0	1368.7	1368.9	1369.0	1369.2	1369.4	1370.9
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332232-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1442.6	1444.9	1447.1	1448.1	1447.9	1447.6	1447.4	1447.2
5°	1435.0	1437.8	1440.6	1441.7	1441.1	1440.6	1440.0	1439.5
7.5°	1419.8	1422.3	1424.8	1425.8	1425.5	1425.2	1424.9	1424.6
10°	1405.9	1408.3	1410.9	1411.8	1411.3	1410.7	1410.2	1409.6
12.5°	1390.6	1392.4	1394.2	1395.0	1394.6	1394.3	1394.0	1393.7
15°	1362.9	1365.2	1367.4	1367.7	1366.0	1364.4	1362.7	1361.0
17.5°	1328.0	1329.6	1331.1	1331.6	1331.0	1330.4	1329.8	1329.2
20°	1302.3	1303.4	1304.5	1304.6	1303.8	1302.9	1302.1	1301.2
22.5°	1274.9	1275.8	1276.7	1276.6	1275.6	1274.5	1273.4	1272.4
25°	1229.6	1229.9	1230.2	1229.9	1229.1	1228.2	1227.4	1226.5
27.5°	1181.5	1181.6	1181.9	1181.5	1180.4	1179.3	1178.3	1177.3
30°	1148.1	1148.1	1148.1	1147.2	1145.2	1143.3	1141.3	1139.4
32.5°	1113.1	1111.6	1110.0	1108.7	1107.7	1106.6	1105.6	1104.5
35°	1056.4	1054.7	1053.0	1051.5	1050.1	1048.8	1047.3	1046.0
37.5°	997.7	995.7	993.7	992.3	991.3	990.5	989.6	988.7
40°	959.4	957.2	955.0	953.3	952.2	951.1	950.0	948.9
42.5°	919.6	917.3	915.1	913.5	912.4	911.2	910.1	909.0
45°	860.1	856.7	853.4	851.0	849.7	848.3	846.9	845.5
47.5°	797.4	794.2	790.8	788.6	787.4	786.2	785.0	783.8
50°	756.0	753.0	749.9	747.6	745.9	744.3	742.6	740.9
52.5°	714.1	711.5	708.8	706.7	705.0	703.4	701.7	700.1
55°	650.1	647.1	644.0	641.8	640.5	639.1	637.7	636.3
57.5°	587.3	584.6	581.9	579.7	578.1	576.6	574.9	573.3
60°	543.0	540.4	538.0	536.0	534.6	533.2	531.9	530.4
62.5°	500.1	497.6	495.1	493.4	492.4	491.5	490.6	489.6
65°	436.4	434.2	432.0	430.5	429.6	428.8	427.9	427.1
67.5°	373.2	371.2	369.3	367.7	366.6	365.4	364.2	363.1
70°	332.3	330.4	328.4	326.8	325.4	324.0	322.7	321.3
72.5°	291.0	289.2	287.5	286.3	285.6	284.9	284.2	283.4
75°	231.3	230.0	228.5	227.4	226.6	225.8	225.0	224.1
77.5°	175.7	174.8	173.8	173.3	173.3	173.3	173.3	173.3
80°	140.1	139.9	139.6	139.5	139.5	139.5	139.5	139.5
82.5°	107.8	107.3	106.9	106.5	106.2	106.1	105.8	105.6
85°	61.2	60.6	60.0	59.8	59.8	59.8	59.8	59.8
87.5°	26.7	26.7	26.6	26.7	26.8	26.9	26.9	27.0
90°	26.2	27.2	28.0	28.8	29.2	29.6	30.1	30.6
92.5°	29.0	30.4	31.8	32.7	33.0	33.3	33.5	33.8
95°	34.8	36.4	37.9	38.7	38.7	38.7	38.7	38.7
97.5°	36.4	38.3	40.0	41.0	41.3	41.5	41.7	42.0
100°	37.2	39.1	40.9	41.9	42.1	42.3	42.5	42.8
102.5°	55.8	50.1	44.6	42.0	42.4	42.8	43.2	43.6
105°	142.9	102.9	62.8	43.0	43.5	43.9	44.4	44.8
107.5°	350.1	320.8	291.4	261.6	231.4	201.1	171.0	140.8
110°	444.4	437.0	429.5	409.6	377.2	344.8	312.5	280.1



TEST NUMBER: P332232-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	511.0	511.1	511.3	507.9	501.1	494.2	487.4	480.6
115°	589.2	591.4	593.7	595.3	596.2	597.1	598.0	599.0
117.5°	660.0	661.8	663.6	664.6	664.8	665.0	665.2	665.4
120°	706.5	708.3	710.1	711.0	711.0	711.0	711.0	711.0
122.5°	751.9	753.1	754.4	755.1	755.3	755.4	755.7	755.8
125°	815.8	816.3	816.7	817.1	817.6	818.1	818.5	819.0
127.5°	879.9	880.6	881.4	881.5	881.1	880.6	880.1	879.6
130°	918.5	919.5	920.4	920.6	920.1	919.7	919.2	918.8
132.5°	955.2	956.2	957.0	957.2	956.6	955.9	955.3	954.7
135°	1010.8	1011.5	1012.2	1012.2	1011.5	1010.8	1010.1	1009.5
137.5°	1060.3	1061.4	1062.5	1062.8	1062.3	1061.9	1061.4	1061.0
140°	1091.7	1092.7	1093.5	1093.8	1093.3	1092.8	1092.4	1091.9
142.5°	1121.5	1122.2	1123.0	1123.0	1122.4	1121.7	1121.1	1120.5
145°	1163.2	1163.6	1164.0	1164.3	1164.3	1164.3	1164.3	1164.3
147.5°	1200.4	1200.9	1201.3	1201.0	1200.0	1199.0	1197.9	1196.8
150°	1223.2	1223.7	1224.2	1224.0	1223.4	1222.7	1222.0	1221.3
152.5°	1243.5	1244.4	1245.2	1245.1	1244.0	1242.9	1241.9	1240.9
155°	1271.5	1272.6	1273.7	1273.6	1272.2	1270.9	1269.6	1268.2
157.5°	1295.8	1297.1	1298.5	1298.2	1296.5	1294.7	1292.9	1291.2
160°	1309.6	1311.0	1312.3	1312.2	1310.6	1309.0	1307.4	1305.8
162.5°	1322.2	1323.7	1325.2	1325.3	1323.9	1322.5	1321.1	1319.7
165°	1339.0	1340.8	1342.7	1342.7	1341.2	1339.6	1338.0	1336.4
167.5°	1352.1	1353.8	1355.7	1355.7	1353.8	1352.1	1350.3	1348.5
170°	1359.4	1361.2	1363.0	1363.0	1361.2	1359.4	1357.6	1355.7
172.5°	1364.3	1366.1	1367.9	1367.8	1365.8	1363.8	1361.8	1359.9
175°	1370.2	1371.7	1373.3	1373.2	1371.4	1369.6	1367.8	1366.0
177.5°	1372.3	1373.8	1375.2	1375.1	1373.2	1371.4	1369.6	1367.8
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0

(END OF REPORT)