

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332233-927

Luminaire Tested: **S123DIW-S1165D1320U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332233-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S1165D1320U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7396.1 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332233-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332233-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	43
2	89	82	75	70	82	76	70	66	64	60	57	54	51	48	44	42	40	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	30
4	74	63	56	49	68	59	52	46	50	45	41	42	38	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	32	28	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	20
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	18
8	54	42	34	28	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15588	15588	15588
5°	15662	15446	15554
10°	15557	15312	15407
15°	15375	15139	15166
20°	15163	14892	14905
25°	14878	14598	14567
30°	14564	14270	14162
35°	14236	13925	13745
40°	13893	13543	13333
45°	13516	13192	12871
50°	13137	12762	12407
55°	12643	12314	11941
60°	12144	11795	11418
65°	11703	11227	10878
70°	11053	10581	10112
75°	10098	9736	9320
80°	9106	8722	8647
85°	7991	7694	7385



TEST NUMBER: P332233-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	136.4	1.8
10°-20°	385.2	5.2
20°-30°	569.0	7.7
30°-40°	664.6	9.0
40°-50°	668.2	9.0
50°-60°	587.0	7.9
60°-70°	437.3	5.9
70°-80°	249.1	3.4
80°-90°	75.4	1.0
90°-100°	85.2	1.2
100°-110°	255.0	3.4
110°-120°	433.8	5.9
120°-130°	570.5	7.7
130°-140°	641.3	8.7
140°-150°	630.4	8.5
150°-160°	530.7	7.2
160°-170°	353.3	4.8
170°-180°	123.7	1.7
0°-30°	1090.6	14.7
0°-40°	1755.3	23.7
0°-60°	3010.4	40.7
0°-90°	3772.2	51.0
90°-120°	774.0	10.5
90°-150°	2616.2	35.4
90°-180°	3624.0	49.0
0°-180°	7396.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1448	1448	1448	1448	1448	
5°	1450	1443	1430	1441	1440	137
15°	1380	1374	1358	1368	1361	389
25°	1253	1245	1229	1230	1226	577
35°	1083	1075	1060	1052	1046	677
45°	888	882	867	852	846	685
55°	674	672	656	643	636	603
65°	460	453	441	431	427	453
75°	243	238	234	228	224	260
85°	65	62	62	60	60	71
90°	1	11	25	29	31	7
95°	61	68	76	80	80	68
105°	231	234	242	243	244	248
115°	437	439	438	439	438	432
125°	639	642	640	636	632	570
135°	829	835	834	830	828	639
145°	1006	1008	1011	1010	1006	628
155°	1152	1152	1153	1156	1150	530
165°	1254	1252	1251	1257	1250	354
175°	1305	1301	1301	1306	1300	124
180°	1308	1308	1308	1308	1308	



TEST NUMBER: P332233-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1453.2	1452.3	1451.4	1450.6	1449.6	1448.0	1445.6	1443.1	1440.7	1438.2	1440.4
5°	1449.5	1448.1	1446.7	1445.3	1443.9	1441.7	1438.7	1435.6	1432.6	1429.5	1432.3
7.5°	1435.3	1433.8	1432.5	1431.1	1429.7	1427.4	1424.3	1421.2	1418.0	1414.8	1417.3
10°	1423.3	1421.9	1420.5	1419.1	1417.8	1415.3	1411.7	1408.1	1404.5	1400.9	1403.4
12.5°	1407.4	1406.2	1405.0	1403.9	1402.7	1400.4	1397.1	1393.7	1390.3	1387.0	1388.8
15°	1379.7	1378.6	1377.5	1376.4	1375.3	1372.9	1369.4	1365.7	1362.2	1358.5	1360.7
17.5°	1347.6	1346.2	1344.7	1343.3	1341.8	1339.3	1335.7	1332.1	1328.5	1324.9	1326.5
20°	1323.7	1322.0	1320.3	1318.7	1317.1	1314.4	1310.8	1307.3	1303.6	1300.1	1301.2
22.5°	1296.8	1295.1	1293.5	1291.8	1290.1	1287.5	1283.9	1280.3	1276.8	1273.1	1274.0
25°	1252.7	1251.0	1249.4	1247.7	1246.1	1243.4	1239.8	1236.3	1232.6	1229.1	1229.3
27.5°	1205.6	1204.0	1202.5	1200.8	1199.2	1196.5	1192.6	1188.7	1184.9	1181.0	1181.2
30°	1171.8	1170.4	1169.0	1167.6	1166.3	1163.6	1159.8	1155.9	1152.0	1148.1	1148.1
32.5°	1137.9	1136.1	1134.2	1132.4	1130.6	1128.1	1125.2	1122.2	1119.2	1116.3	1114.7
35°	1083.4	1081.7	1080.1	1078.4	1076.7	1074.1	1070.5	1066.9	1063.3	1059.7	1058.0
37.5°	1027.5	1025.5	1023.3	1021.3	1019.1	1016.3	1012.6	1009.0	1005.4	1001.6	999.7
40°	988.7	987.1	985.4	983.7	982.1	979.3	975.4	971.5	967.7	963.8	961.6
42.5°	949.8	948.0	946.1	944.2	942.3	939.4	935.6	931.7	927.8	924.0	921.8
45°	887.9	886.8	885.7	884.6	883.4	881.1	877.5	873.9	870.3	866.6	863.4
47.5°	826.3	824.7	823.2	821.5	819.9	817.5	814.0	810.6	807.3	803.9	800.7
50°	784.5	783.2	781.7	780.4	779.0	776.5	772.9	769.3	765.6	762.1	759.1
52.5°	740.7	739.7	738.8	737.8	736.9	734.5	730.7	726.9	723.1	719.2	716.6
55°	673.7	673.4	673.1	672.9	672.6	670.7	667.0	663.5	659.8	656.2	653.2
57.5°	609.9	609.0	608.0	607.1	606.2	604.3	601.3	598.5	595.6	592.7	590.0
60°	564.1	563.8	563.6	563.2	563.0	561.2	557.9	554.5	551.2	547.9	545.4
62.5°	523.2	522.5	521.8	521.1	520.4	518.3	515.0	511.7	508.4	505.1	502.6
65°	459.5	458.1	456.7	455.3	453.9	451.9	449.1	446.3	443.5	440.8	438.6
67.5°	392.0	390.8	389.6	388.3	387.1	385.5	383.3	381.3	379.1	377.1	375.1
70°	351.2	349.5	347.8	346.2	344.5	342.9	341.2	339.5	337.9	336.2	334.3
72.5°	308.3	307.1	305.9	304.7	303.5	301.9	300.0	298.1	296.3	294.4	292.6
75°	242.8	241.7	240.6	239.5	238.4	237.4	236.6	235.8	235.0	234.1	232.7
77.5°	184.8	184.2	183.5	183.0	182.4	181.6	180.5	179.6	178.6	177.6	176.7
80°	146.9	146.1	145.3	144.4	143.6	142.9	142.4	141.8	141.2	140.7	140.5
82.5°	110.1	109.9	109.7	109.6	109.4	109.2	109.2	109.1	108.9	108.8	108.4
85°	64.7	64.2	63.6	63.1	62.5	62.3	62.3	62.3	62.3	62.3	61.7
87.5°	26.1	25.9	25.7	25.5	25.3	25.3	25.7	26.1	26.5	26.9	26.8
90°	1.0	3.3	5.6	7.8	10.1	12.8	15.8	18.7	21.7	24.6	25.6
92.5°	24.9	26.4	28.0	29.5	31.1	32.7	34.4	36.0	37.8	39.5	40.2
95°	60.6	62.2	63.8	65.4	67.0	68.8	70.6	72.4	74.2	76.0	76.9
97.5°	107.7	108.8	110.0	111.2	112.4	113.7	115.0	116.3	117.6	119.0	120.0
100°	139.7	141.1	142.4	143.9	145.2	146.5	147.6	148.8	149.9	151.1	151.7
102.5°	176.7	177.5	178.4	179.2	180.0	181.2	182.7	184.2	185.7	187.2	187.9
105°	231.2	231.6	232.1	232.5	233.0	234.2	236.3	238.4	240.4	242.5	242.5
107.5°	294.5	294.8	295.0	295.3	295.6	296.1	296.9	297.8	298.6	299.4	300.2
110°	333.9	334.4	334.9	335.3	335.7	336.2	336.7	337.2	337.5	338.0	339.0



TEST NUMBER: P332233-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.0	375.3	375.6	375.8	376.1	376.3	376.4	376.4	376.6	376.7	377.8
115°	436.7	437.4	438.0	438.7	439.4	439.5	439.0	438.6	438.2	437.7	437.9
117.5°	498.8	499.2	499.6	500.1	500.6	500.5	499.9	499.3	498.7	498.1	498.0
120°	537.3	538.7	540.1	541.5	542.8	543.0	541.8	540.7	539.6	538.4	538.1
122.5°	577.7	578.6	579.6	580.7	581.6	581.9	581.2	580.7	580.0	579.5	578.8
125°	639.1	639.8	640.4	641.1	641.8	641.9	641.4	641.0	640.6	640.1	639.2
127.5°	695.8	697.3	698.7	700.1	701.6	702.1	701.6	701.1	700.6	700.1	698.8
130°	733.6	735.4	737.3	739.1	740.9	741.5	740.8	740.1	739.4	738.7	737.8
132.5°	771.4	773.2	775.1	776.9	778.7	779.3	778.9	778.4	777.8	777.4	776.3
135°	829.2	830.5	831.9	833.2	834.6	835.2	835.0	834.7	834.5	834.2	833.4
137.5°	882.6	883.7	884.9	886.0	887.2	888.0	888.6	889.2	889.8	890.4	889.4
140°	919.6	920.7	921.9	923.0	924.2	924.8	925.0	925.3	925.5	925.7	925.5
142.5°	953.2	954.4	955.5	956.7	957.8	958.6	959.0	959.4	959.8	960.3	960.0
145°	1005.8	1006.3	1006.8	1007.3	1007.7	1008.3	1008.9	1009.6	1010.3	1011.0	1010.7
147.5°	1051.9	1052.7	1053.5	1054.4	1055.2	1055.9	1056.5	1057.2	1057.8	1058.4	1058.4
150°	1083.9	1084.4	1084.9	1085.3	1085.8	1086.2	1086.7	1087.1	1087.6	1088.1	1088.1
152.5°	1110.2	1110.9	1111.5	1112.1	1112.8	1113.3	1113.6	1113.8	1114.1	1114.4	1114.8
155°	1151.8	1151.8	1151.8	1151.8	1151.8	1151.9	1152.1	1152.3	1152.5	1152.8	1153.7
157.5°	1187.1	1186.8	1186.5	1186.3	1186.0	1186.0	1186.1	1186.3	1186.5	1186.7	1187.6
160°	1209.3	1208.9	1208.4	1207.9	1207.4	1207.2	1207.2	1207.2	1207.2	1207.2	1208.4
162.5°	1229.0	1228.4	1227.7	1227.1	1226.5	1226.2	1226.5	1226.6	1226.8	1226.9	1228.1
165°	1254.5	1253.8	1253.2	1252.4	1251.8	1251.4	1251.4	1251.4	1251.4	1251.4	1252.8
167.5°	1274.9	1273.9	1273.0	1272.1	1271.2	1270.8	1271.0	1271.2	1271.4	1271.5	1273.0
170°	1286.3	1285.5	1284.5	1283.7	1282.7	1282.2	1282.2	1282.2	1282.2	1282.2	1283.8
172.5°	1295.4	1294.5	1293.6	1292.7	1291.7	1291.3	1291.3	1291.3	1291.3	1291.3	1292.7
175°	1304.9	1303.9	1303.1	1302.1	1301.2	1300.8	1300.8	1300.8	1300.8	1300.8	1302.1
177.5°	1308.8	1308.1	1307.3	1306.5	1305.8	1305.4	1305.4	1305.4	1305.4	1305.4	1306.5
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0



TEST NUMBER: P332233-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2	1448.2
2.5°	1442.6	1444.9	1447.1	1448.1	1447.9	1447.6	1447.4	1447.2
5°	1435.0	1437.8	1440.6	1441.7	1441.1	1440.6	1440.0	1439.5
7.5°	1419.8	1422.3	1424.8	1425.8	1425.5	1425.2	1424.9	1424.6
10°	1405.9	1408.3	1410.9	1411.8	1411.3	1410.7	1410.2	1409.6
12.5°	1390.6	1392.4	1394.2	1395.0	1394.6	1394.3	1394.0	1393.7
15°	1362.9	1365.2	1367.4	1367.7	1366.0	1364.4	1362.7	1361.0
17.5°	1328.0	1329.6	1331.1	1331.6	1331.0	1330.4	1329.8	1329.2
20°	1302.3	1303.4	1304.5	1304.6	1303.8	1302.9	1302.1	1301.2
22.5°	1274.9	1275.8	1276.7	1276.6	1275.6	1274.5	1273.4	1272.4
25°	1229.6	1229.9	1230.2	1229.9	1229.1	1228.2	1227.4	1226.5
27.5°	1181.5	1181.6	1181.9	1181.5	1180.4	1179.3	1178.3	1177.3
30°	1148.1	1148.1	1148.1	1147.2	1145.2	1143.3	1141.3	1139.4
32.5°	1113.1	1111.6	1110.0	1108.7	1107.7	1106.6	1105.6	1104.5
35°	1056.4	1054.7	1053.0	1051.5	1050.1	1048.8	1047.3	1046.0
37.5°	997.7	995.7	993.7	992.3	991.3	990.5	989.6	988.7
40°	959.4	957.2	955.0	953.3	952.2	951.1	950.0	948.9
42.5°	919.6	917.3	915.1	913.5	912.4	911.2	910.1	909.0
45°	860.1	856.7	853.4	851.0	849.7	848.3	846.9	845.5
47.5°	797.4	794.2	790.8	788.6	787.4	786.2	785.0	783.8
50°	756.0	753.0	749.9	747.6	745.9	744.3	742.6	740.9
52.5°	714.1	711.5	708.8	706.7	705.0	703.4	701.7	700.1
55°	650.1	647.1	644.0	641.8	640.5	639.1	637.7	636.3
57.5°	587.3	584.6	581.9	579.7	578.1	576.6	574.9	573.3
60°	543.0	540.4	538.0	536.0	534.6	533.2	531.9	530.4
62.5°	500.1	497.6	495.1	493.4	492.4	491.5	490.6	489.6
65°	436.4	434.2	432.0	430.5	429.6	428.8	427.9	427.1
67.5°	373.2	371.2	369.3	367.7	366.6	365.4	364.2	363.1
70°	332.3	330.4	328.4	326.8	325.4	324.0	322.7	321.3
72.5°	291.0	289.2	287.5	286.3	285.6	284.9	284.2	283.4
75°	231.3	230.0	228.5	227.4	226.6	225.8	225.0	224.1
77.5°	175.7	174.8	173.8	173.3	173.3	173.3	173.3	173.3
80°	140.1	139.9	139.6	139.5	139.5	139.5	139.5	139.5
82.5°	107.8	107.3	106.9	106.5	106.2	106.1	105.8	105.6
85°	61.2	60.6	60.0	59.8	59.8	59.8	59.8	59.8
87.5°	26.8	26.7	26.7	26.7	26.8	26.9	27.0	27.1
90°	26.5	27.4	28.3	29.0	29.5	29.9	30.3	30.8
92.5°	40.9	41.7	42.4	42.6	42.3	42.1	41.7	41.5
95°	77.9	78.7	79.7	80.2	80.2	80.2	80.2	80.2
97.5°	121.0	122.2	123.2	123.7	123.6	123.5	123.4	123.3
100°	152.4	153.0	153.8	154.3	154.8	155.3	155.7	156.1
102.5°	188.5	189.3	190.0	190.2	190.1	190.0	190.0	189.9
105°	242.5	242.5	242.5	242.7	243.2	243.6	244.1	244.5
107.5°	300.9	301.6	302.3	302.5	302.3	302.0	301.7	301.4
110°	339.8	340.8	341.7	341.9	341.4	341.0	340.6	340.1





TEST NUMBER: P332233-927

CATALOG NUMBER: S123DIW-S1165D1320U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	378.8	379.9	381.0	381.5	381.4	381.4	381.3	381.2
115°	438.2	438.4	438.6	438.6	438.4	438.2	437.9	437.7
117.5°	498.0	498.0	497.9	497.6	496.9	496.3	495.7	495.0
120°	537.9	537.7	537.5	537.1	536.7	536.2	535.8	535.3
122.5°	578.3	577.7	577.1	576.5	575.8	575.2	574.6	573.9
125°	638.3	637.4	636.4	635.6	634.6	633.7	632.8	631.8
127.5°	697.5	696.2	695.0	693.8	692.8	691.7	690.7	689.6
130°	736.9	736.0	735.1	733.8	732.2	730.6	729.0	727.5
132.5°	775.2	774.0	773.0	771.8	770.6	769.4	768.1	766.9
135°	832.4	831.6	830.6	830.0	829.5	829.0	828.5	828.1
137.5°	888.4	887.5	886.5	885.7	884.8	883.9	883.0	882.2
140°	925.3	925.0	924.8	923.9	922.3	920.7	919.1	917.5
142.5°	959.8	959.6	959.3	958.6	957.4	956.2	954.9	953.7
145°	1010.5	1010.3	1010.1	1009.6	1008.6	1007.7	1006.8	1005.8
147.5°	1058.4	1058.4	1058.4	1057.8	1056.5	1055.0	1053.7	1052.3
150°	1088.1	1088.1	1088.1	1087.3	1086.0	1084.7	1083.2	1081.9
152.5°	1115.1	1115.5	1115.8	1115.4	1114.2	1113.0	1111.8	1110.6
155°	1154.6	1155.6	1156.4	1156.1	1154.5	1152.9	1151.3	1149.7
157.5°	1188.6	1189.5	1190.6	1190.3	1189.1	1187.8	1186.5	1185.3
160°	1209.5	1210.7	1211.8	1212.0	1211.0	1210.1	1209.2	1208.2
162.5°	1229.2	1230.4	1231.5	1231.4	1229.9	1228.4	1227.0	1225.5
165°	1254.2	1255.5	1256.9	1256.8	1255.2	1253.6	1252.0	1250.4
167.5°	1274.4	1275.8	1277.2	1277.2	1275.8	1274.4	1273.0	1271.5
170°	1285.5	1287.1	1288.6	1288.6	1287.1	1285.5	1283.8	1282.2
172.5°	1294.1	1295.5	1297.0	1296.9	1295.3	1293.6	1292.0	1290.5
175°	1303.5	1304.9	1306.2	1306.1	1304.5	1302.9	1301.3	1299.7
177.5°	1307.7	1308.8	1309.9	1309.8	1308.4	1307.2	1305.9	1304.6
180°	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0	1308.0

(END OF REPORT)