

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332115

Luminaire Tested: **S123DIW-S340D1535U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332115
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1535U835-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6775.5 lumens
Efficiency: N/A
Efficacy: 126.9 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° ···· 90°-270° - · - · 135°-315°



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22				
1	92	87	84	80	81	78	75	72	59	57	55	42	41	40	27	26	25	18				
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	22	16				
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	20	18	13				
4	69	59	52	46	61	53	47	42	41	36	33	29	26	24	19	17	16	11				
5	64	53	45	39	56	47	40	36	36	32	28	26	23	21	17	15	14	10				
6	58	47	39	34	52	42	35	31	33	28	24	24	21	18	15	14	12	9				
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11	8				
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	7				
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6				
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5175	5175	5175	5175
5°	6172	5198	4606	5198
10°	7725	5172	4161	5172
15°	9475	5129	3874	5129
20°	11287	5065	3688	5065
25°	11986	4986	3646	4986
30°	10274	4928	3665	4928
35°	7144	4846	3704	4846
40°	5382	4749	3693	4749
45°	4468	4606	3646	4606
50°	4002	4315	3612	4315
55°	3742	4001	3567	4001
60°	3511	3670	3531	3670
65°	3298	3347	3418	3347
70°	3094	2977	3254	2977
75°	2770	2608	2986	2608
80°	2424	2139	2572	2139
85°	1902	1556	1729	1556



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	0.7
10°-20°	151.9	2.2
20°-30°	254.9	3.8
30°-40°	288.6	4.3
40°-50°	258.8	3.8
50°-60°	208.9	3.1
60°-70°	145.6	2.1
70°-80°	76.5	1.1
80°-90°	24.4	0.4
90°-100°	125.1	1.8
100°-110°	374.3	5.5
110°-120°	636.6	9.4
120°-130°	837.4	12.4
130°-140°	941.2	13.9
140°-150°	925.2	13.7
150°-160°	778.9	11.5
160°-170°	518.5	7.7
170°-180°	181.6	2.7
0°-30°	454.2	6.7
0°-40°	742.8	11.0
0°-60°	1210.5	17.9
0°-90°	1456.9	21.5
90°-120°	1136.0	16.8
90°-150°	3839.7	56.7
90°-180°	5319.0	78.5
0°-180°	6775.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	481	481	481	481	481	
5°	571	481	426	481	571	59
15°	850	460	348	460	850	246
25°	1009	420	307	420	1009	443
35°	544	369	282	369	544	353
45°	294	303	240	303	294	232
55°	199	213	190	213	199	179
65°	130	131	134	131	130	129
75°	67	63	72	63	67	71
85°	15	13	14	13	15	19
90°	45	2	45	2	45	23
95°	118	89	118	89	118	121
105°	359	339	359	339	359	381
115°	642	641	642	641	642	636
125°	927	938	927	938	927	829
135°	1215	1217	1215	1217	1215	934
145°	1476	1476	1476	1476	1476	921
155°	1687	1690	1687	1690	1687	777
165°	1835	1841	1835	1841	1835	518
175°	1908	1915	1908	1915	1908	181
180°	1920	1920	1920	1920	1920	



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	510.3	509.9	509.0	509.7	508.2	506.2	506.0	504.1	498.7	498.4	496.9
5°	571.2	569.4	569.1	568.9	565.6	561.2	552.8	552.1	540.9	535.4	528.6
7.5°	650.2	651.1	647.7	644.8	634.8	628.2	619.2	607.7	594.0	580.0	570.8
10°	706.8	714.5	705.0	698.4	692.4	681.0	667.7	651.1	634.6	615.3	600.6
12.5°	767.6	771.3	769.4	763.3	753.9	736.5	713.0	694.7	679.5	647.3	634.3
15°	850.3	864.5	855.4	834.5	834.9	818.4	787.7	753.9	735.9	707.7	669.3
17.5°	938.5	940.2	936.4	918.9	907.3	884.5	856.1	823.8	787.4	753.3	712.5
20°	985.4	984.0	975.9	966.8	946.8	929.1	898.1	862.0	815.4	781.8	737.3
22.5°	1011.5	1009.2	1005.3	997.7	981.1	962.1	934.2	894.8	850.4	804.2	752.8
25°	1009.2	1012.2	1012.7	1010.6	1004.8	993.4	971.5	940.0	895.8	836.3	782.8
27.5°	917.9	922.2	934.6	945.7	958.0	970.6	968.9	953.3	920.5	869.2	803.7
30°	826.6	817.2	840.3	869.4	889.2	924.2	943.7	944.9	926.5	882.5	818.6
32.5°	699.8	710.1	720.3	756.1	799.4	838.6	877.6	908.9	912.5	883.2	827.4
35°	543.7	556.6	575.2	593.8	640.4	680.5	749.0	808.6	856.1	862.4	828.2
37.5°	438.2	444.5	456.3	475.0	505.4	553.0	605.9	681.3	750.2	801.4	803.6
40°	383.0	384.9	398.1	412.3	437.0	476.2	523.9	590.6	673.0	744.6	774.4
42.5°	341.6	345.7	351.4	365.0	384.7	414.1	458.5	513.6	589.2	671.5	729.8
45°	293.5	298.2	301.7	310.8	324.8	344.6	375.5	425.9	483.4	568.4	646.9
47.5°	261.8	262.1	264.7	271.6	281.1	296.0	317.9	350.2	403.0	472.0	552.6
50°	239.0	242.7	243.7	249.0	256.5	267.4	285.6	313.1	356.4	417.0	491.1
52.5°	223.0	224.1	226.7	230.6	237.1	245.6	261.4	282.9	316.9	368.6	436.7
55°	199.4	199.4	202.0	205.0	208.7	216.4	226.9	242.7	268.6	308.7	365.1
57.5°	177.6	178.8	180.6	181.5	184.7	189.8	198.5	210.6	229.8	260.7	305.5
60°	163.1	165.2	164.9	166.8	169.6	173.6	181.0	190.8	208.0	232.7	270.5
62.5°	150.4	150.3	150.2	152.5	155.2	159.0	163.9	172.3	187.0	208.9	241.0
65°	129.5	129.1	130.7	132.1	133.0	135.8	139.5	147.0	156.8	173.1	198.0
67.5°	111.0	109.6	110.5	111.0	112.6	114.8	118.3	122.9	130.6	143.7	162.5
70°	98.3	97.1	96.9	97.4	98.8	100.4	103.0	107.4	114.6	125.1	138.8
72.5°	85.3	84.5	84.4	85.5	86.1	87.2	89.0	93.0	98.8	106.7	119.5
75°	66.6	66.6	66.6	66.9	67.6	68.5	69.9	72.0	76.4	82.0	90.6
77.5°	49.9	49.9	49.6	49.6	50.6	51.0	51.3	53.3	55.8	59.5	65.8
80°	39.1	38.0	38.4	39.1	39.6	39.8	40.5	41.0	43.1	45.2	49.6
82.5°	29.1	28.1	28.2	29.3	29.4	29.6	30.3	30.9	31.7	33.6	36.0
85°	15.4	15.4	15.6	15.6	15.8	15.6	16.3	16.5	16.5	17.7	19.1
87.5°	14.6	14.1	14.2	14.2	13.9	13.9	13.8	13.7	13.7	13.6	12.9
90°	45.2	44.6	43.9	43.2	42.6	41.6	40.2	38.9	37.5	36.2	31.8
92.5°	60.9	61.3	61.7	62.1	62.5	62.2	61.1	60.0	59.0	57.9	55.4
95°	117.6	117.6	117.6	117.6	117.6	116.9	115.6	114.3	112.9	111.6	108.9
97.5°	181.0	181.1	181.2	181.4	181.5	180.8	179.2	177.7	176.2	174.6	172.7
100°	229.2	228.5	227.9	227.2	226.5	225.7	224.7	223.7	222.7	221.7	220.0
102.5°	278.7	278.8	278.9	279.1	279.2	278.8	277.8	276.8	275.8	274.7	272.5
105°	358.9	358.2	357.6	356.9	356.2	355.9	355.9	355.9	355.9	355.9	352.9
107.5°	442.4	442.8	443.2	443.6	444.0	443.7	442.6	441.6	440.5	439.4	438.2
110°	499.1	499.8	500.5	501.1	501.8	501.5	500.1	498.8	497.5	496.1	495.4



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	559.4	559.6	559.7	559.9	560.0	559.2	557.6	556.0	554.4	552.8	552.7
115°	642.4	642.7	643.1	643.4	643.7	643.7	643.4	643.1	642.7	642.4	643.1
117.5°	726.5	727.5	728.4	729.3	730.3	730.8	730.9	730.9	731.0	731.1	731.9
120°	785.6	786.3	787.0	787.7	788.3	788.8	789.2	789.5	789.8	790.2	791.8
122.5°	842.3	843.3	844.2	845.2	846.1	847.0	847.9	848.7	849.6	850.5	851.4
125°	927.4	928.7	930.1	931.4	932.7	934.1	935.4	936.8	938.1	939.5	940.1
127.5°	1012.1	1013.7	1015.2	1016.8	1018.3	1020.0	1021.9	1023.8	1025.6	1027.5	1028.3
130°	1067.6	1070.0	1072.3	1074.7	1077.0	1078.9	1080.2	1081.5	1082.9	1084.2	1085.2
132.5°	1125.5	1127.3	1129.2	1131.0	1132.8	1134.5	1136.1	1137.7	1139.3	1140.9	1141.6
135°	1215.4	1216.1	1216.7	1217.4	1218.1	1219.1	1220.4	1221.8	1223.1	1224.5	1224.8
137.5°	1294.7	1296.0	1297.3	1298.5	1299.8	1301.2	1302.6	1304.0	1305.4	1306.8	1305.9
140°	1346.6	1348.9	1351.3	1353.6	1356.0	1357.3	1357.7	1358.0	1358.3	1358.7	1358.3
142.5°	1399.7	1401.5	1403.3	1405.1	1406.9	1408.0	1408.3	1408.7	1409.0	1409.3	1408.7
145°	1476.3	1477.6	1479.0	1480.3	1481.6	1482.5	1482.8	1483.1	1483.5	1483.8	1482.8
147.5°	1544.4	1546.4	1548.5	1550.5	1552.5	1553.5	1553.5	1553.5	1553.5	1553.5	1552.5
150°	1587.9	1589.9	1591.9	1593.9	1595.9	1596.9	1596.9	1596.9	1596.9	1596.9	1596.2
152.5°	1630.1	1631.8	1633.6	1635.3	1637.1	1637.7	1637.1	1636.6	1636.1	1635.5	1635.1
155°	1687.4	1689.7	1692.1	1694.4	1696.8	1697.3	1695.9	1694.6	1693.3	1691.9	1691.6
157.5°	1739.6	1741.4	1743.3	1745.2	1747.1	1747.3	1745.9	1744.5	1743.1	1741.7	1741.4
160°	1773.3	1774.7	1776.0	1777.4	1778.7	1778.5	1776.9	1775.2	1773.5	1771.8	1771.8
162.5°	1798.7	1800.8	1803.0	1805.1	1807.3	1807.5	1805.8	1804.1	1802.5	1800.8	1800.5
165°	1835.2	1837.5	1839.9	1842.2	1844.6	1844.7	1842.7	1840.7	1838.7	1836.7	1836.7
167.5°	1866.2	1868.3	1870.4	1872.5	1874.5	1874.5	1872.5	1870.4	1868.3	1866.2	1866.0
170°	1881.9	1884.3	1886.6	1889.0	1891.3	1891.3	1889.0	1886.6	1884.3	1881.9	1881.9
172.5°	1894.0	1896.3	1898.7	1901.0	1903.4	1903.5	1901.4	1899.3	1897.3	1895.2	1895.2
175°	1907.6	1909.9	1912.2	1914.6	1916.9	1917.1	1915.1	1913.1	1911.1	1909.1	1909.1
177.5°	1914.8	1916.7	1918.5	1920.4	1922.3	1922.4	1920.8	1919.2	1917.6	1916.0	1916.0
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	495.7	494.3	492.8	490.2	487.9	484.8	483.8	482.7	479.3	476.4	474.1
5°	526.0	520.4	512.3	504.8	498.8	490.6	486.0	481.1	474.1	467.8	462.7
7.5°	557.7	546.7	534.0	520.4	507.6	495.3	485.4	476.5	466.7	457.5	450.2
10°	582.9	567.0	549.3	530.2	513.9	498.1	484.8	473.2	460.6	449.6	440.5
12.5°	611.6	588.1	563.7	540.5	521.2	499.2	483.1	468.3	454.0	440.9	430.7
15°	645.5	615.7	586.8	554.9	525.6	498.1	479.0	460.3	443.8	430.3	417.2
17.5°	676.5	642.7	604.6	565.8	530.4	497.8	471.1	450.0	429.3	412.8	399.8
20°	694.0	655.6	612.5	572.2	533.0	496.7	467.3	442.2	419.8	402.3	387.7
22.5°	709.1	664.1	619.5	576.4	532.8	493.7	460.4	434.5	410.3	393.2	377.6
25°	724.8	670.9	626.2	575.7	527.0	486.4	449.2	419.8	395.6	375.5	359.5
27.5°	738.2	670.5	617.4	563.0	517.7	477.1	437.3	405.8	380.1	358.3	342.0
30°	747.1	671.4	608.3	554.5	508.8	466.9	428.2	396.5	369.5	347.4	332.0
32.5°	752.7	670.8	599.9	542.5	494.6	457.5	418.3	385.5	357.7	336.0	321.2
35°	756.0	666.7	585.4	517.9	471.8	435.6	402.8	368.8	339.7	319.4	302.6
37.5°	749.4	658.1	568.7	494.1	443.6	408.1	380.4	351.5	323.6	301.3	286.8
40°	739.2	652.5	555.6	477.3	424.2	390.0	366.5	338.0	310.5	289.3	275.8
42.5°	719.6	641.2	541.3	458.7	404.1	369.9	348.2	324.4	298.4	278.5	265.0
45°	671.9	616.4	519.7	430.8	374.4	339.0	319.9	302.6	279.1	259.8	248.1
47.5°	605.6	579.2	488.6	401.3	343.3	309.3	289.4	275.6	258.4	242.7	231.6
50°	559.6	548.6	467.6	381.1	322.7	289.3	270.2	257.7	245.3	229.7	219.5
52.5°	506.5	513.2	443.0	360.3	301.6	268.8	250.9	240.9	229.7	216.8	207.9
55°	431.7	456.1	400.5	325.2	270.2	239.0	222.0	213.2	206.6	197.1	189.4
57.5°	361.7	392.8	354.5	289.1	239.4	212.5	196.2	186.6	182.4	177.4	171.3
60°	320.1	350.8	321.7	264.9	218.8	193.1	178.7	170.5	166.3	162.8	157.7
62.5°	283.0	314.1	289.7	240.3	198.4	174.7	162.1	154.1	150.9	149.1	144.7
65°	232.0	258.8	242.5	202.0	169.4	148.4	137.0	131.4	128.4	127.7	124.9
67.5°	188.8	209.2	197.4	167.5	141.9	123.8	114.1	109.3	107.0	106.7	104.6
70°	160.5	179.6	170.5	143.5	121.4	107.2	98.8	94.6	93.2	93.0	91.8
72.5°	138.5	151.8	144.6	122.1	105.0	92.1	85.9	81.5	80.0	80.3	79.5
75°	102.5	112.5	108.3	92.7	79.0	70.6	65.5	62.7	61.3	62.0	61.0
77.5°	73.8	80.1	76.3	65.5	57.0	51.0	47.2	45.5	44.2	44.2	43.8
80°	55.7	59.4	57.3	50.8	43.8	38.7	35.6	34.5	33.8	33.5	33.3
82.5°	39.7	42.8	40.3	35.9	31.1	28.0	26.3	24.8	24.3	24.4	24.2
85°	20.0	21.2	20.3	17.5	15.6	14.2	13.3	12.6	12.1	12.3	11.9
87.5°	12.4	11.7	10.3	8.8	7.7	6.5	5.8	4.8	5.1	5.7	6.2
90°	27.5	23.1	18.8	14.9	11.6	8.2	4.9	1.5	4.9	8.2	11.6
92.5°	52.9	50.5	48.0	45.6	43.3	41.0	38.8	36.5	38.8	41.0	43.3
95°	106.2	103.5	100.9	98.4	96.0	93.7	91.3	89.0	91.3	93.7	96.0
97.5°	170.7	168.8	166.8	165.0	163.3	161.5	159.8	158.0	159.8	161.5	163.3
100°	218.3	216.6	215.0	213.1	211.1	209.1	207.1	205.1	207.1	209.1	211.1
102.5°	270.3	268.1	265.9	264.2	263.0	261.8	260.6	259.4	260.6	261.8	263.0
105°	349.8	346.8	343.8	342.0	341.3	340.6	340.0	339.3	340.0	340.6	341.3
107.5°	437.0	435.8	434.6	433.8	433.4	433.0	432.6	432.2	432.6	433.0	433.4
110°	494.8	494.1	493.4	492.8	492.1	491.4	490.8	490.1	490.8	491.4	492.1



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	552.5	552.4	552.3	552.0	551.6	551.2	550.8	550.4	550.8	551.2	551.6
115°	643.7	644.4	645.1	644.9	643.9	642.9	641.9	640.9	641.9	642.9	643.9
117.5°	732.8	733.7	734.5	734.6	734.0	733.3	732.6	732.0	732.6	733.3	734.0
120°	793.5	795.2	796.9	796.7	794.7	792.7	790.7	788.7	790.7	792.7	794.7
122.5°	852.2	853.1	854.0	853.7	852.2	850.7	849.2	847.8	849.2	850.7	852.2
125°	940.8	941.5	942.1	942.0	941.0	940.0	938.9	937.9	938.9	940.0	941.0
127.5°	1029.0	1029.7	1030.5	1029.8	1027.6	1025.5	1023.3	1021.2	1023.3	1025.5	1027.6
130°	1086.2	1087.2	1088.2	1087.4	1084.7	1082.0	1079.4	1076.7	1079.4	1082.0	1084.7
132.5°	1142.4	1143.1	1143.9	1142.9	1140.2	1137.5	1134.8	1132.2	1134.8	1137.5	1140.2
135°	1225.1	1225.5	1225.8	1225.0	1222.9	1220.9	1218.9	1216.9	1218.9	1220.9	1222.9
137.5°	1305.0	1304.2	1303.3	1302.0	1300.4	1298.7	1297.0	1295.3	1297.0	1298.7	1300.4
140°	1358.0	1357.7	1357.3	1356.3	1354.6	1353.0	1351.3	1349.6	1351.3	1353.0	1354.6
142.5°	1408.1	1407.5	1406.9	1405.8	1404.1	1402.4	1400.7	1399.1	1400.7	1402.4	1404.1
145°	1481.8	1480.8	1479.8	1479.0	1478.3	1477.6	1477.0	1476.3	1477.0	1477.6	1478.3
147.5°	1551.6	1550.7	1549.7	1548.7	1547.5	1546.2	1545.0	1543.8	1545.0	1546.2	1547.5
150°	1595.6	1594.9	1594.2	1593.6	1592.9	1592.2	1591.6	1590.9	1591.6	1592.2	1592.9
152.5°	1634.7	1634.3	1633.9	1633.2	1632.3	1631.4	1630.4	1629.5	1630.4	1631.4	1632.3
155°	1691.2	1690.9	1690.6	1690.4	1690.4	1690.4	1690.4	1690.4	1690.4	1690.4	1690.4
157.5°	1741.1	1740.9	1740.6	1740.7	1741.1	1741.5	1741.9	1742.3	1741.9	1741.5	1741.1
160°	1771.8	1771.8	1771.8	1772.2	1772.8	1773.5	1774.2	1774.9	1774.2	1773.5	1772.8
162.5°	1800.3	1800.0	1799.7	1800.1	1801.0	1801.9	1802.9	1803.8	1802.9	1801.9	1801.0
165°	1836.7	1836.7	1836.7	1837.2	1838.2	1839.2	1840.2	1841.2	1840.2	1839.2	1838.2
167.5°	1865.7	1865.4	1865.2	1865.7	1867.0	1868.4	1869.7	1871.1	1869.7	1868.4	1867.0
170°	1881.9	1881.9	1881.9	1882.6	1883.9	1885.3	1886.6	1887.9	1886.6	1885.3	1883.9
172.5°	1895.2	1895.2	1895.2	1895.9	1897.2	1898.5	1899.9	1901.2	1899.9	1898.5	1897.2
175°	1909.1	1909.1	1909.1	1909.7	1911.1	1912.4	1913.8	1915.1	1913.8	1912.4	1911.1
177.5°	1916.0	1916.0	1916.0	1916.5	1917.6	1918.7	1919.8	1920.8	1919.8	1918.7	1917.6
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	472.8	471.5	469.7	466.9	464.6	461.1	461.1	461.6	461.6	461.5	461.1
5°	458.5	455.0	450.8	445.9	440.8	435.6	434.7	432.8	431.5	430.5	429.4
7.5°	443.3	437.1	431.0	424.2	417.9	412.8	409.2	406.2	404.3	402.2	400.7
10°	433.1	425.4	418.2	411.0	403.0	396.7	392.8	390.0	387.9	386.0	385.1
12.5°	421.0	412.2	404.2	397.3	388.7	382.2	378.4	377.1	374.7	370.7	368.7
15°	403.3	395.1	385.6	375.1	370.9	363.0	358.5	356.4	355.0	352.0	351.1
17.5°	388.1	377.5	366.7	358.9	351.1	344.7	342.2	339.6	337.8	335.3	334.5
20°	376.0	366.5	356.7	348.3	340.1	333.1	331.0	329.2	327.3	326.2	325.2
22.5°	363.7	354.2	346.0	338.2	329.5	324.9	322.7	320.6	319.3	318.5	317.6
25°	346.4	338.0	328.9	322.0	315.0	311.9	310.5	309.4	308.4	307.3	307.0
27.5°	331.0	321.8	314.5	307.9	302.9	300.4	299.0	298.5	298.7	299.1	299.4
30°	319.4	311.0	305.0	299.4	294.7	292.4	292.1	292.1	293.1	293.3	293.8
32.5°	308.8	301.9	295.8	290.4	286.9	285.3	286.2	286.2	286.9	287.5	288.4
35°	293.3	287.2	282.6	277.9	274.9	275.6	276.1	276.5	277.7	279.1	280.0
37.5°	278.5	273.3	268.4	264.8	263.4	264.6	265.8	266.7	268.1	269.2	270.1
40°	267.9	263.9	259.3	256.0	256.5	257.2	258.1	259.3	260.5	261.2	262.1
42.5°	258.0	253.9	250.3	247.6	248.3	249.2	249.7	250.3	251.7	253.0	253.5
45°	243.0	239.7	236.5	234.8	235.3	235.8	236.2	236.9	238.1	239.0	239.3
47.5°	226.1	223.8	221.6	220.0	220.8	220.6	221.2	222.7	223.0	223.6	224.9
50°	215.3	213.2	210.6	210.1	210.1	210.1	210.4	212.2	212.2	213.2	214.1
52.5°	203.3	202.0	200.4	199.5	199.1	199.1	200.1	201.0	201.4	202.7	203.7
55°	185.7	184.3	182.9	182.2	181.7	182.2	184.0	184.5	185.7	186.4	187.1
57.5°	167.3	166.2	165.1	164.7	164.6	165.2	166.2	167.6	167.9	170.1	171.1
60°	155.2	153.5	152.6	152.6	152.1	154.2	153.8	156.1	156.6	158.0	159.6
62.5°	142.7	140.5	140.1	140.1	140.8	141.4	142.0	143.0	144.3	146.0	147.3
65°	122.5	121.4	123.0	122.8	122.3	123.7	123.7	124.9	126.3	127.9	130.5
67.5°	103.5	102.9	103.0	103.0	103.7	104.5	105.2	106.2	107.9	109.6	111.3
70°	90.6	91.3	90.2	91.1	91.8	92.0	92.5	93.9	95.7	96.9	98.8
72.5°	78.1	78.1	78.2	78.6	79.3	79.7	80.2	81.8	83.8	84.8	86.3
75°	60.1	59.9	60.6	60.6	61.7	62.2	62.7	63.4	65.2	66.6	67.8
77.5°	43.9	44.2	44.0	44.8	44.5	44.6	46.0	46.7	46.9	49.7	50.3
80°	33.1	33.5	33.8	34.0	34.2	33.8	35.4	36.1	36.1	37.7	38.9
82.5°	23.8	24.0	24.6	24.9	24.9	25.4	25.5	26.0	26.6	27.3	28.8
85°	11.9	12.6	12.8	12.6	12.8	12.3	13.0	13.3	13.5	13.5	13.5
87.5°	6.7	7.7	8.4	9.4	10.1	11.2	11.4	11.3	11.6	12.4	11.9
90°	14.9	18.8	23.1	27.5	31.8	36.2	37.5	38.9	40.2	41.6	42.6
92.5°	45.6	48.0	50.5	52.9	55.4	57.9	59.0	60.0	61.1	62.2	62.5
95°	98.4	100.9	103.5	106.2	108.9	111.6	112.9	114.3	115.6	116.9	117.6
97.5°	165.0	166.8	168.8	170.7	172.7	174.6	176.2	177.7	179.2	180.8	181.5
100°	213.1	215.0	216.6	218.3	220.0	221.7	222.7	223.7	224.7	225.7	226.5
102.5°	264.2	265.9	268.1	270.3	272.5	274.7	275.8	276.8	277.8	278.8	279.2
105°	342.0	343.8	346.8	349.8	352.9	355.9	355.9	355.9	355.9	355.9	356.2
107.5°	433.8	434.6	435.8	437.0	438.2	439.4	440.5	441.6	442.6	443.7	444.0
110°	492.8	493.4	494.1	494.8	495.4	496.1	497.5	498.8	500.1	501.5	501.8



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	552.0	552.3	552.4	552.5	552.7	552.8	554.4	556.0	557.6	559.2	560.0
115°	644.9	645.1	644.4	643.7	643.1	642.4	642.7	643.1	643.4	643.7	643.7
117.5°	734.6	734.5	733.7	732.8	731.9	731.1	731.0	730.9	730.9	730.8	730.3
120°	796.7	796.9	795.2	793.5	791.8	790.2	789.8	789.5	789.2	788.8	788.3
122.5°	853.7	854.0	853.1	852.2	851.4	850.5	849.6	848.7	847.9	847.0	846.1
125°	942.0	942.1	941.5	940.8	940.1	939.5	938.1	936.8	935.4	934.1	932.7
127.5°	1029.8	1030.5	1029.7	1029.0	1028.3	1027.5	1025.6	1023.8	1021.9	1020.0	1018.3
130°	1087.4	1088.2	1087.2	1086.2	1085.2	1084.2	1082.9	1081.5	1080.2	1078.9	1077.0
132.5°	1142.9	1143.9	1143.1	1142.4	1141.6	1140.9	1139.3	1137.7	1136.1	1134.5	1132.8
135°	1225.0	1225.8	1225.5	1225.1	1224.8	1224.5	1223.1	1221.8	1220.4	1219.1	1218.1
137.5°	1302.0	1303.3	1304.2	1305.0	1305.9	1306.8	1305.4	1304.0	1302.6	1301.2	1299.8
140°	1356.3	1357.3	1357.7	1358.0	1358.3	1358.7	1358.3	1358.0	1357.7	1357.3	1356.0
142.5°	1405.8	1406.9	1407.5	1408.1	1408.7	1409.3	1409.0	1408.7	1408.3	1408.0	1406.9
145°	1479.0	1479.8	1480.8	1481.8	1482.8	1483.8	1483.5	1483.1	1482.8	1482.5	1481.6
147.5°	1548.7	1549.7	1550.7	1551.6	1552.5	1553.5	1553.5	1553.5	1553.5	1553.5	1552.5
150°	1593.6	1594.2	1594.9	1595.6	1596.2	1596.9	1596.9	1596.9	1596.9	1596.9	1595.9
152.5°	1633.2	1633.9	1634.3	1634.7	1635.1	1635.5	1636.1	1636.6	1637.1	1637.7	1637.1
155°	1690.4	1690.6	1690.9	1691.2	1691.6	1691.9	1693.3	1694.6	1695.9	1697.3	1696.8
157.5°	1740.7	1740.6	1740.9	1741.1	1741.4	1741.7	1743.1	1744.5	1745.9	1747.3	1747.1
160°	1772.2	1771.8	1771.8	1771.8	1771.8	1771.8	1773.5	1775.2	1776.9	1778.5	1778.7
162.5°	1800.1	1799.7	1800.0	1800.3	1800.5	1800.8	1802.5	1804.1	1805.8	1807.5	1807.3
165°	1837.2	1836.7	1836.7	1836.7	1836.7	1836.7	1838.7	1840.7	1842.7	1844.7	1844.6
167.5°	1865.7	1865.2	1865.4	1865.7	1866.0	1866.2	1868.3	1870.4	1872.5	1874.5	1874.5
170°	1882.6	1881.9	1881.9	1881.9	1881.9	1881.9	1884.3	1886.6	1889.0	1891.3	1891.3
172.5°	1895.9	1895.2	1895.2	1895.2	1895.2	1895.2	1897.3	1899.3	1901.4	1903.5	1903.4
175°	1909.7	1909.1	1909.1	1909.1	1909.1	1909.1	1911.1	1913.1	1915.1	1917.1	1916.9
177.5°	1916.5	1916.0	1916.0	1916.0	1916.0	1916.0	1917.6	1919.2	1920.8	1922.4	1922.3
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	459.8	459.6	460.9	460.0	460.9	459.6	459.8	461.1	461.5	461.6	461.6
5°	428.0	428.7	426.3	426.3	426.3	428.7	428.0	429.4	430.5	431.5	432.8
7.5°	399.6	398.6	398.7	397.4	398.7	398.6	399.6	400.7	402.2	404.3	406.2
10°	382.3	380.9	380.4	380.7	380.4	380.9	382.3	385.1	386.0	387.9	390.0
12.5°	367.9	367.7	364.6	364.6	364.6	367.7	367.9	368.7	370.7	374.7	377.1
15°	351.1	346.7	346.2	347.6	346.2	346.7	351.1	351.1	352.0	355.0	356.4
17.5°	334.2	331.8	332.0	331.3	332.0	331.8	334.2	334.5	335.3	337.8	339.6
20°	325.2	323.8	323.6	322.0	323.6	323.8	325.2	325.2	326.2	327.3	329.2
22.5°	317.0	316.6	316.7	314.9	316.7	316.6	317.0	317.6	318.5	319.3	320.6
25°	306.8	308.0	307.0	307.0	307.0	308.0	306.8	307.0	307.3	308.4	309.4
27.5°	299.9	299.9	299.4	299.4	299.4	299.9	299.9	299.4	299.1	298.7	298.5
30°	294.7	294.5	294.9	294.9	294.9	294.5	294.7	293.8	293.3	293.1	292.1
32.5°	289.5	289.8	289.9	290.1	289.9	289.8	289.5	288.4	287.5	286.9	286.2
35°	281.4	281.7	282.4	281.9	282.4	281.7	281.4	280.0	279.1	277.7	276.5
37.5°	270.5	271.6	271.4	271.7	271.4	271.6	270.5	270.1	269.2	268.1	266.7
40°	262.3	263.0	262.8	262.8	262.8	263.0	262.3	262.1	261.2	260.5	259.3
42.5°	253.9	254.4	253.8	253.5	253.8	254.4	253.9	253.5	253.0	251.7	250.3
45°	240.2	239.7	240.4	239.5	240.4	239.7	240.2	239.3	239.0	238.1	236.9
47.5°	224.8	225.3	225.5	226.2	225.5	225.3	224.8	224.9	223.6	223.0	222.7
50°	214.6	216.0	216.0	215.7	216.0	216.0	214.6	214.1	213.2	212.2	212.2
52.5°	204.5	205.1	206.1	206.0	206.1	205.1	204.5	203.7	202.7	201.4	201.0
55°	188.9	189.4	189.9	190.1	189.9	189.4	188.9	187.1	186.4	185.7	184.5
57.5°	172.8	172.6	173.7	174.1	173.7	172.6	172.8	171.1	170.1	167.9	167.6
60°	161.4	161.4	163.3	164.0	163.3	161.4	161.4	159.6	158.0	156.6	156.1
62.5°	149.3	150.1	151.9	151.0	151.9	150.1	149.3	147.3	146.0	144.3	143.0
65°	131.6	133.5	133.3	134.2	133.3	133.5	131.6	130.5	127.9	126.3	124.9
67.5°	113.1	114.3	116.0	116.1	116.0	114.3	113.1	111.3	109.6	107.9	106.2
70°	100.6	101.8	102.7	103.4	102.7	101.8	100.6	98.8	96.9	95.7	93.9
72.5°	88.5	89.1	91.4	90.4	91.4	89.1	88.5	86.3	84.8	83.8	81.8
75°	69.4	71.1	72.5	71.8	72.5	71.1	69.4	67.8	66.6	65.2	63.4
77.5°	51.3	53.0	53.6	53.0	53.6	53.0	51.3	50.3	49.7	46.9	46.7
80°	40.5	40.3	41.7	41.5	41.7	40.3	40.5	38.9	37.7	36.1	36.1
82.5°	29.7	29.5	30.1	30.3	30.1	29.5	29.7	28.8	27.3	26.6	26.0
85°	14.4	15.1	14.2	14.0	14.2	15.1	14.4	13.5	13.5	13.5	13.3
87.5°	12.0	12.1	12.1	12.0	12.1	12.1	12.0	11.9	12.4	11.6	11.3
90°	43.2	43.9	44.6	45.2	44.6	43.9	43.2	42.6	41.6	40.2	38.9
92.5°	62.1	61.7	61.3	60.9	61.3	61.7	62.1	62.5	62.2	61.1	60.0
95°	117.6	117.6	117.6	117.6	117.6	117.6	117.6	117.6	116.9	115.6	114.3
97.5°	181.4	181.2	181.1	181.0	181.1	181.2	181.4	181.5	180.8	179.2	177.7
100°	227.2	227.9	228.5	229.2	228.5	227.9	227.2	226.5	225.7	224.7	223.7
102.5°	279.1	278.9	278.8	278.7	278.8	278.9	279.1	279.2	278.8	277.8	276.8
105°	356.9	357.6	358.2	358.9	358.2	357.6	356.9	356.2	355.9	355.9	355.9
107.5°	443.6	443.2	442.8	442.4	442.8	443.2	443.6	444.0	443.7	442.6	441.6
110°	501.1	500.5	499.8	499.1	499.8	500.5	501.1	501.8	501.5	500.1	498.8



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	559.9	559.7	559.6	559.4	559.6	559.7	559.9	560.0	559.2	557.6	556.0
115°	643.4	643.1	642.7	642.4	642.7	643.1	643.4	643.7	643.7	643.4	643.1
117.5°	729.3	728.4	727.5	726.5	727.5	728.4	729.3	730.3	730.8	730.9	730.9
120°	787.7	787.0	786.3	785.6	786.3	787.0	787.7	788.3	788.8	789.2	789.5
122.5°	845.2	844.2	843.3	842.3	843.3	844.2	845.2	846.1	847.0	847.9	848.7
125°	931.4	930.1	928.7	927.4	928.7	930.1	931.4	932.7	934.1	935.4	936.8
127.5°	1016.8	1015.2	1013.7	1012.1	1013.7	1015.2	1016.8	1018.3	1020.0	1021.9	1023.8
130°	1074.7	1072.3	1070.0	1067.6	1070.0	1072.3	1074.7	1077.0	1078.9	1080.2	1081.5
132.5°	1131.0	1129.2	1127.3	1125.5	1127.3	1129.2	1131.0	1132.8	1134.5	1136.1	1137.7
135°	1217.4	1216.7	1216.1	1215.4	1216.1	1216.7	1217.4	1218.1	1219.1	1220.4	1221.8
137.5°	1298.5	1297.3	1296.0	1294.7	1296.0	1297.3	1298.5	1299.8	1301.2	1302.6	1304.0
140°	1353.6	1351.3	1348.9	1346.6	1348.9	1351.3	1353.6	1356.0	1357.3	1357.7	1358.0
142.5°	1405.1	1403.3	1401.5	1399.7	1401.5	1403.3	1405.1	1406.9	1408.0	1408.3	1408.7
145°	1480.3	1479.0	1477.6	1476.3	1477.6	1479.0	1480.3	1481.6	1482.5	1482.8	1483.1
147.5°	1550.5	1548.5	1546.4	1544.4	1546.4	1548.5	1550.5	1552.5	1553.5	1553.5	1553.5
150°	1593.9	1591.9	1589.9	1587.9	1589.9	1591.9	1593.9	1595.9	1596.9	1596.9	1596.9
152.5°	1635.3	1633.6	1631.8	1630.1	1631.8	1633.6	1635.3	1637.1	1637.7	1637.1	1636.6
155°	1694.4	1692.1	1689.7	1687.4	1689.7	1692.1	1694.4	1696.8	1697.3	1695.9	1694.6
157.5°	1745.2	1743.3	1741.4	1739.6	1741.4	1743.3	1745.2	1747.1	1747.3	1745.9	1744.5
160°	1777.4	1776.0	1774.7	1773.3	1774.7	1776.0	1777.4	1778.7	1778.5	1776.9	1775.2
162.5°	1805.1	1803.0	1800.8	1798.7	1800.8	1803.0	1805.1	1807.3	1807.5	1805.8	1804.1
165°	1842.2	1839.9	1837.5	1835.2	1837.5	1839.9	1842.2	1844.6	1844.7	1842.7	1840.7
167.5°	1872.5	1870.4	1868.3	1866.2	1868.3	1870.4	1872.5	1874.5	1874.5	1872.5	1870.4
170°	1889.0	1886.6	1884.3	1881.9	1884.3	1886.6	1889.0	1891.3	1891.3	1889.0	1886.6
172.5°	1901.0	1898.7	1896.3	1894.0	1896.3	1898.7	1901.0	1903.4	1903.5	1901.4	1899.3
175°	1914.6	1912.2	1909.9	1907.6	1909.9	1912.2	1914.6	1916.9	1917.1	1915.1	1913.1
177.5°	1920.4	1918.5	1916.7	1914.8	1916.7	1918.5	1920.4	1922.3	1922.4	1920.8	1919.2
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	461.1	461.1	464.6	466.9	469.7	471.5	472.8	474.1	476.4	479.3	482.7
5°	434.7	435.6	440.8	445.9	450.8	455.0	458.5	462.7	467.8	474.1	481.1
7.5°	409.2	412.8	417.9	424.2	431.0	437.1	443.3	450.2	457.5	466.7	476.5
10°	392.8	396.7	403.0	411.0	418.2	425.4	433.1	440.5	449.6	460.6	473.2
12.5°	378.4	382.2	388.7	397.3	404.2	412.2	421.0	430.7	440.9	454.0	468.3
15°	358.5	363.0	370.9	375.1	385.6	395.1	403.3	417.2	430.3	443.8	460.3
17.5°	342.2	344.7	351.1	358.9	366.7	377.5	388.1	399.8	412.8	429.3	450.0
20°	331.0	333.1	340.1	348.3	356.7	366.5	376.0	387.7	402.3	419.8	442.2
22.5°	322.7	324.9	329.5	338.2	346.0	354.2	363.7	377.6	393.2	410.3	434.5
25°	310.5	311.9	315.0	322.0	328.9	338.0	346.4	359.5	375.5	395.6	419.8
27.5°	299.0	300.4	302.9	307.9	314.5	321.8	331.0	342.0	358.3	380.1	405.8
30°	292.1	292.4	294.7	299.4	305.0	311.0	319.4	332.0	347.4	369.5	396.5
32.5°	286.2	285.3	286.9	290.4	295.8	301.9	308.8	321.2	336.0	357.7	385.5
35°	276.1	275.6	274.9	277.9	282.6	287.2	293.3	302.6	319.4	339.7	368.8
37.5°	265.8	264.6	263.4	264.8	268.4	273.3	278.5	286.8	301.3	323.6	351.5
40°	258.1	257.2	256.5	256.0	259.3	263.9	267.9	275.8	289.3	310.5	338.0
42.5°	249.7	249.2	248.3	247.6	250.3	253.9	258.0	265.0	278.5	298.4	324.4
45°	236.2	235.8	235.3	234.8	236.5	239.7	243.0	248.1	259.8	279.1	302.6
47.5°	221.2	220.6	220.8	220.0	221.6	223.8	226.1	231.6	242.7	258.4	275.6
50°	210.4	210.1	210.1	210.1	210.6	213.2	215.3	219.5	229.7	245.3	257.7
52.5°	200.1	199.1	199.1	199.5	200.4	202.0	203.3	207.9	216.8	229.7	240.9
55°	184.0	182.2	181.7	182.2	182.9	184.3	185.7	189.4	197.1	206.6	213.2
57.5°	166.2	165.2	164.6	164.7	165.1	166.2	167.3	171.3	177.4	182.4	186.6
60°	153.8	154.2	152.1	152.6	152.6	153.5	155.2	157.7	162.8	166.3	170.5
62.5°	142.0	141.4	140.8	140.1	140.1	140.5	142.7	144.7	149.1	150.9	154.1
65°	123.7	123.7	122.3	122.8	123.0	121.4	122.5	124.9	127.7	128.4	131.4
67.5°	105.2	104.5	103.7	103.0	103.0	102.9	103.5	104.6	106.7	107.0	109.3
70°	92.5	92.0	91.8	91.1	90.2	91.3	90.6	91.8	93.0	93.2	94.6
72.5°	80.2	79.7	79.3	78.6	78.2	78.1	78.1	79.5	80.3	80.0	81.5
75°	62.7	62.2	61.7	60.6	60.6	59.9	60.1	61.0	62.0	61.3	62.7
77.5°	46.0	44.6	44.5	44.8	44.0	44.2	43.9	43.8	44.2	44.2	45.5
80°	35.4	33.8	34.2	34.0	33.8	33.5	33.1	33.3	33.5	33.8	34.5
82.5°	25.5	25.4	24.9	24.9	24.6	24.0	23.8	24.2	24.4	24.3	24.8
85°	13.0	12.3	12.8	12.6	12.8	12.6	11.9	11.9	12.3	12.1	12.6
87.5°	11.4	11.2	10.1	9.4	8.4	7.7	6.7	6.2	5.7	5.1	4.8
90°	37.5	36.2	31.8	27.5	23.1	18.8	14.9	11.6	8.2	4.9	1.5
92.5°	59.0	57.9	55.4	52.9	50.5	48.0	45.6	43.3	41.0	38.8	36.5
95°	112.9	111.6	108.9	106.2	103.5	100.9	98.4	96.0	93.7	91.3	89.0
97.5°	176.2	174.6	172.7	170.7	168.8	166.8	165.0	163.3	161.5	159.8	158.0
100°	222.7	221.7	220.0	218.3	216.6	215.0	213.1	211.1	209.1	207.1	205.1
102.5°	275.8	274.7	272.5	270.3	268.1	265.9	264.2	263.0	261.8	260.6	259.4
105°	355.9	355.9	352.9	349.8	346.8	343.8	342.0	341.3	340.6	340.0	339.3
107.5°	440.5	439.4	438.2	437.0	435.8	434.6	433.8	433.4	433.0	432.6	432.2
110°	497.5	496.1	495.4	494.8	494.1	493.4	492.8	492.1	491.4	490.8	490.1



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	554.4	552.8	552.7	552.5	552.4	552.3	552.0	551.6	551.2	550.8	550.4
115°	642.7	642.4	643.1	643.7	644.4	645.1	644.9	643.9	642.9	641.9	640.9
117.5°	731.0	731.1	731.9	732.8	733.7	734.5	734.6	734.0	733.3	732.6	732.0
120°	789.8	790.2	791.8	793.5	795.2	796.9	796.7	794.7	792.7	790.7	788.7
122.5°	849.6	850.5	851.4	852.2	853.1	854.0	853.7	852.2	850.7	849.2	847.8
125°	938.1	939.5	940.1	940.8	941.5	942.1	942.0	941.0	940.0	938.9	937.9
127.5°	1025.6	1027.5	1028.3	1029.0	1029.7	1030.5	1029.8	1027.6	1025.5	1023.3	1021.2
130°	1082.9	1084.2	1085.2	1086.2	1087.2	1088.2	1087.4	1084.7	1082.0	1079.4	1076.7
132.5°	1139.3	1140.9	1141.6	1142.4	1143.1	1143.9	1142.9	1140.2	1137.5	1134.8	1132.2
135°	1223.1	1224.5	1224.8	1225.1	1225.5	1225.8	1225.0	1222.9	1220.9	1218.9	1216.9
137.5°	1305.4	1306.8	1305.9	1305.0	1304.2	1303.3	1302.0	1300.4	1298.7	1297.0	1295.3
140°	1358.3	1358.7	1358.3	1358.0	1357.7	1357.3	1356.3	1354.6	1353.0	1351.3	1349.6
142.5°	1409.0	1409.3	1408.7	1408.1	1407.5	1406.9	1405.8	1404.1	1402.4	1400.7	1399.1
145°	1483.5	1483.8	1482.8	1481.8	1480.8	1479.8	1479.0	1478.3	1477.6	1477.0	1476.3
147.5°	1553.5	1553.5	1552.5	1551.6	1550.7	1549.7	1548.7	1547.5	1546.2	1545.0	1543.8
150°	1596.9	1596.9	1596.2	1595.6	1594.9	1594.2	1593.6	1592.9	1592.2	1591.6	1590.9
152.5°	1636.1	1635.5	1635.1	1634.7	1634.3	1633.9	1633.2	1632.3	1631.4	1630.4	1629.5
155°	1693.3	1691.9	1691.6	1691.2	1690.9	1690.6	1690.4	1690.4	1690.4	1690.4	1690.4
157.5°	1743.1	1741.7	1741.4	1741.1	1740.9	1740.6	1740.7	1741.1	1741.5	1741.9	1742.3
160°	1773.5	1771.8	1771.8	1771.8	1771.8	1771.8	1772.2	1772.8	1773.5	1774.2	1774.9
162.5°	1802.5	1800.8	1800.5	1800.3	1800.0	1799.7	1800.1	1801.0	1801.9	1802.9	1803.8
165°	1838.7	1836.7	1836.7	1836.7	1836.7	1836.7	1837.2	1838.2	1839.2	1840.2	1841.2
167.5°	1868.3	1866.2	1866.0	1865.7	1865.4	1865.2	1865.7	1867.0	1868.4	1869.7	1871.1
170°	1884.3	1881.9	1881.9	1881.9	1881.9	1881.9	1882.6	1883.9	1885.3	1886.6	1887.9
172.5°	1897.3	1895.2	1895.2	1895.2	1895.2	1895.2	1895.9	1897.2	1898.5	1899.9	1901.2
175°	1911.1	1909.1	1909.1	1909.1	1909.1	1909.1	1909.7	1911.1	1912.4	1913.8	1915.1
177.5°	1917.6	1916.0	1916.0	1916.0	1916.0	1916.0	1916.5	1917.6	1918.7	1919.8	1920.8
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	483.8	484.8	487.9	490.2	492.8	494.3	495.7	496.9	498.4	498.7	504.1
5°	486.0	490.6	498.8	504.8	512.3	520.4	526.0	528.6	535.4	540.9	552.1
7.5°	485.4	495.3	507.6	520.4	534.0	546.7	557.7	570.8	580.0	594.0	607.7
10°	484.8	498.1	513.9	530.2	549.3	567.0	582.9	600.6	615.3	634.6	651.1
12.5°	483.1	499.2	521.2	540.5	563.7	588.1	611.6	634.3	647.3	679.5	694.7
15°	479.0	498.1	525.6	554.9	586.8	615.7	645.5	669.3	707.7	735.9	753.9
17.5°	471.1	497.8	530.4	565.8	604.6	642.7	676.5	712.5	753.3	787.4	823.8
20°	467.3	496.7	533.0	572.2	612.5	655.6	694.0	737.3	781.8	815.4	862.0
22.5°	460.4	493.7	532.8	576.4	619.5	664.1	709.1	752.8	804.2	850.4	894.8
25°	449.2	486.4	527.0	575.7	626.2	670.9	724.8	782.8	836.3	895.8	940.0
27.5°	437.3	477.1	517.7	563.0	617.4	670.5	738.2	803.7	869.2	920.5	953.3
30°	428.2	466.9	508.8	554.5	608.3	671.4	747.1	818.6	882.5	926.5	944.9
32.5°	418.3	457.5	494.6	542.5	599.9	670.8	752.7	827.4	883.2	912.5	908.9
35°	402.8	435.6	471.8	517.9	585.4	666.7	756.0	828.2	862.4	856.1	808.6
37.5°	380.4	408.1	443.6	494.1	568.7	658.1	749.4	803.6	801.4	750.2	681.3
40°	366.5	390.0	424.2	477.3	555.6	652.5	739.2	774.4	744.6	673.0	590.6
42.5°	348.2	369.9	404.1	458.7	541.3	641.2	719.6	729.8	671.5	589.2	513.6
45°	319.9	339.0	374.4	430.8	519.7	616.4	671.9	646.9	568.4	483.4	425.9
47.5°	289.4	309.3	343.3	401.3	488.6	579.2	605.6	552.6	472.0	403.0	350.2
50°	270.2	289.3	322.7	381.1	467.6	548.6	559.6	491.1	417.0	356.4	313.1
52.5°	250.9	268.8	301.6	360.3	443.0	513.2	506.5	436.7	368.6	316.9	282.9
55°	222.0	239.0	270.2	325.2	400.5	456.1	431.7	365.1	308.7	268.6	242.7
57.5°	196.2	212.5	239.4	289.1	354.5	392.8	361.7	305.5	260.7	229.8	210.6
60°	178.7	193.1	218.8	264.9	321.7	350.8	320.1	270.5	232.7	208.0	190.8
62.5°	162.1	174.7	198.4	240.3	289.7	314.1	283.0	241.0	208.9	187.0	172.3
65°	137.0	148.4	169.4	202.0	242.5	258.8	232.0	198.0	173.1	156.8	147.0
67.5°	114.1	123.8	141.9	167.5	197.4	209.2	188.8	162.5	143.7	130.6	122.9
70°	98.8	107.2	121.4	143.5	170.5	179.6	160.5	138.8	125.1	114.6	107.4
72.5°	85.9	92.1	105.0	122.1	144.6	151.8	138.5	119.5	106.7	98.8	93.0
75°	65.5	70.6	79.0	92.7	108.3	112.5	102.5	90.6	82.0	76.4	72.0
77.5°	47.2	51.0	57.0	65.5	76.3	80.1	73.8	65.8	59.5	55.8	53.3
80°	35.6	38.7	43.8	50.8	57.3	59.4	55.7	49.6	45.2	43.1	41.0
82.5°	26.3	28.0	31.1	35.9	40.3	42.8	39.7	36.0	33.6	31.7	30.9
85°	13.3	14.2	15.6	17.5	20.3	21.2	20.0	19.1	17.7	16.5	16.5
87.5°	5.8	6.5	7.7	8.8	10.3	11.7	12.4	12.9	13.6	13.7	13.7
90°	4.9	8.2	11.6	14.9	18.8	23.1	27.5	31.8	36.2	37.5	38.9
92.5°	38.8	41.0	43.3	45.6	48.0	50.5	52.9	55.4	57.9	59.0	60.0
95°	91.3	93.7	96.0	98.4	100.9	103.5	106.2	108.9	111.6	112.9	114.3
97.5°	159.8	161.5	163.3	165.0	166.8	168.8	170.7	172.7	174.6	176.2	177.7
100°	207.1	209.1	211.1	213.1	215.0	216.6	218.3	220.0	221.7	222.7	223.7
102.5°	260.6	261.8	263.0	264.2	265.9	268.1	270.3	272.5	274.7	275.8	276.8
105°	340.0	340.6	341.3	342.0	343.8	346.8	349.8	352.9	355.9	355.9	355.9
107.5°	432.6	433.0	433.4	433.8	434.6	435.8	437.0	438.2	439.4	440.5	441.6
110°	490.8	491.4	492.1	492.8	493.4	494.1	494.8	495.4	496.1	497.5	498.8



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	550.8	551.2	551.6	552.0	552.3	552.4	552.5	552.7	552.8	554.4	556.0
115°	641.9	642.9	643.9	644.9	645.1	644.4	643.7	643.1	642.4	642.7	643.1
117.5°	732.6	733.3	734.0	734.6	734.5	733.7	732.8	731.9	731.1	731.0	730.9
120°	790.7	792.7	794.7	796.7	796.9	795.2	793.5	791.8	790.2	789.8	789.5
122.5°	849.2	850.7	852.2	853.7	854.0	853.1	852.2	851.4	850.5	849.6	848.7
125°	938.9	940.0	941.0	942.0	942.1	941.5	940.8	940.1	939.5	938.1	936.8
127.5°	1023.3	1025.5	1027.6	1029.8	1030.5	1029.7	1029.0	1028.3	1027.5	1025.6	1023.8
130°	1079.4	1082.0	1084.7	1087.4	1088.2	1087.2	1086.2	1085.2	1084.2	1082.9	1081.5
132.5°	1134.8	1137.5	1140.2	1142.9	1143.9	1143.1	1142.4	1141.6	1140.9	1139.3	1137.7
135°	1218.9	1220.9	1222.9	1225.0	1225.8	1225.5	1225.1	1224.8	1224.5	1223.1	1221.8
137.5°	1297.0	1298.7	1300.4	1302.0	1303.3	1304.2	1305.0	1305.9	1306.8	1305.4	1304.0
140°	1351.3	1353.0	1354.6	1356.3	1357.3	1357.7	1358.0	1358.3	1358.7	1358.3	1358.0
142.5°	1400.7	1402.4	1404.1	1405.8	1406.9	1407.5	1408.1	1408.7	1409.3	1409.0	1408.7
145°	1477.0	1477.6	1478.3	1479.0	1479.8	1480.8	1481.8	1482.8	1483.8	1483.5	1483.1
147.5°	1545.0	1546.2	1547.5	1548.7	1549.7	1550.7	1551.6	1552.5	1553.5	1553.5	1553.5
150°	1591.6	1592.2	1592.9	1593.6	1594.2	1594.9	1595.6	1596.2	1596.9	1596.9	1596.9
152.5°	1630.4	1631.4	1632.3	1633.2	1633.9	1634.3	1634.7	1635.1	1635.5	1636.1	1636.6
155°	1690.4	1690.4	1690.4	1690.4	1690.6	1690.9	1691.2	1691.6	1691.9	1693.3	1694.6
157.5°	1741.9	1741.5	1741.1	1740.7	1740.6	1740.9	1741.1	1741.4	1741.7	1743.1	1744.5
160°	1774.2	1773.5	1772.8	1772.2	1771.8	1771.8	1771.8	1771.8	1771.8	1773.5	1775.2
162.5°	1802.9	1801.9	1801.0	1800.1	1799.7	1800.0	1800.3	1800.5	1800.8	1802.5	1804.1
165°	1840.2	1839.2	1838.2	1837.2	1836.7	1836.7	1836.7	1836.7	1836.7	1838.7	1840.7
167.5°	1869.7	1868.4	1867.0	1865.7	1865.2	1865.4	1865.7	1866.0	1866.2	1868.3	1870.4
170°	1886.6	1885.3	1883.9	1882.6	1881.9	1881.9	1881.9	1881.9	1881.9	1884.3	1886.6
172.5°	1899.9	1898.5	1897.2	1895.9	1895.2	1895.2	1895.2	1895.2	1895.2	1897.3	1899.3
175°	1913.8	1912.4	1911.1	1909.7	1909.1	1909.1	1909.1	1909.1	1909.1	1911.1	1913.1
177.5°	1919.8	1918.7	1917.6	1916.5	1916.0	1916.0	1916.0	1916.0	1916.0	1917.6	1919.2
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	480.8	480.8	480.8	480.8	480.8	480.8	480.8
2.5°	506.0	506.2	508.2	509.7	509.0	509.9	510.3
5°	552.8	561.2	565.6	568.9	569.1	569.4	571.2
7.5°	619.2	628.2	634.8	644.8	647.7	651.1	650.2
10°	667.7	681.0	692.4	698.4	705.0	714.5	706.8
12.5°	713.0	736.5	753.9	763.3	769.4	771.3	767.6
15°	787.7	818.4	834.9	834.5	855.4	864.5	850.3
17.5°	856.1	884.5	907.3	918.9	936.4	940.2	938.5
20°	898.1	929.1	946.8	966.8	975.9	984.0	985.4
22.5°	934.2	962.1	981.1	997.7	1005.3	1009.2	1011.5
25°	971.5	993.4	1004.8	1010.6	1012.7	1012.2	1009.2
27.5°	968.9	970.6	958.0	945.7	934.6	922.2	917.9
30°	943.7	924.2	889.2	869.4	840.3	817.2	826.6
32.5°	877.6	838.6	799.4	756.1	720.3	710.1	699.8
35°	749.0	680.5	640.4	593.8	575.2	556.6	543.7
37.5°	605.9	553.0	505.4	475.0	456.3	444.5	438.2
40°	523.9	476.2	437.0	412.3	398.1	384.9	383.0
42.5°	458.5	414.1	384.7	365.0	351.4	345.7	341.6
45°	375.5	344.6	324.8	310.8	301.7	298.2	293.5
47.5°	317.9	296.0	281.1	271.6	264.7	262.1	261.8
50°	285.6	267.4	256.5	249.0	243.7	242.7	239.0
52.5°	261.4	245.6	237.1	230.6	226.7	224.1	223.0
55°	226.9	216.4	208.7	205.0	202.0	199.4	199.4
57.5°	198.5	189.8	184.7	181.5	180.6	178.8	177.6
60°	181.0	173.6	169.6	166.8	164.9	165.2	163.1
62.5°	163.9	159.0	155.2	152.5	150.2	150.3	150.4
65°	139.5	135.8	133.0	132.1	130.7	129.1	129.5
67.5°	118.3	114.8	112.6	111.0	110.5	109.6	111.0
70°	103.0	100.4	98.8	97.4	96.9	97.1	98.3
72.5°	89.0	87.2	86.1	85.5	84.4	84.5	85.3
75°	69.9	68.5	67.6	66.9	66.6	66.6	66.6
77.5°	51.3	51.0	50.6	49.6	49.6	49.9	49.9
80°	40.5	39.8	39.6	39.1	38.4	38.0	39.1
82.5°	30.3	29.6	29.4	29.3	28.2	28.1	29.1
85°	16.3	15.6	15.8	15.6	15.6	15.4	15.4
87.5°	13.8	13.9	13.9	14.2	14.2	14.1	14.6
90°	40.2	41.6	42.6	43.2	43.9	44.6	45.2
92.5°	61.1	62.2	62.5	62.1	61.7	61.3	60.9
95°	115.6	116.9	117.6	117.6	117.6	117.6	117.6
97.5°	179.2	180.8	181.5	181.4	181.2	181.1	181.0
100°	224.7	225.7	226.5	227.2	227.9	228.5	229.2
102.5°	277.8	278.8	279.2	279.1	278.9	278.8	278.7
105°	355.9	355.9	356.2	356.9	357.6	358.2	358.9
107.5°	442.6	443.7	444.0	443.6	443.2	442.8	442.4
110°	500.1	501.5	501.8	501.1	500.5	499.8	499.1



TEST NUMBER: P332115

CATALOG NUMBER: S123DIW-S340D1535U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	557.6	559.2	560.0	559.9	559.7	559.6	559.4
115°	643.4	643.7	643.7	643.4	643.1	642.7	642.4
117.5°	730.9	730.8	730.3	729.3	728.4	727.5	726.5
120°	789.2	788.8	788.3	787.7	787.0	786.3	785.6
122.5°	847.9	847.0	846.1	845.2	844.2	843.3	842.3
125°	935.4	934.1	932.7	931.4	930.1	928.7	927.4
127.5°	1021.9	1020.0	1018.3	1016.8	1015.2	1013.7	1012.1
130°	1080.2	1078.9	1077.0	1074.7	1072.3	1070.0	1067.6
132.5°	1136.1	1134.5	1132.8	1131.0	1129.2	1127.3	1125.5
135°	1220.4	1219.1	1218.1	1217.4	1216.7	1216.1	1215.4
137.5°	1302.6	1301.2	1299.8	1298.5	1297.3	1296.0	1294.7
140°	1357.7	1357.3	1356.0	1353.6	1351.3	1348.9	1346.6
142.5°	1408.3	1408.0	1406.9	1405.1	1403.3	1401.5	1399.7
145°	1482.8	1482.5	1481.6	1480.3	1479.0	1477.6	1476.3
147.5°	1553.5	1553.5	1552.5	1550.5	1548.5	1546.4	1544.4
150°	1596.9	1596.9	1595.9	1593.9	1591.9	1589.9	1587.9
152.5°	1637.1	1637.7	1637.1	1635.3	1633.6	1631.8	1630.1
155°	1695.9	1697.3	1696.8	1694.4	1692.1	1689.7	1687.4
157.5°	1745.9	1747.3	1747.1	1745.2	1743.3	1741.4	1739.6
160°	1776.9	1778.5	1778.7	1777.4	1776.0	1774.7	1773.3
162.5°	1805.8	1807.5	1807.3	1805.1	1803.0	1800.8	1798.7
165°	1842.7	1844.7	1844.6	1842.2	1839.9	1837.5	1835.2
167.5°	1872.5	1874.5	1874.5	1872.5	1870.4	1868.3	1866.2
170°	1889.0	1891.3	1891.3	1889.0	1886.6	1884.3	1881.9
172.5°	1901.4	1903.5	1903.4	1901.0	1898.7	1896.3	1894.0
175°	1915.1	1917.1	1916.9	1914.6	1912.2	1909.9	1907.6
177.5°	1920.8	1922.4	1922.3	1920.4	1918.5	1916.7	1914.8
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6

(END OF REPORT)