

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332235-927

Luminaire Tested: **S123DIW-S1165D1535U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332235-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S1165D1535U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8096.3 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.23 / 1.49
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48	
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41	
2	89	82	76	71	82	76	70	66	64	60	57	53	50	48	43	41	39	35	35	35	35	
3	81	72	65	59	75	67	60	55	56	52	48	47	44	41	38	36	34	30	30	30	30	
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	26	26	26	26	
5	68	57	49	43	63	53	46	41	45	40	35	38	34	30	31	28	26	22	22	22	22	
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20	20	20	20	
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	22	20	17	17	17	17	
8	54	42	34	29	50	39	32	27	34	28	24	28	24	21	24	20	18	16	16	16	16	
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14	14	14	14	
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13	13	13	13	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13832	13832	13832	13832
5°	16495	13891	12310	13891
10°	20647	13821	11119	13821
15°	25324	13710	10351	13710
20°	30166	13536	9856	13536
25°	32033	13324	9745	13324
30°	27455	13170	9797	13170
35°	19094	12951	9900	12951
40°	14383	12694	9868	12694
45°	11942	12310	9742	12310
50°	10697	11531	9656	11531
55°	10001	10691	9533	10691
60°	9382	9810	9436	9810
65°	8818	8945	9133	8945
70°	8271	7956	8699	7956
75°	7407	6966	7977	6966
80°	6484	5709	6868	5709
85°	5076	4150	4619	4150



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.6	1.6
10°-20°	405.9	5.0
20°-30°	681.2	8.4
30°-40°	771.4	9.5
40°-50°	691.7	8.5
50°-60°	558.2	6.9
60°-70°	389.0	4.8
70°-80°	204.5	2.5
80°-90°	54.5	0.7
90°-100°	99.1	1.2
100°-110°	296.5	3.7
110°-120°	504.3	6.2
120°-130°	663.4	8.2
130°-140°	745.6	9.2
140°-150°	732.9	9.1
150°-160°	617.0	7.6
160°-170°	410.7	5.1
170°-180°	143.8	1.8
0°-30°	1213.7	15.0
0°-40°	1985.1	24.5
0°-60°	3235.0	40.0
0°-90°	3883.0	48.0
90°-120°	899.9	11.1
90°-150°	3041.8	37.6
90°-180°	4213.0	52.0
0°-180°	8096.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1285	1285	1285	1285	1285	
5°	1527	1286	1139	1286	1527	158
15°	2272	1230	929	1230	2272	656
25°	2697	1122	820	1122	2697	1183
35°	1453	986	753	986	1453	944
45°	784	809	640	809	784	621
55°	533	570	508	570	533	478
65°	346	351	359	351	346	345
75°	178	168	192	168	178	191
85°	41	34	37	34	41	50
90°	36	1	36	1	36	19
95°	93	70	93	70	93	96
105°	284	269	284	269	284	302
115°	509	508	509	508	509	504
125°	735	743	735	743	735	657
135°	963	964	963	964	963	740
145°	1170	1170	1170	1170	1170	730
155°	1337	1339	1337	1339	1337	615
165°	1454	1459	1454	1459	1454	410
175°	1511	1517	1511	1517	1511	144
180°	1521	1521	1521	1521	1521	



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1363.7	1362.7	1360.3	1362.2	1358.3	1352.7	1352.3	1347.3	1332.8	1331.8	1327.9
5°	1526.6	1521.6	1521.0	1520.4	1511.6	1499.8	1477.4	1475.5	1445.7	1430.7	1412.7
7.5°	1737.5	1740.1	1731.1	1723.1	1696.5	1678.9	1654.9	1624.1	1587.4	1550.1	1525.3
10°	1889.0	1909.5	1884.0	1866.5	1850.4	1819.8	1784.4	1740.1	1695.9	1644.3	1605.0
12.5°	2051.4	2061.4	2056.3	2039.9	2014.7	1968.3	1905.4	1856.7	1816.0	1730.0	1695.2
15°	2272.5	2310.5	2286.2	2230.2	2231.3	2187.1	2105.0	2014.7	1966.8	1891.4	1788.7
17.5°	2508.0	2512.8	2502.4	2455.8	2424.6	2363.9	2288.1	2201.5	2104.4	2013.3	1904.2
20°	2633.5	2629.8	2608.0	2583.8	2530.2	2482.9	2400.1	2303.6	2179.1	2089.5	1970.5
22.5°	2703.3	2697.1	2686.8	2666.4	2621.9	2571.0	2496.7	2391.3	2272.7	2149.2	2011.8
25°	2697.1	2705.1	2706.4	2700.8	2685.3	2654.8	2596.2	2512.2	2393.9	2235.1	2091.9
27.5°	2453.0	2464.5	2497.8	2527.2	2560.3	2593.8	2589.3	2547.7	2460.1	2323.0	2147.9
30°	2208.9	2184.0	2245.7	2323.5	2376.5	2469.8	2522.1	2525.2	2476.0	2358.4	2187.8
32.5°	1870.3	1897.7	1924.9	2020.7	2136.4	2241.2	2345.3	2429.1	2438.7	2360.4	2211.2
35°	1453.1	1487.4	1537.2	1587.0	1711.5	1818.6	2001.6	2161.0	2288.1	2304.9	2213.3
37.5°	1171.0	1187.9	1219.4	1269.3	1350.8	1477.8	1619.4	1820.8	2004.9	2141.7	2147.7
40°	1023.6	1028.5	1064.0	1102.0	1168.0	1272.6	1400.2	1578.3	1798.6	1989.8	2069.5
42.5°	913.0	923.9	939.0	975.5	1028.0	1106.8	1225.4	1372.5	1574.5	1794.5	1950.4
45°	784.5	796.9	806.3	830.5	867.9	920.8	1003.6	1138.1	1291.9	1519.1	1728.9
47.5°	699.6	700.5	707.5	725.8	751.2	790.9	849.5	935.9	1077.1	1261.4	1476.8
50°	638.8	648.7	651.3	665.5	685.5	714.7	763.3	836.8	952.6	1114.4	1312.4
52.5°	596.0	599.0	605.9	616.2	633.7	656.5	698.5	756.1	847.0	984.9	1167.0
55°	532.9	532.9	539.8	547.9	557.9	578.4	606.4	648.7	717.9	824.9	975.6
57.5°	474.7	477.8	482.6	485.1	493.6	507.2	530.6	562.7	614.3	696.6	816.5
60°	435.8	441.4	440.8	445.8	453.3	463.8	483.8	509.9	556.0	621.9	722.9
62.5°	402.0	401.6	401.5	407.4	414.9	425.0	437.9	460.6	499.7	558.3	644.1
65°	346.2	344.9	349.3	353.0	355.5	363.0	373.0	392.8	419.0	462.6	529.2
67.5°	296.6	293.0	295.3	296.6	300.9	306.7	316.0	328.4	349.1	384.1	434.4
70°	262.8	259.6	259.0	260.2	264.0	268.3	275.2	287.0	306.3	334.3	371.1
72.5°	227.8	225.8	225.6	228.4	230.1	233.0	237.8	248.7	264.0	285.0	319.2
75°	178.1	178.1	178.1	178.7	180.5	183.1	186.8	192.3	204.2	219.1	242.2
77.5°	133.5	133.3	132.6	132.5	135.2	136.3	137.2	142.4	149.0	159.1	175.9
80°	104.6	101.5	102.7	104.6	105.8	106.5	108.4	109.6	115.2	120.8	132.6
82.5°	77.7	75.1	75.3	78.2	78.4	79.1	81.0	82.7	84.8	89.9	96.3
85°	41.1	41.1	41.7	41.7	42.3	41.7	43.6	44.2	44.2	47.3	51.0
87.5°	22.1	21.0	21.4	21.8	21.2	21.5	21.8	22.1	22.4	22.7	22.5
90°	35.8	35.3	34.8	34.2	33.7	33.0	31.8	30.8	29.7	28.7	25.2
92.5°	48.2	48.6	48.9	49.2	49.5	49.3	48.4	47.5	46.7	45.9	43.9
95°	93.2	93.2	93.2	93.2	93.2	92.6	91.6	90.5	89.4	88.4	86.3
97.5°	143.4	143.5	143.5	143.7	143.8	143.2	142.0	140.8	139.6	138.3	136.8
100°	181.6	181.0	180.5	180.0	179.4	178.8	178.0	177.2	176.4	175.6	174.3
102.5°	220.8	220.9	220.9	221.1	221.2	220.9	220.1	219.3	218.5	217.6	215.9
105°	284.3	283.8	283.3	282.7	282.2	281.9	281.9	281.9	281.9	281.9	279.6
107.5°	350.5	350.8	351.1	351.4	351.7	351.5	350.6	349.8	349.0	348.1	347.1
110°	395.4	395.9	396.5	397.0	397.5	397.3	396.2	395.1	394.1	393.0	392.4



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	443.1	443.3	443.4	443.5	443.6	443.0	441.7	440.5	439.2	437.9	437.8
115°	508.9	509.1	509.5	509.7	509.9	509.9	509.7	509.5	509.1	508.9	509.5
117.5°	575.5	576.3	577.0	577.7	578.5	578.9	579.0	579.0	579.1	579.2	579.8
120°	622.3	622.9	623.4	624.0	624.5	624.9	625.2	625.4	625.7	626.0	627.2
122.5°	667.3	668.0	668.8	669.6	670.3	671.0	671.7	672.3	673.0	673.8	674.5
125°	734.7	735.7	736.8	737.8	738.9	740.0	741.0	742.1	743.1	744.3	744.7
127.5°	801.8	803.0	804.2	805.5	806.7	808.0	809.5	811.0	812.5	814.0	814.6
130°	845.7	847.6	849.5	851.4	853.2	854.7	855.7	856.7	857.9	858.9	859.7
132.5°	891.6	893.0	894.5	896.0	897.4	898.7	900.0	901.3	902.5	903.8	904.4
135°	962.8	963.4	963.8	964.4	965.0	965.7	966.8	967.9	968.9	970.0	970.3
137.5°	1025.6	1026.7	1027.7	1028.6	1029.7	1030.8	1031.9	1033.0	1034.1	1035.2	1034.5
140°	1066.8	1068.6	1070.5	1072.3	1074.2	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0
142.5°	1108.8	1110.2	1111.7	1113.1	1114.5	1115.4	1115.6	1115.9	1116.2	1116.4	1115.9
145°	1169.5	1170.5	1171.6	1172.7	1173.7	1174.4	1174.6	1174.9	1175.2	1175.4	1174.6
147.5°	1223.4	1225.0	1226.7	1228.3	1229.9	1230.7	1230.7	1230.7	1230.7	1230.7	1229.9
150°	1257.9	1259.5	1261.1	1262.7	1264.2	1265.0	1265.0	1265.0	1265.0	1265.0	1264.5
152.5°	1291.3	1292.7	1294.1	1295.5	1296.9	1297.4	1296.9	1296.5	1296.1	1295.6	1295.3
155°	1336.7	1338.6	1340.5	1342.3	1344.2	1344.6	1343.5	1342.4	1341.4	1340.3	1340.1
157.5°	1378.1	1379.5	1381.0	1382.5	1384.0	1384.2	1383.1	1382.0	1380.9	1379.7	1379.5
160°	1404.8	1405.9	1406.9	1408.0	1409.1	1408.9	1407.6	1406.3	1404.9	1403.6	1403.6
162.5°	1424.9	1426.6	1428.3	1430.0	1431.7	1431.9	1430.5	1429.2	1427.9	1426.6	1426.3
165°	1453.8	1455.6	1457.5	1459.4	1461.3	1461.3	1459.8	1458.2	1456.6	1455.0	1455.0
167.5°	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4	1478.2
170°	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8	1490.8
172.5°	1500.4	1502.2	1504.1	1505.9	1507.8	1507.9	1506.3	1504.6	1503.0	1501.3	1501.3
175°	1511.2	1513.0	1514.8	1516.7	1518.5	1518.7	1517.1	1515.5	1513.9	1512.4	1512.4
177.5°	1516.9	1518.4	1519.8	1521.3	1522.8	1522.9	1521.6	1520.4	1519.1	1517.8	1517.8
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1324.8	1320.9	1316.9	1310.0	1303.9	1295.5	1293.0	1290.0	1281.0	1273.1	1267.1
5°	1405.8	1390.8	1369.0	1349.2	1333.0	1311.2	1298.7	1285.6	1266.9	1250.1	1236.4
7.5°	1490.5	1461.1	1427.2	1390.6	1356.5	1323.7	1297.1	1273.4	1247.3	1222.5	1203.2
10°	1557.7	1515.4	1468.1	1417.1	1373.4	1331.1	1295.6	1264.5	1230.9	1201.6	1177.3
12.5°	1634.4	1571.7	1506.4	1444.4	1392.9	1334.1	1291.1	1251.6	1213.5	1178.2	1151.0
15°	1725.2	1645.5	1568.3	1483.0	1404.5	1331.1	1280.1	1230.3	1186.1	1149.9	1115.1
17.5°	1807.9	1717.6	1615.9	1512.1	1417.5	1330.4	1258.9	1202.6	1147.3	1103.1	1068.3
20°	1854.7	1752.0	1636.8	1529.1	1424.5	1327.4	1249.0	1181.7	1121.9	1075.2	1036.0
22.5°	1895.1	1774.9	1655.7	1540.6	1424.0	1319.4	1230.5	1161.3	1096.5	1050.8	1009.1
25°	1936.9	1793.1	1673.6	1538.4	1408.3	1300.0	1200.4	1121.9	1057.2	1003.6	960.7
27.5°	1972.8	1791.8	1650.0	1504.7	1383.6	1275.1	1168.7	1084.6	1015.8	957.7	914.1
30°	1996.6	1794.3	1625.6	1481.8	1359.8	1247.7	1144.3	1059.6	987.5	928.3	887.2
32.5°	2011.6	1792.8	1603.1	1449.9	1321.9	1222.7	1117.9	1030.2	956.1	897.9	858.3
35°	2020.3	1781.9	1564.6	1384.0	1260.8	1164.3	1076.5	985.6	907.8	853.6	808.7
37.5°	2002.9	1758.8	1519.7	1320.5	1185.6	1090.5	1016.7	939.2	864.7	805.2	766.5
40°	1975.5	1743.9	1484.9	1275.7	1133.8	1042.2	979.4	903.4	829.9	773.2	737.1
42.5°	1923.2	1713.5	1446.5	1225.9	1080.0	988.4	930.5	867.0	797.6	744.3	708.3
45°	1795.6	1647.3	1389.0	1151.2	1000.5	905.9	854.8	808.7	745.8	694.2	663.1
47.5°	1618.5	1547.9	1305.8	1072.4	917.6	826.6	773.5	736.4	690.5	648.7	618.9
50°	1495.5	1466.2	1249.5	1018.6	862.3	773.2	722.2	688.6	655.6	613.9	586.5
52.5°	1353.5	1371.6	1183.8	962.7	806.0	718.5	670.4	643.7	613.8	579.5	555.6
55°	1153.7	1219.0	1070.2	869.1	722.2	638.8	593.3	569.7	552.2	526.7	506.2
57.5°	966.5	1049.7	947.5	772.6	639.9	567.9	524.3	498.6	487.4	474.0	457.9
60°	855.5	937.6	859.8	707.9	584.6	516.1	477.5	455.7	444.5	435.2	421.5
62.5°	756.3	839.5	774.1	642.1	530.3	466.8	433.2	411.9	403.2	398.3	386.7
65°	620.1	691.7	648.1	539.8	452.7	396.6	366.1	351.2	343.0	341.2	333.7
67.5°	504.7	559.2	527.4	447.7	379.1	330.7	304.8	292.2	285.9	285.3	279.6
70°	429.0	480.0	455.7	383.5	324.4	286.4	264.0	252.8	249.1	248.4	245.3
72.5°	370.2	405.8	386.5	326.2	280.5	246.1	229.6	217.9	213.7	214.5	212.5
75°	273.9	300.7	289.5	247.8	211.0	188.6	174.9	167.5	163.7	165.6	163.1
77.5°	197.1	214.0	204.0	175.1	152.4	136.3	126.1	121.5	118.2	118.0	116.9
80°	148.8	158.8	153.1	135.7	117.1	103.4	95.2	92.1	90.3	89.7	89.0
82.5°	106.0	114.5	107.8	95.9	83.2	74.9	70.3	66.2	64.9	65.3	64.6
85°	53.6	56.6	54.2	46.7	41.7	37.9	35.5	33.6	32.4	33.0	31.8
87.5°	22.8	22.6	20.4	17.8	16.2	14.3	13.7	12.2	11.7	12.3	12.3
90°	21.8	18.3	14.9	11.8	9.2	6.5	3.9	1.2	3.9	6.5	9.2
92.5°	41.9	40.0	38.0	36.1	34.3	32.5	30.7	28.9	30.7	32.5	34.3
95°	84.1	82.0	79.9	78.0	76.0	74.2	72.3	70.5	72.3	74.2	76.0
97.5°	135.2	133.7	132.1	130.7	129.4	127.9	126.6	125.2	126.6	127.9	129.4
100°	172.9	171.6	170.3	168.8	167.2	165.6	164.1	162.5	164.1	165.6	167.2
102.5°	214.1	212.4	210.6	209.3	208.3	207.4	206.4	205.5	206.4	207.4	208.3
105°	277.1	274.7	272.4	270.9	270.4	269.8	269.3	268.8	269.3	269.8	270.4
107.5°	346.2	345.2	344.3	343.6	343.3	343.0	342.7	342.4	342.7	343.0	343.3
110°	392.0	391.4	390.9	390.4	389.8	389.3	388.8	388.2	388.8	389.3	389.8



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	437.7	437.6	437.5	437.3	437.0	436.7	436.3	436.0	436.3	436.7	437.0
115°	509.9	510.5	511.0	510.9	510.1	509.3	508.5	507.7	508.5	509.3	510.1
117.5°	580.5	581.2	581.9	581.9	581.5	580.9	580.4	579.9	580.4	580.9	581.5
120°	628.6	629.9	631.3	631.1	629.5	628.0	626.4	624.8	626.4	628.0	629.5
122.5°	675.1	675.8	676.5	676.3	675.1	673.9	672.7	671.6	672.7	673.9	675.1
125°	745.3	745.8	746.3	746.2	745.4	744.7	743.8	743.0	743.8	744.7	745.4
127.5°	815.2	815.7	816.3	815.8	814.0	812.4	810.6	809.0	810.6	812.4	814.0
130°	860.5	861.3	862.1	861.4	859.3	857.1	855.1	852.9	855.1	857.1	859.3
132.5°	905.0	905.5	906.2	905.4	903.2	901.1	899.0	896.9	899.0	901.1	903.2
135°	970.5	970.8	971.1	970.4	968.8	967.2	965.6	964.0	965.6	967.2	968.8
137.5°	1033.8	1033.2	1032.5	1031.4	1030.2	1028.8	1027.5	1026.1	1027.5	1028.8	1030.2
140°	1075.8	1075.5	1075.2	1074.4	1073.1	1071.8	1070.5	1069.1	1070.5	1071.8	1073.1
142.5°	1115.5	1115.0	1114.5	1113.6	1112.3	1111.0	1109.6	1108.3	1109.6	1111.0	1112.3
145°	1173.9	1173.1	1172.3	1171.6	1171.1	1170.5	1170.1	1169.5	1170.1	1170.5	1171.1
147.5°	1229.2	1228.4	1227.6	1226.9	1225.9	1224.9	1223.9	1223.0	1223.9	1224.9	1225.9
150°	1264.0	1263.5	1262.9	1262.4	1261.9	1261.3	1260.8	1260.3	1260.8	1261.3	1261.9
152.5°	1295.0	1294.7	1294.3	1293.8	1293.1	1292.4	1291.6	1290.9	1291.6	1292.4	1293.1
155°	1339.7	1339.5	1339.3	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1
157.5°	1379.3	1379.1	1378.9	1379.0	1379.3	1379.6	1379.9	1380.2	1379.9	1379.6	1379.3
160°	1403.6	1403.6	1403.6	1403.9	1404.4	1404.9	1405.5	1406.0	1405.5	1404.9	1404.4
162.5°	1426.2	1425.9	1425.7	1426.0	1426.7	1427.4	1428.2	1428.9	1428.2	1427.4	1426.7
165°	1455.0	1455.0	1455.0	1455.4	1456.2	1457.0	1457.8	1458.6	1457.8	1457.0	1456.2
167.5°	1478.0	1477.7	1477.6	1478.0	1479.0	1480.1	1481.1	1482.3	1481.1	1480.1	1479.0
170°	1490.8	1490.8	1490.8	1491.4	1492.4	1493.5	1494.5	1495.6	1494.5	1493.5	1492.4
172.5°	1501.3	1501.3	1501.3	1501.9	1502.9	1504.0	1505.1	1506.1	1505.1	1504.0	1502.9
175°	1512.4	1512.4	1512.4	1512.8	1513.9	1515.0	1516.1	1517.1	1516.1	1515.0	1513.9
177.5°	1517.8	1517.8	1517.8	1518.2	1519.1	1520.0	1520.8	1521.6	1520.8	1520.0	1519.1
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1263.6	1260.1	1255.1	1247.7	1241.7	1232.2	1232.2	1233.7	1233.7	1233.3	1232.2
5°	1225.3	1215.9	1204.8	1191.7	1178.0	1164.3	1161.7	1156.7	1153.0	1150.6	1147.5
7.5°	1184.8	1168.2	1151.9	1133.6	1116.9	1103.1	1093.5	1085.5	1080.5	1075.0	1071.0
10°	1157.4	1136.9	1117.5	1098.3	1077.1	1060.3	1049.7	1042.2	1036.6	1031.7	1029.1
12.5°	1125.1	1101.5	1080.2	1061.9	1038.7	1021.4	1011.4	1007.8	1001.2	990.8	985.3
15°	1077.7	1055.9	1030.4	1002.3	991.2	970.0	958.1	952.6	948.8	940.7	938.3
17.5°	1037.2	1008.7	980.1	959.2	938.3	921.1	914.6	907.6	902.6	896.0	894.1
20°	1004.9	979.4	953.2	930.8	908.9	890.3	884.7	879.7	874.7	871.6	869.1
22.5°	972.0	946.5	924.8	903.9	880.6	868.4	862.3	856.8	853.3	851.2	848.7
25°	925.8	903.4	879.1	860.4	841.8	833.6	829.9	826.8	824.3	821.2	820.5
27.5°	884.5	860.1	840.3	822.9	809.5	802.8	799.2	797.6	798.2	799.3	800.0
30°	853.6	831.2	815.0	800.0	787.6	781.3	780.7	780.7	783.2	783.9	785.1
32.5°	825.2	806.8	790.6	776.1	766.7	762.4	764.8	764.8	766.8	768.4	770.6
35°	783.9	767.6	755.2	742.8	734.7	736.5	737.8	739.0	742.1	745.8	748.4
37.5°	744.3	730.3	717.3	707.7	703.9	707.3	710.3	712.9	716.4	719.4	721.8
40°	716.0	705.4	692.9	684.2	685.5	687.4	689.8	692.9	696.1	697.9	700.4
42.5°	689.6	678.5	669.1	661.8	663.5	665.9	667.4	669.1	672.6	676.0	677.5
45°	649.4	640.6	631.9	627.6	628.8	630.1	631.3	633.2	636.3	638.8	639.4
47.5°	604.2	598.1	592.2	588.0	589.9	589.5	591.1	595.1	596.0	597.5	601.0
50°	575.3	569.7	562.8	561.6	561.6	561.6	562.2	567.2	567.2	569.7	572.2
52.5°	543.4	539.8	535.4	533.2	532.2	532.2	534.8	537.3	538.3	541.8	544.3
55°	496.2	492.5	488.7	486.9	485.6	486.9	491.9	493.1	496.2	498.0	499.9
57.5°	447.0	444.2	441.2	440.1	439.9	441.6	444.3	448.0	448.8	454.5	457.3
60°	414.6	410.3	407.8	407.8	406.5	412.2	410.9	417.2	418.4	422.2	426.5
62.5°	381.3	375.4	374.5	374.5	376.2	377.8	379.5	382.3	385.5	390.2	393.6
65°	327.5	324.4	328.8	328.1	326.9	330.6	330.6	333.7	337.5	341.8	348.6
67.5°	276.6	275.0	275.3	275.3	277.2	279.3	281.1	283.8	288.3	292.9	297.4
70°	242.2	244.1	241.0	243.4	245.3	245.9	247.2	250.9	255.9	259.0	264.0
72.5°	208.8	208.7	209.1	210.1	211.9	213.0	214.3	218.6	224.0	226.6	230.6
75°	160.7	160.0	161.8	161.8	165.0	166.2	167.5	169.4	174.4	178.1	181.2
77.5°	117.3	118.0	117.6	119.8	118.9	119.1	123.0	124.9	125.4	132.8	134.4
80°	88.4	89.7	90.3	90.9	91.5	90.3	94.7	96.5	96.5	100.8	103.9
82.5°	63.5	64.2	65.9	66.5	66.6	67.9	68.2	69.6	71.1	73.0	77.1
85°	31.8	33.6	34.2	33.6	34.2	33.0	34.9	35.5	36.1	36.1	36.1
87.5°	12.4	13.5	13.6	14.8	15.0	16.2	16.4	15.6	15.8	17.5	15.7
90°	11.8	14.9	18.3	21.8	25.2	28.7	29.7	30.8	31.8	33.0	33.7
92.5°	36.1	38.0	40.0	41.9	43.9	45.9	46.7	47.5	48.4	49.3	49.5
95°	78.0	79.9	82.0	84.1	86.3	88.4	89.4	90.5	91.6	92.6	93.2
97.5°	130.7	132.1	133.7	135.2	136.8	138.3	139.6	140.8	142.0	143.2	143.8
100°	168.8	170.3	171.6	172.9	174.3	175.6	176.4	177.2	178.0	178.8	179.4
102.5°	209.3	210.6	212.4	214.1	215.9	217.6	218.5	219.3	220.1	220.9	221.2
105°	270.9	272.4	274.7	277.1	279.6	281.9	281.9	281.9	281.9	281.9	282.2
107.5°	343.6	344.3	345.2	346.2	347.1	348.1	349.0	349.8	350.6	351.5	351.7
110°	390.4	390.9	391.4	392.0	392.4	393.0	394.1	395.1	396.2	397.3	397.5



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	437.3	437.5	437.6	437.7	437.8	437.9	439.2	440.5	441.7	443.0	443.6
115°	510.9	511.0	510.5	509.9	509.5	508.9	509.1	509.5	509.7	509.9	509.9
117.5°	581.9	581.9	581.2	580.5	579.8	579.2	579.1	579.0	579.0	578.9	578.5
120°	631.1	631.3	629.9	628.6	627.2	626.0	625.7	625.4	625.2	624.9	624.5
122.5°	676.3	676.5	675.8	675.1	674.5	673.8	673.0	672.3	671.7	671.0	670.3
125°	746.2	746.3	745.8	745.3	744.7	744.3	743.1	742.1	741.0	740.0	738.9
127.5°	815.8	816.3	815.7	815.2	814.6	814.0	812.5	811.0	809.5	808.0	806.7
130°	861.4	862.1	861.3	860.5	859.7	858.9	857.9	856.7	855.7	854.7	853.2
132.5°	905.4	906.2	905.5	905.0	904.4	903.8	902.5	901.3	900.0	898.7	897.4
135°	970.4	971.1	970.8	970.5	970.3	970.0	968.9	967.9	966.8	965.7	965.0
137.5°	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1	1033.0	1031.9	1030.8	1029.7
140°	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0	1075.8	1075.5	1075.2	1074.2
142.5°	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2	1115.9	1115.6	1115.4	1114.5
145°	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2	1174.9	1174.6	1174.4	1173.7
147.5°	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7	1230.7	1230.7	1230.7	1229.9
150°	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0	1265.0	1265.0	1265.0	1264.2
152.5°	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1	1296.5	1296.9	1297.4	1296.9
155°	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4	1342.4	1343.5	1344.6	1344.2
157.5°	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9	1382.0	1383.1	1384.2	1384.0
160°	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9	1406.3	1407.6	1408.9	1409.1
162.5°	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9	1429.2	1430.5	1431.9	1431.7
165°	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6	1458.2	1459.8	1461.3	1461.3
167.5°	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9
170°	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3
172.5°	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0	1504.6	1506.3	1507.9	1507.8
175°	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9	1515.5	1517.1	1518.7	1518.5
177.5°	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1	1520.4	1521.6	1522.9	1522.8
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1228.8	1228.3	1231.8	1229.2	1231.8	1228.3	1228.8	1232.2	1233.3	1233.7	1233.7
5°	1143.7	1145.6	1139.3	1139.3	1139.3	1145.6	1143.7	1147.5	1150.6	1153.0	1156.7
7.5°	1068.0	1065.2	1065.5	1062.2	1065.5	1065.2	1068.0	1071.0	1075.0	1080.5	1085.5
10°	1021.7	1018.0	1016.7	1017.3	1016.7	1018.0	1021.7	1029.1	1031.7	1036.6	1042.2
12.5°	983.3	982.5	974.4	974.5	974.4	982.5	983.3	985.3	990.8	1001.2	1007.8
15°	938.3	926.5	925.2	928.9	925.2	926.5	938.3	938.3	940.7	948.8	952.6
17.5°	893.0	886.8	887.2	885.3	887.2	886.8	893.0	894.1	896.0	902.6	907.6
20°	869.1	865.4	864.7	860.4	864.7	865.4	869.1	869.1	871.6	874.7	879.7
22.5°	847.2	846.0	846.4	841.5	846.4	846.0	847.2	848.7	851.2	853.3	856.8
25°	820.0	823.1	820.5	820.5	820.5	823.1	820.0	820.5	821.2	824.3	826.8
27.5°	801.5	801.4	800.2	800.2	800.2	801.4	801.5	800.0	799.3	798.2	797.6
30°	787.6	787.0	788.2	788.2	788.2	787.0	787.6	785.1	783.9	783.2	780.7
32.5°	773.6	774.5	774.8	775.2	774.8	774.5	773.6	770.6	768.4	766.8	764.8
35°	752.1	752.7	754.6	753.4	754.6	752.7	752.1	748.4	745.8	742.1	739.0
37.5°	722.9	725.8	725.2	726.2	725.2	725.8	722.9	721.8	719.4	716.4	712.9
40°	701.0	702.9	702.3	702.3	702.3	702.9	701.0	700.4	697.9	696.1	692.9
42.5°	678.7	680.0	678.3	677.4	678.3	680.0	678.7	677.5	676.0	672.6	669.1
45°	641.9	640.6	642.5	640.0	642.5	640.6	641.9	639.4	638.8	636.3	633.2
47.5°	600.8	602.1	602.5	604.4	602.5	602.1	600.8	601.0	597.5	596.0	595.1
50°	573.4	577.1	577.1	576.6	577.1	577.1	573.4	572.2	569.7	567.2	567.2
52.5°	546.5	548.3	550.7	550.6	550.7	548.3	546.5	544.3	541.8	538.3	537.3
55°	504.9	506.2	507.4	508.0	507.4	506.2	504.9	499.9	498.0	496.2	493.1
57.5°	461.8	461.4	464.3	465.2	464.3	461.4	461.8	457.3	454.5	448.8	448.0
60°	431.4	431.4	436.4	438.3	436.4	431.4	431.4	426.5	422.2	418.4	417.2
62.5°	399.1	401.1	406.1	403.5	406.1	401.1	399.1	393.6	390.2	385.5	382.3
65°	351.7	356.7	356.1	358.6	356.1	356.7	351.7	348.6	341.8	337.5	333.7
67.5°	302.3	305.5	309.9	310.3	309.9	305.5	302.3	297.4	292.9	288.3	283.8
70°	268.9	272.0	274.6	276.4	274.6	272.0	268.9	264.0	259.0	255.9	250.9
72.5°	236.6	238.2	244.2	241.5	244.2	238.2	236.6	230.6	226.6	224.0	218.6
75°	185.5	189.9	193.6	191.8	193.6	189.9	185.5	181.2	178.1	174.4	169.4
77.5°	137.2	141.6	143.3	141.7	143.3	141.6	137.2	134.4	132.8	125.4	124.9
80°	108.4	107.7	111.5	110.8	111.5	107.7	108.4	103.9	100.8	96.5	96.5
82.5°	79.5	78.8	80.6	81.0	80.6	78.8	79.5	77.1	73.0	71.1	69.6
85°	38.6	40.5	37.9	37.4	37.9	40.5	38.6	36.1	36.1	36.1	35.5
87.5°	15.8	15.9	15.5	15.1	15.5	15.9	15.8	15.7	17.5	15.8	15.6
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	33.0	31.8	30.8
92.5°	49.2	48.9	48.6	48.2	48.6	48.9	49.2	49.5	49.3	48.4	47.5
95°	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2	92.6	91.6	90.5
97.5°	143.7	143.5	143.5	143.4	143.5	143.5	143.7	143.8	143.2	142.0	140.8
100°	180.0	180.5	181.0	181.6	181.0	180.5	180.0	179.4	178.8	178.0	177.2
102.5°	221.1	220.9	220.9	220.8	220.9	220.9	221.1	221.2	220.9	220.1	219.3
105°	282.7	283.3	283.8	284.3	283.8	283.3	282.7	282.2	281.9	281.9	281.9
107.5°	351.4	351.1	350.8	350.5	350.8	351.1	351.4	351.7	351.5	350.6	349.8
110°	397.0	396.5	395.9	395.4	395.9	396.5	397.0	397.5	397.3	396.2	395.1



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	443.5	443.4	443.3	443.1	443.3	443.4	443.5	443.6	443.0	441.7	440.5
115°	509.7	509.5	509.1	508.9	509.1	509.5	509.7	509.9	509.9	509.7	509.5
117.5°	577.7	577.0	576.3	575.5	576.3	577.0	577.7	578.5	578.9	579.0	579.0
120°	624.0	623.4	622.9	622.3	622.9	623.4	624.0	624.5	624.9	625.2	625.4
122.5°	669.6	668.8	668.0	667.3	668.0	668.8	669.6	670.3	671.0	671.7	672.3
125°	737.8	736.8	735.7	734.7	735.7	736.8	737.8	738.9	740.0	741.0	742.1
127.5°	805.5	804.2	803.0	801.8	803.0	804.2	805.5	806.7	808.0	809.5	811.0
130°	851.4	849.5	847.6	845.7	847.6	849.5	851.4	853.2	854.7	855.7	856.7
132.5°	896.0	894.5	893.0	891.6	893.0	894.5	896.0	897.4	898.7	900.0	901.3
135°	964.4	963.8	963.4	962.8	963.4	963.8	964.4	965.0	965.7	966.8	967.9
137.5°	1028.6	1027.7	1026.7	1025.6	1026.7	1027.7	1028.6	1029.7	1030.8	1031.9	1033.0
140°	1072.3	1070.5	1068.6	1066.8	1068.6	1070.5	1072.3	1074.2	1075.2	1075.5	1075.8
142.5°	1113.1	1111.7	1110.2	1108.8	1110.2	1111.7	1113.1	1114.5	1115.4	1115.6	1115.9
145°	1172.7	1171.6	1170.5	1169.5	1170.5	1171.6	1172.7	1173.7	1174.4	1174.6	1174.9
147.5°	1228.3	1226.7	1225.0	1223.4	1225.0	1226.7	1228.3	1229.9	1230.7	1230.7	1230.7
150°	1262.7	1261.1	1259.5	1257.9	1259.5	1261.1	1262.7	1264.2	1265.0	1265.0	1265.0
152.5°	1295.5	1294.1	1292.7	1291.3	1292.7	1294.1	1295.5	1296.9	1297.4	1296.9	1296.5
155°	1342.3	1340.5	1338.6	1336.7	1338.6	1340.5	1342.3	1344.2	1344.6	1343.5	1342.4
157.5°	1382.5	1381.0	1379.5	1378.1	1379.5	1381.0	1382.5	1384.0	1384.2	1383.1	1382.0
160°	1408.0	1406.9	1405.9	1404.8	1405.9	1406.9	1408.0	1409.1	1408.9	1407.6	1406.3
162.5°	1430.0	1428.3	1426.6	1424.9	1426.6	1428.3	1430.0	1431.7	1431.9	1430.5	1429.2
165°	1459.4	1457.5	1455.6	1453.8	1455.6	1457.5	1459.4	1461.3	1461.3	1459.8	1458.2
167.5°	1483.4	1481.7	1480.0	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7
170°	1496.4	1494.5	1492.7	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5
172.5°	1505.9	1504.1	1502.2	1500.4	1502.2	1504.1	1505.9	1507.8	1507.9	1506.3	1504.6
175°	1516.7	1514.8	1513.0	1511.2	1513.0	1514.8	1516.7	1518.5	1518.7	1517.1	1515.5
177.5°	1521.3	1519.8	1518.4	1516.9	1518.4	1519.8	1521.3	1522.8	1522.9	1521.6	1520.4
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1232.2	1232.2	1241.7	1247.7	1255.1	1260.1	1263.6	1267.1	1273.1	1281.0	1290.0
5°	1161.7	1164.3	1178.0	1191.7	1204.8	1215.9	1225.3	1236.4	1250.1	1266.9	1285.6
7.5°	1093.5	1103.1	1116.9	1133.6	1151.9	1168.2	1184.8	1203.2	1222.5	1247.3	1273.4
10°	1049.7	1060.3	1077.1	1098.3	1117.5	1136.9	1157.4	1177.3	1201.6	1230.9	1264.5
12.5°	1011.4	1021.4	1038.7	1061.9	1080.2	1101.5	1125.1	1151.0	1178.2	1213.5	1251.6
15°	958.1	970.0	991.2	1002.3	1030.4	1055.9	1077.7	1115.1	1149.9	1186.1	1230.3
17.5°	914.6	921.1	938.3	959.2	980.1	1008.7	1037.2	1068.3	1103.1	1147.3	1202.6
20°	884.7	890.3	908.9	930.8	953.2	979.4	1004.9	1036.0	1075.2	1121.9	1181.7
22.5°	862.3	868.4	880.6	903.9	924.8	946.5	972.0	1009.1	1050.8	1096.5	1161.3
25°	829.9	833.6	841.8	860.4	879.1	903.4	925.8	960.7	1003.6	1057.2	1121.9
27.5°	799.2	802.8	809.5	822.9	840.3	860.1	884.5	914.1	957.7	1015.8	1084.6
30°	780.7	781.3	787.6	800.0	815.0	831.2	853.6	887.2	928.3	987.5	1059.6
32.5°	764.8	762.4	766.7	776.1	790.6	806.8	825.2	858.3	897.9	956.1	1030.2
35°	737.8	736.5	734.7	742.8	755.2	767.6	783.9	808.7	853.6	907.8	985.6
37.5°	710.3	707.3	703.9	707.7	717.3	730.3	744.3	766.5	805.2	864.7	939.2
40°	689.8	687.4	685.5	684.2	692.9	705.4	716.0	737.1	773.2	829.9	903.4
42.5°	667.4	665.9	663.5	661.8	669.1	678.5	689.6	708.3	744.3	797.6	867.0
45°	631.3	630.1	628.8	627.6	631.9	640.6	649.4	663.1	694.2	745.8	808.7
47.5°	591.1	589.5	589.9	588.0	592.2	598.1	604.2	618.9	648.7	690.5	736.4
50°	562.2	561.6	561.6	561.6	562.8	569.7	575.3	586.5	613.9	655.6	688.6
52.5°	534.8	532.2	532.2	533.2	535.4	539.8	543.4	555.6	579.5	613.8	643.7
55°	491.9	486.9	485.6	486.9	488.7	492.5	496.2	506.2	526.7	552.2	569.7
57.5°	444.3	441.6	439.9	440.1	441.2	444.2	447.0	457.9	474.0	487.4	498.6
60°	410.9	412.2	406.5	407.8	407.8	410.3	414.6	421.5	435.2	444.5	455.7
62.5°	379.5	377.8	376.2	374.5	374.5	375.4	381.3	386.7	398.3	403.2	411.9
65°	330.6	330.6	326.9	328.1	328.8	324.4	327.5	333.7	341.2	343.0	351.2
67.5°	281.1	279.3	277.2	275.3	275.3	275.0	276.6	279.6	285.3	285.9	292.2
70°	247.2	245.9	245.3	243.4	241.0	244.1	242.2	245.3	248.4	249.1	252.8
72.5°	214.3	213.0	211.9	210.1	209.1	208.7	208.8	212.5	214.5	213.7	217.9
75°	167.5	166.2	165.0	161.8	161.8	160.0	160.7	163.1	165.6	163.7	167.5
77.5°	123.0	119.1	118.9	119.8	117.6	118.0	117.3	116.9	118.0	118.2	121.5
80°	94.7	90.3	91.5	90.9	90.3	89.7	88.4	89.0	89.7	90.3	92.1
82.5°	68.2	67.9	66.6	66.5	65.9	64.2	63.5	64.6	65.3	64.9	66.2
85°	34.9	33.0	34.2	33.6	34.2	33.6	31.8	31.8	33.0	32.4	33.6
87.5°	16.4	16.2	15.0	14.8	13.6	13.5	12.4	12.3	12.3	11.7	12.2
90°	29.7	28.7	25.2	21.8	18.3	14.9	11.8	9.2	6.5	3.9	1.2
92.5°	46.7	45.9	43.9	41.9	40.0	38.0	36.1	34.3	32.5	30.7	28.9
95°	89.4	88.4	86.3	84.1	82.0	79.9	78.0	76.0	74.2	72.3	70.5
97.5°	139.6	138.3	136.8	135.2	133.7	132.1	130.7	129.4	127.9	126.6	125.2
100°	176.4	175.6	174.3	172.9	171.6	170.3	168.8	167.2	165.6	164.1	162.5
102.5°	218.5	217.6	215.9	214.1	212.4	210.6	209.3	208.3	207.4	206.4	205.5
105°	281.9	281.9	279.6	277.1	274.7	272.4	270.9	270.4	269.8	269.3	268.8
107.5°	349.0	348.1	347.1	346.2	345.2	344.3	343.6	343.3	343.0	342.7	342.4
110°	394.1	393.0	392.4	392.0	391.4	390.9	390.4	389.8	389.3	388.8	388.2



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	439.2	437.9	437.8	437.7	437.6	437.5	437.3	437.0	436.7	436.3	436.0
115°	509.1	508.9	509.5	509.9	510.5	511.0	510.9	510.1	509.3	508.5	507.7
117.5°	579.1	579.2	579.8	580.5	581.2	581.9	581.9	581.5	580.9	580.4	579.9
120°	625.7	626.0	627.2	628.6	629.9	631.3	631.1	629.5	628.0	626.4	624.8
122.5°	673.0	673.8	674.5	675.1	675.8	676.5	676.3	675.1	673.9	672.7	671.6
125°	743.1	744.3	744.7	745.3	745.8	746.3	746.2	745.4	744.7	743.8	743.0
127.5°	812.5	814.0	814.6	815.2	815.7	816.3	815.8	814.0	812.4	810.6	809.0
130°	857.9	858.9	859.7	860.5	861.3	862.1	861.4	859.3	857.1	855.1	852.9
132.5°	902.5	903.8	904.4	905.0	905.5	906.2	905.4	903.2	901.1	899.0	896.9
135°	968.9	970.0	970.3	970.5	970.8	971.1	970.4	968.8	967.2	965.6	964.0
137.5°	1034.1	1035.2	1034.5	1033.8	1033.2	1032.5	1031.4	1030.2	1028.8	1027.5	1026.1
140°	1076.0	1076.3	1076.0	1075.8	1075.5	1075.2	1074.4	1073.1	1071.8	1070.5	1069.1
142.5°	1116.2	1116.4	1115.9	1115.5	1115.0	1114.5	1113.6	1112.3	1111.0	1109.6	1108.3
145°	1175.2	1175.4	1174.6	1173.9	1173.1	1172.3	1171.6	1171.1	1170.5	1170.1	1169.5
147.5°	1230.7	1230.7	1229.9	1229.2	1228.4	1227.6	1226.9	1225.9	1224.9	1223.9	1223.0
150°	1265.0	1265.0	1264.5	1264.0	1263.5	1262.9	1262.4	1261.9	1261.3	1260.8	1260.3
152.5°	1296.1	1295.6	1295.3	1295.0	1294.7	1294.3	1293.8	1293.1	1292.4	1291.6	1290.9
155°	1341.4	1340.3	1340.1	1339.7	1339.5	1339.3	1339.1	1339.1	1339.1	1339.1	1339.1
157.5°	1380.9	1379.7	1379.5	1379.3	1379.1	1378.9	1379.0	1379.3	1379.6	1379.9	1380.2
160°	1404.9	1403.6	1403.6	1403.6	1403.6	1403.6	1403.9	1404.4	1404.9	1405.5	1406.0
162.5°	1427.9	1426.6	1426.3	1426.2	1425.9	1425.7	1426.0	1426.7	1427.4	1428.2	1428.9
165°	1456.6	1455.0	1455.0	1455.0	1455.0	1455.0	1455.4	1456.2	1457.0	1457.8	1458.6
167.5°	1480.0	1478.4	1478.2	1478.0	1477.7	1477.6	1478.0	1479.0	1480.1	1481.1	1482.3
170°	1492.7	1490.8	1490.8	1490.8	1490.8	1490.8	1491.4	1492.4	1493.5	1494.5	1495.6
172.5°	1503.0	1501.3	1501.3	1501.3	1501.3	1501.3	1501.9	1502.9	1504.0	1505.1	1506.1
175°	1513.9	1512.4	1512.4	1512.4	1512.4	1512.4	1512.8	1513.9	1515.0	1516.1	1517.1
177.5°	1519.1	1517.8	1517.8	1517.8	1517.8	1517.8	1518.2	1519.1	1520.0	1520.8	1521.6
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1293.0	1295.5	1303.9	1310.0	1316.9	1320.9	1324.8	1327.9	1331.8	1332.8	1347.3
5°	1298.7	1311.2	1333.0	1349.2	1369.0	1390.8	1405.8	1412.7	1430.7	1445.7	1475.5
7.5°	1297.1	1323.7	1356.5	1390.6	1427.2	1461.1	1490.5	1525.3	1550.1	1587.4	1624.1
10°	1295.6	1331.1	1373.4	1417.1	1468.1	1515.4	1557.7	1605.0	1644.3	1695.9	1740.1
12.5°	1291.1	1334.1	1392.9	1444.4	1506.4	1571.7	1634.4	1695.2	1730.0	1816.0	1856.7
15°	1280.1	1331.1	1404.5	1483.0	1568.3	1645.5	1725.2	1788.7	1891.4	1966.8	2014.7
17.5°	1258.9	1330.4	1417.5	1512.1	1615.9	1717.6	1807.9	1904.2	2013.3	2104.4	2201.5
20°	1249.0	1327.4	1424.5	1529.1	1636.8	1752.0	1854.7	1970.5	2089.5	2179.1	2303.6
22.5°	1230.5	1319.4	1424.0	1540.6	1655.7	1774.9	1895.1	2011.8	2149.2	2272.7	2391.3
25°	1200.4	1300.0	1408.3	1538.4	1673.6	1793.1	1936.9	2091.9	2235.1	2393.9	2512.2
27.5°	1168.7	1275.1	1383.6	1504.7	1650.0	1791.8	1972.8	2147.9	2323.0	2460.1	2547.7
30°	1144.3	1247.7	1359.8	1481.8	1625.6	1794.3	1996.6	2187.8	2358.4	2476.0	2525.2
32.5°	1117.9	1222.7	1321.9	1449.9	1603.1	1792.8	2011.6	2211.2	2360.4	2438.7	2429.1
35°	1076.5	1164.3	1260.8	1384.0	1564.6	1781.9	2020.3	2213.3	2304.9	2288.1	2161.0
37.5°	1016.7	1090.5	1185.6	1320.5	1519.7	1758.8	2002.9	2147.7	2141.7	2004.9	1820.8
40°	979.4	1042.2	1133.8	1275.7	1484.9	1743.9	1975.5	2069.5	1989.8	1798.6	1578.3
42.5°	930.5	988.4	1080.0	1225.9	1446.5	1713.5	1923.2	1950.4	1794.5	1574.5	1372.5
45°	854.8	905.9	1000.5	1151.2	1389.0	1647.3	1795.6	1728.9	1519.1	1291.9	1138.1
47.5°	773.5	826.6	917.6	1072.4	1305.8	1547.9	1618.5	1476.8	1261.4	1077.1	935.9
50°	722.2	773.2	862.3	1018.6	1249.5	1466.2	1495.5	1312.4	1114.4	952.6	836.8
52.5°	670.4	718.5	806.0	962.7	1183.8	1371.6	1353.5	1167.0	984.9	847.0	756.1
55°	593.3	638.8	722.2	869.1	1070.2	1219.0	1153.7	975.6	824.9	717.9	648.7
57.5°	524.3	567.9	639.9	772.6	947.5	1049.7	966.5	816.5	696.6	614.3	562.7
60°	477.5	516.1	584.6	707.9	859.8	937.6	855.5	722.9	621.9	556.0	509.9
62.5°	433.2	466.8	530.3	642.1	774.1	839.5	756.3	644.1	558.3	499.7	460.6
65°	366.1	396.6	452.7	539.8	648.1	691.7	620.1	529.2	462.6	419.0	392.8
67.5°	304.8	330.7	379.1	447.7	527.4	559.2	504.7	434.4	384.1	349.1	328.4
70°	264.0	286.4	324.4	383.5	455.7	480.0	429.0	371.1	334.3	306.3	287.0
72.5°	229.6	246.1	280.5	326.2	386.5	405.8	370.2	319.2	285.0	264.0	248.7
75°	174.9	188.6	211.0	247.8	289.5	300.7	273.9	242.2	219.1	204.2	192.3
77.5°	126.1	136.3	152.4	175.1	204.0	214.0	197.1	175.9	159.1	149.0	142.4
80°	95.2	103.4	117.1	135.7	153.1	158.8	148.8	132.6	120.8	115.2	109.6
82.5°	70.3	74.9	83.2	95.9	107.8	114.5	106.0	96.3	89.9	84.8	82.7
85°	35.5	37.9	41.7	46.7	54.2	56.6	53.6	51.0	47.3	44.2	44.2
87.5°	13.7	14.3	16.2	17.8	20.4	22.6	22.8	22.5	22.7	22.4	22.1
90°	3.9	6.5	9.2	11.8	14.9	18.3	21.8	25.2	28.7	29.7	30.8
92.5°	30.7	32.5	34.3	36.1	38.0	40.0	41.9	43.9	45.9	46.7	47.5
95°	72.3	74.2	76.0	78.0	79.9	82.0	84.1	86.3	88.4	89.4	90.5
97.5°	126.6	127.9	129.4	130.7	132.1	133.7	135.2	136.8	138.3	139.6	140.8
100°	164.1	165.6	167.2	168.8	170.3	171.6	172.9	174.3	175.6	176.4	177.2
102.5°	206.4	207.4	208.3	209.3	210.6	212.4	214.1	215.9	217.6	218.5	219.3
105°	269.3	269.8	270.4	270.9	272.4	274.7	277.1	279.6	281.9	281.9	281.9
107.5°	342.7	343.0	343.3	343.6	344.3	345.2	346.2	347.1	348.1	349.0	349.8
110°	388.8	389.3	389.8	390.4	390.9	391.4	392.0	392.4	393.0	394.1	395.1



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	436.3	436.7	437.0	437.3	437.5	437.6	437.7	437.8	437.9	439.2	440.5
115°	508.5	509.3	510.1	510.9	511.0	510.5	509.9	509.5	508.9	509.1	509.5
117.5°	580.4	580.9	581.5	581.9	581.9	581.2	580.5	579.8	579.2	579.1	579.0
120°	626.4	628.0	629.5	631.1	631.3	629.9	628.6	627.2	626.0	625.7	625.4
122.5°	672.7	673.9	675.1	676.3	676.5	675.8	675.1	674.5	673.8	673.0	672.3
125°	743.8	744.7	745.4	746.2	746.3	745.8	745.3	744.7	744.3	743.1	742.1
127.5°	810.6	812.4	814.0	815.8	816.3	815.7	815.2	814.6	814.0	812.5	811.0
130°	855.1	857.1	859.3	861.4	862.1	861.3	860.5	859.7	858.9	857.9	856.7
132.5°	899.0	901.1	903.2	905.4	906.2	905.5	905.0	904.4	903.8	902.5	901.3
135°	965.6	967.2	968.8	970.4	971.1	970.8	970.5	970.3	970.0	968.9	967.9
137.5°	1027.5	1028.8	1030.2	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1	1033.0
140°	1070.5	1071.8	1073.1	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0	1075.8
142.5°	1109.6	1111.0	1112.3	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2	1115.9
145°	1170.1	1170.5	1171.1	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2	1174.9
147.5°	1223.9	1224.9	1225.9	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7	1230.7
150°	1260.8	1261.3	1261.9	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0	1265.0
152.5°	1291.6	1292.4	1293.1	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1	1296.5
155°	1339.1	1339.1	1339.1	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4	1342.4
157.5°	1379.9	1379.6	1379.3	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9	1382.0
160°	1405.5	1404.9	1404.4	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9	1406.3
162.5°	1428.2	1427.4	1426.7	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9	1429.2
165°	1457.8	1457.0	1456.2	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6	1458.2
167.5°	1481.1	1480.1	1479.0	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0	1481.7
170°	1494.5	1493.5	1492.4	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7	1494.5
172.5°	1505.1	1504.0	1502.9	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0	1504.6
175°	1516.1	1515.0	1513.9	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9	1515.5
177.5°	1520.8	1520.0	1519.1	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1	1520.4
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0	1285.0
2.5°	1352.3	1352.7	1358.3	1362.2	1360.3	1362.7	1363.7
5°	1477.4	1499.8	1511.6	1520.4	1521.0	1521.6	1526.6
7.5°	1654.9	1678.9	1696.5	1723.1	1731.1	1740.1	1737.5
10°	1784.4	1819.8	1850.4	1866.5	1884.0	1909.5	1889.0
12.5°	1905.4	1968.3	2014.7	2039.9	2056.3	2061.4	2051.4
15°	2105.0	2187.1	2231.3	2230.2	2286.2	2310.5	2272.5
17.5°	2288.1	2363.9	2424.6	2455.8	2502.4	2512.8	2508.0
20°	2400.1	2482.9	2530.2	2583.8	2608.0	2629.8	2633.5
22.5°	2496.7	2571.0	2621.9	2666.4	2686.8	2697.1	2703.3
25°	2596.2	2654.8	2685.3	2700.8	2706.4	2705.1	2697.1
27.5°	2589.3	2593.8	2560.3	2527.2	2497.8	2464.5	2453.0
30°	2522.1	2469.8	2376.5	2323.5	2245.7	2184.0	2208.9
32.5°	2345.3	2241.2	2136.4	2020.7	1924.9	1897.7	1870.3
35°	2001.6	1818.6	1711.5	1587.0	1537.2	1487.4	1453.1
37.5°	1619.4	1477.8	1350.8	1269.3	1219.4	1187.9	1171.0
40°	1400.2	1272.6	1168.0	1102.0	1064.0	1028.5	1023.6
42.5°	1225.4	1106.8	1028.0	975.5	939.0	923.9	913.0
45°	1003.6	920.8	867.9	830.5	806.3	796.9	784.5
47.5°	849.5	790.9	751.2	725.8	707.5	700.5	699.6
50°	763.3	714.7	685.5	665.5	651.3	648.7	638.8
52.5°	698.5	656.5	633.7	616.2	605.9	599.0	596.0
55°	606.4	578.4	557.9	547.9	539.8	532.9	532.9
57.5°	530.6	507.2	493.6	485.1	482.6	477.8	474.7
60°	483.8	463.8	453.3	445.8	440.8	441.4	435.8
62.5°	437.9	425.0	414.9	407.4	401.5	401.6	402.0
65°	373.0	363.0	355.5	353.0	349.3	344.9	346.2
67.5°	316.0	306.7	300.9	296.6	295.3	293.0	296.6
70°	275.2	268.3	264.0	260.2	259.0	259.6	262.8
72.5°	237.8	233.0	230.1	228.4	225.6	225.8	227.8
75°	186.8	183.1	180.5	178.7	178.1	178.1	178.1
77.5°	137.2	136.3	135.2	132.5	132.6	133.3	133.5
80°	108.4	106.5	105.8	104.6	102.7	101.5	104.6
82.5°	81.0	79.1	78.4	78.2	75.3	75.1	77.7
85°	43.6	41.7	42.3	41.7	41.7	41.1	41.1
87.5°	21.8	21.5	21.2	21.8	21.4	21.0	22.1
90°	31.8	33.0	33.7	34.2	34.8	35.3	35.8
92.5°	48.4	49.3	49.5	49.2	48.9	48.6	48.2
95°	91.6	92.6	93.2	93.2	93.2	93.2	93.2
97.5°	142.0	143.2	143.8	143.7	143.5	143.5	143.4
100°	178.0	178.8	179.4	180.0	180.5	181.0	181.6
102.5°	220.1	220.9	221.2	221.1	220.9	220.9	220.8
105°	281.9	281.9	282.2	282.7	283.3	283.8	284.3
107.5°	350.6	351.5	351.7	351.4	351.1	350.8	350.5
110°	396.2	397.3	397.5	397.0	396.5	395.9	395.4



TEST NUMBER: P332235-927

CATALOG NUMBER: S123DIW-S1165D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	441.7	443.0	443.6	443.5	443.4	443.3	443.1
115°	509.7	509.9	509.9	509.7	509.5	509.1	508.9
117.5°	579.0	578.9	578.5	577.7	577.0	576.3	575.5
120°	625.2	624.9	624.5	624.0	623.4	622.9	622.3
122.5°	671.7	671.0	670.3	669.6	668.8	668.0	667.3
125°	741.0	740.0	738.9	737.8	736.8	735.7	734.7
127.5°	809.5	808.0	806.7	805.5	804.2	803.0	801.8
130°	855.7	854.7	853.2	851.4	849.5	847.6	845.7
132.5°	900.0	898.7	897.4	896.0	894.5	893.0	891.6
135°	966.8	965.7	965.0	964.4	963.8	963.4	962.8
137.5°	1031.9	1030.8	1029.7	1028.6	1027.7	1026.7	1025.6
140°	1075.5	1075.2	1074.2	1072.3	1070.5	1068.6	1066.8
142.5°	1115.6	1115.4	1114.5	1113.1	1111.7	1110.2	1108.8
145°	1174.6	1174.4	1173.7	1172.7	1171.6	1170.5	1169.5
147.5°	1230.7	1230.7	1229.9	1228.3	1226.7	1225.0	1223.4
150°	1265.0	1265.0	1264.2	1262.7	1261.1	1259.5	1257.9
152.5°	1296.9	1297.4	1296.9	1295.5	1294.1	1292.7	1291.3
155°	1343.5	1344.6	1344.2	1342.3	1340.5	1338.6	1336.7
157.5°	1383.1	1384.2	1384.0	1382.5	1381.0	1379.5	1378.1
160°	1407.6	1408.9	1409.1	1408.0	1406.9	1405.9	1404.8
162.5°	1430.5	1431.9	1431.7	1430.0	1428.3	1426.6	1424.9
165°	1459.8	1461.3	1461.3	1459.4	1457.5	1455.6	1453.8
167.5°	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4
170°	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8
172.5°	1506.3	1507.9	1507.8	1505.9	1504.1	1502.2	1500.4
175°	1517.1	1518.7	1518.5	1516.7	1514.8	1513.0	1511.2
177.5°	1521.6	1522.9	1522.8	1521.3	1519.8	1518.4	1516.9
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7

(END OF REPORT)