

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332107-927

Luminaire Tested: **S123DIW-S340D1030U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332107-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D1030U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1030 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3950.8 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332107-927

CATALOG NUMBER: S123DIW-S340D1030U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332107-927

CATALOG NUMBER: S123DIW-S340D1030U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28
1	93	89	85	81	83	79	76	73	62	60	58	46	45	44	32	31	30	24
2	85	77	71	66	75	69	64	60	55	51	48	41	39	37	28	27	26	20
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	25	23	22	17
4	70	60	52	47	63	54	47	42	43	38	34	32	29	26	22	20	19	14
5	64	53	45	40	57	48	41	36	38	33	29	29	25	23	20	18	16	13
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	13	10
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4621	4621	4621
5°	4643	4578	4611
10°	4611	4539	4568
15°	4558	4488	4496
20°	4495	4415	4418
25°	4410	4327	4318
30°	4318	4230	4197
35°	4221	4127	4075
40°	4118	4014	3953
45°	4007	3911	3815
50°	3893	3783	3677
55°	3748	3652	3539
60°	3599	3496	3384
65°	3469	3326	3224
70°	3276	3138	2996
75°	2994	2886	2766
80°	2703	2585	2566
85°	2371	2285	2186



TEST NUMBER: P332107-927

CATALOG NUMBER: S123DIW-S340D1030U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	1.0
10°-20°	114.2	2.9
20°-30°	168.7	4.3
30°-40°	197.0	5.0
40°-50°	198.1	5.0
50°-60°	174.0	4.4
60°-70°	129.6	3.3
70°-80°	73.8	1.9
80°-90°	24.2	0.6
90°-100°	66.6	1.7
100°-110°	199.2	5.0
110°-120°	338.8	8.6
120°-130°	445.7	11.3
130°-140°	500.9	12.7
140°-150°	492.4	12.5
150°-160°	414.5	10.5
160°-170°	275.9	7.0
170°-180°	96.6	2.4
0°-30°	323.3	8.2
0°-40°	520.3	13.2
0°-60°	892.4	22.6
0°-90°	1120.1	28.4
90°-120°	604.6	15.3
90°-150°	2043.6	51.7
90°-180°	2831.0	71.7
0°-180°	3950.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	429	429	429	429	429	
5°	430	428	424	427	427	41
15°	409	407	403	405	404	115
25°	371	369	364	365	364	171
35°	321	319	314	312	310	201
45°	263	262	257	253	251	203
55°	200	199	195	191	189	179
65°	136	134	131	128	127	134
75°	72	70	69	68	66	77
85°	19	18	18	18	18	21
90°	1	9	19	22	24	4
95°	47	53	59	62	63	53
105°	181	182	189	190	191	193
115°	341	343	342	343	342	337
125°	499	501	500	497	494	445
135°	648	652	652	649	647	499
145°	786	787	790	789	786	491
155°	900	900	900	903	898	414
165°	980	978	978	982	977	276
175°	1019	1016	1016	1020	1015	97
180°	1022	1022	1022	1022	1022	



TEST NUMBER: P332107-927

CATALOG NUMBER: S123DIW-S340D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	430.8	430.5	430.2	430.0	429.7	429.2	428.5	427.8	427.1	426.4	427.0
5°	429.7	429.2	428.8	428.4	428.0	427.4	426.4	425.6	424.6	423.7	424.5
7.5°	425.5	425.0	424.6	424.2	423.8	423.1	422.2	421.3	420.3	419.4	420.1
10°	421.9	421.5	421.0	420.6	420.3	419.5	418.4	417.4	416.3	415.3	416.0
12.5°	417.2	416.8	416.5	416.1	415.8	415.1	414.2	413.1	412.1	411.1	411.7
15°	409.0	408.7	408.3	408.0	407.7	406.9	405.9	404.8	403.8	402.7	403.4
17.5°	399.4	399.0	398.6	398.2	397.8	397.0	395.9	394.9	393.8	392.8	393.2
20°	392.4	391.9	391.4	390.9	390.4	389.6	388.6	387.5	386.4	385.4	385.7
22.5°	384.4	383.9	383.4	382.9	382.5	381.7	380.6	379.5	378.4	377.4	377.6
25°	371.3	370.8	370.3	369.9	369.4	368.6	367.5	366.5	365.4	364.3	364.4
27.5°	357.4	356.9	356.4	355.9	355.5	354.7	353.6	352.4	351.3	350.1	350.1
30°	347.4	346.9	346.5	346.1	345.7	344.9	343.8	342.6	341.5	340.3	340.3
32.5°	337.3	336.8	336.2	335.6	335.2	334.4	333.5	332.6	331.8	330.9	330.4
35°	321.2	320.7	320.1	319.6	319.2	318.4	317.3	316.2	315.2	314.1	313.6
37.5°	304.6	304.0	303.3	302.7	302.1	301.3	300.2	299.0	298.0	296.9	296.4
40°	293.1	292.6	292.1	291.6	291.1	290.3	289.1	288.0	286.8	285.7	285.0
42.5°	281.5	281.0	280.4	279.9	279.3	278.5	277.3	276.2	275.0	273.9	273.2
45°	263.2	262.8	262.5	262.2	261.9	261.2	260.1	259.0	257.9	256.9	256.0
47.5°	244.9	244.5	244.0	243.5	243.0	242.3	241.3	240.3	239.3	238.3	237.3
50°	232.5	232.1	231.7	231.3	230.9	230.1	229.1	228.1	227.0	225.9	225.0
52.5°	219.5	219.3	219.0	218.7	218.4	217.7	216.6	215.5	214.4	213.2	212.5
55°	199.7	199.6	199.6	199.5	199.4	198.8	197.7	196.6	195.6	194.6	193.6
57.5°	180.8	180.5	180.2	180.0	179.7	179.1	178.2	177.4	176.6	175.7	174.9
60°	167.2	167.2	167.1	167.0	166.9	166.4	165.3	164.4	163.4	162.4	161.7
62.5°	155.1	154.9	154.7	154.5	154.2	153.7	152.7	151.7	150.7	149.7	149.0
65°	136.2	135.8	135.4	135.0	134.6	134.0	133.2	132.3	131.5	130.6	130.0
67.5°	116.2	115.8	115.5	115.1	114.8	114.2	113.7	113.0	112.4	111.8	111.2
70°	104.1	103.6	103.1	102.6	102.1	101.6	101.2	100.6	100.1	99.7	99.1
72.5°	91.4	91.0	90.7	90.3	89.9	89.5	89.0	88.4	87.9	87.3	86.7
75°	72.0	71.6	71.3	71.0	70.7	70.3	70.1	69.9	69.6	69.4	69.0
77.5°	54.7	54.6	54.4	54.3	54.0	53.8	53.6	53.2	52.9	52.6	52.4
80°	43.6	43.3	43.1	42.9	42.5	42.4	42.2	42.1	41.9	41.7	41.6
82.5°	32.6	32.6	32.6	32.5	32.4	32.4	32.3	32.3	32.3	32.2	32.1
85°	19.2	19.0	18.9	18.7	18.5	18.5	18.5	18.5	18.5	18.5	18.3
87.5°	7.8	8.0	8.2	8.3	8.5	8.8	9.2	9.6	10.0	10.4	10.5
90°	0.8	2.6	4.4	6.2	7.9	10.0	12.3	14.7	17.0	19.3	20.0
92.5°	19.4	20.6	21.9	23.1	24.2	25.5	26.9	28.2	29.5	30.8	31.4
95°	47.4	48.6	49.8	51.1	52.4	53.7	55.1	56.6	58.0	59.4	60.1
97.5°	84.1	85.0	86.0	86.9	87.9	88.8	89.8	90.9	91.9	92.9	93.8
100°	109.2	110.2	111.3	112.3	113.4	114.4	115.3	116.2	117.1	118.0	118.5
102.5°	138.1	138.7	139.3	140.0	140.6	141.5	142.7	143.9	145.0	146.2	146.8
105°	180.6	180.9	181.3	181.6	182.0	183.0	184.6	186.2	187.8	189.4	189.4
107.5°	230.0	230.2	230.4	230.7	230.8	231.3	232.0	232.6	233.2	233.9	234.4
110°	260.9	261.2	261.6	261.9	262.3	262.6	263.0	263.3	263.7	264.0	264.7



TEST NUMBER: P332107-927

CATALOG NUMBER: S123DIW-S340D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	292.9	293.2	293.3	293.6	293.8	293.9	294.0	294.1	294.1	294.2	295.1
115°	341.1	341.6	342.1	342.7	343.3	343.3	342.9	342.6	342.2	341.9	342.1
117.5°	389.6	389.9	390.3	390.6	391.0	390.9	390.5	390.0	389.5	389.1	389.0
120°	419.8	420.8	421.9	422.9	424.1	424.1	423.2	422.3	421.4	420.6	420.3
122.5°	451.2	452.0	452.8	453.5	454.3	454.5	454.1	453.6	453.1	452.7	452.2
125°	499.2	499.7	500.3	500.8	501.4	501.5	501.1	500.7	500.3	500.0	499.3
127.5°	543.5	544.6	545.8	546.9	548.0	548.4	548.0	547.6	547.2	546.8	545.9
130°	573.1	574.5	575.9	577.3	578.8	579.2	578.7	578.1	577.6	577.0	576.3
132.5°	602.5	604.0	605.4	606.9	608.3	608.8	608.4	608.0	607.6	607.2	606.3
135°	647.7	648.7	649.8	650.9	652.0	652.4	652.2	652.0	651.9	651.6	650.9
137.5°	689.4	690.3	691.2	692.1	693.0	693.6	694.1	694.6	695.1	695.5	694.7
140°	718.3	719.2	720.1	721.0	721.8	722.4	722.5	722.8	722.9	723.1	722.9
142.5°	744.7	745.5	746.4	747.3	748.2	748.8	749.1	749.4	749.8	750.1	749.9
145°	785.7	786.1	786.4	786.8	787.1	787.6	788.1	788.7	789.2	789.7	789.6
147.5°	821.7	822.3	822.9	823.6	824.3	824.8	825.3	825.9	826.3	826.8	826.8
150°	846.7	847.1	847.4	847.8	848.1	848.5	848.8	849.2	849.5	849.9	849.9
152.5°	867.3	867.8	868.2	868.8	869.3	869.6	869.8	870.1	870.3	870.4	870.8
155°	899.7	899.7	899.7	899.7	899.7	899.8	899.9	900.2	900.3	900.5	901.2
157.5°	927.3	927.1	926.9	926.6	926.5	926.4	926.5	926.7	926.9	926.9	927.7
160°	944.6	944.3	943.9	943.6	943.2	943.0	943.0	943.0	943.0	943.0	943.9
162.5°	960.0	959.6	959.0	958.5	958.1	957.8	958.0	958.1	958.3	958.5	959.3
165°	979.9	979.4	978.9	978.3	977.8	977.6	977.6	977.6	977.6	977.6	978.6
167.5°	995.9	995.1	994.4	993.7	993.0	992.7	992.8	993.0	993.2	993.2	994.3
170°	1004.8	1004.1	1003.4	1002.7	1002.0	1001.6	1001.6	1001.6	1001.6	1001.6	1002.8
172.5°	1011.9	1011.1	1010.4	1009.7	1009.0	1008.7	1008.7	1008.7	1008.7	1008.7	1009.8
175°	1019.3	1018.6	1017.9	1017.2	1016.4	1016.1	1016.1	1016.1	1016.1	1016.1	1017.2
177.5°	1022.3	1021.8	1021.2	1020.6	1020.0	1019.8	1019.8	1019.8	1019.8	1019.8	1020.6
180°	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7



TEST NUMBER: P332107-927

CATALOG NUMBER: S123DIW-S340D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	427.6	428.3	429.0	429.3	429.2	429.1	429.0	429.0
5°	425.4	426.2	427.1	427.4	427.2	427.1	426.8	426.7
7.5°	420.9	421.6	422.3	422.6	422.6	422.5	422.4	422.2
10°	416.8	417.5	418.2	418.5	418.4	418.2	418.0	417.9
12.5°	412.2	412.7	413.3	413.5	413.4	413.3	413.2	413.1
15°	404.0	404.6	405.4	405.4	404.9	404.4	403.9	403.5
17.5°	393.6	394.1	394.6	394.7	394.5	394.3	394.2	394.0
20°	386.0	386.3	386.7	386.7	386.4	386.2	386.0	385.7
22.5°	377.9	378.2	378.4	378.4	378.1	377.8	377.5	377.2
25°	364.5	364.6	364.6	364.6	364.3	364.1	363.8	363.6
27.5°	350.2	350.3	350.3	350.2	349.9	349.6	349.3	349.0
30°	340.3	340.3	340.3	340.0	339.5	338.9	338.3	337.7
32.5°	329.9	329.5	329.1	328.7	328.4	328.0	327.7	327.4
35°	313.1	312.7	312.1	311.7	311.3	310.9	310.5	310.1
37.5°	295.7	295.2	294.5	294.1	293.9	293.6	293.3	293.1
40°	284.4	283.8	283.0	282.6	282.3	281.9	281.6	281.3
42.5°	272.6	271.9	271.2	270.8	270.5	270.1	269.8	269.4
45°	254.9	254.0	252.9	252.3	251.8	251.4	251.0	250.6
47.5°	236.4	235.4	234.4	233.8	233.4	233.1	232.7	232.3
50°	224.1	223.2	222.3	221.6	221.1	220.6	220.1	219.6
52.5°	211.7	210.9	210.1	209.5	209.0	208.5	208.0	207.6
55°	192.7	191.8	190.9	190.3	189.9	189.4	189.0	188.6
57.5°	174.1	173.3	172.5	171.8	171.3	170.9	170.4	169.9
60°	161.0	160.2	159.5	158.9	158.4	158.0	157.6	157.2
62.5°	148.2	147.5	146.8	146.2	146.0	145.7	145.4	145.1
65°	129.4	128.7	128.0	127.6	127.4	127.1	126.8	126.6
67.5°	110.6	110.0	109.5	109.0	108.7	108.3	108.0	107.7
70°	98.5	97.9	97.4	96.9	96.5	96.1	95.6	95.2
72.5°	86.3	85.7	85.2	84.8	84.7	84.4	84.2	84.0
75°	68.6	68.1	67.7	67.4	67.2	66.9	66.7	66.5
77.5°	52.0	51.8	51.5	51.4	51.4	51.4	51.4	51.4
80°	41.5	41.4	41.4	41.4	41.4	41.4	41.4	41.4
82.5°	32.0	31.8	31.7	31.5	31.5	31.4	31.4	31.3
85°	18.1	18.0	17.8	17.7	17.7	17.7	17.7	17.7
87.5°	10.5	10.6	10.7	10.7	10.8	10.9	10.9	11.0
90°	20.7	21.4	22.1	22.7	23.0	23.4	23.7	24.1
92.5°	31.9	32.6	33.1	33.3	33.0	32.9	32.6	32.4
95°	60.8	61.6	62.3	62.6	62.6	62.6	62.6	62.6
97.5°	94.6	95.4	96.3	96.6	96.5	96.5	96.4	96.3
100°	119.1	119.6	120.1	120.6	120.9	121.3	121.6	122.0
102.5°	147.3	147.8	148.4	148.6	148.5	148.5	148.4	148.3
105°	189.4	189.4	189.4	189.6	190.0	190.3	190.7	191.0
107.5°	235.0	235.6	236.1	236.3	236.1	235.9	235.7	235.4
110°	265.5	266.2	266.9	267.0	266.7	266.3	266.0	265.6



TEST NUMBER: P332107-927

CATALOG NUMBER: S123DIW-S340D1030U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	296.0	296.8	297.6	298.0	297.9	297.9	297.9	297.8
115°	342.2	342.5	342.6	342.6	342.5	342.2	342.1	341.9
117.5°	389.0	389.0	389.0	388.6	388.2	387.7	387.1	386.7
120°	420.2	420.0	419.9	419.5	419.2	418.8	418.5	418.1
122.5°	451.7	451.2	450.8	450.3	449.8	449.3	448.9	448.3
125°	498.6	497.9	497.2	496.5	495.7	495.0	494.3	493.6
127.5°	544.9	543.9	542.9	541.9	541.1	540.3	539.5	538.7
130°	575.6	574.9	574.2	573.2	572.0	570.7	569.5	568.2
132.5°	605.5	604.7	603.8	602.9	601.9	600.9	600.0	599.0
135°	650.2	649.5	648.8	648.3	647.9	647.6	647.2	646.9
137.5°	694.0	693.2	692.5	691.8	691.1	690.5	689.8	689.1
140°	722.8	722.5	722.4	721.7	720.4	719.2	718.0	716.7
142.5°	749.7	749.6	749.4	748.8	747.8	746.9	745.9	745.0
145°	789.4	789.2	789.0	788.5	787.8	787.1	786.4	785.7
147.5°	826.8	826.8	826.8	826.2	825.2	824.1	823.1	822.0
150°	849.9	849.9	849.9	849.4	848.3	847.2	846.2	845.1
152.5°	871.0	871.3	871.6	871.3	870.4	869.4	868.5	867.6
155°	901.9	902.6	903.3	903.1	901.8	900.6	899.4	898.1
157.5°	928.4	929.2	929.9	929.9	928.8	927.9	926.9	925.8
160°	944.8	945.7	946.6	946.7	945.9	945.2	944.5	943.8
162.5°	960.2	961.1	962.0	961.9	960.8	959.6	958.5	957.3
165°	979.7	980.7	981.8	981.8	980.5	979.2	977.9	976.8
167.5°	995.5	996.6	997.7	997.7	996.6	995.5	994.3	993.2
170°	1004.1	1005.4	1006.6	1006.6	1005.4	1004.1	1002.8	1001.6
172.5°	1010.9	1012.0	1013.1	1013.0	1011.8	1010.5	1009.2	1008.1
175°	1018.2	1019.3	1020.3	1020.3	1019.0	1017.7	1016.5	1015.3
177.5°	1021.4	1022.3	1023.2	1023.1	1022.1	1021.1	1020.1	1019.1
180°	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7	1021.7

(END OF REPORT)