

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332148

Luminaire Tested: **S123DIW-S560D1535U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332148
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D1535U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8460.2 lumens
Efficiency: N/A
Efficacy: 139.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332148

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332148

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27
1	93	88	85	81	83	79	76	73	62	60	58	46	45	43	31	30	30	23
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25	19
3	77	68	61	55	68	61	55	50	48	44	40	36	33	30	24	23	21	16
4	70	60	52	46	62	54	47	42	42	38	34	32	29	26	22	20	18	14
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14	11
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	14	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P332148

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	1.0
10°-20°	237.0	2.8
20°-30°	350.0	4.1
30°-40°	408.9	4.8
40°-50°	411.1	4.9
50°-60°	361.1	4.3
60°-70°	269.0	3.2
70°-80°	153.3	1.8
80°-90°	49.6	0.6
90°-100°	73.2	0.9
100°-110°	348.7	4.1
110°-120°	837.5	9.9
120°-130°	1066.5	12.6
130°-140°	1139.5	13.5
140°-150°	1065.6	12.6
150°-160°	859.5	10.2
160°-170°	554.7	6.6
170°-180°	191.2	2.3
0°-30°	670.9	7.9
0°-40°	1079.8	12.8
0°-60°	1851.9	21.9
0°-90°	2323.8	27.5
90°-120°	1259.4	14.9
90°-150°	4531.0	53.6
90°-180°	6136.0	72.5
0°-180°	8460.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	2	17	36	42	45	6
95°	91	34	46	56	57	113
105°	446	454	327	78	66	472
115°	836	845	858	873	879	825
125°	1178	1190	1196	1199	1202	1052
135°	1467	1475	1482	1486	1482	1129
145°	1692	1702	1706	1709	1709	1059
155°	1864	1862	1863	1869	1861	859
165°	1966	1962	1960	1971	1961	555
175°	2012	2005	2006	2016	2005	191
180°	2012	2012	2012	2012	2012	



TEST NUMBER: P332148

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.2	16.5	16.7	17.0	17.3	17.7	18.5	19.2	19.9	20.7	20.8
90°	1.5	4.8	8.1	11.5	14.8	18.6	22.9	27.2	31.6	35.9	37.2
92.5°	27.8	26.9	25.9	25.0	24.1	25.2	28.5	31.8	35.0	38.3	40.4
95°	91.2	77.6	64.0	50.3	36.7	31.7	35.4	39.0	42.7	46.3	48.7
97.5°	183.3	177.2	171.1	164.9	158.8	143.8	119.9	96.0	72.1	48.1	50.8
100°	252.7	259.3	265.9	272.6	279.2	256.6	204.8	153.0	101.2	49.3	52.0
102.5°	331.6	336.4	341.2	345.9	350.7	324.8	268.2	211.6	155.0	98.4	90.1
105°	445.5	449.2	452.8	456.5	460.1	447.0	417.1	387.2	357.3	327.4	268.6
107.5°	565.7	568.6	571.5	574.5	577.4	581.2	585.9	590.7	595.4	600.1	557.0
110°	645.8	648.5	651.1	653.8	656.5	659.6	663.3	666.9	670.6	674.2	663.3



TEST NUMBER: P332148

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	722.4	724.8	727.2	729.6	731.9	735.0	738.6	742.3	745.9	749.6	749.8
115°	835.7	837.7	839.7	841.7	843.7	846.2	849.2	852.1	855.1	858.1	861.4
117.5°	945.4	947.9	950.3	952.8	955.3	957.3	958.8	960.3	961.8	963.4	966.0
120°	1013.6	1016.6	1019.6	1022.6	1025.6	1027.6	1028.5	1029.5	1030.5	1031.5	1034.2
122.5°	1083.0	1085.4	1087.9	1090.3	1092.8	1094.7	1095.9	1097.2	1098.4	1099.7	1101.6
125°	1178.0	1180.7	1183.4	1186.0	1188.7	1190.7	1192.0	1193.3	1194.7	1196.0	1196.7
127.5°	1270.1	1272.8	1275.5	1278.1	1280.8	1282.9	1284.5	1286.1	1287.7	1289.3	1290.3
130°	1327.5	1330.2	1332.9	1335.5	1338.2	1340.2	1341.5	1342.8	1344.2	1345.5	1346.8
132.5°	1382.6	1385.2	1387.9	1390.5	1393.2	1395.1	1396.1	1397.2	1398.2	1399.3	1400.6
135°	1466.6	1468.6	1470.6	1472.6	1474.6	1476.2	1477.5	1478.9	1480.2	1481.5	1482.5
137.5°	1538.3	1540.9	1543.4	1545.9	1548.4	1550.1	1550.8	1551.5	1552.3	1553.0	1554.6
140°	1586.2	1588.2	1590.2	1592.2	1594.2	1595.6	1596.6	1597.6	1598.6	1599.6	1601.0
142.5°	1630.4	1632.4	1634.4	1636.4	1638.4	1639.9	1640.9	1641.9	1642.9	1643.9	1644.9
145°	1692.3	1694.6	1697.0	1699.3	1701.6	1703.1	1703.8	1704.4	1705.1	1705.8	1706.4
147.5°	1750.6	1752.2	1753.7	1755.2	1756.7	1757.8	1758.5	1759.2	1759.8	1760.5	1761.2
150°	1786.5	1787.5	1788.5	1789.5	1790.5	1791.3	1792.0	1792.7	1793.3	1794.0	1794.6
152.5°	1818.8	1819.3	1819.7	1820.2	1820.7	1821.1	1821.5	1821.9	1822.3	1822.7	1823.9
155°	1864.2	1863.6	1862.9	1862.3	1861.6	1861.4	1861.8	1862.1	1862.4	1862.7	1864.4
157.5°	1899.5	1899.5	1899.4	1899.3	1899.3	1899.1	1898.7	1898.4	1898.1	1897.7	1899.7
160°	1921.1	1920.7	1920.4	1920.1	1919.7	1919.4	1919.1	1918.7	1918.4	1918.1	1920.1
162.5°	1941.4	1940.5	1939.7	1938.8	1937.9	1937.3	1937.0	1936.7	1936.3	1936.0	1938.3
165°	1965.9	1964.9	1963.9	1962.9	1961.9	1961.3	1960.9	1960.6	1960.3	1959.9	1962.6
167.5°	1985.0	1983.7	1982.4	1981.1	1979.7	1979.1	1979.1	1979.1	1979.1	1979.1	1981.7
170°	1995.8	1994.5	1993.1	1991.8	1990.5	1989.8	1989.8	1989.8	1989.8	1989.8	1992.5
172.5°	2003.0	2001.4	1999.8	1998.2	1996.6	1995.9	1996.2	1996.5	1996.7	1997.0	1999.7
175°	2012.2	2010.6	2008.9	2007.3	2005.6	2004.9	2005.3	2005.6	2005.9	2006.3	2008.6
177.5°	2014.6	2013.3	2012.0	2010.7	2009.3	2008.8	2009.1	2009.3	2009.6	2009.9	2012.0
180°	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2



TEST NUMBER: P332148

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	20.9	21.0	21.2	21.3	21.4	21.6	21.7	21.8
90°	38.5	39.9	41.2	42.2	42.9	43.5	44.2	44.8
92.5°	42.5	44.7	46.8	48.0	48.4	48.8	49.2	49.6
95°	51.0	53.3	55.6	56.8	56.8	56.8	56.8	56.8
97.5°	53.5	56.1	58.8	60.3	60.6	60.9	61.3	61.6
100°	54.6	57.3	60.0	61.5	61.8	62.1	62.5	62.8
102.5°	81.9	73.7	65.4	61.6	62.2	62.8	63.4	64.0
105°	209.8	151.0	92.2	63.1	63.8	64.5	65.1	65.8
107.5°	513.8	470.7	427.6	383.9	339.6	295.2	250.9	206.6
110°	652.3	641.3	630.4	601.1	553.6	506.1	458.6	411.1



TEST NUMBER: P332148

CATALOG NUMBER: S123DIW-S560D1535U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	750.0	750.2	750.4	745.5	735.4	725.4	715.4	705.3
115°	864.8	868.1	871.4	873.7	875.1	876.4	877.7	879.1
117.5°	968.7	971.3	974.0	975.5	975.7	976.0	976.3	976.5
120°	1036.9	1039.5	1042.2	1043.5	1043.5	1043.5	1043.5	1043.5
122.5°	1103.4	1105.3	1107.2	1108.2	1108.5	1108.7	1109.0	1109.3
125°	1197.3	1198.0	1198.6	1199.3	1200.0	1200.6	1201.3	1202.0
127.5°	1291.4	1292.5	1293.5	1293.7	1293.1	1292.4	1291.7	1291.1
130°	1348.1	1349.5	1350.8	1351.1	1350.5	1349.8	1349.1	1348.5
132.5°	1402.0	1403.3	1404.6	1404.8	1403.9	1403.0	1402.0	1401.1
135°	1483.5	1484.5	1485.5	1485.5	1484.5	1483.5	1482.5	1481.5
137.5°	1556.2	1557.8	1559.4	1559.8	1559.2	1558.5	1557.8	1557.2
140°	1602.3	1603.6	1604.9	1605.3	1604.6	1604.0	1603.3	1602.6
142.5°	1646.0	1647.1	1648.1	1648.2	1647.3	1646.3	1645.4	1644.5
145°	1707.1	1707.8	1708.4	1708.8	1708.8	1708.8	1708.8	1708.8
147.5°	1761.8	1762.5	1763.2	1762.7	1761.2	1759.7	1758.1	1756.6
150°	1795.3	1796.0	1796.6	1796.5	1795.5	1794.5	1793.5	1792.5
152.5°	1825.1	1826.3	1827.5	1827.3	1825.8	1824.2	1822.7	1821.2
155°	1866.1	1867.7	1869.4	1869.2	1867.2	1865.2	1863.2	1861.3
157.5°	1901.7	1903.7	1905.7	1905.4	1902.8	1900.2	1897.6	1895.0
160°	1922.1	1924.0	1926.0	1925.9	1923.5	1921.2	1918.9	1916.6
162.5°	1940.5	1942.8	1945.0	1945.1	1943.1	1941.0	1939.0	1936.9
165°	1965.2	1967.9	1970.6	1970.7	1968.4	1966.1	1963.7	1961.4
167.5°	1984.4	1987.0	1989.7	1989.7	1987.0	1984.4	1981.7	1979.1
170°	1995.1	1997.8	2000.5	2000.5	1997.8	1995.1	1992.5	1989.8
172.5°	2002.3	2005.0	2007.6	2007.5	2004.6	2001.7	1998.7	1995.8
175°	2010.9	2013.2	2015.6	2015.4	2012.7	2010.1	2007.4	2004.8
177.5°	2014.1	2016.2	2018.4	2018.1	2015.4	2012.8	2010.1	2007.5
180°	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2	2012.2

(END OF REPORT)