

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332125

Luminaire Tested: **S123DIW-S560D460U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332125
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S560D460U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3918.2 lumens
Efficiency: N/A
Efficacy: 129.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332125
CATALOG NUMBER: S123DIW-S560D460U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332125

CATALOG NUMBER: S123DIW-S560D460U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	95	91	88	93	89	86	83	78	75	73	67	65	63	57	56	54	50
2	91	83	77	72	84	78	72	68	68	64	60	59	55	53	50	48	46	42
3	83	73	66	60	77	69	62	57	60	55	50	52	48	45	44	41	39	35
4	76	65	57	51	70	61	54	48	53	48	43	46	42	38	40	36	34	30
5	70	58	49	43	65	54	47	41	48	42	37	41	37	33	36	32	29	26
6	64	52	44	38	60	49	41	36	43	37	32	38	33	29	32	29	26	23
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	30	26	23	20
8	55	43	35	29	51	40	33	28	36	30	25	31	26	23	27	23	20	18
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	19	16
10	48	36	28	24	45	34	27	23	30	24	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9590	9590	9590
5°	9634	9502	9568
10°	9570	9419	9477
15°	9458	9313	9331
20°	9328	9160	9170
25°	9152	8980	8961
30°	8959	8779	8712
35°	8757	8566	8456
40°	8546	8331	8202
45°	8315	8115	7917
50°	8081	7850	7633
55°	7777	7576	7345
60°	7470	7255	7025
65°	7200	6907	6691
70°	6798	6508	6219
75°	6213	5989	5735
80°	5604	5368	5318
85°	4915	4730	4545



TEST NUMBER: P332125

CATALOG NUMBER: S123DIW-S560D460U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	2.1
10°-20°	237.0	6.0
20°-30°	350.0	8.9
30°-40°	408.9	10.4
40°-50°	411.1	10.5
50°-60°	361.1	9.2
60°-70°	269.0	6.9
70°-80°	153.3	3.9
80°-90°	45.7	1.2
90°-100°	37.6	1.0
100°-110°	112.5	2.9
110°-120°	191.3	4.9
120°-130°	251.7	6.4
130°-140°	282.9	7.2
140°-150°	278.0	7.1
150°-160°	234.1	6.0
160°-170°	155.8	4.0
170°-180°	54.6	1.4
0°-30°	670.9	17.1
0°-40°	1079.8	27.6
0°-60°	1851.9	47.3
0°-90°	2319.9	59.2
90°-120°	341.4	8.7
90°-150°	1153.9	29.5
90°-180°	1598.0	40.8
0°-180°	3918.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	879	887	886	84
15°	849	845	836	841	837	239
25°	771	766	756	757	754	355
35°	666	662	652	647	644	417
45°	546	543	533	524	520	421
55°	414	413	404	396	391	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	44
90°	0	5	11	13	14	4
95°	27	30	34	35	35	30
105°	102	103	107	107	108	109
115°	193	194	193	194	193	191
125°	282	283	282	280	279	251
135°	366	368	368	366	365	282
145°	444	445	446	445	444	277
155°	508	508	508	510	507	234
165°	553	552	552	554	552	156
175°	576	574	574	576	573	55
180°	577	577	577	577	577	



TEST NUMBER: P332125

CATALOG NUMBER: S123DIW-S560D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	893.9	893.4	892.9	892.3	891.8	890.7	889.2	887.7	886.3	884.8	886.1
5°	891.6	890.8	889.9	889.1	888.2	886.9	885.0	883.1	881.3	879.4	881.1
7.5°	882.9	882.1	881.2	880.4	879.5	878.1	876.2	874.2	872.3	870.4	871.9
10°	875.6	874.7	873.9	873.0	872.2	870.6	868.4	866.2	864.0	861.8	863.3
12.5°	865.8	865.0	864.3	863.6	862.9	861.5	859.4	857.3	855.3	853.2	854.3
15°	848.7	848.1	847.4	846.7	846.0	844.6	842.4	840.2	837.9	835.7	837.1
17.5°	829.0	828.1	827.2	826.3	825.4	823.9	821.7	819.5	817.3	815.0	816.0
20°	814.3	813.3	812.2	811.2	810.2	808.6	806.4	804.2	801.9	799.7	800.4
22.5°	797.7	796.7	795.7	794.7	793.6	792.0	789.8	787.6	785.4	783.2	783.7
25°	770.6	769.6	768.6	767.6	766.5	764.9	762.7	760.5	758.3	756.1	756.2
27.5°	741.7	740.7	739.7	738.7	737.7	736.0	733.6	731.3	728.9	726.5	726.6
30°	720.8	720.0	719.1	718.3	717.4	715.8	713.4	711.0	708.7	706.3	706.3
32.5°	700.0	698.9	697.7	696.6	695.5	694.0	692.2	690.3	688.5	686.7	685.7
35°	666.4	665.4	664.4	663.4	662.4	660.7	658.5	656.3	654.1	651.9	650.9
37.5°	632.1	630.8	629.5	628.2	626.9	625.2	622.9	620.7	618.4	616.2	615.0
40°	608.2	607.2	606.2	605.2	604.1	602.4	600.0	597.7	595.3	592.9	591.5
42.5°	584.3	583.2	582.0	580.8	579.7	577.9	575.5	573.2	570.8	568.4	567.0
45°	546.2	545.5	544.8	544.1	543.4	542.0	539.8	537.6	535.4	533.1	531.1
47.5°	508.3	507.3	506.4	505.4	504.4	502.8	500.8	498.7	496.6	494.5	492.5
50°	482.6	481.7	480.9	480.0	479.2	477.7	475.4	473.2	471.0	468.8	466.9
52.5°	455.6	455.0	454.5	453.9	453.3	451.8	449.5	447.2	444.8	442.5	440.9
55°	414.4	414.2	414.1	413.9	413.7	412.5	410.3	408.1	405.9	403.7	401.8
57.5°	375.2	374.6	374.0	373.5	372.9	371.7	369.9	368.2	366.4	364.6	363.0
60°	347.0	346.8	346.7	346.5	346.3	345.2	343.2	341.1	339.1	337.0	335.5
62.5°	321.9	321.4	321.0	320.6	320.1	318.9	316.8	314.8	312.7	310.7	309.2
65°	282.7	281.8	281.0	280.1	279.3	278.0	276.3	274.6	272.9	271.2	269.8
67.5°	241.1	240.4	239.6	238.9	238.1	237.1	235.8	234.5	233.2	232.0	230.8
70°	216.0	215.0	214.0	213.0	211.9	210.9	209.9	208.9	207.8	206.8	205.6
72.5°	189.7	188.9	188.2	187.4	186.7	185.7	184.6	183.4	182.2	181.1	180.0
75°	149.4	148.7	148.0	147.3	146.7	146.1	145.5	145.0	144.5	144.0	143.2
77.5°	113.7	113.3	112.9	112.6	112.2	111.7	111.1	110.5	109.8	109.2	108.7
80°	90.4	89.9	89.4	88.9	88.3	87.9	87.6	87.2	86.9	86.6	86.4
82.5°	67.7	67.6	67.5	67.4	67.3	67.2	67.2	67.1	67.0	67.0	66.6
85°	39.8	39.5	39.2	38.8	38.5	38.3	38.3	38.3	38.3	38.3	38.0
87.5°	16.0	15.8	15.6	15.4	15.2	15.2	15.3	15.4	15.5	15.7	15.6
90°	0.5	1.5	2.5	3.5	4.5	5.6	6.9	8.3	9.6	10.9	11.3
92.5°	11.0	11.7	12.3	13.0	13.7	14.4	15.2	15.9	16.7	17.4	17.7
95°	26.7	27.4	28.1	28.9	29.6	30.3	31.1	31.9	32.7	33.5	33.9
97.5°	47.5	48.0	48.5	49.1	49.6	50.1	50.7	51.3	51.9	52.5	52.9
100°	61.6	62.2	62.8	63.4	64.0	64.6	65.1	65.6	66.1	66.6	66.9
102.5°	77.9	78.3	78.7	79.0	79.4	79.9	80.6	81.2	81.9	82.6	82.9
105°	102.0	102.2	102.4	102.6	102.8	103.3	104.2	105.1	106.0	106.9	106.9
107.5°	129.9	130.0	130.1	130.2	130.4	130.6	131.0	131.3	131.7	132.1	132.4
110°	147.3	147.5	147.7	147.9	148.1	148.3	148.5	148.7	148.9	149.1	149.5



TEST NUMBER: P332125

CATALOG NUMBER: S123DIW-S560D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.4	165.5	165.7	165.8	165.9	166.0	166.0	166.1	166.1	166.1	166.6
115°	192.6	192.9	193.2	193.5	193.8	193.9	193.7	193.5	193.3	193.1	193.2
117.5°	220.0	220.2	220.4	220.6	220.8	220.7	220.5	220.2	220.0	219.7	219.7
120°	237.0	237.6	238.2	238.8	239.4	239.5	239.0	238.5	238.0	237.5	237.4
122.5°	254.8	255.2	255.7	256.1	256.5	256.6	256.4	256.1	255.9	255.6	255.3
125°	281.9	282.2	282.5	282.8	283.1	283.1	282.9	282.7	282.5	282.3	281.9
127.5°	306.9	307.5	308.2	308.8	309.5	309.7	309.5	309.2	309.0	308.8	308.2
130°	323.6	324.4	325.2	326.0	326.8	327.0	326.7	326.4	326.1	325.8	325.4
132.5°	340.2	341.0	341.9	342.7	343.5	343.8	343.5	343.3	343.1	342.9	342.4
135°	365.7	366.3	366.9	367.5	368.1	368.4	368.3	368.2	368.1	368.0	367.6
137.5°	389.3	389.8	390.3	390.8	391.3	391.7	391.9	392.2	392.5	392.7	392.3
140°	405.6	406.1	406.6	407.1	407.6	407.9	408.0	408.1	408.2	408.3	408.2
142.5°	420.5	421.0	421.5	422.0	422.5	422.8	423.0	423.2	423.4	423.5	423.4
145°	443.7	443.9	444.1	444.3	444.5	444.7	445.0	445.3	445.6	445.9	445.8
147.5°	464.0	464.3	464.7	465.0	465.4	465.7	466.0	466.3	466.6	466.9	466.9
150°	478.1	478.3	478.5	478.7	478.9	479.1	479.3	479.5	479.7	479.9	479.9
152.5°	489.7	490.0	490.3	490.5	490.8	491.0	491.1	491.3	491.4	491.5	491.7
155°	508.0	508.0	508.0	508.0	508.0	508.1	508.2	508.3	508.4	508.5	508.9
157.5°	523.6	523.5	523.4	523.2	523.1	523.1	523.2	523.3	523.3	523.4	523.8
160°	533.4	533.2	533.0	532.8	532.6	532.5	532.5	532.5	532.5	532.5	533.0
162.5°	542.1	541.8	541.5	541.2	541.0	540.9	540.9	541.0	541.1	541.2	541.7
165°	553.3	553.0	552.7	552.4	552.1	552.0	552.0	552.0	552.0	552.0	552.6
167.5°	562.3	561.9	561.5	561.1	560.7	560.5	560.6	560.7	560.8	560.8	561.5
170°	567.4	567.0	566.6	566.2	565.8	565.6	565.6	565.6	565.6	565.6	566.3
172.5°	571.4	571.0	570.6	570.2	569.7	569.5	569.5	569.5	569.5	569.5	570.2
175°	575.5	575.1	574.7	574.3	573.9	573.7	573.7	573.7	573.7	573.7	574.3
177.5°	577.3	576.9	576.6	576.3	576.0	575.8	575.8	575.8	575.8	575.8	576.3
180°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9



TEST NUMBER: P332125

CATALOG NUMBER: S123DIW-S560D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	890.9	890.9	890.9	890.9	890.9	890.9	890.9	890.9
2.5°	887.5	888.8	890.2	890.8	890.7	890.5	890.4	890.3
5°	882.8	884.5	886.2	886.9	886.5	886.2	885.9	885.5
7.5°	873.4	874.9	876.5	877.1	876.9	876.7	876.5	876.3
10°	864.8	866.4	867.9	868.5	868.2	867.8	867.5	867.1
12.5°	855.4	856.6	857.7	858.1	857.9	857.7	857.5	857.3
15°	838.5	839.8	841.2	841.3	840.3	839.3	838.3	837.3
17.5°	817.0	817.9	818.9	819.1	818.8	818.4	818.0	817.6
20°	801.1	801.8	802.4	802.5	802.0	801.5	801.0	800.5
22.5°	784.3	784.8	785.4	785.3	784.7	784.0	783.4	782.7
25°	756.4	756.6	756.7	756.6	756.1	755.6	755.0	754.5
27.5°	726.8	726.9	727.0	726.8	726.1	725.5	724.8	724.2
30°	706.3	706.3	706.3	705.7	704.5	703.3	702.1	700.9
32.5°	684.8	683.8	682.8	682.0	681.4	680.8	680.1	679.5
35°	649.8	648.8	647.8	646.9	646.0	645.2	644.3	643.5
37.5°	613.7	612.5	611.3	610.4	609.9	609.3	608.8	608.2
40°	590.2	588.8	587.5	586.4	585.7	585.1	584.4	583.7
42.5°	565.7	564.3	562.9	561.9	561.2	560.6	559.9	559.2
45°	529.1	527.0	525.0	523.5	522.7	521.8	521.0	520.1
47.5°	490.5	488.5	486.5	485.1	484.4	483.6	482.9	482.1
50°	465.1	463.2	461.3	459.9	458.8	457.8	456.8	455.8
52.5°	439.3	437.7	436.1	434.7	433.7	432.7	431.7	430.7
55°	399.9	398.1	396.2	394.8	394.0	393.1	392.3	391.4
57.5°	361.3	359.6	358.0	356.6	355.6	354.7	353.7	352.7
60°	334.0	332.5	330.9	329.7	328.9	328.0	327.2	326.3
62.5°	307.6	306.1	304.6	303.5	302.9	302.4	301.8	301.2
65°	268.4	267.1	265.7	264.8	264.3	263.8	263.3	262.7
67.5°	229.6	228.4	227.2	226.2	225.5	224.8	224.1	223.4
70°	204.4	203.3	202.1	201.0	200.2	199.3	198.5	197.6
72.5°	179.0	177.9	176.9	176.1	175.7	175.2	174.8	174.3
75°	142.3	141.5	140.6	139.9	139.4	138.9	138.4	137.9
77.5°	108.1	107.5	106.9	106.6	106.6	106.6	106.6	106.6
80°	86.2	86.0	85.9	85.8	85.8	85.8	85.8	85.8
82.5°	66.3	66.0	65.7	65.5	65.4	65.2	65.1	65.0
85°	37.6	37.3	36.9	36.8	36.8	36.8	36.8	36.8
87.5°	15.5	15.5	15.4	15.4	15.5	15.5	15.5	15.6
90°	11.7	12.1	12.5	12.8	13.0	13.2	13.4	13.6
92.5°	18.0	18.4	18.7	18.8	18.7	18.5	18.4	18.3
95°	34.3	34.7	35.1	35.3	35.3	35.3	35.3	35.3
97.5°	53.4	53.9	54.3	54.5	54.5	54.5	54.4	54.4
100°	67.2	67.5	67.8	68.1	68.3	68.5	68.7	68.9
102.5°	83.2	83.5	83.8	83.9	83.9	83.8	83.8	83.7
105°	106.9	106.9	106.9	107.0	107.3	107.5	107.7	107.9
107.5°	132.7	133.0	133.3	133.4	133.3	133.2	133.1	133.0
110°	149.9	150.3	150.7	150.8	150.6	150.4	150.2	150.0



TEST NUMBER: P332125

CATALOG NUMBER: S123DIW-S560D460U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	167.1	167.6	168.1	168.3	168.2	168.2	168.2	168.1
115°	193.3	193.4	193.5	193.5	193.4	193.3	193.2	193.1
117.5°	219.7	219.6	219.6	219.5	219.2	218.9	218.6	218.3
120°	237.3	237.2	237.1	236.9	236.7	236.5	236.3	236.1
122.5°	255.1	254.8	254.5	254.3	254.0	253.7	253.4	253.1
125°	281.5	281.1	280.7	280.3	279.9	279.5	279.1	278.7
127.5°	307.7	307.1	306.5	306.0	305.6	305.1	304.6	304.2
130°	325.0	324.6	324.2	323.7	323.0	322.3	321.6	320.8
132.5°	341.9	341.4	340.9	340.4	339.9	339.3	338.8	338.2
135°	367.2	366.8	366.4	366.1	365.9	365.7	365.5	365.3
137.5°	391.9	391.5	391.0	390.6	390.2	389.9	389.5	389.1
140°	408.1	408.0	407.9	407.5	406.8	406.1	405.4	404.7
142.5°	423.3	423.2	423.1	422.8	422.3	421.7	421.2	420.6
145°	445.7	445.6	445.5	445.3	444.9	444.5	444.1	443.7
147.5°	466.9	466.9	466.9	466.6	466.0	465.3	464.7	464.1
150°	479.9	479.9	479.9	479.6	479.0	478.4	477.8	477.2
152.5°	491.8	492.0	492.2	492.0	491.5	490.9	490.4	489.9
155°	509.3	509.7	510.1	509.9	509.2	508.5	507.8	507.1
157.5°	524.3	524.7	525.1	525.0	524.5	523.9	523.3	522.8
160°	533.5	534.0	534.5	534.5	534.1	533.7	533.3	532.9
162.5°	542.2	542.7	543.2	543.1	542.5	541.8	541.2	540.5
165°	553.2	553.8	554.4	554.3	553.6	552.9	552.2	551.5
167.5°	562.1	562.7	563.3	563.3	562.7	562.1	561.5	560.8
170°	567.0	567.7	568.4	568.4	567.7	567.0	566.3	565.6
172.5°	570.8	571.4	572.0	572.0	571.3	570.6	569.9	569.2
175°	574.9	575.5	576.1	576.1	575.4	574.7	574.0	573.3
177.5°	576.8	577.3	577.7	577.7	577.1	576.6	576.0	575.4
180°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9

(END OF REPORT)