

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332173

Luminaire Tested: **S123DIW-S775D1320U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332173
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1320U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1320 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7748.1 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332173

CATALOG NUMBER: S123DIW-S775D1320U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332173

CATALOG NUMBER: S123DIW-S775D1320U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41
1	96	91	88	84	87	83	80	77	68	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	34	29
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	33	31	29	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	47	41	60	51	44	38	42	37	33	34	30	27	26	24	22	18
6	61	49	41	36	56	45	38	33	38	32	28	31	27	24	24	21	19	16
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	19	20	17	15	13
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	20	26	21	18	22	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13108	13108	13108
5°	13169	12988	13078
10°	13081	12875	12955
15°	12929	12730	12754
20°	12749	12521	12534
25°	12511	12275	12250
30°	12246	11999	11908
35°	11971	11709	11557
40°	11682	11387	11212
45°	11365	11094	10823
50°	11047	10731	10433
55°	10631	10355	10042
60°	10211	9918	9604
65°	9841	9442	9146
70°	9294	8897	8500
75°	8492	8189	7839
80°	7662	7333	7271
85°	6719	6472	6212



TEST NUMBER: P332173

CATALOG NUMBER: S123DIW-S775D1320U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.7	1.5
10°-20°	323.9	4.2
20°-30°	478.4	6.2
30°-40°	558.9	7.2
40°-50°	561.9	7.3
50°-60°	493.6	6.4
60°-70°	367.7	4.7
70°-80°	209.5	2.7
80°-90°	65.0	0.8
90°-100°	107.6	1.4
100°-110°	321.9	4.2
110°-120°	547.5	7.1
120°-130°	720.2	9.3
130°-140°	809.5	10.4
140°-150°	795.7	10.3
150°-160°	669.9	8.6
160°-170°	445.9	5.8
170°-180°	156.2	2.0
0°-30°	917.1	11.8
0°-40°	1475.9	19.0
0°-60°	2531.4	32.7
0°-90°	3173.6	41.0
90°-120°	977.1	12.6
90°-150°	3302.5	42.6
90°-180°	4574.0	59.0
0°-180°	7748.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1219	1213	1202	1212	1210	115
15°	1160	1155	1142	1150	1144	327
25°	1053	1047	1034	1034	1031	485
35°	911	904	891	885	880	570
45°	747	742	729	717	711	576
55°	566	565	552	541	535	507
65°	386	381	371	363	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	60
90°	1	14	31	36	39	8
95°	76	86	96	101	101	86
105°	292	295	306	306	309	313
115°	551	555	552	554	552	545
125°	807	810	808	803	798	719
135°	1047	1054	1053	1048	1045	806
145°	1270	1272	1276	1275	1270	793
155°	1454	1454	1455	1460	1451	669
165°	1584	1580	1580	1587	1578	446
175°	1647	1642	1642	1649	1641	156
180°	1651	1651	1651	1651	1651	



TEST NUMBER: P332173

CATALOG NUMBER: S123DIW-S775D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1221.9	1221.2	1220.5	1219.7	1219.0	1217.6	1215.5	1213.5	1211.4	1209.4	1211.2
5°	1218.8	1217.6	1216.5	1215.3	1214.1	1212.3	1209.7	1207.2	1204.6	1202.0	1204.4
7.5°	1206.9	1205.7	1204.5	1203.4	1202.2	1200.3	1197.6	1195.0	1192.3	1189.7	1191.8
10°	1196.8	1195.6	1194.5	1193.3	1192.2	1190.1	1187.0	1184.0	1181.0	1178.0	1180.1
12.5°	1183.4	1182.4	1181.5	1180.5	1179.5	1177.6	1174.8	1171.9	1169.1	1166.2	1167.8
15°	1160.2	1159.2	1158.3	1157.4	1156.4	1154.5	1151.4	1148.4	1145.4	1142.4	1144.2
17.5°	1133.1	1131.9	1130.7	1129.5	1128.3	1126.2	1123.2	1120.1	1117.1	1114.1	1115.4
20°	1113.0	1111.6	1110.3	1108.9	1107.5	1105.2	1102.2	1099.2	1096.2	1093.1	1094.1
22.5°	1090.4	1089.0	1087.6	1086.2	1084.8	1082.6	1079.6	1076.6	1073.6	1070.5	1071.3
25°	1053.4	1052.0	1050.6	1049.2	1047.8	1045.6	1042.5	1039.5	1036.5	1033.5	1033.7
27.5°	1013.8	1012.4	1011.1	1009.7	1008.4	1006.1	1002.8	999.6	996.3	993.0	993.2
30°	985.3	984.1	983.0	981.8	980.6	978.4	975.2	971.9	968.7	965.4	965.4
32.5°	956.8	955.3	953.7	952.2	950.7	948.7	946.1	943.6	941.1	938.6	937.3
35°	911.0	909.6	908.2	906.8	905.4	903.2	900.1	897.1	894.1	891.1	889.7
37.5°	864.0	862.3	860.5	858.7	857.0	854.6	851.5	848.4	845.3	842.3	840.6
40°	831.4	830.0	828.6	827.2	825.8	823.5	820.2	817.0	813.7	810.4	808.6
42.5°	798.7	797.1	795.5	794.0	792.4	790.0	786.7	783.4	780.2	776.9	775.1
45°	746.6	745.6	744.7	743.8	742.8	740.9	737.8	734.8	731.8	728.8	726.0
47.5°	694.8	693.5	692.1	690.8	689.4	687.3	684.5	681.7	678.8	676.0	673.2
50°	659.7	658.5	657.3	656.2	655.0	652.9	649.9	646.9	643.8	640.8	638.3
52.5°	622.8	622.0	621.2	620.4	619.6	617.6	614.4	611.2	608.0	604.8	602.6
55°	566.5	566.2	566.0	565.8	565.5	563.9	560.9	557.9	554.8	551.8	549.3
57.5°	512.9	512.1	511.3	510.5	509.7	508.1	505.7	503.2	500.8	498.4	496.1
60°	474.3	474.1	473.9	473.6	473.4	471.9	469.1	466.3	463.5	460.7	458.6
62.5°	440.0	439.4	438.8	438.2	437.6	435.9	433.1	430.3	427.5	424.7	422.6
65°	386.4	385.2	384.0	382.9	381.7	380.0	377.6	375.3	373.0	370.7	368.8
67.5°	329.6	328.6	327.6	326.5	325.5	324.1	322.4	320.6	318.8	317.1	315.4
70°	295.3	293.9	292.5	291.1	289.7	288.3	286.9	285.5	284.1	282.7	281.1
72.5°	259.3	258.2	257.2	256.2	255.2	253.9	252.3	250.7	249.1	247.5	246.1
75°	204.2	203.2	202.3	201.4	200.5	199.6	198.9	198.2	197.5	196.9	195.7
77.5°	155.4	154.9	154.4	153.9	153.3	152.7	151.8	151.0	150.2	149.3	148.5
80°	123.6	122.9	122.2	121.5	120.8	120.2	119.7	119.3	118.8	118.3	118.1
82.5°	92.6	92.4	92.3	92.1	92.0	91.9	91.8	91.7	91.6	91.5	91.1
85°	54.4	54.0	53.5	53.1	52.6	52.4	52.4	52.4	52.4	52.4	51.9
87.5°	22.0	22.1	22.1	22.1	22.1	22.4	23.0	23.5	24.1	24.7	24.7
90°	1.3	4.2	7.1	9.9	12.8	16.1	19.9	23.6	27.4	31.1	32.3
92.5°	31.4	33.3	35.3	37.3	39.2	41.3	43.4	45.5	47.7	49.8	50.7
95°	76.5	78.5	80.6	82.6	84.6	86.8	89.1	91.4	93.7	96.0	97.1
97.5°	135.9	137.4	138.9	140.4	141.9	143.5	145.2	146.8	148.5	150.2	151.5
100°	176.4	178.1	179.8	181.6	183.3	184.9	186.3	187.8	189.2	190.7	191.5
102.5°	223.1	224.1	225.2	226.2	227.2	228.7	230.6	232.5	234.4	236.3	237.2
105°	291.8	292.4	293.0	293.5	294.1	295.7	298.3	300.9	303.5	306.1	306.1
107.5°	371.7	372.1	372.4	372.8	373.1	373.8	374.8	375.9	376.9	377.9	378.9
110°	421.5	422.1	422.7	423.2	423.8	424.4	425.0	425.6	426.1	426.7	427.9



TEST NUMBER: P332173

CATALOG NUMBER: S123DIW-S775D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	473.4	473.7	474.1	474.4	474.8	475.0	475.1	475.2	475.4	475.5	476.9
115°	551.2	552.1	552.9	553.8	554.7	554.8	554.2	553.7	553.1	552.5	552.8
117.5°	629.6	630.1	630.7	631.3	631.9	631.8	631.0	630.3	629.5	628.8	628.7
120°	678.3	680.0	681.8	683.5	685.2	685.4	683.9	682.5	681.1	679.6	679.3
122.5°	729.2	730.4	731.7	733.0	734.2	734.5	733.7	733.0	732.2	731.5	730.7
125°	806.7	807.6	808.4	809.3	810.2	810.3	809.7	809.2	808.6	808.0	806.9
127.5°	878.3	880.2	882.0	883.8	885.7	886.3	885.7	885.0	884.4	883.8	882.1
130°	926.0	928.3	930.7	933.0	935.3	936.0	935.1	934.3	933.4	932.5	931.4
132.5°	973.8	976.1	978.4	980.7	983.0	983.8	983.2	982.6	981.9	981.3	979.9
135°	1046.7	1048.4	1050.1	1051.8	1053.6	1054.3	1054.0	1053.7	1053.4	1053.1	1052.0
137.5°	1114.1	1115.5	1117.0	1118.4	1119.9	1121.0	1121.7	1122.5	1123.2	1124.0	1122.7
140°	1160.8	1162.2	1163.7	1165.1	1166.6	1167.4	1167.7	1168.0	1168.3	1168.6	1168.3
142.5°	1203.3	1204.8	1206.2	1207.7	1209.1	1210.1	1210.6	1211.1	1211.6	1212.2	1211.9
145°	1269.7	1270.3	1270.9	1271.5	1272.0	1272.8	1273.6	1274.5	1275.4	1276.2	1275.9
147.5°	1327.8	1328.9	1329.9	1331.0	1332.0	1332.9	1333.7	1334.5	1335.3	1336.1	1336.1
150°	1368.3	1368.9	1369.5	1370.0	1370.6	1371.2	1371.8	1372.3	1372.9	1373.5	1373.5
152.5°	1401.5	1402.3	1403.1	1403.9	1404.7	1405.3	1405.7	1406.0	1406.4	1406.7	1407.2
155°	1453.9	1453.9	1453.9	1453.9	1453.9	1454.1	1454.3	1454.6	1454.9	1455.2	1456.4
157.5°	1498.5	1498.2	1497.8	1497.5	1497.1	1497.1	1497.3	1497.5	1497.8	1498.0	1499.2
160°	1526.5	1526.0	1525.4	1524.8	1524.2	1523.9	1523.9	1523.9	1523.9	1523.9	1525.4
162.5°	1551.4	1550.6	1549.8	1549.0	1548.2	1547.9	1548.2	1548.4	1548.6	1548.8	1550.3
165°	1583.6	1582.7	1581.9	1581.0	1580.2	1579.7	1579.7	1579.7	1579.7	1579.7	1581.4
167.5°	1609.3	1608.1	1607.0	1605.8	1604.7	1604.2	1604.4	1604.7	1604.9	1605.1	1606.9
170°	1623.8	1622.7	1621.5	1620.4	1619.2	1618.6	1618.6	1618.6	1618.6	1618.6	1620.6
172.5°	1635.2	1634.1	1632.9	1631.8	1630.6	1630.0	1630.0	1630.0	1630.0	1630.0	1631.8
175°	1647.2	1646.0	1644.9	1643.7	1642.5	1642.0	1642.0	1642.0	1642.0	1642.0	1643.7
177.5°	1652.1	1651.2	1650.2	1649.3	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.3
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1



TEST NUMBER: P332173

CATALOG NUMBER: S123DIW-S775D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1213.1	1215.0	1216.8	1217.7	1217.5	1217.3	1217.1	1216.9
5°	1206.7	1209.0	1211.4	1212.3	1211.8	1211.4	1210.9	1210.4
7.5°	1193.9	1196.0	1198.1	1199.0	1198.7	1198.4	1198.1	1197.9
10°	1182.2	1184.2	1186.3	1187.2	1186.7	1186.2	1185.8	1185.3
12.5°	1169.3	1170.8	1172.4	1173.0	1172.7	1172.4	1172.2	1171.9
15°	1146.1	1147.9	1149.8	1150.0	1148.6	1147.2	1145.9	1144.5
17.5°	1116.7	1118.0	1119.3	1119.7	1119.2	1118.7	1118.2	1117.7
20°	1095.0	1095.9	1096.9	1097.0	1096.3	1095.6	1094.9	1094.2
22.5°	1072.0	1072.8	1073.5	1073.4	1072.6	1071.7	1070.8	1069.9
25°	1033.9	1034.2	1034.4	1034.2	1033.5	1032.8	1032.1	1031.4
27.5°	993.4	993.6	993.8	993.4	992.6	991.7	990.8	989.9
30°	965.4	965.4	965.4	964.6	963.0	961.3	959.7	958.1
32.5°	936.0	934.7	933.4	932.3	931.4	930.5	929.6	928.8
35°	888.3	886.9	885.5	884.2	883.0	881.9	880.7	879.5
37.5°	838.9	837.2	835.6	834.4	833.6	832.9	832.1	831.4
40°	806.7	804.9	803.0	801.6	800.7	799.7	798.8	797.9
42.5°	773.2	771.3	769.5	768.1	767.2	766.2	765.3	764.4
45°	723.2	720.4	717.6	715.6	714.5	713.3	712.1	711.0
47.5°	670.5	667.8	665.0	663.1	662.1	661.1	660.1	659.0
50°	635.7	633.1	630.6	628.6	627.2	625.8	624.4	623.0
52.5°	600.4	598.2	596.0	594.3	592.9	591.5	590.1	588.7
55°	546.7	544.1	541.6	539.7	538.5	537.4	536.2	535.1
57.5°	493.8	491.6	489.3	487.5	486.1	484.8	483.4	482.1
60°	456.5	454.4	452.3	450.7	449.5	448.4	447.2	446.1
62.5°	420.5	418.4	416.3	414.9	414.1	413.3	412.5	411.7
65°	366.9	365.1	363.2	361.9	361.2	360.5	359.8	359.1
67.5°	313.8	312.2	310.5	309.2	308.3	307.3	306.3	305.3
70°	279.5	277.8	276.2	274.8	273.6	272.5	271.3	270.1
72.5°	244.6	243.2	241.8	240.7	240.1	239.5	238.9	238.3
75°	194.5	193.4	192.2	191.3	190.6	189.9	189.2	188.5
77.5°	147.7	146.9	146.1	145.8	145.8	145.8	145.8	145.8
80°	117.9	117.6	117.4	117.3	117.3	117.3	117.3	117.3
82.5°	90.7	90.3	89.8	89.5	89.4	89.2	89.0	88.8
85°	51.4	51.0	50.5	50.3	50.3	50.3	50.3	50.3
87.5°	24.7	24.8	24.8	24.9	25.0	25.1	25.3	25.4
90°	33.4	34.6	35.7	36.6	37.2	37.8	38.3	38.9
92.5°	51.6	52.6	53.5	53.8	53.4	53.1	52.7	52.4
95°	98.3	99.4	100.6	101.2	101.2	101.2	101.2	101.2
97.5°	152.8	154.2	155.5	156.1	156.0	155.9	155.8	155.6
100°	192.4	193.2	194.1	194.8	195.4	196.0	196.6	197.1
102.5°	238.0	238.9	239.8	240.1	240.0	239.9	239.8	239.7
105°	306.1	306.1	306.1	306.4	307.0	307.5	308.1	308.7
107.5°	379.8	380.7	381.6	381.9	381.6	381.2	380.9	380.5
110°	429.0	430.2	431.3	431.6	431.0	430.5	429.9	429.3



TEST NUMBER: P332173

CATALOG NUMBER: S123DIW-S775D1320U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	478.2	479.6	481.0	481.6	481.5	481.4	481.3	481.2
115°	553.1	553.4	553.7	553.7	553.4	553.1	552.8	552.5
117.5°	628.7	628.6	628.5	628.1	627.3	626.5	625.7	624.9
120°	679.0	678.8	678.5	678.0	677.5	676.9	676.3	675.7
122.5°	730.0	729.2	728.5	727.7	726.9	726.1	725.3	724.5
125°	805.7	804.6	803.4	802.3	801.1	799.9	798.8	797.6
127.5°	880.5	878.9	877.3	875.8	874.5	873.2	871.9	870.5
130°	930.2	929.1	927.9	926.3	924.3	922.3	920.3	918.3
132.5°	978.5	977.1	975.8	974.3	972.7	971.2	969.6	968.1
135°	1050.8	1049.7	1048.5	1047.7	1047.1	1046.5	1045.9	1045.4
137.5°	1121.5	1120.3	1119.1	1118.0	1116.9	1115.8	1114.7	1113.6
140°	1168.0	1167.7	1167.4	1166.3	1164.3	1162.2	1160.2	1158.2
142.5°	1211.6	1211.3	1211.0	1210.1	1208.5	1207.0	1205.4	1203.9
145°	1275.6	1275.4	1275.1	1274.4	1273.2	1272.0	1270.9	1269.7
147.5°	1336.1	1336.1	1336.1	1335.3	1333.6	1331.8	1330.1	1328.4
150°	1373.5	1373.5	1373.5	1372.6	1370.9	1369.2	1367.4	1365.7
152.5°	1407.6	1408.1	1408.5	1408.0	1406.5	1405.0	1403.5	1402.0
155°	1457.5	1458.7	1459.8	1459.4	1457.4	1455.4	1453.3	1451.3
157.5°	1500.4	1501.6	1502.9	1502.6	1501.0	1499.4	1497.8	1496.2
160°	1526.8	1528.3	1529.7	1529.9	1528.7	1527.6	1526.4	1525.2
162.5°	1551.7	1553.2	1554.6	1554.4	1552.6	1550.7	1548.9	1547.0
165°	1583.2	1584.9	1586.6	1586.5	1584.5	1582.5	1580.4	1578.4
167.5°	1608.7	1610.5	1612.3	1612.3	1610.5	1608.7	1606.9	1605.1
170°	1622.7	1624.7	1626.7	1626.7	1624.7	1622.7	1620.6	1618.6
172.5°	1633.6	1635.4	1637.2	1637.1	1635.1	1633.0	1631.0	1629.0
175°	1645.4	1647.2	1648.9	1648.7	1646.7	1644.7	1642.7	1640.7
177.5°	1650.7	1652.1	1653.5	1653.4	1651.7	1650.1	1648.5	1646.9
180°	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1	1651.1

(END OF REPORT)