

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332179

Luminaire Tested: **S123DIW-S775D1535U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332179
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S775D1535U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8493.0 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332179

CATALOG NUMBER: S123DIW-S775D1535U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332179

CATALOG NUMBER: S123DIW-S775D1535U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	95	91	87	83	86	82	79	76	67	64	62	52	51	50	39	38	37	31
2	86	79	73	68	78	72	67	62	58	55	52	46	43	41	34	33	31	26
3	79	69	62	57	71	63	57	52	51	47	43	41	38	35	31	29	27	22
4	72	61	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	25	22	20	17
6	61	49	41	35	55	45	38	33	37	31	28	29	25	23	22	20	18	14
7	56	44	36	31	51	40	33	29	33	28	24	27	23	20	20	18	16	13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	19	16	14	11
9	48	36	29	24	44	33	27	22	28	23	19	22	19	16	17	15	13	10
10	45	33	26	21	41	31	24	20	25	20	17	21	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13108	13108	13108
5°	13169	12988	13078
10°	13081	12875	12955
15°	12929	12730	12754
20°	12749	12521	12534
25°	12511	12275	12250
30°	12246	11999	11908
35°	11971	11709	11557
40°	11682	11387	11212
45°	11365	11094	10823
50°	11047	10731	10433
55°	10631	10355	10042
60°	10211	9918	9604
65°	9841	9442	9146
70°	9294	8897	8500
75°	8492	8189	7839
80°	7662	7333	7271
85°	6719	6472	6212



TEST NUMBER: P332179

CATALOG NUMBER: S123DIW-S775D1535U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.7	1.4
10°-20°	323.9	3.8
20°-30°	478.4	5.6
30°-40°	558.9	6.6
40°-50°	561.9	6.6
50°-60°	493.6	5.8
60°-70°	367.7	4.3
70°-80°	209.5	2.5
80°-90°	65.8	0.8
90°-100°	125.1	1.5
100°-110°	374.3	4.4
110°-120°	636.6	7.5
120°-130°	837.4	9.9
130°-140°	941.2	11.1
140°-150°	925.2	10.9
150°-160°	778.9	9.2
160°-170°	518.5	6.1
170°-180°	181.6	2.1
0°-30°	917.1	10.8
0°-40°	1475.9	17.4
0°-60°	2531.4	29.8
0°-90°	3174.4	37.4
90°-120°	1136.0	13.4
90°-150°	3839.7	45.2
90°-180°	5319.0	62.6
0°-180°	8493.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1219	1213	1202	1212	1210	115
15°	1160	1155	1142	1150	1144	327
25°	1053	1047	1034	1034	1031	485
35°	911	904	891	885	880	570
45°	747	742	729	717	711	576
55°	566	565	552	541	535	507
65°	386	381	371	363	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	60
90°	2	17	36	42	45	8
95°	89	100	112	117	118	100
105°	339	343	356	356	359	363
115°	641	645	642	644	642	634
125°	938	942	940	933	927	836
135°	1217	1225	1224	1219	1215	937
145°	1476	1479	1484	1482	1476	922
155°	1690	1690	1692	1697	1687	778
165°	1841	1837	1837	1845	1835	519
175°	1915	1909	1909	1917	1908	182
180°	1920	1920	1920	1920	1920	



TEST NUMBER: P332179

CATALOG NUMBER: S123DIW-S775D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1221.9	1221.2	1220.5	1219.7	1219.0	1217.6	1215.5	1213.5	1211.4	1209.4	1211.2
5°	1218.8	1217.6	1216.5	1215.3	1214.1	1212.3	1209.7	1207.2	1204.6	1202.0	1204.4
7.5°	1206.9	1205.7	1204.5	1203.4	1202.2	1200.3	1197.6	1195.0	1192.3	1189.7	1191.8
10°	1196.8	1195.6	1194.5	1193.3	1192.2	1190.1	1187.0	1184.0	1181.0	1178.0	1180.1
12.5°	1183.4	1182.4	1181.5	1180.5	1179.5	1177.6	1174.8	1171.9	1169.1	1166.2	1167.8
15°	1160.2	1159.2	1158.3	1157.4	1156.4	1154.5	1151.4	1148.4	1145.4	1142.4	1144.2
17.5°	1133.1	1131.9	1130.7	1129.5	1128.3	1126.2	1123.2	1120.1	1117.1	1114.1	1115.4
20°	1113.0	1111.6	1110.3	1108.9	1107.5	1105.2	1102.2	1099.2	1096.2	1093.1	1094.1
22.5°	1090.4	1089.0	1087.6	1086.2	1084.8	1082.6	1079.6	1076.6	1073.6	1070.5	1071.3
25°	1053.4	1052.0	1050.6	1049.2	1047.8	1045.6	1042.5	1039.5	1036.5	1033.5	1033.7
27.5°	1013.8	1012.4	1011.1	1009.7	1008.4	1006.1	1002.8	999.6	996.3	993.0	993.2
30°	985.3	984.1	983.0	981.8	980.6	978.4	975.2	971.9	968.7	965.4	965.4
32.5°	956.8	955.3	953.7	952.2	950.7	948.7	946.1	943.6	941.1	938.6	937.3
35°	911.0	909.6	908.2	906.8	905.4	903.2	900.1	897.1	894.1	891.1	889.7
37.5°	864.0	862.3	860.5	858.7	857.0	854.6	851.5	848.4	845.3	842.3	840.6
40°	831.4	830.0	828.6	827.2	825.8	823.5	820.2	817.0	813.7	810.4	808.6
42.5°	798.7	797.1	795.5	794.0	792.4	790.0	786.7	783.4	780.2	776.9	775.1
45°	746.6	745.6	744.7	743.8	742.8	740.9	737.8	734.8	731.8	728.8	726.0
47.5°	694.8	693.5	692.1	690.8	689.4	687.3	684.5	681.7	678.8	676.0	673.2
50°	659.7	658.5	657.3	656.2	655.0	652.9	649.9	646.9	643.8	640.8	638.3
52.5°	622.8	622.0	621.2	620.4	619.6	617.6	614.4	611.2	608.0	604.8	602.6
55°	566.5	566.2	566.0	565.8	565.5	563.9	560.9	557.9	554.8	551.8	549.3
57.5°	512.9	512.1	511.3	510.5	509.7	508.1	505.7	503.2	500.8	498.4	496.1
60°	474.3	474.1	473.9	473.6	473.4	471.9	469.1	466.3	463.5	460.7	458.6
62.5°	440.0	439.4	438.8	438.2	437.6	435.9	433.1	430.3	427.5	424.7	422.6
65°	386.4	385.2	384.0	382.9	381.7	380.0	377.6	375.3	373.0	370.7	368.8
67.5°	329.6	328.6	327.6	326.5	325.5	324.1	322.4	320.6	318.8	317.1	315.4
70°	295.3	293.9	292.5	291.1	289.7	288.3	286.9	285.5	284.1	282.7	281.1
72.5°	259.3	258.2	257.2	256.2	255.2	253.9	252.3	250.7	249.1	247.5	246.1
75°	204.2	203.2	202.3	201.4	200.5	199.6	198.9	198.2	197.5	196.9	195.7
77.5°	155.4	154.9	154.4	153.9	153.3	152.7	151.8	151.0	150.2	149.3	148.5
80°	123.6	122.9	122.2	121.5	120.8	120.2	119.7	119.3	118.8	118.3	118.1
82.5°	92.6	92.4	92.3	92.1	92.0	91.9	91.8	91.7	91.6	91.5	91.1
85°	54.4	54.0	53.5	53.1	52.6	52.4	52.4	52.4	52.4	52.4	51.9
87.5°	22.1	22.2	22.3	22.4	22.5	22.9	23.6	24.3	25.0	25.7	25.7
90°	1.5	4.9	8.2	11.6	14.9	18.8	23.1	27.5	31.8	36.2	37.5
92.5°	36.5	38.8	41.0	43.3	45.6	48.0	50.5	52.9	55.4	57.9	59.0
95°	89.0	91.3	93.7	96.0	98.4	100.9	103.5	106.2	108.9	111.6	112.9
97.5°	158.0	159.8	161.5	163.3	165.0	166.8	168.8	170.7	172.7	174.6	176.2
100°	205.1	207.1	209.1	211.1	213.1	215.0	216.6	218.3	220.0	221.7	222.7
102.5°	259.4	260.6	261.8	263.0	264.2	265.9	268.1	270.3	272.5	274.7	275.8
105°	339.3	340.0	340.6	341.3	342.0	343.8	346.8	349.8	352.9	355.9	355.9
107.5°	432.2	432.6	433.0	433.4	433.8	434.6	435.8	437.0	438.2	439.4	440.5
110°	490.1	490.8	491.4	492.1	492.8	493.4	494.1	494.8	495.4	496.1	497.5



TEST NUMBER: P332179

CATALOG NUMBER: S123DIW-S775D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	550.4	550.8	551.2	551.6	552.0	552.3	552.4	552.5	552.7	552.8	554.4
115°	640.9	641.9	642.9	643.9	644.9	645.1	644.4	643.7	643.1	642.4	642.7
117.5°	732.0	732.6	733.3	734.0	734.6	734.5	733.7	732.8	731.9	731.1	731.0
120°	788.7	790.7	792.7	794.7	796.7	796.9	795.2	793.5	791.8	790.2	789.8
122.5°	847.8	849.2	850.7	852.2	853.7	854.0	853.1	852.2	851.4	850.5	849.6
125°	937.9	938.9	940.0	941.0	942.0	942.1	941.5	940.8	940.1	939.5	938.1
127.5°	1021.2	1023.3	1025.5	1027.6	1029.8	1030.5	1029.7	1029.0	1028.3	1027.5	1025.6
130°	1076.7	1079.4	1082.0	1084.7	1087.4	1088.2	1087.2	1086.2	1085.2	1084.2	1082.9
132.5°	1132.2	1134.8	1137.5	1140.2	1142.9	1143.9	1143.1	1142.4	1141.6	1140.9	1139.3
135°	1216.9	1218.9	1220.9	1222.9	1225.0	1225.8	1225.5	1225.1	1224.8	1224.5	1223.1
137.5°	1295.3	1297.0	1298.7	1300.4	1302.0	1303.3	1304.2	1305.0	1305.9	1306.8	1305.4
140°	1349.6	1351.3	1353.0	1354.6	1356.3	1357.3	1357.7	1358.0	1358.3	1358.7	1358.3
142.5°	1399.1	1400.7	1402.4	1404.1	1405.8	1406.9	1407.5	1408.1	1408.7	1409.3	1409.0
145°	1476.3	1477.0	1477.6	1478.3	1479.0	1479.8	1480.8	1481.8	1482.8	1483.8	1483.5
147.5°	1543.8	1545.0	1546.2	1547.5	1548.7	1549.7	1550.7	1551.6	1552.5	1553.5	1553.5
150°	1590.9	1591.6	1592.2	1592.9	1593.6	1594.2	1594.9	1595.6	1596.2	1596.9	1596.9
152.5°	1629.5	1630.4	1631.4	1632.3	1633.2	1633.9	1634.3	1634.7	1635.1	1635.5	1636.1
155°	1690.4	1690.4	1690.4	1690.4	1690.4	1690.6	1690.9	1691.2	1691.6	1691.9	1693.3
157.5°	1742.3	1741.9	1741.5	1741.1	1740.7	1740.6	1740.9	1741.1	1741.4	1741.7	1743.1
160°	1774.9	1774.2	1773.5	1772.8	1772.2	1771.8	1771.8	1771.8	1771.8	1771.8	1773.5
162.5°	1803.8	1802.9	1801.9	1801.0	1800.1	1799.7	1800.0	1800.3	1800.5	1800.8	1802.5
165°	1841.2	1840.2	1839.2	1838.2	1837.2	1836.7	1836.7	1836.7	1836.7	1836.7	1838.7
167.5°	1871.1	1869.7	1868.4	1867.0	1865.7	1865.2	1865.4	1865.7	1866.0	1866.2	1868.3
170°	1887.9	1886.6	1885.3	1883.9	1882.6	1881.9	1881.9	1881.9	1881.9	1881.9	1884.3
172.5°	1901.2	1899.9	1898.5	1897.2	1895.9	1895.2	1895.2	1895.2	1895.2	1895.2	1897.3
175°	1915.1	1913.8	1912.4	1911.1	1909.7	1909.1	1909.1	1909.1	1909.1	1909.1	1911.1
177.5°	1920.8	1919.8	1918.7	1917.6	1916.5	1916.0	1916.0	1916.0	1916.0	1916.0	1917.6
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6



TEST NUMBER: P332179

CATALOG NUMBER: S123DIW-S775D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1213.1	1215.0	1216.8	1217.7	1217.5	1217.3	1217.1	1216.9
5°	1206.7	1209.0	1211.4	1212.3	1211.8	1211.4	1210.9	1210.4
7.5°	1193.9	1196.0	1198.1	1199.0	1198.7	1198.4	1198.1	1197.9
10°	1182.2	1184.2	1186.3	1187.2	1186.7	1186.2	1185.8	1185.3
12.5°	1169.3	1170.8	1172.4	1173.0	1172.7	1172.4	1172.2	1171.9
15°	1146.1	1147.9	1149.8	1150.0	1148.6	1147.2	1145.9	1144.5
17.5°	1116.7	1118.0	1119.3	1119.7	1119.2	1118.7	1118.2	1117.7
20°	1095.0	1095.9	1096.9	1097.0	1096.3	1095.6	1094.9	1094.2
22.5°	1072.0	1072.8	1073.5	1073.4	1072.6	1071.7	1070.8	1069.9
25°	1033.9	1034.2	1034.4	1034.2	1033.5	1032.8	1032.1	1031.4
27.5°	993.4	993.6	993.8	993.4	992.6	991.7	990.8	989.9
30°	965.4	965.4	965.4	964.6	963.0	961.3	959.7	958.1
32.5°	936.0	934.7	933.4	932.3	931.4	930.5	929.6	928.8
35°	888.3	886.9	885.5	884.2	883.0	881.9	880.7	879.5
37.5°	838.9	837.2	835.6	834.4	833.6	832.9	832.1	831.4
40°	806.7	804.9	803.0	801.6	800.7	799.7	798.8	797.9
42.5°	773.2	771.3	769.5	768.1	767.2	766.2	765.3	764.4
45°	723.2	720.4	717.6	715.6	714.5	713.3	712.1	711.0
47.5°	670.5	667.8	665.0	663.1	662.1	661.1	660.1	659.0
50°	635.7	633.1	630.6	628.6	627.2	625.8	624.4	623.0
52.5°	600.4	598.2	596.0	594.3	592.9	591.5	590.1	588.7
55°	546.7	544.1	541.6	539.7	538.5	537.4	536.2	535.1
57.5°	493.8	491.6	489.3	487.5	486.1	484.8	483.4	482.1
60°	456.5	454.4	452.3	450.7	449.5	448.4	447.2	446.1
62.5°	420.5	418.4	416.3	414.9	414.1	413.3	412.5	411.7
65°	366.9	365.1	363.2	361.9	361.2	360.5	359.8	359.1
67.5°	313.8	312.2	310.5	309.2	308.3	307.3	306.3	305.3
70°	279.5	277.8	276.2	274.8	273.6	272.5	271.3	270.1
72.5°	244.6	243.2	241.8	240.7	240.1	239.5	238.9	238.3
75°	194.5	193.4	192.2	191.3	190.6	189.9	189.2	188.5
77.5°	147.7	146.9	146.1	145.8	145.8	145.8	145.8	145.8
80°	117.9	117.6	117.4	117.3	117.3	117.3	117.3	117.3
82.5°	90.7	90.3	89.8	89.5	89.4	89.2	89.0	88.8
85°	51.4	51.0	50.5	50.3	50.3	50.3	50.3	50.3
87.5°	25.8	25.9	26.0	26.1	26.2	26.4	26.5	26.6
90°	38.9	40.2	41.6	42.6	43.2	43.9	44.6	45.2
92.5°	60.0	61.1	62.2	62.5	62.1	61.7	61.3	60.9
95°	114.3	115.6	116.9	117.6	117.6	117.6	117.6	117.6
97.5°	177.7	179.2	180.8	181.5	181.4	181.2	181.1	181.0
100°	223.7	224.7	225.7	226.5	227.2	227.9	228.5	229.2
102.5°	276.8	277.8	278.8	279.2	279.1	278.9	278.8	278.7
105°	355.9	355.9	355.9	356.2	356.9	357.6	358.2	358.9
107.5°	441.6	442.6	443.7	444.0	443.6	443.2	442.8	442.4
110°	498.8	500.1	501.5	501.8	501.1	500.5	499.8	499.1



TEST NUMBER: P332179

CATALOG NUMBER: S123DIW-S775D1535U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	556.0	557.6	559.2	560.0	559.9	559.7	559.6	559.4
115°	643.1	643.4	643.7	643.7	643.4	643.1	642.7	642.4
117.5°	730.9	730.9	730.8	730.3	729.3	728.4	727.5	726.5
120°	789.5	789.2	788.8	788.3	787.7	787.0	786.3	785.6
122.5°	848.7	847.9	847.0	846.1	845.2	844.2	843.3	842.3
125°	936.8	935.4	934.1	932.7	931.4	930.1	928.7	927.4
127.5°	1023.8	1021.9	1020.0	1018.3	1016.8	1015.2	1013.7	1012.1
130°	1081.5	1080.2	1078.9	1077.0	1074.7	1072.3	1070.0	1067.6
132.5°	1137.7	1136.1	1134.5	1132.8	1131.0	1129.2	1127.3	1125.5
135°	1221.8	1220.4	1219.1	1218.1	1217.4	1216.7	1216.1	1215.4
137.5°	1304.0	1302.6	1301.2	1299.8	1298.5	1297.3	1296.0	1294.7
140°	1358.0	1357.7	1357.3	1356.0	1353.6	1351.3	1348.9	1346.6
142.5°	1408.7	1408.3	1408.0	1406.9	1405.1	1403.3	1401.5	1399.7
145°	1483.1	1482.8	1482.5	1481.6	1480.3	1479.0	1477.6	1476.3
147.5°	1553.5	1553.5	1553.5	1552.5	1550.5	1548.5	1546.4	1544.4
150°	1596.9	1596.9	1596.9	1595.9	1593.9	1591.9	1589.9	1587.9
152.5°	1636.6	1637.1	1637.7	1637.1	1635.3	1633.6	1631.8	1630.1
155°	1694.6	1695.9	1697.3	1696.8	1694.4	1692.1	1689.7	1687.4
157.5°	1744.5	1745.9	1747.3	1747.1	1745.2	1743.3	1741.4	1739.6
160°	1775.2	1776.9	1778.5	1778.7	1777.4	1776.0	1774.7	1773.3
162.5°	1804.1	1805.8	1807.5	1807.3	1805.1	1803.0	1800.8	1798.7
165°	1840.7	1842.7	1844.7	1844.6	1842.2	1839.9	1837.5	1835.2
167.5°	1870.4	1872.5	1874.5	1874.5	1872.5	1870.4	1868.3	1866.2
170°	1886.6	1889.0	1891.3	1891.3	1889.0	1886.6	1884.3	1881.9
172.5°	1899.3	1901.4	1903.5	1903.4	1901.0	1898.7	1896.3	1894.0
175°	1913.1	1915.1	1917.1	1916.9	1914.6	1912.2	1909.9	1907.6
177.5°	1919.2	1920.8	1922.4	1922.3	1920.4	1918.5	1916.7	1914.8
180°	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6	1919.6

(END OF REPORT)