

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332100-927

Luminaire Tested: **S123DIW-S340D755U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332100-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123DIW-S340D755U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3512.0 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332100-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332100-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	39	39	39	32
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	49	43	40	38	31	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4621	4621	4621
5°	4643	4578	4611
10°	4611	4539	4568
15°	4558	4488	4496
20°	4495	4415	4418
25°	4410	4327	4318
30°	4318	4230	4197
35°	4221	4127	4075
40°	4118	4014	3953
45°	4007	3911	3815
50°	3893	3783	3677
55°	3748	3652	3539
60°	3599	3496	3384
65°	3469	3326	3224
70°	3276	3138	2996
75°	2994	2886	2766
80°	2703	2585	2566
85°	2371	2285	2186



TEST NUMBER: P332100-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.4	1.2
10°-20°	114.2	3.3
20°-30°	168.7	4.8
30°-40°	197.0	5.6
40°-50°	198.1	5.6
50°-60°	174.0	5.0
60°-70°	129.6	3.7
70°-80°	73.8	2.1
80°-90°	23.4	0.7
90°-100°	28.5	0.8
100°-110°	136.0	3.9
110°-120°	326.6	9.3
120°-130°	415.9	11.8
130°-140°	444.3	12.7
140°-150°	415.5	11.8
150°-160°	335.2	9.5
160°-170°	216.3	6.2
170°-180°	74.5	2.1
0°-30°	323.3	9.2
0°-40°	520.3	14.8
0°-60°	892.4	25.4
0°-90°	1119.2	31.9
90°-120°	491.1	14.0
90°-150°	1766.8	50.3
90°-180°	2393.0	68.1
0°-180°	3512.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	429	429	429	429	429	
5°	430	428	424	427	427	41
15°	409	407	403	405	404	115
25°	371	369	364	365	364	171
35°	321	319	314	312	310	201
45°	263	262	257	253	251	203
55°	200	199	195	191	189	179
65°	136	134	131	128	127	134
75°	72	70	69	68	66	77
85°	19	18	18	18	18	21
90°	1	7	14	16	18	3
95°	36	13	18	22	22	44
105°	174	177	128	30	26	184
115°	326	329	335	340	343	322
125°	459	464	466	468	469	410
135°	572	575	578	579	578	440
145°	660	664	665	666	666	413
155°	727	726	726	729	726	335
165°	767	765	764	768	765	216
175°	785	782	782	786	782	75
180°	785	785	785	785	785	



TEST NUMBER: P332100-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	430.8	430.5	430.2	430.0	429.7	429.2	428.5	427.8	427.1	426.4	427.0
5°	429.7	429.2	428.8	428.4	428.0	427.4	426.4	425.6	424.6	423.7	424.5
7.5°	425.5	425.0	424.6	424.2	423.8	423.1	422.2	421.3	420.3	419.4	420.1
10°	421.9	421.5	421.0	420.6	420.3	419.5	418.4	417.4	416.3	415.3	416.0
12.5°	417.2	416.8	416.5	416.1	415.8	415.1	414.2	413.1	412.1	411.1	411.7
15°	409.0	408.7	408.3	408.0	407.7	406.9	405.9	404.8	403.8	402.7	403.4
17.5°	399.4	399.0	398.6	398.2	397.8	397.0	395.9	394.9	393.8	392.8	393.2
20°	392.4	391.9	391.4	390.9	390.4	389.6	388.6	387.5	386.4	385.4	385.7
22.5°	384.4	383.9	383.4	382.9	382.5	381.7	380.6	379.5	378.4	377.4	377.6
25°	371.3	370.8	370.3	369.9	369.4	368.6	367.5	366.5	365.4	364.3	364.4
27.5°	357.4	356.9	356.4	355.9	355.5	354.7	353.6	352.4	351.3	350.1	350.1
30°	347.4	346.9	346.5	346.1	345.7	344.9	343.8	342.6	341.5	340.3	340.3
32.5°	337.3	336.8	336.2	335.6	335.2	334.4	333.5	332.6	331.8	330.9	330.4
35°	321.2	320.7	320.1	319.6	319.2	318.4	317.3	316.2	315.2	314.1	313.6
37.5°	304.6	304.0	303.3	302.7	302.1	301.3	300.2	299.0	298.0	296.9	296.4
40°	293.1	292.6	292.1	291.6	291.1	290.3	289.1	288.0	286.8	285.7	285.0
42.5°	281.5	281.0	280.4	279.9	279.3	278.5	277.3	276.2	275.0	273.9	273.2
45°	263.2	262.8	262.5	262.2	261.9	261.2	260.1	259.0	257.9	256.9	256.0
47.5°	244.9	244.5	244.0	243.5	243.0	242.3	241.3	240.3	239.3	238.3	237.3
50°	232.5	232.1	231.7	231.3	230.9	230.1	229.1	228.1	227.0	225.9	225.0
52.5°	219.5	219.3	219.0	218.7	218.4	217.7	216.6	215.5	214.4	213.2	212.5
55°	199.7	199.6	199.6	199.5	199.4	198.8	197.7	196.6	195.6	194.6	193.6
57.5°	180.8	180.5	180.2	180.0	179.7	179.1	178.2	177.4	176.6	175.7	174.9
60°	167.2	167.2	167.1	167.0	166.9	166.4	165.3	164.4	163.4	162.4	161.7
62.5°	155.1	154.9	154.7	154.5	154.2	153.7	152.7	151.7	150.7	149.7	149.0
65°	136.2	135.8	135.4	135.0	134.6	134.0	133.2	132.3	131.5	130.6	130.0
67.5°	116.2	115.8	115.5	115.1	114.8	114.2	113.7	113.0	112.4	111.8	111.2
70°	104.1	103.6	103.1	102.6	102.1	101.6	101.2	100.6	100.1	99.7	99.1
72.5°	91.4	91.0	90.7	90.3	89.9	89.5	89.0	88.4	87.9	87.3	86.7
75°	72.0	71.6	71.3	71.0	70.7	70.3	70.1	69.9	69.6	69.4	69.0
77.5°	54.7	54.6	54.4	54.3	54.0	53.8	53.6	53.2	52.9	52.6	52.4
80°	43.6	43.3	43.1	42.9	42.5	42.4	42.2	42.1	41.9	41.7	41.6
82.5°	32.6	32.6	32.6	32.5	32.4	32.4	32.3	32.3	32.3	32.2	32.1
85°	19.2	19.0	18.9	18.7	18.5	18.5	18.5	18.5	18.5	18.5	18.3
87.5°	7.8	7.8	7.9	8.0	8.1	8.2	8.5	8.7	9.0	9.3	9.3
90°	0.6	1.9	3.2	4.4	5.8	7.3	9.0	10.6	12.3	14.0	14.5
92.5°	10.9	10.5	10.1	9.7	9.4	9.8	11.1	12.4	13.6	14.9	15.8
95°	35.6	30.3	25.0	19.6	14.3	12.4	13.8	15.2	16.6	18.1	19.0
97.5°	71.5	69.1	66.7	64.3	61.9	56.1	46.7	37.4	28.1	18.8	19.8
100°	98.5	101.1	103.7	106.3	108.8	100.1	79.9	59.7	39.5	19.3	20.3
102.5°	129.3	131.2	133.0	134.9	136.7	126.7	104.6	82.5	60.4	38.3	35.2
105°	173.7	175.2	176.6	178.0	179.4	174.3	162.6	151.0	139.3	127.7	104.7
107.5°	220.5	221.7	222.8	224.0	225.1	226.6	228.5	230.3	232.2	234.0	217.1
110°	251.8	252.9	253.9	254.9	256.0	257.2	258.6	260.1	261.5	262.9	258.6



TEST NUMBER: P332100-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	281.7	282.6	283.5	284.5	285.4	286.6	288.0	289.5	290.9	292.3	292.4
115°	325.8	326.6	327.4	328.2	329.0	329.9	331.1	332.2	333.4	334.6	335.9
117.5°	368.7	369.6	370.6	371.5	372.5	373.3	373.8	374.5	375.0	375.7	376.7
120°	395.2	396.4	397.6	398.7	399.9	400.7	401.1	401.5	401.9	402.2	403.3
122.5°	422.3	423.3	424.2	425.2	426.1	426.8	427.3	427.9	428.3	428.8	429.5
125°	459.4	460.4	461.4	462.5	463.5	464.3	464.8	465.3	465.8	466.4	466.6
127.5°	495.3	496.3	497.3	498.4	499.4	500.3	500.9	501.5	502.1	502.7	503.1
130°	517.6	518.7	519.8	520.8	521.8	522.6	523.1	523.6	524.1	524.7	525.1
132.5°	539.1	540.1	541.1	542.2	543.3	544.0	544.4	544.8	545.2	545.7	546.1
135°	571.9	572.7	573.4	574.2	575.0	575.6	576.2	576.6	577.2	577.7	578.1
137.5°	599.8	600.8	601.8	602.8	603.8	604.4	604.7	605.0	605.3	605.5	606.2
140°	618.5	619.2	620.0	620.8	621.6	622.2	622.6	623.0	623.4	623.8	624.2
142.5°	635.7	636.5	637.3	638.1	638.9	639.4	639.8	640.2	640.6	641.0	641.4
145°	659.9	660.8	661.7	662.6	663.5	664.1	664.3	664.6	664.9	665.1	665.4
147.5°	682.6	683.2	683.8	684.4	685.0	685.4	685.7	686.0	686.2	686.4	686.7
150°	696.6	697.0	697.4	697.8	698.2	698.5	698.8	699.0	699.3	699.5	699.8
152.5°	709.2	709.4	709.6	709.7	710.0	710.1	710.3	710.4	710.6	710.7	711.1
155°	726.9	726.7	726.4	726.1	725.9	725.8	726.0	726.1	726.2	726.4	727.0
157.5°	740.7	740.7	740.6	740.6	740.6	740.5	740.4	740.2	740.1	740.0	740.8
160°	749.1	748.9	748.8	748.7	748.5	748.5	748.3	748.1	748.1	747.9	748.7
162.5°	757.0	756.7	756.3	756.0	755.7	755.4	755.3	755.2	755.0	754.9	755.8
165°	766.6	766.2	765.8	765.4	765.0	764.8	764.6	764.5	764.4	764.2	765.2
167.5°	774.0	773.5	773.0	772.5	772.0	771.7	771.7	771.7	771.7	771.7	772.7
170°	778.2	777.7	777.2	776.7	776.2	775.9	775.9	775.9	775.9	775.9	776.9
172.5°	781.0	780.4	779.7	779.2	778.6	778.2	778.4	778.5	778.6	778.7	779.7
175°	784.7	783.9	783.3	782.7	782.0	781.8	781.9	782.0	782.2	782.3	783.2
177.5°	785.5	785.1	784.5	784.0	783.5	783.3	783.4	783.5	783.6	783.7	784.5
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7



TEST NUMBER: P332100-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	429.3	429.3	429.3	429.3	429.3	429.3	429.3	429.3
2.5°	427.6	428.3	429.0	429.3	429.2	429.1	429.0	429.0
5°	425.4	426.2	427.1	427.4	427.2	427.1	426.8	426.7
7.5°	420.9	421.6	422.3	422.6	422.6	422.5	422.4	422.2
10°	416.8	417.5	418.2	418.5	418.4	418.2	418.0	417.9
12.5°	412.2	412.7	413.3	413.5	413.4	413.3	413.2	413.1
15°	404.0	404.6	405.4	405.4	404.9	404.4	403.9	403.5
17.5°	393.6	394.1	394.6	394.7	394.5	394.3	394.2	394.0
20°	386.0	386.3	386.7	386.7	386.4	386.2	386.0	385.7
22.5°	377.9	378.2	378.4	378.4	378.1	377.8	377.5	377.2
25°	364.5	364.6	364.6	364.6	364.3	364.1	363.8	363.6
27.5°	350.2	350.3	350.3	350.2	349.9	349.6	349.3	349.0
30°	340.3	340.3	340.3	340.0	339.5	338.9	338.3	337.7
32.5°	329.9	329.5	329.1	328.7	328.4	328.0	327.7	327.4
35°	313.1	312.7	312.1	311.7	311.3	310.9	310.5	310.1
37.5°	295.7	295.2	294.5	294.1	293.9	293.6	293.3	293.1
40°	284.4	283.8	283.0	282.6	282.3	281.9	281.6	281.3
42.5°	272.6	271.9	271.2	270.8	270.5	270.1	269.8	269.4
45°	254.9	254.0	252.9	252.3	251.8	251.4	251.0	250.6
47.5°	236.4	235.4	234.4	233.8	233.4	233.1	232.7	232.3
50°	224.1	223.2	222.3	221.6	221.1	220.6	220.1	219.6
52.5°	211.7	210.9	210.1	209.5	209.0	208.5	208.0	207.6
55°	192.7	191.8	190.9	190.3	189.9	189.4	189.0	188.6
57.5°	174.1	173.3	172.5	171.8	171.3	170.9	170.4	169.9
60°	161.0	160.2	159.5	158.9	158.4	158.0	157.6	157.2
62.5°	148.2	147.5	146.8	146.2	146.0	145.7	145.4	145.1
65°	129.4	128.7	128.0	127.6	127.4	127.1	126.8	126.6
67.5°	110.6	110.0	109.5	109.0	108.7	108.3	108.0	107.7
70°	98.5	97.9	97.4	96.9	96.5	96.1	95.6	95.2
72.5°	86.3	85.7	85.2	84.8	84.7	84.4	84.2	84.0
75°	68.6	68.1	67.7	67.4	67.2	66.9	66.7	66.5
77.5°	52.0	51.8	51.5	51.4	51.4	51.4	51.4	51.4
80°	41.5	41.4	41.4	41.4	41.4	41.4	41.4	41.4
82.5°	32.0	31.8	31.7	31.5	31.5	31.4	31.4	31.3
85°	18.1	18.0	17.8	17.7	17.7	17.7	17.7	17.7
87.5°	9.3	9.4	9.4	9.5	9.5	9.6	9.7	9.7
90°	15.1	15.5	16.1	16.5	16.7	17.0	17.2	17.5
92.5°	16.6	17.4	18.2	18.7	18.9	19.0	19.2	19.3
95°	19.9	20.8	21.7	22.2	22.2	22.2	22.2	22.2
97.5°	20.8	21.9	22.9	23.5	23.6	23.8	23.9	24.0
100°	21.3	22.3	23.4	24.0	24.1	24.2	24.3	24.5
102.5°	31.9	28.8	25.5	24.0	24.2	24.5	24.7	25.0
105°	81.8	58.9	36.0	24.6	24.9	25.1	25.4	25.7
107.5°	200.3	183.5	166.8	149.7	132.4	115.1	97.8	80.6
110°	254.4	250.1	245.8	234.4	215.9	197.3	178.8	160.3



TEST NUMBER: P332100-927

CATALOG NUMBER: S123DIW-S340D755U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	292.5	292.6	292.6	290.7	286.8	282.9	278.9	275.0
115°	337.2	338.5	339.8	340.7	341.2	341.7	342.2	342.8
117.5°	377.7	378.7	379.8	380.3	380.5	380.6	380.6	380.8
120°	404.3	405.4	406.4	406.9	406.9	406.9	406.9	406.9
122.5°	430.2	430.9	431.7	432.1	432.2	432.3	432.5	432.5
125°	466.8	467.1	467.4	467.6	467.9	468.2	468.4	468.7
127.5°	503.6	504.0	504.4	504.5	504.2	503.9	503.7	503.4
130°	525.7	526.2	526.7	526.9	526.6	526.3	526.1	525.8
132.5°	546.7	547.2	547.7	547.8	547.4	547.1	546.7	546.3
135°	578.5	578.8	579.2	579.2	578.8	578.5	578.1	577.7
137.5°	606.8	607.4	608.1	608.2	608.0	607.7	607.4	607.2
140°	624.8	625.3	625.8	626.0	625.7	625.4	625.2	624.9
142.5°	641.8	642.2	642.6	642.7	642.3	642.0	641.6	641.2
145°	665.7	665.9	666.1	666.3	666.3	666.3	666.3	666.3
147.5°	687.0	687.2	687.5	687.3	686.7	686.1	685.6	684.9
150°	700.1	700.3	700.5	700.5	700.1	699.7	699.3	698.9
152.5°	711.6	712.1	712.6	712.5	711.9	711.3	710.7	710.1
155°	727.6	728.3	729.0	728.9	728.1	727.3	726.5	725.7
157.5°	741.6	742.3	743.1	743.0	742.0	740.9	740.0	738.9
160°	749.5	750.3	751.0	751.0	750.0	749.2	748.2	747.3
162.5°	756.7	757.6	758.4	758.4	757.6	756.9	756.1	755.3
165°	766.3	767.3	768.3	768.4	767.5	766.6	765.7	764.8
167.5°	773.7	774.8	775.9	775.9	774.8	773.7	772.7	771.7
170°	777.9	779.0	780.1	780.1	779.0	777.9	776.9	775.9
172.5°	780.8	781.8	782.8	782.8	781.6	780.5	779.3	778.2
175°	784.1	785.1	785.9	785.8	784.8	783.8	782.8	781.7
177.5°	785.4	786.2	787.0	786.9	785.8	784.8	783.8	782.8
180°	784.7	784.7	784.7	784.7	784.7	784.7	784.7	784.7

(END OF REPORT)