

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332155

Luminaire Tested: **S123DIW-S775D460U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332155  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123DIW-S775D460U835-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 775 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4768.8 lumens  
Efficiency: N/A  
Efficacy: 126.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 37.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332155  
CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332155

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56
2	92	85	78	73	87	80	74	69	71	67	63	63	59	57	55	53	51	47
3	84	74	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40
4	77	66	58	51	72	62	55	49	56	50	45	50	45	41	44	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	36	39	35	32	29
6	65	53	44	38	61	50	43	37	45	39	34	40	35	31	36	32	28	26
7	60	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25	23
8	56	43	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20	18
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13108	13108	13108
5°	13169	12988	13078
10°	13081	12875	12955
15°	12929	12730	12754
20°	12749	12521	12534
25°	12511	12275	12250
30°	12246	11999	11908
35°	11971	11709	11557
40°	11682	11387	11212
45°	11365	11094	10823
50°	11047	10731	10433
55°	10631	10355	10042
60°	10211	9918	9604
65°	9841	9442	9146
70°	9294	8897	8500
75°	8492	8189	7839
80°	7662	7333	7271
85°	6719	6472	6212



TEST NUMBER: P332155

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	114.7	2.4
10°-20°	323.9	6.8
20°-30°	478.4	10.0
30°-40°	558.9	11.7
40°-50°	561.9	11.8
50°-60°	493.6	10.3
60°-70°	367.7	7.7
70°-80°	209.5	4.4
80°-90°	61.9	1.3
90°-100°	37.6	0.8
100°-110°	112.5	2.4
110°-120°	191.3	4.0
120°-130°	251.7	5.3
130°-140°	282.9	5.9
140°-150°	278.0	5.8
150°-160°	234.1	4.9
160°-170°	155.8	3.3
170°-180°	54.6	1.1
0°-30°	917.1	19.2
0°-40°	1475.9	30.9
0°-60°	2531.4	53.1
0°-90°	3170.4	66.5
90°-120°	341.4	7.2
90°-150°	1153.9	24.2
90°-180°	1598.0	33.5
0°-180°	4768.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1218	1218	1218	1218	1218	
5°	1219	1213	1202	1212	1210	115
15°	1160	1155	1142	1150	1144	327
25°	1053	1047	1034	1034	1031	485
35°	911	904	891	885	880	570
45°	747	742	729	717	711	576
55°	566	565	552	541	535	507
65°	386	381	371	363	359	381
75°	204	200	197	192	188	218
85°	54	52	52	50	50	60
90°	0	5	11	13	14	5
95°	27	30	34	35	35	30
105°	102	103	107	107	108	109
115°	193	194	193	194	193	191
125°	282	283	282	280	279	251
135°	366	368	368	366	365	282
145°	444	445	446	445	444	277
155°	508	508	508	510	507	234
165°	553	552	552	554	552	156
175°	576	574	574	576	573	55
180°	577	577	577	577	577	



TEST NUMBER: P332155

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1221.9	1221.2	1220.5	1219.7	1219.0	1217.6	1215.5	1213.5	1211.4	1209.4	1211.2
5°	1218.8	1217.6	1216.5	1215.3	1214.1	1212.3	1209.7	1207.2	1204.6	1202.0	1204.4
7.5°	1206.9	1205.7	1204.5	1203.4	1202.2	1200.3	1197.6	1195.0	1192.3	1189.7	1191.8
10°	1196.8	1195.6	1194.5	1193.3	1192.2	1190.1	1187.0	1184.0	1181.0	1178.0	1180.1
12.5°	1183.4	1182.4	1181.5	1180.5	1179.5	1177.6	1174.8	1171.9	1169.1	1166.2	1167.8
15°	1160.2	1159.2	1158.3	1157.4	1156.4	1154.5	1151.4	1148.4	1145.4	1142.4	1144.2
17.5°	1133.1	1131.9	1130.7	1129.5	1128.3	1126.2	1123.2	1120.1	1117.1	1114.1	1115.4
20°	1113.0	1111.6	1110.3	1108.9	1107.5	1105.2	1102.2	1099.2	1096.2	1093.1	1094.1
22.5°	1090.4	1089.0	1087.6	1086.2	1084.8	1082.6	1079.6	1076.6	1073.6	1070.5	1071.3
25°	1053.4	1052.0	1050.6	1049.2	1047.8	1045.6	1042.5	1039.5	1036.5	1033.5	1033.7
27.5°	1013.8	1012.4	1011.1	1009.7	1008.4	1006.1	1002.8	999.6	996.3	993.0	993.2
30°	985.3	984.1	983.0	981.8	980.6	978.4	975.2	971.9	968.7	965.4	965.4
32.5°	956.8	955.3	953.7	952.2	950.7	948.7	946.1	943.6	941.1	938.6	937.3
35°	911.0	909.6	908.2	906.8	905.4	903.2	900.1	897.1	894.1	891.1	889.7
37.5°	864.0	862.3	860.5	858.7	857.0	854.6	851.5	848.4	845.3	842.3	840.6
40°	831.4	830.0	828.6	827.2	825.8	823.5	820.2	817.0	813.7	810.4	808.6
42.5°	798.7	797.1	795.5	794.0	792.4	790.0	786.7	783.4	780.2	776.9	775.1
45°	746.6	745.6	744.7	743.8	742.8	740.9	737.8	734.8	731.8	728.8	726.0
47.5°	694.8	693.5	692.1	690.8	689.4	687.3	684.5	681.7	678.8	676.0	673.2
50°	659.7	658.5	657.3	656.2	655.0	652.9	649.9	646.9	643.8	640.8	638.3
52.5°	622.8	622.0	621.2	620.4	619.6	617.6	614.4	611.2	608.0	604.8	602.6
55°	566.5	566.2	566.0	565.8	565.5	563.9	560.9	557.9	554.8	551.8	549.3
57.5°	512.9	512.1	511.3	510.5	509.7	508.1	505.7	503.2	500.8	498.4	496.1
60°	474.3	474.1	473.9	473.6	473.4	471.9	469.1	466.3	463.5	460.7	458.6
62.5°	440.0	439.4	438.8	438.2	437.6	435.9	433.1	430.3	427.5	424.7	422.6
65°	386.4	385.2	384.0	382.9	381.7	380.0	377.6	375.3	373.0	370.7	368.8
67.5°	329.6	328.6	327.6	326.5	325.5	324.1	322.4	320.6	318.8	317.1	315.4
70°	295.3	293.9	292.5	291.1	289.7	288.3	286.9	285.5	284.1	282.7	281.1
72.5°	259.3	258.2	257.2	256.2	255.2	253.9	252.3	250.7	249.1	247.5	246.1
75°	204.2	203.2	202.3	201.4	200.5	199.6	198.9	198.2	197.5	196.9	195.7
77.5°	155.4	154.9	154.4	153.9	153.3	152.7	151.8	151.0	150.2	149.3	148.5
80°	123.6	122.9	122.2	121.5	120.8	120.2	119.7	119.3	118.8	118.3	118.1
82.5°	92.6	92.4	92.3	92.1	92.0	91.9	91.8	91.7	91.6	91.5	91.1
85°	54.4	54.0	53.5	53.1	52.6	52.4	52.4	52.4	52.4	52.4	51.9
87.5°	21.9	21.5	21.2	20.8	20.4	20.3	20.4	20.5	20.5	20.6	20.5
90°	0.5	1.5	2.5	3.5	4.5	5.6	6.9	8.3	9.6	10.9	11.3
92.5°	11.0	11.7	12.3	13.0	13.7	14.4	15.2	15.9	16.7	17.4	17.7
95°	26.7	27.4	28.1	28.9	29.6	30.3	31.1	31.9	32.7	33.5	33.9
97.5°	47.5	48.0	48.5	49.1	49.6	50.1	50.7	51.3	51.9	52.5	52.9
100°	61.6	62.2	62.8	63.4	64.0	64.6	65.1	65.6	66.1	66.6	66.9
102.5°	77.9	78.3	78.7	79.0	79.4	79.9	80.6	81.2	81.9	82.6	82.9
105°	102.0	102.2	102.4	102.6	102.8	103.3	104.2	105.1	106.0	106.9	106.9
107.5°	129.9	130.0	130.1	130.2	130.4	130.6	131.0	131.3	131.7	132.1	132.4
110°	147.3	147.5	147.7	147.9	148.1	148.3	148.5	148.7	148.9	149.1	149.5



TEST NUMBER: P332155

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	165.4	165.5	165.7	165.8	165.9	166.0	166.0	166.1	166.1	166.1	166.6
115°	192.6	192.9	193.2	193.5	193.8	193.9	193.7	193.5	193.3	193.1	193.2
117.5°	220.0	220.2	220.4	220.6	220.8	220.7	220.5	220.2	220.0	219.7	219.7
120°	237.0	237.6	238.2	238.8	239.4	239.5	239.0	238.5	238.0	237.5	237.4
122.5°	254.8	255.2	255.7	256.1	256.5	256.6	256.4	256.1	255.9	255.6	255.3
125°	281.9	282.2	282.5	282.8	283.1	283.1	282.9	282.7	282.5	282.3	281.9
127.5°	306.9	307.5	308.2	308.8	309.5	309.7	309.5	309.2	309.0	308.8	308.2
130°	323.6	324.4	325.2	326.0	326.8	327.0	326.7	326.4	326.1	325.8	325.4
132.5°	340.2	341.0	341.9	342.7	343.5	343.8	343.5	343.3	343.1	342.9	342.4
135°	365.7	366.3	366.9	367.5	368.1	368.4	368.3	368.2	368.1	368.0	367.6
137.5°	389.3	389.8	390.3	390.8	391.3	391.7	391.9	392.2	392.5	392.7	392.3
140°	405.6	406.1	406.6	407.1	407.6	407.9	408.0	408.1	408.2	408.3	408.2
142.5°	420.5	421.0	421.5	422.0	422.5	422.8	423.0	423.2	423.4	423.5	423.4
145°	443.7	443.9	444.1	444.3	444.5	444.7	445.0	445.3	445.6	445.9	445.8
147.5°	464.0	464.3	464.7	465.0	465.4	465.7	466.0	466.3	466.6	466.9	466.9
150°	478.1	478.3	478.5	478.7	478.9	479.1	479.3	479.5	479.7	479.9	479.9
152.5°	489.7	490.0	490.3	490.5	490.8	491.0	491.1	491.3	491.4	491.5	491.7
155°	508.0	508.0	508.0	508.0	508.0	508.1	508.2	508.3	508.4	508.5	508.9
157.5°	523.6	523.5	523.4	523.2	523.1	523.1	523.2	523.3	523.3	523.4	523.8
160°	533.4	533.2	533.0	532.8	532.6	532.5	532.5	532.5	532.5	532.5	533.0
162.5°	542.1	541.8	541.5	541.2	541.0	540.9	540.9	541.0	541.1	541.2	541.7
165°	553.3	553.0	552.7	552.4	552.1	552.0	552.0	552.0	552.0	552.0	552.6
167.5°	562.3	561.9	561.5	561.1	560.7	560.5	560.6	560.7	560.8	560.8	561.5
170°	567.4	567.0	566.6	566.2	565.8	565.6	565.6	565.6	565.6	565.6	566.3
172.5°	571.4	571.0	570.6	570.2	569.7	569.5	569.5	569.5	569.5	569.5	570.2
175°	575.5	575.1	574.7	574.3	573.9	573.7	573.7	573.7	573.7	573.7	574.3
177.5°	577.3	576.9	576.6	576.3	576.0	575.8	575.8	575.8	575.8	575.8	576.3
180°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9



TEST NUMBER: P332155

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8	1217.8
2.5°	1213.1	1215.0	1216.8	1217.7	1217.5	1217.3	1217.1	1216.9
5°	1206.7	1209.0	1211.4	1212.3	1211.8	1211.4	1210.9	1210.4
7.5°	1193.9	1196.0	1198.1	1199.0	1198.7	1198.4	1198.1	1197.9
10°	1182.2	1184.2	1186.3	1187.2	1186.7	1186.2	1185.8	1185.3
12.5°	1169.3	1170.8	1172.4	1173.0	1172.7	1172.4	1172.2	1171.9
15°	1146.1	1147.9	1149.8	1150.0	1148.6	1147.2	1145.9	1144.5
17.5°	1116.7	1118.0	1119.3	1119.7	1119.2	1118.7	1118.2	1117.7
20°	1095.0	1095.9	1096.9	1097.0	1096.3	1095.6	1094.9	1094.2
22.5°	1072.0	1072.8	1073.5	1073.4	1072.6	1071.7	1070.8	1069.9
25°	1033.9	1034.2	1034.4	1034.2	1033.5	1032.8	1032.1	1031.4
27.5°	993.4	993.6	993.8	993.4	992.6	991.7	990.8	989.9
30°	965.4	965.4	965.4	964.6	963.0	961.3	959.7	958.1
32.5°	936.0	934.7	933.4	932.3	931.4	930.5	929.6	928.8
35°	888.3	886.9	885.5	884.2	883.0	881.9	880.7	879.5
37.5°	838.9	837.2	835.6	834.4	833.6	832.9	832.1	831.4
40°	806.7	804.9	803.0	801.6	800.7	799.7	798.8	797.9
42.5°	773.2	771.3	769.5	768.1	767.2	766.2	765.3	764.4
45°	723.2	720.4	717.6	715.6	714.5	713.3	712.1	711.0
47.5°	670.5	667.8	665.0	663.1	662.1	661.1	660.1	659.0
50°	635.7	633.1	630.6	628.6	627.2	625.8	624.4	623.0
52.5°	600.4	598.2	596.0	594.3	592.9	591.5	590.1	588.7
55°	546.7	544.1	541.6	539.7	538.5	537.4	536.2	535.1
57.5°	493.8	491.6	489.3	487.5	486.1	484.8	483.4	482.1
60°	456.5	454.4	452.3	450.7	449.5	448.4	447.2	446.1
62.5°	420.5	418.4	416.3	414.9	414.1	413.3	412.5	411.7
65°	366.9	365.1	363.2	361.9	361.2	360.5	359.8	359.1
67.5°	313.8	312.2	310.5	309.2	308.3	307.3	306.3	305.3
70°	279.5	277.8	276.2	274.8	273.6	272.5	271.3	270.1
72.5°	244.6	243.2	241.8	240.7	240.1	239.5	238.9	238.3
75°	194.5	193.4	192.2	191.3	190.6	189.9	189.2	188.5
77.5°	147.7	146.9	146.1	145.8	145.8	145.8	145.8	145.8
80°	117.9	117.6	117.4	117.3	117.3	117.3	117.3	117.3
82.5°	90.7	90.3	89.8	89.5	89.4	89.2	89.0	88.8
85°	51.4	51.0	50.5	50.3	50.3	50.3	50.3	50.3
87.5°	20.4	20.3	20.2	20.1	20.2	20.2	20.3	20.3
90°	11.7	12.1	12.5	12.8	13.0	13.2	13.4	13.6
92.5°	18.0	18.4	18.7	18.8	18.7	18.5	18.4	18.3
95°	34.3	34.7	35.1	35.3	35.3	35.3	35.3	35.3
97.5°	53.4	53.9	54.3	54.5	54.5	54.5	54.4	54.4
100°	67.2	67.5	67.8	68.1	68.3	68.5	68.7	68.9
102.5°	83.2	83.5	83.8	83.9	83.9	83.8	83.8	83.7
105°	106.9	106.9	106.9	107.0	107.3	107.5	107.7	107.9
107.5°	132.7	133.0	133.3	133.4	133.3	133.2	133.1	133.0
110°	149.9	150.3	150.7	150.8	150.6	150.4	150.2	150.0





TEST NUMBER: P332155

CATALOG NUMBER: S123DIW-S775D460U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	167.1	167.6	168.1	168.3	168.2	168.2	168.2	168.1
115°	193.3	193.4	193.5	193.5	193.4	193.3	193.2	193.1
117.5°	219.7	219.6	219.6	219.5	219.2	218.9	218.6	218.3
120°	237.3	237.2	237.1	236.9	236.7	236.5	236.3	236.1
122.5°	255.1	254.8	254.5	254.3	254.0	253.7	253.4	253.1
125°	281.5	281.1	280.7	280.3	279.9	279.5	279.1	278.7
127.5°	307.7	307.1	306.5	306.0	305.6	305.1	304.6	304.2
130°	325.0	324.6	324.2	323.7	323.0	322.3	321.6	320.8
132.5°	341.9	341.4	340.9	340.4	339.9	339.3	338.8	338.2
135°	367.2	366.8	366.4	366.1	365.9	365.7	365.5	365.3
137.5°	391.9	391.5	391.0	390.6	390.2	389.9	389.5	389.1
140°	408.1	408.0	407.9	407.5	406.8	406.1	405.4	404.7
142.5°	423.3	423.2	423.1	422.8	422.3	421.7	421.2	420.6
145°	445.7	445.6	445.5	445.3	444.9	444.5	444.1	443.7
147.5°	466.9	466.9	466.9	466.6	466.0	465.3	464.7	464.1
150°	479.9	479.9	479.9	479.6	479.0	478.4	477.8	477.2
152.5°	491.8	492.0	492.2	492.0	491.5	490.9	490.4	489.9
155°	509.3	509.7	510.1	509.9	509.2	508.5	507.8	507.1
157.5°	524.3	524.7	525.1	525.0	524.5	523.9	523.3	522.8
160°	533.5	534.0	534.5	534.5	534.1	533.7	533.3	532.9
162.5°	542.2	542.7	543.2	543.1	542.5	541.8	541.2	540.5
165°	553.2	553.8	554.4	554.3	553.6	552.9	552.2	551.5
167.5°	562.1	562.7	563.3	563.3	562.7	562.1	561.5	560.8
170°	567.0	567.7	568.4	568.4	567.7	567.0	566.3	565.6
172.5°	570.8	571.4	572.0	572.0	571.3	570.6	569.9	569.2
175°	574.9	575.5	576.1	576.1	575.4	574.7	574.0	573.3
177.5°	576.8	577.3	577.7	577.7	577.1	576.6	576.0	575.4
180°	576.9	576.9	576.9	576.9	576.9	576.9	576.9	576.9

(END OF REPORT)