

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332460

Luminaire Tested: **S123RDIW-S1000D1030U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332460
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1030U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7917.6 lumens
Efficiency: N/A
Efficacy: 129.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332460

CATALOG NUMBER: S123RDIW-S1000D1030U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332460

CATALOG NUMBER: S123RDIW-S1000D1030U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40	35
3	81	72	65	59	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	56	51	68	59	53	47	50	45	41	42	38	35	34	32	30	26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	51	43	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	20	18
8	54	42	35	29	50	39	33	28	34	28	25	29	25	21	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	15
10	47	35	28	24	44	33	27	22	29	24	20	24	20	18	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18064	18064	18064
5°	18133	17882	17986
10°	18030	17658	17598
15°	17836	17245	17063
20°	17570	16728	16339
25°	17296	16149	15631
30°	16933	15479	14633
35°	16561	14808	13717
40°	16218	14018	12584
45°	15767	13239	11561
50°	15270	12353	10416
55°	14763	11340	9348
60°	14299	10256	8174
65°	13692	9082	7002
70°	12935	7626	5655
75°	11832	6001	5319
80°	10544	5312	4891
85°	8904	4705	4372



TEST NUMBER: P332460

CATALOG NUMBER: S123RDIW-S1000D1030U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.6	2.0
10°-20°	438.5	5.5
20°-30°	631.4	8.0
30°-40°	711.2	9.0
40°-50°	680.4	8.6
50°-60°	557.2	7.0
60°-70°	375.9	4.7
70°-80°	189.1	2.4
80°-90°	53.8	0.7
90°-100°	49.2	0.6
100°-110°	234.3	3.0
110°-120°	562.7	7.1
120°-130°	716.5	9.0
130°-140°	765.6	9.7
140°-150°	715.9	9.0
150°-160°	577.5	7.3
160°-170°	372.7	4.7
170°-180°	128.4	1.6
0°-30°	1227.4	15.5
0°-40°	1938.6	24.5
0°-60°	3176.1	40.1
0°-90°	3794.9	47.9
90°-120°	846.1	10.7
90°-150°	3044.1	38.4
90°-180°	4123.0	52.1
0°-180°	7917.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1678	1678	1678	1678	1678	
5°	1678	1671	1655	1666	1665	159
15°	1601	1584	1548	1541	1531	451
25°	1456	1421	1360	1332	1316	669
35°	1260	1209	1127	1070	1044	788
45°	1036	972	870	795	760	799
55°	787	717	604	528	498	705
65°	538	461	357	293	275	532
75°	284	219	144	131	128	303
85°	72	44	38	36	35	81
90°	1	11	24	28	30	6
95°	61	23	31	38	38	76
105°	299	305	220	52	44	317
115°	562	568	576	586	591	554
125°	792	799	804	806	808	707
135°	985	991	995	998	995	758
145°	1137	1144	1146	1148	1148	711
155°	1252	1251	1252	1256	1250	577
165°	1321	1318	1317	1324	1318	373
175°	1352	1347	1348	1354	1347	129
180°	1352	1352	1352	1352	1352	



TEST NUMBER: P332460

CATALOG NUMBER: S123RDIW-S1000D1030U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1683.6	1682.6	1681.7	1680.7	1679.7	1677.8	1674.9	1672.0	1669.1	1666.2	1668.8
5°	1678.2	1676.6	1675.1	1673.6	1672.1	1669.5	1665.9	1662.3	1658.7	1655.0	1657.7
7.5°	1662.6	1661.0	1659.4	1657.7	1656.1	1652.9	1648.2	1643.5	1638.8	1634.1	1635.6
10°	1649.6	1647.5	1645.3	1643.2	1641.1	1637.3	1631.9	1626.4	1621.0	1615.6	1615.9
12.5°	1631.1	1628.7	1626.4	1624.0	1621.6	1617.1	1610.5	1603.8	1597.2	1590.5	1590.3
15°	1600.6	1597.3	1593.9	1590.6	1587.3	1581.4	1572.9	1564.4	1556.0	1547.5	1546.0
17.5°	1562.2	1558.3	1554.5	1550.6	1546.7	1539.4	1528.6	1517.9	1507.1	1496.3	1493.1
20°	1533.9	1529.1	1524.2	1519.4	1514.5	1506.4	1494.9	1483.4	1471.9	1460.4	1456.5
22.5°	1502.3	1496.8	1491.2	1485.6	1480.1	1471.2	1458.9	1446.7	1434.5	1422.3	1417.4
25°	1456.3	1448.8	1441.2	1433.6	1426.1	1415.3	1401.4	1387.5	1373.6	1359.7	1353.3
27.5°	1400.5	1392.2	1383.8	1375.5	1367.1	1355.2	1339.7	1324.2	1308.7	1293.3	1284.4
30°	1362.4	1353.3	1344.3	1335.2	1326.1	1313.1	1296.2	1279.2	1262.3	1245.4	1235.1
32.5°	1324.3	1314.0	1303.7	1293.4	1283.2	1269.1	1251.2	1233.3	1215.3	1197.4	1186.2
35°	1260.3	1249.4	1238.5	1227.7	1216.8	1201.9	1183.2	1164.4	1145.7	1126.9	1113.9
37.5°	1195.5	1183.4	1171.3	1159.2	1147.1	1131.1	1111.1	1091.0	1071.0	1051.0	1036.2
40°	1154.2	1140.9	1127.5	1114.2	1100.9	1083.5	1062.1	1040.6	1019.1	997.6	981.9
42.5°	1107.3	1094.0	1080.7	1067.4	1054.1	1036.4	1014.2	992.0	969.8	947.6	930.4
45°	1035.8	1022.1	1008.5	994.9	981.3	962.9	939.6	916.3	893.0	869.7	852.5
47.5°	964.2	949.2	934.3	919.3	904.4	885.3	862.0	838.7	815.4	792.1	773.4
50°	911.9	897.7	883.5	869.3	855.0	835.7	811.2	786.7	762.2	737.7	718.9
52.5°	865.1	849.7	834.2	818.8	803.4	783.5	759.3	735.0	710.8	686.5	667.0
55°	786.7	771.9	757.0	742.2	727.4	707.1	681.4	655.7	630.0	604.3	586.8
57.5°	714.3	698.1	682.0	665.8	649.7	628.7	602.8	577.0	551.2	525.4	508.8
60°	664.2	647.6	630.9	614.3	597.6	576.8	551.7	526.6	501.5	476.4	460.0
62.5°	614.1	597.5	580.8	564.2	547.6	526.7	501.6	476.5	451.4	426.3	410.9
65°	537.6	521.0	504.3	487.7	471.1	451.0	427.4	403.8	380.2	356.6	341.8
67.5°	461.1	444.3	427.5	410.7	393.9	374.1	351.5	328.9	306.3	283.6	272.6
70°	411.0	394.7	378.4	362.0	345.7	327.0	305.8	284.6	263.4	242.3	231.7
72.5°	360.9	344.9	328.8	312.7	296.6	278.9	259.7	240.5	221.2	202.0	193.3
75°	284.5	269.9	255.4	240.9	226.4	210.8	194.2	177.5	160.9	144.3	141.2
77.5°	214.8	201.6	188.5	175.4	162.3	150.3	139.6	128.9	118.2	107.5	105.9
80°	170.1	157.7	145.3	132.9	120.5	111.2	104.8	98.4	92.1	85.7	84.8
82.5°	127.7	117.0	106.3	95.5	84.8	78.0	75.0	72.1	69.1	66.1	65.2
85°	72.1	65.5	58.8	52.2	45.5	41.7	40.8	39.9	39.0	38.1	37.5
87.5°	26.3	24.1	21.9	19.7	17.5	16.7	17.2	17.8	18.4	19.0	18.9
90°	1.0	3.2	5.5	7.7	9.9	12.5	15.4	18.3	21.2	24.1	25.0
92.5°	18.7	18.1	17.4	16.8	16.2	17.0	19.2	21.3	23.5	25.7	27.1
95°	61.3	52.1	43.0	33.8	24.7	21.3	23.8	26.2	28.7	31.1	32.7
97.5°	123.1	119.0	114.9	110.8	106.7	96.6	80.6	64.5	48.4	32.3	34.1
100°	169.7	174.2	178.7	183.1	187.6	172.4	137.6	102.8	68.0	33.1	34.9
102.5°	222.8	226.0	229.2	232.4	235.6	218.2	180.2	142.2	104.1	66.1	60.6
105°	299.3	301.8	304.2	306.7	309.1	300.3	280.2	260.1	240.1	220.0	180.5
107.5°	380.1	382.0	384.0	386.0	387.9	390.5	393.7	396.8	400.0	403.2	374.2
110°	433.9	435.7	437.5	439.3	441.0	443.2	445.6	448.1	450.5	453.0	445.6



TEST NUMBER: P332460

CATALOG NUMBER: S123RDIW-S1000D1030U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.3	486.9	488.5	490.2	491.8	493.8	496.2	498.7	501.2	503.6	503.7
115°	561.5	562.8	564.1	565.5	566.8	568.5	570.5	572.5	574.5	576.5	578.8
117.5°	635.2	636.8	638.5	640.1	641.8	643.1	644.2	645.2	646.2	647.2	649.0
120°	681.0	683.0	685.0	687.0	689.0	690.4	691.0	691.7	692.4	693.0	694.8
122.5°	727.6	729.2	730.9	732.5	734.2	735.4	736.3	737.1	738.0	738.8	740.1
125°	791.5	793.3	795.0	796.8	798.6	800.0	800.8	801.7	802.6	803.5	804.0
127.5°	853.3	855.1	856.9	858.7	860.5	861.9	863.0	864.1	865.1	866.2	866.9
130°	891.9	893.7	895.5	897.3	899.1	900.4	901.3	902.2	903.1	904.0	904.9
132.5°	928.9	930.7	932.4	934.2	936.0	937.3	938.0	938.7	939.4	940.1	941.0
135°	985.3	986.7	988.0	989.3	990.7	991.8	992.7	993.6	994.5	995.4	996.0
137.5°	1033.5	1035.2	1036.9	1038.6	1040.3	1041.4	1041.9	1042.4	1042.9	1043.4	1044.4
140°	1065.7	1067.0	1068.4	1069.7	1071.0	1072.0	1072.7	1073.4	1074.0	1074.7	1075.6
142.5°	1095.4	1096.7	1098.1	1099.4	1100.8	1101.8	1102.4	1103.1	1103.8	1104.4	1105.2
145°	1137.0	1138.5	1140.1	1141.7	1143.2	1144.2	1144.7	1145.1	1145.6	1146.0	1146.5
147.5°	1176.2	1177.2	1178.2	1179.2	1180.3	1181.0	1181.4	1181.9	1182.3	1182.8	1183.2
150°	1200.3	1200.9	1201.6	1202.3	1202.9	1203.5	1203.9	1204.4	1204.8	1205.3	1205.7
152.5°	1222.0	1222.3	1222.6	1222.9	1223.2	1223.5	1223.8	1224.0	1224.3	1224.6	1225.4
155°	1252.5	1252.0	1251.6	1251.2	1250.7	1250.6	1250.8	1251.0	1251.3	1251.5	1252.6
157.5°	1276.2	1276.2	1276.1	1276.1	1276.0	1275.9	1275.7	1275.4	1275.2	1275.0	1276.3
160°	1290.7	1290.4	1290.2	1290.0	1289.8	1289.5	1289.3	1289.1	1288.9	1288.7	1290.0
162.5°	1304.3	1303.7	1303.2	1302.6	1302.0	1301.6	1301.4	1301.2	1300.9	1300.7	1302.2
165°	1320.8	1320.1	1319.5	1318.8	1318.1	1317.7	1317.4	1317.2	1317.0	1316.8	1318.6
167.5°	1333.6	1332.8	1331.9	1331.0	1330.1	1329.6	1329.6	1329.6	1329.6	1329.6	1331.4
170°	1340.9	1340.0	1339.1	1338.2	1337.3	1336.9	1336.9	1336.9	1336.9	1336.9	1338.6
172.5°	1345.7	1344.6	1343.6	1342.5	1341.4	1341.0	1341.1	1341.3	1341.5	1341.7	1343.5
175°	1351.9	1350.8	1349.7	1348.6	1347.5	1347.0	1347.2	1347.5	1347.7	1347.9	1349.5
177.5°	1353.5	1352.6	1351.8	1350.9	1350.0	1349.6	1349.8	1350.0	1350.1	1350.3	1351.8
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332460

CATALOG NUMBER: S123RDIW-S1000D1030U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1671.5	1674.2	1676.8	1677.9	1677.4	1677.0	1676.5	1676.0
5°	1660.5	1663.2	1665.9	1667.0	1666.4	1665.8	1665.2	1664.6
7.5°	1637.1	1638.6	1640.1	1640.4	1639.3	1638.3	1637.3	1636.2
10°	1616.2	1616.5	1616.8	1616.2	1614.6	1613.1	1611.6	1610.1
12.5°	1590.1	1590.0	1589.8	1588.8	1587.1	1585.3	1583.6	1581.8
15°	1544.5	1543.0	1541.5	1539.6	1537.5	1535.4	1533.3	1531.2
17.5°	1489.9	1486.7	1483.5	1480.3	1477.2	1474.0	1470.9	1467.7
20°	1452.5	1448.6	1444.7	1440.9	1437.3	1433.6	1430.0	1426.4
22.5°	1412.5	1407.6	1402.7	1398.5	1395.2	1391.8	1388.4	1385.0
25°	1347.0	1340.6	1334.3	1329.4	1326.1	1322.8	1319.5	1316.1
27.5°	1275.6	1266.8	1257.9	1251.0	1245.9	1240.8	1235.7	1230.7
30°	1224.8	1214.5	1204.2	1196.7	1191.8	1187.0	1182.1	1177.3
32.5°	1174.9	1163.7	1152.4	1144.3	1139.2	1134.1	1129.0	1123.9
35°	1100.9	1087.9	1074.9	1065.7	1060.3	1054.8	1049.4	1043.9
37.5°	1021.5	1006.7	992.0	981.2	974.5	967.8	961.1	954.4
40°	966.2	950.5	934.7	923.4	916.4	909.5	902.5	895.6
42.5°	913.2	896.0	878.8	867.1	860.9	854.7	848.4	842.2
45°	835.2	818.0	800.7	788.5	781.2	774.0	766.7	759.5
47.5°	754.6	735.9	717.1	704.5	698.0	691.6	685.1	678.6
50°	700.2	681.4	662.7	649.8	642.9	635.9	629.0	622.0
52.5°	647.6	628.1	608.6	595.7	589.5	583.3	577.1	570.8
55°	569.2	551.7	534.1	522.3	516.3	510.2	504.2	498.1
57.5°	492.2	475.6	459.1	448.2	443.1	437.9	432.8	427.6
60°	443.7	427.4	411.0	400.3	395.2	390.0	384.9	379.7
62.5°	395.5	380.2	364.8	354.4	349.1	343.7	338.3	332.9
65°	327.0	312.1	297.3	288.2	284.9	281.6	278.3	274.9
67.5°	261.5	250.4	239.4	232.0	228.5	224.9	221.3	217.8
70°	221.1	210.5	199.9	193.0	189.6	186.3	183.0	179.7
72.5°	184.7	176.0	167.4	162.4	161.0	159.6	158.2	156.8
75°	138.2	135.2	132.2	130.4	129.8	129.1	128.5	127.9
77.5°	104.3	102.6	101.0	99.9	99.3	98.7	98.1	97.5
80°	83.9	83.0	82.1	81.4	80.8	80.2	79.5	78.9
82.5°	64.3	63.4	62.5	62.0	61.9	61.8	61.6	61.5
85°	36.9	36.3	35.7	35.4	35.4	35.4	35.4	35.4
87.5°	18.8	18.8	18.7	18.6	18.5	18.3	18.2	18.0
90°	25.9	26.8	27.7	28.3	28.8	29.2	29.7	30.1
92.5°	28.6	30.0	31.4	32.3	32.5	32.8	33.1	33.3
95°	34.3	35.8	37.4	38.2	38.2	38.2	38.2	38.2
97.5°	35.9	37.7	39.5	40.5	40.7	40.9	41.2	41.4
100°	36.7	38.5	40.3	41.3	41.5	41.7	42.0	42.2
102.5°	55.0	49.5	43.9	41.4	41.8	42.2	42.6	43.0
105°	141.0	101.4	61.9	42.4	42.9	43.3	43.7	44.2
107.5°	345.2	316.3	287.3	257.9	228.1	198.4	168.6	138.8
110°	438.3	430.9	423.5	403.9	372.0	340.0	308.1	276.2



TEST NUMBER: P332460

CATALOG NUMBER: S123RDIW-S1000D1030U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	503.9	504.0	504.1	500.8	494.1	487.4	480.6	473.9
115°	581.0	583.2	585.5	587.0	587.9	588.8	589.7	590.6
117.5°	650.8	652.6	654.4	655.4	655.5	655.7	655.9	656.1
120°	696.6	698.4	700.2	701.1	701.1	701.1	701.1	701.1
122.5°	741.3	742.6	743.8	744.6	744.7	744.9	745.1	745.3
125°	804.4	804.9	805.3	805.8	806.2	806.6	807.1	807.5
127.5°	867.6	868.3	869.1	869.2	868.7	868.3	867.9	867.4
130°	905.8	906.6	907.5	907.8	907.3	906.9	906.4	906.0
132.5°	941.9	942.8	943.7	943.8	943.2	942.6	942.0	941.3
135°	996.7	997.4	998.0	998.0	997.4	996.7	996.0	995.4
137.5°	1045.5	1046.6	1047.7	1048.0	1047.5	1047.1	1046.6	1046.2
140°	1076.5	1077.4	1078.3	1078.5	1078.1	1077.6	1077.2	1076.7
142.5°	1105.9	1106.6	1107.3	1107.3	1106.7	1106.1	1105.5	1104.8
145°	1146.9	1147.4	1147.8	1148.0	1148.0	1148.0	1148.0	1148.0
147.5°	1183.7	1184.1	1184.6	1184.3	1183.3	1182.2	1181.2	1180.2
150°	1206.2	1206.6	1207.1	1207.0	1206.3	1205.6	1205.0	1204.3
152.5°	1226.2	1227.0	1227.8	1227.7	1226.6	1225.6	1224.6	1223.6
155°	1253.7	1254.8	1256.0	1255.8	1254.5	1253.2	1251.8	1250.5
157.5°	1277.7	1279.0	1280.3	1280.1	1278.4	1276.7	1274.9	1273.2
160°	1291.3	1292.7	1294.0	1293.9	1292.3	1290.8	1289.2	1287.6
162.5°	1303.7	1305.3	1306.8	1306.8	1305.5	1304.1	1302.7	1301.3
165°	1320.3	1322.1	1323.9	1324.0	1322.5	1320.9	1319.3	1317.8
167.5°	1333.2	1335.0	1336.8	1336.8	1335.0	1333.2	1331.4	1329.6
170°	1340.4	1342.2	1344.0	1344.0	1342.2	1340.4	1338.6	1336.9
172.5°	1345.3	1347.0	1348.8	1348.7	1346.8	1344.8	1342.8	1340.9
175°	1351.0	1352.6	1354.2	1354.1	1352.3	1350.5	1348.7	1346.9
177.5°	1353.2	1354.6	1356.0	1355.9	1354.1	1352.3	1350.5	1348.7
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9

(END OF REPORT)