

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332452

Luminaire Tested: **S123RDIW-S1000D460U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332452
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D460U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5636.9 lumens
Efficiency: N/A
Efficacy: 122.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332452

CATALOG NUMBER: S123RDIW-S1000D460U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332452

CATALOG NUMBER: S123RDIW-S1000D460U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	62	58
2	93	86	80	75	88	81	76	71	73	68	65	65	61	59	57	55	53	49
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42
4	78	68	60	54	74	64	57	51	58	52	47	52	47	43	46	42	39	36
5	72	61	52	46	68	58	50	45	52	46	41	46	42	38	42	38	35	32
6	67	55	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31	28
7	62	49	41	36	58	47	40	35	43	37	32	39	34	30	35	31	27	25
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	23
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	25	22	20
10	50	38	31	26	48	36	30	25	33	28	24	30	25	22	27	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18064	18064	18064
5°	18133	17882	17986
10°	18030	17658	17598
15°	17836	17245	17063
20°	17570	16728	16339
25°	17296	16149	15631
30°	16933	15479	14633
35°	16561	14808	13717
40°	16218	14018	12584
45°	15767	13239	11561
50°	15270	12353	10416
55°	14763	11340	9348
60°	14299	10256	8174
65°	13692	9082	7002
70°	12935	7626	5655
75°	11832	6001	5319
80°	10544	5312	4891
85°	8904	4705	4372



TEST NUMBER: P332452

CATALOG NUMBER: S123RDIW-S1000D460U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.6	2.8
10°-20°	438.5	7.8
20°-30°	631.4	11.2
30°-40°	711.2	12.6
40°-50°	680.4	12.1
50°-60°	557.2	9.9
60°-70°	375.9	6.7
70°-80°	189.1	3.4
80°-90°	51.7	0.9
90°-100°	22.0	0.4
100°-110°	104.8	1.9
110°-120°	251.7	4.5
120°-130°	320.5	5.7
130°-140°	342.4	6.1
140°-150°	320.2	5.7
150°-160°	258.3	4.6
160°-170°	166.7	3.0
170°-180°	57.5	1.0
0°-30°	1227.4	21.8
0°-40°	1938.6	34.4
0°-60°	3176.1	56.3
0°-90°	3792.8	67.3
90°-120°	378.5	6.7
90°-150°	1361.6	24.2
90°-180°	1844.0	32.7
0°-180°	5636.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1678	1678	1678	1678	1678	
5°	1678	1671	1655	1666	1665	159
15°	1601	1584	1548	1541	1531	451
25°	1456	1421	1360	1332	1316	669
35°	1260	1209	1127	1070	1044	788
45°	1036	972	870	795	760	799
55°	787	717	604	528	498	705
65°	538	461	357	293	275	532
75°	284	219	144	131	128	303
85°	72	44	38	36	35	81
90°	0	5	11	13	14	5
95°	27	10	14	17	17	34
105°	134	136	98	23	20	142
115°	251	254	258	262	264	248
125°	354	358	359	360	361	316
135°	441	443	445	446	445	339
145°	509	512	513	513	514	318
155°	560	559	560	562	559	258
165°	591	590	589	592	590	167
175°	605	603	603	606	602	58
180°	605	605	605	605	605	



TEST NUMBER: P332452

CATALOG NUMBER: S123RDIW-S1000D460U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1683.6	1682.6	1681.7	1680.7	1679.7	1677.8	1674.9	1672.0	1669.1	1666.2	1668.8
5°	1678.2	1676.6	1675.1	1673.6	1672.1	1669.5	1665.9	1662.3	1658.7	1655.0	1657.7
7.5°	1662.6	1661.0	1659.4	1657.7	1656.1	1652.9	1648.2	1643.5	1638.8	1634.1	1635.6
10°	1649.6	1647.5	1645.3	1643.2	1641.1	1637.3	1631.9	1626.4	1621.0	1615.6	1615.9
12.5°	1631.1	1628.7	1626.4	1624.0	1621.6	1617.1	1610.5	1603.8	1597.2	1590.5	1590.3
15°	1600.6	1597.3	1593.9	1590.6	1587.3	1581.4	1572.9	1564.4	1556.0	1547.5	1546.0
17.5°	1562.2	1558.3	1554.5	1550.6	1546.7	1539.4	1528.6	1517.9	1507.1	1496.3	1493.1
20°	1533.9	1529.1	1524.2	1519.4	1514.5	1506.4	1494.9	1483.4	1471.9	1460.4	1456.5
22.5°	1502.3	1496.8	1491.2	1485.6	1480.1	1471.2	1458.9	1446.7	1434.5	1422.3	1417.4
25°	1456.3	1448.8	1441.2	1433.6	1426.1	1415.3	1401.4	1387.5	1373.6	1359.7	1353.3
27.5°	1400.5	1392.2	1383.8	1375.5	1367.1	1355.2	1339.7	1324.2	1308.7	1293.3	1284.4
30°	1362.4	1353.3	1344.3	1335.2	1326.1	1313.1	1296.2	1279.2	1262.3	1245.4	1235.1
32.5°	1324.3	1314.0	1303.7	1293.4	1283.2	1269.1	1251.2	1233.3	1215.3	1197.4	1186.2
35°	1260.3	1249.4	1238.5	1227.7	1216.8	1201.9	1183.2	1164.4	1145.7	1126.9	1113.9
37.5°	1195.5	1183.4	1171.3	1159.2	1147.1	1131.1	1111.1	1091.0	1071.0	1051.0	1036.2
40°	1154.2	1140.9	1127.5	1114.2	1100.9	1083.5	1062.1	1040.6	1019.1	997.6	981.9
42.5°	1107.3	1094.0	1080.7	1067.4	1054.1	1036.4	1014.2	992.0	969.8	947.6	930.4
45°	1035.8	1022.1	1008.5	994.9	981.3	962.9	939.6	916.3	893.0	869.7	852.5
47.5°	964.2	949.2	934.3	919.3	904.4	885.3	862.0	838.7	815.4	792.1	773.4
50°	911.9	897.7	883.5	869.3	855.0	835.7	811.2	786.7	762.2	737.7	718.9
52.5°	865.1	849.7	834.2	818.8	803.4	783.5	759.3	735.0	710.8	686.5	667.0
55°	786.7	771.9	757.0	742.2	727.4	707.1	681.4	655.7	630.0	604.3	586.8
57.5°	714.3	698.1	682.0	665.8	649.7	628.7	602.8	577.0	551.2	525.4	508.8
60°	664.2	647.6	630.9	614.3	597.6	576.8	551.7	526.6	501.5	476.4	460.0
62.5°	614.1	597.5	580.8	564.2	547.6	526.7	501.6	476.5	451.4	426.3	410.9
65°	537.6	521.0	504.3	487.7	471.1	451.0	427.4	403.8	380.2	356.6	341.8
67.5°	461.1	444.3	427.5	410.7	393.9	374.1	351.5	328.9	306.3	283.6	272.6
70°	411.0	394.7	378.4	362.0	345.7	327.0	305.8	284.6	263.4	242.3	231.7
72.5°	360.9	344.9	328.8	312.7	296.6	278.9	259.7	240.5	221.2	202.0	193.3
75°	284.5	269.9	255.4	240.9	226.4	210.8	194.2	177.5	160.9	144.3	141.2
77.5°	214.8	201.6	188.5	175.4	162.3	150.3	139.6	128.9	118.2	107.5	105.9
80°	170.1	157.7	145.3	132.9	120.5	111.2	104.8	98.4	92.1	85.7	84.8
82.5°	127.7	117.0	106.3	95.5	84.8	78.0	75.0	72.1	69.1	66.1	65.2
85°	72.1	65.5	58.8	52.2	45.5	41.7	40.8	39.9	39.0	38.1	37.5
87.5°	26.2	23.8	21.3	18.8	16.4	15.3	15.5	15.8	16.1	16.3	16.1
90°	0.4	1.4	2.4	3.4	4.4	5.6	6.9	8.2	9.5	10.8	11.2
92.5°	8.4	8.1	7.8	7.5	7.2	7.6	8.6	9.5	10.5	11.5	12.1
95°	27.4	23.3	19.2	15.1	11.0	9.5	10.6	11.7	12.8	13.9	14.6
97.5°	55.1	53.2	51.4	49.6	47.7	43.2	36.0	28.8	21.7	14.5	15.3
100°	75.9	77.9	79.9	81.9	83.9	77.1	61.6	46.0	30.4	14.8	15.6
102.5°	99.6	101.1	102.5	104.0	105.4	97.6	80.6	63.6	46.6	29.6	27.1
105°	133.9	135.0	136.1	137.2	138.3	134.3	125.3	116.4	107.4	98.4	80.7
107.5°	170.0	170.9	171.8	172.6	173.5	174.7	176.1	177.5	178.9	180.3	167.4
110°	194.1	194.9	195.7	196.5	197.3	198.2	199.3	200.4	201.5	202.6	199.3



TEST NUMBER: P332452

CATALOG NUMBER: S123RDIW-S1000D460U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.1	217.8	218.5	219.2	220.0	220.9	222.0	223.1	224.2	225.3	225.3
115°	251.1	251.7	252.3	252.9	253.5	254.3	255.2	256.1	257.0	257.9	258.9
117.5°	284.1	284.9	285.6	286.3	287.1	287.7	288.1	288.6	289.1	289.5	290.3
120°	304.6	305.5	306.4	307.3	308.2	308.8	309.1	309.4	309.7	310.0	310.8
122.5°	325.5	326.2	326.9	327.7	328.4	329.0	329.4	329.7	330.1	330.5	331.0
125°	354.0	354.8	355.6	356.4	357.2	357.8	358.2	358.6	359.0	359.4	359.6
127.5°	381.7	382.5	383.3	384.1	384.9	385.5	386.0	386.5	387.0	387.5	387.8
130°	399.0	399.8	400.6	401.4	402.2	402.8	403.2	403.6	404.0	404.3	404.7
132.5°	415.5	416.3	417.1	417.9	418.7	419.2	419.6	419.9	420.2	420.5	420.9
135°	440.7	441.3	441.9	442.5	443.1	443.6	444.0	444.4	444.8	445.2	445.5
137.5°	462.3	463.1	463.8	464.6	465.3	465.8	466.1	466.3	466.5	466.7	467.2
140°	476.7	477.3	477.9	478.5	479.1	479.5	479.8	480.1	480.4	480.7	481.1
142.5°	490.0	490.6	491.2	491.8	492.4	492.8	493.1	493.4	493.7	494.0	494.3
145°	508.6	509.3	510.0	510.7	511.4	511.8	512.0	512.2	512.4	512.6	512.8
147.5°	526.1	526.6	527.0	527.5	527.9	528.3	528.5	528.7	528.9	529.1	529.3
150°	536.9	537.2	537.5	537.8	538.1	538.3	538.5	538.7	538.9	539.1	539.3
152.5°	546.6	546.7	546.9	547.0	547.2	547.3	547.4	547.5	547.6	547.8	548.1
155°	560.2	560.0	559.8	559.7	559.5	559.4	559.5	559.6	559.7	559.8	560.3
157.5°	570.9	570.8	570.8	570.8	570.8	570.7	570.6	570.5	570.4	570.3	570.9
160°	577.3	577.2	577.1	577.0	576.9	576.8	576.7	576.6	576.5	576.4	577.0
162.5°	583.4	583.2	582.9	582.7	582.4	582.2	582.1	582.0	581.9	581.8	582.5
165°	590.8	590.5	590.2	589.9	589.6	589.4	589.3	589.2	589.1	589.0	589.8
167.5°	596.6	596.2	595.8	595.4	595.0	594.8	594.8	594.8	594.8	594.8	595.6
170°	599.8	599.4	599.0	598.6	598.2	598.0	598.0	598.0	598.0	598.0	598.8
172.5°	601.9	601.5	601.0	600.5	600.0	599.8	599.9	600.0	600.1	600.1	600.9
175°	604.7	604.2	603.7	603.2	602.7	602.5	602.6	602.7	602.8	602.9	603.6
177.5°	605.4	605.0	604.6	604.2	603.8	603.7	603.8	603.8	603.9	604.0	604.6
180°	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7



TEST NUMBER: P332452

CATALOG NUMBER: S123RDIW-S1000D460U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2	1678.2
2.5°	1671.5	1674.2	1676.8	1677.9	1677.4	1677.0	1676.5	1676.0
5°	1660.5	1663.2	1665.9	1667.0	1666.4	1665.8	1665.2	1664.6
7.5°	1637.1	1638.6	1640.1	1640.4	1639.3	1638.3	1637.3	1636.2
10°	1616.2	1616.5	1616.8	1616.2	1614.6	1613.1	1611.6	1610.1
12.5°	1590.1	1590.0	1589.8	1588.8	1587.1	1585.3	1583.6	1581.8
15°	1544.5	1543.0	1541.5	1539.6	1537.5	1535.4	1533.3	1531.2
17.5°	1489.9	1486.7	1483.5	1480.3	1477.2	1474.0	1470.9	1467.7
20°	1452.5	1448.6	1444.7	1440.9	1437.3	1433.6	1430.0	1426.4
22.5°	1412.5	1407.6	1402.7	1398.5	1395.2	1391.8	1388.4	1385.0
25°	1347.0	1340.6	1334.3	1329.4	1326.1	1322.8	1319.5	1316.1
27.5°	1275.6	1266.8	1257.9	1251.0	1245.9	1240.8	1235.7	1230.7
30°	1224.8	1214.5	1204.2	1196.7	1191.8	1187.0	1182.1	1177.3
32.5°	1174.9	1163.7	1152.4	1144.3	1139.2	1134.1	1129.0	1123.9
35°	1100.9	1087.9	1074.9	1065.7	1060.3	1054.8	1049.4	1043.9
37.5°	1021.5	1006.7	992.0	981.2	974.5	967.8	961.1	954.4
40°	966.2	950.5	934.7	923.4	916.4	909.5	902.5	895.6
42.5°	913.2	896.0	878.8	867.1	860.9	854.7	848.4	842.2
45°	835.2	818.0	800.7	788.5	781.2	774.0	766.7	759.5
47.5°	754.6	735.9	717.1	704.5	698.0	691.6	685.1	678.6
50°	700.2	681.4	662.7	649.8	642.9	635.9	629.0	622.0
52.5°	647.6	628.1	608.6	595.7	589.5	583.3	577.1	570.8
55°	569.2	551.7	534.1	522.3	516.3	510.2	504.2	498.1
57.5°	492.2	475.6	459.1	448.2	443.1	437.9	432.8	427.6
60°	443.7	427.4	411.0	400.3	395.2	390.0	384.9	379.7
62.5°	395.5	380.2	364.8	354.4	349.1	343.7	338.3	332.9
65°	327.0	312.1	297.3	288.2	284.9	281.6	278.3	274.9
67.5°	261.5	250.4	239.4	232.0	228.5	224.9	221.3	217.8
70°	221.1	210.5	199.9	193.0	189.6	186.3	183.0	179.7
72.5°	184.7	176.0	167.4	162.4	161.0	159.6	158.2	156.8
75°	138.2	135.2	132.2	130.4	129.8	129.1	128.5	127.9
77.5°	104.3	102.6	101.0	99.9	99.3	98.7	98.1	97.5
80°	83.9	83.0	82.1	81.4	80.8	80.2	79.5	78.9
82.5°	64.3	63.4	62.5	62.0	61.9	61.8	61.6	61.5
85°	36.9	36.3	35.7	35.4	35.4	35.4	35.4	35.4
87.5°	16.0	15.8	15.7	15.5	15.3	15.1	14.9	14.7
90°	11.6	12.0	12.4	12.7	12.9	13.1	13.3	13.5
92.5°	12.8	13.4	14.1	14.4	14.6	14.7	14.8	14.9
95°	15.3	16.0	16.7	17.1	17.1	17.1	17.1	17.1
97.5°	16.1	16.9	17.7	18.1	18.2	18.3	18.4	18.5
100°	16.4	17.2	18.0	18.5	18.6	18.7	18.8	18.9
102.5°	24.6	22.1	19.7	18.5	18.7	18.9	19.0	19.2
105°	63.0	45.4	27.7	19.0	19.2	19.4	19.6	19.8
107.5°	154.4	141.5	128.5	115.4	102.0	88.7	75.4	62.1
110°	196.0	192.7	189.4	180.7	166.4	152.1	137.8	123.6



TEST NUMBER: P332452

CATALOG NUMBER: S123RDIW-S1000D460U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	225.4	225.4	225.5	224.0	221.0	218.0	215.0	212.0
115°	259.9	260.9	261.9	262.6	263.0	263.4	263.8	264.2
117.5°	291.1	291.9	292.7	293.1	293.2	293.3	293.4	293.5
120°	311.6	312.4	313.2	313.6	313.6	313.6	313.6	313.6
122.5°	331.6	332.2	332.7	333.0	333.1	333.2	333.3	333.4
125°	359.8	360.0	360.2	360.4	360.6	360.8	361.0	361.2
127.5°	388.1	388.4	388.7	388.8	388.6	388.4	388.2	388.0
130°	405.1	405.5	405.9	406.0	405.8	405.6	405.4	405.2
132.5°	421.3	421.7	422.1	422.2	421.9	421.6	421.3	421.1
135°	445.8	446.1	446.4	446.4	446.1	445.8	445.5	445.2
137.5°	467.7	468.1	468.6	468.8	468.6	468.4	468.2	468.0
140°	481.5	481.9	482.3	482.4	482.2	482.0	481.8	481.6
142.5°	494.7	495.0	495.3	495.3	495.0	494.8	494.5	494.2
145°	513.0	513.2	513.4	513.5	513.5	513.5	513.5	513.5
147.5°	529.5	529.7	529.9	529.7	529.3	528.8	528.4	527.9
150°	539.5	539.7	539.9	539.9	539.6	539.3	539.0	538.7
152.5°	548.5	548.8	549.2	549.1	548.7	548.2	547.8	547.3
155°	560.8	561.3	561.8	561.7	561.1	560.5	559.9	559.4
157.5°	571.5	572.1	572.7	572.6	571.8	571.1	570.3	569.5
160°	577.6	578.2	578.8	578.8	578.1	577.4	576.7	576.0
162.5°	583.2	583.9	584.5	584.6	583.9	583.3	582.7	582.1
165°	590.6	591.4	592.2	592.2	591.5	590.9	590.2	589.5
167.5°	596.4	597.1	597.9	597.9	597.1	596.4	595.6	594.8
170°	599.6	600.4	601.2	601.2	600.4	599.6	598.8	598.0
172.5°	601.7	602.5	603.3	603.3	602.4	601.5	600.7	599.8
175°	604.3	605.0	605.7	605.7	604.9	604.1	603.3	602.5
177.5°	605.3	605.9	606.6	606.5	605.7	604.9	604.1	603.3
180°	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7

(END OF REPORT)