

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332467-927

Luminaire Tested: **S123RDIW-S1000D1535U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332467-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7353.4 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	43																												
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	44	43	37																												
2	88	81	76	71	81	75	70	65	62	59	55	50	48	46	40	38	37	32																												
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27																												
4	74	64	56	51	68	59	52	47	49	44	41	40	37	34	32	30	28	24																												
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	27	24	21																												
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	27	24	22	19																												
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17																												
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	18	15																												
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14																												
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13																												

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13555	13555	13555	13555
5°	16159	13613	11988	13613
10°	20176	13535	10831	13535
15°	23682	13397	9877	13397
20°	26431	13190	9065	13190
25°	26008	12973	8568	12973
30°	18695	12771	8054	12771
35°	12482	12510	7721	12510
40°	9197	12197	7378	12197
45°	7715	11645	7042	11645
50°	6807	10923	6571	10923
55°	5970	10098	5928	10098
60°	5315	9309	5431	9309
65°	4669	8458	5053	8458
70°	3666	7704	4614	7704
75°	3227	6729	4213	6729
80°	2808	5715	4147	5715
85°	2260	4594	4397	4594



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	1.7
10°-20°	386.9	5.3
20°-30°	607.8	8.3
30°-40°	634.2	8.6
40°-50°	542.7	7.4
50°-60°	413.6	5.6
60°-70°	265.1	3.6
70°-80°	127.5	1.7
80°-90°	38.2	0.5
90°-100°	99.1	1.3
100°-110°	296.5	4.0
110°-120°	504.3	6.9
120°-130°	663.4	9.0
130°-140°	745.6	10.1
140°-150°	732.9	10.0
150°-160°	617.0	8.4
160°-170°	410.7	5.6
170°-180°	143.8	2.0
0°-30°	1118.6	15.2
0°-40°	1752.8	23.8
0°-60°	2709.1	36.8
0°-90°	3140.1	42.7
90°-120°	899.9	12.2
90°-150°	3041.8	41.4
90°-180°	4213.0	57.3
0°-180°	7353.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1259	1259	1259	1259	1259	
5°	1496	1260	1110	1260	1496	154
15°	2125	1202	886	1202	2125	603
25°	2190	1092	721	1092	2190	941
35°	950	952	588	952	950	623
45°	507	765	463	765	507	398
55°	318	538	316	538	318	288
65°	183	332	198	332	183	180
75°	78	162	101	162	78	83
85°	18	37	36	37	18	22
90°	36	1	36	1	36	18
95°	93	70	93	70	93	96
105°	284	269	284	269	284	302
115°	509	508	509	508	509	504
125°	735	743	735	743	735	657
135°	963	964	963	964	963	740
145°	1170	1170	1170	1170	1170	730
155°	1337	1339	1337	1339	1337	615
165°	1454	1459	1454	1459	1454	410
175°	1511	1517	1511	1517	1511	144
180°	1521	1521	1521	1521	1521	



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1341.3	1343.0	1337.4	1336.6	1330.1	1328.3	1328.3	1319.3	1313.7	1306.4	1302.0
5°	1495.5	1504.1	1499.8	1490.1	1473.9	1470.1	1459.9	1443.8	1425.4	1402.7	1391.9
7.5°	1688.1	1699.8	1695.3	1680.3	1663.3	1649.6	1620.8	1593.9	1556.3	1523.3	1495.1
10°	1845.9	1833.5	1823.8	1809.3	1793.6	1768.2	1738.0	1696.5	1648.6	1610.8	1568.8
12.5°	1964.1	1962.0	1949.7	1934.7	1912.6	1888.6	1851.5	1800.9	1745.2	1690.7	1642.5
15°	2125.2	2128.4	2120.3	2104.7	2073.4	2030.8	1974.8	1953.8	1873.9	1814.7	1755.3
17.5°	2236.6	2236.0	2234.9	2213.3	2181.4	2151.0	2099.0	2043.8	1971.5	1887.9	1808.1
20°	2307.4	2302.0	2303.0	2278.8	2255.1	2220.0	2169.4	2089.1	2029.7	1933.2	1850.8
22.5°	2305.6	2304.5	2308.7	2300.3	2283.1	2256.3	2216.4	2148.6	2072.8	1975.5	1882.7
25°	2189.8	2185.6	2210.9	2217.9	2245.4	2250.2	2238.4	2201.2	2129.5	2029.2	1914.4
27.5°	1832.7	1830.3	1877.4	1936.3	2010.9	2068.9	2124.9	2152.0	2129.5	2057.7	1942.6
30°	1504.1	1554.8	1578.5	1663.7	1758.6	1871.8	1970.9	2065.3	2088.5	2057.2	1962.9
32.5°	1248.8	1293.0	1312.8	1385.9	1474.3	1606.9	1755.8	1889.4	1983.7	2007.6	1950.8
35°	949.9	950.5	995.7	1028.1	1110.0	1246.4	1390.9	1569.9	1747.8	1882.5	1896.6
37.5°	758.0	760.7	788.1	820.3	881.8	953.9	1081.1	1229.9	1435.4	1642.4	1763.6
40°	654.5	659.3	679.9	711.6	755.8	810.2	909.5	1049.6	1221.1	1451.3	1639.4
42.5°	588.0	596.0	606.5	631.0	658.4	709.3	789.6	897.9	1053.8	1271.5	1488.5
45°	506.8	511.0	519.2	530.4	555.2	590.9	644.8	717.6	846.9	1022.2	1239.4
47.5°	447.0	444.7	453.3	462.5	479.0	503.2	539.3	598.7	691.0	831.6	1015.9
50°	406.5	405.9	411.9	418.9	434.5	452.3	482.0	526.7	600.0	716.4	885.2
52.5°	368.5	370.6	374.8	383.5	394.8	409.2	435.8	468.0	531.0	631.5	772.2
55°	318.1	319.7	325.6	330.5	338.6	353.1	369.8	396.8	439.9	510.0	625.9
57.5°	275.4	274.6	280.4	281.5	290.7	302.5	315.4	336.4	367.7	419.8	497.8
60°	246.9	245.3	250.2	253.9	258.8	268.5	279.2	299.8	324.6	362.8	429.7
62.5°	221.0	220.3	223.9	227.6	231.6	240.4	249.5	265.2	284.9	317.1	370.2
65°	183.3	184.9	186.6	188.1	190.3	195.7	204.3	215.1	228.5	251.2	289.5
67.5°	144.0	145.7	146.2	149.6	154.2	157.6	162.8	172.4	181.8	200.9	222.7
70°	116.5	115.9	116.5	118.0	124.0	129.9	137.0	143.9	149.9	163.3	181.6
72.5°	100.1	99.1	100.5	100.8	103.7	105.4	109.8	116.4	124.0	133.2	146.3
75°	77.6	77.6	77.6	77.6	79.8	80.9	82.5	84.1	86.8	91.1	100.8
77.5°	57.4	57.4	58.2	58.8	59.2	59.8	60.8	62.4	63.4	65.7	69.9
80°	45.3	45.8	45.3	45.8	45.8	46.9	47.5	49.0	49.6	52.3	53.9
82.5°	34.1	33.7	34.1	34.6	34.6	35.7	35.8	37.0	37.1	38.5	40.1
85°	18.3	17.3	18.3	17.8	18.9	17.8	18.3	19.4	19.4	20.0	22.1
87.5°	11.5	12.2	11.2	11.6	11.5	11.7	11.6	11.3	12.0	11.3	11.1
90°	35.8	35.3	34.8	34.2	33.7	33.0	31.8	30.8	29.7	28.7	25.2
92.5°	48.2	48.6	48.9	49.2	49.5	49.3	48.4	47.5	46.7	45.9	43.9
95°	93.2	93.2	93.2	93.2	93.2	92.6	91.6	90.5	89.4	88.4	86.3
97.5°	143.4	143.5	143.5	143.7	143.8	143.2	142.0	140.8	139.6	138.3	136.8
100°	181.6	181.0	180.5	180.0	179.4	178.8	178.0	177.2	176.4	175.6	174.3
102.5°	220.8	220.9	220.9	221.1	221.2	220.9	220.1	219.3	218.5	217.6	215.9
105°	284.3	283.8	283.3	282.7	282.2	281.9	281.9	281.9	281.9	281.9	279.6
107.5°	350.5	350.8	351.1	351.4	351.7	351.5	350.6	349.8	349.0	348.1	347.1
110°	395.4	395.9	396.5	397.0	397.5	397.3	396.2	395.1	394.1	393.0	392.4



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	443.1	443.3	443.4	443.5	443.6	443.0	441.7	440.5	439.2	437.9	437.8
115°	508.9	509.1	509.5	509.7	509.9	509.9	509.7	509.5	509.1	508.9	509.5
117.5°	575.5	576.3	577.0	577.7	578.5	578.9	579.0	579.0	579.1	579.2	579.8
120°	622.3	622.9	623.4	624.0	624.5	624.9	625.2	625.4	625.7	626.0	627.2
122.5°	667.3	668.0	668.8	669.6	670.3	671.0	671.7	672.3	673.0	673.8	674.5
125°	734.7	735.7	736.8	737.8	738.9	740.0	741.0	742.1	743.1	744.3	744.7
127.5°	801.8	803.0	804.2	805.5	806.7	808.0	809.5	811.0	812.5	814.0	814.6
130°	845.7	847.6	849.5	851.4	853.2	854.7	855.7	856.7	857.9	858.9	859.7
132.5°	891.6	893.0	894.5	896.0	897.4	898.7	900.0	901.3	902.5	903.8	904.4
135°	962.8	963.4	963.8	964.4	965.0	965.7	966.8	967.9	968.9	970.0	970.3
137.5°	1025.6	1026.7	1027.7	1028.6	1029.7	1030.8	1031.9	1033.0	1034.1	1035.2	1034.5
140°	1066.8	1068.6	1070.5	1072.3	1074.2	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0
142.5°	1108.8	1110.2	1111.7	1113.1	1114.5	1115.4	1115.6	1115.9	1116.2	1116.4	1115.9
145°	1169.5	1170.5	1171.6	1172.7	1173.7	1174.4	1174.6	1174.9	1175.2	1175.4	1174.6
147.5°	1223.4	1225.0	1226.7	1228.3	1229.9	1230.7	1230.7	1230.7	1230.7	1230.7	1229.9
150°	1257.9	1259.5	1261.1	1262.7	1264.2	1265.0	1265.0	1265.0	1265.0	1265.0	1264.5
152.5°	1291.3	1292.7	1294.1	1295.5	1296.9	1297.4	1296.9	1296.5	1296.1	1295.6	1295.3
155°	1336.7	1338.6	1340.5	1342.3	1344.2	1344.6	1343.5	1342.4	1341.4	1340.3	1340.1
157.5°	1378.1	1379.5	1381.0	1382.5	1384.0	1384.2	1383.1	1382.0	1380.9	1379.7	1379.5
160°	1404.8	1405.9	1406.9	1408.0	1409.1	1408.9	1407.6	1406.3	1404.9	1403.6	1403.6
162.5°	1424.9	1426.6	1428.3	1430.0	1431.7	1431.9	1430.5	1429.2	1427.9	1426.6	1426.3
165°	1453.8	1455.6	1457.5	1459.4	1461.3	1461.3	1459.8	1458.2	1456.6	1455.0	1455.0
167.5°	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4	1478.2
170°	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8	1490.8
172.5°	1500.4	1502.2	1504.1	1505.9	1507.8	1507.9	1506.3	1504.6	1503.0	1501.3	1501.3
175°	1511.2	1513.0	1514.8	1516.7	1518.5	1518.7	1517.1	1515.5	1513.9	1512.4	1512.4
177.5°	1516.9	1518.4	1519.8	1521.3	1522.8	1522.9	1521.6	1520.4	1519.1	1517.8	1517.8
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1300.3	1299.0	1293.0	1286.1	1277.0	1271.0	1266.2	1263.7	1255.9	1246.4	1239.9
5°	1380.6	1364.5	1347.3	1326.2	1306.8	1286.8	1274.5	1259.9	1242.1	1222.2	1208.2
7.5°	1466.7	1435.0	1400.8	1365.6	1330.7	1299.5	1271.8	1248.2	1219.9	1191.3	1171.2
10°	1532.7	1486.3	1438.4	1389.3	1344.5	1302.5	1270.1	1238.3	1204.4	1171.5	1146.7
12.5°	1592.6	1531.6	1476.3	1416.0	1358.8	1308.5	1261.9	1224.6	1183.7	1148.6	1120.4
15°	1668.5	1606.0	1539.1	1447.5	1371.5	1307.9	1251.3	1202.2	1152.6	1109.5	1082.0
17.5°	1739.5	1645.4	1555.5	1479.1	1380.3	1300.8	1231.8	1173.1	1118.6	1072.9	1039.1
20°	1768.8	1677.7	1580.1	1482.6	1385.5	1296.6	1216.2	1151.5	1095.0	1043.1	1011.9
22.5°	1786.5	1683.3	1580.6	1475.7	1372.5	1280.2	1200.7	1129.6	1068.2	1019.0	980.4
25°	1807.0	1684.2	1571.0	1467.4	1362.3	1262.0	1167.7	1092.3	1026.0	973.6	932.6
27.5°	1820.7	1676.1	1542.3	1427.2	1320.6	1220.8	1134.2	1054.2	987.0	931.7	887.7
30°	1823.3	1669.6	1520.3	1395.7	1287.4	1195.7	1104.1	1027.5	956.4	897.6	856.7
32.5°	1826.7	1653.7	1490.5	1358.2	1247.3	1156.5	1073.5	1000.4	927.5	869.6	827.8
35°	1812.5	1644.8	1445.3	1293.3	1182.3	1094.4	1019.5	952.0	880.4	824.3	781.7
37.5°	1751.2	1609.8	1398.5	1220.2	1104.1	1022.7	961.6	902.9	837.1	776.7	736.5
40°	1689.6	1575.3	1362.3	1175.8	1054.5	970.9	915.9	868.0	804.4	747.7	704.6
42.5°	1597.7	1528.3	1327.9	1129.2	998.4	917.9	871.5	826.6	770.7	713.2	672.7
45°	1429.2	1438.4	1257.2	1055.0	920.8	840.0	796.2	765.0	715.4	668.0	626.5
47.5°	1217.8	1303.5	1174.3	976.0	838.9	763.0	724.8	697.6	664.2	617.6	579.7
50°	1079.8	1202.2	1107.9	923.0	787.7	712.2	674.4	652.3	623.2	586.5	550.4
52.5°	952.6	1084.0	1027.6	863.9	732.0	663.0	626.1	607.9	584.8	550.3	517.6
55°	776.8	910.0	897.1	774.7	648.6	586.5	558.5	538.1	522.4	496.5	470.6
57.5°	628.4	754.6	761.3	675.5	575.0	513.7	489.6	474.2	464.0	444.4	420.5
60°	534.8	650.7	673.4	608.6	522.4	468.5	444.7	432.4	424.3	408.6	390.3
62.5°	457.2	555.8	581.5	534.9	471.9	421.4	402.9	390.9	385.5	372.0	355.8
65°	349.9	431.8	456.6	430.7	397.8	357.4	342.3	332.1	327.3	319.7	307.8
67.5°	263.1	322.8	350.0	331.8	319.9	294.4	284.8	279.2	275.0	269.7	259.8
70°	211.4	255.6	283.6	278.7	269.0	255.6	248.5	244.8	240.4	236.1	227.5
72.5°	169.9	200.3	226.6	229.1	221.2	218.5	212.3	210.7	208.1	203.0	198.2
75°	112.6	133.7	152.0	159.1	162.2	164.9	162.2	161.8	161.2	156.9	154.2
77.5°	73.8	85.2	96.7	108.7	113.8	117.4	118.3	120.3	118.8	116.5	115.3
80°	56.6	59.3	67.4	77.6	85.7	89.0	91.1	92.2	91.7	91.1	89.0
82.5°	41.1	43.3	47.1	54.3	61.2	66.5	67.8	67.6	68.8	69.1	67.4
85°	22.1	22.7	23.7	24.8	28.6	34.5	36.1	37.2	38.3	38.3	35.0
87.5°	11.2	10.1	10.3	9.7	10.5	10.4	12.4	14.0	15.0	13.8	14.3
90°	21.8	18.3	14.9	11.8	9.2	6.5	3.9	1.2	3.9	6.5	9.2
92.5°	41.9	40.0	38.0	36.1	34.3	32.5	30.7	28.9	30.7	32.5	34.3
95°	84.1	82.0	79.9	78.0	76.0	74.2	72.3	70.5	72.3	74.2	76.0
97.5°	135.2	133.7	132.1	130.7	129.4	127.9	126.6	125.2	126.6	127.9	129.4
100°	172.9	171.6	170.3	168.8	167.2	165.6	164.1	162.5	164.1	165.6	167.2
102.5°	214.1	212.4	210.6	209.3	208.3	207.4	206.4	205.5	206.4	207.4	208.3
105°	277.1	274.7	272.4	270.9	270.4	269.8	269.3	268.8	269.3	269.8	270.4
107.5°	346.2	345.2	344.3	343.6	343.3	343.0	342.7	342.4	342.7	343.0	343.3
110°	392.0	391.4	390.9	390.4	389.8	389.3	388.8	388.2	388.8	389.3	389.8



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	437.7	437.6	437.5	437.3	437.0	436.7	436.3	436.0	436.3	436.7	437.0
115°	509.9	510.5	511.0	510.9	510.1	509.3	508.5	507.7	508.5	509.3	510.1
117.5°	580.5	581.2	581.9	581.9	581.5	580.9	580.4	579.9	580.4	580.9	581.5
120°	628.6	629.9	631.3	631.1	629.5	628.0	626.4	624.8	626.4	628.0	629.5
122.5°	675.1	675.8	676.5	676.3	675.1	673.9	672.7	671.6	672.7	673.9	675.1
125°	745.3	745.8	746.3	746.2	745.4	744.7	743.8	743.0	743.8	744.7	745.4
127.5°	815.2	815.7	816.3	815.8	814.0	812.4	810.6	809.0	810.6	812.4	814.0
130°	860.5	861.3	862.1	861.4	859.3	857.1	855.1	852.9	855.1	857.1	859.3
132.5°	905.0	905.5	906.2	905.4	903.2	901.1	899.0	896.9	899.0	901.1	903.2
135°	970.5	970.8	971.1	970.4	968.8	967.2	965.6	964.0	965.6	967.2	968.8
137.5°	1033.8	1033.2	1032.5	1031.4	1030.2	1028.8	1027.5	1026.1	1027.5	1028.8	1030.2
140°	1075.8	1075.5	1075.2	1074.4	1073.1	1071.8	1070.5	1069.1	1070.5	1071.8	1073.1
142.5°	1115.5	1115.0	1114.5	1113.6	1112.3	1111.0	1109.6	1108.3	1109.6	1111.0	1112.3
145°	1173.9	1173.1	1172.3	1171.6	1171.1	1170.5	1170.1	1169.5	1170.1	1170.5	1171.1
147.5°	1229.2	1228.4	1227.6	1226.9	1225.9	1224.9	1223.9	1223.0	1223.9	1224.9	1225.9
150°	1264.0	1263.5	1262.9	1262.4	1261.9	1261.3	1260.8	1260.3	1260.8	1261.3	1261.9
152.5°	1295.0	1294.7	1294.3	1293.8	1293.1	1292.4	1291.6	1290.9	1291.6	1292.4	1293.1
155°	1339.7	1339.5	1339.3	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1
157.5°	1379.3	1379.1	1378.9	1379.0	1379.3	1379.6	1379.9	1380.2	1379.9	1379.6	1379.3
160°	1403.6	1403.6	1403.6	1403.9	1404.4	1404.9	1405.5	1406.0	1405.5	1404.9	1404.4
162.5°	1426.2	1425.9	1425.7	1426.0	1426.7	1427.4	1428.2	1428.9	1428.2	1427.4	1426.7
165°	1455.0	1455.0	1455.0	1455.4	1456.2	1457.0	1457.8	1458.6	1457.8	1457.0	1456.2
167.5°	1478.0	1477.7	1477.6	1478.0	1479.0	1480.1	1481.1	1482.3	1481.1	1480.1	1479.0
170°	1490.8	1490.8	1490.8	1491.4	1492.4	1493.5	1494.5	1495.6	1494.5	1493.5	1492.4
172.5°	1501.3	1501.3	1501.3	1501.9	1502.9	1504.0	1505.1	1506.1	1505.1	1504.0	1502.9
175°	1512.4	1512.4	1512.4	1512.8	1513.9	1515.0	1516.1	1517.1	1516.1	1515.0	1513.9
177.5°	1517.8	1517.8	1517.8	1518.2	1519.1	1520.0	1520.8	1521.6	1520.8	1520.0	1519.1
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1237.8	1232.2	1228.3	1219.6	1214.1	1208.0	1202.0	1205.9	1205.5	1205.0	1205.0
5°	1196.3	1183.8	1172.6	1158.0	1148.8	1137.5	1128.9	1127.8	1130.0	1122.4	1118.1
7.5°	1155.1	1138.1	1122.1	1106.0	1089.0	1075.4	1066.9	1062.9	1057.4	1052.7	1047.9
10°	1126.2	1106.3	1090.6	1070.6	1052.3	1036.2	1026.0	1018.9	1015.1	1011.4	1004.3
12.5°	1096.5	1076.9	1057.0	1034.4	1017.0	998.2	990.5	982.7	975.5	971.2	961.6
15°	1052.9	1027.5	1006.5	982.8	963.4	945.1	934.3	918.6	916.5	911.1	901.4
17.5°	1009.2	981.7	952.7	935.2	913.2	894.1	877.7	872.5	857.1	851.3	842.8
20°	974.7	949.4	927.2	904.1	872.3	854.4	841.5	834.6	822.1	814.6	809.2
22.5°	944.9	919.2	893.7	866.6	840.3	820.4	811.0	800.0	793.2	782.7	776.8
25°	902.5	874.4	843.7	814.6	795.7	780.6	765.6	755.8	746.2	741.2	730.5
27.5°	853.1	823.8	795.0	772.9	749.8	734.9	721.2	712.6	700.9	692.8	686.8
30°	825.9	791.4	766.6	746.6	717.0	703.0	692.8	682.0	673.4	664.7	658.8
32.5°	794.4	763.0	739.4	714.8	692.0	676.7	663.5	653.9	646.6	638.4	632.5
35°	745.0	718.7	694.3	669.6	652.8	637.2	621.6	613.5	606.5	599.0	593.6
37.5°	700.4	675.7	652.7	629.2	608.4	595.7	583.1	576.9	567.4	562.4	556.9
40°	672.8	648.6	623.8	601.1	579.6	569.8	558.5	549.4	540.7	536.9	531.0
42.5°	642.6	618.4	597.5	573.1	555.4	542.2	531.8	521.7	515.3	509.8	506.4
45°	597.9	576.3	555.8	531.6	514.8	503.5	491.6	482.5	476.6	472.8	466.8
47.5°	554.4	532.8	512.1	490.9	474.8	461.8	450.0	443.5	435.7	431.1	427.1
50°	522.9	503.5	481.4	462.0	445.8	432.9	423.2	415.1	408.1	402.2	399.5
52.5°	494.0	473.3	454.2	436.2	419.1	404.4	395.6	387.1	381.8	375.0	371.9
55°	446.4	426.4	410.3	392.4	375.7	363.4	352.6	345.0	339.6	332.1	327.8
57.5°	401.6	383.7	364.4	349.0	331.8	321.3	312.4	302.1	295.6	289.6	285.4
60°	371.5	350.9	334.2	319.7	304.6	291.1	283.0	275.0	267.9	262.0	258.3
62.5°	339.9	322.1	306.2	290.3	276.6	264.8	255.4	248.7	242.5	238.7	235.0
65°	291.7	277.7	261.5	248.5	235.6	227.0	219.4	213.5	209.1	206.4	203.3
67.5°	247.2	233.6	219.5	206.8	198.2	191.6	186.6	181.6	179.4	175.9	173.8
70°	218.3	204.3	191.9	182.2	173.6	168.7	165.5	161.8	159.5	155.3	153.1
72.5°	186.9	176.7	167.8	159.8	152.9	148.5	144.3	139.7	136.3	131.5	129.4
75°	147.2	138.0	131.0	125.6	121.3	115.3	109.4	104.6	103.0	101.3	100.8
77.5°	109.0	103.2	98.2	93.6	88.2	83.9	82.6	81.5	81.2	80.3	80.3
80°	85.7	80.3	76.5	71.1	67.9	67.9	67.9	66.9	67.4	67.4	67.4
82.5°	63.7	58.8	56.7	54.7	54.1	54.6	54.6	54.7	54.4	55.3	54.9
85°	32.9	33.4	34.5	34.0	34.5	34.5	35.6	35.0	35.6	34.5	35.6
87.5°	14.4	16.3	17.4	18.6	19.7	20.0	20.6	20.8	21.5	21.7	21.9
90°	11.8	14.9	18.3	21.8	25.2	28.7	29.7	30.8	31.8	33.0	33.7
92.5°	36.1	38.0	40.0	41.9	43.9	45.9	46.7	47.5	48.4	49.3	49.5
95°	78.0	79.9	82.0	84.1	86.3	88.4	89.4	90.5	91.6	92.6	93.2
97.5°	130.7	132.1	133.7	135.2	136.8	138.3	139.6	140.8	142.0	143.2	143.8
100°	168.8	170.3	171.6	172.9	174.3	175.6	176.4	177.2	178.0	178.8	179.4
102.5°	209.3	210.6	212.4	214.1	215.9	217.6	218.5	219.3	220.1	220.9	221.2
105°	270.9	272.4	274.7	277.1	279.6	281.9	281.9	281.9	281.9	281.9	282.2
107.5°	343.6	344.3	345.2	346.2	347.1	348.1	349.0	349.8	350.6	351.5	351.7
110°	390.4	390.9	391.4	392.0	392.4	393.0	394.1	395.1	396.2	397.3	397.5



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	437.3	437.5	437.6	437.7	437.8	437.9	439.2	440.5	441.7	443.0	443.6
115°	510.9	511.0	510.5	509.9	509.5	508.9	509.1	509.5	509.7	509.9	509.9
117.5°	581.9	581.9	581.2	580.5	579.8	579.2	579.1	579.0	579.0	578.9	578.5
120°	631.1	631.3	629.9	628.6	627.2	626.0	625.7	625.4	625.2	624.9	624.5
122.5°	676.3	676.5	675.8	675.1	674.5	673.8	673.0	672.3	671.7	671.0	670.3
125°	746.2	746.3	745.8	745.3	744.7	744.3	743.1	742.1	741.0	740.0	738.9
127.5°	815.8	816.3	815.7	815.2	814.6	814.0	812.5	811.0	809.5	808.0	806.7
130°	861.4	862.1	861.3	860.5	859.7	858.9	857.9	856.7	855.7	854.7	853.2
132.5°	905.4	906.2	905.5	905.0	904.4	903.8	902.5	901.3	900.0	898.7	897.4
135°	970.4	971.1	970.8	970.5	970.3	970.0	968.9	967.9	966.8	965.7	965.0
137.5°	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1	1033.0	1031.9	1030.8	1029.7
140°	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0	1075.8	1075.5	1075.2	1074.2
142.5°	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2	1115.9	1115.6	1115.4	1114.5
145°	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2	1174.9	1174.6	1174.4	1173.7
147.5°	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7	1230.7	1230.7	1230.7	1229.9
150°	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0	1265.0	1265.0	1265.0	1264.2
152.5°	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1	1296.5	1296.9	1297.4	1296.9
155°	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4	1342.4	1343.5	1344.6	1344.2
157.5°	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9	1382.0	1383.1	1384.2	1384.0
160°	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9	1406.3	1407.6	1408.9	1409.1
162.5°	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9	1429.2	1430.5	1431.9	1431.7
165°	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6	1458.2	1459.8	1461.3	1461.3
167.5°	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9
170°	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3
172.5°	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0	1504.6	1506.3	1507.9	1507.8
175°	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9	1515.5	1517.1	1518.7	1518.5
177.5°	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1	1520.4	1521.6	1522.9	1522.8
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1199.8	1199.4	1199.8	1198.1	1199.8	1199.4	1199.8	1205.0	1205.0	1205.5	1205.9
5°	1116.5	1115.9	1114.4	1109.5	1114.4	1115.9	1116.5	1118.1	1122.4	1130.0	1127.8
7.5°	1043.7	1043.0	1038.2	1038.3	1038.2	1043.0	1043.7	1047.9	1052.7	1057.4	1062.9
10°	1000.6	1001.1	994.7	990.9	994.7	1001.1	1000.6	1004.3	1011.4	1015.1	1018.9
12.5°	958.8	956.2	951.1	946.9	951.1	956.2	958.8	961.6	971.2	975.5	982.7
15°	903.6	898.2	885.2	886.3	885.2	898.2	903.6	901.4	911.1	916.5	918.6
17.5°	838.5	834.6	834.3	826.8	834.3	834.6	838.5	842.8	851.3	857.1	872.5
20°	800.6	797.9	798.9	791.4	798.9	797.9	800.6	809.2	814.6	822.1	834.6
22.5°	770.8	768.1	763.6	761.2	763.6	768.1	770.8	776.8	782.7	793.2	800.0
25°	727.2	722.9	718.7	721.4	718.7	722.9	727.2	730.5	741.2	746.2	755.8
27.5°	683.7	680.5	676.1	675.6	676.1	680.5	683.7	686.8	692.8	700.9	712.6
30°	656.1	652.8	650.7	648.0	650.7	652.8	656.1	658.8	664.7	673.4	682.0
32.5°	628.0	627.4	623.5	623.0	623.5	627.4	628.0	632.5	638.4	646.6	653.9
35°	591.4	588.2	587.1	587.6	587.1	588.2	591.4	593.6	599.0	606.5	613.5
37.5°	556.6	552.2	550.3	548.3	550.3	552.2	556.6	556.9	562.4	567.4	576.9
40°	531.6	527.3	526.2	525.1	526.2	527.3	531.6	531.0	536.9	540.7	549.4
42.5°	503.5	501.8	501.1	499.2	501.1	501.8	503.5	506.4	509.8	515.3	521.7
45°	465.2	464.7	461.4	462.6	461.4	464.7	465.2	466.8	472.8	476.6	482.5
47.5°	424.9	422.6	420.3	421.8	420.3	422.6	424.9	427.1	431.1	435.7	443.5
50°	397.4	396.2	391.4	392.4	391.4	396.2	397.4	399.5	402.2	408.1	415.1
52.5°	369.7	365.6	363.8	363.1	363.8	365.6	369.7	371.9	375.0	381.8	387.1
55°	324.0	319.2	317.0	315.9	317.0	319.2	324.0	327.8	332.1	339.6	345.0
57.5°	279.2	277.8	276.2	277.3	276.2	277.8	279.2	285.4	289.6	295.6	302.1
60°	252.9	252.9	252.9	252.3	252.9	252.9	252.9	258.3	262.0	267.9	275.0
62.5°	232.6	231.2	230.8	231.6	230.8	231.2	232.6	235.0	238.7	242.5	248.7
65°	201.6	201.1	198.9	198.4	198.9	201.1	201.6	203.3	206.4	209.1	213.5
67.5°	172.4	170.5	169.8	169.1	169.8	170.5	172.4	173.8	175.9	179.4	181.6
70°	150.4	149.3	146.1	146.6	146.1	149.3	150.4	153.1	155.3	159.5	161.8
72.5°	126.7	125.6	124.9	124.2	124.9	125.6	126.7	129.4	131.5	136.3	139.7
75°	100.3	99.7	99.2	101.3	99.2	99.7	100.3	100.8	101.3	103.0	104.6
77.5°	80.3	80.3	80.6	79.8	80.6	80.3	80.3	80.3	80.3	81.2	81.5
80°	67.4	67.4	66.9	66.9	66.9	67.4	67.4	67.4	67.4	67.4	66.9
82.5°	54.0	54.4	54.7	53.9	54.7	54.4	54.0	54.9	55.3	54.4	54.7
85°	35.6	35.0	36.1	35.6	36.1	35.0	35.6	35.6	34.5	35.6	35.0
87.5°	22.8	22.0	22.2	22.7	22.2	22.0	22.8	21.9	21.7	21.5	20.8
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	33.0	31.8	30.8
92.5°	49.2	48.9	48.6	48.2	48.6	48.9	49.2	49.5	49.3	48.4	47.5
95°	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2	92.6	91.6	90.5
97.5°	143.7	143.5	143.5	143.4	143.5	143.5	143.7	143.8	143.2	142.0	140.8
100°	180.0	180.5	181.0	181.6	181.0	180.5	180.0	179.4	178.8	178.0	177.2
102.5°	221.1	220.9	220.9	220.8	220.9	220.9	221.1	221.2	220.9	220.1	219.3
105°	282.7	283.3	283.8	284.3	283.8	283.3	282.7	282.2	281.9	281.9	281.9
107.5°	351.4	351.1	350.8	350.5	350.8	351.1	351.4	351.7	351.5	350.6	349.8
110°	397.0	396.5	395.9	395.4	395.9	396.5	397.0	397.5	397.3	396.2	395.1



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	443.5	443.4	443.3	443.1	443.3	443.4	443.5	443.6	443.0	441.7	440.5
115°	509.7	509.5	509.1	508.9	509.1	509.5	509.7	509.9	509.9	509.7	509.5
117.5°	577.7	577.0	576.3	575.5	576.3	577.0	577.7	578.5	578.9	579.0	579.0
120°	624.0	623.4	622.9	622.3	622.9	623.4	624.0	624.5	624.9	625.2	625.4
122.5°	669.6	668.8	668.0	667.3	668.0	668.8	669.6	670.3	671.0	671.7	672.3
125°	737.8	736.8	735.7	734.7	735.7	736.8	737.8	738.9	740.0	741.0	742.1
127.5°	805.5	804.2	803.0	801.8	803.0	804.2	805.5	806.7	808.0	809.5	811.0
130°	851.4	849.5	847.6	845.7	847.6	849.5	851.4	853.2	854.7	855.7	856.7
132.5°	896.0	894.5	893.0	891.6	893.0	894.5	896.0	897.4	898.7	900.0	901.3
135°	964.4	963.8	963.4	962.8	963.4	963.8	964.4	965.0	965.7	966.8	967.9
137.5°	1028.6	1027.7	1026.7	1025.6	1026.7	1027.7	1028.6	1029.7	1030.8	1031.9	1033.0
140°	1072.3	1070.5	1068.6	1066.8	1068.6	1070.5	1072.3	1074.2	1075.2	1075.5	1075.8
142.5°	1113.1	1111.7	1110.2	1108.8	1110.2	1111.7	1113.1	1114.5	1115.4	1115.6	1115.9
145°	1172.7	1171.6	1170.5	1169.5	1170.5	1171.6	1172.7	1173.7	1174.4	1174.6	1174.9
147.5°	1228.3	1226.7	1225.0	1223.4	1225.0	1226.7	1228.3	1229.9	1230.7	1230.7	1230.7
150°	1262.7	1261.1	1259.5	1257.9	1259.5	1261.1	1262.7	1264.2	1265.0	1265.0	1265.0
152.5°	1295.5	1294.1	1292.7	1291.3	1292.7	1294.1	1295.5	1296.9	1297.4	1296.9	1296.5
155°	1342.3	1340.5	1338.6	1336.7	1338.6	1340.5	1342.3	1344.2	1344.6	1343.5	1342.4
157.5°	1382.5	1381.0	1379.5	1378.1	1379.5	1381.0	1382.5	1384.0	1384.2	1383.1	1382.0
160°	1408.0	1406.9	1405.9	1404.8	1405.9	1406.9	1408.0	1409.1	1408.9	1407.6	1406.3
162.5°	1430.0	1428.3	1426.6	1424.9	1426.6	1428.3	1430.0	1431.7	1431.9	1430.5	1429.2
165°	1459.4	1457.5	1455.6	1453.8	1455.6	1457.5	1459.4	1461.3	1461.3	1459.8	1458.2
167.5°	1483.4	1481.7	1480.0	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7
170°	1496.4	1494.5	1492.7	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5
172.5°	1505.9	1504.1	1502.2	1500.4	1502.2	1504.1	1505.9	1507.8	1507.9	1506.3	1504.6
175°	1516.7	1514.8	1513.0	1511.2	1513.0	1514.8	1516.7	1518.5	1518.7	1517.1	1515.5
177.5°	1521.3	1519.8	1518.4	1516.9	1518.4	1519.8	1521.3	1522.8	1522.9	1521.6	1520.4
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1202.0	1208.0	1214.1	1219.6	1228.3	1232.2	1237.8	1239.9	1246.4	1255.9	1263.7
5°	1128.9	1137.5	1148.8	1158.0	1172.6	1183.8	1196.3	1208.2	1222.2	1242.1	1259.9
7.5°	1066.9	1075.4	1089.0	1106.0	1122.1	1138.1	1155.1	1171.2	1191.3	1219.9	1248.2
10°	1026.0	1036.2	1052.3	1070.6	1090.6	1106.3	1126.2	1146.7	1171.5	1204.4	1238.3
12.5°	990.5	998.2	1017.0	1034.4	1057.0	1076.9	1096.5	1120.4	1148.6	1183.7	1224.6
15°	934.3	945.1	963.4	982.8	1006.5	1027.5	1052.9	1082.0	1109.5	1152.6	1202.2
17.5°	877.7	894.1	913.2	935.2	952.7	981.7	1009.2	1039.1	1072.9	1118.6	1173.1
20°	841.5	854.4	872.3	904.1	927.2	949.4	974.7	1011.9	1043.1	1095.0	1151.5
22.5°	811.0	820.4	840.3	866.6	893.7	919.2	944.9	980.4	1019.0	1068.2	1129.6
25°	765.6	780.6	795.7	814.6	843.7	874.4	902.5	932.6	973.6	1026.0	1092.3
27.5°	721.2	734.9	749.8	772.9	795.0	823.8	853.1	887.7	931.7	987.0	1054.2
30°	692.8	703.0	717.0	746.6	766.6	791.4	825.9	856.7	897.6	956.4	1027.5
32.5°	663.5	676.7	692.0	714.8	739.4	763.0	794.4	827.8	869.6	927.5	1000.4
35°	621.6	637.2	652.8	669.6	694.3	718.7	745.0	781.7	824.3	880.4	952.0
37.5°	583.1	595.7	608.4	629.2	652.7	675.7	700.4	736.5	776.7	837.1	902.9
40°	558.5	569.8	579.6	601.1	623.8	648.6	672.8	704.6	747.7	804.4	868.0
42.5°	531.8	542.2	555.4	573.1	597.5	618.4	642.6	672.7	713.2	770.7	826.6
45°	491.6	503.5	514.8	531.6	555.8	576.3	597.9	626.5	668.0	715.4	765.0
47.5°	450.0	461.8	474.8	490.9	512.1	532.8	554.4	579.7	617.6	664.2	697.6
50°	423.2	432.9	445.8	462.0	481.4	503.5	522.9	550.4	586.5	623.2	652.3
52.5°	395.6	404.4	419.1	436.2	454.2	473.3	494.0	517.6	550.3	584.8	607.9
55°	352.6	363.4	375.7	392.4	410.3	426.4	446.4	470.6	496.5	522.4	538.1
57.5°	312.4	321.3	331.8	349.0	364.4	383.7	401.6	420.5	444.4	464.0	474.2
60°	283.0	291.1	304.6	319.7	334.2	350.9	371.5	390.3	408.6	424.3	432.4
62.5°	255.4	264.8	276.6	290.3	306.2	322.1	339.9	355.8	372.0	385.5	390.9
65°	219.4	227.0	235.6	248.5	261.5	277.7	291.7	307.8	319.7	327.3	332.1
67.5°	186.6	191.6	198.2	206.8	219.5	233.6	247.2	259.8	269.7	275.0	279.2
70°	165.5	168.7	173.6	182.2	191.9	204.3	218.3	227.5	236.1	240.4	244.8
72.5°	144.3	148.5	152.9	159.8	167.8	176.7	186.9	198.2	203.0	208.1	210.7
75°	109.4	115.3	121.3	125.6	131.0	138.0	147.2	154.2	156.9	161.2	161.8
77.5°	82.6	83.9	88.2	93.6	98.2	103.2	109.0	115.3	116.5	118.8	120.3
80°	67.9	67.9	67.9	71.1	76.5	80.3	85.7	89.0	91.1	91.7	92.2
82.5°	54.6	54.6	54.1	54.7	56.7	58.8	63.7	67.4	69.1	68.8	67.6
85°	35.6	34.5	34.5	34.0	34.5	33.4	32.9	35.0	38.3	38.3	37.2
87.5°	20.6	20.0	19.7	18.6	17.4	16.3	14.4	14.3	13.8	15.0	14.0
90°	29.7	28.7	25.2	21.8	18.3	14.9	11.8	9.2	6.5	3.9	1.2
92.5°	46.7	45.9	43.9	41.9	40.0	38.0	36.1	34.3	32.5	30.7	28.9
95°	89.4	88.4	86.3	84.1	82.0	79.9	78.0	76.0	74.2	72.3	70.5
97.5°	139.6	138.3	136.8	135.2	133.7	132.1	130.7	129.4	127.9	126.6	125.2
100°	176.4	175.6	174.3	172.9	171.6	170.3	168.8	167.2	165.6	164.1	162.5
102.5°	218.5	217.6	215.9	214.1	212.4	210.6	209.3	208.3	207.4	206.4	205.5
105°	281.9	281.9	279.6	277.1	274.7	272.4	270.9	270.4	269.8	269.3	268.8
107.5°	349.0	348.1	347.1	346.2	345.2	344.3	343.6	343.3	343.0	342.7	342.4
110°	394.1	393.0	392.4	392.0	391.4	390.9	390.4	389.8	389.3	388.8	388.2



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	439.2	437.9	437.8	437.7	437.6	437.5	437.3	437.0	436.7	436.3	436.0
115°	509.1	508.9	509.5	509.9	510.5	511.0	510.9	510.1	509.3	508.5	507.7
117.5°	579.1	579.2	579.8	580.5	581.2	581.9	581.9	581.5	580.9	580.4	579.9
120°	625.7	626.0	627.2	628.6	629.9	631.3	631.1	629.5	628.0	626.4	624.8
122.5°	673.0	673.8	674.5	675.1	675.8	676.5	676.3	675.1	673.9	672.7	671.6
125°	743.1	744.3	744.7	745.3	745.8	746.3	746.2	745.4	744.7	743.8	743.0
127.5°	812.5	814.0	814.6	815.2	815.7	816.3	815.8	814.0	812.4	810.6	809.0
130°	857.9	858.9	859.7	860.5	861.3	862.1	861.4	859.3	857.1	855.1	852.9
132.5°	902.5	903.8	904.4	905.0	905.5	906.2	905.4	903.2	901.1	899.0	896.9
135°	968.9	970.0	970.3	970.5	970.8	971.1	970.4	968.8	967.2	965.6	964.0
137.5°	1034.1	1035.2	1034.5	1033.8	1033.2	1032.5	1031.4	1030.2	1028.8	1027.5	1026.1
140°	1076.0	1076.3	1076.0	1075.8	1075.5	1075.2	1074.4	1073.1	1071.8	1070.5	1069.1
142.5°	1116.2	1116.4	1115.9	1115.5	1115.0	1114.5	1113.6	1112.3	1111.0	1109.6	1108.3
145°	1175.2	1175.4	1174.6	1173.9	1173.1	1172.3	1171.6	1171.1	1170.5	1170.1	1169.5
147.5°	1230.7	1230.7	1229.9	1229.2	1228.4	1227.6	1226.9	1225.9	1224.9	1223.9	1223.0
150°	1265.0	1265.0	1264.5	1264.0	1263.5	1262.9	1262.4	1261.9	1261.3	1260.8	1260.3
152.5°	1296.1	1295.6	1295.3	1295.0	1294.7	1294.3	1293.8	1293.1	1292.4	1291.6	1290.9
155°	1341.4	1340.3	1340.1	1339.7	1339.5	1339.3	1339.1	1339.1	1339.1	1339.1	1339.1
157.5°	1380.9	1379.7	1379.5	1379.3	1379.1	1378.9	1379.0	1379.3	1379.6	1379.9	1380.2
160°	1404.9	1403.6	1403.6	1403.6	1403.6	1403.6	1403.9	1404.4	1404.9	1405.5	1406.0
162.5°	1427.9	1426.6	1426.3	1426.2	1425.9	1425.7	1426.0	1426.7	1427.4	1428.2	1428.9
165°	1456.6	1455.0	1455.0	1455.0	1455.0	1455.0	1455.4	1456.2	1457.0	1457.8	1458.6
167.5°	1480.0	1478.4	1478.2	1478.0	1477.7	1477.6	1478.0	1479.0	1480.1	1481.1	1482.3
170°	1492.7	1490.8	1490.8	1490.8	1490.8	1490.8	1491.4	1492.4	1493.5	1494.5	1495.6
172.5°	1503.0	1501.3	1501.3	1501.3	1501.3	1501.3	1501.9	1502.9	1504.0	1505.1	1506.1
175°	1513.9	1512.4	1512.4	1512.4	1512.4	1512.4	1512.8	1513.9	1515.0	1516.1	1517.1
177.5°	1519.1	1517.8	1517.8	1517.8	1517.8	1517.8	1518.2	1519.1	1520.0	1520.8	1521.6
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1266.2	1271.0	1277.0	1286.1	1293.0	1299.0	1300.3	1302.0	1306.4	1313.7	1319.3
5°	1274.5	1286.8	1306.8	1326.2	1347.3	1364.5	1380.6	1391.9	1402.7	1425.4	1443.8
7.5°	1271.8	1299.5	1330.7	1365.6	1400.8	1435.0	1466.7	1495.1	1523.3	1556.3	1593.9
10°	1270.1	1302.5	1344.5	1389.3	1438.4	1486.3	1532.7	1568.8	1610.8	1648.6	1696.5
12.5°	1261.9	1308.5	1358.8	1416.0	1476.3	1531.6	1592.6	1642.5	1690.7	1745.2	1800.9
15°	1251.3	1307.9	1371.5	1447.5	1539.1	1606.0	1668.5	1755.3	1814.7	1873.9	1953.8
17.5°	1231.8	1300.8	1380.3	1479.1	1555.5	1645.4	1739.5	1808.1	1887.9	1971.5	2043.8
20°	1216.2	1296.6	1385.5	1482.6	1580.1	1677.7	1768.8	1850.8	1933.2	2029.7	2089.1
22.5°	1200.7	1280.2	1372.5	1475.7	1580.6	1683.3	1786.5	1882.7	1975.5	2072.8	2148.6
25°	1167.7	1262.0	1362.3	1467.4	1571.0	1684.2	1807.0	1914.4	2029.2	2129.5	2201.2
27.5°	1134.2	1220.8	1320.6	1427.2	1542.3	1676.1	1820.7	1942.6	2057.7	2129.5	2152.0
30°	1104.1	1195.7	1287.4	1395.7	1520.3	1669.6	1823.3	1962.9	2057.2	2088.5	2065.3
32.5°	1073.5	1156.5	1247.3	1358.2	1490.5	1653.7	1826.7	1950.8	2007.6	1983.7	1889.4
35°	1019.5	1094.4	1182.3	1293.3	1445.3	1644.8	1812.5	1896.6	1882.5	1747.8	1569.9
37.5°	961.6	1022.7	1104.1	1220.2	1398.5	1609.8	1751.2	1763.6	1642.4	1435.4	1229.9
40°	915.9	970.9	1054.5	1175.8	1362.3	1575.3	1689.6	1639.4	1451.3	1221.1	1049.6
42.5°	871.5	917.9	998.4	1129.2	1327.9	1528.3	1597.7	1488.5	1271.5	1053.8	897.9
45°	796.2	840.0	920.8	1055.0	1257.2	1438.4	1429.2	1239.4	1022.2	846.9	717.6
47.5°	724.8	763.0	838.9	976.0	1174.3	1303.5	1217.8	1015.9	831.6	691.0	598.7
50°	674.4	712.2	787.7	923.0	1107.9	1202.2	1079.8	885.2	716.4	600.0	526.7
52.5°	626.1	663.0	732.0	863.9	1027.6	1084.0	952.6	772.2	631.5	531.0	468.0
55°	558.5	586.5	648.6	774.7	897.1	910.0	776.8	625.9	510.0	439.9	396.8
57.5°	489.6	513.7	575.0	675.5	761.3	754.6	628.4	497.8	419.8	367.7	336.4
60°	444.7	468.5	522.4	608.6	673.4	650.7	534.8	429.7	362.8	324.6	299.8
62.5°	402.9	421.4	471.9	534.9	581.5	555.8	457.2	370.2	317.1	284.9	265.2
65°	342.3	357.4	397.8	430.7	456.6	431.8	349.9	289.5	251.2	228.5	215.1
67.5°	284.8	294.4	319.9	331.8	350.0	322.8	263.1	222.7	200.9	181.8	172.4
70°	248.5	255.6	269.0	278.7	283.6	255.6	211.4	181.6	163.3	149.9	143.9
72.5°	212.3	218.5	221.2	229.1	226.6	200.3	169.9	146.3	133.2	124.0	116.4
75°	162.2	164.9	162.2	159.1	152.0	133.7	112.6	100.8	91.1	86.8	84.1
77.5°	118.3	117.4	113.8	108.7	96.7	85.2	73.8	69.9	65.7	63.4	62.4
80°	91.1	89.0	85.7	77.6	67.4	59.3	56.6	53.9	52.3	49.6	49.0
82.5°	67.8	66.5	61.2	54.3	47.1	43.3	41.1	40.1	38.5	37.1	37.0
85°	36.1	34.5	28.6	24.8	23.7	22.7	22.1	22.1	20.0	19.4	19.4
87.5°	12.4	10.4	10.5	9.7	10.3	10.1	11.2	11.1	11.3	12.0	11.3
90°	3.9	6.5	9.2	11.8	14.9	18.3	21.8	25.2	28.7	29.7	30.8
92.5°	30.7	32.5	34.3	36.1	38.0	40.0	41.9	43.9	45.9	46.7	47.5
95°	72.3	74.2	76.0	78.0	79.9	82.0	84.1	86.3	88.4	89.4	90.5
97.5°	126.6	127.9	129.4	130.7	132.1	133.7	135.2	136.8	138.3	139.6	140.8
100°	164.1	165.6	167.2	168.8	170.3	171.6	172.9	174.3	175.6	176.4	177.2
102.5°	206.4	207.4	208.3	209.3	210.6	212.4	214.1	215.9	217.6	218.5	219.3
105°	269.3	269.8	270.4	270.9	272.4	274.7	277.1	279.6	281.9	281.9	281.9
107.5°	342.7	343.0	343.3	343.6	344.3	345.2	346.2	347.1	348.1	349.0	349.8
110°	388.8	389.3	389.8	390.4	390.9	391.4	392.0	392.4	393.0	394.1	395.1



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	436.3	436.7	437.0	437.3	437.5	437.6	437.7	437.8	437.9	439.2	440.5
115°	508.5	509.3	510.1	510.9	511.0	510.5	509.9	509.5	508.9	509.1	509.5
117.5°	580.4	580.9	581.5	581.9	581.9	581.2	580.5	579.8	579.2	579.1	579.0
120°	626.4	628.0	629.5	631.1	631.3	629.9	628.6	627.2	626.0	625.7	625.4
122.5°	672.7	673.9	675.1	676.3	676.5	675.8	675.1	674.5	673.8	673.0	672.3
125°	743.8	744.7	745.4	746.2	746.3	745.8	745.3	744.7	744.3	743.1	742.1
127.5°	810.6	812.4	814.0	815.8	816.3	815.7	815.2	814.6	814.0	812.5	811.0
130°	855.1	857.1	859.3	861.4	862.1	861.3	860.5	859.7	858.9	857.9	856.7
132.5°	899.0	901.1	903.2	905.4	906.2	905.5	905.0	904.4	903.8	902.5	901.3
135°	965.6	967.2	968.8	970.4	971.1	970.8	970.5	970.3	970.0	968.9	967.9
137.5°	1027.5	1028.8	1030.2	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1	1033.0
140°	1070.5	1071.8	1073.1	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0	1075.8
142.5°	1109.6	1111.0	1112.3	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2	1115.9
145°	1170.1	1170.5	1171.1	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2	1174.9
147.5°	1223.9	1224.9	1225.9	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7	1230.7
150°	1260.8	1261.3	1261.9	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0	1265.0
152.5°	1291.6	1292.4	1293.1	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1	1296.5
155°	1339.1	1339.1	1339.1	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4	1342.4
157.5°	1379.9	1379.6	1379.3	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9	1382.0
160°	1405.5	1404.9	1404.4	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9	1406.3
162.5°	1428.2	1427.4	1426.7	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9	1429.2
165°	1457.8	1457.0	1456.2	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6	1458.2
167.5°	1481.1	1480.1	1479.0	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0	1481.7
170°	1494.5	1493.5	1492.4	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7	1494.5
172.5°	1505.1	1504.0	1502.9	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0	1504.6
175°	1516.1	1515.0	1513.9	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9	1515.5
177.5°	1520.8	1520.0	1519.1	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1	1520.4
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1328.3	1328.3	1330.1	1336.6	1337.4	1343.0	1341.3
5°	1459.9	1470.1	1473.9	1490.1	1499.8	1504.1	1495.5
7.5°	1620.8	1649.6	1663.3	1680.3	1695.3	1699.8	1688.1
10°	1738.0	1768.2	1793.6	1809.3	1823.8	1833.5	1845.9
12.5°	1851.5	1888.6	1912.6	1934.7	1949.7	1962.0	1964.1
15°	1974.8	2030.8	2073.4	2104.7	2120.3	2128.4	2125.2
17.5°	2099.0	2151.0	2181.4	2213.3	2234.9	2236.0	2236.6
20°	2169.4	2220.0	2255.1	2278.8	2303.0	2302.0	2307.4
22.5°	2216.4	2256.3	2283.1	2300.3	2308.7	2304.5	2305.6
25°	2238.4	2250.2	2245.4	2217.9	2210.9	2185.6	2189.8
27.5°	2124.9	2068.9	2010.9	1936.3	1877.4	1830.3	1832.7
30°	1970.9	1871.8	1758.6	1663.7	1578.5	1554.8	1504.1
32.5°	1755.8	1606.9	1474.3	1385.9	1312.8	1293.0	1248.8
35°	1390.9	1246.4	1110.0	1028.1	995.7	950.5	949.9
37.5°	1081.1	953.9	881.8	820.3	788.1	760.7	758.0
40°	909.5	810.2	755.8	711.6	679.9	659.3	654.5
42.5°	789.6	709.3	658.4	631.0	606.5	596.0	588.0
45°	644.8	590.9	555.2	530.4	519.2	511.0	506.8
47.5°	539.3	503.2	479.0	462.5	453.3	444.7	447.0
50°	482.0	452.3	434.5	418.9	411.9	405.9	406.5
52.5°	435.8	409.2	394.8	383.5	374.8	370.6	368.5
55°	369.8	353.1	338.6	330.5	325.6	319.7	318.1
57.5°	315.4	302.5	290.7	281.5	280.4	274.6	275.4
60°	279.2	268.5	258.8	253.9	250.2	245.3	246.9
62.5°	249.5	240.4	231.6	227.6	223.9	220.3	221.0
65°	204.3	195.7	190.3	188.1	186.6	184.9	183.3
67.5°	162.8	157.6	154.2	149.6	146.2	145.7	144.0
70°	137.0	129.9	124.0	118.0	116.5	115.9	116.5
72.5°	109.8	105.4	103.7	100.8	100.5	99.1	100.1
75°	82.5	80.9	79.8	77.6	77.6	77.6	77.6
77.5°	60.8	59.8	59.2	58.8	58.2	57.4	57.4
80°	47.5	46.9	45.8	45.8	45.3	45.8	45.3
82.5°	35.8	35.7	34.6	34.6	34.1	33.7	34.1
85°	18.3	17.8	18.9	17.8	18.3	17.3	18.3
87.5°	11.6	11.7	11.5	11.6	11.2	12.2	11.5
90°	31.8	33.0	33.7	34.2	34.8	35.3	35.8
92.5°	48.4	49.3	49.5	49.2	48.9	48.6	48.2
95°	91.6	92.6	93.2	93.2	93.2	93.2	93.2
97.5°	142.0	143.2	143.8	143.7	143.5	143.5	143.4
100°	178.0	178.8	179.4	180.0	180.5	181.0	181.6
102.5°	220.1	220.9	221.2	221.1	220.9	220.9	220.8
105°	281.9	281.9	282.2	282.7	283.3	283.8	284.3
107.5°	350.6	351.5	351.7	351.4	351.1	350.8	350.5
110°	396.2	397.3	397.5	397.0	396.5	395.9	395.4



TEST NUMBER: P332467-927

CATALOG NUMBER: S123RDIW-S1000D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	441.7	443.0	443.6	443.5	443.4	443.3	443.1
115°	509.7	509.9	509.9	509.7	509.5	509.1	508.9
117.5°	579.0	578.9	578.5	577.7	577.0	576.3	575.5
120°	625.2	624.9	624.5	624.0	623.4	622.9	622.3
122.5°	671.7	671.0	670.3	669.6	668.8	668.0	667.3
125°	741.0	740.0	738.9	737.8	736.8	735.7	734.7
127.5°	809.5	808.0	806.7	805.5	804.2	803.0	801.8
130°	855.7	854.7	853.2	851.4	849.5	847.6	845.7
132.5°	900.0	898.7	897.4	896.0	894.5	893.0	891.6
135°	966.8	965.7	965.0	964.4	963.8	963.4	962.8
137.5°	1031.9	1030.8	1029.7	1028.6	1027.7	1026.7	1025.6
140°	1075.5	1075.2	1074.2	1072.3	1070.5	1068.6	1066.8
142.5°	1115.6	1115.4	1114.5	1113.1	1111.7	1110.2	1108.8
145°	1174.6	1174.4	1173.7	1172.7	1171.6	1170.5	1169.5
147.5°	1230.7	1230.7	1229.9	1228.3	1226.7	1225.0	1223.4
150°	1265.0	1265.0	1264.2	1262.7	1261.1	1259.5	1257.9
152.5°	1296.9	1297.4	1296.9	1295.5	1294.1	1292.7	1291.3
155°	1343.5	1344.6	1344.2	1342.3	1340.5	1338.6	1336.7
157.5°	1383.1	1384.2	1384.0	1382.5	1381.0	1379.5	1378.1
160°	1407.6	1408.9	1409.1	1408.0	1406.9	1405.9	1404.8
162.5°	1430.5	1431.9	1431.7	1430.0	1428.3	1426.6	1424.9
165°	1459.8	1461.3	1461.3	1459.4	1457.5	1455.6	1453.8
167.5°	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4
170°	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8
172.5°	1506.3	1507.9	1507.8	1505.9	1504.1	1502.2	1500.4
175°	1517.1	1518.7	1518.5	1516.7	1514.8	1513.0	1511.2
177.5°	1521.6	1522.9	1522.8	1521.3	1519.8	1518.4	1516.9
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7

(END OF REPORT)