

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332480

Luminaire Tested: **S123RDIW-S1165D1030U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332480  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1165D1030U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8505.0 lumens  
Efficiency: N/A  
Efficacy: 126.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 67.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332480

CATALOG NUMBER: S123RDIW-S1165D1030U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332480

CATALOG NUMBER: S123RDIW-S1165D1030U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	58	55	52	50	46	44	42	37
3	82	73	66	60	76	68	62	56	58	53	49	49	46	43	41	38	36	32
4	75	65	57	51	69	60	53	48	52	47	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	42	46	41	37	40	35	32	33	30	27	24
6	64	52	44	38	59	49	41	36	42	36	32	36	32	28	30	27	24	21
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25	30	26	22	25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23	28	23	20	23	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332480

CATALOG NUMBER: S123RDIW-S1165D1030U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.0	2.1
10°-20°	506.4	6.0
20°-30°	729.2	8.6
30°-40°	821.3	9.7
40°-50°	785.8	9.2
50°-60°	643.5	7.6
60°-70°	434.1	5.1
70°-80°	218.4	2.6
80°-90°	61.6	0.7
90°-100°	49.2	0.6
100°-110°	234.3	2.8
110°-120°	562.7	6.6
120°-130°	716.5	8.4
130°-140°	765.6	9.0
140°-150°	715.9	8.4
150°-160°	577.5	6.8
160°-170°	372.7	4.4
170°-180°	128.4	1.5
0°-30°	1417.6	16.7
0°-40°	2238.9	26.3
0°-60°	3668.1	43.1
0°-90°	4382.3	51.5
90°-120°	846.1	9.9
90°-150°	3044.1	35.8
90°-180°	4123.0	48.5
0°-180°	8505.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	1	11	24	28	30	7
95°	61	23	31	38	38	76
105°	299	305	220	52	44	317
115°	562	568	576	586	591	554
125°	792	799	804	806	808	707
135°	985	991	995	998	995	758
145°	1137	1144	1146	1148	1148	711
155°	1252	1251	1252	1256	1250	577
165°	1321	1318	1317	1324	1318	373
175°	1352	1347	1348	1354	1347	129
180°	1352	1352	1352	1352	1352	



TEST NUMBER: P332480

CATALOG NUMBER: S123RDIW-S1165D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.4	27.8	25.1	22.5	19.9	18.8	19.4	20.0	20.6	21.2	21.1
90°	1.0	3.2	5.5	7.7	9.9	12.5	15.4	18.3	21.2	24.1	25.0
92.5°	18.7	18.1	17.4	16.8	16.2	17.0	19.2	21.3	23.5	25.7	27.1
95°	61.3	52.1	43.0	33.8	24.7	21.3	23.8	26.2	28.7	31.1	32.7
97.5°	123.1	119.0	114.9	110.8	106.7	96.6	80.6	64.5	48.4	32.3	34.1
100°	169.7	174.2	178.7	183.1	187.6	172.4	137.6	102.8	68.0	33.1	34.9
102.5°	222.8	226.0	229.2	232.4	235.6	218.2	180.2	142.2	104.1	66.1	60.6
105°	299.3	301.8	304.2	306.7	309.1	300.3	280.2	260.1	240.1	220.0	180.5
107.5°	380.1	382.0	384.0	386.0	387.9	390.5	393.7	396.8	400.0	403.2	374.2
110°	433.9	435.7	437.5	439.3	441.0	443.2	445.6	448.1	450.5	453.0	445.6



TEST NUMBER: P332480

CATALOG NUMBER: S123RDIW-S1165D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.3	486.9	488.5	490.2	491.8	493.8	496.2	498.7	501.2	503.6	503.7
115°	561.5	562.8	564.1	565.5	566.8	568.5	570.5	572.5	574.5	576.5	578.8
117.5°	635.2	636.8	638.5	640.1	641.8	643.1	644.2	645.2	646.2	647.2	649.0
120°	681.0	683.0	685.0	687.0	689.0	690.4	691.0	691.7	692.4	693.0	694.8
122.5°	727.6	729.2	730.9	732.5	734.2	735.4	736.3	737.1	738.0	738.8	740.1
125°	791.5	793.3	795.0	796.8	798.6	800.0	800.8	801.7	802.6	803.5	804.0
127.5°	853.3	855.1	856.9	858.7	860.5	861.9	863.0	864.1	865.1	866.2	866.9
130°	891.9	893.7	895.5	897.3	899.1	900.4	901.3	902.2	903.1	904.0	904.9
132.5°	928.9	930.7	932.4	934.2	936.0	937.3	938.0	938.7	939.4	940.1	941.0
135°	985.3	986.7	988.0	989.3	990.7	991.8	992.7	993.6	994.5	995.4	996.0
137.5°	1033.5	1035.2	1036.9	1038.6	1040.3	1041.4	1041.9	1042.4	1042.9	1043.4	1044.4
140°	1065.7	1067.0	1068.4	1069.7	1071.0	1072.0	1072.7	1073.4	1074.0	1074.7	1075.6
142.5°	1095.4	1096.7	1098.1	1099.4	1100.8	1101.8	1102.4	1103.1	1103.8	1104.4	1105.2
145°	1137.0	1138.5	1140.1	1141.7	1143.2	1144.2	1144.7	1145.1	1145.6	1146.0	1146.5
147.5°	1176.2	1177.2	1178.2	1179.2	1180.3	1181.0	1181.4	1181.9	1182.3	1182.8	1183.2
150°	1200.3	1200.9	1201.6	1202.3	1202.9	1203.5	1203.9	1204.4	1204.8	1205.3	1205.7
152.5°	1222.0	1222.3	1222.6	1222.9	1223.2	1223.5	1223.8	1224.0	1224.3	1224.6	1225.4
155°	1252.5	1252.0	1251.6	1251.2	1250.7	1250.6	1250.8	1251.0	1251.3	1251.5	1252.6
157.5°	1276.2	1276.2	1276.1	1276.1	1276.0	1275.9	1275.7	1275.4	1275.2	1275.0	1276.3
160°	1290.7	1290.4	1290.2	1290.0	1289.8	1289.5	1289.3	1289.1	1288.9	1288.7	1290.0
162.5°	1304.3	1303.7	1303.2	1302.6	1302.0	1301.6	1301.4	1301.2	1300.9	1300.7	1302.2
165°	1320.8	1320.1	1319.5	1318.8	1318.1	1317.7	1317.4	1317.2	1317.0	1316.8	1318.6
167.5°	1333.6	1332.8	1331.9	1331.0	1330.1	1329.6	1329.6	1329.6	1329.6	1329.6	1331.4
170°	1340.9	1340.0	1339.1	1338.2	1337.3	1336.9	1336.9	1336.9	1336.9	1336.9	1338.6
172.5°	1345.7	1344.6	1343.6	1342.5	1341.4	1341.0	1341.1	1341.3	1341.5	1341.7	1343.5
175°	1351.9	1350.8	1349.7	1348.6	1347.5	1347.0	1347.2	1347.5	1347.7	1347.9	1349.5
177.5°	1353.5	1352.6	1351.8	1350.9	1350.0	1349.6	1349.8	1350.0	1350.1	1350.3	1351.8
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332480

CATALOG NUMBER: S123RDIW-S1165D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	21.0	20.9	20.8	20.6	20.4	20.2	20.0	19.9
90°	25.9	26.8	27.7	28.3	28.8	29.2	29.7	30.1
92.5°	28.6	30.0	31.4	32.3	32.5	32.8	33.1	33.3
95°	34.3	35.8	37.4	38.2	38.2	38.2	38.2	38.2
97.5°	35.9	37.7	39.5	40.5	40.7	40.9	41.2	41.4
100°	36.7	38.5	40.3	41.3	41.5	41.7	42.0	42.2
102.5°	55.0	49.5	43.9	41.4	41.8	42.2	42.6	43.0
105°	141.0	101.4	61.9	42.4	42.9	43.3	43.7	44.2
107.5°	345.2	316.3	287.3	257.9	228.1	198.4	168.6	138.8
110°	438.3	430.9	423.5	403.9	372.0	340.0	308.1	276.2





TEST NUMBER: P332480

CATALOG NUMBER: S123RDIW-S1165D1030U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	503.9	504.0	504.1	500.8	494.1	487.4	480.6	473.9
115°	581.0	583.2	585.5	587.0	587.9	588.8	589.7	590.6
117.5°	650.8	652.6	654.4	655.4	655.5	655.7	655.9	656.1
120°	696.6	698.4	700.2	701.1	701.1	701.1	701.1	701.1
122.5°	741.3	742.6	743.8	744.6	744.7	744.9	745.1	745.3
125°	804.4	804.9	805.3	805.8	806.2	806.6	807.1	807.5
127.5°	867.6	868.3	869.1	869.2	868.7	868.3	867.9	867.4
130°	905.8	906.6	907.5	907.8	907.3	906.9	906.4	906.0
132.5°	941.9	942.8	943.7	943.8	943.2	942.6	942.0	941.3
135°	996.7	997.4	998.0	998.0	997.4	996.7	996.0	995.4
137.5°	1045.5	1046.6	1047.7	1048.0	1047.5	1047.1	1046.6	1046.2
140°	1076.5	1077.4	1078.3	1078.5	1078.1	1077.6	1077.2	1076.7
142.5°	1105.9	1106.6	1107.3	1107.3	1106.7	1106.1	1105.5	1104.8
145°	1146.9	1147.4	1147.8	1148.0	1148.0	1148.0	1148.0	1148.0
147.5°	1183.7	1184.1	1184.6	1184.3	1183.3	1182.2	1181.2	1180.2
150°	1206.2	1206.6	1207.1	1207.0	1206.3	1205.6	1205.0	1204.3
152.5°	1226.2	1227.0	1227.8	1227.7	1226.6	1225.6	1224.6	1223.6
155°	1253.7	1254.8	1256.0	1255.8	1254.5	1253.2	1251.8	1250.5
157.5°	1277.7	1279.0	1280.3	1280.1	1278.4	1276.7	1274.9	1273.2
160°	1291.3	1292.7	1294.0	1293.9	1292.3	1290.8	1289.2	1287.6
162.5°	1303.7	1305.3	1306.8	1306.8	1305.5	1304.1	1302.7	1301.3
165°	1320.3	1322.1	1323.9	1324.0	1322.5	1320.9	1319.3	1317.8
167.5°	1333.2	1335.0	1336.8	1336.8	1335.0	1333.2	1331.4	1329.6
170°	1340.4	1342.2	1344.0	1344.0	1342.2	1340.4	1338.6	1336.9
172.5°	1345.3	1347.0	1348.8	1348.7	1346.8	1344.8	1342.8	1340.9
175°	1351.0	1352.6	1354.2	1354.1	1352.3	1350.5	1348.7	1346.9
177.5°	1353.2	1354.6	1356.0	1355.9	1354.1	1352.3	1350.5	1348.7
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9

(END OF REPORT)