

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332484

Luminaire Tested: **S123RDIW-S1165D1320U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332484
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1320U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9661.2 lumens
Efficiency: N/A
Efficacy: 126.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332484

CATALOG NUMBER: S123RDIW-S1165D1320U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332484

CATALOG NUMBER: S123RDIW-S1165D1320U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39
2	89	81	75	70	81	75	70	65	63	59	56	51	49	47	41	39	38	33
3	81	72	65	59	74	66	60	55	56	51	47	46	42	40	37	34	32	28
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	30	28	24
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25	21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	20	17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	30	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332484

CATALOG NUMBER: S123RDIW-S1165D1320U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	1.9
10°-20°	506.4	5.2
20°-30°	729.2	7.5
30°-40°	821.3	8.5
40°-50°	785.8	8.1
50°-60°	643.5	6.7
60°-70°	434.1	4.5
70°-80°	218.4	2.3
80°-90°	62.6	0.6
90°-100°	62.9	0.7
100°-110°	299.9	3.1
110°-120°	720.3	7.5
120°-130°	917.3	9.5
130°-140°	980.1	10.1
140°-150°	916.5	9.5
150°-160°	739.3	7.7
160°-170°	477.1	4.9
170°-180°	164.4	1.7
0°-30°	1417.6	14.7
0°-40°	2238.9	23.2
0°-60°	3668.1	38.0
0°-90°	4383.3	45.4
90°-120°	1083.2	11.2
90°-150°	3897.1	40.3
90°-180°	5278.0	54.6
0°-180°	9661.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	1	14	31	36	39	8
95°	78	29	40	48	49	97
105°	383	390	282	67	57	406
115°	719	727	738	750	756	709
125°	1013	1023	1029	1031	1034	905
135°	1261	1269	1274	1278	1274	971
145°	1456	1464	1467	1470	1470	911
155°	1603	1601	1602	1608	1601	738
165°	1691	1687	1686	1695	1687	478
175°	1731	1725	1726	1734	1724	165
180°	1731	1731	1731	1731	1731	



TEST NUMBER: P332484

CATALOG NUMBER: S123RDIW-S1165D1320U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.4	27.9	25.4	22.9	20.4	19.5	20.3	21.0	21.8	22.5	22.5
90°	1.3	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.1	30.9	32.0
92.5°	23.9	23.1	22.3	21.5	20.7	21.7	24.5	27.3	30.1	32.9	34.7
95°	78.4	66.7	55.0	43.3	31.6	27.3	30.4	33.6	36.7	39.9	41.9
97.5°	157.6	152.4	147.1	141.9	136.6	123.7	103.1	82.6	62.0	41.4	43.7
100°	217.3	223.0	228.7	234.4	240.2	220.7	176.2	131.6	87.0	42.4	44.7
102.5°	285.2	289.3	293.4	297.5	301.7	279.4	230.7	182.0	133.3	84.6	77.5
105°	383.2	386.3	389.5	392.6	395.7	384.5	358.7	333.0	307.3	281.6	231.0
107.5°	486.6	489.1	491.6	494.1	496.6	499.9	504.0	508.0	512.1	516.1	479.0
110°	555.5	557.8	560.0	562.3	564.6	567.3	570.5	573.6	576.8	579.9	570.5



TEST NUMBER: P332484

CATALOG NUMBER: S123RDIW-S1165D1320U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	621.3	623.4	625.4	627.5	629.5	632.1	635.3	638.4	641.6	644.7	644.9
115°	718.8	720.5	722.2	723.9	725.6	727.8	730.3	732.9	735.5	738.1	740.9
117.5°	813.2	815.3	817.4	819.5	821.6	823.3	824.6	826.0	827.3	828.6	830.9
120°	871.8	874.4	876.9	879.5	882.1	883.8	884.6	885.5	886.4	887.2	889.5
122.5°	931.5	933.6	935.7	937.8	939.9	941.5	942.6	943.7	944.8	945.9	947.5
125°	1013.2	1015.5	1017.8	1020.1	1022.4	1024.1	1025.2	1026.4	1027.5	1028.7	1029.2
127.5°	1092.4	1094.7	1097.0	1099.3	1101.6	1103.4	1104.8	1106.2	1107.5	1108.9	1109.8
130°	1141.8	1144.1	1146.4	1148.7	1151.0	1152.7	1153.8	1155.0	1156.1	1157.2	1158.4
132.5°	1189.1	1191.4	1193.7	1196.0	1198.3	1199.9	1200.8	1201.7	1202.6	1203.5	1204.7
135°	1261.4	1263.1	1264.8	1266.5	1268.3	1269.7	1270.8	1272.0	1273.1	1274.3	1275.1
137.5°	1323.1	1325.3	1327.5	1329.6	1331.8	1333.2	1333.8	1334.5	1335.1	1335.7	1337.1
140°	1364.3	1366.0	1367.7	1369.4	1371.1	1372.4	1373.3	1374.1	1375.0	1375.8	1377.0
142.5°	1402.3	1404.0	1405.8	1407.5	1409.2	1410.5	1411.3	1412.2	1413.0	1413.9	1414.8
145°	1455.6	1457.6	1459.6	1461.6	1463.6	1464.8	1465.4	1466.0	1466.6	1467.1	1467.7
147.5°	1505.7	1507.0	1508.3	1509.6	1511.0	1511.9	1512.5	1513.0	1513.6	1514.2	1514.8
150°	1536.6	1537.4	1538.3	1539.1	1540.0	1540.7	1541.3	1541.8	1542.4	1543.0	1543.6
152.5°	1564.3	1564.7	1565.1	1565.5	1565.9	1566.3	1566.7	1567.0	1567.3	1567.7	1568.7
155°	1603.4	1602.9	1602.3	1601.7	1601.1	1601.0	1601.3	1601.6	1601.9	1602.1	1603.6
157.5°	1633.8	1633.7	1633.7	1633.6	1633.5	1633.4	1633.1	1632.8	1632.5	1632.2	1633.9
160°	1652.3	1652.0	1651.7	1651.4	1651.1	1650.9	1650.6	1650.3	1650.0	1649.7	1651.4
162.5°	1669.8	1669.0	1668.3	1667.5	1666.8	1666.3	1666.0	1665.7	1665.4	1665.1	1667.1
165°	1690.9	1690.0	1689.1	1688.3	1687.4	1686.9	1686.6	1686.3	1686.0	1685.7	1688.0
167.5°	1707.3	1706.2	1705.0	1703.9	1702.7	1702.2	1702.2	1702.2	1702.2	1702.2	1704.5
170°	1716.6	1715.4	1714.3	1713.2	1712.0	1711.4	1711.4	1711.4	1711.4	1711.4	1713.7
172.5°	1722.8	1721.4	1720.0	1718.6	1717.3	1716.7	1716.9	1717.2	1717.4	1717.6	1719.9
175°	1730.7	1729.3	1727.9	1726.4	1725.0	1724.4	1724.7	1725.0	1725.3	1725.6	1727.6
177.5°	1732.8	1731.6	1730.5	1729.4	1728.2	1727.8	1728.0	1728.2	1728.4	1728.7	1730.5
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332484

CATALOG NUMBER: S123RDIW-S1165D1320U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	22.4	22.4	22.3	22.2	22.0	21.9	21.7	21.5
90°	33.1	34.3	35.4	36.3	36.9	37.4	38.0	38.6
92.5°	36.6	38.4	40.2	41.3	41.7	42.0	42.3	42.7
95°	43.9	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	46.0	48.3	50.5	51.8	52.1	52.4	52.7	53.0
100°	47.0	49.3	51.6	52.9	53.1	53.4	53.7	54.0
102.5°	70.4	63.3	56.3	53.0	53.5	54.0	54.5	55.0
105°	180.4	129.9	79.3	54.3	54.9	55.4	56.0	56.6
107.5°	442.0	404.9	367.8	330.2	292.1	253.9	215.8	177.7
110°	561.0	551.6	542.2	517.0	476.2	435.3	394.5	353.6



TEST NUMBER: P332484

CATALOG NUMBER: S123RDIW-S1165D1320U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	645.1	645.2	645.4	641.2	632.5	623.9	615.3	606.7
115°	743.8	746.6	749.5	751.5	752.6	753.8	754.9	756.1
117.5°	833.2	835.4	837.7	839.0	839.2	839.4	839.7	839.9
120°	891.8	894.1	896.4	897.5	897.5	897.5	897.5	897.5
122.5°	949.1	950.7	952.3	953.2	953.4	953.6	953.9	954.1
125°	1029.8	1030.4	1030.9	1031.5	1032.1	1032.7	1033.2	1033.8
127.5°	1110.7	1111.6	1112.6	1112.7	1112.2	1111.6	1111.0	1110.4
130°	1159.5	1160.7	1161.8	1162.1	1161.5	1161.0	1160.4	1159.8
132.5°	1205.8	1207.0	1208.1	1208.3	1207.5	1206.7	1205.9	1205.1
135°	1276.0	1276.8	1277.7	1277.7	1276.8	1276.0	1275.1	1274.3
137.5°	1338.5	1339.8	1341.2	1341.6	1341.0	1340.5	1339.9	1339.3
140°	1378.1	1379.3	1380.4	1380.7	1380.1	1379.5	1379.0	1378.4
142.5°	1415.7	1416.6	1417.6	1417.6	1416.8	1416.0	1415.2	1414.4
145°	1468.3	1468.8	1469.4	1469.7	1469.7	1469.7	1469.7	1469.7
147.5°	1515.3	1515.9	1516.5	1516.1	1514.8	1513.5	1512.2	1510.8
150°	1544.1	1544.7	1545.3	1545.1	1544.3	1543.4	1542.6	1541.7
152.5°	1569.7	1570.8	1571.8	1571.7	1570.3	1569.0	1567.7	1566.4
155°	1605.0	1606.4	1607.9	1607.7	1606.0	1604.3	1602.6	1600.9
157.5°	1635.7	1637.4	1639.1	1638.8	1636.6	1634.4	1632.1	1629.9
160°	1653.1	1654.9	1656.6	1656.4	1654.4	1652.4	1650.4	1648.4
162.5°	1669.0	1671.0	1672.9	1673.0	1671.2	1669.5	1667.7	1665.9
165°	1690.3	1692.6	1694.9	1695.0	1693.0	1691.0	1689.0	1687.0
167.5°	1706.8	1709.0	1711.3	1711.3	1709.0	1706.8	1704.5	1702.2
170°	1716.0	1718.3	1720.6	1720.6	1718.3	1716.0	1713.7	1711.4
172.5°	1722.2	1724.5	1726.8	1726.6	1724.1	1721.6	1719.1	1716.6
175°	1729.6	1731.6	1733.6	1733.4	1731.2	1728.9	1726.6	1724.3
177.5°	1732.3	1734.2	1736.0	1735.8	1733.5	1731.2	1728.9	1726.6
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7

(END OF REPORT)