

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332450-927

Luminaire Tested: **S123RDIW-S1000D460U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332450-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S1000D460U927-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 460 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4597.8 lumens  
Efficiency: N/A  
Efficacy: 99.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	68								
1	103	99	95	91	97	93	90	87	83	81	79	74	72	71	66	64	63	59								
2	94	87	81	76	89	82	77	73	74	70	66	66	63	60	59	56	54	51								
3	86	77	70	64	81	73	67	62	66	61	57	59	55	52	53	50	47	44								
4	80	69	61	55	75	66	59	53	59	54	49	53	49	45	48	44	41	38								
5	73	62	54	48	69	59	52	46	53	48	43	48	43	40	43	40	37	34								
6	68	56	48	42	64	53	46	41	48	42	38	44	39	35	40	36	33	30								
7	63	51	43	37	59	49	41	36	44	38	34	40	35	31	36	32	29	27								
8	59	46	39	33	55	44	37	32	41	35	30	37	32	28	34	29	26	24								
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	22								
10	51	39	32	27	49	38	31	26	35	29	25	32	27	23	29	25	22	20								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	13555	13555	13555	13555
5°	16159	13613	11988	13613
10°	20176	13535	10831	13535
15°	23682	13397	9877	13397
20°	26431	13190	9065	13190
25°	26008	12973	8568	12973
30°	18695	12771	8054	12771
35°	12482	12510	7721	12510
40°	9197	12197	7378	12197
45°	7715	11645	7042	11645
50°	6807	10923	6571	10923
55°	5970	10098	5928	10098
60°	5315	9309	5431	9309
65°	4669	8458	5053	8458
70°	3666	7704	4614	7704
75°	3227	6729	4213	6729
80°	2808	5715	4147	5715
85°	2260	4594	4397	4594



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.8	2.7
10°-20°	386.9	8.4
20°-30°	607.8	13.2
30°-40°	634.2	13.8
40°-50°	542.7	11.8
50°-60°	413.6	9.0
60°-70°	265.1	5.8
70°-80°	127.5	2.8
80°-90°	35.1	0.8
90°-100°	17.4	0.4
100°-110°	83.0	1.8
110°-120°	199.4	4.3
120°-130°	253.9	5.5
130°-140°	271.3	5.9
140°-150°	253.7	5.5
150°-160°	204.6	4.5
160°-170°	132.1	2.9
170°-180°	45.5	1.0
0°-30°	1118.6	24.3
0°-40°	1752.8	38.1
0°-60°	2709.1	58.9
0°-90°	3136.9	68.2
90°-120°	299.8	6.5
90°-150°	1078.7	23.5
90°-180°	1461.0	31.8
0°-180°	4597.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1259	1259	1259	1259	1259	
5°	1496	1260	1110	1260	1496	154
15°	2125	1202	886	1202	2125	603
25°	2190	1092	721	1092	2190	941
35°	950	952	588	952	950	623
45°	507	765	463	765	507	398
55°	318	538	316	538	318	288
65°	183	332	198	332	183	180
75°	78	162	101	162	78	83
85°	18	37	36	37	18	21
90°	11	0	11	0	11	5
95°	14	22	14	22	14	11
105°	16	106	16	106	16	36
115°	209	199	209	199	209	193
125°	286	280	286	280	286	256
135°	353	349	353	349	353	272
145°	407	403	407	403	407	254
155°	443	444	443	444	443	204
165°	467	468	467	468	467	132
175°	477	479	477	479	477	45
180°	479	479	479	479	479	



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1341.3	1343.0	1337.4	1336.6	1330.1	1328.3	1328.3	1319.3	1313.7	1306.4	1302.0
5°	1495.5	1504.1	1499.8	1490.1	1473.9	1470.1	1459.9	1443.8	1425.4	1402.7	1391.9
7.5°	1688.1	1699.8	1695.3	1680.3	1663.3	1649.6	1620.8	1593.9	1556.3	1523.3	1495.1
10°	1845.9	1833.5	1823.8	1809.3	1793.6	1768.2	1738.0	1696.5	1648.6	1610.8	1568.8
12.5°	1964.1	1962.0	1949.7	1934.7	1912.6	1888.6	1851.5	1800.9	1745.2	1690.7	1642.5
15°	2125.2	2128.4	2120.3	2104.7	2073.4	2030.8	1974.8	1953.8	1873.9	1814.7	1755.3
17.5°	2236.6	2236.0	2234.9	2213.3	2181.4	2151.0	2099.0	2043.8	1971.5	1887.9	1808.1
20°	2307.4	2302.0	2303.0	2278.8	2255.1	2220.0	2169.4	2089.1	2029.7	1933.2	1850.8
22.5°	2305.6	2304.5	2308.7	2300.3	2283.1	2256.3	2216.4	2148.6	2072.8	1975.5	1882.7
25°	2189.8	2185.6	2210.9	2217.9	2245.4	2250.2	2238.4	2201.2	2129.5	2029.2	1914.4
27.5°	1832.7	1830.3	1877.4	1936.3	2010.9	2068.9	2124.9	2152.0	2129.5	2057.7	1942.6
30°	1504.1	1554.8	1578.5	1663.7	1758.6	1871.8	1970.9	2065.3	2088.5	2057.2	1962.9
32.5°	1248.8	1293.0	1312.8	1385.9	1474.3	1606.9	1755.8	1889.4	1983.7	2007.6	1950.8
35°	949.9	950.5	995.7	1028.1	1110.0	1246.4	1390.9	1569.9	1747.8	1882.5	1896.6
37.5°	758.0	760.7	788.1	820.3	881.8	953.9	1081.1	1229.9	1435.4	1642.4	1763.6
40°	654.5	659.3	679.9	711.6	755.8	810.2	909.5	1049.6	1221.1	1451.3	1639.4
42.5°	588.0	596.0	606.5	631.0	658.4	709.3	789.6	897.9	1053.8	1271.5	1488.5
45°	506.8	511.0	519.2	530.4	555.2	590.9	644.8	717.6	846.9	1022.2	1239.4
47.5°	447.0	444.7	453.3	462.5	479.0	503.2	539.3	598.7	691.0	831.6	1015.9
50°	406.5	405.9	411.9	418.9	434.5	452.3	482.0	526.7	600.0	716.4	885.2
52.5°	368.5	370.6	374.8	383.5	394.8	409.2	435.8	468.0	531.0	631.5	772.2
55°	318.1	319.7	325.6	330.5	338.6	353.1	369.8	396.8	439.9	510.0	625.9
57.5°	275.4	274.6	280.4	281.5	290.7	302.5	315.4	336.4	367.7	419.8	497.8
60°	246.9	245.3	250.2	253.9	258.8	268.5	279.2	299.8	324.6	362.8	429.7
62.5°	221.0	220.3	223.9	227.6	231.6	240.4	249.5	265.2	284.9	317.1	370.2
65°	183.3	184.9	186.6	188.1	190.3	195.7	204.3	215.1	228.5	251.2	289.5
67.5°	144.0	145.7	146.2	149.6	154.2	157.6	162.8	172.4	181.8	200.9	222.7
70°	116.5	115.9	116.5	118.0	124.0	129.9	137.0	143.9	149.9	163.3	181.6
72.5°	100.1	99.1	100.5	100.8	103.7	105.4	109.8	116.4	124.0	133.2	146.3
75°	77.6	77.6	77.6	77.6	79.8	80.9	82.5	84.1	86.8	91.1	100.8
77.5°	57.4	57.4	58.2	58.8	59.2	59.8	60.8	62.4	63.4	65.7	69.9
80°	45.3	45.8	45.3	45.8	45.8	46.9	47.5	49.0	49.6	52.3	53.9
82.5°	34.1	33.7	34.1	34.6	34.6	35.7	35.8	37.0	37.1	38.5	40.1
85°	18.3	17.3	18.3	17.8	18.9	17.8	18.3	19.4	19.4	20.0	22.1
87.5°	6.4	7.3	6.4	6.8	6.7	7.1	7.1	7.0	7.8	7.3	7.5
90°	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2	8.9	8.6	7.5
92.5°	11.8	11.7	11.6	11.6	11.4	11.2	10.6	10.1	9.6	9.1	8.3
95°	13.5	13.5	13.5	13.5	13.5	13.2	12.7	12.1	11.6	11.0	10.1
97.5°	14.7	14.6	14.5	14.4	14.3	14.0	13.4	12.8	12.1	11.5	17.2
100°	15.0	14.9	14.8	14.7	14.7	14.3	13.6	13.0	12.4	11.7	24.1
102.5°	15.2	15.1	15.0	14.8	14.7	15.6	17.5	19.5	21.5	23.4	36.9
105°	15.7	15.5	15.4	15.2	15.1	21.9	36.0	49.9	63.9	78.0	85.1
107.5°	49.2	59.7	70.3	80.8	91.4	101.8	112.1	122.3	132.6	142.8	141.7
110°	97.9	109.2	120.5	131.8	143.1	150.0	152.7	155.3	157.9	160.5	159.6



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.9	170.3	172.7	175.1	177.4	178.6	178.6	178.6	178.5	178.5	177.6
115°	209.3	209.0	208.7	208.3	208.0	207.5	206.7	205.9	205.1	204.3	203.6
117.5°	232.5	232.4	232.3	232.3	232.2	231.9	231.2	230.6	230.0	229.3	229.0
120°	248.4	248.4	248.4	248.4	248.4	248.1	247.5	246.8	246.2	245.6	245.3
122.5°	264.1	264.0	264.0	263.9	263.8	263.6	263.2	262.7	262.2	261.8	261.5
125°	286.1	286.0	285.8	285.7	285.5	285.3	285.2	285.0	284.9	284.7	284.4
127.5°	307.4	307.5	307.7	307.8	308.0	307.9	307.7	307.4	307.2	307.0	306.6
130°	321.0	321.2	321.3	321.5	321.6	321.5	321.2	320.9	320.6	320.3	320.0
132.5°	333.6	333.7	334.0	334.2	334.5	334.4	334.1	333.7	333.4	333.1	332.9
135°	352.7	352.9	353.2	353.4	353.6	353.6	353.4	353.2	352.9	352.7	352.4
137.5°	370.7	370.9	371.1	371.2	371.4	371.2	370.8	370.5	370.1	369.7	369.6
140°	381.5	381.7	381.8	382.0	382.1	382.1	381.8	381.4	381.1	380.8	380.6
142.5°	391.5	391.7	392.0	392.1	392.4	392.4	392.1	391.9	391.6	391.3	391.1
145°	406.8	406.8	406.8	406.8	406.8	406.7	406.5	406.4	406.2	406.1	405.9
147.5°	418.2	418.6	418.9	419.3	419.6	419.8	419.6	419.5	419.3	419.1	419.0
150°	426.7	427.0	427.2	427.5	427.7	427.7	427.5	427.4	427.2	427.1	426.9
152.5°	433.6	434.0	434.3	434.7	435.0	435.1	434.7	434.5	434.2	434.0	433.8
155°	443.1	443.5	444.0	444.5	445.0	445.0	444.7	444.3	443.9	443.5	443.4
157.5°	451.1	451.8	452.4	453.0	453.6	453.7	453.2	452.7	452.3	451.8	451.9
160°	456.3	456.9	457.4	458.0	458.5	458.5	458.0	457.6	457.1	456.6	456.7
162.5°	461.1	461.6	462.1	462.6	463.1	463.0	462.6	462.0	461.4	460.9	461.0
165°	467.0	467.5	468.1	468.6	469.1	469.1	468.5	467.9	467.2	466.6	466.7
167.5°	471.2	471.8	472.5	473.0	473.6	473.6	473.0	472.5	471.8	471.2	471.2
170°	473.7	474.4	475.0	475.6	476.3	476.3	475.6	475.0	474.4	473.7	473.7
172.5°	475.2	475.9	476.5	477.2	477.9	477.9	477.3	476.7	476.0	475.4	475.4
175°	477.3	477.9	478.6	479.2	479.8	479.8	479.3	478.7	478.2	477.6	477.5
177.5°	477.9	478.6	479.2	479.8	480.5	480.5	480.0	479.5	479.0	478.5	478.4
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1300.3	1299.0	1293.0	1286.1	1277.0	1271.0	1266.2	1263.7	1255.9	1246.4	1239.9
5°	1380.6	1364.5	1347.3	1326.2	1306.8	1286.8	1274.5	1259.9	1242.1	1222.2	1208.2
7.5°	1466.7	1435.0	1400.8	1365.6	1330.7	1299.5	1271.8	1248.2	1219.9	1191.3	1171.2
10°	1532.7	1486.3	1438.4	1389.3	1344.5	1302.5	1270.1	1238.3	1204.4	1171.5	1146.7
12.5°	1592.6	1531.6	1476.3	1416.0	1358.8	1308.5	1261.9	1224.6	1183.7	1148.6	1120.4
15°	1668.5	1606.0	1539.1	1447.5	1371.5	1307.9	1251.3	1202.2	1152.6	1109.5	1082.0
17.5°	1739.5	1645.4	1555.5	1479.1	1380.3	1300.8	1231.8	1173.1	1118.6	1072.9	1039.1
20°	1768.8	1677.7	1580.1	1482.6	1385.5	1296.6	1216.2	1151.5	1095.0	1043.1	1011.9
22.5°	1786.5	1683.3	1580.6	1475.7	1372.5	1280.2	1200.7	1129.6	1068.2	1019.0	980.4
25°	1807.0	1684.2	1571.0	1467.4	1362.3	1262.0	1167.7	1092.3	1026.0	973.6	932.6
27.5°	1820.7	1676.1	1542.3	1427.2	1320.6	1220.8	1134.2	1054.2	987.0	931.7	887.7
30°	1823.3	1669.6	1520.3	1395.7	1287.4	1195.7	1104.1	1027.5	956.4	897.6	856.7
32.5°	1826.7	1653.7	1490.5	1358.2	1247.3	1156.5	1073.5	1000.4	927.5	869.6	827.8
35°	1812.5	1644.8	1445.3	1293.3	1182.3	1094.4	1019.5	952.0	880.4	824.3	781.7
37.5°	1751.2	1609.8	1398.5	1220.2	1104.1	1022.7	961.6	902.9	837.1	776.7	736.5
40°	1689.6	1575.3	1362.3	1175.8	1054.5	970.9	915.9	868.0	804.4	747.7	704.6
42.5°	1597.7	1528.3	1327.9	1129.2	998.4	917.9	871.5	826.6	770.7	713.2	672.7
45°	1429.2	1438.4	1257.2	1055.0	920.8	840.0	796.2	765.0	715.4	668.0	626.5
47.5°	1217.8	1303.5	1174.3	976.0	838.9	763.0	724.8	697.6	664.2	617.6	579.7
50°	1079.8	1202.2	1107.9	923.0	787.7	712.2	674.4	652.3	623.2	586.5	550.4
52.5°	952.6	1084.0	1027.6	863.9	732.0	663.0	626.1	607.9	584.8	550.3	517.6
55°	776.8	910.0	897.1	774.7	648.6	586.5	558.5	538.1	522.4	496.5	470.6
57.5°	628.4	754.6	761.3	675.5	575.0	513.7	489.6	474.2	464.0	444.4	420.5
60°	534.8	650.7	673.4	608.6	522.4	468.5	444.7	432.4	424.3	408.6	390.3
62.5°	457.2	555.8	581.5	534.9	471.9	421.4	402.9	390.9	385.5	372.0	355.8
65°	349.9	431.8	456.6	430.7	397.8	357.4	342.3	332.1	327.3	319.7	307.8
67.5°	263.1	322.8	350.0	331.8	319.9	294.4	284.8	279.2	275.0	269.7	259.8
70°	211.4	255.6	283.6	278.7	269.0	255.6	248.5	244.8	240.4	236.1	227.5
72.5°	169.9	200.3	226.6	229.1	221.2	218.5	212.3	210.7	208.1	203.0	198.2
75°	112.6	133.7	152.0	159.1	162.2	164.9	162.2	161.8	161.2	156.9	154.2
77.5°	73.8	85.2	96.7	108.7	113.8	117.4	118.3	120.3	118.8	116.5	115.3
80°	56.6	59.3	67.4	77.6	85.7	89.0	91.1	92.2	91.7	91.1	89.0
82.5°	41.1	43.3	47.1	54.3	61.2	66.5	67.8	67.6	68.8	69.1	67.4
85°	22.1	22.7	23.7	24.8	28.6	34.5	36.1	37.2	38.3	38.3	35.0
87.5°	8.2	7.5	8.2	8.0	9.2	9.4	11.9	13.9	14.5	12.9	13.1
90°	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.5	6.8	6.0	5.7	5.9	6.2	6.4	6.7	6.4	6.2	5.9
95°	9.3	8.4	7.5	8.7	12.0	15.2	18.5	21.7	18.5	15.2	12.0
97.5°	22.8	28.5	34.2	37.8	39.3	40.7	42.1	43.6	42.1	40.7	39.3
100°	36.4	48.8	61.1	66.5	64.9	63.3	61.7	60.1	61.7	63.3	64.9
102.5°	50.4	63.8	77.3	83.5	82.4	81.2	80.1	78.9	80.1	81.2	82.4
105°	92.2	99.3	106.4	109.6	108.7	107.8	106.9	106.1	106.9	107.8	108.7
107.5°	140.6	139.5	138.4	137.4	136.7	136.1	135.4	134.7	135.4	136.1	136.7
110°	158.8	157.9	157.0	156.3	155.7	155.0	154.4	153.8	154.4	155.0	155.7





TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	176.7	175.9	175.0	174.3	173.6	173.1	172.5	172.0	172.5	173.1	173.6
115°	202.9	202.2	201.5	200.8	200.3	199.9	199.4	198.9	199.4	199.9	200.3
117.5°	228.6	228.2	227.9	227.4	226.8	226.2	225.7	225.1	225.7	226.2	226.8
120°	245.1	244.9	244.6	244.2	243.4	242.7	242.0	241.3	242.0	242.7	243.4
122.5°	261.2	260.9	260.6	260.2	259.6	259.0	258.4	257.9	258.4	259.0	259.6
125°	284.1	283.8	283.4	283.0	282.3	281.7	281.1	280.4	281.1	281.7	282.3
127.5°	306.2	305.8	305.4	304.9	304.3	303.6	303.0	302.4	303.0	303.6	304.3
130°	319.7	319.4	319.1	318.6	318.0	317.3	316.7	316.1	316.7	317.3	318.0
132.5°	332.6	332.4	332.1	331.7	331.1	330.4	329.8	329.2	329.8	330.4	331.1
135°	352.0	351.7	351.4	351.0	350.5	350.1	349.6	349.1	349.6	350.1	350.5
137.5°	369.4	369.2	369.0	368.6	368.0	367.4	366.9	366.2	366.9	367.4	368.0
140°	380.3	380.1	379.9	379.5	379.1	378.6	378.1	377.6	378.1	378.6	379.1
142.5°	390.9	390.6	390.4	390.1	389.6	389.1	388.6	388.2	388.6	389.1	389.6
145°	405.8	405.6	405.4	405.1	404.6	404.0	403.5	402.9	403.5	404.0	404.6
147.5°	418.8	418.7	418.5	418.2	417.9	417.5	417.2	416.8	417.2	417.5	417.9
150°	426.7	426.6	426.4	426.3	426.0	425.8	425.6	425.3	425.6	425.8	426.0
152.5°	433.7	433.6	433.6	433.5	433.3	433.2	433.1	433.0	433.1	433.2	433.3
155°	443.3	443.2	443.1	443.2	443.4	443.5	443.6	443.8	443.6	443.5	443.4
157.5°	451.9	452.0	452.1	452.2	452.2	452.2	452.2	452.3	452.2	452.2	452.2
160°	456.8	456.9	456.9	457.0	457.1	457.2	457.2	457.3	457.2	457.2	457.1
162.5°	461.1	461.1	461.2	461.4	461.6	461.8	462.0	462.2	462.0	461.8	461.6
165°	466.8	466.8	466.9	467.1	467.3	467.5	467.8	468.0	467.8	467.5	467.3
167.5°	471.2	471.2	471.2	471.3	471.7	472.0	472.3	472.6	472.3	472.0	471.7
170°	473.7	473.7	473.7	473.9	474.2	474.5	474.8	475.2	474.8	474.5	474.2
172.5°	475.3	475.2	475.2	475.3	475.7	476.1	476.5	476.8	476.5	476.1	475.7
175°	477.4	477.4	477.3	477.4	477.8	478.2	478.6	479.0	478.6	478.2	477.8
177.5°	478.3	478.3	478.2	478.3	478.6	479.0	479.3	479.6	479.3	479.0	478.6
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1237.8	1232.2	1228.3	1219.6	1214.1	1208.0	1202.0	1205.9	1205.5	1205.0	1205.0
5°	1196.3	1183.8	1172.6	1158.0	1148.8	1137.5	1128.9	1127.8	1130.0	1122.4	1118.1
7.5°	1155.1	1138.1	1122.1	1106.0	1089.0	1075.4	1066.9	1062.9	1057.4	1052.7	1047.9
10°	1126.2	1106.3	1090.6	1070.6	1052.3	1036.2	1026.0	1018.9	1015.1	1011.4	1004.3
12.5°	1096.5	1076.9	1057.0	1034.4	1017.0	998.2	990.5	982.7	975.5	971.2	961.6
15°	1052.9	1027.5	1006.5	982.8	963.4	945.1	934.3	918.6	916.5	911.1	901.4
17.5°	1009.2	981.7	952.7	935.2	913.2	894.1	877.7	872.5	857.1	851.3	842.8
20°	974.7	949.4	927.2	904.1	872.3	854.4	841.5	834.6	822.1	814.6	809.2
22.5°	944.9	919.2	893.7	866.6	840.3	820.4	811.0	800.0	793.2	782.7	776.8
25°	902.5	874.4	843.7	814.6	795.7	780.6	765.6	755.8	746.2	741.2	730.5
27.5°	853.1	823.8	795.0	772.9	749.8	734.9	721.2	712.6	700.9	692.8	686.8
30°	825.9	791.4	766.6	746.6	717.0	703.0	692.8	682.0	673.4	664.7	658.8
32.5°	794.4	763.0	739.4	714.8	692.0	676.7	663.5	653.9	646.6	638.4	632.5
35°	745.0	718.7	694.3	669.6	652.8	637.2	621.6	613.5	606.5	599.0	593.6
37.5°	700.4	675.7	652.7	629.2	608.4	595.7	583.1	576.9	567.4	562.4	556.9
40°	672.8	648.6	623.8	601.1	579.6	569.8	558.5	549.4	540.7	536.9	531.0
42.5°	642.6	618.4	597.5	573.1	555.4	542.2	531.8	521.7	515.3	509.8	506.4
45°	597.9	576.3	555.8	531.6	514.8	503.5	491.6	482.5	476.6	472.8	466.8
47.5°	554.4	532.8	512.1	490.9	474.8	461.8	450.0	443.5	435.7	431.1	427.1
50°	522.9	503.5	481.4	462.0	445.8	432.9	423.2	415.1	408.1	402.2	399.5
52.5°	494.0	473.3	454.2	436.2	419.1	404.4	395.6	387.1	381.8	375.0	371.9
55°	446.4	426.4	410.3	392.4	375.7	363.4	352.6	345.0	339.6	332.1	327.8
57.5°	401.6	383.7	364.4	349.0	331.8	321.3	312.4	302.1	295.6	289.6	285.4
60°	371.5	350.9	334.2	319.7	304.6	291.1	283.0	275.0	267.9	262.0	258.3
62.5°	339.9	322.1	306.2	290.3	276.6	264.8	255.4	248.7	242.5	238.7	235.0
65°	291.7	277.7	261.5	248.5	235.6	227.0	219.4	213.5	209.1	206.4	203.3
67.5°	247.2	233.6	219.5	206.8	198.2	191.6	186.6	181.6	179.4	175.9	173.8
70°	218.3	204.3	191.9	182.2	173.6	168.7	165.5	161.8	159.5	155.3	153.1
72.5°	186.9	176.7	167.8	159.8	152.9	148.5	144.3	139.7	136.3	131.5	129.4
75°	147.2	138.0	131.0	125.6	121.3	115.3	109.4	104.6	103.0	101.3	100.8
77.5°	109.0	103.2	98.2	93.6	88.2	83.9	82.6	81.5	81.2	80.3	80.3
80°	85.7	80.3	76.5	71.1	67.9	67.9	67.9	66.9	67.4	67.4	67.4
82.5°	63.7	58.8	56.7	54.7	54.1	54.6	54.6	54.7	54.4	55.3	54.9
85°	32.9	33.4	34.5	34.0	34.5	34.5	35.6	35.0	35.6	34.5	35.6
87.5°	12.8	14.3	14.9	15.5	16.2	15.9	16.4	16.5	17.0	17.0	17.1
90°	3.5	4.4	5.5	6.5	7.5	8.6	8.9	9.2	9.5	9.8	10.1
92.5°	5.7	6.0	6.8	7.5	8.3	9.1	9.6	10.1	10.6	11.2	11.4
95°	8.7	7.5	8.4	9.3	10.1	11.0	11.6	12.1	12.7	13.2	13.5
97.5°	37.8	34.2	28.5	22.8	17.2	11.5	12.1	12.8	13.4	14.0	14.3
100°	66.5	61.1	48.8	36.4	24.1	11.7	12.4	13.0	13.6	14.3	14.7
102.5°	83.5	77.3	63.8	50.4	36.9	23.4	21.5	19.5	17.5	15.6	14.7
105°	109.6	106.4	99.3	92.2	85.1	78.0	63.9	49.9	36.0	21.9	15.1
107.5°	137.4	138.4	139.5	140.6	141.7	142.8	132.6	122.3	112.1	101.8	91.4
110°	156.3	157.0	157.9	158.8	159.6	160.5	157.9	155.3	152.7	150.0	143.1



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	174.3	175.0	175.9	176.7	177.6	178.5	178.5	178.6	178.6	178.6	177.4
115°	200.8	201.5	202.2	202.9	203.6	204.3	205.1	205.9	206.7	207.5	208.0
117.5°	227.4	227.9	228.2	228.6	229.0	229.3	230.0	230.6	231.2	231.9	232.2
120°	244.2	244.6	244.9	245.1	245.3	245.6	246.2	246.8	247.5	248.1	248.4
122.5°	260.2	260.6	260.9	261.2	261.5	261.8	262.2	262.7	263.2	263.6	263.8
125°	283.0	283.4	283.8	284.1	284.4	284.7	284.9	285.0	285.2	285.3	285.5
127.5°	304.9	305.4	305.8	306.2	306.6	307.0	307.2	307.4	307.7	307.9	308.0
130°	318.6	319.1	319.4	319.7	320.0	320.3	320.6	320.9	321.2	321.5	321.6
132.5°	331.7	332.1	332.4	332.6	332.9	333.1	333.4	333.7	334.1	334.4	334.5
135°	351.0	351.4	351.7	352.0	352.4	352.7	352.9	353.2	353.4	353.6	353.6
137.5°	368.6	369.0	369.2	369.4	369.6	369.7	370.1	370.5	370.8	371.2	371.4
140°	379.5	379.9	380.1	380.3	380.6	380.8	381.1	381.4	381.8	382.1	382.1
142.5°	390.1	390.4	390.6	390.9	391.1	391.3	391.6	391.9	392.1	392.4	392.4
145°	405.1	405.4	405.6	405.8	405.9	406.1	406.2	406.4	406.5	406.7	406.8
147.5°	418.2	418.5	418.7	418.8	419.0	419.1	419.3	419.5	419.6	419.8	419.6
150°	426.3	426.4	426.6	426.7	426.9	427.1	427.2	427.4	427.5	427.7	427.7
152.5°	433.5	433.6	433.6	433.7	433.8	434.0	434.2	434.5	434.7	435.1	435.0
155°	443.2	443.1	443.2	443.3	443.4	443.5	443.9	444.3	444.7	445.0	445.0
157.5°	452.2	452.1	452.0	451.9	451.9	451.8	452.3	452.7	453.2	453.7	453.6
160°	457.0	456.9	456.9	456.8	456.7	456.6	457.1	457.6	458.0	458.5	458.5
162.5°	461.4	461.2	461.1	461.1	461.0	460.9	461.4	462.0	462.6	463.0	463.1
165°	467.1	466.9	466.8	466.8	466.7	466.6	467.2	467.9	468.5	469.1	469.1
167.5°	471.3	471.2	471.2	471.2	471.2	471.2	471.8	472.5	473.0	473.6	473.6
170°	473.9	473.7	473.7	473.7	473.7	473.7	474.4	475.0	475.6	476.3	476.3
172.5°	475.3	475.2	475.2	475.3	475.4	475.4	476.0	476.7	477.3	477.9	477.9
175°	477.4	477.3	477.4	477.4	477.5	477.6	478.2	478.7	479.3	479.8	479.8
177.5°	478.3	478.2	478.3	478.3	478.4	478.5	479.0	479.5	480.0	480.5	480.5
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1199.8	1199.4	1199.8	1198.1	1199.8	1199.4	1199.8	1205.0	1205.0	1205.5	1205.9
5°	1116.5	1115.9	1114.4	1109.5	1114.4	1115.9	1116.5	1118.1	1122.4	1130.0	1127.8
7.5°	1043.7	1043.0	1038.2	1038.3	1038.2	1043.0	1043.7	1047.9	1052.7	1057.4	1062.9
10°	1000.6	1001.1	994.7	990.9	994.7	1001.1	1000.6	1004.3	1011.4	1015.1	1018.9
12.5°	958.8	956.2	951.1	946.9	951.1	956.2	958.8	961.6	971.2	975.5	982.7
15°	903.6	898.2	885.2	886.3	885.2	898.2	903.6	901.4	911.1	916.5	918.6
17.5°	838.5	834.6	834.3	826.8	834.3	834.6	838.5	842.8	851.3	857.1	872.5
20°	800.6	797.9	798.9	791.4	798.9	797.9	800.6	809.2	814.6	822.1	834.6
22.5°	770.8	768.1	763.6	761.2	763.6	768.1	770.8	776.8	782.7	793.2	800.0
25°	727.2	722.9	718.7	721.4	718.7	722.9	727.2	730.5	741.2	746.2	755.8
27.5°	683.7	680.5	676.1	675.6	676.1	680.5	683.7	686.8	692.8	700.9	712.6
30°	656.1	652.8	650.7	648.0	650.7	652.8	656.1	658.8	664.7	673.4	682.0
32.5°	628.0	627.4	623.5	623.0	623.5	627.4	628.0	632.5	638.4	646.6	653.9
35°	591.4	588.2	587.1	587.6	587.1	588.2	591.4	593.6	599.0	606.5	613.5
37.5°	556.6	552.2	550.3	548.3	550.3	552.2	556.6	556.9	562.4	567.4	576.9
40°	531.6	527.3	526.2	525.1	526.2	527.3	531.6	531.0	536.9	540.7	549.4
42.5°	503.5	501.8	501.1	499.2	501.1	501.8	503.5	506.4	509.8	515.3	521.7
45°	465.2	464.7	461.4	462.6	461.4	464.7	465.2	466.8	472.8	476.6	482.5
47.5°	424.9	422.6	420.3	421.8	420.3	422.6	424.9	427.1	431.1	435.7	443.5
50°	397.4	396.2	391.4	392.4	391.4	396.2	397.4	399.5	402.2	408.1	415.1
52.5°	369.7	365.6	363.8	363.1	363.8	365.6	369.7	371.9	375.0	381.8	387.1
55°	324.0	319.2	317.0	315.9	317.0	319.2	324.0	327.8	332.1	339.6	345.0
57.5°	279.2	277.8	276.2	277.3	276.2	277.8	279.2	285.4	289.6	295.6	302.1
60°	252.9	252.9	252.9	252.3	252.9	252.9	252.9	258.3	262.0	267.9	275.0
62.5°	232.6	231.2	230.8	231.6	230.8	231.2	232.6	235.0	238.7	242.5	248.7
65°	201.6	201.1	198.9	198.4	198.9	201.1	201.6	203.3	206.4	209.1	213.5
67.5°	172.4	170.5	169.8	169.1	169.8	170.5	172.4	173.8	175.9	179.4	181.6
70°	150.4	149.3	146.1	146.6	146.1	149.3	150.4	153.1	155.3	159.5	161.8
72.5°	126.7	125.6	124.9	124.2	124.9	125.6	126.7	129.4	131.5	136.3	139.7
75°	100.3	99.7	99.2	101.3	99.2	99.7	100.3	100.8	101.3	103.0	104.6
77.5°	80.3	80.3	80.6	79.8	80.6	80.3	80.3	80.3	80.3	81.2	81.5
80°	67.4	67.4	66.9	66.9	66.9	67.4	67.4	67.4	67.4	67.4	66.9
82.5°	54.0	54.4	54.7	53.9	54.7	54.4	54.0	54.9	55.3	54.4	54.7
85°	35.6	35.0	36.1	35.6	36.1	35.0	35.6	35.6	34.5	35.6	35.0
87.5°	18.0	17.2	17.2	17.7	17.2	17.2	18.0	17.1	17.0	17.0	16.5
90°	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2
92.5°	11.6	11.6	11.7	11.8	11.7	11.6	11.6	11.4	11.2	10.6	10.1
95°	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.2	12.7	12.1
97.5°	14.4	14.5	14.6	14.7	14.6	14.5	14.4	14.3	14.0	13.4	12.8
100°	14.7	14.8	14.9	15.0	14.9	14.8	14.7	14.7	14.3	13.6	13.0
102.5°	14.8	15.0	15.1	15.2	15.1	15.0	14.8	14.7	15.6	17.5	19.5
105°	15.2	15.4	15.5	15.7	15.5	15.4	15.2	15.1	21.9	36.0	49.9
107.5°	80.8	70.3	59.7	49.2	59.7	70.3	80.8	91.4	101.8	112.1	122.3
110°	131.8	120.5	109.2	97.9	109.2	120.5	131.8	143.1	150.0	152.7	155.3



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	175.1	172.7	170.3	167.9	170.3	172.7	175.1	177.4	178.6	178.6	178.6
115°	208.3	208.7	209.0	209.3	209.0	208.7	208.3	208.0	207.5	206.7	205.9
117.5°	232.3	232.3	232.4	232.5	232.4	232.3	232.3	232.2	231.9	231.2	230.6
120°	248.4	248.4	248.4	248.4	248.4	248.4	248.4	248.4	248.1	247.5	246.8
122.5°	263.9	264.0	264.0	264.1	264.0	264.0	263.9	263.8	263.6	263.2	262.7
125°	285.7	285.8	286.0	286.1	286.0	285.8	285.7	285.5	285.3	285.2	285.0
127.5°	307.8	307.7	307.5	307.4	307.5	307.7	307.8	308.0	307.9	307.7	307.4
130°	321.5	321.3	321.2	321.0	321.2	321.3	321.5	321.6	321.5	321.2	320.9
132.5°	334.2	334.0	333.7	333.6	333.7	334.0	334.2	334.5	334.4	334.1	333.7
135°	353.4	353.2	352.9	352.7	352.9	353.2	353.4	353.6	353.6	353.4	353.2
137.5°	371.2	371.1	370.9	370.7	370.9	371.1	371.2	371.4	371.2	370.8	370.5
140°	382.0	381.8	381.7	381.5	381.7	381.8	382.0	382.1	382.1	381.8	381.4
142.5°	392.1	392.0	391.7	391.5	391.7	392.0	392.1	392.4	392.4	392.1	391.9
145°	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.7	406.5	406.4
147.5°	419.3	418.9	418.6	418.2	418.6	418.9	419.3	419.6	419.8	419.6	419.5
150°	427.5	427.2	427.0	426.7	427.0	427.2	427.5	427.7	427.7	427.5	427.4
152.5°	434.7	434.3	434.0	433.6	434.0	434.3	434.7	435.0	435.1	434.7	434.5
155°	444.5	444.0	443.5	443.1	443.5	444.0	444.5	445.0	445.0	444.7	444.3
157.5°	453.0	452.4	451.8	451.1	451.8	452.4	453.0	453.6	453.7	453.2	452.7
160°	458.0	457.4	456.9	456.3	456.9	457.4	458.0	458.5	458.5	458.0	457.6
162.5°	462.6	462.1	461.6	461.1	461.6	462.1	462.6	463.1	463.0	462.6	462.0
165°	468.6	468.1	467.5	467.0	467.5	468.1	468.6	469.1	469.1	468.5	467.9
167.5°	473.0	472.5	471.8	471.2	471.8	472.5	473.0	473.6	473.6	473.0	472.5
170°	475.6	475.0	474.4	473.7	474.4	475.0	475.6	476.3	476.3	475.6	475.0
172.5°	477.2	476.5	475.9	475.2	475.9	476.5	477.2	477.9	477.9	477.3	476.7
175°	479.2	478.6	477.9	477.3	477.9	478.6	479.2	479.8	479.8	479.3	478.7
177.5°	479.8	479.2	478.6	477.9	478.6	479.2	479.8	480.5	480.5	480.0	479.5
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1202.0	1208.0	1214.1	1219.6	1228.3	1232.2	1237.8	1239.9	1246.4	1255.9	1263.7
5°	1128.9	1137.5	1148.8	1158.0	1172.6	1183.8	1196.3	1208.2	1222.2	1242.1	1259.9
7.5°	1066.9	1075.4	1089.0	1106.0	1122.1	1138.1	1155.1	1171.2	1191.3	1219.9	1248.2
10°	1026.0	1036.2	1052.3	1070.6	1090.6	1106.3	1126.2	1146.7	1171.5	1204.4	1238.3
12.5°	990.5	998.2	1017.0	1034.4	1057.0	1076.9	1096.5	1120.4	1148.6	1183.7	1224.6
15°	934.3	945.1	963.4	982.8	1006.5	1027.5	1052.9	1082.0	1109.5	1152.6	1202.2
17.5°	877.7	894.1	913.2	935.2	952.7	981.7	1009.2	1039.1	1072.9	1118.6	1173.1
20°	841.5	854.4	872.3	904.1	927.2	949.4	974.7	1011.9	1043.1	1095.0	1151.5
22.5°	811.0	820.4	840.3	866.6	893.7	919.2	944.9	980.4	1019.0	1068.2	1129.6
25°	765.6	780.6	795.7	814.6	843.7	874.4	902.5	932.6	973.6	1026.0	1092.3
27.5°	721.2	734.9	749.8	772.9	795.0	823.8	853.1	887.7	931.7	987.0	1054.2
30°	692.8	703.0	717.0	746.6	766.6	791.4	825.9	856.7	897.6	956.4	1027.5
32.5°	663.5	676.7	692.0	714.8	739.4	763.0	794.4	827.8	869.6	927.5	1000.4
35°	621.6	637.2	652.8	669.6	694.3	718.7	745.0	781.7	824.3	880.4	952.0
37.5°	583.1	595.7	608.4	629.2	652.7	675.7	700.4	736.5	776.7	837.1	902.9
40°	558.5	569.8	579.6	601.1	623.8	648.6	672.8	704.6	747.7	804.4	868.0
42.5°	531.8	542.2	555.4	573.1	597.5	618.4	642.6	672.7	713.2	770.7	826.6
45°	491.6	503.5	514.8	531.6	555.8	576.3	597.9	626.5	668.0	715.4	765.0
47.5°	450.0	461.8	474.8	490.9	512.1	532.8	554.4	579.7	617.6	664.2	697.6
50°	423.2	432.9	445.8	462.0	481.4	503.5	522.9	550.4	586.5	623.2	652.3
52.5°	395.6	404.4	419.1	436.2	454.2	473.3	494.0	517.6	550.3	584.8	607.9
55°	352.6	363.4	375.7	392.4	410.3	426.4	446.4	470.6	496.5	522.4	538.1
57.5°	312.4	321.3	331.8	349.0	364.4	383.7	401.6	420.5	444.4	464.0	474.2
60°	283.0	291.1	304.6	319.7	334.2	350.9	371.5	390.3	408.6	424.3	432.4
62.5°	255.4	264.8	276.6	290.3	306.2	322.1	339.9	355.8	372.0	385.5	390.9
65°	219.4	227.0	235.6	248.5	261.5	277.7	291.7	307.8	319.7	327.3	332.1
67.5°	186.6	191.6	198.2	206.8	219.5	233.6	247.2	259.8	269.7	275.0	279.2
70°	165.5	168.7	173.6	182.2	191.9	204.3	218.3	227.5	236.1	240.4	244.8
72.5°	144.3	148.5	152.9	159.8	167.8	176.7	186.9	198.2	203.0	208.1	210.7
75°	109.4	115.3	121.3	125.6	131.0	138.0	147.2	154.2	156.9	161.2	161.8
77.5°	82.6	83.9	88.2	93.6	98.2	103.2	109.0	115.3	116.5	118.8	120.3
80°	67.9	67.9	67.9	71.1	76.5	80.3	85.7	89.0	91.1	91.7	92.2
82.5°	54.6	54.6	54.1	54.7	56.7	58.8	63.7	67.4	69.1	68.8	67.6
85°	35.6	34.5	34.5	34.0	34.5	33.4	32.9	35.0	38.3	38.3	37.2
87.5°	16.4	15.9	16.2	15.5	14.9	14.3	12.8	13.1	12.9	14.5	13.9
90°	8.9	8.6	7.5	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.3
92.5°	9.6	9.1	8.3	7.5	6.8	6.0	5.7	5.9	6.2	6.4	6.7
95°	11.6	11.0	10.1	9.3	8.4	7.5	8.7	12.0	15.2	18.5	21.7
97.5°	12.1	11.5	17.2	22.8	28.5	34.2	37.8	39.3	40.7	42.1	43.6
100°	12.4	11.7	24.1	36.4	48.8	61.1	66.5	64.9	63.3	61.7	60.1
102.5°	21.5	23.4	36.9	50.4	63.8	77.3	83.5	82.4	81.2	80.1	78.9
105°	63.9	78.0	85.1	92.2	99.3	106.4	109.6	108.7	107.8	106.9	106.1
107.5°	132.6	142.8	141.7	140.6	139.5	138.4	137.4	136.7	136.1	135.4	134.7
110°	157.9	160.5	159.6	158.8	157.9	157.0	156.3	155.7	155.0	154.4	153.8



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	178.5	178.5	177.6	176.7	175.9	175.0	174.3	173.6	173.1	172.5	172.0
115°	205.1	204.3	203.6	202.9	202.2	201.5	200.8	200.3	199.9	199.4	198.9
117.5°	230.0	229.3	229.0	228.6	228.2	227.9	227.4	226.8	226.2	225.7	225.1
120°	246.2	245.6	245.3	245.1	244.9	244.6	244.2	243.4	242.7	242.0	241.3
122.5°	262.2	261.8	261.5	261.2	260.9	260.6	260.2	259.6	259.0	258.4	257.9
125°	284.9	284.7	284.4	284.1	283.8	283.4	283.0	282.3	281.7	281.1	280.4
127.5°	307.2	307.0	306.6	306.2	305.8	305.4	304.9	304.3	303.6	303.0	302.4
130°	320.6	320.3	320.0	319.7	319.4	319.1	318.6	318.0	317.3	316.7	316.1
132.5°	333.4	333.1	332.9	332.6	332.4	332.1	331.7	331.1	330.4	329.8	329.2
135°	352.9	352.7	352.4	352.0	351.7	351.4	351.0	350.5	350.1	349.6	349.1
137.5°	370.1	369.7	369.6	369.4	369.2	369.0	368.6	368.0	367.4	366.9	366.2
140°	381.1	380.8	380.6	380.3	380.1	379.9	379.5	379.1	378.6	378.1	377.6
142.5°	391.6	391.3	391.1	390.9	390.6	390.4	390.1	389.6	389.1	388.6	388.2
145°	406.2	406.1	405.9	405.8	405.6	405.4	405.1	404.6	404.0	403.5	402.9
147.5°	419.3	419.1	419.0	418.8	418.7	418.5	418.2	417.9	417.5	417.2	416.8
150°	427.2	427.1	426.9	426.7	426.6	426.4	426.3	426.0	425.8	425.6	425.3
152.5°	434.2	434.0	433.8	433.7	433.6	433.6	433.5	433.3	433.2	433.1	433.0
155°	443.9	443.5	443.4	443.3	443.2	443.1	443.2	443.4	443.5	443.6	443.8
157.5°	452.3	451.8	451.9	451.9	452.0	452.1	452.2	452.2	452.2	452.2	452.3
160°	457.1	456.6	456.7	456.8	456.9	456.9	457.0	457.1	457.2	457.2	457.3
162.5°	461.4	460.9	461.0	461.1	461.1	461.2	461.4	461.6	461.8	462.0	462.2
165°	467.2	466.6	466.7	466.8	466.8	466.9	467.1	467.3	467.5	467.8	468.0
167.5°	471.8	471.2	471.2	471.2	471.2	471.2	471.3	471.7	472.0	472.3	472.6
170°	474.4	473.7	473.7	473.7	473.7	473.7	473.9	474.2	474.5	474.8	475.2
172.5°	476.0	475.4	475.4	475.3	475.2	475.2	475.3	475.7	476.1	476.5	476.8
175°	478.2	477.6	477.5	477.4	477.4	477.3	477.4	477.8	478.2	478.6	479.0
177.5°	479.0	478.5	478.4	478.3	478.3	478.2	478.3	478.6	479.0	479.3	479.6
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1266.2	1271.0	1277.0	1286.1	1293.0	1299.0	1300.3	1302.0	1306.4	1313.7	1319.3
5°	1274.5	1286.8	1306.8	1326.2	1347.3	1364.5	1380.6	1391.9	1402.7	1425.4	1443.8
7.5°	1271.8	1299.5	1330.7	1365.6	1400.8	1435.0	1466.7	1495.1	1523.3	1556.3	1593.9
10°	1270.1	1302.5	1344.5	1389.3	1438.4	1486.3	1532.7	1568.8	1610.8	1648.6	1696.5
12.5°	1261.9	1308.5	1358.8	1416.0	1476.3	1531.6	1592.6	1642.5	1690.7	1745.2	1800.9
15°	1251.3	1307.9	1371.5	1447.5	1539.1	1606.0	1668.5	1755.3	1814.7	1873.9	1953.8
17.5°	1231.8	1300.8	1380.3	1479.1	1555.5	1645.4	1739.5	1808.1	1887.9	1971.5	2043.8
20°	1216.2	1296.6	1385.5	1482.6	1580.1	1677.7	1768.8	1850.8	1933.2	2029.7	2089.1
22.5°	1200.7	1280.2	1372.5	1475.7	1580.6	1683.3	1786.5	1882.7	1975.5	2072.8	2148.6
25°	1167.7	1262.0	1362.3	1467.4	1571.0	1684.2	1807.0	1914.4	2029.2	2129.5	2201.2
27.5°	1134.2	1220.8	1320.6	1427.2	1542.3	1676.1	1820.7	1942.6	2057.7	2129.5	2152.0
30°	1104.1	1195.7	1287.4	1395.7	1520.3	1669.6	1823.3	1962.9	2057.2	2088.5	2065.3
32.5°	1073.5	1156.5	1247.3	1358.2	1490.5	1653.7	1826.7	1950.8	2007.6	1983.7	1889.4
35°	1019.5	1094.4	1182.3	1293.3	1445.3	1644.8	1812.5	1896.6	1882.5	1747.8	1569.9
37.5°	961.6	1022.7	1104.1	1220.2	1398.5	1609.8	1751.2	1763.6	1642.4	1435.4	1229.9
40°	915.9	970.9	1054.5	1175.8	1362.3	1575.3	1689.6	1639.4	1451.3	1221.1	1049.6
42.5°	871.5	917.9	998.4	1129.2	1327.9	1528.3	1597.7	1488.5	1271.5	1053.8	897.9
45°	796.2	840.0	920.8	1055.0	1257.2	1438.4	1429.2	1239.4	1022.2	846.9	717.6
47.5°	724.8	763.0	838.9	976.0	1174.3	1303.5	1217.8	1015.9	831.6	691.0	598.7
50°	674.4	712.2	787.7	923.0	1107.9	1202.2	1079.8	885.2	716.4	600.0	526.7
52.5°	626.1	663.0	732.0	863.9	1027.6	1084.0	952.6	772.2	631.5	531.0	468.0
55°	558.5	586.5	648.6	774.7	897.1	910.0	776.8	625.9	510.0	439.9	396.8
57.5°	489.6	513.7	575.0	675.5	761.3	754.6	628.4	497.8	419.8	367.7	336.4
60°	444.7	468.5	522.4	608.6	673.4	650.7	534.8	429.7	362.8	324.6	299.8
62.5°	402.9	421.4	471.9	534.9	581.5	555.8	457.2	370.2	317.1	284.9	265.2
65°	342.3	357.4	397.8	430.7	456.6	431.8	349.9	289.5	251.2	228.5	215.1
67.5°	284.8	294.4	319.9	331.8	350.0	322.8	263.1	222.7	200.9	181.8	172.4
70°	248.5	255.6	269.0	278.7	283.6	255.6	211.4	181.6	163.3	149.9	143.9
72.5°	212.3	218.5	221.2	229.1	226.6	200.3	169.9	146.3	133.2	124.0	116.4
75°	162.2	164.9	162.2	159.1	152.0	133.7	112.6	100.8	91.1	86.8	84.1
77.5°	118.3	117.4	113.8	108.7	96.7	85.2	73.8	69.9	65.7	63.4	62.4
80°	91.1	89.0	85.7	77.6	67.4	59.3	56.6	53.9	52.3	49.6	49.0
82.5°	67.8	66.5	61.2	54.3	47.1	43.3	41.1	40.1	38.5	37.1	37.0
85°	36.1	34.5	28.6	24.8	23.7	22.7	22.1	22.1	20.0	19.4	19.4
87.5°	11.9	9.4	9.2	8.0	8.2	7.5	8.2	7.5	7.3	7.8	7.0
90°	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.5	8.6	8.9	9.2
92.5°	6.4	6.2	5.9	5.7	6.0	6.8	7.5	8.3	9.1	9.6	10.1
95°	18.5	15.2	12.0	8.7	7.5	8.4	9.3	10.1	11.0	11.6	12.1
97.5°	42.1	40.7	39.3	37.8	34.2	28.5	22.8	17.2	11.5	12.1	12.8
100°	61.7	63.3	64.9	66.5	61.1	48.8	36.4	24.1	11.7	12.4	13.0
102.5°	80.1	81.2	82.4	83.5	77.3	63.8	50.4	36.9	23.4	21.5	19.5
105°	106.9	107.8	108.7	109.6	106.4	99.3	92.2	85.1	78.0	63.9	49.9
107.5°	135.4	136.1	136.7	137.4	138.4	139.5	140.6	141.7	142.8	132.6	122.3
110°	154.4	155.0	155.7	156.3	157.0	157.9	158.8	159.6	160.5	157.9	155.3





TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	172.5	173.1	173.6	174.3	175.0	175.9	176.7	177.6	178.5	178.5	178.6
115°	199.4	199.9	200.3	200.8	201.5	202.2	202.9	203.6	204.3	205.1	205.9
117.5°	225.7	226.2	226.8	227.4	227.9	228.2	228.6	229.0	229.3	230.0	230.6
120°	242.0	242.7	243.4	244.2	244.6	244.9	245.1	245.3	245.6	246.2	246.8
122.5°	258.4	259.0	259.6	260.2	260.6	260.9	261.2	261.5	261.8	262.2	262.7
125°	281.1	281.7	282.3	283.0	283.4	283.8	284.1	284.4	284.7	284.9	285.0
127.5°	303.0	303.6	304.3	304.9	305.4	305.8	306.2	306.6	307.0	307.2	307.4
130°	316.7	317.3	318.0	318.6	319.1	319.4	319.7	320.0	320.3	320.6	320.9
132.5°	329.8	330.4	331.1	331.7	332.1	332.4	332.6	332.9	333.1	333.4	333.7
135°	349.6	350.1	350.5	351.0	351.4	351.7	352.0	352.4	352.7	352.9	353.2
137.5°	366.9	367.4	368.0	368.6	369.0	369.2	369.4	369.6	369.7	370.1	370.5
140°	378.1	378.6	379.1	379.5	379.9	380.1	380.3	380.6	380.8	381.1	381.4
142.5°	388.6	389.1	389.6	390.1	390.4	390.6	390.9	391.1	391.3	391.6	391.9
145°	403.5	404.0	404.6	405.1	405.4	405.6	405.8	405.9	406.1	406.2	406.4
147.5°	417.2	417.5	417.9	418.2	418.5	418.7	418.8	419.0	419.1	419.3	419.5
150°	425.6	425.8	426.0	426.3	426.4	426.6	426.7	426.9	427.1	427.2	427.4
152.5°	433.1	433.2	433.3	433.5	433.6	433.6	433.7	433.8	434.0	434.2	434.5
155°	443.6	443.5	443.4	443.2	443.1	443.2	443.3	443.4	443.5	443.9	444.3
157.5°	452.2	452.2	452.2	452.2	452.1	452.0	451.9	451.9	451.8	452.3	452.7
160°	457.2	457.2	457.1	457.0	456.9	456.9	456.8	456.7	456.6	457.1	457.6
162.5°	462.0	461.8	461.6	461.4	461.2	461.1	461.1	461.0	460.9	461.4	462.0
165°	467.8	467.5	467.3	467.1	466.9	466.8	466.8	466.7	466.6	467.2	467.9
167.5°	472.3	472.0	471.7	471.3	471.2	471.2	471.2	471.2	471.2	471.8	472.5
170°	474.8	474.5	474.2	473.9	473.7	473.7	473.7	473.7	473.7	474.4	475.0
172.5°	476.5	476.1	475.7	475.3	475.2	475.2	475.3	475.4	475.4	476.0	476.7
175°	478.6	478.2	477.8	477.4	477.3	477.4	477.4	477.5	477.6	478.2	478.7
177.5°	479.3	479.0	478.6	478.3	478.2	478.3	478.3	478.4	478.5	479.0	479.5
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3	1259.3
2.5°	1328.3	1328.3	1330.1	1336.6	1337.4	1343.0	1341.3
5°	1459.9	1470.1	1473.9	1490.1	1499.8	1504.1	1495.5
7.5°	1620.8	1649.6	1663.3	1680.3	1695.3	1699.8	1688.1
10°	1738.0	1768.2	1793.6	1809.3	1823.8	1833.5	1845.9
12.5°	1851.5	1888.6	1912.6	1934.7	1949.7	1962.0	1964.1
15°	1974.8	2030.8	2073.4	2104.7	2120.3	2128.4	2125.2
17.5°	2099.0	2151.0	2181.4	2213.3	2234.9	2236.0	2236.6
20°	2169.4	2220.0	2255.1	2278.8	2303.0	2302.0	2307.4
22.5°	2216.4	2256.3	2283.1	2300.3	2308.7	2304.5	2305.6
25°	2238.4	2250.2	2245.4	2217.9	2210.9	2185.6	2189.8
27.5°	2124.9	2068.9	2010.9	1936.3	1877.4	1830.3	1832.7
30°	1970.9	1871.8	1758.6	1663.7	1578.5	1554.8	1504.1
32.5°	1755.8	1606.9	1474.3	1385.9	1312.8	1293.0	1248.8
35°	1390.9	1246.4	1110.0	1028.1	995.7	950.5	949.9
37.5°	1081.1	953.9	881.8	820.3	788.1	760.7	758.0
40°	909.5	810.2	755.8	711.6	679.9	659.3	654.5
42.5°	789.6	709.3	658.4	631.0	606.5	596.0	588.0
45°	644.8	590.9	555.2	530.4	519.2	511.0	506.8
47.5°	539.3	503.2	479.0	462.5	453.3	444.7	447.0
50°	482.0	452.3	434.5	418.9	411.9	405.9	406.5
52.5°	435.8	409.2	394.8	383.5	374.8	370.6	368.5
55°	369.8	353.1	338.6	330.5	325.6	319.7	318.1
57.5°	315.4	302.5	290.7	281.5	280.4	274.6	275.4
60°	279.2	268.5	258.8	253.9	250.2	245.3	246.9
62.5°	249.5	240.4	231.6	227.6	223.9	220.3	221.0
65°	204.3	195.7	190.3	188.1	186.6	184.9	183.3
67.5°	162.8	157.6	154.2	149.6	146.2	145.7	144.0
70°	137.0	129.9	124.0	118.0	116.5	115.9	116.5
72.5°	109.8	105.4	103.7	100.8	100.5	99.1	100.1
75°	82.5	80.9	79.8	77.6	77.6	77.6	77.6
77.5°	60.8	59.8	59.2	58.8	58.2	57.4	57.4
80°	47.5	46.9	45.8	45.8	45.3	45.8	45.3
82.5°	35.8	35.7	34.6	34.6	34.1	33.7	34.1
85°	18.3	17.8	18.9	17.8	18.3	17.3	18.3
87.5°	7.1	7.1	6.7	6.8	6.4	7.3	6.4
90°	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.6	11.2	11.4	11.6	11.6	11.7	11.8
95°	12.7	13.2	13.5	13.5	13.5	13.5	13.5
97.5°	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.6	14.3	14.7	14.7	14.8	14.9	15.0
102.5°	17.5	15.6	14.7	14.8	15.0	15.1	15.2
105°	36.0	21.9	15.1	15.2	15.4	15.5	15.7
107.5°	112.1	101.8	91.4	80.8	70.3	59.7	49.2
110°	152.7	150.0	143.1	131.8	120.5	109.2	97.9



TEST NUMBER: P332450-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	178.6	178.6	177.4	175.1	172.7	170.3	167.9
115°	206.7	207.5	208.0	208.3	208.7	209.0	209.3
117.5°	231.2	231.9	232.2	232.3	232.3	232.4	232.5
120°	247.5	248.1	248.4	248.4	248.4	248.4	248.4
122.5°	263.2	263.6	263.8	263.9	264.0	264.0	264.1
125°	285.2	285.3	285.5	285.7	285.8	286.0	286.1
127.5°	307.7	307.9	308.0	307.8	307.7	307.5	307.4
130°	321.2	321.5	321.6	321.5	321.3	321.2	321.0
132.5°	334.1	334.4	334.5	334.2	334.0	333.7	333.6
135°	353.4	353.6	353.6	353.4	353.2	352.9	352.7
137.5°	370.8	371.2	371.4	371.2	371.1	370.9	370.7
140°	381.8	382.1	382.1	382.0	381.8	381.7	381.5
142.5°	392.1	392.4	392.4	392.1	392.0	391.7	391.5
145°	406.5	406.7	406.8	406.8	406.8	406.8	406.8
147.5°	419.6	419.8	419.6	419.3	418.9	418.6	418.2
150°	427.5	427.7	427.7	427.5	427.2	427.0	426.7
152.5°	434.7	435.1	435.0	434.7	434.3	434.0	433.6
155°	444.7	445.0	445.0	444.5	444.0	443.5	443.1
157.5°	453.2	453.7	453.6	453.0	452.4	451.8	451.1
160°	458.0	458.5	458.5	458.0	457.4	456.9	456.3
162.5°	462.6	463.0	463.1	462.6	462.1	461.6	461.1
165°	468.5	469.1	469.1	468.6	468.1	467.5	467.0
167.5°	473.0	473.6	473.6	473.0	472.5	471.8	471.2
170°	475.6	476.3	476.3	475.6	475.0	474.4	473.7
172.5°	477.3	477.9	477.9	477.2	476.5	475.9	475.2
175°	479.3	479.8	479.8	479.2	478.6	477.9	477.3
177.5°	480.0	480.5	480.5	479.8	479.2	478.6	477.9
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0

(END OF REPORT)