

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332453-927

Luminaire Tested: **S123RDIW-S1000D460U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332453-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1000D460U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1000 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4270.8 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332453-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332453-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70				
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60				
2	94	87	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	51				
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44				
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38				
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33				
6	67	55	47	41	64	53	45	40	48	42	37	43	38	34	39	35	32	29				
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26				
8	58	46	38	32	55	44	36	31	40	34	29	36	31	28	33	29	26	24				
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	26	23	21				
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14310	14310	14310
5°	14364	14166	14249
10°	14283	13988	13941
15°	14130	13661	13517
20°	13919	13252	12944
25°	13702	12792	12383
30°	13415	12263	11591
35°	13119	11730	10867
40°	12847	11105	9969
45°	12490	10488	9159
50°	12097	9786	8251
55°	11695	8983	7405
60°	11328	8125	6476
65°	10847	7195	5547
70°	10247	6039	4482
75°	9374	4754	4213
80°	8356	4209	3874
85°	7052	3730	3458



TEST NUMBER: P332453-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	2.9
10°-20°	347.3	8.1
20°-30°	500.2	11.7
30°-40°	563.4	13.2
40°-50°	539.0	12.6
50°-60°	441.4	10.3
60°-70°	297.8	7.0
70°-80°	149.8	3.5
80°-90°	41.0	1.0
90°-100°	29.8	0.7
100°-110°	89.1	2.1
110°-120°	151.6	3.5
120°-130°	199.4	4.7
130°-140°	224.1	5.2
140°-150°	220.3	5.2
150°-160°	185.4	4.3
160°-170°	123.4	2.9
170°-180°	43.2	1.0
0°-30°	972.3	22.8
0°-40°	1535.7	36.0
0°-60°	2516.0	58.9
0°-90°	3004.6	70.4
90°-120°	270.4	6.3
90°-150°	914.1	21.4
90°-180°	1266.0	29.6
0°-180°	4270.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1329	1329	1329	1329	1329	
5°	1329	1324	1311	1320	1319	126
15°	1268	1255	1226	1220	1213	357
25°	1154	1125	1077	1055	1043	530
35°	998	958	893	848	827	625
45°	820	770	689	629	602	633
55°	623	568	479	418	395	559
65°	426	365	282	232	218	421
75°	225	173	114	104	101	240
85°	57	34	30	28	28	64
90°	0	4	9	10	11	4
95°	21	24	26	28	28	24
105°	81	82	85	85	86	87
115°	153	154	153	153	153	151
125°	223	224	224	222	221	199
135°	290	292	292	290	289	223
145°	352	352	353	353	352	219
155°	402	402	403	404	402	185
165°	438	437	437	439	437	124
175°	456	455	454	456	454	43
180°	457	457	457	457	457	



TEST NUMBER: P332453-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1333.7	1332.9	1332.2	1331.4	1330.6	1329.1	1326.8	1324.5	1322.2	1319.9	1322.0
5°	1329.4	1328.2	1327.0	1325.8	1324.6	1322.5	1319.7	1316.8	1314.0	1311.1	1313.2
7.5°	1317.1	1315.8	1314.5	1313.2	1311.9	1309.4	1305.7	1302.0	1298.2	1294.5	1295.7
10°	1306.8	1305.1	1303.4	1301.7	1300.1	1297.0	1292.8	1288.4	1284.1	1279.8	1280.1
12.5°	1292.1	1290.2	1288.4	1286.5	1284.6	1281.0	1275.8	1270.5	1265.3	1260.0	1259.8
15°	1268.0	1265.4	1262.7	1260.0	1257.4	1252.8	1246.0	1239.3	1232.6	1225.9	1224.7
17.5°	1237.5	1234.5	1231.4	1228.4	1225.3	1219.5	1210.9	1202.5	1193.9	1185.3	1182.8
20°	1215.1	1211.3	1207.4	1203.6	1199.8	1193.3	1184.2	1175.1	1166.0	1156.9	1153.8
22.5°	1190.1	1185.7	1181.3	1176.9	1172.5	1165.5	1155.7	1146.1	1136.4	1126.7	1122.8
25°	1153.7	1147.7	1141.7	1135.7	1129.7	1121.2	1110.2	1099.2	1088.1	1077.1	1072.1
27.5°	1109.5	1102.9	1096.2	1089.6	1083.0	1073.6	1061.3	1049.0	1036.7	1024.5	1017.5
30°	1079.3	1072.1	1064.9	1057.7	1050.5	1040.2	1026.8	1013.4	1000.0	986.6	978.4
32.5°	1049.1	1040.9	1032.8	1024.6	1016.5	1005.4	991.2	977.0	962.7	948.6	939.7
35°	998.4	989.8	981.1	972.6	963.9	952.1	937.3	922.4	907.6	892.7	882.4
37.5°	947.1	937.5	927.9	918.3	908.7	896.0	880.2	864.3	848.4	832.6	820.9
40°	914.3	903.8	893.2	882.6	872.1	858.3	841.4	824.3	807.3	790.3	777.8
42.5°	877.2	866.6	856.1	845.6	835.0	821.0	803.4	785.8	768.3	750.7	737.0
45°	820.5	809.7	798.9	788.1	777.4	762.8	744.3	725.9	707.4	689.0	675.3
47.5°	763.8	751.9	740.1	728.3	716.4	701.3	682.9	664.4	645.9	627.5	612.7
50°	722.4	711.1	699.9	688.6	677.3	662.0	642.6	623.2	603.8	584.4	569.5
52.5°	685.3	673.1	660.8	648.6	636.4	620.7	601.5	582.3	563.1	543.8	528.4
55°	623.2	611.5	599.7	588.0	576.2	560.2	539.8	519.4	499.1	478.7	464.9
57.5°	565.9	553.0	540.3	527.4	514.7	498.0	477.5	457.1	436.7	416.2	403.1
60°	526.2	513.0	499.8	486.6	473.4	456.9	437.0	417.2	397.3	377.4	364.4
62.5°	486.5	473.3	460.1	446.9	433.8	417.2	397.4	377.5	357.6	337.7	325.5
65°	425.9	412.7	399.5	386.3	373.2	357.3	338.6	319.9	301.2	282.5	270.8
67.5°	365.3	352.0	338.7	325.3	312.0	296.4	278.5	260.5	242.6	224.7	215.9
70°	325.6	312.7	299.8	286.8	273.9	259.0	242.2	225.5	208.7	191.9	183.5
72.5°	285.9	273.2	260.5	247.7	235.0	220.9	205.7	190.5	175.2	160.0	153.1
75°	225.4	213.8	202.3	190.8	179.4	167.0	153.8	140.6	127.5	114.3	111.9
77.5°	170.2	159.7	149.3	138.9	128.6	119.1	110.6	102.1	93.6	85.2	83.9
80°	134.8	124.9	115.1	105.3	95.5	88.1	83.0	78.0	73.0	67.9	67.2
82.5°	101.2	92.7	84.2	75.7	67.2	61.8	59.4	57.1	54.7	52.4	51.7
85°	57.1	51.9	46.6	41.4	36.0	33.0	32.3	31.6	30.9	30.2	29.7
87.5°	20.8	18.9	16.9	14.9	13.0	12.1	12.3	12.5	12.8	12.9	12.8
90°	0.4	1.2	2.0	2.8	3.6	4.4	5.5	6.6	7.6	8.6	9.0
92.5°	8.7	9.3	9.7	10.3	10.9	11.4	12.0	12.6	13.2	13.8	14.0
95°	21.2	21.7	22.3	22.9	23.4	24.0	24.6	25.3	25.9	26.5	26.9
97.5°	37.6	38.0	38.4	38.9	39.3	39.7	40.2	40.6	41.1	41.6	41.9
100°	48.8	49.3	49.7	50.2	50.7	51.2	51.6	52.0	52.4	52.8	53.0
102.5°	61.7	62.0	62.3	62.6	62.9	63.3	63.8	64.3	64.9	65.4	65.7
105°	80.8	81.0	81.1	81.3	81.4	81.8	82.5	83.3	84.0	84.7	84.7
107.5°	102.9	103.0	103.1	103.1	103.3	103.5	103.8	104.0	104.3	104.6	104.9
110°	116.7	116.8	117.0	117.2	117.3	117.5	117.6	117.8	118.0	118.1	118.4



TEST NUMBER: P332453-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	131.0	131.1	131.3	131.3	131.4	131.5	131.5	131.6	131.6	131.6	132.0
115°	152.6	152.8	153.0	153.3	153.5	153.6	153.4	153.3	153.1	153.0	153.0
117.5°	174.3	174.4	174.6	174.8	174.9	174.8	174.7	174.4	174.3	174.0	174.0
120°	187.7	188.2	188.7	189.2	189.6	189.7	189.3	188.9	188.5	188.1	188.1
122.5°	201.8	202.2	202.6	202.9	203.2	203.3	203.1	202.9	202.7	202.5	202.2
125°	223.3	223.6	223.8	224.0	224.3	224.3	224.1	223.9	223.8	223.6	223.3
127.5°	243.1	243.6	244.2	244.6	245.2	245.3	245.2	244.9	244.8	244.6	244.2
130°	256.4	257.0	257.6	258.3	258.9	259.0	258.8	258.6	258.3	258.1	257.8
132.5°	269.5	270.1	270.8	271.5	272.1	272.4	272.1	272.0	271.8	271.6	271.2
135°	289.7	290.2	290.7	291.1	291.6	291.8	291.8	291.7	291.6	291.5	291.2
137.5°	308.4	308.8	309.2	309.6	310.0	310.3	310.5	310.7	310.9	311.1	310.8
140°	321.3	321.7	322.1	322.5	322.9	323.1	323.2	323.3	323.4	323.4	323.4
142.5°	333.1	333.5	333.9	334.3	334.7	334.9	335.1	335.3	335.4	335.5	335.4
145°	351.5	351.6	351.8	352.0	352.1	352.3	352.5	352.8	353.0	353.2	353.2
147.5°	367.6	367.8	368.1	368.4	368.7	368.9	369.2	369.4	369.6	369.9	369.9
150°	378.7	378.9	379.1	379.2	379.4	379.5	379.7	379.9	380.0	380.2	380.2
152.5°	387.9	388.2	388.4	388.6	388.8	389.0	389.0	389.2	389.3	389.4	389.5
155°	402.4	402.4	402.4	402.4	402.4	402.5	402.6	402.7	402.7	402.8	403.1
157.5°	414.8	414.7	414.6	414.5	414.4	414.4	414.5	414.5	414.5	414.6	414.9
160°	422.6	422.4	422.2	422.1	421.9	421.8	421.8	421.8	421.8	421.8	422.2
162.5°	429.4	429.2	429.0	428.7	428.6	428.5	428.5	428.6	428.6	428.7	429.1
165°	438.3	438.1	437.8	437.6	437.4	437.3	437.3	437.3	437.3	437.3	437.8
167.5°	445.4	445.1	444.8	444.5	444.2	444.0	444.1	444.2	444.3	444.3	444.8
170°	449.5	449.2	448.9	448.5	448.2	448.1	448.1	448.1	448.1	448.1	448.6
172.5°	452.7	452.3	452.0	451.7	451.3	451.1	451.1	451.1	451.1	451.1	451.7
175°	455.9	455.6	455.3	455.0	454.6	454.5	454.5	454.5	454.5	454.5	455.0
177.5°	457.3	457.0	456.8	456.5	456.3	456.1	456.1	456.1	456.1	456.1	456.5
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0



TEST NUMBER: P332453-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4	1329.4
2.5°	1324.1	1326.3	1328.3	1329.2	1328.8	1328.5	1328.1	1327.7
5°	1315.4	1317.6	1319.7	1320.6	1320.1	1319.6	1319.1	1318.7
7.5°	1296.9	1298.1	1299.3	1299.5	1298.6	1297.8	1297.0	1296.2
10°	1280.3	1280.6	1280.8	1280.3	1279.1	1277.9	1276.7	1275.5
12.5°	1259.6	1259.6	1259.4	1258.6	1257.3	1255.8	1254.5	1253.1
15°	1223.5	1222.3	1221.1	1219.6	1218.0	1216.3	1214.7	1213.0
17.5°	1180.3	1177.7	1175.2	1172.7	1170.2	1167.7	1165.2	1162.7
20°	1150.6	1147.6	1144.5	1141.5	1138.6	1135.7	1132.8	1130.0
22.5°	1119.0	1115.1	1111.2	1107.9	1105.3	1102.6	1099.9	1097.2
25°	1067.1	1062.0	1057.0	1053.1	1050.5	1047.9	1045.3	1042.6
27.5°	1010.5	1003.5	996.5	991.0	987.0	982.9	978.9	974.9
30°	970.3	962.1	953.9	948.0	944.1	940.3	936.4	932.6
32.5°	930.7	921.9	912.9	906.5	902.5	898.4	894.4	890.3
35°	872.1	861.8	851.5	844.2	840.0	835.6	831.3	827.0
37.5°	809.2	797.5	785.8	777.3	772.0	766.7	761.4	756.1
40°	765.4	753.0	740.5	731.5	726.0	720.5	714.9	709.5
42.5°	723.4	709.8	696.2	686.9	682.0	677.1	672.1	667.2
45°	661.6	648.0	634.3	624.6	618.9	613.1	607.4	601.7
47.5°	597.8	583.0	568.1	558.1	552.9	547.9	542.7	537.6
50°	554.7	539.8	525.0	514.8	509.3	503.7	498.3	492.7
52.5°	513.0	497.6	482.1	471.9	467.0	462.1	457.2	452.2
55°	450.9	437.0	423.1	413.8	409.0	404.2	399.4	394.6
57.5°	389.9	376.8	363.7	355.1	351.0	346.9	342.9	338.7
60°	351.5	338.6	325.6	317.1	313.1	309.0	304.9	300.8
62.5°	313.3	301.2	289.0	280.7	276.6	272.3	268.0	263.7
65°	259.0	247.2	235.5	228.3	225.7	223.1	220.5	217.8
67.5°	207.2	198.4	189.6	183.8	181.0	178.2	175.3	172.5
70°	175.2	166.8	158.4	152.9	150.2	147.6	145.0	142.4
72.5°	146.3	139.4	132.6	128.7	127.5	126.4	125.3	124.2
75°	109.5	107.1	104.7	103.3	102.8	102.3	101.8	101.3
77.5°	82.6	81.3	80.0	79.1	78.7	78.2	77.7	77.2
80°	66.5	65.8	65.0	64.5	64.0	63.5	63.0	62.5
82.5°	50.9	50.2	49.5	49.1	49.0	49.0	48.8	48.7
85°	29.2	28.8	28.3	28.0	28.0	28.0	28.0	28.0
87.5°	12.7	12.5	12.4	12.3	12.1	12.0	11.8	11.6
90°	9.3	9.6	9.9	10.1	10.3	10.5	10.6	10.8
92.5°	14.3	14.6	14.8	14.9	14.8	14.7	14.6	14.5
95°	27.2	27.5	27.8	28.0	28.0	28.0	28.0	28.0
97.5°	42.3	42.7	43.0	43.2	43.2	43.2	43.1	43.1
100°	53.2	53.5	53.7	53.9	54.1	54.3	54.4	54.6
102.5°	65.9	66.1	66.4	66.5	66.5	66.4	66.4	66.3
105°	84.7	84.7	84.7	84.8	85.0	85.2	85.3	85.5
107.5°	105.1	105.4	105.6	105.7	105.6	105.5	105.4	105.4
110°	118.7	119.1	119.4	119.5	119.3	119.1	119.0	118.8



TEST NUMBER: P332453-927

CATALOG NUMBER: S123RDIW-S1000D460U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	132.4	132.8	133.2	133.3	133.2	133.2	133.2	133.2
115°	153.1	153.2	153.3	153.3	153.2	153.1	153.0	153.0
117.5°	174.0	174.0	174.0	173.9	173.6	173.4	173.2	172.9
120°	188.0	187.9	187.8	187.7	187.5	187.4	187.2	187.0
122.5°	202.1	201.8	201.6	201.5	201.2	201.0	200.7	200.5
125°	223.0	222.7	222.4	222.0	221.7	221.4	221.1	220.8
127.5°	243.8	243.3	242.8	242.4	242.1	241.7	241.3	241.0
130°	257.5	257.1	256.8	256.4	255.9	255.3	254.8	254.1
132.5°	270.8	270.5	270.1	269.7	269.3	268.8	268.4	267.9
135°	290.9	290.6	290.3	290.0	289.9	289.7	289.5	289.4
137.5°	310.5	310.1	309.7	309.4	309.1	308.9	308.6	308.2
140°	323.3	323.2	323.1	322.8	322.3	321.7	321.2	320.6
142.5°	335.3	335.3	335.2	334.9	334.5	334.1	333.7	333.2
145°	353.1	353.0	352.9	352.8	352.4	352.1	351.8	351.5
147.5°	369.9	369.9	369.9	369.6	369.2	368.6	368.1	367.7
150°	380.2	380.2	380.2	379.9	379.5	379.0	378.5	378.0
152.5°	389.6	389.8	389.9	389.8	389.4	388.9	388.5	388.1
155°	403.5	403.8	404.1	403.9	403.4	402.8	402.3	401.7
157.5°	415.3	415.7	416.0	415.9	415.5	415.0	414.5	414.2
160°	422.6	423.0	423.4	423.4	423.1	422.8	422.5	422.2
162.5°	429.5	429.9	430.3	430.2	429.8	429.2	428.7	428.2
165°	438.2	438.7	439.2	439.1	438.6	438.0	437.4	436.9
167.5°	445.3	445.8	446.2	446.2	445.8	445.3	444.8	444.3
170°	449.2	449.7	450.3	450.3	449.7	449.2	448.6	448.1
172.5°	452.2	452.7	453.1	453.1	452.6	452.0	451.5	450.9
175°	455.4	455.9	456.4	456.4	455.8	455.3	454.7	454.2
177.5°	456.9	457.3	457.6	457.6	457.2	456.8	456.3	455.8
180°	457.0	457.0	457.0	457.0	457.0	457.0	457.0	457.0

(END OF REPORT)