

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332480-927

Luminaire Tested: **S123RDIW-S1165D1030U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332480-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D1030U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6737.5 lumens
Efficiency: N/A
Efficacy: 100.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332480-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332480-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	108	108	108	108	99	99	99	99	84	84	84		70	70	70		58	58	58	52
1	98	94	90	87	91	87	84	81	74	72	70		62	61	59		51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	58		55	52	50		46	44	42	37
3	82	73	66	60	76	68	62	56	58	53	49		49	46	43		41	38	36	32
4	75	65	57	51	69	60	53	48	52	47	42		44	40	37		37	34	31	28
5	69	58	50	44	64	54	47	42	46	41	37		40	35	32		33	30	27	24
6	64	52	44	38	59	49	41	36	42	36	32		36	32	28		30	27	24	21
7	59	47	39	34	55	44	37	32	38	33	28		33	28	25		28	24	22	19
8	55	43	35	30	51	40	33	28	35	29	25		30	26	22		25	22	20	17
9	51	39	32	27	47	37	30	25	32	27	23		28	23	20		23	20	18	16
10	48	36	29	24	44	34	27	23	30	24	21		26	21	18		22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16527	16527	16527
5°	16590	16361	16455
10°	16497	16156	16101
15°	16319	15778	15611
20°	16076	15306	14948
25°	15824	14775	14301
30°	15493	14162	13387
35°	15152	13548	12550
40°	14838	12826	11514
45°	14425	12113	10577
50°	13971	11302	9530
55°	13508	10376	8552
60°	13082	9384	7481
65°	12528	8308	6406
70°	11833	6977	5174
75°	10821	5490	4870
80°	9651	4860	4475
85°	8151	4310	4001



TEST NUMBER: P332480-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	2.1
10°-20°	401.2	6.0
20°-30°	577.6	8.6
30°-40°	650.7	9.7
40°-50°	622.5	9.2
50°-60°	509.7	7.6
60°-70°	343.9	5.1
70°-80°	173.0	2.6
80°-90°	48.8	0.7
90°-100°	38.9	0.6
100°-110°	185.6	2.8
110°-120°	445.8	6.6
120°-130°	567.6	8.4
130°-140°	606.5	9.0
140°-150°	567.1	8.4
150°-160°	457.5	6.8
160°-170°	295.2	4.4
170°-180°	101.8	1.5
0°-30°	1123.0	16.7
0°-40°	1773.6	26.3
0°-60°	2905.8	43.1
0°-90°	3471.6	51.5
90°-120°	670.3	9.9
90°-150°	2411.5	35.8
90°-180°	3266.0	48.5
0°-180°	6737.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1535	1535	1535	1535	1535	
5°	1535	1529	1514	1525	1523	146
15°	1464	1450	1416	1410	1401	412
25°	1332	1300	1244	1219	1204	613
35°	1153	1106	1031	979	955	721
45°	948	889	796	727	695	731
55°	720	656	553	483	456	645
65°	492	422	326	268	252	487
75°	260	200	132	120	117	278
85°	66	40	35	32	32	74
90°	1	9	19	22	24	6
95°	49	18	25	30	30	60
105°	237	241	174	41	35	251
115°	445	450	457	464	468	439
125°	627	633	636	638	640	560
135°	780	785	788	791	788	601
145°	901	906	908	909	909	564
155°	992	991	991	995	991	457
165°	1046	1044	1043	1049	1044	295
175°	1071	1067	1068	1073	1067	102
180°	1071	1071	1071	1071	1071	



TEST NUMBER: P332480-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1540.4	1539.4	1538.6	1537.7	1536.8	1535.0	1532.4	1529.7	1527.1	1524.4	1526.9
5°	1535.4	1534.0	1532.6	1531.2	1529.9	1527.5	1524.2	1520.8	1517.5	1514.2	1516.7
7.5°	1521.1	1519.7	1518.2	1516.7	1515.2	1512.3	1508.0	1503.6	1499.4	1495.0	1496.4
10°	1509.3	1507.3	1505.4	1503.4	1501.5	1498.0	1493.0	1488.0	1483.0	1478.1	1478.4
12.5°	1492.3	1490.2	1488.0	1485.8	1483.7	1479.6	1473.5	1467.4	1461.3	1455.2	1455.0
15°	1464.4	1461.3	1458.3	1455.2	1452.2	1446.8	1439.1	1431.3	1423.6	1415.9	1414.4
17.5°	1429.3	1425.8	1422.2	1418.6	1415.2	1408.4	1398.6	1388.7	1378.9	1369.0	1366.1
20°	1403.4	1399.0	1394.6	1390.1	1385.7	1378.2	1367.7	1357.2	1346.6	1336.2	1332.5
22.5°	1374.5	1369.4	1364.3	1359.2	1354.2	1346.0	1334.8	1323.7	1312.5	1301.2	1296.8
25°	1332.4	1325.5	1318.6	1311.6	1304.7	1294.9	1282.1	1269.5	1256.7	1244.0	1238.2
27.5°	1281.4	1273.7	1266.1	1258.5	1250.8	1239.9	1225.7	1211.6	1197.4	1183.2	1175.1
30°	1246.5	1238.2	1229.9	1221.5	1213.3	1201.3	1185.9	1170.4	1154.9	1139.4	1130.0
32.5°	1211.6	1202.2	1192.8	1183.4	1174.0	1161.1	1144.7	1128.3	1111.9	1095.6	1085.3
35°	1153.1	1143.1	1133.1	1123.2	1113.3	1099.7	1082.5	1065.4	1048.2	1031.0	1019.1
37.5°	1093.8	1082.8	1071.7	1060.6	1049.6	1034.8	1016.5	998.2	979.9	961.6	948.1
40°	1056.0	1043.8	1031.6	1019.5	1007.3	991.3	971.7	952.0	932.4	912.8	898.3
42.5°	1013.1	1000.9	988.8	976.6	964.4	948.2	927.9	907.5	887.2	867.0	851.2
45°	947.6	935.2	922.7	910.3	897.8	880.9	859.6	838.3	817.0	795.7	779.9
47.5°	882.1	868.5	854.8	841.1	827.4	809.9	788.6	767.3	746.0	724.8	707.6
50°	834.3	821.3	808.3	795.3	782.3	764.6	742.2	719.8	697.4	674.9	657.7
52.5°	791.5	777.4	763.3	749.2	735.0	716.8	694.7	672.5	650.3	628.1	610.3
55°	719.8	706.2	692.6	679.1	665.5	647.0	623.4	599.9	576.4	552.9	536.9
57.5°	653.5	638.7	623.9	609.2	594.4	575.2	551.6	527.9	504.3	480.7	465.5
60°	607.7	592.5	577.3	562.1	546.8	527.7	504.7	481.8	458.8	435.9	420.9
62.5°	561.8	546.6	531.4	516.2	501.0	481.9	458.9	435.9	413.0	390.0	376.0
65°	491.9	476.7	461.4	446.2	431.0	412.6	391.0	369.4	347.8	326.2	312.7
67.5°	421.9	406.5	391.1	375.7	360.4	342.3	321.6	300.9	280.2	259.5	249.4
70°	376.0	361.2	346.2	331.2	316.3	299.1	279.8	260.4	241.1	221.7	212.0
72.5°	330.3	315.5	300.8	286.1	271.3	255.2	237.6	220.0	202.4	184.8	176.9
75°	260.2	247.0	233.7	220.4	207.2	192.9	177.7	162.4	147.2	132.0	129.2
77.5°	196.5	184.5	172.5	160.5	148.5	137.5	127.8	118.0	108.1	98.4	96.9
80°	155.7	144.3	132.9	121.6	110.3	101.7	95.9	90.1	84.3	78.4	77.6
82.5°	116.8	107.0	97.2	87.4	77.6	71.4	68.7	65.9	63.2	60.5	59.7
85°	66.0	59.9	53.8	47.8	41.7	38.2	37.4	36.5	35.7	34.9	34.3
87.5°	24.1	22.0	19.9	17.8	15.8	14.9	15.4	15.8	16.3	16.8	16.7
90°	0.8	2.5	4.4	6.1	7.8	9.9	12.2	14.5	16.8	19.1	19.8
92.5°	14.8	14.3	13.8	13.3	12.8	13.5	15.2	16.9	18.6	20.4	21.5
95°	48.6	41.3	34.1	26.8	19.6	16.9	18.9	20.8	22.7	24.6	25.9
97.5°	97.5	94.3	91.0	87.8	84.5	76.5	63.8	51.1	38.3	25.6	27.0
100°	134.4	138.0	141.6	145.0	148.6	136.6	109.0	81.4	53.9	26.2	27.6
102.5°	176.5	179.0	181.6	184.1	186.6	172.9	142.8	112.6	82.5	52.4	48.0
105°	237.1	239.1	241.0	243.0	244.9	237.9	222.0	206.0	190.2	174.3	143.0
107.5°	301.1	302.6	304.2	305.8	307.3	309.3	311.9	314.3	316.9	319.4	296.4
110°	343.7	345.2	346.6	348.0	349.4	351.1	353.0	355.0	356.9	358.9	353.0



TEST NUMBER: P332480-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	384.4	385.7	387.0	388.3	389.6	391.2	393.1	395.1	397.0	398.9	399.0
115°	444.8	445.8	446.9	448.0	449.0	450.4	451.9	453.5	455.1	456.7	458.5
117.5°	503.2	504.5	505.8	507.1	508.4	509.5	510.3	511.1	511.9	512.7	514.1
120°	539.5	541.1	542.6	544.2	545.8	546.9	547.4	548.0	548.5	549.0	550.4
122.5°	576.4	577.7	579.0	580.3	581.6	582.6	583.3	583.9	584.6	585.3	586.3
125°	627.0	628.4	629.8	631.2	632.6	633.7	634.4	635.1	635.8	636.5	636.9
127.5°	676.0	677.4	678.8	680.2	681.7	682.8	683.7	684.5	685.3	686.2	686.7
130°	706.5	708.0	709.4	710.8	712.3	713.3	714.0	714.7	715.4	716.1	716.8
132.5°	735.9	737.3	738.6	740.1	741.5	742.5	743.1	743.6	744.2	744.7	745.4
135°	780.5	781.6	782.7	783.7	784.8	785.7	786.4	787.1	787.8	788.5	789.0
137.5°	818.7	820.1	821.4	822.8	824.1	825.0	825.4	825.8	826.2	826.6	827.4
140°	844.2	845.3	846.4	847.4	848.4	849.2	849.8	850.3	850.8	851.4	852.1
142.5°	867.8	868.8	869.9	870.9	872.0	872.8	873.3	873.9	874.4	874.9	875.5
145°	900.7	901.9	903.2	904.4	905.6	906.4	906.8	907.1	907.5	907.8	908.2
147.5°	931.8	932.6	933.3	934.1	935.0	935.6	935.9	936.3	936.6	937.0	937.3
150°	950.9	951.3	951.9	952.4	952.9	953.4	953.7	954.1	954.4	954.8	955.1
152.5°	968.0	968.3	968.5	968.8	969.0	969.2	969.5	969.6	969.9	970.1	970.7
155°	992.2	991.8	991.5	991.2	990.8	990.7	990.9	991.0	991.3	991.4	992.3
157.5°	1011.0	1011.0	1010.9	1010.9	1010.8	1010.7	1010.6	1010.3	1010.2	1010.0	1011.1
160°	1022.5	1022.2	1022.1	1021.9	1021.8	1021.5	1021.4	1021.2	1021.0	1020.9	1021.9
162.5°	1033.2	1032.8	1032.4	1031.9	1031.4	1031.1	1030.9	1030.8	1030.5	1030.4	1031.6
165°	1046.3	1045.8	1045.3	1044.7	1044.2	1043.9	1043.6	1043.5	1043.3	1043.1	1044.6
167.5°	1056.5	1055.8	1055.1	1054.4	1053.7	1053.3	1053.3	1053.3	1053.3	1053.3	1054.7
170°	1062.2	1061.5	1060.8	1060.1	1059.4	1059.1	1059.1	1059.1	1059.1	1059.1	1060.4
172.5°	1066.0	1065.2	1064.4	1063.5	1062.6	1062.3	1062.4	1062.6	1062.7	1062.9	1064.3
175°	1071.0	1070.1	1069.2	1068.3	1067.5	1067.1	1067.2	1067.5	1067.6	1067.8	1069.1
177.5°	1072.2	1071.5	1070.9	1070.2	1069.4	1069.1	1069.3	1069.4	1069.5	1069.7	1070.9
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332480-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1529.3	1531.8	1534.1	1535.2	1534.7	1534.3	1533.8	1533.3
5°	1519.2	1521.7	1524.2	1525.1	1524.6	1524.0	1523.4	1522.9
7.5°	1497.8	1499.2	1500.6	1500.8	1499.8	1498.9	1497.9	1497.0
10°	1478.7	1478.9	1479.2	1478.7	1477.3	1475.9	1474.5	1473.1
12.5°	1454.8	1454.7	1454.5	1453.7	1452.1	1450.4	1448.8	1447.2
15°	1413.1	1411.7	1410.3	1408.7	1406.7	1404.8	1402.8	1400.9
17.5°	1363.2	1360.2	1357.2	1354.4	1351.5	1348.6	1345.8	1342.8
20°	1329.0	1325.3	1321.8	1318.3	1314.9	1311.6	1308.4	1305.0
22.5°	1292.3	1287.9	1283.3	1279.5	1276.4	1273.4	1270.3	1267.2
25°	1232.4	1226.5	1220.8	1216.3	1213.3	1210.2	1207.2	1204.1
27.5°	1167.0	1159.0	1150.9	1144.5	1139.9	1135.3	1130.6	1125.9
30°	1120.5	1111.2	1101.8	1094.9	1090.4	1086.0	1081.6	1077.1
32.5°	1075.0	1064.7	1054.4	1046.9	1042.3	1037.6	1033.0	1028.3
35°	1007.3	995.4	983.5	975.0	970.0	965.0	960.0	955.1
37.5°	934.5	921.1	907.5	897.7	891.6	885.4	879.3	873.1
40°	884.0	869.6	855.2	844.9	838.4	832.1	825.8	819.4
42.5°	835.5	819.8	804.1	793.4	787.7	782.0	776.3	770.6
45°	764.1	748.4	732.6	721.4	714.8	708.1	701.5	694.8
47.5°	690.4	673.3	656.1	644.6	638.7	632.7	626.8	620.9
50°	640.6	623.4	606.3	594.5	588.2	581.8	575.4	569.1
52.5°	592.5	574.6	556.8	545.0	539.3	533.7	528.0	522.3
55°	520.8	504.7	488.7	477.9	472.4	466.8	461.3	455.7
57.5°	450.4	435.1	420.0	410.0	405.4	400.7	395.9	391.3
60°	405.9	391.0	376.0	366.2	361.6	356.8	352.1	347.5
62.5°	361.9	347.8	333.7	324.3	319.3	314.4	309.5	304.6
65°	299.1	285.6	272.0	263.7	260.7	257.6	254.6	251.5
67.5°	239.2	229.1	219.0	212.3	209.1	205.7	202.5	199.2
70°	202.2	192.6	182.9	176.6	173.5	170.5	167.4	164.4
72.5°	169.0	161.1	153.1	148.5	147.3	146.0	144.7	143.5
75°	126.4	123.7	120.9	119.3	118.7	118.2	117.6	117.1
77.5°	95.4	93.9	92.4	91.3	90.8	90.2	89.7	89.1
80°	76.8	76.0	75.1	74.5	73.9	73.4	72.8	72.2
82.5°	58.9	58.1	57.2	56.7	56.6	56.5	56.4	56.3
85°	33.7	33.2	32.6	32.4	32.4	32.4	32.4	32.4
87.5°	16.6	16.6	16.5	16.3	16.2	16.0	15.8	15.8
90°	20.5	21.2	21.9	22.4	22.8	23.1	23.5	23.8
92.5°	22.7	23.8	24.9	25.6	25.7	26.0	26.2	26.4
95°	27.2	28.4	29.6	30.3	30.3	30.3	30.3	30.3
97.5°	28.4	29.9	31.3	32.1	32.2	32.4	32.6	32.8
100°	29.1	30.5	31.9	32.7	32.9	33.0	33.3	33.4
102.5°	43.6	39.2	34.8	32.8	33.1	33.4	33.7	34.1
105°	111.7	80.3	49.0	33.6	34.0	34.3	34.6	35.0
107.5°	273.5	250.6	227.6	204.3	180.7	157.2	133.6	110.0
110°	347.2	341.4	335.5	320.0	294.7	269.3	244.1	218.8



TEST NUMBER: P332480-927

CATALOG NUMBER: S123RDIW-S1165D1030U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	399.2	399.3	399.3	396.7	391.4	386.1	380.7	375.4
115°	460.3	462.0	463.8	465.0	465.7	466.4	467.1	467.9
117.5°	515.6	517.0	518.4	519.2	519.3	519.4	519.6	519.8
120°	551.8	553.3	554.7	555.4	555.4	555.4	555.4	555.4
122.5°	587.2	588.3	589.2	589.9	589.9	590.1	590.3	590.4
125°	637.2	637.6	637.9	638.3	638.7	639.0	639.4	639.7
127.5°	687.3	687.9	688.5	688.6	688.2	687.9	687.5	687.1
130°	717.6	718.2	718.9	719.1	718.7	718.4	718.0	717.7
132.5°	746.2	746.9	747.6	747.7	747.2	746.7	746.2	745.7
135°	789.6	790.1	790.6	790.6	790.1	789.6	789.0	788.5
137.5°	828.2	829.1	830.0	830.2	829.8	829.5	829.1	828.8
140°	852.8	853.5	854.2	854.4	854.1	853.7	853.3	852.9
142.5°	876.1	876.6	877.2	877.2	876.7	876.2	875.8	875.2
145°	908.6	908.9	909.3	909.4	909.4	909.4	909.4	909.4
147.5°	937.7	938.0	938.4	938.2	937.4	936.5	935.7	934.9
150°	955.5	955.8	956.2	956.2	955.6	955.1	954.6	954.0
152.5°	971.4	972.0	972.6	972.6	971.7	970.9	970.1	969.3
155°	993.2	994.0	995.0	994.8	993.8	992.8	991.7	990.6
157.5°	1012.2	1013.2	1014.2	1014.1	1012.7	1011.4	1010.0	1008.6
160°	1022.9	1024.1	1025.1	1025.0	1023.7	1022.5	1021.3	1020.0
162.5°	1032.8	1034.0	1035.2	1035.2	1034.2	1033.1	1032.0	1030.9
165°	1045.9	1047.3	1048.8	1048.8	1047.7	1046.4	1045.1	1043.9
167.5°	1056.1	1057.6	1059.0	1059.0	1057.6	1056.1	1054.7	1053.3
170°	1061.8	1063.3	1064.7	1064.7	1063.3	1061.8	1060.4	1059.1
172.5°	1065.7	1067.1	1068.5	1068.4	1066.9	1065.3	1063.7	1062.2
175°	1070.2	1071.5	1072.8	1072.7	1071.3	1069.8	1068.4	1067.0
177.5°	1072.0	1073.1	1074.2	1074.1	1072.7	1071.3	1069.8	1068.4
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0

(END OF REPORT)