

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332477

Luminaire Tested: **S123RDIW-S1165D755U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332477
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D755U835-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6999.2 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332477

CATALOG NUMBER: S123RDIW-S1165D755U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332477

CATALOG NUMBER: S123RDIW-S1165D755U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58	54
2	92	85	79	74	86	80	75	70	71	66	63	62	59	56	54	51	49	45
3	84	75	68	62	79	71	64	59	63	58	53	55	51	48	48	45	43	39
4	78	67	59	53	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	60	52	46	67	56	49	44	50	44	40	44	40	36	39	35	32	30
6	66	54	46	40	62	51	44	38	45	39	35	40	36	32	36	32	29	26
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26	23
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21	19
10	50	37	30	25	47	36	29	24	32	27	23	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20863	20863	20863
5°	20942	20653	20772
10°	20824	20394	20325
15°	20600	19917	19706
20°	20292	19321	18871
25°	19975	18650	18053
30°	19557	17877	16900
35°	19127	17102	15843
40°	18730	16190	14533
45°	18209	15289	13352
50°	17637	14267	12030
55°	17051	13097	10796
60°	16514	11845	9442
65°	15814	10488	8087
70°	14940	8806	6530
75°	13662	6929	6147
80°	12180	6137	5653
85°	10288	5434	5051



TEST NUMBER: P332477

CATALOG NUMBER: S123RDIW-S1165D755U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.0	2.6
10°-20°	506.4	7.2
20°-30°	729.2	10.4
30°-40°	821.3	11.7
40°-50°	785.8	11.2
50°-60°	643.5	9.2
60°-70°	434.1	6.2
70°-80°	218.4	3.1
80°-90°	60.6	0.9
90°-100°	61.6	0.9
100°-110°	184.2	2.6
110°-120°	313.4	4.5
120°-130°	412.2	5.9
130°-140°	463.3	6.6
140°-150°	455.4	6.5
150°-160°	383.4	5.5
160°-170°	255.2	3.6
170°-180°	89.4	1.3
0°-30°	1417.6	20.3
0°-40°	2238.9	32.0
0°-60°	3668.1	52.4
0°-90°	4381.3	62.6
90°-120°	559.2	8.0
90°-150°	1890.0	27.0
90°-180°	2618.0	37.4
0°-180°	6999.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1938	1938	1938	1938	1938	
5°	1938	1930	1911	1925	1922	184
15°	1849	1830	1787	1779	1768	521
25°	1682	1641	1570	1538	1520	773
35°	1456	1397	1302	1236	1206	911
45°	1196	1123	1004	918	877	923
55°	909	828	698	610	575	814
65°	621	532	412	338	318	614
75°	328	252	167	152	148	350
85°	83	50	44	41	41	94
90°	1	8	18	21	22	7
95°	44	49	55	58	58	49
105°	167	169	175	175	177	179
115°	316	317	316	317	316	312
125°	462	464	462	459	456	412
135°	599	603	603	600	598	461
145°	727	728	730	730	727	454
155°	832	832	833	835	831	383
165°	906	904	904	908	903	255
175°	943	940	940	944	939	89
180°	945	945	945	945	945	



TEST NUMBER: P332477

CATALOG NUMBER: S123RDIW-S1165D755U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1944.5	1943.3	1942.2	1941.1	1940.0	1937.7	1934.4	1931.0	1927.7	1924.3	1927.4
5°	1938.2	1936.4	1934.7	1932.9	1931.2	1928.2	1924.0	1919.8	1915.6	1911.4	1914.6
7.5°	1920.2	1918.4	1916.5	1914.6	1912.7	1909.0	1903.6	1898.1	1892.7	1887.2	1889.0
10°	1905.2	1902.7	1900.3	1897.8	1895.4	1891.0	1884.7	1878.4	1872.1	1865.9	1866.2
12.5°	1883.8	1881.1	1878.3	1875.6	1872.9	1867.7	1860.0	1852.3	1844.6	1836.9	1836.7
15°	1848.6	1844.7	1840.9	1837.0	1833.2	1826.4	1816.6	1806.8	1797.0	1787.3	1785.5
17.5°	1804.2	1799.8	1795.3	1790.8	1786.4	1777.9	1765.5	1753.0	1740.6	1728.2	1724.5
20°	1771.5	1766.0	1760.4	1754.8	1749.2	1739.8	1726.5	1713.2	1699.9	1686.7	1682.1
22.5°	1735.1	1728.6	1722.2	1715.8	1709.4	1699.1	1685.0	1670.9	1656.8	1642.6	1637.0
25°	1681.9	1673.2	1664.5	1655.7	1647.0	1634.6	1618.5	1602.5	1586.4	1570.3	1563.0
27.5°	1617.5	1607.9	1598.2	1588.6	1578.9	1565.2	1547.3	1529.4	1511.5	1493.6	1483.4
30°	1573.5	1563.0	1552.5	1542.0	1531.6	1516.5	1497.0	1477.4	1457.9	1438.3	1426.4
32.5°	1529.5	1517.6	1505.7	1493.8	1482.0	1465.7	1445.0	1424.3	1403.6	1383.0	1370.0
35°	1455.6	1443.0	1430.4	1417.9	1405.3	1388.2	1366.5	1344.9	1323.2	1301.5	1286.5
37.5°	1380.8	1366.8	1352.8	1338.8	1324.9	1306.3	1283.2	1260.1	1237.0	1213.8	1196.8
40°	1333.0	1317.6	1302.2	1286.9	1271.5	1251.4	1226.6	1201.8	1177.0	1152.2	1134.0
42.5°	1278.9	1263.5	1248.2	1232.8	1217.4	1196.9	1171.3	1145.6	1120.0	1094.4	1074.5
45°	1196.2	1180.5	1164.8	1149.1	1133.3	1112.0	1085.1	1058.2	1031.3	1004.4	984.5
47.5°	1113.5	1096.3	1079.0	1061.8	1044.5	1022.4	995.5	968.6	941.7	914.9	893.2
50°	1053.2	1036.8	1020.3	1003.9	987.5	965.2	936.9	908.6	880.3	852.0	830.3
52.5°	999.1	981.3	963.5	945.7	927.8	904.9	876.9	848.9	820.9	792.9	770.4
55°	908.6	891.4	874.3	857.2	840.1	816.7	787.0	757.3	727.6	697.9	677.7
57.5°	824.9	806.3	787.6	769.0	750.3	726.1	696.3	666.4	636.6	606.8	587.6
60°	767.1	747.9	728.7	709.5	690.2	666.1	637.1	608.2	579.2	550.2	531.3
62.5°	709.2	690.0	670.8	651.6	632.4	608.3	579.3	550.3	521.3	492.3	474.6
65°	620.9	601.7	582.5	563.3	544.1	520.8	493.6	466.3	439.1	411.8	394.7
67.5°	532.6	513.1	493.7	474.3	454.9	432.1	406.0	379.8	353.7	327.6	314.8
70°	474.7	455.9	437.0	418.1	399.3	377.6	353.2	328.7	304.3	279.8	267.6
72.5°	416.9	398.3	379.7	361.1	342.5	322.1	299.9	277.7	255.5	233.3	223.3
75°	328.5	311.8	295.0	278.2	261.5	243.5	224.3	205.0	185.8	166.6	163.1
77.5°	248.0	232.9	217.7	202.6	187.4	173.6	161.3	148.9	136.5	124.2	122.3
80°	196.5	182.2	167.8	153.5	139.2	128.4	121.0	113.7	106.4	99.0	98.0
82.5°	147.4	135.1	122.7	110.3	98.0	90.1	86.7	83.2	79.8	76.4	75.3
85°	83.3	75.6	67.9	60.3	52.6	48.2	47.2	46.1	45.1	44.0	43.3
87.5°	30.3	27.6	24.8	22.1	19.4	18.2	18.6	19.1	19.5	19.9	19.8
90°	0.7	2.4	4.0	5.7	7.3	9.2	11.4	13.5	15.7	17.8	18.5
92.5°	18.0	19.1	20.2	21.3	22.4	23.6	24.8	26.1	27.3	28.5	29.0
95°	43.8	44.9	46.1	47.3	48.4	49.6	51.0	52.3	53.6	54.9	55.6
97.5°	77.8	78.6	79.5	80.4	81.2	82.1	83.1	84.0	85.0	86.0	86.7
100°	100.9	101.9	102.9	103.9	104.9	105.8	106.6	107.5	108.3	109.1	109.6
102.5°	127.7	128.3	128.9	129.4	130.0	130.9	132.0	133.1	134.1	135.2	135.7
105°	167.0	167.3	167.7	168.0	168.3	169.2	170.7	172.2	173.7	175.2	175.2
107.5°	212.7	212.9	213.1	213.3	213.5	213.9	214.5	215.1	215.7	216.3	216.8
110°	241.2	241.6	241.9	242.2	242.5	242.9	243.2	243.5	243.9	244.2	244.9



TEST NUMBER: P332477

CATALOG NUMBER: S123RDIW-S1165D755U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	270.9	271.1	271.3	271.5	271.7	271.8	271.9	272.0	272.0	272.1	272.9
115°	315.5	315.9	316.4	316.9	317.4	317.5	317.2	316.9	316.5	316.2	316.4
117.5°	360.3	360.6	360.9	361.3	361.6	361.6	361.1	360.7	360.3	359.8	359.8
120°	388.2	389.2	390.2	391.2	392.2	392.2	391.4	390.6	389.8	388.9	388.8
122.5°	417.3	418.0	418.7	419.5	420.2	420.3	419.9	419.5	419.1	418.6	418.2
125°	461.7	462.2	462.7	463.2	463.7	463.7	463.4	463.1	462.7	462.4	461.8
127.5°	502.6	503.7	504.8	505.8	506.9	507.2	506.9	506.5	506.1	505.8	504.8
130°	530.0	531.3	532.6	533.9	535.2	535.7	535.2	534.7	534.2	533.7	533.0
132.5°	557.3	558.6	559.9	561.2	562.6	563.0	562.7	562.3	561.9	561.6	560.8
135°	599.0	600.0	601.0	602.0	602.9	603.4	603.2	603.0	602.9	602.7	602.0
137.5°	637.6	638.4	639.2	640.1	640.9	641.5	641.9	642.4	642.8	643.2	642.5
140°	664.3	665.1	666.0	666.8	667.6	668.1	668.3	668.4	668.6	668.8	668.6
142.5°	688.7	689.5	690.3	691.1	691.9	692.5	692.8	693.1	693.4	693.7	693.5
145°	726.7	727.0	727.3	727.6	728.0	728.4	728.9	729.4	729.9	730.4	730.2
147.5°	759.9	760.5	761.1	761.7	762.3	762.8	763.3	763.7	764.2	764.7	764.7
150°	783.1	783.4	783.7	784.1	784.4	784.7	785.0	785.4	785.7	786.0	786.0
152.5°	802.1	802.5	803.0	803.5	803.9	804.2	804.4	804.6	804.8	805.0	805.3
155°	832.1	832.1	832.1	832.1	832.1	832.1	832.3	832.5	832.6	832.8	833.5
157.5°	857.6	857.4	857.2	857.0	856.8	856.8	856.9	857.0	857.2	857.3	858.0
160°	873.6	873.3	873.0	872.6	872.3	872.1	872.1	872.1	872.1	872.1	873.0
162.5°	887.9	887.4	886.9	886.5	886.0	885.9	886.0	886.1	886.3	886.4	887.2
165°	906.3	905.8	905.3	904.8	904.3	904.0	904.0	904.0	904.0	904.0	905.0
167.5°	921.0	920.3	919.7	919.0	918.3	918.1	918.2	918.3	918.5	918.6	919.6
170°	929.3	928.6	928.0	927.3	926.6	926.3	926.3	926.3	926.3	926.3	927.5
172.5°	935.8	935.2	934.5	933.8	933.2	932.8	932.8	932.8	932.8	932.8	933.9
175°	942.6	942.0	941.3	940.7	940.0	939.7	939.7	939.7	939.7	939.7	940.7
177.5°	945.5	944.9	944.4	943.9	943.4	943.1	943.1	943.1	943.1	943.1	943.9
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9



TEST NUMBER: P332477

CATALOG NUMBER: S123RDIW-S1165D755U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2	1938.2
2.5°	1930.5	1933.6	1936.6	1937.9	1937.3	1936.8	1936.2	1935.6
5°	1917.7	1920.9	1924.0	1925.2	1924.5	1923.8	1923.1	1922.4
7.5°	1890.7	1892.5	1894.2	1894.5	1893.3	1892.1	1890.9	1889.7
10°	1866.6	1866.9	1867.3	1866.6	1864.8	1863.1	1861.3	1859.6
12.5°	1836.5	1836.3	1836.1	1835.0	1833.0	1830.9	1828.9	1826.9
15°	1783.8	1782.0	1780.3	1778.2	1775.7	1773.3	1770.8	1768.4
17.5°	1720.8	1717.0	1713.3	1709.7	1706.0	1702.4	1698.8	1695.1
20°	1677.6	1673.0	1668.5	1664.1	1659.9	1655.7	1651.6	1647.4
22.5°	1631.3	1625.7	1620.0	1615.2	1611.3	1607.4	1603.5	1599.6
25°	1555.7	1548.3	1541.0	1535.4	1531.6	1527.7	1523.9	1520.0
27.5°	1473.2	1463.0	1452.8	1444.8	1438.9	1433.1	1427.2	1421.3
30°	1414.5	1402.7	1390.8	1382.1	1376.5	1370.9	1365.3	1359.7
32.5°	1357.0	1344.0	1331.0	1321.6	1315.7	1309.8	1304.0	1298.1
35°	1271.5	1256.5	1241.5	1230.8	1224.5	1218.2	1211.9	1205.7
37.5°	1179.7	1162.7	1145.6	1133.2	1125.5	1117.7	1110.0	1102.2
40°	1115.9	1097.7	1079.6	1066.5	1058.4	1050.4	1042.4	1034.3
42.5°	1054.7	1034.8	1015.0	1001.5	994.3	987.1	979.9	972.7
45°	964.6	944.7	924.8	910.7	902.3	893.9	885.5	877.1
47.5°	871.5	849.9	828.2	813.7	806.2	798.7	791.2	783.8
50°	808.7	787.0	765.3	750.5	742.5	734.4	726.4	718.4
52.5°	747.9	725.4	702.9	688.0	680.8	673.7	666.5	659.3
55°	657.4	637.1	616.9	603.3	596.3	589.3	582.3	575.3
57.5°	568.5	549.3	530.2	517.6	511.7	505.8	499.8	493.9
60°	512.4	493.6	474.7	462.3	456.4	450.4	444.5	438.6
62.5°	456.8	439.1	421.3	409.4	403.1	396.9	390.7	384.5
65°	377.6	360.5	343.4	332.9	329.1	325.2	321.4	317.5
67.5°	302.0	289.2	276.4	268.0	263.9	259.7	255.6	251.5
70°	255.3	243.1	230.9	222.9	219.0	215.2	211.3	207.5
72.5°	213.3	203.3	193.3	187.5	185.9	184.3	182.7	181.1
75°	159.6	156.1	152.6	150.6	149.9	149.2	148.5	147.8
77.5°	120.4	118.5	116.6	115.3	114.6	113.9	113.2	112.5
80°	96.9	95.9	94.8	94.0	93.3	92.6	91.9	91.2
82.5°	74.3	73.3	72.2	71.6	71.5	71.3	71.2	71.1
85°	42.6	41.9	41.2	40.9	40.9	40.9	40.9	40.9
87.5°	19.6	19.5	19.3	19.1	18.9	18.7	18.5	18.3
90°	19.1	19.8	20.5	20.9	21.3	21.6	21.9	22.3
92.5°	29.6	30.1	30.6	30.8	30.6	30.4	30.2	30.0
95°	56.2	56.9	57.6	57.9	57.9	57.9	57.9	57.9
97.5°	87.5	88.2	89.0	89.3	89.3	89.2	89.1	89.1
100°	110.1	110.6	111.1	111.5	111.8	112.2	112.5	112.8
102.5°	136.2	136.7	137.2	137.4	137.4	137.3	137.2	137.2
105°	175.2	175.2	175.2	175.3	175.7	176.0	176.3	176.7
107.5°	217.3	217.9	218.4	218.6	218.4	218.2	218.0	217.8
110°	245.5	246.2	246.8	247.0	246.7	246.3	246.0	245.7



TEST NUMBER: P332477

CATALOG NUMBER: S123RDIW-S1165D755U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	273.7	274.5	275.3	275.6	275.6	275.5	275.4	275.4
115°	316.5	316.7	316.9	316.9	316.7	316.5	316.4	316.2
117.5°	359.8	359.7	359.7	359.5	359.0	358.5	358.1	357.6
120°	388.6	388.4	388.3	388.0	387.7	387.4	387.0	386.7
122.5°	417.8	417.3	416.9	416.5	416.0	415.5	415.1	414.6
125°	461.1	460.4	459.8	459.1	458.5	457.8	457.1	456.5
127.5°	503.9	503.0	502.1	501.2	500.5	499.7	499.0	498.2
130°	532.4	531.7	531.0	530.1	529.0	527.8	526.7	525.5
132.5°	560.0	559.2	558.4	557.6	556.7	555.8	554.9	554.0
135°	601.4	600.7	600.1	599.6	599.2	598.9	598.6	598.2
137.5°	641.8	641.1	640.5	639.8	639.2	638.5	637.9	637.3
140°	668.4	668.3	668.1	667.4	666.3	665.1	664.0	662.8
142.5°	693.4	693.2	693.0	692.5	691.6	690.7	689.8	688.9
145°	730.0	729.9	729.7	729.3	728.6	728.0	727.3	726.7
147.5°	764.7	764.7	764.7	764.2	763.2	762.2	761.2	760.2
150°	786.0	786.0	786.0	785.5	784.5	783.6	782.6	781.6
152.5°	805.6	805.8	806.1	805.8	804.9	804.1	803.2	802.4
155°	834.1	834.8	835.4	835.2	834.0	832.9	831.7	830.6
157.5°	858.7	859.4	860.1	859.9	859.0	858.1	857.2	856.2
160°	873.8	874.6	875.4	875.5	874.9	874.2	873.5	872.9
162.5°	888.0	888.9	889.7	889.6	888.5	887.5	886.4	885.3
165°	906.0	907.0	908.0	907.9	906.8	905.6	904.5	903.3
167.5°	920.6	921.7	922.7	922.7	921.7	920.6	919.6	918.6
170°	928.6	929.8	930.9	930.9	929.8	928.6	927.5	926.3
172.5°	934.9	935.9	936.9	936.9	935.7	934.6	933.4	932.3
175°	941.7	942.6	943.6	943.6	942.4	941.2	940.1	938.9
177.5°	944.7	945.5	946.3	946.2	945.3	944.3	943.4	942.5
180°	944.9	944.9	944.9	944.9	944.9	944.9	944.9	944.9

(END OF REPORT)