

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332472-927

Luminaire Tested: **S123RDIW-S1165D460U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332472-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S1165D460U927-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1165 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4930.8 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332472-927

CATALOG NUMBER: S123RDIW-S1165D460U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332472-927

CATALOG NUMBER: S123RDIW-S1165D460U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	51
3	86	77	69	63	81	73	66	61	66	60	56	59	55	52	53	50	47	44
4	79	68	60	54	75	65	58	52	59	53	48	53	48	45	48	44	41	38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36	33
6	67	55	47	41	64	53	45	40	48	42	37	43	38	34	39	35	32	29
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	46	38	32	55	44	36	31	40	34	29	36	31	28	33	29	26	24
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	26	23	21
10	51	39	31	26	48	37	30	26	34	28	24	31	26	23	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16527	16527	16527
5°	16590	16361	16455
10°	16497	16156	16101
15°	16319	15778	15611
20°	16076	15306	14948
25°	15824	14775	14301
30°	15493	14162	13387
35°	15152	13548	12550
40°	14838	12826	11514
45°	14425	12113	10577
50°	13971	11302	9530
55°	13508	10376	8552
60°	13082	9384	7481
65°	12528	8308	6406
70°	11833	6977	5174
75°	10821	5490	4870
80°	9651	4860	4475
85°	8151	4310	4001



TEST NUMBER: P332472-927

CATALOG NUMBER: S123RDIW-S1165D460U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	2.9
10°-20°	401.2	8.1
20°-30°	577.6	11.7
30°-40°	650.7	13.2
40°-50°	622.5	12.6
50°-60°	509.7	10.3
60°-70°	343.9	7.0
70°-80°	173.0	3.5
80°-90°	47.1	1.0
90°-100°	17.4	0.4
100°-110°	83.0	1.7
110°-120°	199.4	4.0
120°-130°	253.9	5.1
130°-140°	271.3	5.5
140°-150°	253.7	5.1
150°-160°	204.6	4.2
160°-170°	132.1	2.7
170°-180°	45.5	0.9
0°-30°	1123.0	22.8
0°-40°	1773.6	36.0
0°-60°	2905.8	58.9
0°-90°	3469.9	70.4
90°-120°	299.8	6.1
90°-150°	1078.7	21.9
90°-180°	1461.0	29.6
0°-180°	4930.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1535	1535	1535	1535	1535	
5°	1535	1529	1514	1525	1523	146
15°	1464	1450	1416	1410	1401	412
25°	1332	1300	1244	1219	1204	613
35°	1153	1106	1031	979	955	721
45°	948	889	796	727	695	731
55°	720	656	553	483	456	645
65°	492	422	326	268	252	487
75°	260	200	132	120	117	278
85°	66	40	35	32	32	74
90°	0	4	9	10	11	4
95°	22	8	11	13	14	27
105°	106	108	78	18	16	112
115°	199	201	204	208	209	196
125°	280	283	285	285	286	250
135°	349	351	353	354	353	269
145°	403	405	406	407	407	252
155°	444	443	444	445	443	204
165°	468	467	467	469	467	132
175°	479	477	478	480	477	46
180°	479	479	479	479	479	



TEST NUMBER: P332472-927

CATALOG NUMBER: S123RDIW-S1165D460U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1540.4	1539.4	1538.6	1537.7	1536.8	1535.0	1532.4	1529.7	1527.1	1524.4	1526.9
5°	1535.4	1534.0	1532.6	1531.2	1529.9	1527.5	1524.2	1520.8	1517.5	1514.2	1516.7
7.5°	1521.1	1519.7	1518.2	1516.7	1515.2	1512.3	1508.0	1503.6	1499.4	1495.0	1496.4
10°	1509.3	1507.3	1505.4	1503.4	1501.5	1498.0	1493.0	1488.0	1483.0	1478.1	1478.4
12.5°	1492.3	1490.2	1488.0	1485.8	1483.7	1479.6	1473.5	1467.4	1461.3	1455.2	1455.0
15°	1464.4	1461.3	1458.3	1455.2	1452.2	1446.8	1439.1	1431.3	1423.6	1415.9	1414.4
17.5°	1429.3	1425.8	1422.2	1418.6	1415.2	1408.4	1398.6	1388.7	1378.9	1369.0	1366.1
20°	1403.4	1399.0	1394.6	1390.1	1385.7	1378.2	1367.7	1357.2	1346.6	1336.2	1332.5
22.5°	1374.5	1369.4	1364.3	1359.2	1354.2	1346.0	1334.8	1323.7	1312.5	1301.2	1296.8
25°	1332.4	1325.5	1318.6	1311.6	1304.7	1294.9	1282.1	1269.5	1256.7	1244.0	1238.2
27.5°	1281.4	1273.7	1266.1	1258.5	1250.8	1239.9	1225.7	1211.6	1197.4	1183.2	1175.1
30°	1246.5	1238.2	1229.9	1221.5	1213.3	1201.3	1185.9	1170.4	1154.9	1139.4	1130.0
32.5°	1211.6	1202.2	1192.8	1183.4	1174.0	1161.1	1144.7	1128.3	1111.9	1095.6	1085.3
35°	1153.1	1143.1	1133.1	1123.2	1113.3	1099.7	1082.5	1065.4	1048.2	1031.0	1019.1
37.5°	1093.8	1082.8	1071.7	1060.6	1049.6	1034.8	1016.5	998.2	979.9	961.6	948.1
40°	1056.0	1043.8	1031.6	1019.5	1007.3	991.3	971.7	952.0	932.4	912.8	898.3
42.5°	1013.1	1000.9	988.8	976.6	964.4	948.2	927.9	907.5	887.2	867.0	851.2
45°	947.6	935.2	922.7	910.3	897.8	880.9	859.6	838.3	817.0	795.7	779.9
47.5°	882.1	868.5	854.8	841.1	827.4	809.9	788.6	767.3	746.0	724.8	707.6
50°	834.3	821.3	808.3	795.3	782.3	764.6	742.2	719.8	697.4	674.9	657.7
52.5°	791.5	777.4	763.3	749.2	735.0	716.8	694.7	672.5	650.3	628.1	610.3
55°	719.8	706.2	692.6	679.1	665.5	647.0	623.4	599.9	576.4	552.9	536.9
57.5°	653.5	638.7	623.9	609.2	594.4	575.2	551.6	527.9	504.3	480.7	465.5
60°	607.7	592.5	577.3	562.1	546.8	527.7	504.7	481.8	458.8	435.9	420.9
62.5°	561.8	546.6	531.4	516.2	501.0	481.9	458.9	435.9	413.0	390.0	376.0
65°	491.9	476.7	461.4	446.2	431.0	412.6	391.0	369.4	347.8	326.2	312.7
67.5°	421.9	406.5	391.1	375.7	360.4	342.3	321.6	300.9	280.2	259.5	249.4
70°	376.0	361.2	346.2	331.2	316.3	299.1	279.8	260.4	241.1	221.7	212.0
72.5°	330.3	315.5	300.8	286.1	271.3	255.2	237.6	220.0	202.4	184.8	176.9
75°	260.2	247.0	233.7	220.4	207.2	192.9	177.7	162.4	147.2	132.0	129.2
77.5°	196.5	184.5	172.5	160.5	148.5	137.5	127.8	118.0	108.1	98.4	96.9
80°	155.7	144.3	132.9	121.6	110.3	101.7	95.9	90.1	84.3	78.4	77.6
82.5°	116.8	107.0	97.2	87.4	77.6	71.4	68.7	65.9	63.2	60.5	59.7
85°	66.0	59.9	53.8	47.8	41.7	38.2	37.4	36.5	35.7	34.9	34.3
87.5°	24.0	21.7	19.4	17.1	14.9	13.9	14.0	14.3	14.4	14.7	14.5
90°	0.3	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.5	8.6	8.9
92.5°	6.7	6.4	6.2	5.9	5.7	6.0	6.8	7.5	8.3	9.1	9.6
95°	21.7	18.5	15.2	12.0	8.7	7.5	8.4	9.3	10.1	11.0	11.6
97.5°	43.6	42.1	40.7	39.3	37.8	34.2	28.5	22.8	17.2	11.5	12.1
100°	60.1	61.7	63.3	64.9	66.5	61.1	48.8	36.4	24.1	11.7	12.4
102.5°	78.9	80.1	81.2	82.4	83.5	77.3	63.8	50.4	36.9	23.4	21.5
105°	106.1	106.9	107.8	108.7	109.6	106.4	99.3	92.2	85.1	78.0	63.9
107.5°	134.7	135.4	136.1	136.7	137.4	138.4	139.5	140.6	141.7	142.8	132.6
110°	153.8	154.4	155.0	155.7	156.3	157.0	157.9	158.8	159.6	160.5	157.9



TEST NUMBER: P332472-927

CATALOG NUMBER: S123RDIW-S1165D460U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.0	172.5	173.1	173.6	174.3	175.0	175.9	176.7	177.6	178.5	178.5
115°	198.9	199.4	199.9	200.3	200.8	201.5	202.2	202.9	203.6	204.3	205.1
117.5°	225.1	225.7	226.2	226.8	227.4	227.9	228.2	228.6	229.0	229.3	230.0
120°	241.3	242.0	242.7	243.4	244.2	244.6	244.9	245.1	245.3	245.6	246.2
122.5°	257.9	258.4	259.0	259.6	260.2	260.6	260.9	261.2	261.5	261.8	262.2
125°	280.4	281.1	281.7	282.3	283.0	283.4	283.8	284.1	284.4	284.7	284.9
127.5°	302.4	303.0	303.6	304.3	304.9	305.4	305.8	306.2	306.6	307.0	307.2
130°	316.1	316.7	317.3	318.0	318.6	319.1	319.4	319.7	320.0	320.3	320.6
132.5°	329.2	329.8	330.4	331.1	331.7	332.1	332.4	332.6	332.9	333.1	333.4
135°	349.1	349.6	350.1	350.5	351.0	351.4	351.7	352.0	352.4	352.7	352.9
137.5°	366.2	366.9	367.4	368.0	368.6	369.0	369.2	369.4	369.6	369.7	370.1
140°	377.6	378.1	378.6	379.1	379.5	379.9	380.1	380.3	380.6	380.8	381.1
142.5°	388.2	388.6	389.1	389.6	390.1	390.4	390.6	390.9	391.1	391.3	391.6
145°	402.9	403.5	404.0	404.6	405.1	405.4	405.6	405.8	405.9	406.1	406.2
147.5°	416.8	417.2	417.5	417.9	418.2	418.5	418.7	418.8	419.0	419.1	419.3
150°	425.3	425.6	425.8	426.0	426.3	426.4	426.6	426.7	426.9	427.1	427.2
152.5°	433.0	433.1	433.2	433.3	433.5	433.6	433.6	433.7	433.8	434.0	434.2
155°	443.8	443.6	443.5	443.4	443.2	443.1	443.2	443.3	443.4	443.5	443.9
157.5°	452.3	452.2	452.2	452.2	452.2	452.1	452.0	451.9	451.9	451.8	452.3
160°	457.3	457.2	457.2	457.1	457.0	456.9	456.9	456.8	456.7	456.6	457.1
162.5°	462.2	462.0	461.8	461.6	461.4	461.2	461.1	461.1	461.0	460.9	461.4
165°	468.0	467.8	467.5	467.3	467.1	466.9	466.8	466.8	466.7	466.6	467.2
167.5°	472.6	472.3	472.0	471.7	471.3	471.2	471.2	471.2	471.2	471.2	471.8
170°	475.2	474.8	474.5	474.2	473.9	473.7	473.7	473.7	473.7	473.7	474.4
172.5°	476.8	476.5	476.1	475.7	475.3	475.2	475.2	475.3	475.4	475.4	476.0
175°	479.0	478.6	478.2	477.8	477.4	477.3	477.4	477.4	477.5	477.6	478.2
177.5°	479.6	479.3	479.0	478.6	478.3	478.2	478.3	478.3	478.4	478.5	479.0
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332472-927

CATALOG NUMBER: S123RDIW-S1165D460U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4	1535.4
2.5°	1529.3	1531.8	1534.1	1535.2	1534.7	1534.3	1533.8	1533.3
5°	1519.2	1521.7	1524.2	1525.1	1524.6	1524.0	1523.4	1522.9
7.5°	1497.8	1499.2	1500.6	1500.8	1499.8	1498.9	1497.9	1497.0
10°	1478.7	1478.9	1479.2	1478.7	1477.3	1475.9	1474.5	1473.1
12.5°	1454.8	1454.7	1454.5	1453.7	1452.1	1450.4	1448.8	1447.2
15°	1413.1	1411.7	1410.3	1408.7	1406.7	1404.8	1402.8	1400.9
17.5°	1363.2	1360.2	1357.2	1354.4	1351.5	1348.6	1345.8	1342.8
20°	1329.0	1325.3	1321.8	1318.3	1314.9	1311.6	1308.4	1305.0
22.5°	1292.3	1287.9	1283.3	1279.5	1276.4	1273.4	1270.3	1267.2
25°	1232.4	1226.5	1220.8	1216.3	1213.3	1210.2	1207.2	1204.1
27.5°	1167.0	1159.0	1150.9	1144.5	1139.9	1135.3	1130.6	1125.9
30°	1120.5	1111.2	1101.8	1094.9	1090.4	1086.0	1081.6	1077.1
32.5°	1075.0	1064.7	1054.4	1046.9	1042.3	1037.6	1033.0	1028.3
35°	1007.3	995.4	983.5	975.0	970.0	965.0	960.0	955.1
37.5°	934.5	921.1	907.5	897.7	891.6	885.4	879.3	873.1
40°	884.0	869.6	855.2	844.9	838.4	832.1	825.8	819.4
42.5°	835.5	819.8	804.1	793.4	787.7	782.0	776.3	770.6
45°	764.1	748.4	732.6	721.4	714.8	708.1	701.5	694.8
47.5°	690.4	673.3	656.1	644.6	638.7	632.7	626.8	620.9
50°	640.6	623.4	606.3	594.5	588.2	581.8	575.4	569.1
52.5°	592.5	574.6	556.8	545.0	539.3	533.7	528.0	522.3
55°	520.8	504.7	488.7	477.9	472.4	466.8	461.3	455.7
57.5°	450.4	435.1	420.0	410.0	405.4	400.7	395.9	391.3
60°	405.9	391.0	376.0	366.2	361.6	356.8	352.1	347.5
62.5°	361.9	347.8	333.7	324.3	319.3	314.4	309.5	304.6
65°	299.1	285.6	272.0	263.7	260.7	257.6	254.6	251.5
67.5°	239.2	229.1	219.0	212.3	209.1	205.7	202.5	199.2
70°	202.2	192.6	182.9	176.6	173.5	170.5	167.4	164.4
72.5°	169.0	161.1	153.1	148.5	147.3	146.0	144.7	143.5
75°	126.4	123.7	120.9	119.3	118.7	118.2	117.6	117.1
77.5°	95.4	93.9	92.4	91.3	90.8	90.2	89.7	89.1
80°	76.8	76.0	75.1	74.5	73.9	73.4	72.8	72.2
82.5°	58.9	58.1	57.2	56.7	56.6	56.5	56.4	56.3
85°	33.7	33.2	32.6	32.4	32.4	32.4	32.4	32.4
87.5°	14.3	14.2	14.0	13.9	13.6	13.5	13.3	13.1
90°	9.2	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.1	10.6	11.2	11.4	11.6	11.6	11.7	11.8
95°	12.1	12.7	13.2	13.5	13.5	13.5	13.5	13.5
97.5°	12.8	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.0	13.6	14.3	14.7	14.7	14.8	14.9	15.0
102.5°	19.5	17.5	15.6	14.7	14.8	15.0	15.1	15.2
105°	49.9	36.0	21.9	15.1	15.2	15.4	15.5	15.7
107.5°	122.3	112.1	101.8	91.4	80.8	70.3	59.7	49.2
110°	155.3	152.7	150.0	143.1	131.8	120.5	109.2	97.9



TEST NUMBER: P332472-927

CATALOG NUMBER: S123RDIW-S1165D460U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	178.6	178.6	178.6	177.4	175.1	172.7	170.3	167.9
115°	205.9	206.7	207.5	208.0	208.3	208.7	209.0	209.3
117.5°	230.6	231.2	231.9	232.2	232.3	232.3	232.4	232.5
120°	246.8	247.5	248.1	248.4	248.4	248.4	248.4	248.4
122.5°	262.7	263.2	263.6	263.8	263.9	264.0	264.0	264.1
125°	285.0	285.2	285.3	285.5	285.7	285.8	286.0	286.1
127.5°	307.4	307.7	307.9	308.0	307.8	307.7	307.5	307.4
130°	320.9	321.2	321.5	321.6	321.5	321.3	321.2	321.0
132.5°	333.7	334.1	334.4	334.5	334.2	334.0	333.7	333.6
135°	353.2	353.4	353.6	353.6	353.4	353.2	352.9	352.7
137.5°	370.5	370.8	371.2	371.4	371.2	371.1	370.9	370.7
140°	381.4	381.8	382.1	382.1	382.0	381.8	381.7	381.5
142.5°	391.9	392.1	392.4	392.4	392.1	392.0	391.7	391.5
145°	406.4	406.5	406.7	406.8	406.8	406.8	406.8	406.8
147.5°	419.5	419.6	419.8	419.6	419.3	418.9	418.6	418.2
150°	427.4	427.5	427.7	427.7	427.5	427.2	427.0	426.7
152.5°	434.5	434.7	435.1	435.0	434.7	434.3	434.0	433.6
155°	444.3	444.7	445.0	445.0	444.5	444.0	443.5	443.1
157.5°	452.7	453.2	453.7	453.6	453.0	452.4	451.8	451.1
160°	457.6	458.0	458.5	458.5	458.0	457.4	456.9	456.3
162.5°	462.0	462.6	463.0	463.1	462.6	462.1	461.6	461.1
165°	467.9	468.5	469.1	469.1	468.6	468.1	467.5	467.0
167.5°	472.5	473.0	473.6	473.6	473.0	472.5	471.8	471.2
170°	475.0	475.6	476.3	476.3	475.6	475.0	474.4	473.7
172.5°	476.7	477.3	477.9	477.9	477.2	476.5	475.9	475.2
175°	478.7	479.3	479.8	479.8	479.2	478.6	477.9	477.3
177.5°	479.5	480.0	480.5	480.5	479.8	479.2	478.6	477.9
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0

(END OF REPORT)