

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332400

Luminaire Tested: **S123RDIW-S340D1030U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332400
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1030U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1030 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5424.4 lumens
Efficiency: N/A
Efficacy: 142.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332400

CATALOG NUMBER: S123RDIW-S340D1030U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332400

CATALOG NUMBER: S123RDIW-S340D1030U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27	20
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	52	47	62	54	47	42	42	37	34	31	28	25	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	34	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	54	43	35	30	48	38	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	20	20	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6184	6184	6184
5°	6207	6122	6158
10°	6172	6045	6025
15°	6107	5904	5841
20°	6015	5727	5593
25°	5922	5529	5352
30°	5797	5299	5009
35°	5670	5070	4696
40°	5552	4799	4308
45°	5398	4532	3958
50°	5228	4228	3565
55°	5054	3883	3200
60°	4895	3511	2799
65°	4689	3110	2397
70°	4428	2609	1936
75°	4051	2054	1822
80°	3608	1822	1674
85°	3051	1606	1494



TEST NUMBER: P332400

CATALOG NUMBER: S123RDIW-S340D1030U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.0
10°-20°	150.1	2.8
20°-30°	216.1	4.0
30°-40°	243.5	4.5
40°-50°	232.9	4.3
50°-60°	190.7	3.5
60°-70°	128.7	2.4
70°-80°	64.7	1.2
80°-90°	20.9	0.4
90°-100°	49.2	0.9
100°-110°	234.3	4.3
110°-120°	562.7	10.4
120°-130°	716.5	13.2
130°-140°	765.6	14.1
140°-150°	715.9	13.2
150°-160°	577.5	10.6
160°-170°	372.7	6.9
170°-180°	128.4	2.4
0°-30°	420.2	7.7
0°-40°	663.7	12.2
0°-60°	1087.3	20.0
0°-90°	1301.7	24.0
90°-120°	846.1	15.6
90°-150°	3044.1	56.1
90°-180°	4123.0	76.0
0°-180°	5424.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	574	572	567	570	570	54
15°	548	542	530	527	524	154
25°	499	486	466	456	451	229
35°	432	414	386	366	357	270
45°	355	333	298	272	260	273
55°	269	246	207	181	170	241
65°	184	158	122	100	94	182
75°	97	75	49	45	44	104
85°	25	15	13	12	12	28
90°	1	11	24	28	30	4
95°	61	23	31	38	38	76
105°	299	305	220	52	44	317
115°	562	568	576	586	591	554
125°	792	799	804	806	808	707
135°	985	991	995	998	995	758
145°	1137	1144	1146	1148	1148	711
155°	1252	1251	1252	1256	1250	577
165°	1321	1318	1317	1324	1318	373
175°	1352	1347	1348	1354	1347	129
180°	1352	1352	1352	1352	1352	



TEST NUMBER: P332400

CATALOG NUMBER: S123RDIW-S340D1030U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	576.4	576.0	575.7	575.4	575.1	574.4	573.4	572.4	571.4	570.4	571.3
5°	574.5	574.0	573.5	573.0	572.4	571.6	570.3	569.1	567.8	566.6	567.5
7.5°	569.2	568.6	568.1	567.5	567.0	565.9	564.3	562.7	561.0	559.4	559.9
10°	564.7	564.0	563.3	562.6	561.8	560.5	558.7	556.8	554.9	553.1	553.2
12.5°	558.4	557.6	556.8	556.0	555.2	553.6	551.3	549.1	546.8	544.5	544.4
15°	548.0	546.8	545.7	544.5	543.4	541.4	538.5	535.6	532.7	529.8	529.3
17.5°	534.8	533.5	532.2	530.8	529.5	527.0	523.3	519.6	516.0	512.3	511.2
20°	525.1	523.5	521.8	520.2	518.5	515.7	511.8	507.8	503.9	500.0	498.6
22.5°	514.3	512.4	510.5	508.6	506.7	503.7	499.5	495.3	491.1	486.9	485.2
25°	498.6	496.0	493.4	490.8	488.2	484.5	479.8	475.0	470.2	465.5	463.3
27.5°	479.5	476.6	473.7	470.9	468.0	464.0	458.7	453.3	448.0	442.7	439.7
30°	466.4	463.3	460.2	457.1	454.0	449.5	443.7	437.9	432.1	426.3	422.8
32.5°	453.4	449.8	446.3	442.8	439.3	434.5	428.3	422.2	416.1	409.9	406.1
35°	431.5	427.7	424.0	420.3	416.6	411.5	405.1	398.6	392.2	385.8	381.4
37.5°	409.3	405.1	401.0	396.9	392.7	387.2	380.4	373.5	366.7	359.8	354.8
40°	395.1	390.6	386.0	381.5	376.9	370.9	363.6	356.2	348.9	341.5	336.2
42.5°	379.1	374.5	370.0	365.4	360.9	354.8	347.2	339.6	332.0	324.4	318.5
45°	354.6	349.9	345.3	340.6	335.9	329.6	321.7	313.7	305.7	297.7	291.8
47.5°	330.1	325.0	319.8	314.7	309.6	303.1	295.1	287.1	279.2	271.2	264.8
50°	312.2	307.3	302.5	297.6	292.7	286.1	277.7	269.3	260.9	252.5	246.1
52.5°	296.2	290.9	285.6	280.3	275.0	268.2	259.9	251.6	243.3	235.0	228.4
55°	269.3	264.2	259.2	254.1	249.0	242.1	233.3	224.5	215.7	206.9	200.9
57.5°	244.5	239.0	233.5	227.9	222.4	215.2	206.4	197.5	188.7	179.9	174.2
60°	227.4	221.7	216.0	210.3	204.6	197.5	188.9	180.3	171.7	163.1	157.5
62.5°	210.2	204.5	198.8	193.2	187.5	180.3	171.7	163.1	154.5	145.9	140.7
65°	184.1	178.4	172.7	167.0	161.3	154.4	146.3	138.2	130.2	122.1	117.0
67.5°	157.9	152.1	146.3	140.6	134.8	128.1	120.3	112.6	104.8	97.1	93.3
70°	140.7	135.1	129.5	123.9	118.4	111.9	104.7	97.4	90.2	82.9	79.3
72.5°	123.6	118.1	112.6	107.0	101.5	95.5	88.9	82.3	75.7	69.1	66.2
75°	97.4	92.4	87.4	82.5	77.5	72.2	66.5	60.8	55.1	49.4	48.4
77.5°	73.5	69.0	64.5	60.0	55.6	51.5	47.8	44.1	40.5	36.8	36.3
80°	58.2	54.0	49.8	45.5	41.3	38.1	35.9	33.7	31.5	29.4	29.0
82.5°	43.7	40.0	36.4	32.7	29.0	26.7	25.7	24.7	23.7	22.6	22.3
85°	24.7	22.4	20.1	17.9	15.6	14.3	14.0	13.7	13.4	13.0	12.8
87.5°	9.1	8.7	8.2	7.8	7.3	7.3	7.9	8.5	9.1	9.7	9.8
90°	1.0	3.2	5.5	7.7	9.9	12.5	15.4	18.3	21.2	24.1	25.0
92.5°	18.7	18.1	17.4	16.8	16.2	17.0	19.2	21.3	23.5	25.7	27.1
95°	61.3	52.1	43.0	33.8	24.7	21.3	23.8	26.2	28.7	31.1	32.7
97.5°	123.1	119.0	114.9	110.8	106.7	96.6	80.6	64.5	48.4	32.3	34.1
100°	169.7	174.2	178.7	183.1	187.6	172.4	137.6	102.8	68.0	33.1	34.9
102.5°	222.8	226.0	229.2	232.4	235.6	218.2	180.2	142.2	104.1	66.1	60.6
105°	299.3	301.8	304.2	306.7	309.1	300.3	280.2	260.1	240.1	220.0	180.5
107.5°	380.1	382.0	384.0	386.0	387.9	390.5	393.7	396.8	400.0	403.2	374.2
110°	433.9	435.7	437.5	439.3	441.0	443.2	445.6	448.1	450.5	453.0	445.6



TEST NUMBER: P332400

CATALOG NUMBER: S123RDIW-S340D1030U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	485.3	486.9	488.5	490.2	491.8	493.8	496.2	498.7	501.2	503.6	503.7
115°	561.5	562.8	564.1	565.5	566.8	568.5	570.5	572.5	574.5	576.5	578.8
117.5°	635.2	636.8	638.5	640.1	641.8	643.1	644.2	645.2	646.2	647.2	649.0
120°	681.0	683.0	685.0	687.0	689.0	690.4	691.0	691.7	692.4	693.0	694.8
122.5°	727.6	729.2	730.9	732.5	734.2	735.4	736.3	737.1	738.0	738.8	740.1
125°	791.5	793.3	795.0	796.8	798.6	800.0	800.8	801.7	802.6	803.5	804.0
127.5°	853.3	855.1	856.9	858.7	860.5	861.9	863.0	864.1	865.1	866.2	866.9
130°	891.9	893.7	895.5	897.3	899.1	900.4	901.3	902.2	903.1	904.0	904.9
132.5°	928.9	930.7	932.4	934.2	936.0	937.3	938.0	938.7	939.4	940.1	941.0
135°	985.3	986.7	988.0	989.3	990.7	991.8	992.7	993.6	994.5	995.4	996.0
137.5°	1033.5	1035.2	1036.9	1038.6	1040.3	1041.4	1041.9	1042.4	1042.9	1043.4	1044.4
140°	1065.7	1067.0	1068.4	1069.7	1071.0	1072.0	1072.7	1073.4	1074.0	1074.7	1075.6
142.5°	1095.4	1096.7	1098.1	1099.4	1100.8	1101.8	1102.4	1103.1	1103.8	1104.4	1105.2
145°	1137.0	1138.5	1140.1	1141.7	1143.2	1144.2	1144.7	1145.1	1145.6	1146.0	1146.5
147.5°	1176.2	1177.2	1178.2	1179.2	1180.3	1181.0	1181.4	1181.9	1182.3	1182.8	1183.2
150°	1200.3	1200.9	1201.6	1202.3	1202.9	1203.5	1203.9	1204.4	1204.8	1205.3	1205.7
152.5°	1222.0	1222.3	1222.6	1222.9	1223.2	1223.5	1223.8	1224.0	1224.3	1224.6	1225.4
155°	1252.5	1252.0	1251.6	1251.2	1250.7	1250.6	1250.8	1251.0	1251.3	1251.5	1252.6
157.5°	1276.2	1276.2	1276.1	1276.1	1276.0	1275.9	1275.7	1275.4	1275.2	1275.0	1276.3
160°	1290.7	1290.4	1290.2	1290.0	1289.8	1289.5	1289.3	1289.1	1288.9	1288.7	1290.0
162.5°	1304.3	1303.7	1303.2	1302.6	1302.0	1301.6	1301.4	1301.2	1300.9	1300.7	1302.2
165°	1320.8	1320.1	1319.5	1318.8	1318.1	1317.7	1317.4	1317.2	1317.0	1316.8	1318.6
167.5°	1333.6	1332.8	1331.9	1331.0	1330.1	1329.6	1329.6	1329.6	1329.6	1329.6	1331.4
170°	1340.9	1340.0	1339.1	1338.2	1337.3	1336.9	1336.9	1336.9	1336.9	1336.9	1338.6
172.5°	1345.7	1344.6	1343.6	1342.5	1341.4	1341.0	1341.1	1341.3	1341.5	1341.7	1343.5
175°	1351.9	1350.8	1349.7	1348.6	1347.5	1347.0	1347.2	1347.5	1347.7	1347.9	1349.5
177.5°	1353.5	1352.6	1351.8	1350.9	1350.0	1349.6	1349.8	1350.0	1350.1	1350.3	1351.8
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332400

CATALOG NUMBER: S123RDIW-S340D1030U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	572.2	573.1	574.1	574.4	574.3	574.1	573.9	573.8
5°	568.5	569.4	570.3	570.7	570.5	570.3	570.1	569.9
7.5°	560.5	561.0	561.5	561.6	561.2	560.9	560.5	560.2
10°	553.3	553.4	553.5	553.3	552.8	552.3	551.7	551.2
12.5°	544.4	544.3	544.3	543.9	543.3	542.7	542.1	541.5
15°	528.7	528.2	527.7	527.1	526.4	525.6	524.9	524.2
17.5°	510.1	509.0	507.9	506.8	505.7	504.6	503.6	502.5
20°	497.3	495.9	494.6	493.3	492.0	490.8	489.6	488.3
22.5°	483.6	481.9	480.2	478.8	477.6	476.5	475.3	474.2
25°	461.1	459.0	456.8	455.1	454.0	452.9	451.7	450.6
27.5°	436.7	433.7	430.7	428.3	426.5	424.8	423.1	421.3
30°	419.3	415.8	412.3	409.7	408.0	406.4	404.7	403.0
32.5°	402.2	398.4	394.5	391.7	390.0	388.3	386.5	384.8
35°	376.9	372.4	368.0	364.8	363.0	361.1	359.2	357.4
37.5°	349.7	344.6	339.6	335.9	333.6	331.3	329.0	326.7
40°	330.8	325.4	320.0	316.1	313.7	311.4	309.0	306.6
42.5°	312.6	306.8	300.9	296.9	294.7	292.6	290.5	288.3
45°	285.9	280.0	274.1	269.9	267.5	265.0	262.5	260.0
47.5°	258.3	251.9	245.5	241.2	239.0	236.8	234.5	232.3
50°	239.7	233.3	226.9	222.5	220.1	217.7	215.3	212.9
52.5°	221.7	215.0	208.4	204.0	201.8	199.7	197.6	195.4
55°	194.9	188.9	182.9	178.8	176.8	174.7	172.6	170.5
57.5°	168.5	162.8	157.2	153.4	151.7	149.9	148.2	146.4
60°	151.9	146.3	140.7	137.0	135.3	133.5	131.8	130.0
62.5°	135.4	130.2	124.9	121.3	119.5	117.7	115.8	114.0
65°	111.9	106.9	101.8	98.7	97.5	96.4	95.3	94.1
67.5°	89.5	85.7	81.9	79.4	78.2	77.0	75.8	74.6
70°	75.7	72.1	68.4	66.1	64.9	63.8	62.6	61.5
72.5°	63.2	60.3	57.3	55.6	55.1	54.6	54.2	53.7
75°	47.3	46.3	45.2	44.6	44.4	44.2	44.0	43.8
77.5°	35.7	35.1	34.6	34.2	34.0	33.8	33.6	33.4
80°	28.7	28.4	28.1	27.9	27.6	27.4	27.2	27.0
82.5°	22.0	21.7	21.4	21.2	21.2	21.1	21.1	21.1
85°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
87.5°	9.9	10.0	10.0	10.1	10.1	10.1	10.1	10.1
90°	25.9	26.8	27.7	28.3	28.8	29.2	29.7	30.1
92.5°	28.6	30.0	31.4	32.3	32.5	32.8	33.1	33.3
95°	34.3	35.8	37.4	38.2	38.2	38.2	38.2	38.2
97.5°	35.9	37.7	39.5	40.5	40.7	40.9	41.2	41.4
100°	36.7	38.5	40.3	41.3	41.5	41.7	42.0	42.2
102.5°	55.0	49.5	43.9	41.4	41.8	42.2	42.6	43.0
105°	141.0	101.4	61.9	42.4	42.9	43.3	43.7	44.2
107.5°	345.2	316.3	287.3	257.9	228.1	198.4	168.6	138.8
110°	438.3	430.9	423.5	403.9	372.0	340.0	308.1	276.2



TEST NUMBER: P332400

CATALOG NUMBER: S123RDIW-S340D1030U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	503.9	504.0	504.1	500.8	494.1	487.4	480.6	473.9
115°	581.0	583.2	585.5	587.0	587.9	588.8	589.7	590.6
117.5°	650.8	652.6	654.4	655.4	655.5	655.7	655.9	656.1
120°	696.6	698.4	700.2	701.1	701.1	701.1	701.1	701.1
122.5°	741.3	742.6	743.8	744.6	744.7	744.9	745.1	745.3
125°	804.4	804.9	805.3	805.8	806.2	806.6	807.1	807.5
127.5°	867.6	868.3	869.1	869.2	868.7	868.3	867.9	867.4
130°	905.8	906.6	907.5	907.8	907.3	906.9	906.4	906.0
132.5°	941.9	942.8	943.7	943.8	943.2	942.6	942.0	941.3
135°	996.7	997.4	998.0	998.0	997.4	996.7	996.0	995.4
137.5°	1045.5	1046.6	1047.7	1048.0	1047.5	1047.1	1046.6	1046.2
140°	1076.5	1077.4	1078.3	1078.5	1078.1	1077.6	1077.2	1076.7
142.5°	1105.9	1106.6	1107.3	1107.3	1106.7	1106.1	1105.5	1104.8
145°	1146.9	1147.4	1147.8	1148.0	1148.0	1148.0	1148.0	1148.0
147.5°	1183.7	1184.1	1184.6	1184.3	1183.3	1182.2	1181.2	1180.2
150°	1206.2	1206.6	1207.1	1207.0	1206.3	1205.6	1205.0	1204.3
152.5°	1226.2	1227.0	1227.8	1227.7	1226.6	1225.6	1224.6	1223.6
155°	1253.7	1254.8	1256.0	1255.8	1254.5	1253.2	1251.8	1250.5
157.5°	1277.7	1279.0	1280.3	1280.1	1278.4	1276.7	1274.9	1273.2
160°	1291.3	1292.7	1294.0	1293.9	1292.3	1290.8	1289.2	1287.6
162.5°	1303.7	1305.3	1306.8	1306.8	1305.5	1304.1	1302.7	1301.3
165°	1320.3	1322.1	1323.9	1324.0	1322.5	1320.9	1319.3	1317.8
167.5°	1333.2	1335.0	1336.8	1336.8	1335.0	1333.2	1331.4	1329.6
170°	1340.4	1342.2	1344.0	1344.0	1342.2	1340.4	1338.6	1336.9
172.5°	1345.3	1347.0	1348.8	1348.7	1346.8	1344.8	1342.8	1340.9
175°	1351.0	1352.6	1354.2	1354.1	1352.3	1350.5	1348.7	1346.9
177.5°	1353.2	1354.6	1356.0	1355.9	1354.1	1352.3	1350.5	1348.7
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9

(END OF REPORT)