

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332402-927

Luminaire Tested: **S123RDIW-S340D1320U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332402-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1320U927-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1320 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5258.3 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	20
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	25	25	18
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	61	55	67	60	54	50	46	42	39	33	30	28	21	19	18	13
4	70	60	52	47	61	53	47	42	41	36	33	29	27	24	19	17	16	11
5	64	53	45	40	56	47	41	36	36	32	29	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	16	14	12	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	15	13	11	10	7
9	47	35	28	23	41	31	25	21	25	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4640	4640	4640	4640
5°	5532	4660	4105	4660
10°	6907	4634	3707	4634
15°	8107	4586	3381	4586
20°	9049	4515	3103	4515
25°	8904	4441	2932	4441
30°	6400	4373	2757	4373
35°	4273	4282	2643	4282
40°	3147	4175	2525	4175
45°	2641	3987	2411	3987
50°	2331	3739	2251	3739
55°	2044	3457	2029	3457
60°	1819	3186	1858	3186
65°	1597	2896	1729	2896
70°	1253	2637	1580	2637
75°	1102	2304	1443	2304
80°	961	1953	1420	1953
85°	778	1581	1507	1581



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.4	0.8
10°-20°	132.5	2.5
20°-30°	208.1	4.0
30°-40°	217.1	4.1
40°-50°	185.8	3.5
50°-60°	141.6	2.7
60°-70°	90.8	1.7
70°-80°	43.7	0.8
80°-90°	15.4	0.3
90°-100°	49.8	0.9
100°-110°	237.6	4.5
110°-120°	570.6	10.9
120°-130°	726.7	13.8
130°-140°	776.4	14.8
140°-150°	726.0	13.8
150°-160°	585.6	11.1
160°-170°	378.0	7.2
170°-180°	130.3	2.5
0°-30°	382.9	7.3
0°-40°	600.1	11.4
0°-60°	927.5	17.6
0°-90°	1077.3	20.5
90°-120°	858.1	16.3
90°-150°	3087.2	58.7
90°-180°	4181.0	79.5
0°-180°	5258.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	512	431	380	431	512	53
15°	728	412	303	412	728	206
25°	750	374	247	374	750	322
35°	325	326	201	326	325	213
45°	174	262	158	262	174	136
55°	109	184	108	184	109	98
65°	63	114	68	114	63	62
75°	26	55	35	55	26	28
85°	6	13	12	13	6	8
90°	31	1	31	1	31	14
95°	39	62	39	62	39	32
105°	45	304	45	304	45	102
115°	599	569	599	569	599	553
125°	819	803	819	803	819	731
135°	1010	999	1010	999	1010	778
145°	1164	1153	1164	1153	1164	727
155°	1268	1270	1268	1270	1268	585
165°	1336	1340	1336	1340	1336	377
175°	1366	1371	1366	1371	1366	130
180°	1371	1371	1371	1371	1371	



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	459.2	459.8	457.9	457.6	455.3	454.8	454.8	451.6	449.7	447.3	445.8
5°	512.0	514.9	513.4	510.2	504.6	503.3	499.8	494.2	488.0	480.2	476.6
7.5°	577.9	581.9	580.4	575.3	569.4	564.7	554.8	545.7	532.8	521.5	511.8
10°	631.9	627.7	624.4	619.4	614.0	605.4	595.0	580.8	564.4	551.4	537.1
12.5°	672.4	671.7	667.5	662.3	654.8	646.6	633.8	616.6	597.5	578.8	562.3
15°	727.5	728.6	725.9	720.6	709.8	695.2	676.0	668.8	641.5	621.2	600.9
17.5°	765.7	765.5	765.1	757.7	746.8	736.4	718.6	699.7	674.9	646.3	619.0
20°	790.0	788.1	788.5	780.1	772.1	760.0	742.7	715.2	694.9	661.9	633.6
22.5°	789.3	788.9	790.4	787.5	781.6	772.5	758.8	735.5	709.6	676.3	644.5
25°	749.7	748.2	756.9	759.3	768.7	770.4	766.3	753.6	729.0	694.7	655.4
27.5°	627.4	626.6	642.7	662.9	688.4	708.3	727.5	736.7	729.0	704.4	665.0
30°	514.9	532.3	540.4	569.6	602.1	640.8	674.8	707.0	715.0	704.3	672.0
32.5°	427.5	442.7	449.5	474.4	504.8	550.2	601.1	646.8	679.1	687.3	667.9
35°	325.2	325.3	340.9	352.0	380.0	426.7	476.2	537.4	598.3	644.5	649.3
37.5°	259.5	260.4	269.8	280.8	301.9	326.5	370.1	421.0	491.4	562.2	603.8
40°	224.0	225.7	232.7	243.6	258.7	277.4	311.3	359.3	418.0	496.9	561.3
42.5°	201.3	204.0	207.6	216.0	225.4	242.9	270.3	307.4	360.8	435.3	509.6
45°	173.5	175.0	177.8	181.6	190.1	202.2	220.7	245.7	289.9	349.9	424.3
47.5°	153.0	152.3	155.2	158.3	164.0	172.3	184.7	204.9	236.5	284.7	347.8
50°	139.2	138.9	141.0	143.4	148.8	154.9	165.0	180.3	205.4	245.3	303.1
52.5°	126.2	126.8	128.3	131.3	135.1	140.1	149.2	160.3	181.8	216.2	264.4
55°	108.9	109.5	111.5	113.1	115.9	120.9	126.6	135.9	150.6	174.6	214.3
57.5°	94.3	94.0	95.9	96.4	99.5	103.5	108.0	115.2	125.9	143.7	170.4
60°	84.5	84.0	85.6	86.9	88.6	91.9	95.6	102.6	111.1	124.2	147.1
62.5°	75.7	75.4	76.6	78.0	79.3	82.3	85.4	90.8	97.5	108.5	126.7
65°	62.7	63.3	63.8	64.4	65.1	67.0	69.9	73.7	78.3	86.0	99.1
67.5°	49.4	49.9	50.1	51.2	52.8	53.9	55.8	59.0	62.3	68.8	76.2
70°	39.8	39.7	39.8	40.4	42.5	44.4	46.9	49.3	51.3	55.9	62.2
72.5°	34.2	33.9	34.4	34.5	35.5	36.0	37.5	39.8	42.5	45.6	50.1
75°	26.5	26.5	26.5	26.5	27.3	27.6	28.2	28.8	29.7	31.2	34.5
77.5°	19.6	19.6	20.0	20.1	20.3	20.5	20.8	21.4	21.7	22.5	23.9
80°	15.5	15.7	15.5	15.7	15.7	16.1	16.2	16.8	17.0	17.9	18.5
82.5°	11.6	11.6	11.6	11.9	11.9	12.2	12.3	12.7	12.7	13.2	13.7
85°	6.3	5.9	6.3	6.1	6.5	6.1	6.3	6.7	6.7	6.8	7.6
87.5°	7.6	7.8	7.4	7.4	7.4	7.4	7.2	7.1	7.1	6.8	6.3
90°	30.6	30.1	29.6	29.2	28.8	28.0	27.2	26.2	25.3	24.5	21.5
92.5°	33.8	33.5	33.3	33.0	32.7	31.8	30.4	29.0	27.5	26.1	23.8
95°	38.7	38.7	38.7	38.7	38.7	37.9	36.4	34.8	33.2	31.6	29.1
97.5°	42.0	41.7	41.5	41.3	41.0	40.0	38.3	36.4	34.6	32.8	49.1
100°	42.8	42.5	42.3	42.1	41.9	40.9	39.1	37.2	35.4	33.6	68.9
102.5°	43.6	43.2	42.8	42.4	42.0	44.6	50.1	55.8	61.4	67.0	105.6
105°	44.8	44.4	43.9	43.5	43.0	62.8	102.9	142.9	183.0	223.1	243.4
107.5°	140.8	171.0	201.1	231.4	261.6	291.4	320.8	350.1	379.5	408.8	405.7
110°	280.1	312.5	344.8	377.2	409.6	429.5	437.0	444.4	451.9	459.4	456.9



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	480.6	487.4	494.2	501.1	507.9	511.3	511.1	511.0	510.9	510.7	508.3
115°	599.0	598.0	597.1	596.2	595.3	593.7	591.4	589.2	586.9	584.7	582.7
117.5°	665.4	665.2	665.0	664.8	664.6	663.6	661.8	660.0	658.2	656.4	655.4
120°	711.0	711.0	711.0	711.0	711.0	710.1	708.3	706.5	704.6	702.8	702.2
122.5°	755.8	755.7	755.4	755.3	755.1	754.4	753.1	751.9	750.6	749.3	748.5
125°	819.0	818.5	818.1	817.6	817.1	816.7	816.3	815.8	815.3	814.9	814.0
127.5°	879.6	880.1	880.6	881.1	881.5	881.4	880.6	879.9	879.2	878.5	877.3
130°	918.8	919.2	919.7	920.1	920.6	920.4	919.5	918.5	917.7	916.7	915.8
132.5°	954.7	955.3	955.9	956.6	957.2	957.0	956.2	955.2	954.3	953.4	952.7
135°	1009.5	1010.1	1010.8	1011.5	1012.2	1012.2	1011.5	1010.8	1010.1	1009.5	1008.5
137.5°	1061.0	1061.4	1061.9	1062.3	1062.8	1062.5	1061.4	1060.3	1059.2	1058.1	1057.6
140°	1091.9	1092.4	1092.8	1093.3	1093.8	1093.5	1092.7	1091.7	1090.8	1089.9	1089.3
142.5°	1120.5	1121.1	1121.7	1122.4	1123.0	1123.0	1122.2	1121.5	1120.8	1120.1	1119.4
145°	1164.3	1164.3	1164.3	1164.3	1164.3	1164.0	1163.6	1163.2	1162.7	1162.2	1161.8
147.5°	1196.8	1197.9	1199.0	1200.0	1201.0	1201.3	1200.9	1200.4	1200.0	1199.5	1199.0
150°	1221.3	1222.0	1222.7	1223.4	1224.0	1224.2	1223.7	1223.2	1222.8	1222.3	1221.9
152.5°	1240.9	1241.9	1242.9	1244.0	1245.1	1245.2	1244.4	1243.5	1242.7	1241.9	1241.6
155°	1268.2	1269.6	1270.9	1272.2	1273.6	1273.7	1272.6	1271.5	1270.3	1269.2	1269.0
157.5°	1291.2	1292.9	1294.7	1296.5	1298.2	1298.5	1297.1	1295.8	1294.3	1293.0	1293.2
160°	1305.8	1307.4	1309.0	1310.6	1312.2	1312.3	1311.0	1309.6	1308.2	1306.9	1307.1
162.5°	1319.7	1321.1	1322.5	1323.9	1325.3	1325.2	1323.7	1322.2	1320.6	1319.1	1319.3
165°	1336.4	1338.0	1339.6	1341.2	1342.7	1342.7	1340.8	1339.0	1337.2	1335.4	1335.6
167.5°	1348.5	1350.3	1352.1	1353.8	1355.7	1355.7	1353.8	1352.1	1350.3	1348.5	1348.5
170°	1355.7	1357.6	1359.4	1361.2	1363.0	1363.0	1361.2	1359.4	1357.6	1355.7	1355.7
172.5°	1359.9	1361.8	1363.8	1365.8	1367.8	1367.9	1366.1	1364.3	1362.5	1360.7	1360.5
175°	1366.0	1367.8	1369.6	1371.4	1373.2	1373.3	1371.7	1370.2	1368.6	1367.0	1366.8
177.5°	1367.8	1369.6	1371.4	1373.2	1375.1	1375.2	1373.8	1372.3	1370.9	1369.4	1369.2
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	445.1	444.7	442.7	440.3	437.2	435.1	433.5	432.6	429.9	426.7	424.5
5°	472.7	467.1	461.2	454.0	447.3	440.5	436.3	431.3	425.2	418.4	413.6
7.5°	502.1	491.2	479.6	467.5	455.6	444.9	435.4	427.3	417.6	407.8	401.0
10°	524.7	508.8	492.4	475.6	460.3	445.9	434.8	424.0	412.3	401.1	392.5
12.5°	545.3	524.3	505.4	484.7	465.2	448.0	432.1	419.2	405.2	393.2	383.6
15°	571.2	549.8	527.0	495.5	469.5	447.7	428.3	411.5	394.6	379.9	370.4
17.5°	595.5	563.3	532.5	506.4	472.5	445.4	421.7	401.6	382.9	367.3	355.7
20°	605.5	574.3	541.0	507.6	474.4	443.9	416.4	394.2	374.9	357.1	346.4
22.5°	611.6	576.3	541.1	505.2	469.9	438.2	411.1	386.7	365.7	348.9	335.6
25°	618.6	576.6	537.8	502.4	466.4	432.1	399.7	373.9	351.3	333.4	319.3
27.5°	623.3	573.8	528.0	488.6	452.1	418.0	388.3	360.9	337.9	318.9	303.9
30°	624.2	571.6	520.5	477.8	440.8	409.3	378.0	351.8	327.4	307.3	293.3
32.5°	625.3	566.1	510.2	465.0	427.0	395.9	367.5	342.5	317.5	297.7	283.4
35°	620.5	563.1	494.8	442.8	404.7	374.6	349.0	325.9	301.4	282.2	267.6
37.5°	599.5	551.1	478.8	417.7	378.0	350.1	329.2	309.1	286.6	265.9	252.2
40°	578.5	539.3	466.4	402.5	361.0	332.4	313.5	297.1	275.4	256.0	241.2
42.5°	547.0	523.2	454.6	386.6	341.8	314.3	298.3	283.0	263.9	244.2	230.3
45°	489.3	492.4	430.4	361.2	315.2	287.6	272.6	261.9	244.9	228.7	214.4
47.5°	416.9	446.2	402.0	334.1	287.2	261.3	248.2	238.8	227.4	211.4	198.4
50°	369.7	411.5	379.3	316.0	269.7	243.8	230.9	223.3	213.3	200.8	188.5
52.5°	326.1	371.1	351.8	295.7	250.6	227.0	214.4	208.1	200.2	188.4	177.2
55°	265.9	311.6	307.1	265.2	222.0	200.8	191.2	184.2	178.9	170.0	161.1
57.5°	215.2	258.3	260.6	231.2	196.9	175.9	167.6	162.3	158.8	152.2	143.9
60°	183.1	222.8	230.5	208.3	178.9	160.4	152.3	148.0	145.3	139.9	133.6
62.5°	156.5	190.3	199.1	183.2	161.6	144.3	137.9	133.9	132.0	127.4	121.8
65°	119.8	147.8	156.3	147.5	136.2	122.4	117.2	113.7	112.0	109.5	105.4
67.5°	90.1	110.5	119.9	113.6	109.5	100.8	97.5	95.6	94.1	92.4	89.0
70°	72.3	87.5	97.0	95.5	92.1	87.5	85.1	83.8	82.3	80.8	77.9
72.5°	58.1	68.6	77.6	78.4	75.7	74.8	72.6	72.1	71.2	69.5	67.8
75°	38.6	45.8	52.0	54.4	55.5	56.5	55.5	55.4	55.2	53.7	52.8
77.5°	25.3	29.2	33.1	37.2	39.0	40.2	40.5	41.2	40.6	39.9	39.5
80°	19.4	20.3	23.1	26.5	29.3	30.4	31.2	31.5	31.4	31.2	30.4
82.5°	14.1	14.8	16.2	18.6	20.9	22.7	23.2	23.1	23.5	23.7	23.1
85°	7.6	7.8	8.2	8.5	9.7	11.8	12.4	12.8	13.1	13.1	12.0
87.5°	6.1	5.3	5.1	4.5	4.5	4.2	4.7	4.9	5.5	5.4	5.9
90°	18.5	15.6	12.7	10.1	7.8	5.5	3.2	1.0	3.2	5.5	7.8
92.5°	21.6	19.4	17.2	16.4	17.0	17.7	18.3	18.9	18.3	17.7	17.0
95°	26.6	24.1	21.6	25.0	34.3	43.6	52.8	62.1	52.8	43.6	34.3
97.5°	65.4	81.7	98.0	108.2	112.4	116.5	120.7	124.8	120.7	116.5	112.4
100°	104.3	139.6	174.8	190.3	185.7	181.2	176.7	172.1	176.7	181.2	185.7
102.5°	144.2	182.8	221.3	239.0	235.7	232.4	229.2	225.9	229.2	232.4	235.7
105°	263.8	284.2	304.6	313.5	311.0	308.6	306.0	303.6	306.0	308.6	311.0
107.5°	402.4	399.3	396.0	393.4	391.4	389.4	387.5	385.5	387.5	389.4	391.4
110°	454.4	451.9	449.4	447.3	445.4	443.6	441.9	440.1	441.9	443.6	445.4



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	505.7	503.3	500.7	498.7	497.1	495.4	493.8	492.2	493.8	495.4	497.1
115°	580.6	578.5	576.6	574.8	573.5	572.1	570.8	569.4	570.8	572.1	573.5
117.5°	654.3	653.2	652.2	650.9	649.2	647.5	645.9	644.2	645.9	647.5	649.2
120°	701.5	700.8	700.1	698.8	696.7	694.7	692.7	690.6	692.7	694.7	696.7
122.5°	747.6	746.7	745.8	744.6	742.9	741.2	739.6	737.9	739.6	741.2	742.9
125°	813.1	812.1	811.3	809.9	808.1	806.3	804.5	802.6	804.5	806.3	808.1
127.5°	876.3	875.2	874.1	872.7	870.8	869.0	867.2	865.4	867.2	869.0	870.8
130°	915.0	914.0	913.1	911.8	910.0	908.2	906.3	904.5	906.3	908.2	910.0
132.5°	952.0	951.3	950.5	949.3	947.5	945.6	943.8	942.0	943.8	945.6	947.5
135°	1007.7	1006.7	1005.8	1004.7	1003.3	1002.0	1000.6	999.3	1000.6	1002.0	1003.3
137.5°	1057.2	1056.6	1056.1	1055.0	1053.3	1051.6	1049.9	1048.1	1049.9	1051.6	1053.3
140°	1088.5	1087.9	1087.2	1086.2	1084.8	1083.5	1082.1	1080.8	1082.1	1083.5	1084.8
142.5°	1118.7	1118.0	1117.4	1116.3	1115.0	1113.6	1112.2	1110.9	1112.2	1113.6	1115.0
145°	1161.3	1160.9	1160.4	1159.4	1157.9	1156.3	1154.7	1153.1	1154.7	1156.3	1157.9
147.5°	1198.6	1198.2	1197.7	1197.0	1195.9	1194.8	1193.8	1192.8	1193.8	1194.8	1195.9
150°	1221.4	1221.0	1220.5	1220.0	1219.2	1218.6	1217.9	1217.3	1217.9	1218.6	1219.2
152.5°	1241.3	1241.1	1240.8	1240.5	1240.2	1239.8	1239.5	1239.2	1239.5	1239.8	1240.2
155°	1268.8	1268.5	1268.3	1268.4	1268.8	1269.3	1269.8	1270.2	1269.8	1269.3	1268.8
157.5°	1293.5	1293.7	1294.0	1294.0	1294.1	1294.2	1294.2	1294.3	1294.2	1294.2	1294.1
160°	1307.3	1307.6	1307.8	1308.0	1308.2	1308.4	1308.7	1308.9	1308.7	1308.4	1308.2
162.5°	1319.5	1319.8	1320.0	1320.4	1321.0	1321.6	1322.2	1322.8	1322.2	1321.6	1321.0
165°	1335.9	1336.1	1336.3	1336.7	1337.4	1338.1	1338.8	1339.5	1338.8	1338.1	1337.4
167.5°	1348.5	1348.5	1348.5	1348.8	1349.8	1350.7	1351.6	1352.5	1351.6	1350.7	1349.8
170°	1355.7	1355.7	1355.7	1356.2	1357.2	1358.0	1358.9	1359.9	1358.9	1358.0	1357.2
172.5°	1360.3	1360.1	1359.9	1360.4	1361.4	1362.6	1363.7	1364.8	1363.7	1362.6	1361.4
175°	1366.5	1366.3	1366.0	1366.5	1367.6	1368.8	1369.9	1371.0	1369.9	1368.8	1367.6
177.5°	1369.0	1368.9	1368.7	1369.0	1370.0	1370.9	1371.7	1372.7	1371.7	1370.9	1370.0
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	423.7	421.8	420.5	417.6	415.7	413.6	411.5	412.8	412.6	412.6	412.6
5°	409.6	405.3	401.4	396.4	393.3	389.4	386.5	386.1	386.8	384.3	382.8
7.5°	395.5	389.7	384.1	378.7	372.8	368.1	365.3	363.8	362.0	360.4	358.8
10°	385.6	378.7	373.4	366.5	360.3	354.7	351.3	348.8	347.5	346.3	343.8
12.5°	375.3	368.7	361.9	354.1	348.2	341.7	339.1	336.4	334.0	332.5	329.2
15°	360.4	351.8	344.6	336.4	329.8	323.5	319.9	314.5	313.8	311.9	308.6
17.5°	345.5	336.1	326.1	320.1	312.7	306.1	300.5	298.7	293.4	291.4	288.5
20°	333.7	325.0	317.4	309.5	298.7	292.6	288.1	285.7	281.5	278.8	277.0
22.5°	323.5	314.7	305.9	296.7	287.7	280.8	277.6	273.9	271.6	267.9	265.9
25°	309.0	299.4	288.8	278.8	272.4	267.3	262.1	258.7	255.4	253.7	250.1
27.5°	292.1	282.0	272.2	264.6	256.7	251.6	246.9	244.0	240.0	237.2	235.1
30°	282.7	270.9	262.4	255.6	245.5	240.7	237.2	233.5	230.5	227.6	225.5
32.5°	272.0	261.2	253.2	244.7	236.9	231.6	227.1	223.9	221.3	218.6	216.5
35°	255.1	246.1	237.7	229.3	223.5	218.2	212.8	210.0	207.6	205.0	203.2
37.5°	239.8	231.3	223.4	215.4	208.3	203.9	199.6	197.5	194.2	192.5	190.7
40°	230.4	222.0	213.6	205.8	198.4	195.1	191.2	188.1	185.1	183.8	181.8
42.5°	220.0	211.7	204.5	196.2	190.1	185.6	182.0	178.6	176.4	174.5	173.4
45°	204.7	197.3	190.3	182.0	176.3	172.4	168.3	165.2	163.2	161.8	159.9
47.5°	189.8	182.4	175.3	168.1	162.6	158.1	154.0	151.9	149.2	147.6	146.2
50°	179.0	172.4	164.9	158.2	152.7	148.2	144.9	142.1	139.7	137.7	136.7
52.5°	169.1	162.1	155.5	149.3	143.5	138.5	135.5	132.5	130.7	128.4	127.3
55°	152.8	146.0	140.5	134.4	128.7	124.4	120.7	118.1	116.3	113.7	112.3
57.5°	137.5	131.3	124.8	119.5	113.6	110.0	106.9	103.5	101.2	99.2	97.7
60°	127.1	120.2	114.4	109.5	104.3	99.7	96.9	94.1	91.7	89.7	88.4
62.5°	116.4	110.3	104.8	99.4	94.7	90.6	87.5	85.2	83.0	81.8	80.4
65°	99.8	95.1	89.5	85.1	80.6	77.7	75.1	73.1	71.6	70.7	69.6
67.5°	84.6	80.0	75.2	70.8	67.8	65.6	63.9	62.2	61.4	60.2	59.5
70°	74.8	69.9	65.7	62.3	59.4	57.8	56.6	55.4	54.7	53.2	52.4
72.5°	64.0	60.5	57.4	54.7	52.4	50.9	49.4	47.8	46.7	45.0	44.3
75°	50.4	47.2	44.8	43.0	41.5	39.5	37.5	35.8	35.3	34.7	34.5
77.5°	37.3	35.3	33.6	32.0	30.2	28.8	28.3	27.9	27.8	27.5	27.5
80°	29.3	27.5	26.2	24.4	23.3	23.3	23.3	22.9	23.1	23.1	23.1
82.5°	21.8	20.1	19.4	18.8	18.5	18.7	18.7	18.8	18.6	18.9	18.8
85°	11.2	11.4	11.8	11.6	11.8	11.8	12.2	12.0	12.2	11.8	12.2
87.5°	6.2	7.1	7.8	8.6	9.3	9.7	10.1	10.3	10.6	10.8	10.9
90°	10.1	12.7	15.6	18.5	21.5	24.5	25.3	26.2	27.2	28.0	28.8
92.5°	16.4	17.2	19.4	21.6	23.8	26.1	27.5	29.0	30.4	31.8	32.7
95°	25.0	21.6	24.1	26.6	29.1	31.6	33.2	34.8	36.4	37.9	38.7
97.5°	108.2	98.0	81.7	65.4	49.1	32.8	34.6	36.4	38.3	40.0	41.0
100°	190.3	174.8	139.6	104.3	68.9	33.6	35.4	37.2	39.1	40.9	41.9
102.5°	239.0	221.3	182.8	144.2	105.6	67.0	61.4	55.8	50.1	44.6	42.0
105°	313.5	304.6	284.2	263.8	243.4	223.1	183.0	142.9	102.9	62.8	43.0
107.5°	393.4	396.0	399.3	402.4	405.7	408.8	379.5	350.1	320.8	291.4	261.6
110°	447.3	449.4	451.9	454.4	456.9	459.4	451.9	444.4	437.0	429.5	409.6



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	498.7	500.7	503.3	505.7	508.3	510.7	510.9	511.0	511.1	511.3	507.9
115°	574.8	576.6	578.5	580.6	582.7	584.7	586.9	589.2	591.4	593.7	595.3
117.5°	650.9	652.2	653.2	654.3	655.4	656.4	658.2	660.0	661.8	663.6	664.6
120°	698.8	700.1	700.8	701.5	702.2	702.8	704.6	706.5	708.3	710.1	711.0
122.5°	744.6	745.8	746.7	747.6	748.5	749.3	750.6	751.9	753.1	754.4	755.1
125°	809.9	811.3	812.1	813.1	814.0	814.9	815.3	815.8	816.3	816.7	817.1
127.5°	872.7	874.1	875.2	876.3	877.3	878.5	879.2	879.9	880.6	881.4	881.5
130°	911.8	913.1	914.0	915.0	915.8	916.7	917.7	918.5	919.5	920.4	920.6
132.5°	949.3	950.5	951.3	952.0	952.7	953.4	954.3	955.2	956.2	957.0	957.2
135°	1004.7	1005.8	1006.7	1007.7	1008.5	1009.5	1010.1	1010.8	1011.5	1012.2	1012.2
137.5°	1055.0	1056.1	1056.6	1057.2	1057.6	1058.1	1059.2	1060.3	1061.4	1062.5	1062.8
140°	1086.2	1087.2	1087.9	1088.5	1089.3	1089.9	1090.8	1091.7	1092.7	1093.5	1093.8
142.5°	1116.3	1117.4	1118.0	1118.7	1119.4	1120.1	1120.8	1121.5	1122.2	1123.0	1123.0
145°	1159.4	1160.4	1160.9	1161.3	1161.8	1162.2	1162.7	1163.2	1163.6	1164.0	1164.3
147.5°	1197.0	1197.7	1198.2	1198.6	1199.0	1199.5	1200.0	1200.4	1200.9	1201.3	1201.0
150°	1220.0	1220.5	1221.0	1221.4	1221.9	1222.3	1222.8	1223.2	1223.7	1224.2	1224.0
152.5°	1240.5	1240.8	1241.1	1241.3	1241.6	1241.9	1242.7	1243.5	1244.4	1245.2	1245.1
155°	1268.4	1268.3	1268.5	1268.8	1269.0	1269.2	1270.3	1271.5	1272.6	1273.7	1273.6
157.5°	1294.0	1294.0	1293.7	1293.5	1293.2	1293.0	1294.3	1295.8	1297.1	1298.5	1298.2
160°	1308.0	1307.8	1307.6	1307.3	1307.1	1306.9	1308.2	1309.6	1311.0	1312.3	1312.2
162.5°	1320.4	1320.0	1319.8	1319.5	1319.3	1319.1	1320.6	1322.2	1323.7	1325.2	1325.3
165°	1336.7	1336.3	1336.1	1335.9	1335.6	1335.4	1337.2	1339.0	1340.8	1342.7	1342.7
167.5°	1348.8	1348.5	1348.5	1348.5	1348.5	1348.5	1350.3	1352.1	1353.8	1355.7	1355.7
170°	1356.2	1355.7	1355.7	1355.7	1355.7	1355.7	1357.6	1359.4	1361.2	1363.0	1363.0
172.5°	1360.4	1359.9	1360.1	1360.3	1360.5	1360.7	1362.5	1364.3	1366.1	1367.9	1367.8
175°	1366.5	1366.0	1366.3	1366.5	1366.8	1367.0	1368.6	1370.2	1371.7	1373.3	1373.2
177.5°	1369.0	1368.7	1368.9	1369.0	1369.2	1369.4	1370.9	1372.3	1373.8	1375.2	1375.1
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	410.7	410.6	410.7	410.2	410.7	410.6	410.7	412.6	412.6	412.6	412.8
5°	382.2	382.1	381.5	379.9	381.5	382.1	382.2	382.8	384.3	386.8	386.1
7.5°	357.3	357.0	355.5	355.5	355.5	357.0	357.3	358.8	360.4	362.0	363.8
10°	342.5	342.7	340.5	339.2	340.5	342.7	342.5	343.8	346.3	347.5	348.8
12.5°	328.2	327.4	325.6	324.2	325.6	327.4	328.2	329.2	332.5	334.0	336.4
15°	309.3	307.4	303.1	303.4	303.1	307.4	309.3	308.6	311.9	313.8	314.5
17.5°	287.1	285.7	285.7	283.0	285.7	285.7	287.1	288.5	291.4	293.4	298.7
20°	274.1	273.1	273.5	270.9	273.5	273.1	274.1	277.0	278.8	281.5	285.7
22.5°	263.9	262.9	261.4	260.6	261.4	262.9	263.9	265.9	267.9	271.6	273.9
25°	249.0	247.5	246.1	246.9	246.1	247.5	249.0	250.1	253.7	255.4	258.7
27.5°	234.1	233.0	231.5	231.3	231.5	233.0	234.1	235.1	237.2	240.0	244.0
30°	224.6	223.5	222.8	221.8	222.8	223.5	224.6	225.5	227.6	230.5	233.5
32.5°	215.0	214.8	213.5	213.3	213.5	214.8	215.0	216.5	218.6	221.3	223.9
35°	202.5	201.4	201.0	201.1	201.0	201.4	202.5	203.2	205.0	207.6	210.0
37.5°	190.5	189.1	188.4	187.7	188.4	189.1	190.5	190.7	192.5	194.2	197.5
40°	182.0	180.5	180.1	179.7	180.1	180.5	182.0	181.8	183.8	185.1	188.1
42.5°	172.4	171.8	171.6	170.9	171.6	171.8	172.4	173.4	174.5	176.4	178.6
45°	159.3	159.1	158.0	158.4	158.0	159.1	159.3	159.9	161.8	163.2	165.2
47.5°	145.4	144.7	143.9	144.4	143.9	144.7	145.4	146.2	147.6	149.2	151.9
50°	136.0	135.6	134.0	134.4	134.0	135.6	136.0	136.7	137.7	139.7	142.1
52.5°	126.6	125.2	124.5	124.3	124.5	125.2	126.6	127.3	128.4	130.7	132.5
55°	110.9	109.2	108.5	108.1	108.5	109.2	110.9	112.3	113.7	116.3	118.1
57.5°	95.5	95.1	94.5	94.9	94.5	95.1	95.5	97.7	99.2	101.2	103.5
60°	86.6	86.6	86.6	86.3	86.6	86.6	86.6	88.4	89.7	91.7	94.1
62.5°	79.6	79.1	79.1	79.3	79.1	79.1	79.6	80.4	81.8	83.0	85.2
65°	69.0	68.8	68.1	67.9	68.1	68.8	69.0	69.6	70.7	71.6	73.1
67.5°	59.0	58.4	58.1	57.9	58.1	58.4	59.0	59.5	60.2	61.4	62.2
70°	51.5	51.1	50.0	50.2	50.0	51.1	51.5	52.4	53.2	54.7	55.4
72.5°	43.4	43.0	42.8	42.5	42.8	43.0	43.4	44.3	45.0	46.7	47.8
75°	34.3	34.1	34.0	34.7	34.0	34.1	34.3	34.5	34.7	35.3	35.8
77.5°	27.5	27.5	27.6	27.3	27.6	27.5	27.5	27.5	27.5	27.8	27.9
80°	23.1	23.1	22.9	22.9	22.9	23.1	23.1	23.1	23.1	23.1	22.9
82.5°	18.5	18.6	18.8	18.5	18.8	18.6	18.5	18.8	18.9	18.6	18.8
85°	12.2	12.0	12.4	12.2	12.4	12.0	12.2	12.2	11.8	12.2	12.0
87.5°	11.3	11.1	11.2	11.4	11.2	11.1	11.3	10.9	10.8	10.6	10.3
90°	29.2	29.6	30.1	30.6	30.1	29.6	29.2	28.8	28.0	27.2	26.2
92.5°	33.0	33.3	33.5	33.8	33.5	33.3	33.0	32.7	31.8	30.4	29.0
95°	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	37.9	36.4	34.8
97.5°	41.3	41.5	41.7	42.0	41.7	41.5	41.3	41.0	40.0	38.3	36.4
100°	42.1	42.3	42.5	42.8	42.5	42.3	42.1	41.9	40.9	39.1	37.2
102.5°	42.4	42.8	43.2	43.6	43.2	42.8	42.4	42.0	44.6	50.1	55.8
105°	43.5	43.9	44.4	44.8	44.4	43.9	43.5	43.0	62.8	102.9	142.9
107.5°	231.4	201.1	171.0	140.8	171.0	201.1	231.4	261.6	291.4	320.8	350.1
110°	377.2	344.8	312.5	280.1	312.5	344.8	377.2	409.6	429.5	437.0	444.4



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	501.1	494.2	487.4	480.6	487.4	494.2	501.1	507.9	511.3	511.1	511.0
115°	596.2	597.1	598.0	599.0	598.0	597.1	596.2	595.3	593.7	591.4	589.2
117.5°	664.8	665.0	665.2	665.4	665.2	665.0	664.8	664.6	663.6	661.8	660.0
120°	711.0	711.0	711.0	711.0	711.0	711.0	711.0	711.0	710.1	708.3	706.5
122.5°	755.3	755.4	755.7	755.8	755.7	755.4	755.3	755.1	754.4	753.1	751.9
125°	817.6	818.1	818.5	819.0	818.5	818.1	817.6	817.1	816.7	816.3	815.8
127.5°	881.1	880.6	880.1	879.6	880.1	880.6	881.1	881.5	881.4	880.6	879.9
130°	920.1	919.7	919.2	918.8	919.2	919.7	920.1	920.6	920.4	919.5	918.5
132.5°	956.6	955.9	955.3	954.7	955.3	955.9	956.6	957.2	957.0	956.2	955.2
135°	1011.5	1010.8	1010.1	1009.5	1010.1	1010.8	1011.5	1012.2	1012.2	1011.5	1010.8
137.5°	1062.3	1061.9	1061.4	1061.0	1061.4	1061.9	1062.3	1062.8	1062.5	1061.4	1060.3
140°	1093.3	1092.8	1092.4	1091.9	1092.4	1092.8	1093.3	1093.8	1093.5	1092.7	1091.7
142.5°	1122.4	1121.7	1121.1	1120.5	1121.1	1121.7	1122.4	1123.0	1123.0	1122.2	1121.5
145°	1164.3	1164.3	1164.3	1164.3	1164.3	1164.3	1164.3	1164.3	1164.0	1163.6	1163.2
147.5°	1200.0	1199.0	1197.9	1196.8	1197.9	1199.0	1200.0	1201.0	1201.3	1200.9	1200.4
150°	1223.4	1222.7	1222.0	1221.3	1222.0	1222.7	1223.4	1224.0	1224.2	1223.7	1223.2
152.5°	1244.0	1242.9	1241.9	1240.9	1241.9	1242.9	1244.0	1245.1	1245.2	1244.4	1243.5
155°	1272.2	1270.9	1269.6	1268.2	1269.6	1270.9	1272.2	1273.6	1273.7	1272.6	1271.5
157.5°	1296.5	1294.7	1292.9	1291.2	1292.9	1294.7	1296.5	1298.2	1298.5	1297.1	1295.8
160°	1310.6	1309.0	1307.4	1305.8	1307.4	1309.0	1310.6	1312.2	1312.3	1311.0	1309.6
162.5°	1323.9	1322.5	1321.1	1319.7	1321.1	1322.5	1323.9	1325.3	1325.2	1323.7	1322.2
165°	1341.2	1339.6	1338.0	1336.4	1338.0	1339.6	1341.2	1342.7	1342.7	1340.8	1339.0
167.5°	1353.8	1352.1	1350.3	1348.5	1350.3	1352.1	1353.8	1355.7	1355.7	1353.8	1352.1
170°	1361.2	1359.4	1357.6	1355.7	1357.6	1359.4	1361.2	1363.0	1363.0	1361.2	1359.4
172.5°	1365.8	1363.8	1361.8	1359.9	1361.8	1363.8	1365.8	1367.8	1367.9	1366.1	1364.3
175°	1371.4	1369.6	1367.8	1366.0	1367.8	1369.6	1371.4	1373.2	1373.3	1371.7	1370.2
177.5°	1373.2	1371.4	1369.6	1367.8	1369.6	1371.4	1373.2	1375.1	1375.2	1373.8	1372.3
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	411.5	413.6	415.7	417.6	420.5	421.8	423.7	424.5	426.7	429.9	432.6
5°	386.5	389.4	393.3	396.4	401.4	405.3	409.6	413.6	418.4	425.2	431.3
7.5°	365.3	368.1	372.8	378.7	384.1	389.7	395.5	401.0	407.8	417.6	427.3
10°	351.3	354.7	360.3	366.5	373.4	378.7	385.6	392.5	401.1	412.3	424.0
12.5°	339.1	341.7	348.2	354.1	361.9	368.7	375.3	383.6	393.2	405.2	419.2
15°	319.9	323.5	329.8	336.4	344.6	351.8	360.4	370.4	379.9	394.6	411.5
17.5°	300.5	306.1	312.7	320.1	326.1	336.1	345.5	355.7	367.3	382.9	401.6
20°	288.1	292.6	298.7	309.5	317.4	325.0	333.7	346.4	357.1	374.9	394.2
22.5°	277.6	280.8	287.7	296.7	305.9	314.7	323.5	335.6	348.9	365.7	386.7
25°	262.1	267.3	272.4	278.8	288.8	299.4	309.0	319.3	333.4	351.3	373.9
27.5°	246.9	251.6	256.7	264.6	272.2	282.0	292.1	303.9	318.9	337.9	360.9
30°	237.2	240.7	245.5	255.6	262.4	270.9	282.7	293.3	307.3	327.4	351.8
32.5°	227.1	231.6	236.9	244.7	253.2	261.2	272.0	283.4	297.7	317.5	342.5
35°	212.8	218.2	223.5	229.3	237.7	246.1	255.1	267.6	282.2	301.4	325.9
37.5°	199.6	203.9	208.3	215.4	223.4	231.3	239.8	252.2	265.9	286.6	309.1
40°	191.2	195.1	198.4	205.8	213.6	222.0	230.4	241.2	256.0	275.4	297.1
42.5°	182.0	185.6	190.1	196.2	204.5	211.7	220.0	230.3	244.2	263.9	283.0
45°	168.3	172.4	176.3	182.0	190.3	197.3	204.7	214.4	228.7	244.9	261.9
47.5°	154.0	158.1	162.6	168.1	175.3	182.4	189.8	198.4	211.4	227.4	238.8
50°	144.9	148.2	152.7	158.2	164.9	172.4	179.0	188.5	200.8	213.3	223.3
52.5°	135.5	138.5	143.5	149.3	155.5	162.1	169.1	177.2	188.4	200.2	208.1
55°	120.7	124.4	128.7	134.4	140.5	146.0	152.8	161.1	170.0	178.9	184.2
57.5°	106.9	110.0	113.6	119.5	124.8	131.3	137.5	143.9	152.2	158.8	162.3
60°	96.9	99.7	104.3	109.5	114.4	120.2	127.1	133.6	139.9	145.3	148.0
62.5°	87.5	90.6	94.7	99.4	104.8	110.3	116.4	121.8	127.4	132.0	133.9
65°	75.1	77.7	80.6	85.1	89.5	95.1	99.8	105.4	109.5	112.0	113.7
67.5°	63.9	65.6	67.8	70.8	75.2	80.0	84.6	89.0	92.4	94.1	95.6
70°	56.6	57.8	59.4	62.3	65.7	69.9	74.8	77.9	80.8	82.3	83.8
72.5°	49.4	50.9	52.4	54.7	57.4	60.5	64.0	67.8	69.5	71.2	72.1
75°	37.5	39.5	41.5	43.0	44.8	47.2	50.4	52.8	53.7	55.2	55.4
77.5°	28.3	28.8	30.2	32.0	33.6	35.3	37.3	39.5	39.9	40.6	41.2
80°	23.3	23.3	23.3	24.4	26.2	27.5	29.3	30.4	31.2	31.4	31.5
82.5°	18.7	18.7	18.5	18.8	19.4	20.1	21.8	23.1	23.7	23.5	23.1
85°	12.2	11.8	11.8	11.6	11.8	11.4	11.2	12.0	13.1	13.1	12.8
87.5°	10.1	9.7	9.3	8.6	7.8	7.1	6.2	5.9	5.4	5.5	4.9
90°	25.3	24.5	21.5	18.5	15.6	12.7	10.1	7.8	5.5	3.2	1.0
92.5°	27.5	26.1	23.8	21.6	19.4	17.2	16.4	17.0	17.7	18.3	18.9
95°	33.2	31.6	29.1	26.6	24.1	21.6	25.0	34.3	43.6	52.8	62.1
97.5°	34.6	32.8	49.1	65.4	81.7	98.0	108.2	112.4	116.5	120.7	124.8
100°	35.4	33.6	68.9	104.3	139.6	174.8	190.3	185.7	181.2	176.7	172.1
102.5°	61.4	67.0	105.6	144.2	182.8	221.3	239.0	235.7	232.4	229.2	225.9
105°	183.0	223.1	243.4	263.8	284.2	304.6	313.5	311.0	308.6	306.0	303.6
107.5°	379.5	408.8	405.7	402.4	399.3	396.0	393.4	391.4	389.4	387.5	385.5
110°	451.9	459.4	456.9	454.4	451.9	449.4	447.3	445.4	443.6	441.9	440.1



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	510.9	510.7	508.3	505.7	503.3	500.7	498.7	497.1	495.4	493.8	492.2
115°	586.9	584.7	582.7	580.6	578.5	576.6	574.8	573.5	572.1	570.8	569.4
117.5°	658.2	656.4	655.4	654.3	653.2	652.2	650.9	649.2	647.5	645.9	644.2
120°	704.6	702.8	702.2	701.5	700.8	700.1	698.8	696.7	694.7	692.7	690.6
122.5°	750.6	749.3	748.5	747.6	746.7	745.8	744.6	742.9	741.2	739.6	737.9
125°	815.3	814.9	814.0	813.1	812.1	811.3	809.9	808.1	806.3	804.5	802.6
127.5°	879.2	878.5	877.3	876.3	875.2	874.1	872.7	870.8	869.0	867.2	865.4
130°	917.7	916.7	915.8	915.0	914.0	913.1	911.8	910.0	908.2	906.3	904.5
132.5°	954.3	953.4	952.7	952.0	951.3	950.5	949.3	947.5	945.6	943.8	942.0
135°	1010.1	1009.5	1008.5	1007.7	1006.7	1005.8	1004.7	1003.3	1002.0	1000.6	999.3
137.5°	1059.2	1058.1	1057.6	1057.2	1056.6	1056.1	1055.0	1053.3	1051.6	1049.9	1048.1
140°	1090.8	1089.9	1089.3	1088.5	1087.9	1087.2	1086.2	1084.8	1083.5	1082.1	1080.8
142.5°	1120.8	1120.1	1119.4	1118.7	1118.0	1117.4	1116.3	1115.0	1113.6	1112.2	1110.9
145°	1162.7	1162.2	1161.8	1161.3	1160.9	1160.4	1159.4	1157.9	1156.3	1154.7	1153.1
147.5°	1200.0	1199.5	1199.0	1198.6	1198.2	1197.7	1197.0	1195.9	1194.8	1193.8	1192.8
150°	1222.8	1222.3	1221.9	1221.4	1221.0	1220.5	1220.0	1219.2	1218.6	1217.9	1217.3
152.5°	1242.7	1241.9	1241.6	1241.3	1241.1	1240.8	1240.5	1240.2	1239.8	1239.5	1239.2
155°	1270.3	1269.2	1269.0	1268.8	1268.5	1268.3	1268.4	1268.8	1269.3	1269.8	1270.2
157.5°	1294.3	1293.0	1293.2	1293.5	1293.7	1294.0	1294.0	1294.1	1294.2	1294.2	1294.3
160°	1308.2	1306.9	1307.1	1307.3	1307.6	1307.8	1308.0	1308.2	1308.4	1308.7	1308.9
162.5°	1320.6	1319.1	1319.3	1319.5	1319.8	1320.0	1320.4	1321.0	1321.6	1322.2	1322.8
165°	1337.2	1335.4	1335.6	1335.9	1336.1	1336.3	1336.7	1337.4	1338.1	1338.8	1339.5
167.5°	1350.3	1348.5	1348.5	1348.5	1348.5	1348.5	1348.8	1349.8	1350.7	1351.6	1352.5
170°	1357.6	1355.7	1355.7	1355.7	1355.7	1355.7	1356.2	1357.2	1358.0	1358.9	1359.9
172.5°	1362.5	1360.7	1360.5	1360.3	1360.1	1359.9	1360.4	1361.4	1362.6	1363.7	1364.8
175°	1368.6	1367.0	1366.8	1366.5	1366.3	1366.0	1366.5	1367.6	1368.8	1369.9	1371.0
177.5°	1370.9	1369.4	1369.2	1369.0	1368.9	1368.7	1369.0	1370.0	1370.9	1371.7	1372.7
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	433.5	435.1	437.2	440.3	442.7	444.7	445.1	445.8	447.3	449.7	451.6
5°	436.3	440.5	447.3	454.0	461.2	467.1	472.7	476.6	480.2	488.0	494.2
7.5°	435.4	444.9	455.6	467.5	479.6	491.2	502.1	511.8	521.5	532.8	545.7
10°	434.8	445.9	460.3	475.6	492.4	508.8	524.7	537.1	551.4	564.4	580.8
12.5°	432.1	448.0	465.2	484.7	505.4	524.3	545.3	562.3	578.8	597.5	616.6
15°	428.3	447.7	469.5	495.5	527.0	549.8	571.2	600.9	621.2	641.5	668.8
17.5°	421.7	445.4	472.5	506.4	532.5	563.3	595.5	619.0	646.3	674.9	699.7
20°	416.4	443.9	474.4	507.6	541.0	574.3	605.5	633.6	661.9	694.9	715.2
22.5°	411.1	438.2	469.9	505.2	541.1	576.3	611.6	644.5	676.3	709.6	735.5
25°	399.7	432.1	466.4	502.4	537.8	576.6	618.6	655.4	694.7	729.0	753.6
27.5°	388.3	418.0	452.1	488.6	528.0	573.8	623.3	665.0	704.4	729.0	736.7
30°	378.0	409.3	440.8	477.8	520.5	571.6	624.2	672.0	704.3	715.0	707.0
32.5°	367.5	395.9	427.0	465.0	510.2	566.1	625.3	667.9	687.3	679.1	646.8
35°	349.0	374.6	404.7	442.8	494.8	563.1	620.5	649.3	644.5	598.3	537.4
37.5°	329.2	350.1	378.0	417.7	478.8	551.1	599.5	603.8	562.2	491.4	421.0
40°	313.5	332.4	361.0	402.5	466.4	539.3	578.5	561.3	496.9	418.0	359.3
42.5°	298.3	314.3	341.8	386.6	454.6	523.2	547.0	509.6	435.3	360.8	307.4
45°	272.6	287.6	315.2	361.2	430.4	492.4	489.3	424.3	349.9	289.9	245.7
47.5°	248.2	261.3	287.2	334.1	402.0	446.2	416.9	347.8	284.7	236.5	204.9
50°	230.9	243.8	269.7	316.0	379.3	411.5	369.7	303.1	245.3	205.4	180.3
52.5°	214.4	227.0	250.6	295.7	351.8	371.1	326.1	264.4	216.2	181.8	160.3
55°	191.2	200.8	222.0	265.2	307.1	311.6	265.9	214.3	174.6	150.6	135.9
57.5°	167.6	175.9	196.9	231.2	260.6	258.3	215.2	170.4	143.7	125.9	115.2
60°	152.3	160.4	178.9	208.3	230.5	222.8	183.1	147.1	124.2	111.1	102.6
62.5°	137.9	144.3	161.6	183.2	199.1	190.3	156.5	126.7	108.5	97.5	90.8
65°	117.2	122.4	136.2	147.5	156.3	147.8	119.8	99.1	86.0	78.3	73.7
67.5°	97.5	100.8	109.5	113.6	119.9	110.5	90.1	76.2	68.8	62.3	59.0
70°	85.1	87.5	92.1	95.5	97.0	87.5	72.3	62.2	55.9	51.3	49.3
72.5°	72.6	74.8	75.7	78.4	77.6	68.6	58.1	50.1	45.6	42.5	39.8
75°	55.5	56.5	55.5	54.4	52.0	45.8	38.6	34.5	31.2	29.7	28.8
77.5°	40.5	40.2	39.0	37.2	33.1	29.2	25.3	23.9	22.5	21.7	21.4
80°	31.2	30.4	29.3	26.5	23.1	20.3	19.4	18.5	17.9	17.0	16.8
82.5°	23.2	22.7	20.9	18.6	16.2	14.8	14.1	13.7	13.2	12.7	12.7
85°	12.4	11.8	9.7	8.5	8.2	7.8	7.6	7.6	6.8	6.7	6.7
87.5°	4.7	4.2	4.5	4.5	5.1	5.3	6.1	6.3	6.8	7.1	7.1
90°	3.2	5.5	7.8	10.1	12.7	15.6	18.5	21.5	24.5	25.3	26.2
92.5°	18.3	17.7	17.0	16.4	17.2	19.4	21.6	23.8	26.1	27.5	29.0
95°	52.8	43.6	34.3	25.0	21.6	24.1	26.6	29.1	31.6	33.2	34.8
97.5°	120.7	116.5	112.4	108.2	98.0	81.7	65.4	49.1	32.8	34.6	36.4
100°	176.7	181.2	185.7	190.3	174.8	139.6	104.3	68.9	33.6	35.4	37.2
102.5°	229.2	232.4	235.7	239.0	221.3	182.8	144.2	105.6	67.0	61.4	55.8
105°	306.0	308.6	311.0	313.5	304.6	284.2	263.8	243.4	223.1	183.0	142.9
107.5°	387.5	389.4	391.4	393.4	396.0	399.3	402.4	405.7	408.8	379.5	350.1
110°	441.9	443.6	445.4	447.3	449.4	451.9	454.4	456.9	459.4	451.9	444.4



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	493.8	495.4	497.1	498.7	500.7	503.3	505.7	508.3	510.7	510.9	511.0
115°	570.8	572.1	573.5	574.8	576.6	578.5	580.6	582.7	584.7	586.9	589.2
117.5°	645.9	647.5	649.2	650.9	652.2	653.2	654.3	655.4	656.4	658.2	660.0
120°	692.7	694.7	696.7	698.8	700.1	700.8	701.5	702.2	702.8	704.6	706.5
122.5°	739.6	741.2	742.9	744.6	745.8	746.7	747.6	748.5	749.3	750.6	751.9
125°	804.5	806.3	808.1	809.9	811.3	812.1	813.1	814.0	814.9	815.3	815.8
127.5°	867.2	869.0	870.8	872.7	874.1	875.2	876.3	877.3	878.5	879.2	879.9
130°	906.3	908.2	910.0	911.8	913.1	914.0	915.0	915.8	916.7	917.7	918.5
132.5°	943.8	945.6	947.5	949.3	950.5	951.3	952.0	952.7	953.4	954.3	955.2
135°	1000.6	1002.0	1003.3	1004.7	1005.8	1006.7	1007.7	1008.5	1009.5	1010.1	1010.8
137.5°	1049.9	1051.6	1053.3	1055.0	1056.1	1056.6	1057.2	1057.6	1058.1	1059.2	1060.3
140°	1082.1	1083.5	1084.8	1086.2	1087.2	1087.9	1088.5	1089.3	1089.9	1090.8	1091.7
142.5°	1112.2	1113.6	1115.0	1116.3	1117.4	1118.0	1118.7	1119.4	1120.1	1120.8	1121.5
145°	1154.7	1156.3	1157.9	1159.4	1160.4	1160.9	1161.3	1161.8	1162.2	1162.7	1163.2
147.5°	1193.8	1194.8	1195.9	1197.0	1197.7	1198.2	1198.6	1199.0	1199.5	1200.0	1200.4
150°	1217.9	1218.6	1219.2	1220.0	1220.5	1221.0	1221.4	1221.9	1222.3	1222.8	1223.2
152.5°	1239.5	1239.8	1240.2	1240.5	1240.8	1241.1	1241.3	1241.6	1241.9	1242.7	1243.5
155°	1269.8	1269.3	1268.8	1268.4	1268.3	1268.5	1268.8	1269.0	1269.2	1270.3	1271.5
157.5°	1294.2	1294.2	1294.1	1294.0	1294.0	1293.7	1293.5	1293.2	1293.0	1294.3	1295.8
160°	1308.7	1308.4	1308.2	1308.0	1307.8	1307.6	1307.3	1307.1	1306.9	1308.2	1309.6
162.5°	1322.2	1321.6	1321.0	1320.4	1320.0	1319.8	1319.5	1319.3	1319.1	1320.6	1322.2
165°	1338.8	1338.1	1337.4	1336.7	1336.3	1336.1	1335.9	1335.6	1335.4	1337.2	1339.0
167.5°	1351.6	1350.7	1349.8	1348.8	1348.5	1348.5	1348.5	1348.5	1348.5	1350.3	1352.1
170°	1358.9	1358.0	1357.2	1356.2	1355.7	1355.7	1355.7	1355.7	1355.7	1357.6	1359.4
172.5°	1363.7	1362.6	1361.4	1360.4	1359.9	1360.1	1360.3	1360.5	1360.7	1362.5	1364.3
175°	1369.9	1368.8	1367.6	1366.5	1366.0	1366.3	1366.5	1366.8	1367.0	1368.6	1370.2
177.5°	1371.7	1370.9	1370.0	1369.0	1368.7	1368.9	1369.0	1369.2	1369.4	1370.9	1372.3
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	454.8	454.8	455.3	457.6	457.9	459.8	459.2
5°	499.8	503.3	504.6	510.2	513.4	514.9	512.0
7.5°	554.8	564.7	569.4	575.3	580.4	581.9	577.9
10°	595.0	605.4	614.0	619.4	624.4	627.7	631.9
12.5°	633.8	646.6	654.8	662.3	667.5	671.7	672.4
15°	676.0	695.2	709.8	720.6	725.9	728.6	727.5
17.5°	718.6	736.4	746.8	757.7	765.1	765.5	765.7
20°	742.7	760.0	772.1	780.1	788.5	788.1	790.0
22.5°	758.8	772.5	781.6	787.5	790.4	788.9	789.3
25°	766.3	770.4	768.7	759.3	756.9	748.2	749.7
27.5°	727.5	708.3	688.4	662.9	642.7	626.6	627.4
30°	674.8	640.8	602.1	569.6	540.4	532.3	514.9
32.5°	601.1	550.2	504.8	474.4	449.5	442.7	427.5
35°	476.2	426.7	380.0	352.0	340.9	325.3	325.2
37.5°	370.1	326.5	301.9	280.8	269.8	260.4	259.5
40°	311.3	277.4	258.7	243.6	232.7	225.7	224.0
42.5°	270.3	242.9	225.4	216.0	207.6	204.0	201.3
45°	220.7	202.2	190.1	181.6	177.8	175.0	173.5
47.5°	184.7	172.3	164.0	158.3	155.2	152.3	153.0
50°	165.0	154.9	148.8	143.4	141.0	138.9	139.2
52.5°	149.2	140.1	135.1	131.3	128.3	126.8	126.2
55°	126.6	120.9	115.9	113.1	111.5	109.5	108.9
57.5°	108.0	103.5	99.5	96.4	95.9	94.0	94.3
60°	95.6	91.9	88.6	86.9	85.6	84.0	84.5
62.5°	85.4	82.3	79.3	78.0	76.6	75.4	75.7
65°	69.9	67.0	65.1	64.4	63.8	63.3	62.7
67.5°	55.8	53.9	52.8	51.2	50.1	49.9	49.4
70°	46.9	44.4	42.5	40.4	39.8	39.7	39.8
72.5°	37.5	36.0	35.5	34.5	34.4	33.9	34.2
75°	28.2	27.6	27.3	26.5	26.5	26.5	26.5
77.5°	20.8	20.5	20.3	20.1	20.0	19.6	19.6
80°	16.2	16.1	15.7	15.7	15.5	15.7	15.5
82.5°	12.3	12.2	11.9	11.9	11.6	11.6	11.6
85°	6.3	6.1	6.5	6.1	6.3	5.9	6.3
87.5°	7.2	7.4	7.4	7.4	7.4	7.8	7.6
90°	27.2	28.0	28.8	29.2	29.6	30.1	30.6
92.5°	30.4	31.8	32.7	33.0	33.3	33.5	33.8
95°	36.4	37.9	38.7	38.7	38.7	38.7	38.7
97.5°	38.3	40.0	41.0	41.3	41.5	41.7	42.0
100°	39.1	40.9	41.9	42.1	42.3	42.5	42.8
102.5°	50.1	44.6	42.0	42.4	42.8	43.2	43.6
105°	102.9	62.8	43.0	43.5	43.9	44.4	44.8
107.5°	320.8	291.4	261.6	231.4	201.1	171.0	140.8
110°	437.0	429.5	409.6	377.2	344.8	312.5	280.1



TEST NUMBER: P332402-927

CATALOG NUMBER: S123RDIW-S340D1320U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	511.1	511.3	507.9	501.1	494.2	487.4	480.6
115°	591.4	593.7	595.3	596.2	597.1	598.0	599.0
117.5°	661.8	663.6	664.6	664.8	665.0	665.2	665.4
120°	708.3	710.1	711.0	711.0	711.0	711.0	711.0
122.5°	753.1	754.4	755.1	755.3	755.4	755.7	755.8
125°	816.3	816.7	817.1	817.6	818.1	818.5	819.0
127.5°	880.6	881.4	881.5	881.1	880.6	880.1	879.6
130°	919.5	920.4	920.6	920.1	919.7	919.2	918.8
132.5°	956.2	957.0	957.2	956.6	955.9	955.3	954.7
135°	1011.5	1012.2	1012.2	1011.5	1010.8	1010.1	1009.5
137.5°	1061.4	1062.5	1062.8	1062.3	1061.9	1061.4	1061.0
140°	1092.7	1093.5	1093.8	1093.3	1092.8	1092.4	1091.9
142.5°	1122.2	1123.0	1123.0	1122.4	1121.7	1121.1	1120.5
145°	1163.6	1164.0	1164.3	1164.3	1164.3	1164.3	1164.3
147.5°	1200.9	1201.3	1201.0	1200.0	1199.0	1197.9	1196.8
150°	1223.7	1224.2	1224.0	1223.4	1222.7	1222.0	1221.3
152.5°	1244.4	1245.2	1245.1	1244.0	1242.9	1241.9	1240.9
155°	1272.6	1273.7	1273.6	1272.2	1270.9	1269.6	1268.2
157.5°	1297.1	1298.5	1298.2	1296.5	1294.7	1292.9	1291.2
160°	1311.0	1312.3	1312.2	1310.6	1309.0	1307.4	1305.8
162.5°	1323.7	1325.2	1325.3	1323.9	1322.5	1321.1	1319.7
165°	1340.8	1342.7	1342.7	1341.2	1339.6	1338.0	1336.4
167.5°	1353.8	1355.7	1355.7	1353.8	1352.1	1350.3	1348.5
170°	1361.2	1363.0	1363.0	1361.2	1359.4	1357.6	1355.7
172.5°	1366.1	1367.9	1367.8	1365.8	1363.8	1361.8	1359.9
175°	1371.7	1373.3	1373.2	1371.4	1369.6	1367.8	1366.0
177.5°	1373.8	1375.2	1375.1	1373.2	1371.4	1369.6	1367.8
180°	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0	1371.0

(END OF REPORT)