

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P332407-927

Luminaire Tested: **S123RDIW-S340D1535U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332407-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D1535U927-4F0-1E-UDD-A1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5291.3 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	47	47	47	29	29	29	20
1	91	87	84	80	81	77	74	72	59	57	55	42	40	39	26	25	25	18
2	83	76	71	66	73	68	63	59	52	49	46	37	35	33	23	22	21	15
3	76	67	61	55	67	60	54	50	46	42	39	33	30	28	21	19	18	13
4	70	60	52	47	61	53	47	42	41	36	33	29	27	24	18	17	16	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	21	19	16	14	12	11	8
8	50	39	31	26	44	35	28	24	27	22	19	20	17	14	13	11	10	7
9	47	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	7
10	43	32	25	21	38	29	23	19	22	18	15	17	14	12	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4640	4640	4640	4640
5°	5532	4660	4105	4660
10°	6907	4634	3707	4634
15°	8107	4586	3381	4586
20°	9049	4515	3103	4515
25°	8904	4441	2932	4441
30°	6400	4373	2757	4373
35°	4273	4282	2643	4282
40°	3147	4175	2525	4175
45°	2641	3987	2411	3987
50°	2331	3739	2251	3739
55°	2044	3457	2029	3457
60°	1819	3186	1858	3186
65°	1597	2896	1729	2896
70°	1253	2637	1580	2637
75°	1102	2304	1443	2304
80°	961	1953	1420	1953
85°	778	1581	1507	1581



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.4	0.8
10°-20°	132.5	2.5
20°-30°	208.1	3.9
30°-40°	217.1	4.1
40°-50°	185.8	3.5
50°-60°	141.6	2.7
60°-70°	90.8	1.7
70°-80°	43.7	0.8
80°-90°	16.1	0.3
90°-100°	99.1	1.9
100°-110°	296.5	5.6
110°-120°	504.3	9.5
120°-130°	663.4	12.5
130°-140°	745.6	14.1
140°-150°	732.9	13.9
150°-160°	617.0	11.7
160°-170°	410.7	7.8
170°-180°	143.8	2.7
0°-30°	382.9	7.2
0°-40°	600.1	11.3
0°-60°	927.5	17.5
0°-90°	1078.0	20.4
90°-120°	899.9	17.0
90°-150°	3041.8	57.5
90°-180°	4213.0	79.6
0°-180°	5291.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	512	431	380	431	512	53
15°	728	412	303	412	728	206
25°	750	374	247	374	750	322
35°	325	326	201	326	325	213
45°	174	262	158	262	174	136
55°	109	184	108	184	109	98
65°	63	114	68	114	63	62
75°	26	55	35	55	26	28
85°	6	13	12	13	6	8
90°	36	1	36	1	36	18
95°	93	70	93	70	93	96
105°	284	269	284	269	284	302
115°	509	508	509	508	509	504
125°	735	743	735	743	735	657
135°	963	964	963	964	963	740
145°	1170	1170	1170	1170	1170	730
155°	1337	1339	1337	1339	1337	615
165°	1454	1459	1454	1459	1454	410
175°	1511	1517	1511	1517	1511	144
180°	1521	1521	1521	1521	1521	



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	459.2	459.8	457.9	457.6	455.3	454.8	454.8	451.6	449.7	447.3	445.8
5°	512.0	514.9	513.4	510.2	504.6	503.3	499.8	494.2	488.0	480.2	476.6
7.5°	577.9	581.9	580.4	575.3	569.4	564.7	554.8	545.7	532.8	521.5	511.8
10°	631.9	627.7	624.4	619.4	614.0	605.4	595.0	580.8	564.4	551.4	537.1
12.5°	672.4	671.7	667.5	662.3	654.8	646.6	633.8	616.6	597.5	578.8	562.3
15°	727.5	728.6	725.9	720.6	709.8	695.2	676.0	668.8	641.5	621.2	600.9
17.5°	765.7	765.5	765.1	757.7	746.8	736.4	718.6	699.7	674.9	646.3	619.0
20°	790.0	788.1	788.5	780.1	772.1	760.0	742.7	715.2	694.9	661.9	633.6
22.5°	789.3	788.9	790.4	787.5	781.6	772.5	758.8	735.5	709.6	676.3	644.5
25°	749.7	748.2	756.9	759.3	768.7	770.4	766.3	753.6	729.0	694.7	655.4
27.5°	627.4	626.6	642.7	662.9	688.4	708.3	727.5	736.7	729.0	704.4	665.0
30°	514.9	532.3	540.4	569.6	602.1	640.8	674.8	707.0	715.0	704.3	672.0
32.5°	427.5	442.7	449.5	474.4	504.8	550.2	601.1	646.8	679.1	687.3	667.9
35°	325.2	325.3	340.9	352.0	380.0	426.7	476.2	537.4	598.3	644.5	649.3
37.5°	259.5	260.4	269.8	280.8	301.9	326.5	370.1	421.0	491.4	562.2	603.8
40°	224.0	225.7	232.7	243.6	258.7	277.4	311.3	359.3	418.0	496.9	561.3
42.5°	201.3	204.0	207.6	216.0	225.4	242.9	270.3	307.4	360.8	435.3	509.6
45°	173.5	175.0	177.8	181.6	190.1	202.2	220.7	245.7	289.9	349.9	424.3
47.5°	153.0	152.3	155.2	158.3	164.0	172.3	184.7	204.9	236.5	284.7	347.8
50°	139.2	138.9	141.0	143.4	148.8	154.9	165.0	180.3	205.4	245.3	303.1
52.5°	126.2	126.8	128.3	131.3	135.1	140.1	149.2	160.3	181.8	216.2	264.4
55°	108.9	109.5	111.5	113.1	115.9	120.9	126.6	135.9	150.6	174.6	214.3
57.5°	94.3	94.0	95.9	96.4	99.5	103.5	108.0	115.2	125.9	143.7	170.4
60°	84.5	84.0	85.6	86.9	88.6	91.9	95.6	102.6	111.1	124.2	147.1
62.5°	75.7	75.4	76.6	78.0	79.3	82.3	85.4	90.8	97.5	108.5	126.7
65°	62.7	63.3	63.8	64.4	65.1	67.0	69.9	73.7	78.3	86.0	99.1
67.5°	49.4	49.9	50.1	51.2	52.8	53.9	55.8	59.0	62.3	68.8	76.2
70°	39.8	39.7	39.8	40.4	42.5	44.4	46.9	49.3	51.3	55.9	62.2
72.5°	34.2	33.9	34.4	34.5	35.5	36.0	37.5	39.8	42.5	45.6	50.1
75°	26.5	26.5	26.5	26.5	27.3	27.6	28.2	28.8	29.7	31.2	34.5
77.5°	19.6	19.6	20.0	20.1	20.3	20.5	20.8	21.4	21.7	22.5	23.9
80°	15.5	15.7	15.5	15.7	15.7	16.1	16.2	16.8	17.0	17.9	18.5
82.5°	11.6	11.6	11.6	11.9	11.9	12.2	12.3	12.7	12.7	13.2	13.7
85°	6.3	5.9	6.3	6.1	6.5	6.1	6.3	6.7	6.7	6.8	7.6
87.5°	8.6	8.9	8.4	8.5	8.4	8.3	8.2	7.9	8.0	7.7	7.1
90°	35.8	35.3	34.8	34.2	33.7	33.0	31.8	30.8	29.7	28.7	25.2
92.5°	48.2	48.6	48.9	49.2	49.5	49.3	48.4	47.5	46.7	45.9	43.9
95°	93.2	93.2	93.2	93.2	93.2	92.6	91.6	90.5	89.4	88.4	86.3
97.5°	143.4	143.5	143.5	143.7	143.8	143.2	142.0	140.8	139.6	138.3	136.8
100°	181.6	181.0	180.5	180.0	179.4	178.8	178.0	177.2	176.4	175.6	174.3
102.5°	220.8	220.9	220.9	221.1	221.2	220.9	220.1	219.3	218.5	217.6	215.9
105°	284.3	283.8	283.3	282.7	282.2	281.9	281.9	281.9	281.9	281.9	279.6
107.5°	350.5	350.8	351.1	351.4	351.7	351.5	350.6	349.8	349.0	348.1	347.1
110°	395.4	395.9	396.5	397.0	397.5	397.3	396.2	395.1	394.1	393.0	392.4



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	443.1	443.3	443.4	443.5	443.6	443.0	441.7	440.5	439.2	437.9	437.8
115°	508.9	509.1	509.5	509.7	509.9	509.9	509.7	509.5	509.1	508.9	509.5
117.5°	575.5	576.3	577.0	577.7	578.5	578.9	579.0	579.0	579.1	579.2	579.8
120°	622.3	622.9	623.4	624.0	624.5	624.9	625.2	625.4	625.7	626.0	627.2
122.5°	667.3	668.0	668.8	669.6	670.3	671.0	671.7	672.3	673.0	673.8	674.5
125°	734.7	735.7	736.8	737.8	738.9	740.0	741.0	742.1	743.1	744.3	744.7
127.5°	801.8	803.0	804.2	805.5	806.7	808.0	809.5	811.0	812.5	814.0	814.6
130°	845.7	847.6	849.5	851.4	853.2	854.7	855.7	856.7	857.9	858.9	859.7
132.5°	891.6	893.0	894.5	896.0	897.4	898.7	900.0	901.3	902.5	903.8	904.4
135°	962.8	963.4	963.8	964.4	965.0	965.7	966.8	967.9	968.9	970.0	970.3
137.5°	1025.6	1026.7	1027.7	1028.6	1029.7	1030.8	1031.9	1033.0	1034.1	1035.2	1034.5
140°	1066.8	1068.6	1070.5	1072.3	1074.2	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0
142.5°	1108.8	1110.2	1111.7	1113.1	1114.5	1115.4	1115.6	1115.9	1116.2	1116.4	1115.9
145°	1169.5	1170.5	1171.6	1172.7	1173.7	1174.4	1174.6	1174.9	1175.2	1175.4	1174.6
147.5°	1223.4	1225.0	1226.7	1228.3	1229.9	1230.7	1230.7	1230.7	1230.7	1230.7	1229.9
150°	1257.9	1259.5	1261.1	1262.7	1264.2	1265.0	1265.0	1265.0	1265.0	1265.0	1264.5
152.5°	1291.3	1292.7	1294.1	1295.5	1296.9	1297.4	1296.9	1296.5	1296.1	1295.6	1295.3
155°	1336.7	1338.6	1340.5	1342.3	1344.2	1344.6	1343.5	1342.4	1341.4	1340.3	1340.1
157.5°	1378.1	1379.5	1381.0	1382.5	1384.0	1384.2	1383.1	1382.0	1380.9	1379.7	1379.5
160°	1404.8	1405.9	1406.9	1408.0	1409.1	1408.9	1407.6	1406.3	1404.9	1403.6	1403.6
162.5°	1424.9	1426.6	1428.3	1430.0	1431.7	1431.9	1430.5	1429.2	1427.9	1426.6	1426.3
165°	1453.8	1455.6	1457.5	1459.4	1461.3	1461.3	1459.8	1458.2	1456.6	1455.0	1455.0
167.5°	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4	1478.2
170°	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8	1490.8
172.5°	1500.4	1502.2	1504.1	1505.9	1507.8	1507.9	1506.3	1504.6	1503.0	1501.3	1501.3
175°	1511.2	1513.0	1514.8	1516.7	1518.5	1518.7	1517.1	1515.5	1513.9	1512.4	1512.4
177.5°	1516.9	1518.4	1519.8	1521.3	1522.8	1522.9	1521.6	1520.4	1519.1	1517.8	1517.8
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	445.1	444.7	442.7	440.3	437.2	435.1	433.5	432.6	429.9	426.7	424.5
5°	472.7	467.1	461.2	454.0	447.3	440.5	436.3	431.3	425.2	418.4	413.6
7.5°	502.1	491.2	479.6	467.5	455.6	444.9	435.4	427.3	417.6	407.8	401.0
10°	524.7	508.8	492.4	475.6	460.3	445.9	434.8	424.0	412.3	401.1	392.5
12.5°	545.3	524.3	505.4	484.7	465.2	448.0	432.1	419.2	405.2	393.2	383.6
15°	571.2	549.8	527.0	495.5	469.5	447.7	428.3	411.5	394.6	379.9	370.4
17.5°	595.5	563.3	532.5	506.4	472.5	445.4	421.7	401.6	382.9	367.3	355.7
20°	605.5	574.3	541.0	507.6	474.4	443.9	416.4	394.2	374.9	357.1	346.4
22.5°	611.6	576.3	541.1	505.2	469.9	438.2	411.1	386.7	365.7	348.9	335.6
25°	618.6	576.6	537.8	502.4	466.4	432.1	399.7	373.9	351.3	333.4	319.3
27.5°	623.3	573.8	528.0	488.6	452.1	418.0	388.3	360.9	337.9	318.9	303.9
30°	624.2	571.6	520.5	477.8	440.8	409.3	378.0	351.8	327.4	307.3	293.3
32.5°	625.3	566.1	510.2	465.0	427.0	395.9	367.5	342.5	317.5	297.7	283.4
35°	620.5	563.1	494.8	442.8	404.7	374.6	349.0	325.9	301.4	282.2	267.6
37.5°	599.5	551.1	478.8	417.7	378.0	350.1	329.2	309.1	286.6	265.9	252.2
40°	578.5	539.3	466.4	402.5	361.0	332.4	313.5	297.1	275.4	256.0	241.2
42.5°	547.0	523.2	454.6	386.6	341.8	314.3	298.3	283.0	263.9	244.2	230.3
45°	489.3	492.4	430.4	361.2	315.2	287.6	272.6	261.9	244.9	228.7	214.4
47.5°	416.9	446.2	402.0	334.1	287.2	261.3	248.2	238.8	227.4	211.4	198.4
50°	369.7	411.5	379.3	316.0	269.7	243.8	230.9	223.3	213.3	200.8	188.5
52.5°	326.1	371.1	351.8	295.7	250.6	227.0	214.4	208.1	200.2	188.4	177.2
55°	265.9	311.6	307.1	265.2	222.0	200.8	191.2	184.2	178.9	170.0	161.1
57.5°	215.2	258.3	260.6	231.2	196.9	175.9	167.6	162.3	158.8	152.2	143.9
60°	183.1	222.8	230.5	208.3	178.9	160.4	152.3	148.0	145.3	139.9	133.6
62.5°	156.5	190.3	199.1	183.2	161.6	144.3	137.9	133.9	132.0	127.4	121.8
65°	119.8	147.8	156.3	147.5	136.2	122.4	117.2	113.7	112.0	109.5	105.4
67.5°	90.1	110.5	119.9	113.6	109.5	100.8	97.5	95.6	94.1	92.4	89.0
70°	72.3	87.5	97.0	95.5	92.1	87.5	85.1	83.8	82.3	80.8	77.9
72.5°	58.1	68.6	77.6	78.4	75.7	74.8	72.6	72.1	71.2	69.5	67.8
75°	38.6	45.8	52.0	54.4	55.5	56.5	55.5	55.4	55.2	53.7	52.8
77.5°	25.3	29.2	33.1	37.2	39.0	40.2	40.5	41.2	40.6	39.9	39.5
80°	19.4	20.3	23.1	26.5	29.3	30.4	31.2	31.5	31.4	31.2	30.4
82.5°	14.1	14.8	16.2	18.6	20.9	22.7	23.2	23.1	23.5	23.7	23.1
85°	7.6	7.8	8.2	8.5	9.7	11.8	12.4	12.8	13.1	13.1	12.0
87.5°	6.7	5.9	5.5	4.9	4.8	4.4	4.8	5.0	5.6	5.5	6.1
90°	21.8	18.3	14.9	11.8	9.2	6.5	3.9	1.2	3.9	6.5	9.2
92.5°	41.9	40.0	38.0	36.1	34.3	32.5	30.7	28.9	30.7	32.5	34.3
95°	84.1	82.0	79.9	78.0	76.0	74.2	72.3	70.5	72.3	74.2	76.0
97.5°	135.2	133.7	132.1	130.7	129.4	127.9	126.6	125.2	126.6	127.9	129.4
100°	172.9	171.6	170.3	168.8	167.2	165.6	164.1	162.5	164.1	165.6	167.2
102.5°	214.1	212.4	210.6	209.3	208.3	207.4	206.4	205.5	206.4	207.4	208.3
105°	277.1	274.7	272.4	270.9	270.4	269.8	269.3	268.8	269.3	269.8	270.4
107.5°	346.2	345.2	344.3	343.6	343.3	343.0	342.7	342.4	342.7	343.0	343.3
110°	392.0	391.4	390.9	390.4	389.8	389.3	388.8	388.2	388.8	389.3	389.8



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	437.7	437.6	437.5	437.3	437.0	436.7	436.3	436.0	436.3	436.7	437.0
115°	509.9	510.5	511.0	510.9	510.1	509.3	508.5	507.7	508.5	509.3	510.1
117.5°	580.5	581.2	581.9	581.9	581.5	580.9	580.4	579.9	580.4	580.9	581.5
120°	628.6	629.9	631.3	631.1	629.5	628.0	626.4	624.8	626.4	628.0	629.5
122.5°	675.1	675.8	676.5	676.3	675.1	673.9	672.7	671.6	672.7	673.9	675.1
125°	745.3	745.8	746.3	746.2	745.4	744.7	743.8	743.0	743.8	744.7	745.4
127.5°	815.2	815.7	816.3	815.8	814.0	812.4	810.6	809.0	810.6	812.4	814.0
130°	860.5	861.3	862.1	861.4	859.3	857.1	855.1	852.9	855.1	857.1	859.3
132.5°	905.0	905.5	906.2	905.4	903.2	901.1	899.0	896.9	899.0	901.1	903.2
135°	970.5	970.8	971.1	970.4	968.8	967.2	965.6	964.0	965.6	967.2	968.8
137.5°	1033.8	1033.2	1032.5	1031.4	1030.2	1028.8	1027.5	1026.1	1027.5	1028.8	1030.2
140°	1075.8	1075.5	1075.2	1074.4	1073.1	1071.8	1070.5	1069.1	1070.5	1071.8	1073.1
142.5°	1115.5	1115.0	1114.5	1113.6	1112.3	1111.0	1109.6	1108.3	1109.6	1111.0	1112.3
145°	1173.9	1173.1	1172.3	1171.6	1171.1	1170.5	1170.1	1169.5	1170.1	1170.5	1171.1
147.5°	1229.2	1228.4	1227.6	1226.9	1225.9	1224.9	1223.9	1223.0	1223.9	1224.9	1225.9
150°	1264.0	1263.5	1262.9	1262.4	1261.9	1261.3	1260.8	1260.3	1260.8	1261.3	1261.9
152.5°	1295.0	1294.7	1294.3	1293.8	1293.1	1292.4	1291.6	1290.9	1291.6	1292.4	1293.1
155°	1339.7	1339.5	1339.3	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1	1339.1
157.5°	1379.3	1379.1	1378.9	1379.0	1379.3	1379.6	1379.9	1380.2	1379.9	1379.6	1379.3
160°	1403.6	1403.6	1403.6	1403.9	1404.4	1404.9	1405.5	1406.0	1405.5	1404.9	1404.4
162.5°	1426.2	1425.9	1425.7	1426.0	1426.7	1427.4	1428.2	1428.9	1428.2	1427.4	1426.7
165°	1455.0	1455.0	1455.0	1455.4	1456.2	1457.0	1457.8	1458.6	1457.8	1457.0	1456.2
167.5°	1478.0	1477.7	1477.6	1478.0	1479.0	1480.1	1481.1	1482.3	1481.1	1480.1	1479.0
170°	1490.8	1490.8	1490.8	1491.4	1492.4	1493.5	1494.5	1495.6	1494.5	1493.5	1492.4
172.5°	1501.3	1501.3	1501.3	1501.9	1502.9	1504.0	1505.1	1506.1	1505.1	1504.0	1502.9
175°	1512.4	1512.4	1512.4	1512.8	1513.9	1515.0	1516.1	1517.1	1516.1	1515.0	1513.9
177.5°	1517.8	1517.8	1517.8	1518.2	1519.1	1520.0	1520.8	1521.6	1520.8	1520.0	1519.1
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	423.7	421.8	420.5	417.6	415.7	413.6	411.5	412.8	412.6	412.6	412.6
5°	409.6	405.3	401.4	396.4	393.3	389.4	386.5	386.1	386.8	384.3	382.8
7.5°	395.5	389.7	384.1	378.7	372.8	368.1	365.3	363.8	362.0	360.4	358.8
10°	385.6	378.7	373.4	366.5	360.3	354.7	351.3	348.8	347.5	346.3	343.8
12.5°	375.3	368.7	361.9	354.1	348.2	341.7	339.1	336.4	334.0	332.5	329.2
15°	360.4	351.8	344.6	336.4	329.8	323.5	319.9	314.5	313.8	311.9	308.6
17.5°	345.5	336.1	326.1	320.1	312.7	306.1	300.5	298.7	293.4	291.4	288.5
20°	333.7	325.0	317.4	309.5	298.7	292.6	288.1	285.7	281.5	278.8	277.0
22.5°	323.5	314.7	305.9	296.7	287.7	280.8	277.6	273.9	271.6	267.9	265.9
25°	309.0	299.4	288.8	278.8	272.4	267.3	262.1	258.7	255.4	253.7	250.1
27.5°	292.1	282.0	272.2	264.6	256.7	251.6	246.9	244.0	240.0	237.2	235.1
30°	282.7	270.9	262.4	255.6	245.5	240.7	237.2	233.5	230.5	227.6	225.5
32.5°	272.0	261.2	253.2	244.7	236.9	231.6	227.1	223.9	221.3	218.6	216.5
35°	255.1	246.1	237.7	229.3	223.5	218.2	212.8	210.0	207.6	205.0	203.2
37.5°	239.8	231.3	223.4	215.4	208.3	203.9	199.6	197.5	194.2	192.5	190.7
40°	230.4	222.0	213.6	205.8	198.4	195.1	191.2	188.1	185.1	183.8	181.8
42.5°	220.0	211.7	204.5	196.2	190.1	185.6	182.0	178.6	176.4	174.5	173.4
45°	204.7	197.3	190.3	182.0	176.3	172.4	168.3	165.2	163.2	161.8	159.9
47.5°	189.8	182.4	175.3	168.1	162.6	158.1	154.0	151.9	149.2	147.6	146.2
50°	179.0	172.4	164.9	158.2	152.7	148.2	144.9	142.1	139.7	137.7	136.7
52.5°	169.1	162.1	155.5	149.3	143.5	138.5	135.5	132.5	130.7	128.4	127.3
55°	152.8	146.0	140.5	134.4	128.7	124.4	120.7	118.1	116.3	113.7	112.3
57.5°	137.5	131.3	124.8	119.5	113.6	110.0	106.9	103.5	101.2	99.2	97.7
60°	127.1	120.2	114.4	109.5	104.3	99.7	96.9	94.1	91.7	89.7	88.4
62.5°	116.4	110.3	104.8	99.4	94.7	90.6	87.5	85.2	83.0	81.8	80.4
65°	99.8	95.1	89.5	85.1	80.6	77.7	75.1	73.1	71.6	70.7	69.6
67.5°	84.6	80.0	75.2	70.8	67.8	65.6	63.9	62.2	61.4	60.2	59.5
70°	74.8	69.9	65.7	62.3	59.4	57.8	56.6	55.4	54.7	53.2	52.4
72.5°	64.0	60.5	57.4	54.7	52.4	50.9	49.4	47.8	46.7	45.0	44.3
75°	50.4	47.2	44.8	43.0	41.5	39.5	37.5	35.8	35.3	34.7	34.5
77.5°	37.3	35.3	33.6	32.0	30.2	28.8	28.3	27.9	27.8	27.5	27.5
80°	29.3	27.5	26.2	24.4	23.3	23.3	23.3	22.9	23.1	23.1	23.1
82.5°	21.8	20.1	19.4	18.8	18.5	18.7	18.7	18.8	18.6	18.9	18.8
85°	11.2	11.4	11.8	11.6	11.8	11.8	12.2	12.0	12.2	11.8	12.2
87.5°	6.5	7.5	8.4	9.2	10.1	10.6	10.9	11.2	11.6	11.7	11.9
90°	11.8	14.9	18.3	21.8	25.2	28.7	29.7	30.8	31.8	33.0	33.7
92.5°	36.1	38.0	40.0	41.9	43.9	45.9	46.7	47.5	48.4	49.3	49.5
95°	78.0	79.9	82.0	84.1	86.3	88.4	89.4	90.5	91.6	92.6	93.2
97.5°	130.7	132.1	133.7	135.2	136.8	138.3	139.6	140.8	142.0	143.2	143.8
100°	168.8	170.3	171.6	172.9	174.3	175.6	176.4	177.2	178.0	178.8	179.4
102.5°	209.3	210.6	212.4	214.1	215.9	217.6	218.5	219.3	220.1	220.9	221.2
105°	270.9	272.4	274.7	277.1	279.6	281.9	281.9	281.9	281.9	281.9	282.2
107.5°	343.6	344.3	345.2	346.2	347.1	348.1	349.0	349.8	350.6	351.5	351.7
110°	390.4	390.9	391.4	392.0	392.4	393.0	394.1	395.1	396.2	397.3	397.5



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	437.3	437.5	437.6	437.7	437.8	437.9	439.2	440.5	441.7	443.0	443.6
115°	510.9	511.0	510.5	509.9	509.5	508.9	509.1	509.5	509.7	509.9	509.9
117.5°	581.9	581.9	581.2	580.5	579.8	579.2	579.1	579.0	579.0	578.9	578.5
120°	631.1	631.3	629.9	628.6	627.2	626.0	625.7	625.4	625.2	624.9	624.5
122.5°	676.3	676.5	675.8	675.1	674.5	673.8	673.0	672.3	671.7	671.0	670.3
125°	746.2	746.3	745.8	745.3	744.7	744.3	743.1	742.1	741.0	740.0	738.9
127.5°	815.8	816.3	815.7	815.2	814.6	814.0	812.5	811.0	809.5	808.0	806.7
130°	861.4	862.1	861.3	860.5	859.7	858.9	857.9	856.7	855.7	854.7	853.2
132.5°	905.4	906.2	905.5	905.0	904.4	903.8	902.5	901.3	900.0	898.7	897.4
135°	970.4	971.1	970.8	970.5	970.3	970.0	968.9	967.9	966.8	965.7	965.0
137.5°	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1	1033.0	1031.9	1030.8	1029.7
140°	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0	1075.8	1075.5	1075.2	1074.2
142.5°	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2	1115.9	1115.6	1115.4	1114.5
145°	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2	1174.9	1174.6	1174.4	1173.7
147.5°	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7	1230.7	1230.7	1230.7	1229.9
150°	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0	1265.0	1265.0	1265.0	1264.2
152.5°	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1	1296.5	1296.9	1297.4	1296.9
155°	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4	1342.4	1343.5	1344.6	1344.2
157.5°	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9	1382.0	1383.1	1384.2	1384.0
160°	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9	1406.3	1407.6	1408.9	1409.1
162.5°	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9	1429.2	1430.5	1431.9	1431.7
165°	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6	1458.2	1459.8	1461.3	1461.3
167.5°	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9
170°	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3
172.5°	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0	1504.6	1506.3	1507.9	1507.8
175°	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9	1515.5	1517.1	1518.7	1518.5
177.5°	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1	1520.4	1521.6	1522.9	1522.8
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	410.7	410.6	410.7	410.2	410.7	410.6	410.7	412.6	412.6	412.6	412.8
5°	382.2	382.1	381.5	379.9	381.5	382.1	382.2	382.8	384.3	386.8	386.1
7.5°	357.3	357.0	355.5	355.5	355.5	357.0	357.3	358.8	360.4	362.0	363.8
10°	342.5	342.7	340.5	339.2	340.5	342.7	342.5	343.8	346.3	347.5	348.8
12.5°	328.2	327.4	325.6	324.2	325.6	327.4	328.2	329.2	332.5	334.0	336.4
15°	309.3	307.4	303.1	303.4	303.1	307.4	309.3	308.6	311.9	313.8	314.5
17.5°	287.1	285.7	285.7	283.0	285.7	285.7	287.1	288.5	291.4	293.4	298.7
20°	274.1	273.1	273.5	270.9	273.5	273.1	274.1	277.0	278.8	281.5	285.7
22.5°	263.9	262.9	261.4	260.6	261.4	262.9	263.9	265.9	267.9	271.6	273.9
25°	249.0	247.5	246.1	246.9	246.1	247.5	249.0	250.1	253.7	255.4	258.7
27.5°	234.1	233.0	231.5	231.3	231.5	233.0	234.1	235.1	237.2	240.0	244.0
30°	224.6	223.5	222.8	221.8	222.8	223.5	224.6	225.5	227.6	230.5	233.5
32.5°	215.0	214.8	213.5	213.3	213.5	214.8	215.0	216.5	218.6	221.3	223.9
35°	202.5	201.4	201.0	201.1	201.0	201.4	202.5	203.2	205.0	207.6	210.0
37.5°	190.5	189.1	188.4	187.7	188.4	189.1	190.5	190.7	192.5	194.2	197.5
40°	182.0	180.5	180.1	179.7	180.1	180.5	182.0	181.8	183.8	185.1	188.1
42.5°	172.4	171.8	171.6	170.9	171.6	171.8	172.4	173.4	174.5	176.4	178.6
45°	159.3	159.1	158.0	158.4	158.0	159.1	159.3	159.9	161.8	163.2	165.2
47.5°	145.4	144.7	143.9	144.4	143.9	144.7	145.4	146.2	147.6	149.2	151.9
50°	136.0	135.6	134.0	134.4	134.0	135.6	136.0	136.7	137.7	139.7	142.1
52.5°	126.6	125.2	124.5	124.3	124.5	125.2	126.6	127.3	128.4	130.7	132.5
55°	110.9	109.2	108.5	108.1	108.5	109.2	110.9	112.3	113.7	116.3	118.1
57.5°	95.5	95.1	94.5	94.9	94.5	95.1	95.5	97.7	99.2	101.2	103.5
60°	86.6	86.6	86.6	86.3	86.6	86.6	86.6	88.4	89.7	91.7	94.1
62.5°	79.6	79.1	79.1	79.3	79.1	79.1	79.6	80.4	81.8	83.0	85.2
65°	69.0	68.8	68.1	67.9	68.1	68.8	69.0	69.6	70.7	71.6	73.1
67.5°	59.0	58.4	58.1	57.9	58.1	58.4	59.0	59.5	60.2	61.4	62.2
70°	51.5	51.1	50.0	50.2	50.0	51.1	51.5	52.4	53.2	54.7	55.4
72.5°	43.4	43.0	42.8	42.5	42.8	43.0	43.4	44.3	45.0	46.7	47.8
75°	34.3	34.1	34.0	34.7	34.0	34.1	34.3	34.5	34.7	35.3	35.8
77.5°	27.5	27.5	27.6	27.3	27.6	27.5	27.5	27.5	27.5	27.8	27.9
80°	23.1	23.1	22.9	22.9	22.9	23.1	23.1	23.1	23.1	23.1	22.9
82.5°	18.5	18.6	18.8	18.5	18.8	18.6	18.5	18.8	18.9	18.6	18.8
85°	12.2	12.0	12.4	12.2	12.4	12.0	12.2	12.2	11.8	12.2	12.0
87.5°	12.3	12.1	12.2	12.5	12.2	12.1	12.3	11.9	11.7	11.6	11.2
90°	34.2	34.8	35.3	35.8	35.3	34.8	34.2	33.7	33.0	31.8	30.8
92.5°	49.2	48.9	48.6	48.2	48.6	48.9	49.2	49.5	49.3	48.4	47.5
95°	93.2	93.2	93.2	93.2	93.2	93.2	93.2	93.2	92.6	91.6	90.5
97.5°	143.7	143.5	143.5	143.4	143.5	143.5	143.7	143.8	143.2	142.0	140.8
100°	180.0	180.5	181.0	181.6	181.0	180.5	180.0	179.4	178.8	178.0	177.2
102.5°	221.1	220.9	220.9	220.8	220.9	220.9	221.1	221.2	220.9	220.1	219.3
105°	282.7	283.3	283.8	284.3	283.8	283.3	282.7	282.2	281.9	281.9	281.9
107.5°	351.4	351.1	350.8	350.5	350.8	351.1	351.4	351.7	351.5	350.6	349.8
110°	397.0	396.5	395.9	395.4	395.9	396.5	397.0	397.5	397.3	396.2	395.1



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	443.5	443.4	443.3	443.1	443.3	443.4	443.5	443.6	443.0	441.7	440.5
115°	509.7	509.5	509.1	508.9	509.1	509.5	509.7	509.9	509.9	509.7	509.5
117.5°	577.7	577.0	576.3	575.5	576.3	577.0	577.7	578.5	578.9	579.0	579.0
120°	624.0	623.4	622.9	622.3	622.9	623.4	624.0	624.5	624.9	625.2	625.4
122.5°	669.6	668.8	668.0	667.3	668.0	668.8	669.6	670.3	671.0	671.7	672.3
125°	737.8	736.8	735.7	734.7	735.7	736.8	737.8	738.9	740.0	741.0	742.1
127.5°	805.5	804.2	803.0	801.8	803.0	804.2	805.5	806.7	808.0	809.5	811.0
130°	851.4	849.5	847.6	845.7	847.6	849.5	851.4	853.2	854.7	855.7	856.7
132.5°	896.0	894.5	893.0	891.6	893.0	894.5	896.0	897.4	898.7	900.0	901.3
135°	964.4	963.8	963.4	962.8	963.4	963.8	964.4	965.0	965.7	966.8	967.9
137.5°	1028.6	1027.7	1026.7	1025.6	1026.7	1027.7	1028.6	1029.7	1030.8	1031.9	1033.0
140°	1072.3	1070.5	1068.6	1066.8	1068.6	1070.5	1072.3	1074.2	1075.2	1075.5	1075.8
142.5°	1113.1	1111.7	1110.2	1108.8	1110.2	1111.7	1113.1	1114.5	1115.4	1115.6	1115.9
145°	1172.7	1171.6	1170.5	1169.5	1170.5	1171.6	1172.7	1173.7	1174.4	1174.6	1174.9
147.5°	1228.3	1226.7	1225.0	1223.4	1225.0	1226.7	1228.3	1229.9	1230.7	1230.7	1230.7
150°	1262.7	1261.1	1259.5	1257.9	1259.5	1261.1	1262.7	1264.2	1265.0	1265.0	1265.0
152.5°	1295.5	1294.1	1292.7	1291.3	1292.7	1294.1	1295.5	1296.9	1297.4	1296.9	1296.5
155°	1342.3	1340.5	1338.6	1336.7	1338.6	1340.5	1342.3	1344.2	1344.6	1343.5	1342.4
157.5°	1382.5	1381.0	1379.5	1378.1	1379.5	1381.0	1382.5	1384.0	1384.2	1383.1	1382.0
160°	1408.0	1406.9	1405.9	1404.8	1405.9	1406.9	1408.0	1409.1	1408.9	1407.6	1406.3
162.5°	1430.0	1428.3	1426.6	1424.9	1426.6	1428.3	1430.0	1431.7	1431.9	1430.5	1429.2
165°	1459.4	1457.5	1455.6	1453.8	1455.6	1457.5	1459.4	1461.3	1461.3	1459.8	1458.2
167.5°	1483.4	1481.7	1480.0	1478.4	1480.0	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7
170°	1496.4	1494.5	1492.7	1490.8	1492.7	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5
172.5°	1505.9	1504.1	1502.2	1500.4	1502.2	1504.1	1505.9	1507.8	1507.9	1506.3	1504.6
175°	1516.7	1514.8	1513.0	1511.2	1513.0	1514.8	1516.7	1518.5	1518.7	1517.1	1515.5
177.5°	1521.3	1519.8	1518.4	1516.9	1518.4	1519.8	1521.3	1522.8	1522.9	1521.6	1520.4
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	411.5	413.6	415.7	417.6	420.5	421.8	423.7	424.5	426.7	429.9	432.6
5°	386.5	389.4	393.3	396.4	401.4	405.3	409.6	413.6	418.4	425.2	431.3
7.5°	365.3	368.1	372.8	378.7	384.1	389.7	395.5	401.0	407.8	417.6	427.3
10°	351.3	354.7	360.3	366.5	373.4	378.7	385.6	392.5	401.1	412.3	424.0
12.5°	339.1	341.7	348.2	354.1	361.9	368.7	375.3	383.6	393.2	405.2	419.2
15°	319.9	323.5	329.8	336.4	344.6	351.8	360.4	370.4	379.9	394.6	411.5
17.5°	300.5	306.1	312.7	320.1	326.1	336.1	345.5	355.7	367.3	382.9	401.6
20°	288.1	292.6	298.7	309.5	317.4	325.0	333.7	346.4	357.1	374.9	394.2
22.5°	277.6	280.8	287.7	296.7	305.9	314.7	323.5	335.6	348.9	365.7	386.7
25°	262.1	267.3	272.4	278.8	288.8	299.4	309.0	319.3	333.4	351.3	373.9
27.5°	246.9	251.6	256.7	264.6	272.2	282.0	292.1	303.9	318.9	337.9	360.9
30°	237.2	240.7	245.5	255.6	262.4	270.9	282.7	293.3	307.3	327.4	351.8
32.5°	227.1	231.6	236.9	244.7	253.2	261.2	272.0	283.4	297.7	317.5	342.5
35°	212.8	218.2	223.5	229.3	237.7	246.1	255.1	267.6	282.2	301.4	325.9
37.5°	199.6	203.9	208.3	215.4	223.4	231.3	239.8	252.2	265.9	286.6	309.1
40°	191.2	195.1	198.4	205.8	213.6	222.0	230.4	241.2	256.0	275.4	297.1
42.5°	182.0	185.6	190.1	196.2	204.5	211.7	220.0	230.3	244.2	263.9	283.0
45°	168.3	172.4	176.3	182.0	190.3	197.3	204.7	214.4	228.7	244.9	261.9
47.5°	154.0	158.1	162.6	168.1	175.3	182.4	189.8	198.4	211.4	227.4	238.8
50°	144.9	148.2	152.7	158.2	164.9	172.4	179.0	188.5	200.8	213.3	223.3
52.5°	135.5	138.5	143.5	149.3	155.5	162.1	169.1	177.2	188.4	200.2	208.1
55°	120.7	124.4	128.7	134.4	140.5	146.0	152.8	161.1	170.0	178.9	184.2
57.5°	106.9	110.0	113.6	119.5	124.8	131.3	137.5	143.9	152.2	158.8	162.3
60°	96.9	99.7	104.3	109.5	114.4	120.2	127.1	133.6	139.9	145.3	148.0
62.5°	87.5	90.6	94.7	99.4	104.8	110.3	116.4	121.8	127.4	132.0	133.9
65°	75.1	77.7	80.6	85.1	89.5	95.1	99.8	105.4	109.5	112.0	113.7
67.5°	63.9	65.6	67.8	70.8	75.2	80.0	84.6	89.0	92.4	94.1	95.6
70°	56.6	57.8	59.4	62.3	65.7	69.9	74.8	77.9	80.8	82.3	83.8
72.5°	49.4	50.9	52.4	54.7	57.4	60.5	64.0	67.8	69.5	71.2	72.1
75°	37.5	39.5	41.5	43.0	44.8	47.2	50.4	52.8	53.7	55.2	55.4
77.5°	28.3	28.8	30.2	32.0	33.6	35.3	37.3	39.5	39.9	40.6	41.2
80°	23.3	23.3	23.3	24.4	26.2	27.5	29.3	30.4	31.2	31.4	31.5
82.5°	18.7	18.7	18.5	18.8	19.4	20.1	21.8	23.1	23.7	23.5	23.1
85°	12.2	11.8	11.8	11.6	11.8	11.4	11.2	12.0	13.1	13.1	12.8
87.5°	10.9	10.6	10.1	9.2	8.4	7.5	6.5	6.1	5.5	5.6	5.0
90°	29.7	28.7	25.2	21.8	18.3	14.9	11.8	9.2	6.5	3.9	1.2
92.5°	46.7	45.9	43.9	41.9	40.0	38.0	36.1	34.3	32.5	30.7	28.9
95°	89.4	88.4	86.3	84.1	82.0	79.9	78.0	76.0	74.2	72.3	70.5
97.5°	139.6	138.3	136.8	135.2	133.7	132.1	130.7	129.4	127.9	126.6	125.2
100°	176.4	175.6	174.3	172.9	171.6	170.3	168.8	167.2	165.6	164.1	162.5
102.5°	218.5	217.6	215.9	214.1	212.4	210.6	209.3	208.3	207.4	206.4	205.5
105°	281.9	281.9	279.6	277.1	274.7	272.4	270.9	270.4	269.8	269.3	268.8
107.5°	349.0	348.1	347.1	346.2	345.2	344.3	343.6	343.3	343.0	342.7	342.4
110°	394.1	393.0	392.4	392.0	391.4	390.9	390.4	389.8	389.3	388.8	388.2



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	439.2	437.9	437.8	437.7	437.6	437.5	437.3	437.0	436.7	436.3	436.0
115°	509.1	508.9	509.5	509.9	510.5	511.0	510.9	510.1	509.3	508.5	507.7
117.5°	579.1	579.2	579.8	580.5	581.2	581.9	581.9	581.5	580.9	580.4	579.9
120°	625.7	626.0	627.2	628.6	629.9	631.3	631.1	629.5	628.0	626.4	624.8
122.5°	673.0	673.8	674.5	675.1	675.8	676.5	676.3	675.1	673.9	672.7	671.6
125°	743.1	744.3	744.7	745.3	745.8	746.3	746.2	745.4	744.7	743.8	743.0
127.5°	812.5	814.0	814.6	815.2	815.7	816.3	815.8	814.0	812.4	810.6	809.0
130°	857.9	858.9	859.7	860.5	861.3	862.1	861.4	859.3	857.1	855.1	852.9
132.5°	902.5	903.8	904.4	905.0	905.5	906.2	905.4	903.2	901.1	899.0	896.9
135°	968.9	970.0	970.3	970.5	970.8	971.1	970.4	968.8	967.2	965.6	964.0
137.5°	1034.1	1035.2	1034.5	1033.8	1033.2	1032.5	1031.4	1030.2	1028.8	1027.5	1026.1
140°	1076.0	1076.3	1076.0	1075.8	1075.5	1075.2	1074.4	1073.1	1071.8	1070.5	1069.1
142.5°	1116.2	1116.4	1115.9	1115.5	1115.0	1114.5	1113.6	1112.3	1111.0	1109.6	1108.3
145°	1175.2	1175.4	1174.6	1173.9	1173.1	1172.3	1171.6	1171.1	1170.5	1170.1	1169.5
147.5°	1230.7	1230.7	1229.9	1229.2	1228.4	1227.6	1226.9	1225.9	1224.9	1223.9	1223.0
150°	1265.0	1265.0	1264.5	1264.0	1263.5	1262.9	1262.4	1261.9	1261.3	1260.8	1260.3
152.5°	1296.1	1295.6	1295.3	1295.0	1294.7	1294.3	1293.8	1293.1	1292.4	1291.6	1290.9
155°	1341.4	1340.3	1340.1	1339.7	1339.5	1339.3	1339.1	1339.1	1339.1	1339.1	1339.1
157.5°	1380.9	1379.7	1379.5	1379.3	1379.1	1378.9	1379.0	1379.3	1379.6	1379.9	1380.2
160°	1404.9	1403.6	1403.6	1403.6	1403.6	1403.6	1403.9	1404.4	1404.9	1405.5	1406.0
162.5°	1427.9	1426.6	1426.3	1426.2	1425.9	1425.7	1426.0	1426.7	1427.4	1428.2	1428.9
165°	1456.6	1455.0	1455.0	1455.0	1455.0	1455.0	1455.4	1456.2	1457.0	1457.8	1458.6
167.5°	1480.0	1478.4	1478.2	1478.0	1477.7	1477.6	1478.0	1479.0	1480.1	1481.1	1482.3
170°	1492.7	1490.8	1490.8	1490.8	1490.8	1490.8	1491.4	1492.4	1493.5	1494.5	1495.6
172.5°	1503.0	1501.3	1501.3	1501.3	1501.3	1501.3	1501.9	1502.9	1504.0	1505.1	1506.1
175°	1513.9	1512.4	1512.4	1512.4	1512.4	1512.4	1512.8	1513.9	1515.0	1516.1	1517.1
177.5°	1519.1	1517.8	1517.8	1517.8	1517.8	1517.8	1518.2	1519.1	1520.0	1520.8	1521.6
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	433.5	435.1	437.2	440.3	442.7	444.7	445.1	445.8	447.3	449.7	451.6
5°	436.3	440.5	447.3	454.0	461.2	467.1	472.7	476.6	480.2	488.0	494.2
7.5°	435.4	444.9	455.6	467.5	479.6	491.2	502.1	511.8	521.5	532.8	545.7
10°	434.8	445.9	460.3	475.6	492.4	508.8	524.7	537.1	551.4	564.4	580.8
12.5°	432.1	448.0	465.2	484.7	505.4	524.3	545.3	562.3	578.8	597.5	616.6
15°	428.3	447.7	469.5	495.5	527.0	549.8	571.2	600.9	621.2	641.5	668.8
17.5°	421.7	445.4	472.5	506.4	532.5	563.3	595.5	619.0	646.3	674.9	699.7
20°	416.4	443.9	474.4	507.6	541.0	574.3	605.5	633.6	661.9	694.9	715.2
22.5°	411.1	438.2	469.9	505.2	541.1	576.3	611.6	644.5	676.3	709.6	735.5
25°	399.7	432.1	466.4	502.4	537.8	576.6	618.6	655.4	694.7	729.0	753.6
27.5°	388.3	418.0	452.1	488.6	528.0	573.8	623.3	665.0	704.4	729.0	736.7
30°	378.0	409.3	440.8	477.8	520.5	571.6	624.2	672.0	704.3	715.0	707.0
32.5°	367.5	395.9	427.0	465.0	510.2	566.1	625.3	667.9	687.3	679.1	646.8
35°	349.0	374.6	404.7	442.8	494.8	563.1	620.5	649.3	644.5	598.3	537.4
37.5°	329.2	350.1	378.0	417.7	478.8	551.1	599.5	603.8	562.2	491.4	421.0
40°	313.5	332.4	361.0	402.5	466.4	539.3	578.5	561.3	496.9	418.0	359.3
42.5°	298.3	314.3	341.8	386.6	454.6	523.2	547.0	509.6	435.3	360.8	307.4
45°	272.6	287.6	315.2	361.2	430.4	492.4	489.3	424.3	349.9	289.9	245.7
47.5°	248.2	261.3	287.2	334.1	402.0	446.2	416.9	347.8	284.7	236.5	204.9
50°	230.9	243.8	269.7	316.0	379.3	411.5	369.7	303.1	245.3	205.4	180.3
52.5°	214.4	227.0	250.6	295.7	351.8	371.1	326.1	264.4	216.2	181.8	160.3
55°	191.2	200.8	222.0	265.2	307.1	311.6	265.9	214.3	174.6	150.6	135.9
57.5°	167.6	175.9	196.9	231.2	260.6	258.3	215.2	170.4	143.7	125.9	115.2
60°	152.3	160.4	178.9	208.3	230.5	222.8	183.1	147.1	124.2	111.1	102.6
62.5°	137.9	144.3	161.6	183.2	199.1	190.3	156.5	126.7	108.5	97.5	90.8
65°	117.2	122.4	136.2	147.5	156.3	147.8	119.8	99.1	86.0	78.3	73.7
67.5°	97.5	100.8	109.5	113.6	119.9	110.5	90.1	76.2	68.8	62.3	59.0
70°	85.1	87.5	92.1	95.5	97.0	87.5	72.3	62.2	55.9	51.3	49.3
72.5°	72.6	74.8	75.7	78.4	77.6	68.6	58.1	50.1	45.6	42.5	39.8
75°	55.5	56.5	55.5	54.4	52.0	45.8	38.6	34.5	31.2	29.7	28.8
77.5°	40.5	40.2	39.0	37.2	33.1	29.2	25.3	23.9	22.5	21.7	21.4
80°	31.2	30.4	29.3	26.5	23.1	20.3	19.4	18.5	17.9	17.0	16.8
82.5°	23.2	22.7	20.9	18.6	16.2	14.8	14.1	13.7	13.2	12.7	12.7
85°	12.4	11.8	9.7	8.5	8.2	7.8	7.6	7.6	6.8	6.7	6.7
87.5°	4.8	4.4	4.8	4.9	5.5	5.9	6.7	7.1	7.7	8.0	7.9
90°	3.9	6.5	9.2	11.8	14.9	18.3	21.8	25.2	28.7	29.7	30.8
92.5°	30.7	32.5	34.3	36.1	38.0	40.0	41.9	43.9	45.9	46.7	47.5
95°	72.3	74.2	76.0	78.0	79.9	82.0	84.1	86.3	88.4	89.4	90.5
97.5°	126.6	127.9	129.4	130.7	132.1	133.7	135.2	136.8	138.3	139.6	140.8
100°	164.1	165.6	167.2	168.8	170.3	171.6	172.9	174.3	175.6	176.4	177.2
102.5°	206.4	207.4	208.3	209.3	210.6	212.4	214.1	215.9	217.6	218.5	219.3
105°	269.3	269.8	270.4	270.9	272.4	274.7	277.1	279.6	281.9	281.9	281.9
107.5°	342.7	343.0	343.3	343.6	344.3	345.2	346.2	347.1	348.1	349.0	349.8
110°	388.8	389.3	389.8	390.4	390.9	391.4	392.0	392.4	393.0	394.1	395.1



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	436.3	436.7	437.0	437.3	437.5	437.6	437.7	437.8	437.9	439.2	440.5
115°	508.5	509.3	510.1	510.9	511.0	510.5	509.9	509.5	508.9	509.1	509.5
117.5°	580.4	580.9	581.5	581.9	581.9	581.2	580.5	579.8	579.2	579.1	579.0
120°	626.4	628.0	629.5	631.1	631.3	629.9	628.6	627.2	626.0	625.7	625.4
122.5°	672.7	673.9	675.1	676.3	676.5	675.8	675.1	674.5	673.8	673.0	672.3
125°	743.8	744.7	745.4	746.2	746.3	745.8	745.3	744.7	744.3	743.1	742.1
127.5°	810.6	812.4	814.0	815.8	816.3	815.7	815.2	814.6	814.0	812.5	811.0
130°	855.1	857.1	859.3	861.4	862.1	861.3	860.5	859.7	858.9	857.9	856.7
132.5°	899.0	901.1	903.2	905.4	906.2	905.5	905.0	904.4	903.8	902.5	901.3
135°	965.6	967.2	968.8	970.4	971.1	970.8	970.5	970.3	970.0	968.9	967.9
137.5°	1027.5	1028.8	1030.2	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1	1033.0
140°	1070.5	1071.8	1073.1	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0	1075.8
142.5°	1109.6	1111.0	1112.3	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2	1115.9
145°	1170.1	1170.5	1171.1	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2	1174.9
147.5°	1223.9	1224.9	1225.9	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7	1230.7
150°	1260.8	1261.3	1261.9	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0	1265.0
152.5°	1291.6	1292.4	1293.1	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1	1296.5
155°	1339.1	1339.1	1339.1	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4	1342.4
157.5°	1379.9	1379.6	1379.3	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9	1382.0
160°	1405.5	1404.9	1404.4	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9	1406.3
162.5°	1428.2	1427.4	1426.7	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9	1429.2
165°	1457.8	1457.0	1456.2	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6	1458.2
167.5°	1481.1	1480.1	1479.0	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0	1481.7
170°	1494.5	1493.5	1492.4	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7	1494.5
172.5°	1505.1	1504.0	1502.9	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0	1504.6
175°	1516.1	1515.0	1513.9	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9	1515.5
177.5°	1520.8	1520.0	1519.1	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1	1520.4
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	454.8	454.8	455.3	457.6	457.9	459.8	459.2
5°	499.8	503.3	504.6	510.2	513.4	514.9	512.0
7.5°	554.8	564.7	569.4	575.3	580.4	581.9	577.9
10°	595.0	605.4	614.0	619.4	624.4	627.7	631.9
12.5°	633.8	646.6	654.8	662.3	667.5	671.7	672.4
15°	676.0	695.2	709.8	720.6	725.9	728.6	727.5
17.5°	718.6	736.4	746.8	757.7	765.1	765.5	765.7
20°	742.7	760.0	772.1	780.1	788.5	788.1	790.0
22.5°	758.8	772.5	781.6	787.5	790.4	788.9	789.3
25°	766.3	770.4	768.7	759.3	756.9	748.2	749.7
27.5°	727.5	708.3	688.4	662.9	642.7	626.6	627.4
30°	674.8	640.8	602.1	569.6	540.4	532.3	514.9
32.5°	601.1	550.2	504.8	474.4	449.5	442.7	427.5
35°	476.2	426.7	380.0	352.0	340.9	325.3	325.2
37.5°	370.1	326.5	301.9	280.8	269.8	260.4	259.5
40°	311.3	277.4	258.7	243.6	232.7	225.7	224.0
42.5°	270.3	242.9	225.4	216.0	207.6	204.0	201.3
45°	220.7	202.2	190.1	181.6	177.8	175.0	173.5
47.5°	184.7	172.3	164.0	158.3	155.2	152.3	153.0
50°	165.0	154.9	148.8	143.4	141.0	138.9	139.2
52.5°	149.2	140.1	135.1	131.3	128.3	126.8	126.2
55°	126.6	120.9	115.9	113.1	111.5	109.5	108.9
57.5°	108.0	103.5	99.5	96.4	95.9	94.0	94.3
60°	95.6	91.9	88.6	86.9	85.6	84.0	84.5
62.5°	85.4	82.3	79.3	78.0	76.6	75.4	75.7
65°	69.9	67.0	65.1	64.4	63.8	63.3	62.7
67.5°	55.8	53.9	52.8	51.2	50.1	49.9	49.4
70°	46.9	44.4	42.5	40.4	39.8	39.7	39.8
72.5°	37.5	36.0	35.5	34.5	34.4	33.9	34.2
75°	28.2	27.6	27.3	26.5	26.5	26.5	26.5
77.5°	20.8	20.5	20.3	20.1	20.0	19.6	19.6
80°	16.2	16.1	15.7	15.7	15.5	15.7	15.5
82.5°	12.3	12.2	11.9	11.9	11.6	11.6	11.6
85°	6.3	6.1	6.5	6.1	6.3	5.9	6.3
87.5°	8.2	8.3	8.4	8.5	8.4	8.9	8.6
90°	31.8	33.0	33.7	34.2	34.8	35.3	35.8
92.5°	48.4	49.3	49.5	49.2	48.9	48.6	48.2
95°	91.6	92.6	93.2	93.2	93.2	93.2	93.2
97.5°	142.0	143.2	143.8	143.7	143.5	143.5	143.4
100°	178.0	178.8	179.4	180.0	180.5	181.0	181.6
102.5°	220.1	220.9	221.2	221.1	220.9	220.9	220.8
105°	281.9	281.9	282.2	282.7	283.3	283.8	284.3
107.5°	350.6	351.5	351.7	351.4	351.1	350.8	350.5
110°	396.2	397.3	397.5	397.0	396.5	395.9	395.4



TEST NUMBER: P332407-927

CATALOG NUMBER: S123RDIW-S340D1535U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	441.7	443.0	443.6	443.5	443.4	443.3	443.1
115°	509.7	509.9	509.9	509.7	509.5	509.1	508.9
117.5°	579.0	578.9	578.5	577.7	577.0	576.3	575.5
120°	625.2	624.9	624.5	624.0	623.4	622.9	622.3
122.5°	671.7	671.0	670.3	669.6	668.8	668.0	667.3
125°	741.0	740.0	738.9	737.8	736.8	735.7	734.7
127.5°	809.5	808.0	806.7	805.5	804.2	803.0	801.8
130°	855.7	854.7	853.2	851.4	849.5	847.6	845.7
132.5°	900.0	898.7	897.4	896.0	894.5	893.0	891.6
135°	966.8	965.7	965.0	964.4	963.8	963.4	962.8
137.5°	1031.9	1030.8	1029.7	1028.6	1027.7	1026.7	1025.6
140°	1075.5	1075.2	1074.2	1072.3	1070.5	1068.6	1066.8
142.5°	1115.6	1115.4	1114.5	1113.1	1111.7	1110.2	1108.8
145°	1174.6	1174.4	1173.7	1172.7	1171.6	1170.5	1169.5
147.5°	1230.7	1230.7	1229.9	1228.3	1226.7	1225.0	1223.4
150°	1265.0	1265.0	1264.2	1262.7	1261.1	1259.5	1257.9
152.5°	1296.9	1297.4	1296.9	1295.5	1294.1	1292.7	1291.3
155°	1343.5	1344.6	1344.2	1342.3	1340.5	1338.6	1336.7
157.5°	1383.1	1384.2	1384.0	1382.5	1381.0	1379.5	1378.1
160°	1407.6	1408.9	1409.1	1408.0	1406.9	1405.9	1404.8
162.5°	1430.5	1431.9	1431.7	1430.0	1428.3	1426.6	1424.9
165°	1459.8	1461.3	1461.3	1459.4	1457.5	1455.6	1453.8
167.5°	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4
170°	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8
172.5°	1506.3	1507.9	1507.8	1505.9	1504.1	1502.2	1500.4
175°	1517.1	1518.7	1518.5	1516.7	1514.8	1513.0	1511.2
177.5°	1521.6	1522.9	1522.8	1521.3	1519.8	1518.4	1516.9
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7

(END OF REPORT)