

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332390-927

Luminaire Tested: **S123RDIW-S340D460U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332390-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D460U927-4F0-1E-UDD-A
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 460 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2535.7 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	97	92	89	86	88	85	82	79	70	68	66	57	55	54	44	43	42	37
2	88	81	76	71	81	75	70	65	62	58	55	50	48	46	39	38	36	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32	27
4	74	64	56	51	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	26	24	21
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	26	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	17	15
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	23	20	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4640	4640	4640	4640
5°	5532	4660	4105	4660
10°	6907	4634	3707	4634
15°	8107	4586	3381	4586
20°	9049	4515	3103	4515
25°	8904	4441	2932	4441
30°	6400	4373	2757	4373
35°	4273	4282	2643	4282
40°	3147	4175	2525	4175
45°	2641	3987	2411	3987
50°	2331	3739	2251	3739
55°	2044	3457	2029	3457
60°	1819	3186	1858	3186
65°	1597	2896	1729	2896
70°	1253	2637	1580	2637
75°	1102	2304	1443	2304
80°	961	1953	1420	1953
85°	778	1581	1507	1581



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.4	1.7
10°-20°	132.5	5.2
20°-30°	208.1	8.2
30°-40°	217.1	8.6
40°-50°	185.8	7.3
50°-60°	141.6	5.6
60°-70°	90.8	3.6
70°-80°	43.7	1.7
80°-90°	12.9	0.5
90°-100°	17.4	0.7
100°-110°	83.0	3.3
110°-120°	199.4	7.9
120°-130°	253.9	10.0
130°-140°	271.3	10.7
140°-150°	253.7	10.0
150°-160°	204.6	8.1
160°-170°	132.1	5.2
170°-180°	45.5	1.8
0°-30°	382.9	15.1
0°-40°	600.1	23.7
0°-60°	927.5	36.6
0°-90°	1074.8	42.4
90°-120°	299.8	11.8
90°-150°	1078.7	42.5
90°-180°	1461.0	57.6
0°-180°	2535.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	512	431	380	431	512	53
15°	728	412	303	412	728	206
25°	750	374	247	374	750	322
35°	325	326	201	326	325	213
45°	174	262	158	262	174	136
55°	109	184	108	184	109	98
65°	63	114	68	114	63	62
75°	26	55	35	55	26	28
85°	6	13	12	13	6	7
90°	11	0	11	0	11	5
95°	14	22	14	22	14	11
105°	16	106	16	106	16	36
115°	209	199	209	199	209	193
125°	286	280	286	280	286	256
135°	353	349	353	349	353	272
145°	407	403	407	403	407	254
155°	443	444	443	444	443	204
165°	467	468	467	468	467	132
175°	477	479	477	479	477	45
180°	479	479	479	479	479	



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	459.2	459.8	457.9	457.6	455.3	454.8	454.8	451.6	449.7	447.3	445.8
5°	512.0	514.9	513.4	510.2	504.6	503.3	499.8	494.2	488.0	480.2	476.6
7.5°	577.9	581.9	580.4	575.3	569.4	564.7	554.8	545.7	532.8	521.5	511.8
10°	631.9	627.7	624.4	619.4	614.0	605.4	595.0	580.8	564.4	551.4	537.1
12.5°	672.4	671.7	667.5	662.3	654.8	646.6	633.8	616.6	597.5	578.8	562.3
15°	727.5	728.6	725.9	720.6	709.8	695.2	676.0	668.8	641.5	621.2	600.9
17.5°	765.7	765.5	765.1	757.7	746.8	736.4	718.6	699.7	674.9	646.3	619.0
20°	790.0	788.1	788.5	780.1	772.1	760.0	742.7	715.2	694.9	661.9	633.6
22.5°	789.3	788.9	790.4	787.5	781.6	772.5	758.8	735.5	709.6	676.3	644.5
25°	749.7	748.2	756.9	759.3	768.7	770.4	766.3	753.6	729.0	694.7	655.4
27.5°	627.4	626.6	642.7	662.9	688.4	708.3	727.5	736.7	729.0	704.4	665.0
30°	514.9	532.3	540.4	569.6	602.1	640.8	674.8	707.0	715.0	704.3	672.0
32.5°	427.5	442.7	449.5	474.4	504.8	550.2	601.1	646.8	679.1	687.3	667.9
35°	325.2	325.3	340.9	352.0	380.0	426.7	476.2	537.4	598.3	644.5	649.3
37.5°	259.5	260.4	269.8	280.8	301.9	326.5	370.1	421.0	491.4	562.2	603.8
40°	224.0	225.7	232.7	243.6	258.7	277.4	311.3	359.3	418.0	496.9	561.3
42.5°	201.3	204.0	207.6	216.0	225.4	242.9	270.3	307.4	360.8	435.3	509.6
45°	173.5	175.0	177.8	181.6	190.1	202.2	220.7	245.7	289.9	349.9	424.3
47.5°	153.0	152.3	155.2	158.3	164.0	172.3	184.7	204.9	236.5	284.7	347.8
50°	139.2	138.9	141.0	143.4	148.8	154.9	165.0	180.3	205.4	245.3	303.1
52.5°	126.2	126.8	128.3	131.3	135.1	140.1	149.2	160.3	181.8	216.2	264.4
55°	108.9	109.5	111.5	113.1	115.9	120.9	126.6	135.9	150.6	174.6	214.3
57.5°	94.3	94.0	95.9	96.4	99.5	103.5	108.0	115.2	125.9	143.7	170.4
60°	84.5	84.0	85.6	86.9	88.6	91.9	95.6	102.6	111.1	124.2	147.1
62.5°	75.7	75.4	76.6	78.0	79.3	82.3	85.4	90.8	97.5	108.5	126.7
65°	62.7	63.3	63.8	64.4	65.1	67.0	69.9	73.7	78.3	86.0	99.1
67.5°	49.4	49.9	50.1	51.2	52.8	53.9	55.8	59.0	62.3	68.8	76.2
70°	39.8	39.7	39.8	40.4	42.5	44.4	46.9	49.3	51.3	55.9	62.2
72.5°	34.2	33.9	34.4	34.5	35.5	36.0	37.5	39.8	42.5	45.6	50.1
75°	26.5	26.5	26.5	26.5	27.3	27.6	28.2	28.8	29.7	31.2	34.5
77.5°	19.6	19.6	20.0	20.1	20.3	20.5	20.8	21.4	21.7	22.5	23.9
80°	15.5	15.7	15.5	15.7	15.7	16.1	16.2	16.8	17.0	17.9	18.5
82.5°	11.6	11.6	11.6	11.9	11.9	12.2	12.3	12.7	12.7	13.2	13.7
85°	6.3	5.9	6.3	6.1	6.5	6.1	6.3	6.7	6.7	6.8	7.6
87.5°	3.6	3.9	3.6	3.6	3.6	3.7	3.6	3.6	3.8	3.6	3.6
90°	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2	8.9	8.6	7.5
92.5°	11.8	11.7	11.6	11.6	11.4	11.2	10.6	10.1	9.6	9.1	8.3
95°	13.5	13.5	13.5	13.5	13.5	13.2	12.7	12.1	11.6	11.0	10.1
97.5°	14.7	14.6	14.5	14.4	14.3	14.0	13.4	12.8	12.1	11.5	17.2
100°	15.0	14.9	14.8	14.7	14.7	14.3	13.6	13.0	12.4	11.7	24.1
102.5°	15.2	15.1	15.0	14.8	14.7	15.6	17.5	19.5	21.5	23.4	36.9
105°	15.7	15.5	15.4	15.2	15.1	21.9	36.0	49.9	63.9	78.0	85.1
107.5°	49.2	59.7	70.3	80.8	91.4	101.8	112.1	122.3	132.6	142.8	141.7
110°	97.9	109.2	120.5	131.8	143.1	150.0	152.7	155.3	157.9	160.5	159.6



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.9	170.3	172.7	175.1	177.4	178.6	178.6	178.6	178.5	178.5	177.6
115°	209.3	209.0	208.7	208.3	208.0	207.5	206.7	205.9	205.1	204.3	203.6
117.5°	232.5	232.4	232.3	232.3	232.2	231.9	231.2	230.6	230.0	229.3	229.0
120°	248.4	248.4	248.4	248.4	248.4	248.1	247.5	246.8	246.2	245.6	245.3
122.5°	264.1	264.0	264.0	263.9	263.8	263.6	263.2	262.7	262.2	261.8	261.5
125°	286.1	286.0	285.8	285.7	285.5	285.3	285.2	285.0	284.9	284.7	284.4
127.5°	307.4	307.5	307.7	307.8	308.0	307.9	307.7	307.4	307.2	307.0	306.6
130°	321.0	321.2	321.3	321.5	321.6	321.5	321.2	320.9	320.6	320.3	320.0
132.5°	333.6	333.7	334.0	334.2	334.5	334.4	334.1	333.7	333.4	333.1	332.9
135°	352.7	352.9	353.2	353.4	353.6	353.6	353.4	353.2	352.9	352.7	352.4
137.5°	370.7	370.9	371.1	371.2	371.4	371.2	370.8	370.5	370.1	369.7	369.6
140°	381.5	381.7	381.8	382.0	382.1	382.1	381.8	381.4	381.1	380.8	380.6
142.5°	391.5	391.7	392.0	392.1	392.4	392.4	392.1	391.9	391.6	391.3	391.1
145°	406.8	406.8	406.8	406.8	406.8	406.7	406.5	406.4	406.2	406.1	405.9
147.5°	418.2	418.6	418.9	419.3	419.6	419.8	419.6	419.5	419.3	419.1	419.0
150°	426.7	427.0	427.2	427.5	427.7	427.7	427.5	427.4	427.2	427.1	426.9
152.5°	433.6	434.0	434.3	434.7	435.0	435.1	434.7	434.5	434.2	434.0	433.8
155°	443.1	443.5	444.0	444.5	445.0	445.0	444.7	444.3	443.9	443.5	443.4
157.5°	451.1	451.8	452.4	453.0	453.6	453.7	453.2	452.7	452.3	451.8	451.9
160°	456.3	456.9	457.4	458.0	458.5	458.5	458.0	457.6	457.1	456.6	456.7
162.5°	461.1	461.6	462.1	462.6	463.1	463.0	462.6	462.0	461.4	460.9	461.0
165°	467.0	467.5	468.1	468.6	469.1	469.1	468.5	467.9	467.2	466.6	466.7
167.5°	471.2	471.8	472.5	473.0	473.6	473.6	473.0	472.5	471.8	471.2	471.2
170°	473.7	474.4	475.0	475.6	476.3	476.3	475.6	475.0	474.4	473.7	473.7
172.5°	475.2	475.9	476.5	477.2	477.9	477.9	477.3	476.7	476.0	475.4	475.4
175°	477.3	477.9	478.6	479.2	479.8	479.8	479.3	478.7	478.2	477.6	477.5
177.5°	477.9	478.6	479.2	479.8	480.5	480.5	480.0	479.5	479.0	478.5	478.4
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	445.1	444.7	442.7	440.3	437.2	435.1	433.5	432.6	429.9	426.7	424.5
5°	472.7	467.1	461.2	454.0	447.3	440.5	436.3	431.3	425.2	418.4	413.6
7.5°	502.1	491.2	479.6	467.5	455.6	444.9	435.4	427.3	417.6	407.8	401.0
10°	524.7	508.8	492.4	475.6	460.3	445.9	434.8	424.0	412.3	401.1	392.5
12.5°	545.3	524.3	505.4	484.7	465.2	448.0	432.1	419.2	405.2	393.2	383.6
15°	571.2	549.8	527.0	495.5	469.5	447.7	428.3	411.5	394.6	379.9	370.4
17.5°	595.5	563.3	532.5	506.4	472.5	445.4	421.7	401.6	382.9	367.3	355.7
20°	605.5	574.3	541.0	507.6	474.4	443.9	416.4	394.2	374.9	357.1	346.4
22.5°	611.6	576.3	541.1	505.2	469.9	438.2	411.1	386.7	365.7	348.9	335.6
25°	618.6	576.6	537.8	502.4	466.4	432.1	399.7	373.9	351.3	333.4	319.3
27.5°	623.3	573.8	528.0	488.6	452.1	418.0	388.3	360.9	337.9	318.9	303.9
30°	624.2	571.6	520.5	477.8	440.8	409.3	378.0	351.8	327.4	307.3	293.3
32.5°	625.3	566.1	510.2	465.0	427.0	395.9	367.5	342.5	317.5	297.7	283.4
35°	620.5	563.1	494.8	442.8	404.7	374.6	349.0	325.9	301.4	282.2	267.6
37.5°	599.5	551.1	478.8	417.7	378.0	350.1	329.2	309.1	286.6	265.9	252.2
40°	578.5	539.3	466.4	402.5	361.0	332.4	313.5	297.1	275.4	256.0	241.2
42.5°	547.0	523.2	454.6	386.6	341.8	314.3	298.3	283.0	263.9	244.2	230.3
45°	489.3	492.4	430.4	361.2	315.2	287.6	272.6	261.9	244.9	228.7	214.4
47.5°	416.9	446.2	402.0	334.1	287.2	261.3	248.2	238.8	227.4	211.4	198.4
50°	369.7	411.5	379.3	316.0	269.7	243.8	230.9	223.3	213.3	200.8	188.5
52.5°	326.1	371.1	351.8	295.7	250.6	227.0	214.4	208.1	200.2	188.4	177.2
55°	265.9	311.6	307.1	265.2	222.0	200.8	191.2	184.2	178.9	170.0	161.1
57.5°	215.2	258.3	260.6	231.2	196.9	175.9	167.6	162.3	158.8	152.2	143.9
60°	183.1	222.8	230.5	208.3	178.9	160.4	152.3	148.0	145.3	139.9	133.6
62.5°	156.5	190.3	199.1	183.2	161.6	144.3	137.9	133.9	132.0	127.4	121.8
65°	119.8	147.8	156.3	147.5	136.2	122.4	117.2	113.7	112.0	109.5	105.4
67.5°	90.1	110.5	119.9	113.6	109.5	100.8	97.5	95.6	94.1	92.4	89.0
70°	72.3	87.5	97.0	95.5	92.1	87.5	85.1	83.8	82.3	80.8	77.9
72.5°	58.1	68.6	77.6	78.4	75.7	74.8	72.6	72.1	71.2	69.5	67.8
75°	38.6	45.8	52.0	54.4	55.5	56.5	55.5	55.4	55.2	53.7	52.8
77.5°	25.3	29.2	33.1	37.2	39.0	40.2	40.5	41.2	40.6	39.9	39.5
80°	19.4	20.3	23.1	26.5	29.3	30.4	31.2	31.5	31.4	31.2	30.4
82.5°	14.1	14.8	16.2	18.6	20.9	22.7	23.2	23.1	23.5	23.7	23.1
85°	7.6	7.8	8.2	8.5	9.7	11.8	12.4	12.8	13.1	13.1	12.0
87.5°	3.6	3.3	3.4	3.2	3.5	3.5	4.2	4.8	5.1	4.7	4.8
90°	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	7.5	6.8	6.0	5.7	5.9	6.2	6.4	6.7	6.4	6.2	5.9
95°	9.3	8.4	7.5	8.7	12.0	15.2	18.5	21.7	18.5	15.2	12.0
97.5°	22.8	28.5	34.2	37.8	39.3	40.7	42.1	43.6	42.1	40.7	39.3
100°	36.4	48.8	61.1	66.5	64.9	63.3	61.7	60.1	61.7	63.3	64.9
102.5°	50.4	63.8	77.3	83.5	82.4	81.2	80.1	78.9	80.1	81.2	82.4
105°	92.2	99.3	106.4	109.6	108.7	107.8	106.9	106.1	106.9	107.8	108.7
107.5°	140.6	139.5	138.4	137.4	136.7	136.1	135.4	134.7	135.4	136.1	136.7
110°	158.8	157.9	157.0	156.3	155.7	155.0	154.4	153.8	154.4	155.0	155.7



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	176.7	175.9	175.0	174.3	173.6	173.1	172.5	172.0	172.5	173.1	173.6
115°	202.9	202.2	201.5	200.8	200.3	199.9	199.4	198.9	199.4	199.9	200.3
117.5°	228.6	228.2	227.9	227.4	226.8	226.2	225.7	225.1	225.7	226.2	226.8
120°	245.1	244.9	244.6	244.2	243.4	242.7	242.0	241.3	242.0	242.7	243.4
122.5°	261.2	260.9	260.6	260.2	259.6	259.0	258.4	257.9	258.4	259.0	259.6
125°	284.1	283.8	283.4	283.0	282.3	281.7	281.1	280.4	281.1	281.7	282.3
127.5°	306.2	305.8	305.4	304.9	304.3	303.6	303.0	302.4	303.0	303.6	304.3
130°	319.7	319.4	319.1	318.6	318.0	317.3	316.7	316.1	316.7	317.3	318.0
132.5°	332.6	332.4	332.1	331.7	331.1	330.4	329.8	329.2	329.8	330.4	331.1
135°	352.0	351.7	351.4	351.0	350.5	350.1	349.6	349.1	349.6	350.1	350.5
137.5°	369.4	369.2	369.0	368.6	368.0	367.4	366.9	366.2	366.9	367.4	368.0
140°	380.3	380.1	379.9	379.5	379.1	378.6	378.1	377.6	378.1	378.6	379.1
142.5°	390.9	390.6	390.4	390.1	389.6	389.1	388.6	388.2	388.6	389.1	389.6
145°	405.8	405.6	405.4	405.1	404.6	404.0	403.5	402.9	403.5	404.0	404.6
147.5°	418.8	418.7	418.5	418.2	417.9	417.5	417.2	416.8	417.2	417.5	417.9
150°	426.7	426.6	426.4	426.3	426.0	425.8	425.6	425.3	425.6	425.8	426.0
152.5°	433.7	433.6	433.6	433.5	433.3	433.2	433.1	433.0	433.1	433.2	433.3
155°	443.3	443.2	443.1	443.2	443.4	443.5	443.6	443.8	443.6	443.5	443.4
157.5°	451.9	452.0	452.1	452.2	452.2	452.2	452.2	452.3	452.2	452.2	452.2
160°	456.8	456.9	456.9	457.0	457.1	457.2	457.2	457.3	457.2	457.2	457.1
162.5°	461.1	461.1	461.2	461.4	461.6	461.8	462.0	462.2	462.0	461.8	461.6
165°	466.8	466.8	466.9	467.1	467.3	467.5	467.8	468.0	467.8	467.5	467.3
167.5°	471.2	471.2	471.2	471.3	471.7	472.0	472.3	472.6	472.3	472.0	471.7
170°	473.7	473.7	473.7	473.9	474.2	474.5	474.8	475.2	474.8	474.5	474.2
172.5°	475.3	475.2	475.2	475.3	475.7	476.1	476.5	476.8	476.5	476.1	475.7
175°	477.4	477.4	477.3	477.4	477.8	478.2	478.6	479.0	478.6	478.2	477.8
177.5°	478.3	478.3	478.2	478.3	478.6	479.0	479.3	479.6	479.3	479.0	478.6
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	423.7	421.8	420.5	417.6	415.7	413.6	411.5	412.8	412.6	412.6	412.6
5°	409.6	405.3	401.4	396.4	393.3	389.4	386.5	386.1	386.8	384.3	382.8
7.5°	395.5	389.7	384.1	378.7	372.8	368.1	365.3	363.8	362.0	360.4	358.8
10°	385.6	378.7	373.4	366.5	360.3	354.7	351.3	348.8	347.5	346.3	343.8
12.5°	375.3	368.7	361.9	354.1	348.2	341.7	339.1	336.4	334.0	332.5	329.2
15°	360.4	351.8	344.6	336.4	329.8	323.5	319.9	314.5	313.8	311.9	308.6
17.5°	345.5	336.1	326.1	320.1	312.7	306.1	300.5	298.7	293.4	291.4	288.5
20°	333.7	325.0	317.4	309.5	298.7	292.6	288.1	285.7	281.5	278.8	277.0
22.5°	323.5	314.7	305.9	296.7	287.7	280.8	277.6	273.9	271.6	267.9	265.9
25°	309.0	299.4	288.8	278.8	272.4	267.3	262.1	258.7	255.4	253.7	250.1
27.5°	292.1	282.0	272.2	264.6	256.7	251.6	246.9	244.0	240.0	237.2	235.1
30°	282.7	270.9	262.4	255.6	245.5	240.7	237.2	233.5	230.5	227.6	225.5
32.5°	272.0	261.2	253.2	244.7	236.9	231.6	227.1	223.9	221.3	218.6	216.5
35°	255.1	246.1	237.7	229.3	223.5	218.2	212.8	210.0	207.6	205.0	203.2
37.5°	239.8	231.3	223.4	215.4	208.3	203.9	199.6	197.5	194.2	192.5	190.7
40°	230.4	222.0	213.6	205.8	198.4	195.1	191.2	188.1	185.1	183.8	181.8
42.5°	220.0	211.7	204.5	196.2	190.1	185.6	182.0	178.6	176.4	174.5	173.4
45°	204.7	197.3	190.3	182.0	176.3	172.4	168.3	165.2	163.2	161.8	159.9
47.5°	189.8	182.4	175.3	168.1	162.6	158.1	154.0	151.9	149.2	147.6	146.2
50°	179.0	172.4	164.9	158.2	152.7	148.2	144.9	142.1	139.7	137.7	136.7
52.5°	169.1	162.1	155.5	149.3	143.5	138.5	135.5	132.5	130.7	128.4	127.3
55°	152.8	146.0	140.5	134.4	128.7	124.4	120.7	118.1	116.3	113.7	112.3
57.5°	137.5	131.3	124.8	119.5	113.6	110.0	106.9	103.5	101.2	99.2	97.7
60°	127.1	120.2	114.4	109.5	104.3	99.7	96.9	94.1	91.7	89.7	88.4
62.5°	116.4	110.3	104.8	99.4	94.7	90.6	87.5	85.2	83.0	81.8	80.4
65°	99.8	95.1	89.5	85.1	80.6	77.7	75.1	73.1	71.6	70.7	69.6
67.5°	84.6	80.0	75.2	70.8	67.8	65.6	63.9	62.2	61.4	60.2	59.5
70°	74.8	69.9	65.7	62.3	59.4	57.8	56.6	55.4	54.7	53.2	52.4
72.5°	64.0	60.5	57.4	54.7	52.4	50.9	49.4	47.8	46.7	45.0	44.3
75°	50.4	47.2	44.8	43.0	41.5	39.5	37.5	35.8	35.3	34.7	34.5
77.5°	37.3	35.3	33.6	32.0	30.2	28.8	28.3	27.9	27.8	27.5	27.5
80°	29.3	27.5	26.2	24.4	23.3	23.3	23.3	22.9	23.1	23.1	23.1
82.5°	21.8	20.1	19.4	18.8	18.5	18.7	18.7	18.8	18.6	18.9	18.8
85°	11.2	11.4	11.8	11.6	11.8	11.8	12.2	12.0	12.2	11.8	12.2
87.5°	4.8	5.5	5.8	6.2	6.5	6.6	6.8	6.9	7.1	7.1	7.2
90°	3.5	4.4	5.5	6.5	7.5	8.6	8.9	9.2	9.5	9.8	10.1
92.5°	5.7	6.0	6.8	7.5	8.3	9.1	9.6	10.1	10.6	11.2	11.4
95°	8.7	7.5	8.4	9.3	10.1	11.0	11.6	12.1	12.7	13.2	13.5
97.5°	37.8	34.2	28.5	22.8	17.2	11.5	12.1	12.8	13.4	14.0	14.3
100°	66.5	61.1	48.8	36.4	24.1	11.7	12.4	13.0	13.6	14.3	14.7
102.5°	83.5	77.3	63.8	50.4	36.9	23.4	21.5	19.5	17.5	15.6	14.7
105°	109.6	106.4	99.3	92.2	85.1	78.0	63.9	49.9	36.0	21.9	15.1
107.5°	137.4	138.4	139.5	140.6	141.7	142.8	132.6	122.3	112.1	101.8	91.4
110°	156.3	157.0	157.9	158.8	159.6	160.5	157.9	155.3	152.7	150.0	143.1



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	174.3	175.0	175.9	176.7	177.6	178.5	178.5	178.6	178.6	178.6	177.4
115°	200.8	201.5	202.2	202.9	203.6	204.3	205.1	205.9	206.7	207.5	208.0
117.5°	227.4	227.9	228.2	228.6	229.0	229.3	230.0	230.6	231.2	231.9	232.2
120°	244.2	244.6	244.9	245.1	245.3	245.6	246.2	246.8	247.5	248.1	248.4
122.5°	260.2	260.6	260.9	261.2	261.5	261.8	262.2	262.7	263.2	263.6	263.8
125°	283.0	283.4	283.8	284.1	284.4	284.7	284.9	285.0	285.2	285.3	285.5
127.5°	304.9	305.4	305.8	306.2	306.6	307.0	307.2	307.4	307.7	307.9	308.0
130°	318.6	319.1	319.4	319.7	320.0	320.3	320.6	320.9	321.2	321.5	321.6
132.5°	331.7	332.1	332.4	332.6	332.9	333.1	333.4	333.7	334.1	334.4	334.5
135°	351.0	351.4	351.7	352.0	352.4	352.7	352.9	353.2	353.4	353.6	353.6
137.5°	368.6	369.0	369.2	369.4	369.6	369.7	370.1	370.5	370.8	371.2	371.4
140°	379.5	379.9	380.1	380.3	380.6	380.8	381.1	381.4	381.8	382.1	382.1
142.5°	390.1	390.4	390.6	390.9	391.1	391.3	391.6	391.9	392.1	392.4	392.4
145°	405.1	405.4	405.6	405.8	405.9	406.1	406.2	406.4	406.5	406.7	406.8
147.5°	418.2	418.5	418.7	418.8	419.0	419.1	419.3	419.5	419.6	419.8	419.6
150°	426.3	426.4	426.6	426.7	426.9	427.1	427.2	427.4	427.5	427.7	427.7
152.5°	433.5	433.6	433.6	433.7	433.8	434.0	434.2	434.5	434.7	435.1	435.0
155°	443.2	443.1	443.2	443.3	443.4	443.5	443.9	444.3	444.7	445.0	445.0
157.5°	452.2	452.1	452.0	451.9	451.9	451.8	452.3	452.7	453.2	453.7	453.6
160°	457.0	456.9	456.9	456.8	456.7	456.6	457.1	457.6	458.0	458.5	458.5
162.5°	461.4	461.2	461.1	461.1	461.0	460.9	461.4	462.0	462.6	463.0	463.1
165°	467.1	466.9	466.8	466.8	466.7	466.6	467.2	467.9	468.5	469.1	469.1
167.5°	471.3	471.2	471.2	471.2	471.2	471.2	471.8	472.5	473.0	473.6	473.6
170°	473.9	473.7	473.7	473.7	473.7	473.7	474.4	475.0	475.6	476.3	476.3
172.5°	475.3	475.2	475.2	475.3	475.4	475.4	476.0	476.7	477.3	477.9	477.9
175°	477.4	477.3	477.4	477.4	477.5	477.6	478.2	478.7	479.3	479.8	479.8
177.5°	478.3	478.2	478.3	478.3	478.4	478.5	479.0	479.5	480.0	480.5	480.5
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	410.7	410.6	410.7	410.2	410.7	410.6	410.7	412.6	412.6	412.6	412.8
5°	382.2	382.1	381.5	379.9	381.5	382.1	382.2	382.8	384.3	386.8	386.1
7.5°	357.3	357.0	355.5	355.5	355.5	357.0	357.3	358.8	360.4	362.0	363.8
10°	342.5	342.7	340.5	339.2	340.5	342.7	342.5	343.8	346.3	347.5	348.8
12.5°	328.2	327.4	325.6	324.2	325.6	327.4	328.2	329.2	332.5	334.0	336.4
15°	309.3	307.4	303.1	303.4	303.1	307.4	309.3	308.6	311.9	313.8	314.5
17.5°	287.1	285.7	285.7	283.0	285.7	285.7	287.1	288.5	291.4	293.4	298.7
20°	274.1	273.1	273.5	270.9	273.5	273.1	274.1	277.0	278.8	281.5	285.7
22.5°	263.9	262.9	261.4	260.6	261.4	262.9	263.9	265.9	267.9	271.6	273.9
25°	249.0	247.5	246.1	246.9	246.1	247.5	249.0	250.1	253.7	255.4	258.7
27.5°	234.1	233.0	231.5	231.3	231.5	233.0	234.1	235.1	237.2	240.0	244.0
30°	224.6	223.5	222.8	221.8	222.8	223.5	224.6	225.5	227.6	230.5	233.5
32.5°	215.0	214.8	213.5	213.3	213.5	214.8	215.0	216.5	218.6	221.3	223.9
35°	202.5	201.4	201.0	201.1	201.0	201.4	202.5	203.2	205.0	207.6	210.0
37.5°	190.5	189.1	188.4	187.7	188.4	189.1	190.5	190.7	192.5	194.2	197.5
40°	182.0	180.5	180.1	179.7	180.1	180.5	182.0	181.8	183.8	185.1	188.1
42.5°	172.4	171.8	171.6	170.9	171.6	171.8	172.4	173.4	174.5	176.4	178.6
45°	159.3	159.1	158.0	158.4	158.0	159.1	159.3	159.9	161.8	163.2	165.2
47.5°	145.4	144.7	143.9	144.4	143.9	144.7	145.4	146.2	147.6	149.2	151.9
50°	136.0	135.6	134.0	134.4	134.0	135.6	136.0	136.7	137.7	139.7	142.1
52.5°	126.6	125.2	124.5	124.3	124.5	125.2	126.6	127.3	128.4	130.7	132.5
55°	110.9	109.2	108.5	108.1	108.5	109.2	110.9	112.3	113.7	116.3	118.1
57.5°	95.5	95.1	94.5	94.9	94.5	95.1	95.5	97.7	99.2	101.2	103.5
60°	86.6	86.6	86.6	86.3	86.6	86.6	86.6	88.4	89.7	91.7	94.1
62.5°	79.6	79.1	79.1	79.3	79.1	79.1	79.6	80.4	81.8	83.0	85.2
65°	69.0	68.8	68.1	67.9	68.1	68.8	69.0	69.6	70.7	71.6	73.1
67.5°	59.0	58.4	58.1	57.9	58.1	58.4	59.0	59.5	60.2	61.4	62.2
70°	51.5	51.1	50.0	50.2	50.0	51.1	51.5	52.4	53.2	54.7	55.4
72.5°	43.4	43.0	42.8	42.5	42.8	43.0	43.4	44.3	45.0	46.7	47.8
75°	34.3	34.1	34.0	34.7	34.0	34.1	34.3	34.5	34.7	35.3	35.8
77.5°	27.5	27.5	27.6	27.3	27.6	27.5	27.5	27.5	27.5	27.8	27.9
80°	23.1	23.1	22.9	22.9	22.9	23.1	23.1	23.1	23.1	23.1	22.9
82.5°	18.5	18.6	18.8	18.5	18.8	18.6	18.5	18.8	18.9	18.6	18.8
85°	12.2	12.0	12.4	12.2	12.4	12.0	12.2	12.2	11.8	12.2	12.0
87.5°	7.5	7.2	7.3	7.4	7.3	7.2	7.5	7.2	7.1	7.1	6.9
90°	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	9.8	9.5	9.2
92.5°	11.6	11.6	11.7	11.8	11.7	11.6	11.6	11.4	11.2	10.6	10.1
95°	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.2	12.7	12.1
97.5°	14.4	14.5	14.6	14.7	14.6	14.5	14.4	14.3	14.0	13.4	12.8
100°	14.7	14.8	14.9	15.0	14.9	14.8	14.7	14.7	14.3	13.6	13.0
102.5°	14.8	15.0	15.1	15.2	15.1	15.0	14.8	14.7	15.6	17.5	19.5
105°	15.2	15.4	15.5	15.7	15.5	15.4	15.2	15.1	21.9	36.0	49.9
107.5°	80.8	70.3	59.7	49.2	59.7	70.3	80.8	91.4	101.8	112.1	122.3
110°	131.8	120.5	109.2	97.9	109.2	120.5	131.8	143.1	150.0	152.7	155.3



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	175.1	172.7	170.3	167.9	170.3	172.7	175.1	177.4	178.6	178.6	178.6
115°	208.3	208.7	209.0	209.3	209.0	208.7	208.3	208.0	207.5	206.7	205.9
117.5°	232.3	232.3	232.4	232.5	232.4	232.3	232.3	232.2	231.9	231.2	230.6
120°	248.4	248.4	248.4	248.4	248.4	248.4	248.4	248.4	248.1	247.5	246.8
122.5°	263.9	264.0	264.0	264.1	264.0	264.0	263.9	263.8	263.6	263.2	262.7
125°	285.7	285.8	286.0	286.1	286.0	285.8	285.7	285.5	285.3	285.2	285.0
127.5°	307.8	307.7	307.5	307.4	307.5	307.7	307.8	308.0	307.9	307.7	307.4
130°	321.5	321.3	321.2	321.0	321.2	321.3	321.5	321.6	321.5	321.2	320.9
132.5°	334.2	334.0	333.7	333.6	333.7	334.0	334.2	334.5	334.4	334.1	333.7
135°	353.4	353.2	352.9	352.7	352.9	353.2	353.4	353.6	353.6	353.4	353.2
137.5°	371.2	371.1	370.9	370.7	370.9	371.1	371.2	371.4	371.2	370.8	370.5
140°	382.0	381.8	381.7	381.5	381.7	381.8	382.0	382.1	382.1	381.8	381.4
142.5°	392.1	392.0	391.7	391.5	391.7	392.0	392.1	392.4	392.4	392.1	391.9
145°	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.8	406.7	406.5	406.4
147.5°	419.3	418.9	418.6	418.2	418.6	418.9	419.3	419.6	419.8	419.6	419.5
150°	427.5	427.2	427.0	426.7	427.0	427.2	427.5	427.7	427.7	427.5	427.4
152.5°	434.7	434.3	434.0	433.6	434.0	434.3	434.7	435.0	435.1	434.7	434.5
155°	444.5	444.0	443.5	443.1	443.5	444.0	444.5	445.0	445.0	444.7	444.3
157.5°	453.0	452.4	451.8	451.1	451.8	452.4	453.0	453.6	453.7	453.2	452.7
160°	458.0	457.4	456.9	456.3	456.9	457.4	458.0	458.5	458.5	458.0	457.6
162.5°	462.6	462.1	461.6	461.1	461.6	462.1	462.6	463.1	463.0	462.6	462.0
165°	468.6	468.1	467.5	467.0	467.5	468.1	468.6	469.1	469.1	468.5	467.9
167.5°	473.0	472.5	471.8	471.2	471.8	472.5	473.0	473.6	473.6	473.0	472.5
170°	475.6	475.0	474.4	473.7	474.4	475.0	475.6	476.3	476.3	475.6	475.0
172.5°	477.2	476.5	475.9	475.2	475.9	476.5	477.2	477.9	477.9	477.3	476.7
175°	479.2	478.6	477.9	477.3	477.9	478.6	479.2	479.8	479.8	479.3	478.7
177.5°	479.8	479.2	478.6	477.9	478.6	479.2	479.8	480.5	480.5	480.0	479.5
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	411.5	413.6	415.7	417.6	420.5	421.8	423.7	424.5	426.7	429.9	432.6
5°	386.5	389.4	393.3	396.4	401.4	405.3	409.6	413.6	418.4	425.2	431.3
7.5°	365.3	368.1	372.8	378.7	384.1	389.7	395.5	401.0	407.8	417.6	427.3
10°	351.3	354.7	360.3	366.5	373.4	378.7	385.6	392.5	401.1	412.3	424.0
12.5°	339.1	341.7	348.2	354.1	361.9	368.7	375.3	383.6	393.2	405.2	419.2
15°	319.9	323.5	329.8	336.4	344.6	351.8	360.4	370.4	379.9	394.6	411.5
17.5°	300.5	306.1	312.7	320.1	326.1	336.1	345.5	355.7	367.3	382.9	401.6
20°	288.1	292.6	298.7	309.5	317.4	325.0	333.7	346.4	357.1	374.9	394.2
22.5°	277.6	280.8	287.7	296.7	305.9	314.7	323.5	335.6	348.9	365.7	386.7
25°	262.1	267.3	272.4	278.8	288.8	299.4	309.0	319.3	333.4	351.3	373.9
27.5°	246.9	251.6	256.7	264.6	272.2	282.0	292.1	303.9	318.9	337.9	360.9
30°	237.2	240.7	245.5	255.6	262.4	270.9	282.7	293.3	307.3	327.4	351.8
32.5°	227.1	231.6	236.9	244.7	253.2	261.2	272.0	283.4	297.7	317.5	342.5
35°	212.8	218.2	223.5	229.3	237.7	246.1	255.1	267.6	282.2	301.4	325.9
37.5°	199.6	203.9	208.3	215.4	223.4	231.3	239.8	252.2	265.9	286.6	309.1
40°	191.2	195.1	198.4	205.8	213.6	222.0	230.4	241.2	256.0	275.4	297.1
42.5°	182.0	185.6	190.1	196.2	204.5	211.7	220.0	230.3	244.2	263.9	283.0
45°	168.3	172.4	176.3	182.0	190.3	197.3	204.7	214.4	228.7	244.9	261.9
47.5°	154.0	158.1	162.6	168.1	175.3	182.4	189.8	198.4	211.4	227.4	238.8
50°	144.9	148.2	152.7	158.2	164.9	172.4	179.0	188.5	200.8	213.3	223.3
52.5°	135.5	138.5	143.5	149.3	155.5	162.1	169.1	177.2	188.4	200.2	208.1
55°	120.7	124.4	128.7	134.4	140.5	146.0	152.8	161.1	170.0	178.9	184.2
57.5°	106.9	110.0	113.6	119.5	124.8	131.3	137.5	143.9	152.2	158.8	162.3
60°	96.9	99.7	104.3	109.5	114.4	120.2	127.1	133.6	139.9	145.3	148.0
62.5°	87.5	90.6	94.7	99.4	104.8	110.3	116.4	121.8	127.4	132.0	133.9
65°	75.1	77.7	80.6	85.1	89.5	95.1	99.8	105.4	109.5	112.0	113.7
67.5°	63.9	65.6	67.8	70.8	75.2	80.0	84.6	89.0	92.4	94.1	95.6
70°	56.6	57.8	59.4	62.3	65.7	69.9	74.8	77.9	80.8	82.3	83.8
72.5°	49.4	50.9	52.4	54.7	57.4	60.5	64.0	67.8	69.5	71.2	72.1
75°	37.5	39.5	41.5	43.0	44.8	47.2	50.4	52.8	53.7	55.2	55.4
77.5°	28.3	28.8	30.2	32.0	33.6	35.3	37.3	39.5	39.9	40.6	41.2
80°	23.3	23.3	23.3	24.4	26.2	27.5	29.3	30.4	31.2	31.4	31.5
82.5°	18.7	18.7	18.5	18.8	19.4	20.1	21.8	23.1	23.7	23.5	23.1
85°	12.2	11.8	11.8	11.6	11.8	11.4	11.2	12.0	13.1	13.1	12.8
87.5°	6.8	6.6	6.5	6.2	5.8	5.5	4.8	4.8	4.7	5.1	4.8
90°	8.9	8.6	7.5	6.5	5.5	4.4	3.5	2.7	1.9	1.1	0.3
92.5°	9.6	9.1	8.3	7.5	6.8	6.0	5.7	5.9	6.2	6.4	6.7
95°	11.6	11.0	10.1	9.3	8.4	7.5	8.7	12.0	15.2	18.5	21.7
97.5°	12.1	11.5	17.2	22.8	28.5	34.2	37.8	39.3	40.7	42.1	43.6
100°	12.4	11.7	24.1	36.4	48.8	61.1	66.5	64.9	63.3	61.7	60.1
102.5°	21.5	23.4	36.9	50.4	63.8	77.3	83.5	82.4	81.2	80.1	78.9
105°	63.9	78.0	85.1	92.2	99.3	106.4	109.6	108.7	107.8	106.9	106.1
107.5°	132.6	142.8	141.7	140.6	139.5	138.4	137.4	136.7	136.1	135.4	134.7
110°	157.9	160.5	159.6	158.8	157.9	157.0	156.3	155.7	155.0	154.4	153.8



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	178.5	178.5	177.6	176.7	175.9	175.0	174.3	173.6	173.1	172.5	172.0
115°	205.1	204.3	203.6	202.9	202.2	201.5	200.8	200.3	199.9	199.4	198.9
117.5°	230.0	229.3	229.0	228.6	228.2	227.9	227.4	226.8	226.2	225.7	225.1
120°	246.2	245.6	245.3	245.1	244.9	244.6	244.2	243.4	242.7	242.0	241.3
122.5°	262.2	261.8	261.5	261.2	260.9	260.6	260.2	259.6	259.0	258.4	257.9
125°	284.9	284.7	284.4	284.1	283.8	283.4	283.0	282.3	281.7	281.1	280.4
127.5°	307.2	307.0	306.6	306.2	305.8	305.4	304.9	304.3	303.6	303.0	302.4
130°	320.6	320.3	320.0	319.7	319.4	319.1	318.6	318.0	317.3	316.7	316.1
132.5°	333.4	333.1	332.9	332.6	332.4	332.1	331.7	331.1	330.4	329.8	329.2
135°	352.9	352.7	352.4	352.0	351.7	351.4	351.0	350.5	350.1	349.6	349.1
137.5°	370.1	369.7	369.6	369.4	369.2	369.0	368.6	368.0	367.4	366.9	366.2
140°	381.1	380.8	380.6	380.3	380.1	379.9	379.5	379.1	378.6	378.1	377.6
142.5°	391.6	391.3	391.1	390.9	390.6	390.4	390.1	389.6	389.1	388.6	388.2
145°	406.2	406.1	405.9	405.8	405.6	405.4	405.1	404.6	404.0	403.5	402.9
147.5°	419.3	419.1	419.0	418.8	418.7	418.5	418.2	417.9	417.5	417.2	416.8
150°	427.2	427.1	426.9	426.7	426.6	426.4	426.3	426.0	425.8	425.6	425.3
152.5°	434.2	434.0	433.8	433.7	433.6	433.6	433.5	433.3	433.2	433.1	433.0
155°	443.9	443.5	443.4	443.3	443.2	443.1	443.2	443.4	443.5	443.6	443.8
157.5°	452.3	451.8	451.9	451.9	452.0	452.1	452.2	452.2	452.2	452.2	452.3
160°	457.1	456.6	456.7	456.8	456.9	456.9	457.0	457.1	457.2	457.2	457.3
162.5°	461.4	460.9	461.0	461.1	461.1	461.2	461.4	461.6	461.8	462.0	462.2
165°	467.2	466.6	466.7	466.8	466.8	466.9	467.1	467.3	467.5	467.8	468.0
167.5°	471.8	471.2	471.2	471.2	471.2	471.2	471.3	471.7	472.0	472.3	472.6
170°	474.4	473.7	473.7	473.7	473.7	473.7	473.9	474.2	474.5	474.8	475.2
172.5°	476.0	475.4	475.4	475.3	475.2	475.2	475.3	475.7	476.1	476.5	476.8
175°	478.2	477.6	477.5	477.4	477.4	477.3	477.4	477.8	478.2	478.6	479.0
177.5°	479.0	478.5	478.4	478.3	478.3	478.2	478.3	478.6	479.0	479.3	479.6
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	433.5	435.1	437.2	440.3	442.7	444.7	445.1	445.8	447.3	449.7	451.6
5°	436.3	440.5	447.3	454.0	461.2	467.1	472.7	476.6	480.2	488.0	494.2
7.5°	435.4	444.9	455.6	467.5	479.6	491.2	502.1	511.8	521.5	532.8	545.7
10°	434.8	445.9	460.3	475.6	492.4	508.8	524.7	537.1	551.4	564.4	580.8
12.5°	432.1	448.0	465.2	484.7	505.4	524.3	545.3	562.3	578.8	597.5	616.6
15°	428.3	447.7	469.5	495.5	527.0	549.8	571.2	600.9	621.2	641.5	668.8
17.5°	421.7	445.4	472.5	506.4	532.5	563.3	595.5	619.0	646.3	674.9	699.7
20°	416.4	443.9	474.4	507.6	541.0	574.3	605.5	633.6	661.9	694.9	715.2
22.5°	411.1	438.2	469.9	505.2	541.1	576.3	611.6	644.5	676.3	709.6	735.5
25°	399.7	432.1	466.4	502.4	537.8	576.6	618.6	655.4	694.7	729.0	753.6
27.5°	388.3	418.0	452.1	488.6	528.0	573.8	623.3	665.0	704.4	729.0	736.7
30°	378.0	409.3	440.8	477.8	520.5	571.6	624.2	672.0	704.3	715.0	707.0
32.5°	367.5	395.9	427.0	465.0	510.2	566.1	625.3	667.9	687.3	679.1	646.8
35°	349.0	374.6	404.7	442.8	494.8	563.1	620.5	649.3	644.5	598.3	537.4
37.5°	329.2	350.1	378.0	417.7	478.8	551.1	599.5	603.8	562.2	491.4	421.0
40°	313.5	332.4	361.0	402.5	466.4	539.3	578.5	561.3	496.9	418.0	359.3
42.5°	298.3	314.3	341.8	386.6	454.6	523.2	547.0	509.6	435.3	360.8	307.4
45°	272.6	287.6	315.2	361.2	430.4	492.4	489.3	424.3	349.9	289.9	245.7
47.5°	248.2	261.3	287.2	334.1	402.0	446.2	416.9	347.8	284.7	236.5	204.9
50°	230.9	243.8	269.7	316.0	379.3	411.5	369.7	303.1	245.3	205.4	180.3
52.5°	214.4	227.0	250.6	295.7	351.8	371.1	326.1	264.4	216.2	181.8	160.3
55°	191.2	200.8	222.0	265.2	307.1	311.6	265.9	214.3	174.6	150.6	135.9
57.5°	167.6	175.9	196.9	231.2	260.6	258.3	215.2	170.4	143.7	125.9	115.2
60°	152.3	160.4	178.9	208.3	230.5	222.8	183.1	147.1	124.2	111.1	102.6
62.5°	137.9	144.3	161.6	183.2	199.1	190.3	156.5	126.7	108.5	97.5	90.8
65°	117.2	122.4	136.2	147.5	156.3	147.8	119.8	99.1	86.0	78.3	73.7
67.5°	97.5	100.8	109.5	113.6	119.9	110.5	90.1	76.2	68.8	62.3	59.0
70°	85.1	87.5	92.1	95.5	97.0	87.5	72.3	62.2	55.9	51.3	49.3
72.5°	72.6	74.8	75.7	78.4	77.6	68.6	58.1	50.1	45.6	42.5	39.8
75°	55.5	56.5	55.5	54.4	52.0	45.8	38.6	34.5	31.2	29.7	28.8
77.5°	40.5	40.2	39.0	37.2	33.1	29.2	25.3	23.9	22.5	21.7	21.4
80°	31.2	30.4	29.3	26.5	23.1	20.3	19.4	18.5	17.9	17.0	16.8
82.5°	23.2	22.7	20.9	18.6	16.2	14.8	14.1	13.7	13.2	12.7	12.7
85°	12.4	11.8	9.7	8.5	8.2	7.8	7.6	7.6	6.8	6.7	6.7
87.5°	4.2	3.5	3.5	3.2	3.4	3.3	3.6	3.6	3.6	3.8	3.6
90°	1.1	1.9	2.7	3.5	4.4	5.5	6.5	7.5	8.6	8.9	9.2
92.5°	6.4	6.2	5.9	5.7	6.0	6.8	7.5	8.3	9.1	9.6	10.1
95°	18.5	15.2	12.0	8.7	7.5	8.4	9.3	10.1	11.0	11.6	12.1
97.5°	42.1	40.7	39.3	37.8	34.2	28.5	22.8	17.2	11.5	12.1	12.8
100°	61.7	63.3	64.9	66.5	61.1	48.8	36.4	24.1	11.7	12.4	13.0
102.5°	80.1	81.2	82.4	83.5	77.3	63.8	50.4	36.9	23.4	21.5	19.5
105°	106.9	107.8	108.7	109.6	106.4	99.3	92.2	85.1	78.0	63.9	49.9
107.5°	135.4	136.1	136.7	137.4	138.4	139.5	140.6	141.7	142.8	132.6	122.3
110°	154.4	155.0	155.7	156.3	157.0	157.9	158.8	159.6	160.5	157.9	155.3



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	172.5	173.1	173.6	174.3	175.0	175.9	176.7	177.6	178.5	178.5	178.6
115°	199.4	199.9	200.3	200.8	201.5	202.2	202.9	203.6	204.3	205.1	205.9
117.5°	225.7	226.2	226.8	227.4	227.9	228.2	228.6	229.0	229.3	230.0	230.6
120°	242.0	242.7	243.4	244.2	244.6	244.9	245.1	245.3	245.6	246.2	246.8
122.5°	258.4	259.0	259.6	260.2	260.6	260.9	261.2	261.5	261.8	262.2	262.7
125°	281.1	281.7	282.3	283.0	283.4	283.8	284.1	284.4	284.7	284.9	285.0
127.5°	303.0	303.6	304.3	304.9	305.4	305.8	306.2	306.6	307.0	307.2	307.4
130°	316.7	317.3	318.0	318.6	319.1	319.4	319.7	320.0	320.3	320.6	320.9
132.5°	329.8	330.4	331.1	331.7	332.1	332.4	332.6	332.9	333.1	333.4	333.7
135°	349.6	350.1	350.5	351.0	351.4	351.7	352.0	352.4	352.7	352.9	353.2
137.5°	366.9	367.4	368.0	368.6	369.0	369.2	369.4	369.6	369.7	370.1	370.5
140°	378.1	378.6	379.1	379.5	379.9	380.1	380.3	380.6	380.8	381.1	381.4
142.5°	388.6	389.1	389.6	390.1	390.4	390.6	390.9	391.1	391.3	391.6	391.9
145°	403.5	404.0	404.6	405.1	405.4	405.6	405.8	405.9	406.1	406.2	406.4
147.5°	417.2	417.5	417.9	418.2	418.5	418.7	418.8	419.0	419.1	419.3	419.5
150°	425.6	425.8	426.0	426.3	426.4	426.6	426.7	426.9	427.1	427.2	427.4
152.5°	433.1	433.2	433.3	433.5	433.6	433.6	433.7	433.8	434.0	434.2	434.5
155°	443.6	443.5	443.4	443.2	443.1	443.2	443.3	443.4	443.5	443.9	444.3
157.5°	452.2	452.2	452.2	452.2	452.1	452.0	451.9	451.9	451.8	452.3	452.7
160°	457.2	457.2	457.1	457.0	456.9	456.9	456.8	456.7	456.6	457.1	457.6
162.5°	462.0	461.8	461.6	461.4	461.2	461.1	461.1	461.0	460.9	461.4	462.0
165°	467.8	467.5	467.3	467.1	466.9	466.8	466.8	466.7	466.6	467.2	467.9
167.5°	472.3	472.0	471.7	471.3	471.2	471.2	471.2	471.2	471.2	471.8	472.5
170°	474.8	474.5	474.2	473.9	473.7	473.7	473.7	473.7	473.7	474.4	475.0
172.5°	476.5	476.1	475.7	475.3	475.2	475.2	475.3	475.4	475.4	476.0	476.7
175°	478.6	478.2	477.8	477.4	477.3	477.4	477.4	477.5	477.6	478.2	478.7
177.5°	479.3	479.0	478.6	478.3	478.2	478.3	478.3	478.4	478.5	479.0	479.5
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0	479.0



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	431.1	431.1	431.1	431.1	431.1	431.1	431.1
2.5°	454.8	454.8	455.3	457.6	457.9	459.8	459.2
5°	499.8	503.3	504.6	510.2	513.4	514.9	512.0
7.5°	554.8	564.7	569.4	575.3	580.4	581.9	577.9
10°	595.0	605.4	614.0	619.4	624.4	627.7	631.9
12.5°	633.8	646.6	654.8	662.3	667.5	671.7	672.4
15°	676.0	695.2	709.8	720.6	725.9	728.6	727.5
17.5°	718.6	736.4	746.8	757.7	765.1	765.5	765.7
20°	742.7	760.0	772.1	780.1	788.5	788.1	790.0
22.5°	758.8	772.5	781.6	787.5	790.4	788.9	789.3
25°	766.3	770.4	768.7	759.3	756.9	748.2	749.7
27.5°	727.5	708.3	688.4	662.9	642.7	626.6	627.4
30°	674.8	640.8	602.1	569.6	540.4	532.3	514.9
32.5°	601.1	550.2	504.8	474.4	449.5	442.7	427.5
35°	476.2	426.7	380.0	352.0	340.9	325.3	325.2
37.5°	370.1	326.5	301.9	280.8	269.8	260.4	259.5
40°	311.3	277.4	258.7	243.6	232.7	225.7	224.0
42.5°	270.3	242.9	225.4	216.0	207.6	204.0	201.3
45°	220.7	202.2	190.1	181.6	177.8	175.0	173.5
47.5°	184.7	172.3	164.0	158.3	155.2	152.3	153.0
50°	165.0	154.9	148.8	143.4	141.0	138.9	139.2
52.5°	149.2	140.1	135.1	131.3	128.3	126.8	126.2
55°	126.6	120.9	115.9	113.1	111.5	109.5	108.9
57.5°	108.0	103.5	99.5	96.4	95.9	94.0	94.3
60°	95.6	91.9	88.6	86.9	85.6	84.0	84.5
62.5°	85.4	82.3	79.3	78.0	76.6	75.4	75.7
65°	69.9	67.0	65.1	64.4	63.8	63.3	62.7
67.5°	55.8	53.9	52.8	51.2	50.1	49.9	49.4
70°	46.9	44.4	42.5	40.4	39.8	39.7	39.8
72.5°	37.5	36.0	35.5	34.5	34.4	33.9	34.2
75°	28.2	27.6	27.3	26.5	26.5	26.5	26.5
77.5°	20.8	20.5	20.3	20.1	20.0	19.6	19.6
80°	16.2	16.1	15.7	15.7	15.5	15.7	15.5
82.5°	12.3	12.2	11.9	11.9	11.6	11.6	11.6
85°	6.3	6.1	6.5	6.1	6.3	5.9	6.3
87.5°	3.6	3.7	3.6	3.6	3.6	3.9	3.6
90°	9.5	9.8	10.1	10.2	10.4	10.5	10.7
92.5°	10.6	11.2	11.4	11.6	11.6	11.7	11.8
95°	12.7	13.2	13.5	13.5	13.5	13.5	13.5
97.5°	13.4	14.0	14.3	14.4	14.5	14.6	14.7
100°	13.6	14.3	14.7	14.7	14.8	14.9	15.0
102.5°	17.5	15.6	14.7	14.8	15.0	15.1	15.2
105°	36.0	21.9	15.1	15.2	15.4	15.5	15.7
107.5°	112.1	101.8	91.4	80.8	70.3	59.7	49.2
110°	152.7	150.0	143.1	131.8	120.5	109.2	97.9



TEST NUMBER: P332390-927

CATALOG NUMBER: S123RDIW-S340D460U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	178.6	178.6	177.4	175.1	172.7	170.3	167.9
115°	206.7	207.5	208.0	208.3	208.7	209.0	209.3
117.5°	231.2	231.9	232.2	232.3	232.3	232.4	232.5
120°	247.5	248.1	248.4	248.4	248.4	248.4	248.4
122.5°	263.2	263.6	263.8	263.9	264.0	264.0	264.1
125°	285.2	285.3	285.5	285.7	285.8	286.0	286.1
127.5°	307.7	307.9	308.0	307.8	307.7	307.5	307.4
130°	321.2	321.5	321.6	321.5	321.3	321.2	321.0
132.5°	334.1	334.4	334.5	334.2	334.0	333.7	333.6
135°	353.4	353.6	353.6	353.4	353.2	352.9	352.7
137.5°	370.8	371.2	371.4	371.2	371.1	370.9	370.7
140°	381.8	382.1	382.1	382.0	381.8	381.7	381.5
142.5°	392.1	392.4	392.4	392.1	392.0	391.7	391.5
145°	406.5	406.7	406.8	406.8	406.8	406.8	406.8
147.5°	419.6	419.8	419.6	419.3	418.9	418.6	418.2
150°	427.5	427.7	427.7	427.5	427.2	427.0	426.7
152.5°	434.7	435.1	435.0	434.7	434.3	434.0	433.6
155°	444.7	445.0	445.0	444.5	444.0	443.5	443.1
157.5°	453.2	453.7	453.6	453.0	452.4	451.8	451.1
160°	458.0	458.5	458.5	458.0	457.4	456.9	456.3
162.5°	462.6	463.0	463.1	462.6	462.1	461.6	461.1
165°	468.5	469.1	469.1	468.6	468.1	467.5	467.0
167.5°	473.0	473.6	473.6	473.0	472.5	471.8	471.2
170°	475.6	476.3	476.3	475.6	475.0	474.4	473.7
172.5°	477.3	477.9	477.9	477.2	476.5	475.9	475.2
175°	479.3	479.8	479.8	479.2	478.6	477.9	477.3
177.5°	480.0	480.5	480.5	479.8	479.2	478.6	477.9
180°	479.0	479.0	479.0	479.0	479.0	479.0	479.0

(END OF REPORT)