

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332396

Luminaire Tested: **S123RDIW-S340D755U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332396
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D755U835-4F0-1E-UDD-F
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4321.1 lumens
Efficiency: N/A
Efficacy: 142.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332396

CATALOG NUMBER: S123RDIW-S340D755U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P332396

CATALOG NUMBER: S123RDIW-S340D755U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	89	86	82	84	80	77	74	63	61	60	48	47	45	34	33	32	26
2	85	78	72	68	76	70	66	61	56	52	50	42	40	38	30	29	27	22
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24	19
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20	16
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	11
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	16	14	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6184	6184	6184
5°	6207	6122	6158
10°	6172	6045	6025
15°	6107	5904	5841
20°	6015	5727	5593
25°	5922	5529	5352
30°	5797	5299	5009
35°	5670	5070	4696
40°	5552	4799	4308
45°	5398	4532	3958
50°	5228	4228	3565
55°	5054	3883	3200
60°	4895	3511	2799
65°	4689	3110	2397
70°	4428	2609	1936
75°	4051	2054	1822
80°	3608	1822	1674
85°	3051	1606	1494



TEST NUMBER: P332396

CATALOG NUMBER: S123RDIW-S340D755U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	1.2
10°-20°	150.1	3.5
20°-30°	216.1	5.0
30°-40°	243.5	5.6
40°-50°	232.9	5.4
50°-60°	190.7	4.4
60°-70°	128.7	3.0
70°-80°	64.7	1.5
80°-90°	19.9	0.5
90°-100°	36.0	0.8
100°-110°	171.6	4.0
110°-120°	412.3	9.5
120°-130°	525.0	12.1
130°-140°	560.9	13.0
140°-150°	524.5	12.1
150°-160°	423.1	9.8
160°-170°	273.1	6.3
170°-180°	94.1	2.2
0°-30°	420.2	9.7
0°-40°	663.7	15.4
0°-60°	1087.3	25.2
0°-90°	1300.6	30.1
90°-120°	619.9	14.3
90°-150°	2230.2	51.6
90°-180°	3020.0	69.9
0°-180°	4321.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	574	574	574	574	574	
5°	574	572	567	570	570	54
15°	548	542	530	527	524	154
25°	499	486	466	456	451	229
35°	432	414	386	366	357	270
45°	355	333	298	272	260	273
55°	269	246	207	181	170	241
65°	184	158	122	100	94	182
75°	97	75	49	45	44	104
85°	25	15	13	12	12	28
90°	1	8	18	21	22	3
95°	45	17	23	28	28	55
105°	219	223	161	38	32	232
115°	411	416	422	430	433	406
125°	580	586	589	590	592	518
135°	722	726	729	731	729	555
145°	833	838	840	841	841	521
155°	918	916	917	920	916	423
165°	968	966	965	970	965	273
175°	990	987	988	992	987	94
180°	990	990	990	990	990	



TEST NUMBER: P332396

CATALOG NUMBER: S123RDIW-S340D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	576.4	576.0	575.7	575.4	575.1	574.4	573.4	572.4	571.4	570.4	571.3
5°	574.5	574.0	573.5	573.0	572.4	571.6	570.3	569.1	567.8	566.6	567.5
7.5°	569.2	568.6	568.1	567.5	567.0	565.9	564.3	562.7	561.0	559.4	559.9
10°	564.7	564.0	563.3	562.6	561.8	560.5	558.7	556.8	554.9	553.1	553.2
12.5°	558.4	557.6	556.8	556.0	555.2	553.6	551.3	549.1	546.8	544.5	544.4
15°	548.0	546.8	545.7	544.5	543.4	541.4	538.5	535.6	532.7	529.8	529.3
17.5°	534.8	533.5	532.2	530.8	529.5	527.0	523.3	519.6	516.0	512.3	511.2
20°	525.1	523.5	521.8	520.2	518.5	515.7	511.8	507.8	503.9	500.0	498.6
22.5°	514.3	512.4	510.5	508.6	506.7	503.7	499.5	495.3	491.1	486.9	485.2
25°	498.6	496.0	493.4	490.8	488.2	484.5	479.8	475.0	470.2	465.5	463.3
27.5°	479.5	476.6	473.7	470.9	468.0	464.0	458.7	453.3	448.0	442.7	439.7
30°	466.4	463.3	460.2	457.1	454.0	449.5	443.7	437.9	432.1	426.3	422.8
32.5°	453.4	449.8	446.3	442.8	439.3	434.5	428.3	422.2	416.1	409.9	406.1
35°	431.5	427.7	424.0	420.3	416.6	411.5	405.1	398.6	392.2	385.8	381.4
37.5°	409.3	405.1	401.0	396.9	392.7	387.2	380.4	373.5	366.7	359.8	354.8
40°	395.1	390.6	386.0	381.5	376.9	370.9	363.6	356.2	348.9	341.5	336.2
42.5°	379.1	374.5	370.0	365.4	360.9	354.8	347.2	339.6	332.0	324.4	318.5
45°	354.6	349.9	345.3	340.6	335.9	329.6	321.7	313.7	305.7	297.7	291.8
47.5°	330.1	325.0	319.8	314.7	309.6	303.1	295.1	287.1	279.2	271.2	264.8
50°	312.2	307.3	302.5	297.6	292.7	286.1	277.7	269.3	260.9	252.5	246.1
52.5°	296.2	290.9	285.6	280.3	275.0	268.2	259.9	251.6	243.3	235.0	228.4
55°	269.3	264.2	259.2	254.1	249.0	242.1	233.3	224.5	215.7	206.9	200.9
57.5°	244.5	239.0	233.5	227.9	222.4	215.2	206.4	197.5	188.7	179.9	174.2
60°	227.4	221.7	216.0	210.3	204.6	197.5	188.9	180.3	171.7	163.1	157.5
62.5°	210.2	204.5	198.8	193.2	187.5	180.3	171.7	163.1	154.5	145.9	140.7
65°	184.1	178.4	172.7	167.0	161.3	154.4	146.3	138.2	130.2	122.1	117.0
67.5°	157.9	152.1	146.3	140.6	134.8	128.1	120.3	112.6	104.8	97.1	93.3
70°	140.7	135.1	129.5	123.9	118.4	111.9	104.7	97.4	90.2	82.9	79.3
72.5°	123.6	118.1	112.6	107.0	101.5	95.5	88.9	82.3	75.7	69.1	66.2
75°	97.4	92.4	87.4	82.5	77.5	72.2	66.5	60.8	55.1	49.4	48.4
77.5°	73.5	69.0	64.5	60.0	55.6	51.5	47.8	44.1	40.5	36.8	36.3
80°	58.2	54.0	49.8	45.5	41.3	38.1	35.9	33.7	31.5	29.4	29.0
82.5°	43.7	40.0	36.4	32.7	29.0	26.7	25.7	24.7	23.7	22.6	22.3
85°	24.7	22.4	20.1	17.9	15.6	14.3	14.0	13.7	13.4	13.0	12.8
87.5°	9.1	8.5	7.9	7.3	6.8	6.7	7.1	7.5	8.0	8.4	8.4
90°	0.7	2.4	4.0	5.6	7.3	9.2	11.3	13.4	15.5	17.7	18.3
92.5°	13.7	13.2	12.8	12.3	11.9	12.4	14.0	15.6	17.2	18.8	19.9
95°	44.9	38.2	31.5	24.8	18.1	15.6	17.4	19.2	21.0	22.8	24.0
97.5°	90.2	87.2	84.2	81.2	78.2	70.8	59.0	47.2	35.5	23.7	25.0
100°	124.4	127.6	130.9	134.2	137.4	126.3	100.8	75.3	49.8	24.3	25.6
102.5°	163.2	165.6	167.9	170.3	172.6	159.9	132.0	104.1	76.3	48.4	44.4
105°	219.3	221.1	222.9	224.7	226.5	220.0	205.3	190.6	175.9	161.2	132.2
107.5°	278.4	279.9	281.3	282.8	284.2	286.1	288.4	290.7	293.1	295.4	274.1
110°	317.9	319.2	320.5	321.8	323.1	324.7	326.5	328.3	330.1	331.9	326.5



TEST NUMBER: P332396

CATALOG NUMBER: S123RDIW-S340D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	355.6	356.7	357.9	359.1	360.3	361.8	363.6	365.4	367.2	369.0	369.1
115°	411.3	412.3	413.3	414.3	415.3	416.5	418.0	419.4	420.9	422.4	424.0
117.5°	465.4	466.6	467.8	469.0	470.2	471.2	471.9	472.7	473.4	474.2	475.5
120°	498.9	500.4	501.9	503.3	504.8	505.8	506.3	506.8	507.3	507.7	509.1
122.5°	533.1	534.3	535.5	536.7	537.9	538.8	539.4	540.1	540.7	541.3	542.2
125°	579.9	581.2	582.5	583.8	585.1	586.1	586.7	587.4	588.0	588.7	589.0
127.5°	625.2	626.5	627.8	629.1	630.4	631.5	632.3	633.0	633.8	634.6	635.1
130°	653.4	654.8	656.1	657.4	658.7	659.7	660.3	661.0	661.6	662.3	662.9
132.5°	680.5	681.8	683.1	684.4	685.8	686.7	687.2	687.7	688.2	688.8	689.4
135°	721.9	722.9	723.8	724.8	725.8	726.6	727.3	727.9	728.6	729.2	729.7
137.5°	757.2	758.4	759.7	760.9	762.2	763.0	763.3	763.7	764.1	764.4	765.2
140°	780.7	781.7	782.7	783.7	784.7	785.4	785.9	786.4	786.9	787.4	788.0
142.5°	802.5	803.5	804.5	805.5	806.5	807.2	807.7	808.2	808.7	809.2	809.7
145°	833.0	834.1	835.3	836.4	837.6	838.3	838.6	839.0	839.3	839.6	839.9
147.5°	861.7	862.4	863.2	863.9	864.7	865.2	865.6	865.9	866.2	866.5	866.9
150°	879.4	879.8	880.3	880.8	881.3	881.7	882.1	882.4	882.7	883.0	883.4
152.5°	895.2	895.5	895.7	895.9	896.2	896.4	896.6	896.8	897.0	897.2	897.7
155°	917.6	917.3	917.0	916.6	916.3	916.2	916.4	916.6	916.7	916.9	917.7
157.5°	935.0	935.0	934.9	934.9	934.9	934.8	934.6	934.4	934.3	934.1	935.1
160°	945.6	945.4	945.3	945.1	944.9	944.8	944.6	944.4	944.3	944.1	945.1
162.5°	955.6	955.2	954.7	954.3	953.9	953.6	953.4	953.3	953.1	952.9	954.1
165°	967.7	967.2	966.7	966.2	965.7	965.4	965.2	965.0	964.9	964.7	966.0
167.5°	977.1	976.4	975.8	975.1	974.5	974.1	974.1	974.1	974.1	974.1	975.4
170°	982.4	981.7	981.1	980.4	979.8	979.4	979.4	979.4	979.4	979.4	980.7
172.5°	985.9	985.1	984.3	983.6	982.8	982.4	982.6	982.7	982.8	983.0	984.3
175°	990.5	989.6	988.8	988.0	987.2	986.9	987.0	987.2	987.4	987.5	988.7
177.5°	991.6	991.0	990.3	989.7	989.0	988.8	988.9	989.0	989.2	989.3	990.3
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5



TEST NUMBER: P332396

CATALOG NUMBER: S123RDIW-S340D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	574.5	574.5	574.5	574.5	574.5	574.5	574.5	574.5
2.5°	572.2	573.1	574.1	574.4	574.3	574.1	573.9	573.8
5°	568.5	569.4	570.3	570.7	570.5	570.3	570.1	569.9
7.5°	560.5	561.0	561.5	561.6	561.2	560.9	560.5	560.2
10°	553.3	553.4	553.5	553.3	552.8	552.3	551.7	551.2
12.5°	544.4	544.3	544.3	543.9	543.3	542.7	542.1	541.5
15°	528.7	528.2	527.7	527.1	526.4	525.6	524.9	524.2
17.5°	510.1	509.0	507.9	506.8	505.7	504.6	503.6	502.5
20°	497.3	495.9	494.6	493.3	492.0	490.8	489.6	488.3
22.5°	483.6	481.9	480.2	478.8	477.6	476.5	475.3	474.2
25°	461.1	459.0	456.8	455.1	454.0	452.9	451.7	450.6
27.5°	436.7	433.7	430.7	428.3	426.5	424.8	423.1	421.3
30°	419.3	415.8	412.3	409.7	408.0	406.4	404.7	403.0
32.5°	402.2	398.4	394.5	391.7	390.0	388.3	386.5	384.8
35°	376.9	372.4	368.0	364.8	363.0	361.1	359.2	357.4
37.5°	349.7	344.6	339.6	335.9	333.6	331.3	329.0	326.7
40°	330.8	325.4	320.0	316.1	313.7	311.4	309.0	306.6
42.5°	312.6	306.8	300.9	296.9	294.7	292.6	290.5	288.3
45°	285.9	280.0	274.1	269.9	267.5	265.0	262.5	260.0
47.5°	258.3	251.9	245.5	241.2	239.0	236.8	234.5	232.3
50°	239.7	233.3	226.9	222.5	220.1	217.7	215.3	212.9
52.5°	221.7	215.0	208.4	204.0	201.8	199.7	197.6	195.4
55°	194.9	188.9	182.9	178.8	176.8	174.7	172.6	170.5
57.5°	168.5	162.8	157.2	153.4	151.7	149.9	148.2	146.4
60°	151.9	146.3	140.7	137.0	135.3	133.5	131.8	130.0
62.5°	135.4	130.2	124.9	121.3	119.5	117.7	115.8	114.0
65°	111.9	106.9	101.8	98.7	97.5	96.4	95.3	94.1
67.5°	89.5	85.7	81.9	79.4	78.2	77.0	75.8	74.6
70°	75.7	72.1	68.4	66.1	64.9	63.8	62.6	61.5
72.5°	63.2	60.3	57.3	55.6	55.1	54.6	54.2	53.7
75°	47.3	46.3	45.2	44.6	44.4	44.2	44.0	43.8
77.5°	35.7	35.1	34.6	34.2	34.0	33.8	33.6	33.4
80°	28.7	28.4	28.1	27.9	27.6	27.4	27.2	27.0
82.5°	22.0	21.7	21.4	21.2	21.2	21.1	21.1	21.1
85°	12.6	12.4	12.2	12.1	12.1	12.1	12.1	12.1
87.5°	8.5	8.5	8.6	8.6	8.6	8.6	8.5	8.5
90°	19.0	19.6	20.3	20.8	21.1	21.4	21.7	22.1
92.5°	20.9	22.0	23.0	23.6	23.8	24.0	24.2	24.4
95°	25.1	26.2	27.4	28.0	28.0	28.0	28.0	28.0
97.5°	26.3	27.6	28.9	29.7	29.8	30.0	30.2	30.3
100°	26.9	28.2	29.5	30.3	30.4	30.6	30.7	30.9
102.5°	40.3	36.3	32.2	30.3	30.6	30.9	31.2	31.5
105°	103.3	74.3	45.4	31.1	31.4	31.7	32.1	32.4
107.5°	252.9	231.7	210.5	189.0	167.1	145.3	123.5	101.7
110°	321.1	315.7	310.3	295.9	272.5	249.1	225.7	202.4



TEST NUMBER: P332396

CATALOG NUMBER: S123RDIW-S340D755U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	369.2	369.3	369.4	366.9	362.0	357.1	352.1	347.2
115°	425.7	427.3	428.9	430.1	430.7	431.4	432.0	432.7
117.5°	476.8	478.1	479.4	480.1	480.3	480.4	480.5	480.7
120°	510.4	511.7	513.0	513.6	513.6	513.6	513.6	513.6
122.5°	543.1	544.0	545.0	545.5	545.6	545.7	545.9	546.0
125°	589.3	589.7	590.0	590.3	590.7	591.0	591.3	591.6
127.5°	635.7	636.2	636.7	636.8	636.5	636.1	635.8	635.5
130°	663.6	664.2	664.9	665.1	664.7	664.4	664.1	663.7
132.5°	690.1	690.7	691.4	691.5	691.0	690.6	690.1	689.6
135°	730.2	730.7	731.2	731.2	730.7	730.2	729.7	729.2
137.5°	766.0	766.8	767.6	767.8	767.5	767.1	766.8	766.5
140°	788.7	789.3	790.0	790.2	789.8	789.5	789.2	788.8
142.5°	810.2	810.7	811.2	811.3	810.8	810.4	809.9	809.4
145°	840.3	840.6	840.9	841.1	841.1	841.1	841.1	841.1
147.5°	867.2	867.5	867.9	867.6	866.9	866.1	865.4	864.6
150°	883.7	884.0	884.3	884.3	883.8	883.3	882.8	882.3
152.5°	898.3	898.9	899.5	899.4	898.7	897.9	897.2	896.4
155°	918.5	919.3	920.2	920.1	919.1	918.1	917.1	916.1
157.5°	936.1	937.0	938.0	937.9	936.6	935.3	934.1	932.8
160°	946.1	947.1	948.0	948.0	946.8	945.7	944.5	943.4
162.5°	955.2	956.3	957.4	957.4	956.4	955.4	954.4	953.4
165°	967.3	968.6	969.9	970.0	968.9	967.7	966.6	965.4
167.5°	976.7	978.1	979.4	979.4	978.1	976.7	975.4	974.1
170°	982.0	983.4	984.7	984.7	983.4	982.0	980.7	979.4
172.5°	985.6	986.9	988.2	988.1	986.7	985.3	983.8	982.4
175°	989.8	991.0	992.1	992.0	990.7	989.4	988.1	986.8
177.5°	991.4	992.4	993.5	993.3	992.0	990.7	989.4	988.1
180°	990.5	990.5	990.5	990.5	990.5	990.5	990.5	990.5

(END OF REPORT)