

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332418

Luminaire Tested: **S123RDIW-S560D1030U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332418  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S560D1030U835-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6354.3 lumens  
Efficiency: N/A  
Efficacy: 140.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	31	26
3	79	70	63	58	71	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	27	25	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	15
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14	11
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9630	9630	9630	9630
5°	11480	9672	8518	9672
10°	14335	9616	7695	9616
15°	16826	9518	7017	9518
20°	18778	9371	6441	9371
25°	18478	9216	6087	9216
30°	13282	9073	5722	9073
35°	8868	8888	5486	8888
40°	6534	8665	5243	8665
45°	5480	8273	5002	8273
50°	4836	7762	4669	7762
55°	4241	7174	4211	7174
60°	3776	6613	3860	6613
65°	3316	6008	3591	6008
70°	2603	5473	3279	5473
75°	2296	4779	2994	4779
80°	1996	4060	2944	4060
85°	1606	3260	3125	3260



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.0	1.4
10°-20°	274.9	4.3
20°-30°	431.9	6.8
30°-40°	450.6	7.1
40°-50°	385.6	6.1
50°-60°	293.9	4.6
60°-70°	188.4	3.0
70°-80°	90.6	1.4
80°-90°	27.8	0.4
90°-100°	49.2	0.8
100°-110°	234.3	3.7
110°-120°	562.7	8.9
120°-130°	716.5	11.3
130°-140°	765.6	12.0
140°-150°	715.9	11.3
150°-160°	577.5	9.1
160°-170°	372.7	5.9
170°-180°	128.4	2.0
0°-30°	794.7	12.5
0°-40°	1245.3	19.6
0°-60°	1924.8	30.3
0°-90°	2231.5	35.1
90°-120°	846.1	13.3
90°-150°	3044.1	47.9
90°-180°	4123.0	64.9
0°-180°	6354.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	895	895	895	895	895	
5°	1062	895	788	895	1062	110
15°	1510	854	630	854	1510	428
25°	1556	776	512	776	1556	669
35°	675	676	418	676	675	442
45°	360	544	329	544	360	283
55°	226	382	224	382	226	204
65°	130	236	141	236	130	128
75°	55	115	72	115	55	59
85°	13	26	25	26	13	16
90°	30	1	30	1	30	14
95°	38	61	38	61	38	32
105°	44	299	44	299	44	101
115°	591	562	591	562	591	546
125°	808	792	808	792	808	721
135°	995	985	995	985	995	767
145°	1148	1137	1148	1137	1148	717
155°	1250	1252	1250	1252	1250	577
165°	1318	1321	1318	1321	1318	372
175°	1347	1352	1347	1352	1347	128
180°	1352	1352	1352	1352	1352	



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	952.9	954.2	950.2	949.6	945.0	943.8	943.8	937.3	933.3	928.1	925.1
5°	1062.5	1068.6	1065.6	1058.7	1047.2	1044.5	1037.2	1025.7	1012.7	996.6	989.0
7.5°	1199.3	1207.7	1204.4	1193.8	1181.8	1172.0	1151.5	1132.4	1105.7	1082.3	1062.2
10°	1311.5	1302.6	1295.8	1285.4	1274.3	1256.3	1234.9	1205.4	1171.3	1144.5	1114.6
12.5°	1395.4	1394.0	1385.2	1374.6	1358.9	1341.8	1315.4	1279.5	1239.9	1201.1	1167.0
15°	1509.9	1512.2	1506.4	1495.3	1473.1	1442.8	1403.0	1388.1	1331.4	1289.2	1247.1
17.5°	1589.1	1588.6	1587.8	1572.4	1549.8	1528.2	1491.3	1452.0	1400.7	1341.3	1284.6
20°	1639.3	1635.5	1636.3	1619.0	1602.2	1577.3	1541.3	1484.2	1442.1	1373.5	1314.9
22.5°	1638.1	1637.3	1640.2	1634.3	1622.1	1603.0	1574.7	1526.5	1472.7	1403.5	1337.6
25°	1555.8	1552.8	1570.8	1575.7	1595.3	1598.7	1590.3	1563.9	1512.9	1441.7	1360.1
27.5°	1302.1	1300.4	1333.8	1375.6	1428.7	1469.9	1509.7	1528.9	1512.9	1461.9	1380.2
30°	1068.6	1104.6	1121.5	1182.0	1249.4	1329.8	1400.3	1467.3	1483.8	1461.6	1394.6
32.5°	887.2	918.6	932.7	984.7	1047.5	1141.7	1247.4	1342.3	1409.4	1426.4	1386.0
35°	674.9	675.3	707.4	730.4	788.6	885.5	988.2	1115.3	1241.7	1337.5	1347.5
37.5°	538.5	540.4	559.9	582.8	626.5	677.7	768.1	873.8	1019.8	1166.8	1253.0
40°	465.0	468.4	483.0	505.6	537.0	575.7	646.2	745.7	867.5	1031.1	1164.8
42.5°	417.8	423.4	430.9	448.3	467.7	504.0	561.0	637.9	748.6	903.3	1057.5
45°	360.0	363.1	368.8	376.9	394.5	419.8	458.1	509.8	601.7	726.2	880.6
47.5°	317.6	316.0	322.0	328.6	340.3	357.5	383.2	425.4	491.0	590.8	721.8
50°	288.8	288.4	292.6	297.6	308.7	321.4	342.4	374.2	426.3	509.0	628.9
52.5°	261.8	263.3	266.3	272.5	280.5	290.7	309.6	332.5	377.3	448.7	548.6
55°	226.0	227.1	231.3	234.8	240.5	250.9	262.8	281.9	312.5	362.3	444.7
57.5°	195.6	195.1	199.2	200.0	206.5	214.9	224.1	239.0	261.2	298.2	353.7
60°	175.4	174.3	177.7	180.4	183.8	190.7	198.4	213.0	230.6	257.8	305.3
62.5°	157.0	156.5	159.0	161.7	164.5	170.8	177.3	188.4	202.4	225.3	263.0
65°	130.2	131.4	132.5	133.7	135.2	139.0	145.2	152.8	162.4	178.5	205.7
67.5°	102.3	103.5	103.9	106.2	109.5	111.9	115.7	122.5	129.2	142.7	158.2
70°	82.7	82.3	82.7	83.9	88.1	92.3	97.3	102.3	106.5	116.1	129.1
72.5°	71.1	70.4	71.4	71.6	73.7	74.8	78.0	82.7	88.1	94.6	104.0
75°	55.2	55.2	55.2	55.2	56.7	57.5	58.6	59.8	61.7	64.7	71.6
77.5°	40.8	40.8	41.4	41.7	42.1	42.5	43.2	44.4	45.0	46.7	49.6
80°	32.2	32.6	32.2	32.6	32.6	33.3	33.7	34.9	35.2	37.2	38.3
82.5°	24.2	24.0	24.2	24.6	24.6	25.4	25.4	26.3	26.4	27.3	28.5
85°	13.0	12.3	13.0	12.6	13.4	12.6	13.0	13.8	13.8	14.2	15.7
87.5°	9.1	9.6	8.9	9.1	9.0	9.2	9.0	8.9	9.3	8.8	8.5
90°	30.1	29.7	29.2	28.8	28.3	27.7	26.8	25.9	25.0	24.1	21.2
92.5°	33.3	33.1	32.8	32.5	32.3	31.4	30.0	28.6	27.1	25.7	23.5
95°	38.2	38.2	38.2	38.2	38.2	37.4	35.8	34.3	32.7	31.1	28.7
97.5°	41.4	41.2	40.9	40.7	40.5	39.5	37.7	35.9	34.1	32.3	28.4
100°	42.2	42.0	41.7	41.5	41.3	40.3	38.5	36.7	34.9	33.1	28.0
102.5°	43.0	42.6	42.2	41.8	41.4	43.9	49.5	55.0	60.6	66.1	104.1
105°	44.2	43.7	43.3	42.9	42.4	61.9	101.4	141.0	180.5	220.0	240.1
107.5°	138.8	168.6	198.4	228.1	257.9	287.3	316.3	345.2	374.2	403.2	400.0
110°	276.2	308.1	340.0	372.0	403.9	423.5	430.9	438.3	445.6	453.0	450.5



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	473.9	480.6	487.4	494.1	500.8	504.1	504.0	503.9	503.7	503.6	501.2
115°	590.6	589.7	588.8	587.9	587.0	585.5	583.2	581.0	578.8	576.5	574.5
117.5°	656.1	655.9	655.7	655.5	655.4	654.4	652.6	650.8	649.0	647.2	646.2
120°	701.1	701.1	701.1	701.1	701.1	700.2	698.4	696.6	694.8	693.0	692.4
122.5°	745.3	745.1	744.9	744.7	744.6	743.8	742.6	741.3	740.1	738.8	738.0
125°	807.5	807.1	806.6	806.2	805.8	805.3	804.9	804.4	804.0	803.5	802.6
127.5°	867.4	867.9	868.3	868.7	869.2	869.1	868.3	867.6	866.9	866.2	865.1
130°	906.0	906.4	906.9	907.3	907.8	907.5	906.6	905.8	904.9	904.0	903.1
132.5°	941.3	942.0	942.6	943.2	943.8	943.7	942.8	941.9	941.0	940.1	939.4
135°	995.4	996.0	996.7	997.4	998.0	998.0	997.4	996.7	996.0	995.4	994.5
137.5°	1046.2	1046.6	1047.1	1047.5	1048.0	1047.7	1046.6	1045.5	1044.4	1043.4	1042.9
140°	1076.7	1077.2	1077.6	1078.1	1078.5	1078.3	1077.4	1076.5	1075.6	1074.7	1074.0
142.5°	1104.8	1105.5	1106.1	1106.7	1107.3	1107.3	1106.6	1105.9	1105.2	1104.4	1103.8
145°	1148.0	1148.0	1148.0	1148.0	1148.0	1147.8	1147.4	1146.9	1146.5	1146.0	1145.6
147.5°	1180.2	1181.2	1182.2	1183.3	1184.3	1184.6	1184.1	1183.7	1183.2	1182.8	1182.3
150°	1204.3	1205.0	1205.6	1206.3	1207.0	1207.1	1206.6	1206.2	1205.7	1205.3	1204.8
152.5°	1223.6	1224.6	1225.6	1226.6	1227.7	1227.8	1227.0	1226.2	1225.4	1224.6	1224.3
155°	1250.5	1251.8	1253.2	1254.5	1255.8	1256.0	1254.8	1253.7	1252.6	1251.5	1251.3
157.5°	1273.2	1274.9	1276.7	1278.4	1280.1	1280.3	1279.0	1277.7	1276.3	1275.0	1275.2
160°	1287.6	1289.2	1290.8	1292.3	1293.9	1294.0	1292.7	1291.3	1290.0	1288.7	1288.9
162.5°	1301.3	1302.7	1304.1	1305.5	1306.8	1306.8	1305.3	1303.7	1302.2	1300.7	1300.9
165°	1317.8	1319.3	1320.9	1322.5	1324.0	1323.9	1322.1	1320.3	1318.6	1316.8	1317.0
167.5°	1329.6	1331.4	1333.2	1335.0	1336.8	1336.8	1335.0	1333.2	1331.4	1329.6	1329.6
170°	1336.9	1338.6	1340.4	1342.2	1344.0	1344.0	1342.2	1340.4	1338.6	1336.9	1336.9
172.5°	1340.9	1342.8	1344.8	1346.8	1348.7	1348.8	1347.0	1345.3	1343.5	1341.7	1341.5
175°	1346.9	1348.7	1350.5	1352.3	1354.1	1354.2	1352.6	1351.0	1349.5	1347.9	1347.7
177.5°	1348.7	1350.5	1352.3	1354.1	1355.9	1356.0	1354.6	1353.2	1351.8	1350.3	1350.1
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	923.8	922.9	918.6	913.7	907.3	903.0	899.6	897.8	892.3	885.5	880.9
5°	980.9	969.4	957.2	942.2	928.4	914.3	905.5	895.1	882.5	868.3	858.3
7.5°	1042.0	1019.5	995.2	970.2	945.4	923.2	903.6	886.8	866.7	846.4	832.1
10°	1088.9	1056.0	1021.9	987.0	955.2	925.4	902.4	879.8	855.7	832.3	814.7
12.5°	1131.5	1088.2	1048.9	1006.0	965.4	929.7	896.6	870.0	841.0	816.1	796.0
15°	1185.4	1141.0	1093.5	1028.4	974.4	929.2	889.0	854.1	818.9	788.3	768.7
17.5°	1235.8	1169.0	1105.2	1050.8	980.7	924.2	875.1	833.4	794.8	762.3	738.2
20°	1256.7	1192.0	1122.6	1053.3	984.4	921.2	864.1	818.1	777.9	741.1	718.9
22.5°	1269.2	1195.9	1122.9	1048.4	975.2	909.5	853.1	802.5	758.9	724.0	696.6
25°	1283.9	1196.5	1116.1	1042.6	967.9	896.6	829.6	776.0	728.9	691.7	662.6
27.5°	1293.5	1190.8	1095.7	1014.0	938.2	867.3	805.9	749.0	701.2	661.9	630.7
30°	1295.4	1186.2	1080.1	991.6	914.6	849.5	784.4	730.0	679.5	637.7	608.6
32.5°	1297.8	1174.9	1059.0	965.0	886.2	821.7	762.7	710.7	658.9	617.8	588.1
35°	1287.7	1168.6	1026.9	918.9	840.0	777.5	724.3	676.4	625.5	585.6	555.4
37.5°	1244.2	1143.7	993.6	866.9	784.4	726.6	683.2	641.5	594.8	551.8	523.3
40°	1200.4	1119.2	967.9	835.4	749.2	689.8	650.7	616.7	571.5	531.2	500.6
42.5°	1135.1	1085.8	943.4	802.3	709.3	652.1	619.2	587.2	547.6	506.7	477.9
45°	1015.4	1021.9	893.2	749.6	654.2	596.7	565.7	543.5	508.3	474.6	445.1
47.5°	865.2	926.1	834.3	693.4	596.1	542.1	515.0	495.6	471.9	438.8	411.9
50°	767.2	854.1	787.1	655.7	559.6	506.0	479.2	463.5	442.8	416.7	391.1
52.5°	676.8	770.2	730.1	613.7	520.1	471.0	444.8	431.9	415.5	391.0	367.8
55°	551.9	646.5	637.3	550.4	460.8	416.7	396.8	382.3	371.1	352.8	334.4
57.5°	446.4	536.1	540.9	479.9	408.5	365.0	347.9	336.9	329.6	315.8	298.8
60°	380.0	462.3	478.4	432.4	371.1	332.8	316.0	307.2	301.4	290.3	277.3
62.5°	324.8	394.9	413.1	380.0	335.3	299.4	286.3	277.8	273.9	264.3	252.8
65°	248.6	306.8	324.4	306.0	282.7	253.9	243.2	235.9	232.5	227.1	218.7
67.5°	186.9	229.4	248.7	235.7	227.3	209.1	202.3	198.4	195.3	191.7	184.6
70°	150.1	181.6	201.5	198.0	191.1	181.6	176.6	173.9	170.8	167.8	161.6
72.5°	120.7	142.3	161.0	162.8	157.1	155.2	150.8	149.7	147.8	144.2	140.8
75°	80.1	95.0	108.0	113.0	115.3	117.2	115.3	114.9	114.5	111.5	109.5
77.5°	52.5	60.5	68.7	77.2	80.8	83.4	84.0	85.4	84.4	82.8	81.9
80°	40.2	42.1	47.9	55.2	60.9	63.2	64.7	65.5	65.1	64.7	63.2
82.5°	29.2	30.8	33.5	38.6	43.4	47.3	48.2	48.0	48.9	49.1	47.9
85°	15.7	16.1	16.9	17.6	20.3	24.5	25.7	26.4	27.2	27.2	24.9
87.5°	8.6	7.7	7.7	7.2	7.7	7.5	8.9	10.0	10.8	10.0	10.4
90°	18.3	15.4	12.5	9.9	7.7	5.5	3.2	1.0	3.2	5.5	7.7
92.5°	21.3	19.2	17.0	16.2	16.8	17.4	18.1	18.7	18.1	17.4	16.8
95°	26.2	23.8	21.3	24.7	33.8	43.0	52.1	61.3	52.1	43.0	33.8
97.5°	64.5	80.6	96.6	106.7	110.8	114.9	119.0	123.1	119.0	114.9	110.8
100°	102.8	137.6	172.4	187.6	183.1	178.7	174.2	169.7	174.2	178.7	183.1
102.5°	142.2	180.2	218.2	235.6	232.4	229.2	226.0	222.8	226.0	229.2	232.4
105°	260.1	280.2	300.3	309.1	306.7	304.2	301.8	299.3	301.8	304.2	306.7
107.5°	396.8	393.7	390.5	387.9	386.0	384.0	382.0	380.1	382.0	384.0	386.0
110°	448.1	445.6	443.2	441.0	439.3	437.5	435.7	433.9	435.7	437.5	439.3





TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	498.7	496.2	493.8	491.8	490.2	488.5	486.9	485.3	486.9	488.5	490.2
115°	572.5	570.5	568.5	566.8	565.5	564.1	562.8	561.5	562.8	564.1	565.5
117.5°	645.2	644.2	643.1	641.8	640.1	638.5	636.8	635.2	636.8	638.5	640.1
120°	691.7	691.0	690.4	689.0	687.0	685.0	683.0	681.0	683.0	685.0	687.0
122.5°	737.1	736.3	735.4	734.2	732.5	730.9	729.2	727.6	729.2	730.9	732.5
125°	801.7	800.8	800.0	798.6	796.8	795.0	793.3	791.5	793.3	795.0	796.8
127.5°	864.1	863.0	861.9	860.5	858.7	856.9	855.1	853.3	855.1	856.9	858.7
130°	902.2	901.3	900.4	899.1	897.3	895.5	893.7	891.9	893.7	895.5	897.3
132.5°	938.7	938.0	937.3	936.0	934.2	932.4	930.7	928.9	930.7	932.4	934.2
135°	993.6	992.7	991.8	990.7	989.3	988.0	986.7	985.3	986.7	988.0	989.3
137.5°	1042.4	1041.9	1041.4	1040.3	1038.6	1036.9	1035.2	1033.5	1035.2	1036.9	1038.6
140°	1073.4	1072.7	1072.0	1071.0	1069.7	1068.4	1067.0	1065.7	1067.0	1068.4	1069.7
142.5°	1103.1	1102.4	1101.8	1100.8	1099.4	1098.1	1096.7	1095.4	1096.7	1098.1	1099.4
145°	1145.1	1144.7	1144.2	1143.2	1141.7	1140.1	1138.5	1137.0	1138.5	1140.1	1141.7
147.5°	1181.9	1181.4	1181.0	1180.3	1179.2	1178.2	1177.2	1176.2	1177.2	1178.2	1179.2
150°	1204.4	1203.9	1203.5	1202.9	1202.3	1201.6	1200.9	1200.3	1200.9	1201.6	1202.3
152.5°	1224.0	1223.8	1223.5	1223.2	1222.9	1222.6	1222.3	1222.0	1222.3	1222.6	1222.9
155°	1251.0	1250.8	1250.6	1250.7	1251.2	1251.6	1252.0	1252.5	1252.0	1251.6	1251.2
157.5°	1275.4	1275.7	1275.9	1276.0	1276.1	1276.1	1276.2	1276.2	1276.2	1276.1	1276.1
160°	1289.1	1289.3	1289.5	1289.8	1290.0	1290.2	1290.4	1290.7	1290.4	1290.2	1290.0
162.5°	1301.2	1301.4	1301.6	1302.0	1302.6	1303.2	1303.7	1304.3	1303.7	1303.2	1302.6
165°	1317.2	1317.4	1317.7	1318.1	1318.8	1319.5	1320.1	1320.8	1320.1	1319.5	1318.8
167.5°	1329.6	1329.6	1329.6	1330.1	1331.0	1331.9	1332.8	1333.6	1332.8	1331.9	1331.0
170°	1336.9	1336.9	1336.9	1337.3	1338.2	1339.1	1340.0	1340.9	1340.0	1339.1	1338.2
172.5°	1341.3	1341.1	1341.0	1341.4	1342.5	1343.6	1344.6	1345.7	1344.6	1343.6	1342.5
175°	1347.5	1347.2	1347.0	1347.5	1348.6	1349.7	1350.8	1351.9	1350.8	1349.7	1348.6
177.5°	1350.0	1349.8	1349.6	1350.0	1350.9	1351.8	1352.6	1353.5	1352.6	1351.8	1350.9
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	879.4	875.4	872.7	866.5	862.6	858.3	854.0	856.7	856.4	856.1	856.1
5°	849.9	841.1	833.1	822.7	816.2	808.2	802.0	801.3	802.8	797.4	794.4
7.5°	820.7	808.6	797.2	785.8	773.7	764.0	758.0	755.2	751.3	748.0	744.5
10°	800.1	786.0	774.8	760.7	747.7	736.2	728.9	723.9	721.2	718.5	713.6
12.5°	779.0	765.1	750.9	734.9	722.5	709.2	703.8	698.2	693.0	690.0	683.2
15°	748.0	730.0	715.1	698.2	684.5	671.4	663.8	652.7	651.1	647.3	640.4
17.5°	717.0	697.5	676.9	664.4	648.8	635.3	623.6	619.9	608.9	604.8	598.8
20°	692.5	674.5	658.8	642.3	619.7	607.1	597.9	592.9	584.1	578.7	574.9
22.5°	671.4	653.0	634.9	615.7	597.0	582.9	576.1	568.4	563.6	556.1	551.9
25°	641.2	621.3	599.4	578.7	565.3	554.6	543.9	537.0	530.1	526.6	519.0
27.5°	606.1	585.3	564.9	549.2	532.7	522.1	512.4	506.3	498.0	492.2	488.0
30°	586.8	562.3	544.7	530.5	509.4	499.5	492.2	484.5	478.4	472.3	468.0
32.5°	564.4	542.0	525.3	507.8	491.6	480.8	471.3	464.6	459.4	453.6	449.4
35°	529.3	510.6	493.3	475.7	463.8	452.7	441.6	435.9	430.9	425.5	421.7
37.5°	497.6	480.1	463.7	447.0	432.3	423.2	414.3	409.9	403.2	399.6	395.7
40°	478.0	460.8	443.2	427.1	411.7	404.9	396.8	390.3	384.2	381.5	377.3
42.5°	456.6	439.3	424.5	407.1	394.6	385.2	377.8	370.7	366.1	362.2	359.8
45°	424.8	409.4	394.9	377.7	365.8	357.7	349.3	342.8	338.6	335.9	331.7
47.5°	393.9	378.6	363.8	348.8	337.3	328.1	319.7	315.1	309.6	306.3	303.4
50°	371.5	357.7	342.0	328.2	316.8	307.6	300.7	294.9	289.9	285.7	283.8
52.5°	351.0	336.3	322.7	309.9	297.8	287.3	281.1	275.0	271.3	266.4	264.2
55°	317.1	303.0	291.5	278.8	267.0	258.2	250.5	245.1	241.3	235.9	232.9
57.5°	285.3	272.6	258.9	248.0	235.7	228.3	221.9	214.6	210.0	205.8	202.8
60°	263.9	249.3	237.5	227.1	216.4	206.8	201.1	195.3	190.4	186.1	183.5
62.5°	241.5	228.8	217.6	206.3	196.5	188.1	181.5	176.6	172.3	169.6	166.9
65°	207.2	197.3	185.8	176.6	167.4	161.3	155.9	151.7	148.6	146.7	144.4
67.5°	175.7	166.0	156.0	146.9	140.8	136.1	132.6	129.0	127.5	125.0	123.5
70°	155.1	145.2	136.4	129.5	123.3	119.9	117.6	114.9	113.4	110.3	108.8
72.5°	132.8	125.6	119.2	113.5	108.6	105.5	102.6	99.3	96.8	93.5	91.9
75°	104.6	98.1	93.1	89.2	86.2	82.0	77.8	74.3	73.2	72.0	71.6
77.5°	77.4	73.3	69.7	66.5	62.7	59.6	58.7	57.9	57.7	57.1	57.1
80°	60.9	57.1	54.4	50.6	48.3	48.3	48.3	47.5	47.9	47.9	47.9
82.5°	45.3	41.7	40.3	38.9	38.5	38.8	38.8	38.9	38.7	39.3	39.0
85°	23.4	23.7	24.5	24.1	24.5	24.5	25.3	24.9	25.3	24.5	25.3
87.5°	10.6	12.0	12.9	13.8	14.7	14.9	15.4	15.6	16.1	16.3	16.4
90°	9.9	12.5	15.4	18.3	21.2	24.1	25.0	25.9	26.8	27.7	28.3
92.5°	16.2	17.0	19.2	21.3	23.5	25.7	27.1	28.6	30.0	31.4	32.3
95°	24.7	21.3	23.8	26.2	28.7	31.1	32.7	34.3	35.8	37.4	38.2
97.5°	106.7	96.6	80.6	64.5	48.4	32.3	34.1	35.9	37.7	39.5	40.5
100°	187.6	172.4	137.6	102.8	68.0	33.1	34.9	36.7	38.5	40.3	41.3
102.5°	235.6	218.2	180.2	142.2	104.1	66.1	60.6	55.0	49.5	43.9	41.4
105°	309.1	300.3	280.2	260.1	240.1	220.0	180.5	141.0	101.4	61.9	42.4
107.5°	387.9	390.5	393.7	396.8	400.0	403.2	374.2	345.2	316.3	287.3	257.9
110°	441.0	443.2	445.6	448.1	450.5	453.0	445.6	438.3	430.9	423.5	403.9



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	491.8	493.8	496.2	498.7	501.2	503.6	503.7	503.9	504.0	504.1	500.8
115°	566.8	568.5	570.5	572.5	574.5	576.5	578.8	581.0	583.2	585.5	587.0
117.5°	641.8	643.1	644.2	645.2	646.2	647.2	649.0	650.8	652.6	654.4	655.4
120°	689.0	690.4	691.0	691.7	692.4	693.0	694.8	696.6	698.4	700.2	701.1
122.5°	734.2	735.4	736.3	737.1	738.0	738.8	740.1	741.3	742.6	743.8	744.6
125°	798.6	800.0	800.8	801.7	802.6	803.5	804.0	804.4	804.9	805.3	805.8
127.5°	860.5	861.9	863.0	864.1	865.1	866.2	866.9	867.6	868.3	869.1	869.2
130°	899.1	900.4	901.3	902.2	903.1	904.0	904.9	905.8	906.6	907.5	907.8
132.5°	936.0	937.3	938.0	938.7	939.4	940.1	941.0	941.9	942.8	943.7	943.8
135°	990.7	991.8	992.7	993.6	994.5	995.4	996.0	996.7	997.4	998.0	998.0
137.5°	1040.3	1041.4	1041.9	1042.4	1042.9	1043.4	1044.4	1045.5	1046.6	1047.7	1048.0
140°	1071.0	1072.0	1072.7	1073.4	1074.0	1074.7	1075.6	1076.5	1077.4	1078.3	1078.5
142.5°	1100.8	1101.8	1102.4	1103.1	1103.8	1104.4	1105.2	1105.9	1106.6	1107.3	1107.3
145°	1143.2	1144.2	1144.7	1145.1	1145.6	1146.0	1146.5	1146.9	1147.4	1147.8	1148.0
147.5°	1180.3	1181.0	1181.4	1181.9	1182.3	1182.8	1183.2	1183.7	1184.1	1184.6	1184.3
150°	1202.9	1203.5	1203.9	1204.4	1204.8	1205.3	1205.7	1206.2	1206.6	1207.1	1207.0
152.5°	1223.2	1223.5	1223.8	1224.0	1224.3	1224.6	1225.4	1226.2	1227.0	1227.8	1227.7
155°	1250.7	1250.6	1250.8	1251.0	1251.3	1251.5	1252.6	1253.7	1254.8	1256.0	1255.8
157.5°	1276.0	1275.9	1275.7	1275.4	1275.2	1275.0	1276.3	1277.7	1279.0	1280.3	1280.1
160°	1289.8	1289.5	1289.3	1289.1	1288.9	1288.7	1290.0	1291.3	1292.7	1294.0	1293.9
162.5°	1302.0	1301.6	1301.4	1301.2	1300.9	1300.7	1302.2	1303.7	1305.3	1306.8	1306.8
165°	1318.1	1317.7	1317.4	1317.2	1317.0	1316.8	1318.6	1320.3	1322.1	1323.9	1324.0
167.5°	1330.1	1329.6	1329.6	1329.6	1329.6	1329.6	1331.4	1333.2	1335.0	1336.8	1336.8
170°	1337.3	1336.9	1336.9	1336.9	1336.9	1336.9	1338.6	1340.4	1342.2	1344.0	1344.0
172.5°	1341.4	1341.0	1341.1	1341.3	1341.5	1341.7	1343.5	1345.3	1347.0	1348.8	1348.7
175°	1347.5	1347.0	1347.2	1347.5	1347.7	1347.9	1349.5	1351.0	1352.6	1354.2	1354.1
177.5°	1350.0	1349.6	1349.8	1350.0	1350.1	1350.3	1351.8	1353.2	1354.6	1356.0	1355.9
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	852.4	852.1	852.4	851.2	852.4	852.1	852.4	856.1	856.1	856.4	856.7
5°	793.2	792.8	791.7	788.3	791.7	792.8	793.2	794.4	797.4	802.8	801.3
7.5°	741.5	741.0	737.6	737.7	737.6	741.0	741.5	744.5	748.0	751.3	755.2
10°	710.9	711.3	706.7	704.0	706.7	711.3	710.9	713.6	718.5	721.2	723.9
12.5°	681.2	679.4	675.7	672.7	675.7	679.4	681.2	683.2	690.0	693.0	698.2
15°	641.9	638.1	628.9	629.7	628.9	638.1	641.9	640.4	647.3	651.1	652.7
17.5°	595.7	592.9	592.8	587.4	592.8	592.9	595.7	598.8	604.8	608.9	619.9
20°	568.8	566.9	567.6	562.3	567.6	566.9	568.8	574.9	578.7	584.1	592.9
22.5°	547.6	545.7	542.5	540.8	542.5	545.7	547.6	551.9	556.1	563.6	568.4
25°	516.7	513.6	510.6	512.5	510.6	513.6	516.7	519.0	526.6	530.1	537.0
27.5°	485.7	483.4	480.4	480.0	480.4	483.4	485.7	488.0	492.2	498.0	506.3
30°	466.1	463.8	462.3	460.4	462.3	463.8	466.1	468.0	472.3	478.4	484.5
32.5°	446.2	445.8	443.0	442.6	443.0	445.8	446.2	449.4	453.6	459.4	464.6
35°	420.2	417.9	417.1	417.5	417.1	417.9	420.2	421.7	425.5	430.9	435.9
37.5°	395.4	392.4	391.0	389.6	391.0	392.4	395.4	395.7	399.6	403.2	409.9
40°	377.7	374.6	373.8	373.1	373.8	374.6	377.7	377.3	381.5	384.2	390.3
42.5°	357.7	356.5	356.1	354.7	356.1	356.5	357.7	359.8	362.2	366.1	370.7
45°	330.5	330.2	327.9	328.6	327.9	330.2	330.5	331.7	335.9	338.6	342.8
47.5°	301.9	300.2	298.6	299.7	298.6	300.2	301.9	303.4	306.3	309.6	315.1
50°	282.3	281.5	278.1	278.8	278.1	281.5	282.3	283.8	285.7	289.9	294.9
52.5°	262.7	259.8	258.5	258.0	258.5	259.8	262.7	264.2	266.4	271.3	275.0
55°	230.2	226.7	225.2	224.4	225.2	226.7	230.2	232.9	235.9	241.3	245.1
57.5°	198.3	197.4	196.2	197.0	196.2	197.4	198.3	202.8	205.8	210.0	214.6
60°	179.6	179.6	179.6	179.3	179.6	179.6	179.6	183.5	186.1	190.4	195.3
62.5°	165.2	164.3	164.0	164.5	164.0	164.3	165.2	166.9	169.6	172.3	176.6
65°	143.2	142.9	141.3	141.0	141.3	142.9	143.2	144.4	146.7	148.6	151.7
67.5°	122.5	121.1	120.7	120.1	120.7	121.1	122.5	123.5	125.0	127.5	129.0
70°	106.9	106.1	103.8	104.2	103.8	106.1	106.9	108.8	110.3	113.4	114.9
72.5°	90.0	89.2	88.8	88.2	88.8	89.2	90.0	91.9	93.5	96.8	99.3
75°	71.2	70.9	70.5	72.0	70.5	70.9	71.2	71.6	72.0	73.2	74.3
77.5°	57.1	57.1	57.3	56.7	57.3	57.1	57.1	57.1	57.1	57.7	57.9
80°	47.9	47.9	47.5	47.5	47.5	47.9	47.9	47.9	47.9	47.9	47.5
82.5°	38.4	38.7	38.9	38.3	38.9	38.7	38.4	39.0	39.3	38.7	38.9
85°	25.3	24.9	25.7	25.3	25.7	24.9	25.3	25.3	24.5	25.3	24.9
87.5°	17.1	16.6	16.7	17.1	16.7	16.6	17.1	16.4	16.3	16.1	15.6
90°	28.8	29.2	29.7	30.1	29.7	29.2	28.8	28.3	27.7	26.8	25.9
92.5°	32.5	32.8	33.1	33.3	33.1	32.8	32.5	32.3	31.4	30.0	28.6
95°	38.2	38.2	38.2	38.2	38.2	38.2	38.2	38.2	37.4	35.8	34.3
97.5°	40.7	40.9	41.2	41.4	41.2	40.9	40.7	40.5	39.5	37.7	35.9
100°	41.5	41.7	42.0	42.2	42.0	41.7	41.5	41.3	40.3	38.5	36.7
102.5°	41.8	42.2	42.6	43.0	42.6	42.2	41.8	41.4	43.9	49.5	55.0
105°	42.9	43.3	43.7	44.2	43.7	43.3	42.9	42.4	61.9	101.4	141.0
107.5°	228.1	198.4	168.6	138.8	168.6	198.4	228.1	257.9	287.3	316.3	345.2
110°	372.0	340.0	308.1	276.2	308.1	340.0	372.0	403.9	423.5	430.9	438.3



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	494.1	487.4	480.6	473.9	480.6	487.4	494.1	500.8	504.1	504.0	503.9
115°	587.9	588.8	589.7	590.6	589.7	588.8	587.9	587.0	585.5	583.2	581.0
117.5°	655.5	655.7	655.9	656.1	655.9	655.7	655.5	655.4	654.4	652.6	650.8
120°	701.1	701.1	701.1	701.1	701.1	701.1	701.1	701.1	700.2	698.4	696.6
122.5°	744.7	744.9	745.1	745.3	745.1	744.9	744.7	744.6	743.8	742.6	741.3
125°	806.2	806.6	807.1	807.5	807.1	806.6	806.2	805.8	805.3	804.9	804.4
127.5°	868.7	868.3	867.9	867.4	867.9	868.3	868.7	869.2	869.1	868.3	867.6
130°	907.3	906.9	906.4	906.0	906.4	906.9	907.3	907.8	907.5	906.6	905.8
132.5°	943.2	942.6	942.0	941.3	942.0	942.6	943.2	943.8	943.7	942.8	941.9
135°	997.4	996.7	996.0	995.4	996.0	996.7	997.4	998.0	998.0	997.4	996.7
137.5°	1047.5	1047.1	1046.6	1046.2	1046.6	1047.1	1047.5	1048.0	1047.7	1046.6	1045.5
140°	1078.1	1077.6	1077.2	1076.7	1077.2	1077.6	1078.1	1078.5	1078.3	1077.4	1076.5
142.5°	1106.7	1106.1	1105.5	1104.8	1105.5	1106.1	1106.7	1107.3	1107.3	1106.6	1105.9
145°	1148.0	1148.0	1148.0	1148.0	1148.0	1148.0	1148.0	1148.0	1147.8	1147.4	1146.9
147.5°	1183.3	1182.2	1181.2	1180.2	1181.2	1182.2	1183.3	1184.3	1184.6	1184.1	1183.7
150°	1206.3	1205.6	1205.0	1204.3	1205.0	1205.6	1206.3	1207.0	1207.1	1206.6	1206.2
152.5°	1226.6	1225.6	1224.6	1223.6	1224.6	1225.6	1226.6	1227.7	1227.8	1227.0	1226.2
155°	1254.5	1253.2	1251.8	1250.5	1251.8	1253.2	1254.5	1255.8	1256.0	1254.8	1253.7
157.5°	1278.4	1276.7	1274.9	1273.2	1274.9	1276.7	1278.4	1280.1	1280.3	1279.0	1277.7
160°	1292.3	1290.8	1289.2	1287.6	1289.2	1290.8	1292.3	1293.9	1294.0	1292.7	1291.3
162.5°	1305.5	1304.1	1302.7	1301.3	1302.7	1304.1	1305.5	1306.8	1306.8	1305.3	1303.7
165°	1322.5	1320.9	1319.3	1317.8	1319.3	1320.9	1322.5	1324.0	1323.9	1322.1	1320.3
167.5°	1335.0	1333.2	1331.4	1329.6	1331.4	1333.2	1335.0	1336.8	1336.8	1335.0	1333.2
170°	1342.2	1340.4	1338.6	1336.9	1338.6	1340.4	1342.2	1344.0	1344.0	1342.2	1340.4
172.5°	1346.8	1344.8	1342.8	1340.9	1342.8	1344.8	1346.8	1348.7	1348.8	1347.0	1345.3
175°	1352.3	1350.5	1348.7	1346.9	1348.7	1350.5	1352.3	1354.1	1354.2	1352.6	1351.0
177.5°	1354.1	1352.3	1350.5	1348.7	1350.5	1352.3	1354.1	1355.9	1356.0	1354.6	1353.2
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	854.0	858.3	862.6	866.5	872.7	875.4	879.4	880.9	885.5	892.3	897.8
5°	802.0	808.2	816.2	822.7	833.1	841.1	849.9	858.3	868.3	882.5	895.1
7.5°	758.0	764.0	773.7	785.8	797.2	808.6	820.7	832.1	846.4	866.7	886.8
10°	728.9	736.2	747.7	760.7	774.8	786.0	800.1	814.7	832.3	855.7	879.8
12.5°	703.8	709.2	722.5	734.9	750.9	765.1	779.0	796.0	816.1	841.0	870.0
15°	663.8	671.4	684.5	698.2	715.1	730.0	748.0	768.7	788.3	818.9	854.1
17.5°	623.6	635.3	648.8	664.4	676.9	697.5	717.0	738.2	762.3	794.8	833.4
20°	597.9	607.1	619.7	642.3	658.8	674.5	692.5	718.9	741.1	777.9	818.1
22.5°	576.1	582.9	597.0	615.7	634.9	653.0	671.4	696.6	724.0	758.9	802.5
25°	543.9	554.6	565.3	578.7	599.4	621.3	641.2	662.6	691.7	728.9	776.0
27.5°	512.4	522.1	532.7	549.2	564.9	585.3	606.1	630.7	661.9	701.2	749.0
30°	492.2	499.5	509.4	530.5	544.7	562.3	586.8	608.6	637.7	679.5	730.0
32.5°	471.3	480.8	491.6	507.8	525.3	542.0	564.4	588.1	617.8	658.9	710.7
35°	441.6	452.7	463.8	475.7	493.3	510.6	529.3	555.4	585.6	625.5	676.4
37.5°	414.3	423.2	432.3	447.0	463.7	480.1	497.6	523.3	551.8	594.8	641.5
40°	396.8	404.9	411.7	427.1	443.2	460.8	478.0	500.6	531.2	571.5	616.7
42.5°	377.8	385.2	394.6	407.1	424.5	439.3	456.6	477.9	506.7	547.6	587.2
45°	349.3	357.7	365.8	377.7	394.9	409.4	424.8	445.1	474.6	508.3	543.5
47.5°	319.7	328.1	337.3	348.8	363.8	378.6	393.9	411.9	438.8	471.9	495.6
50°	300.7	307.6	316.8	328.2	342.0	357.7	371.5	391.1	416.7	442.8	463.5
52.5°	281.1	287.3	297.8	309.9	322.7	336.3	351.0	367.8	391.0	415.5	431.9
55°	250.5	258.2	267.0	278.8	291.5	303.0	317.1	334.4	352.8	371.1	382.3
57.5°	221.9	228.3	235.7	248.0	258.9	272.6	285.3	298.8	315.8	329.6	336.9
60°	201.1	206.8	216.4	227.1	237.5	249.3	263.9	277.3	290.3	301.4	307.2
62.5°	181.5	188.1	196.5	206.3	217.6	228.8	241.5	252.8	264.3	273.9	277.8
65°	155.9	161.3	167.4	176.6	185.8	197.3	207.2	218.7	227.1	232.5	235.9
67.5°	132.6	136.1	140.8	146.9	156.0	166.0	175.7	184.6	191.7	195.3	198.4
70°	117.6	119.9	123.3	129.5	136.4	145.2	155.1	161.6	167.8	170.8	173.9
72.5°	102.6	105.5	108.6	113.5	119.2	125.6	132.8	140.8	144.2	147.8	149.7
75°	77.8	82.0	86.2	89.2	93.1	98.1	104.6	109.5	111.5	114.5	114.9
77.5°	58.7	59.6	62.7	66.5	69.7	73.3	77.4	81.9	82.8	84.4	85.4
80°	48.3	48.3	48.3	50.6	54.4	57.1	60.9	63.2	64.7	65.1	65.5
82.5°	38.8	38.8	38.5	38.9	40.3	41.7	45.3	47.9	49.1	48.9	48.0
85°	25.3	24.5	24.5	24.1	24.5	23.7	23.4	24.9	27.2	27.2	26.4
87.5°	15.4	14.9	14.7	13.8	12.9	12.0	10.6	10.4	10.0	10.8	10.0
90°	25.0	24.1	21.2	18.3	15.4	12.5	9.9	7.7	5.5	3.2	1.0
92.5°	27.1	25.7	23.5	21.3	19.2	17.0	16.2	16.8	17.4	18.1	18.7
95°	32.7	31.1	28.7	26.2	23.8	21.3	24.7	33.8	43.0	52.1	61.3
97.5°	34.1	32.3	48.4	64.5	80.6	96.6	106.7	110.8	114.9	119.0	123.1
100°	34.9	33.1	68.0	102.8	137.6	172.4	187.6	183.1	178.7	174.2	169.7
102.5°	60.6	66.1	104.1	142.2	180.2	218.2	235.6	232.4	229.2	226.0	222.8
105°	180.5	220.0	240.1	260.1	280.2	300.3	309.1	306.7	304.2	301.8	299.3
107.5°	374.2	403.2	400.0	396.8	393.7	390.5	387.9	386.0	384.0	382.0	380.1
110°	445.6	453.0	450.5	448.1	445.6	443.2	441.0	439.3	437.5	435.7	433.9



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	503.7	503.6	501.2	498.7	496.2	493.8	491.8	490.2	488.5	486.9	485.3
115°	578.8	576.5	574.5	572.5	570.5	568.5	566.8	565.5	564.1	562.8	561.5
117.5°	649.0	647.2	646.2	645.2	644.2	643.1	641.8	640.1	638.5	636.8	635.2
120°	694.8	693.0	692.4	691.7	691.0	690.4	689.0	687.0	685.0	683.0	681.0
122.5°	740.1	738.8	738.0	737.1	736.3	735.4	734.2	732.5	730.9	729.2	727.6
125°	804.0	803.5	802.6	801.7	800.8	800.0	798.6	796.8	795.0	793.3	791.5
127.5°	866.9	866.2	865.1	864.1	863.0	861.9	860.5	858.7	856.9	855.1	853.3
130°	904.9	904.0	903.1	902.2	901.3	900.4	899.1	897.3	895.5	893.7	891.9
132.5°	941.0	940.1	939.4	938.7	938.0	937.3	936.0	934.2	932.4	930.7	928.9
135°	996.0	995.4	994.5	993.6	992.7	991.8	990.7	989.3	988.0	986.7	985.3
137.5°	1044.4	1043.4	1042.9	1042.4	1041.9	1041.4	1040.3	1038.6	1036.9	1035.2	1033.5
140°	1075.6	1074.7	1074.0	1073.4	1072.7	1072.0	1071.0	1069.7	1068.4	1067.0	1065.7
142.5°	1105.2	1104.4	1103.8	1103.1	1102.4	1101.8	1100.8	1099.4	1098.1	1096.7	1095.4
145°	1146.5	1146.0	1145.6	1145.1	1144.7	1144.2	1143.2	1141.7	1140.1	1138.5	1137.0
147.5°	1183.2	1182.8	1182.3	1181.9	1181.4	1181.0	1180.3	1179.2	1178.2	1177.2	1176.2
150°	1205.7	1205.3	1204.8	1204.4	1203.9	1203.5	1202.9	1202.3	1201.6	1200.9	1200.3
152.5°	1225.4	1224.6	1224.3	1224.0	1223.8	1223.5	1223.2	1222.9	1222.6	1222.3	1222.0
155°	1252.6	1251.5	1251.3	1251.0	1250.8	1250.6	1250.7	1251.2	1251.6	1252.0	1252.5
157.5°	1276.3	1275.0	1275.2	1275.4	1275.7	1275.9	1276.0	1276.1	1276.1	1276.2	1276.2
160°	1290.0	1288.7	1288.9	1289.1	1289.3	1289.5	1289.8	1290.0	1290.2	1290.4	1290.7
162.5°	1302.2	1300.7	1300.9	1301.2	1301.4	1301.6	1302.0	1302.6	1303.2	1303.7	1304.3
165°	1318.6	1316.8	1317.0	1317.2	1317.4	1317.7	1318.1	1318.8	1319.5	1320.1	1320.8
167.5°	1331.4	1329.6	1329.6	1329.6	1329.6	1329.6	1330.1	1331.0	1331.9	1332.8	1333.6
170°	1338.6	1336.9	1336.9	1336.9	1336.9	1336.9	1337.3	1338.2	1339.1	1340.0	1340.9
172.5°	1343.5	1341.7	1341.5	1341.3	1341.1	1341.0	1341.4	1342.5	1343.6	1344.6	1345.7
175°	1349.5	1347.9	1347.7	1347.5	1347.2	1347.0	1347.5	1348.6	1349.7	1350.8	1351.9
177.5°	1351.8	1350.3	1350.1	1350.0	1349.8	1349.6	1350.0	1350.9	1351.8	1352.6	1353.5
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	899.6	903.0	907.3	913.7	918.6	922.9	923.8	925.1	928.1	933.3	937.3
5°	905.5	914.3	928.4	942.2	957.2	969.4	980.9	989.0	996.6	1012.7	1025.7
7.5°	903.6	923.2	945.4	970.2	995.2	1019.5	1042.0	1062.2	1082.3	1105.7	1132.4
10°	902.4	925.4	955.2	987.0	1021.9	1056.0	1088.9	1114.6	1144.5	1171.3	1205.4
12.5°	896.6	929.7	965.4	1006.0	1048.9	1088.2	1131.5	1167.0	1201.1	1239.9	1279.5
15°	889.0	929.2	974.4	1028.4	1093.5	1141.0	1185.4	1247.1	1289.2	1331.4	1388.1
17.5°	875.1	924.2	980.7	1050.8	1105.2	1169.0	1235.8	1284.6	1341.3	1400.7	1452.0
20°	864.1	921.2	984.4	1053.3	1122.6	1192.0	1256.7	1314.9	1373.5	1442.1	1484.2
22.5°	853.1	909.5	975.2	1048.4	1122.9	1195.9	1269.2	1337.6	1403.5	1472.7	1526.5
25°	829.6	896.6	967.9	1042.6	1116.1	1196.5	1283.9	1360.1	1441.7	1512.9	1563.9
27.5°	805.9	867.3	938.2	1014.0	1095.7	1190.8	1293.5	1380.2	1461.9	1512.9	1528.9
30°	784.4	849.5	914.6	991.6	1080.1	1186.2	1295.4	1394.6	1461.6	1483.8	1467.3
32.5°	762.7	821.7	886.2	965.0	1059.0	1174.9	1297.8	1386.0	1426.4	1409.4	1342.3
35°	724.3	777.5	840.0	918.9	1026.9	1168.6	1287.7	1347.5	1337.5	1241.7	1115.3
37.5°	683.2	726.6	784.4	866.9	993.6	1143.7	1244.2	1253.0	1166.8	1019.8	873.8
40°	650.7	689.8	749.2	835.4	967.9	1119.2	1200.4	1164.8	1031.1	867.5	745.7
42.5°	619.2	652.1	709.3	802.3	943.4	1085.8	1135.1	1057.5	903.3	748.6	637.9
45°	565.7	596.7	654.2	749.6	893.2	1021.9	1015.4	880.6	726.2	601.7	509.8
47.5°	515.0	542.1	596.1	693.4	834.3	926.1	865.2	721.8	590.8	491.0	425.4
50°	479.2	506.0	559.6	655.7	787.1	854.1	767.2	628.9	509.0	426.3	374.2
52.5°	444.8	471.0	520.1	613.7	730.1	770.2	676.8	548.6	448.7	377.3	332.5
55°	396.8	416.7	460.8	550.4	637.3	646.5	551.9	444.7	362.3	312.5	281.9
57.5°	347.9	365.0	408.5	479.9	540.9	536.1	446.4	353.7	298.2	261.2	239.0
60°	316.0	332.8	371.1	432.4	478.4	462.3	380.0	305.3	257.8	230.6	213.0
62.5°	286.3	299.4	335.3	380.0	413.1	394.9	324.8	263.0	225.3	202.4	188.4
65°	243.2	253.9	282.7	306.0	324.4	306.8	248.6	205.7	178.5	162.4	152.8
67.5°	202.3	209.1	227.3	235.7	248.7	229.4	186.9	158.2	142.7	129.2	122.5
70°	176.6	181.6	191.1	198.0	201.5	181.6	150.1	129.1	116.1	106.5	102.3
72.5°	150.8	155.2	157.1	162.8	161.0	142.3	120.7	104.0	94.6	88.1	82.7
75°	115.3	117.2	115.3	113.0	108.0	95.0	80.1	71.6	64.7	61.7	59.8
77.5°	84.0	83.4	80.8	77.2	68.7	60.5	52.5	49.6	46.7	45.0	44.4
80°	64.7	63.2	60.9	55.2	47.9	42.1	40.2	38.3	37.2	35.2	34.9
82.5°	48.2	47.3	43.4	38.6	33.5	30.8	29.2	28.5	27.3	26.4	26.3
85°	25.7	24.5	20.3	17.6	16.9	16.1	15.7	15.7	14.2	13.8	13.8
87.5°	8.9	7.5	7.7	7.2	7.7	7.7	8.6	8.5	8.8	9.3	8.9
90°	3.2	5.5	7.7	9.9	12.5	15.4	18.3	21.2	24.1	25.0	25.9
92.5°	18.1	17.4	16.8	16.2	17.0	19.2	21.3	23.5	25.7	27.1	28.6
95°	52.1	43.0	33.8	24.7	21.3	23.8	26.2	28.7	31.1	32.7	34.3
97.5°	119.0	114.9	110.8	106.7	96.6	80.6	64.5	48.4	32.3	34.1	35.9
100°	174.2	178.7	183.1	187.6	172.4	137.6	102.8	68.0	33.1	34.9	36.7
102.5°	226.0	229.2	232.4	235.6	218.2	180.2	142.2	104.1	66.1	60.6	55.0
105°	301.8	304.2	306.7	309.1	300.3	280.2	260.1	240.1	220.0	180.5	141.0
107.5°	382.0	384.0	386.0	387.9	390.5	393.7	396.8	400.0	403.2	374.2	345.2
110°	435.7	437.5	439.3	441.0	443.2	445.6	448.1	450.5	453.0	445.6	438.3





TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	486.9	488.5	490.2	491.8	493.8	496.2	498.7	501.2	503.6	503.7	503.9
115°	562.8	564.1	565.5	566.8	568.5	570.5	572.5	574.5	576.5	578.8	581.0
117.5°	636.8	638.5	640.1	641.8	643.1	644.2	645.2	646.2	647.2	649.0	650.8
120°	683.0	685.0	687.0	689.0	690.4	691.0	691.7	692.4	693.0	694.8	696.6
122.5°	729.2	730.9	732.5	734.2	735.4	736.3	737.1	738.0	738.8	740.1	741.3
125°	793.3	795.0	796.8	798.6	800.0	800.8	801.7	802.6	803.5	804.0	804.4
127.5°	855.1	856.9	858.7	860.5	861.9	863.0	864.1	865.1	866.2	866.9	867.6
130°	893.7	895.5	897.3	899.1	900.4	901.3	902.2	903.1	904.0	904.9	905.8
132.5°	930.7	932.4	934.2	936.0	937.3	938.0	938.7	939.4	940.1	941.0	941.9
135°	986.7	988.0	989.3	990.7	991.8	992.7	993.6	994.5	995.4	996.0	996.7
137.5°	1035.2	1036.9	1038.6	1040.3	1041.4	1041.9	1042.4	1042.9	1043.4	1044.4	1045.5
140°	1067.0	1068.4	1069.7	1071.0	1072.0	1072.7	1073.4	1074.0	1074.7	1075.6	1076.5
142.5°	1096.7	1098.1	1099.4	1100.8	1101.8	1102.4	1103.1	1103.8	1104.4	1105.2	1105.9
145°	1138.5	1140.1	1141.7	1143.2	1144.2	1144.7	1145.1	1145.6	1146.0	1146.5	1146.9
147.5°	1177.2	1178.2	1179.2	1180.3	1181.0	1181.4	1181.9	1182.3	1182.8	1183.2	1183.7
150°	1200.9	1201.6	1202.3	1202.9	1203.5	1203.9	1204.4	1204.8	1205.3	1205.7	1206.2
152.5°	1222.3	1222.6	1222.9	1223.2	1223.5	1223.8	1224.0	1224.3	1224.6	1225.4	1226.2
155°	1252.0	1251.6	1251.2	1250.7	1250.6	1250.8	1251.0	1251.3	1251.5	1252.6	1253.7
157.5°	1276.2	1276.1	1276.1	1276.0	1275.9	1275.7	1275.4	1275.2	1275.0	1276.3	1277.7
160°	1290.4	1290.2	1290.0	1289.8	1289.5	1289.3	1289.1	1288.9	1288.7	1290.0	1291.3
162.5°	1303.7	1303.2	1302.6	1302.0	1301.6	1301.4	1301.2	1300.9	1300.7	1302.2	1303.7
165°	1320.1	1319.5	1318.8	1318.1	1317.7	1317.4	1317.2	1317.0	1316.8	1318.6	1320.3
167.5°	1332.8	1331.9	1331.0	1330.1	1329.6	1329.6	1329.6	1329.6	1329.6	1331.4	1333.2
170°	1340.0	1339.1	1338.2	1337.3	1336.9	1336.9	1336.9	1336.9	1336.9	1338.6	1340.4
172.5°	1344.6	1343.6	1342.5	1341.4	1341.0	1341.1	1341.3	1341.5	1341.7	1343.5	1345.3
175°	1350.8	1349.7	1348.6	1347.5	1347.0	1347.2	1347.5	1347.7	1347.9	1349.5	1351.0
177.5°	1352.6	1351.8	1350.9	1350.0	1349.6	1349.8	1350.0	1350.1	1350.3	1351.8	1353.2
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	894.7	894.7	894.7	894.7	894.7	894.7	894.7
2.5°	943.8	943.8	945.0	949.6	950.2	954.2	952.9
5°	1037.2	1044.5	1047.2	1058.7	1065.6	1068.6	1062.5
7.5°	1151.5	1172.0	1181.8	1193.8	1204.4	1207.7	1199.3
10°	1234.9	1256.3	1274.3	1285.4	1295.8	1302.6	1311.5
12.5°	1315.4	1341.8	1358.9	1374.6	1385.2	1394.0	1395.4
15°	1403.0	1442.8	1473.1	1495.3	1506.4	1512.2	1509.9
17.5°	1491.3	1528.2	1549.8	1572.4	1587.8	1588.6	1589.1
20°	1541.3	1577.3	1602.2	1619.0	1636.3	1635.5	1639.3
22.5°	1574.7	1603.0	1622.1	1634.3	1640.2	1637.3	1638.1
25°	1590.3	1598.7	1595.3	1575.7	1570.8	1552.8	1555.8
27.5°	1509.7	1469.9	1428.7	1375.6	1333.8	1300.4	1302.1
30°	1400.3	1329.8	1249.4	1182.0	1121.5	1104.6	1068.6
32.5°	1247.4	1141.7	1047.5	984.7	932.7	918.6	887.2
35°	988.2	885.5	788.6	730.4	707.4	675.3	674.9
37.5°	768.1	677.7	626.5	582.8	559.9	540.4	538.5
40°	646.2	575.7	537.0	505.6	483.0	468.4	465.0
42.5°	561.0	504.0	467.7	448.3	430.9	423.4	417.8
45°	458.1	419.8	394.5	376.9	368.8	363.1	360.0
47.5°	383.2	357.5	340.3	328.6	322.0	316.0	317.6
50°	342.4	321.4	308.7	297.6	292.6	288.4	288.8
52.5°	309.6	290.7	280.5	272.5	266.3	263.3	261.8
55°	262.8	250.9	240.5	234.8	231.3	227.1	226.0
57.5°	224.1	214.9	206.5	200.0	199.2	195.1	195.6
60°	198.4	190.7	183.8	180.4	177.7	174.3	175.4
62.5°	177.3	170.8	164.5	161.7	159.0	156.5	157.0
65°	145.2	139.0	135.2	133.7	132.5	131.4	130.2
67.5°	115.7	111.9	109.5	106.2	103.9	103.5	102.3
70°	97.3	92.3	88.1	83.9	82.7	82.3	82.7
72.5°	78.0	74.8	73.7	71.6	71.4	70.4	71.1
75°	58.6	57.5	56.7	55.2	55.2	55.2	55.2
77.5°	43.2	42.5	42.1	41.7	41.4	40.8	40.8
80°	33.7	33.3	32.6	32.6	32.2	32.6	32.2
82.5°	25.4	25.4	24.6	24.6	24.2	24.0	24.2
85°	13.0	12.6	13.4	12.6	13.0	12.3	13.0
87.5°	9.0	9.2	9.0	9.1	8.9	9.6	9.1
90°	26.8	27.7	28.3	28.8	29.2	29.7	30.1
92.5°	30.0	31.4	32.3	32.5	32.8	33.1	33.3
95°	35.8	37.4	38.2	38.2	38.2	38.2	38.2
97.5°	37.7	39.5	40.5	40.7	40.9	41.2	41.4
100°	38.5	40.3	41.3	41.5	41.7	42.0	42.2
102.5°	49.5	43.9	41.4	41.8	42.2	42.6	43.0
105°	101.4	61.9	42.4	42.9	43.3	43.7	44.2
107.5°	316.3	287.3	257.9	228.1	198.4	168.6	138.8
110°	430.9	423.5	403.9	372.0	340.0	308.1	276.2



TEST NUMBER: P332418

CATALOG NUMBER: S123RDIW-S560D1030U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	504.0	504.1	500.8	494.1	487.4	480.6	473.9
115°	583.2	585.5	587.0	587.9	588.8	589.7	590.6
117.5°	652.6	654.4	655.4	655.5	655.7	655.9	656.1
120°	698.4	700.2	701.1	701.1	701.1	701.1	701.1
122.5°	742.6	743.8	744.6	744.7	744.9	745.1	745.3
125°	804.9	805.3	805.8	806.2	806.6	807.1	807.5
127.5°	868.3	869.1	869.2	868.7	868.3	867.9	867.4
130°	906.6	907.5	907.8	907.3	906.9	906.4	906.0
132.5°	942.8	943.7	943.8	943.2	942.6	942.0	941.3
135°	997.4	998.0	998.0	997.4	996.7	996.0	995.4
137.5°	1046.6	1047.7	1048.0	1047.5	1047.1	1046.6	1046.2
140°	1077.4	1078.3	1078.5	1078.1	1077.6	1077.2	1076.7
142.5°	1106.6	1107.3	1107.3	1106.7	1106.1	1105.5	1104.8
145°	1147.4	1147.8	1148.0	1148.0	1148.0	1148.0	1148.0
147.5°	1184.1	1184.6	1184.3	1183.3	1182.2	1181.2	1180.2
150°	1206.6	1207.1	1207.0	1206.3	1205.6	1205.0	1204.3
152.5°	1227.0	1227.8	1227.7	1226.6	1225.6	1224.6	1223.6
155°	1254.8	1256.0	1255.8	1254.5	1253.2	1251.8	1250.5
157.5°	1279.0	1280.3	1280.1	1278.4	1276.7	1274.9	1273.2
160°	1292.7	1294.0	1293.9	1292.3	1290.8	1289.2	1287.6
162.5°	1305.3	1306.8	1306.8	1305.5	1304.1	1302.7	1301.3
165°	1322.1	1323.9	1324.0	1322.5	1320.9	1319.3	1317.8
167.5°	1335.0	1336.8	1336.8	1335.0	1333.2	1331.4	1329.6
170°	1342.2	1344.0	1344.0	1342.2	1340.4	1338.6	1336.9
172.5°	1347.0	1348.8	1348.7	1346.8	1344.8	1342.8	1340.9
175°	1352.6	1354.2	1354.1	1352.3	1350.5	1348.7	1346.9
177.5°	1354.6	1356.0	1355.9	1354.1	1352.3	1350.5	1348.7
180°	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9	1351.9

(END OF REPORT)