

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332397-927

Luminaire Tested: **S123RDIW-S340D755U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P332397-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S123RDIW-S340D755U927-4F0-1E-UDD-F1
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 755 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3104.2 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332397-927

CATALOG NUMBER: S123RDIW-S340D755U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P332397-927

CATALOG NUMBER: S123RDIW-S340D755U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	28	25	22	21	19	17	14
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15	12
8	52	40	33	28	47	37	30	26	30	25	21	24	20	18	18	15	14	11
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4899	4899	4899
5°	4917	4850	4878
10°	4889	4790	4773
15°	4837	4677	4628
20°	4765	4537	4431
25°	4691	4380	4240
30°	4593	4197	3967
35°	4491	4016	3720
40°	4398	3801	3413
45°	4276	3589	3136
50°	4141	3349	2825
55°	4003	3076	2535
60°	3877	2781	2217
65°	3713	2463	1897
70°	3509	2068	1533
75°	3211	1626	1443
80°	2858	1444	1327
85°	2421	1272	1186



TEST NUMBER: P332397-927

CATALOG NUMBER: S123RDIW-S340D755U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	1.4
10°-20°	118.9	3.8
20°-30°	171.2	5.5
30°-40°	192.9	6.2
40°-50°	184.5	5.9
50°-60°	151.1	4.9
60°-70°	101.9	3.3
70°-80°	51.3	1.7
80°-90°	15.8	0.5
90°-100°	48.8	1.6
100°-110°	145.9	4.7
110°-120°	248.2	8.0
120°-130°	326.5	10.5
130°-140°	367.0	11.8
140°-150°	360.7	11.6
150°-160°	303.7	9.8
160°-170°	202.2	6.5
170°-180°	70.8	2.3
0°-30°	332.9	10.7
0°-40°	525.7	16.9
0°-60°	861.4	27.7
0°-90°	1030.4	33.2
90°-120°	442.9	14.3
90°-150°	1497.2	48.2
90°-180°	2074.0	66.8
0°-180°	3104.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	455	455	455	455	455	
5°	455	453	449	452	452	43
15°	434	430	420	418	415	122
25°	395	385	369	361	357	182
35°	342	328	306	290	283	214
45°	281	264	236	215	206	217
55°	213	195	164	143	135	191
65°	146	125	97	79	74	144
75°	77	59	39	36	35	82
85°	20	12	10	10	10	22
90°	1	7	14	16	18	3
95°	35	39	44	46	46	39
105°	132	134	139	139	140	142
115°	250	251	250	251	250	247
125°	366	367	366	364	362	326
135°	474	478	477	475	474	366
145°	576	577	579	578	576	359
155°	659	659	660	662	658	303
165°	718	716	716	719	716	202
175°	747	745	744	748	744	71
180°	748	748	748	748	748	



TEST NUMBER: P332397-927

CATALOG NUMBER: S123RDIW-S340D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	456.6	456.3	456.1	455.8	455.6	455.0	454.2	453.4	452.7	451.9	452.6
5°	455.1	454.7	454.3	453.9	453.4	452.8	451.8	450.8	449.8	448.9	449.6
7.5°	450.9	450.4	450.0	449.6	449.2	448.3	447.0	445.8	444.4	443.1	443.5
10°	447.3	446.8	446.2	445.7	445.0	444.0	442.6	441.1	439.6	438.2	438.2
12.5°	442.4	441.7	441.1	440.5	439.8	438.6	436.7	435.0	433.2	431.3	431.3
15°	434.1	433.2	432.3	431.3	430.5	428.9	426.6	424.3	422.0	419.7	419.3
17.5°	423.7	422.6	421.6	420.5	419.5	417.5	414.5	411.6	408.8	405.8	405.0
20°	416.0	414.7	413.4	412.1	410.7	408.5	405.4	402.3	399.2	396.1	395.0
22.5°	407.4	405.9	404.4	402.9	401.4	399.0	395.7	392.4	389.0	385.7	384.4
25°	395.0	392.9	390.9	388.8	386.7	383.8	380.1	376.3	372.5	368.8	367.0
27.5°	379.9	377.6	375.3	373.0	370.7	367.6	363.4	359.1	354.9	350.7	348.3
30°	369.5	367.0	364.6	362.1	359.7	356.1	351.5	346.9	342.3	337.7	334.9
32.5°	359.2	356.3	353.6	350.8	348.0	344.2	339.3	334.5	329.6	324.7	321.7
35°	341.8	338.8	335.9	333.0	330.0	326.0	320.9	315.8	310.7	305.6	302.1
37.5°	324.2	320.9	317.7	314.4	311.1	306.7	301.3	295.9	290.5	285.0	281.1
40°	313.0	309.4	305.8	302.2	298.6	293.8	288.0	282.2	276.4	270.5	266.3
42.5°	300.3	296.7	293.1	289.5	285.9	281.1	275.0	269.0	263.0	257.0	252.3
45°	280.9	277.2	273.5	269.8	266.1	261.1	254.8	248.5	242.2	235.8	231.2
47.5°	261.5	257.5	253.3	249.3	245.3	240.1	233.8	227.4	221.2	214.8	209.8
50°	247.3	243.4	239.6	235.8	231.9	226.6	220.0	213.3	206.7	200.0	195.0
52.5°	234.6	230.4	226.2	222.0	217.9	212.5	205.9	199.3	192.7	186.2	180.9
55°	213.3	209.3	205.3	201.3	197.3	191.8	184.8	177.8	170.9	163.9	159.1
57.5°	193.7	189.3	185.0	180.5	176.2	170.5	163.5	156.5	149.5	142.5	138.0
60°	180.1	175.6	171.1	166.6	162.1	156.5	149.6	142.8	136.0	129.2	124.8
62.5°	166.5	162.0	157.5	153.0	148.5	142.8	136.0	129.2	122.4	115.6	111.5
65°	145.8	141.3	136.8	132.3	127.8	122.3	115.9	109.5	103.1	96.7	92.7
67.5°	125.1	120.5	115.9	111.4	106.8	101.5	95.3	89.2	83.0	76.9	73.9
70°	111.5	107.0	102.6	98.2	93.8	88.6	82.9	77.2	71.5	65.7	62.8
72.5°	97.9	93.6	89.2	84.8	80.4	75.7	70.4	65.2	60.0	54.7	52.4
75°	77.2	73.2	69.2	65.4	61.4	57.2	52.7	48.2	43.6	39.1	38.3
77.5°	58.2	54.7	51.1	47.5	44.0	40.8	37.9	34.9	32.1	29.2	28.8
80°	46.1	42.8	39.5	36.0	32.7	30.2	28.4	26.7	25.0	23.3	23.0
82.5°	34.6	31.7	28.8	25.9	23.0	21.2	20.4	19.6	18.8	17.9	17.7
85°	19.6	17.7	15.9	14.2	12.4	11.3	11.1	10.9	10.6	10.3	10.1
87.5°	7.2	6.7	6.3	5.9	5.4	5.3	5.6	6.0	6.3	6.7	6.7
90°	0.6	1.9	3.2	4.5	5.8	7.3	9.0	10.7	12.4	14.1	14.7
92.5°	14.3	15.1	16.0	16.9	17.7	18.7	19.6	20.7	21.6	22.6	23.0
95°	34.7	35.6	36.5	37.5	38.3	39.3	40.4	41.4	42.5	43.5	44.0
97.5°	61.6	62.3	63.0	63.7	64.3	65.0	65.8	66.5	67.3	68.1	68.7
100°	79.9	80.7	81.5	82.3	83.1	83.8	84.4	85.2	85.8	86.4	86.8
102.5°	101.2	101.6	102.1	102.5	103.0	103.7	104.6	105.4	106.2	107.1	107.5
105°	132.3	132.5	132.8	133.1	133.3	134.0	135.2	136.4	137.6	138.8	138.8
107.5°	168.5	168.7	168.8	169.0	169.1	169.4	169.9	170.4	170.9	171.3	171.7
110°	191.1	191.4	191.6	191.9	192.1	192.4	192.7	192.9	193.2	193.5	194.0



TEST NUMBER: P332397-927

CATALOG NUMBER: S123RDIW-S340D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	214.6	214.8	214.9	215.1	215.2	215.3	215.4	215.5	215.5	215.6	216.2
115°	249.9	250.3	250.6	251.0	251.4	251.5	251.3	251.0	250.7	250.5	250.6
117.5°	285.4	285.7	285.9	286.2	286.5	286.5	286.1	285.7	285.4	285.0	285.0
120°	307.5	308.3	309.1	309.9	310.7	310.7	310.1	309.4	308.8	308.1	308.0
122.5°	330.6	331.1	331.7	332.3	332.9	333.0	332.6	332.3	332.0	331.6	331.3
125°	365.8	366.1	366.5	366.9	367.3	367.3	367.1	366.9	366.5	366.3	365.8
127.5°	398.2	399.0	399.9	400.7	401.6	401.8	401.6	401.2	400.9	400.7	399.9
130°	419.9	420.9	421.9	422.9	424.0	424.4	424.0	423.6	423.2	422.8	422.2
132.5°	441.5	442.5	443.5	444.6	445.7	446.0	445.8	445.4	445.1	444.9	444.3
135°	474.5	475.3	476.1	476.9	477.6	478.0	477.8	477.7	477.6	477.4	476.9
137.5°	505.1	505.7	506.4	507.1	507.7	508.2	508.5	508.9	509.2	509.5	509.0
140°	526.2	526.9	527.6	528.2	528.9	529.3	529.4	529.5	529.7	529.8	529.7
142.5°	545.6	546.2	546.8	547.5	548.1	548.6	548.8	549.1	549.3	549.5	549.4
145°	575.7	575.9	576.2	576.4	576.7	577.0	577.4	577.8	578.2	578.6	578.5
147.5°	602.0	602.5	602.9	603.4	603.9	604.3	604.7	605.0	605.4	605.8	605.8
150°	620.4	620.6	620.8	621.2	621.4	621.6	621.9	622.2	622.4	622.7	622.7
152.5°	635.4	635.7	636.1	636.5	636.8	637.1	637.2	637.4	637.5	637.7	637.9
155°	659.2	659.2	659.2	659.2	659.2	659.2	659.3	659.5	659.6	659.7	660.3
157.5°	679.4	679.2	679.1	678.9	678.7	678.7	678.8	678.9	679.1	679.1	679.7
160°	692.1	691.8	691.6	691.3	691.0	690.9	690.9	690.9	690.9	690.9	691.6
162.5°	703.4	703.0	702.6	702.3	701.9	701.8	701.9	702.0	702.1	702.2	702.8
165°	718.0	717.6	717.2	716.8	716.4	716.1	716.1	716.1	716.1	716.1	716.9
167.5°	729.6	729.0	728.6	728.0	727.5	727.3	727.4	727.5	727.6	727.7	728.5
170°	736.2	735.6	735.1	734.6	734.0	733.8	733.8	733.8	733.8	733.8	734.7
172.5°	741.3	740.8	740.3	739.7	739.3	738.9	738.9	738.9	738.9	738.9	739.8
175°	746.7	746.2	745.7	745.2	744.7	744.4	744.4	744.4	744.4	744.4	745.2
177.5°	749.0	748.5	748.1	747.7	747.3	747.1	747.1	747.1	747.1	747.1	747.7
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5



TEST NUMBER: P332397-927

CATALOG NUMBER: S123RDIW-S340D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	455.1	455.1	455.1	455.1	455.1	455.1	455.1	455.1
2.5°	453.3	454.0	454.8	455.0	455.0	454.8	454.6	454.6
5°	450.4	451.1	451.8	452.1	451.9	451.8	451.6	451.5
7.5°	444.0	444.4	444.8	444.9	444.6	444.3	444.0	443.8
10°	438.3	438.4	438.5	438.3	437.9	437.5	437.0	436.7
12.5°	431.3	431.2	431.2	430.9	430.4	429.9	429.4	429.0
15°	418.8	418.4	418.0	417.6	417.0	416.4	415.8	415.3
17.5°	404.1	403.2	402.3	401.5	400.6	399.7	398.9	398.1
20°	394.0	392.8	391.8	390.8	389.8	388.8	387.9	386.8
22.5°	383.1	381.8	380.4	379.3	378.3	377.5	376.5	375.7
25°	365.3	363.6	361.9	360.5	359.7	358.8	357.8	357.0
27.5°	345.9	343.6	341.2	339.3	337.9	336.5	335.2	333.7
30°	332.2	329.4	326.6	324.6	323.2	321.9	320.6	319.2
32.5°	318.6	315.6	312.5	310.3	309.0	307.6	306.2	304.8
35°	298.6	295.0	291.5	289.0	287.6	286.1	284.6	283.1
37.5°	277.0	273.0	269.0	266.1	264.3	262.4	260.6	258.8
40°	262.1	257.8	253.5	250.4	248.5	246.7	244.8	242.9
42.5°	247.6	243.0	238.4	235.2	233.5	231.8	230.1	228.4
45°	226.5	221.8	217.1	213.8	211.9	209.9	207.9	206.0
47.5°	204.6	199.6	194.5	191.1	189.3	187.6	185.8	184.0
50°	189.9	184.8	179.7	176.3	174.4	172.5	170.6	168.7
52.5°	175.6	170.3	165.1	161.6	159.9	158.2	156.5	154.8
55°	154.4	149.6	144.9	141.6	140.1	138.4	136.7	135.1
57.5°	133.5	129.0	124.5	121.5	120.2	118.7	117.4	116.0
60°	120.3	115.9	111.5	108.5	107.2	105.8	104.4	103.0
62.5°	107.3	103.1	98.9	96.1	94.7	93.2	91.7	90.3
65°	88.6	84.7	80.6	78.2	77.2	76.4	75.5	74.5
67.5°	70.9	67.9	64.9	62.9	61.9	61.0	60.0	59.1
70°	60.0	57.1	54.2	52.4	51.4	50.5	49.6	48.7
72.5°	50.1	47.8	45.4	44.0	43.6	43.3	42.9	42.5
75°	37.5	36.7	35.8	35.3	35.2	35.0	34.9	34.7
77.5°	28.3	27.8	27.4	27.1	26.9	26.8	26.6	26.5
80°	22.7	22.5	22.3	22.1	21.9	21.7	21.5	21.4
82.5°	17.4	17.2	17.0	16.8	16.8	16.7	16.7	16.7
85°	10.0	9.8	9.7	9.6	9.6	9.6	9.6	9.6
87.5°	6.7	6.8	6.8	6.8	6.8	6.8	6.8	6.8
90°	15.1	15.7	16.2	16.6	16.9	17.1	17.3	17.7
92.5°	23.4	23.8	24.2	24.4	24.2	24.1	23.9	23.8
95°	44.5	45.1	45.6	45.9	45.9	45.9	45.9	45.9
97.5°	69.3	69.9	70.5	70.7	70.7	70.7	70.6	70.6
100°	87.2	87.6	88.0	88.3	88.6	88.9	89.1	89.4
102.5°	107.9	108.3	108.7	108.8	108.8	108.8	108.7	108.7
105°	138.8	138.8	138.8	138.9	139.2	139.4	139.7	140.0
107.5°	172.1	172.6	173.0	173.2	173.0	172.9	172.7	172.5
110°	194.5	195.0	195.5	195.7	195.4	195.1	194.9	194.6



TEST NUMBER: P332397-927

CATALOG NUMBER: S123RDIW-S340D755U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	216.8	217.5	218.1	218.3	218.3	218.2	218.2	218.2
115°	250.7	250.9	251.0	251.0	250.9	250.7	250.6	250.5
117.5°	285.0	284.9	284.9	284.8	284.4	284.0	283.7	283.3
120°	307.8	307.7	307.6	307.4	307.1	306.9	306.6	306.3
122.5°	331.0	330.6	330.3	329.9	329.5	329.2	328.8	328.4
125°	365.3	364.7	364.2	363.7	363.2	362.7	362.1	361.6
127.5°	399.2	398.5	397.8	397.0	396.5	395.9	395.3	394.7
130°	421.8	421.2	420.6	419.9	419.1	418.1	417.2	416.3
132.5°	443.6	443.0	442.4	441.7	441.0	440.3	439.6	438.9
135°	476.4	475.9	475.4	475.0	474.7	474.4	474.2	473.9
137.5°	508.4	507.9	507.4	506.8	506.4	505.8	505.3	504.9
140°	529.5	529.4	529.3	528.7	527.8	526.9	526.0	525.1
142.5°	549.3	549.1	549.0	548.6	547.9	547.2	546.4	545.7
145°	578.3	578.2	578.1	577.7	577.2	576.7	576.2	575.7
147.5°	605.8	605.8	605.8	605.4	604.6	603.8	603.0	602.2
150°	622.7	622.7	622.7	622.3	621.5	620.8	620.0	619.2
152.5°	638.2	638.3	638.6	638.3	637.6	637.0	636.3	635.6
155°	660.8	661.3	661.8	661.6	660.7	659.8	658.9	658.0
157.5°	680.2	680.8	681.4	681.2	680.5	679.8	679.1	678.3
160°	692.2	692.8	693.5	693.6	693.1	692.5	692.0	691.5
162.5°	703.5	704.2	704.8	704.7	703.9	703.1	702.2	701.3
165°	717.7	718.5	719.3	719.2	718.4	717.4	716.5	715.6
167.5°	729.3	730.2	730.9	730.9	730.2	729.3	728.5	727.7
170°	735.6	736.6	737.4	737.4	736.6	735.6	734.7	733.8
172.5°	740.6	741.4	742.2	742.2	741.2	740.4	739.4	738.6
175°	746.0	746.7	747.5	747.5	746.6	745.6	744.7	743.8
177.5°	748.4	749.0	749.6	749.6	748.8	748.1	747.3	746.6
180°	748.5	748.5	748.5	748.5	748.5	748.5	748.5	748.5

(END OF REPORT)