

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332424

Luminaire Tested: **S123RDIW-S560D1320U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332424  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S560D1320U835-4F0-1E-UDD-F  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1320 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7416.5 lumens  
Efficiency: N/A  
Efficacy: 137.9 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332424

CATALOG NUMBER: S123RDIW-S560D1320U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P332424

CATALOG NUMBER: S123RDIW-S560D1320U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27	21
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	16
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17	14
6	60	48	41	35	54	44	37	32	35	30	26	27	23	21	19	17	15	12
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10167	10167	10167
5°	10205	10065	10122
10°	10147	9939	9905
15°	10038	9706	9604
20°	9889	9415	9196
25°	9734	9089	8797
30°	9531	8712	8236
35°	9320	8335	7720
40°	9128	7890	7082
45°	8873	7451	6506
50°	8594	6953	5863
55°	8310	6382	5262
60°	8047	5772	4600
65°	7707	5112	3940
70°	7279	4293	3182
75°	6658	3377	2994
80°	5938	2994	2752
85°	5014	2643	2458



TEST NUMBER: P332424

CATALOG NUMBER: S123RDIW-S560D1320U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.7	1.2
10°-20°	246.8	3.3
20°-30°	355.3	4.8
30°-40°	400.3	5.4
40°-50°	382.9	5.2
50°-60°	313.6	4.2
60°-70°	211.6	2.9
70°-80°	106.4	1.4
80°-90°	33.0	0.4
90°-100°	62.9	0.8
100°-110°	299.9	4.0
110°-120°	720.3	9.7
120°-130°	917.3	12.4
130°-140°	980.1	13.2
140°-150°	916.5	12.4
150°-160°	739.3	10.0
160°-170°	477.1	6.4
170°-180°	164.4	2.2
0°-30°	690.8	9.3
0°-40°	1091.1	14.7
0°-60°	1787.6	24.1
0°-90°	2138.6	28.8
90°-120°	1083.2	14.6
90°-150°	3897.1	52.5
90°-180°	5278.0	71.2
0°-180°	7416.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	944	944	944	944	944	
5°	944	940	932	938	937	90
15°	901	892	871	867	862	254
25°	820	800	765	750	741	377
35°	709	681	634	602	588	444
45°	583	547	490	447	427	450
55°	443	404	340	297	280	397
65°	303	259	201	165	155	299
75°	160	123	81	74	72	171
85°	41	25	21	20	20	46
90°	1	14	31	36	39	6
95°	78	29	40	48	49	97
105°	383	390	282	67	57	406
115°	719	727	738	750	756	709
125°	1013	1023	1029	1031	1034	905
135°	1261	1269	1274	1278	1274	971
145°	1456	1464	1467	1470	1470	911
155°	1603	1601	1602	1608	1601	738
165°	1691	1687	1686	1695	1687	478
175°	1731	1725	1726	1734	1724	165
180°	1731	1731	1731	1731	1731	



TEST NUMBER: P332424

CATALOG NUMBER: S123RDIW-S560D1320U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	947.6	947.0	946.5	945.9	945.4	944.3	942.7	941.0	939.4	937.8	939.3
5°	944.5	943.7	942.8	942.0	941.1	939.7	937.6	935.6	933.5	931.5	933.0
7.5°	935.8	934.9	933.9	933.0	932.1	930.3	927.7	925.0	922.3	919.7	920.5
10°	928.4	927.2	926.0	924.8	923.7	921.5	918.5	915.4	912.3	909.3	909.4
12.5°	918.0	916.7	915.3	914.0	912.7	910.2	906.4	902.7	898.9	895.2	895.1
15°	900.8	899.0	897.1	895.2	893.4	890.0	885.3	880.5	875.7	871.0	870.1
17.5°	879.2	877.1	874.9	872.7	870.5	866.4	860.3	854.3	848.2	842.2	840.4
20°	863.3	860.6	857.9	855.1	852.4	847.8	841.3	834.9	828.4	821.9	819.7
22.5°	845.5	842.4	839.3	836.1	833.0	828.0	821.1	814.2	807.4	800.5	797.7
25°	819.6	815.4	811.1	806.9	802.6	796.6	788.7	780.9	773.1	765.3	761.7
27.5°	788.2	783.5	778.8	774.1	769.4	762.7	754.0	745.3	736.6	727.9	722.9
30°	766.8	761.7	756.6	751.5	746.4	739.0	729.5	720.0	710.4	700.9	695.1
32.5°	745.3	739.6	733.8	728.0	722.2	714.3	704.2	694.1	684.0	673.9	667.6
35°	709.3	703.2	697.1	691.0	684.8	676.5	665.9	655.4	644.8	634.3	626.9
37.5°	672.9	666.1	659.3	652.4	645.6	636.6	625.3	614.1	602.8	591.5	583.2
40°	649.6	642.1	634.6	627.1	619.6	609.8	597.8	585.7	573.6	561.5	552.6
42.5°	623.2	615.7	608.3	600.8	593.3	583.3	570.8	558.3	545.8	533.3	523.6
45°	582.9	575.3	567.6	560.0	552.3	541.9	528.8	515.7	502.6	489.5	479.8
47.5°	542.6	534.2	525.8	517.4	509.0	498.3	485.1	472.0	458.9	445.8	435.3
50°	513.2	505.2	497.2	489.2	481.2	470.3	456.5	442.8	429.0	415.2	404.6
52.5°	486.9	478.2	469.5	460.8	452.2	441.0	427.3	413.7	400.0	386.4	375.4
55°	442.8	434.4	426.1	417.7	409.4	398.0	383.5	369.1	354.6	340.1	330.2
57.5°	402.0	392.9	383.8	374.7	365.6	353.8	339.3	324.8	310.2	295.7	286.4
60°	373.8	364.5	355.1	345.7	336.4	324.6	310.5	296.4	282.2	268.1	258.9
62.5°	345.6	336.3	326.9	317.5	308.2	296.4	282.3	268.2	254.0	239.9	231.3
65°	302.6	293.2	283.9	274.5	265.1	253.8	240.5	227.3	214.0	200.7	192.4
67.5°	259.5	250.1	240.6	231.1	221.7	210.6	197.8	185.1	172.4	159.6	153.4
70°	231.3	222.1	213.0	203.8	194.6	184.0	172.1	160.2	148.3	136.4	130.4
72.5°	203.1	194.1	185.0	176.0	166.9	157.0	146.2	135.3	124.5	113.7	108.8
75°	160.1	151.9	143.8	135.6	127.4	118.6	109.3	99.9	90.6	81.2	79.5
77.5°	120.9	113.5	106.1	98.7	91.3	84.6	78.6	72.6	66.5	60.5	59.6
80°	95.8	88.8	81.8	74.8	67.8	62.6	59.0	55.4	51.8	48.3	47.7
82.5°	71.9	65.8	59.8	53.8	47.7	43.9	42.2	40.6	38.9	37.2	36.7
85°	40.6	36.9	33.1	29.4	25.6	23.5	23.0	22.5	22.0	21.4	21.1
87.5°	15.0	14.0	13.1	12.2	11.3	11.2	11.9	12.7	13.4	14.1	14.2
90°	1.3	4.1	7.0	9.9	12.7	16.0	19.7	23.4	27.1	30.9	32.0
92.5°	23.9	23.1	22.3	21.5	20.7	21.7	24.5	27.3	30.1	32.9	34.7
95°	78.4	66.7	55.0	43.3	31.6	27.3	30.4	33.6	36.7	39.9	41.9
97.5°	157.6	152.4	147.1	141.9	136.6	123.7	103.1	82.6	62.0	41.4	43.7
100°	217.3	223.0	228.7	234.4	240.2	220.7	176.2	131.6	87.0	42.4	44.7
102.5°	285.2	289.3	293.4	297.5	301.7	279.4	230.7	182.0	133.3	84.6	77.5
105°	383.2	386.3	389.5	392.6	395.7	384.5	358.7	333.0	307.3	281.6	231.0
107.5°	486.6	489.1	491.6	494.1	496.6	499.9	504.0	508.0	512.1	516.1	479.0
110°	555.5	557.8	560.0	562.3	564.6	567.3	570.5	573.6	576.8	579.9	570.5



TEST NUMBER: P332424

CATALOG NUMBER: S123RDIW-S560D1320U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	621.3	623.4	625.4	627.5	629.5	632.1	635.3	638.4	641.6	644.7	644.9
115°	718.8	720.5	722.2	723.9	725.6	727.8	730.3	732.9	735.5	738.1	740.9
117.5°	813.2	815.3	817.4	819.5	821.6	823.3	824.6	826.0	827.3	828.6	830.9
120°	871.8	874.4	876.9	879.5	882.1	883.8	884.6	885.5	886.4	887.2	889.5
122.5°	931.5	933.6	935.7	937.8	939.9	941.5	942.6	943.7	944.8	945.9	947.5
125°	1013.2	1015.5	1017.8	1020.1	1022.4	1024.1	1025.2	1026.4	1027.5	1028.7	1029.2
127.5°	1092.4	1094.7	1097.0	1099.3	1101.6	1103.4	1104.8	1106.2	1107.5	1108.9	1109.8
130°	1141.8	1144.1	1146.4	1148.7	1151.0	1152.7	1153.8	1155.0	1156.1	1157.2	1158.4
132.5°	1189.1	1191.4	1193.7	1196.0	1198.3	1199.9	1200.8	1201.7	1202.6	1203.5	1204.7
135°	1261.4	1263.1	1264.8	1266.5	1268.3	1269.7	1270.8	1272.0	1273.1	1274.3	1275.1
137.5°	1323.1	1325.3	1327.5	1329.6	1331.8	1333.2	1333.8	1334.5	1335.1	1335.7	1337.1
140°	1364.3	1366.0	1367.7	1369.4	1371.1	1372.4	1373.3	1374.1	1375.0	1375.8	1377.0
142.5°	1402.3	1404.0	1405.8	1407.5	1409.2	1410.5	1411.3	1412.2	1413.0	1413.9	1414.8
145°	1455.6	1457.6	1459.6	1461.6	1463.6	1464.8	1465.4	1466.0	1466.6	1467.1	1467.7
147.5°	1505.7	1507.0	1508.3	1509.6	1511.0	1511.9	1512.5	1513.0	1513.6	1514.2	1514.8
150°	1536.6	1537.4	1538.3	1539.1	1540.0	1540.7	1541.3	1541.8	1542.4	1543.0	1543.6
152.5°	1564.3	1564.7	1565.1	1565.5	1565.9	1566.3	1566.7	1567.0	1567.3	1567.7	1568.7
155°	1603.4	1602.9	1602.3	1601.7	1601.1	1601.0	1601.3	1601.6	1601.9	1602.1	1603.6
157.5°	1633.8	1633.7	1633.7	1633.6	1633.5	1633.4	1633.1	1632.8	1632.5	1632.2	1633.9
160°	1652.3	1652.0	1651.7	1651.4	1651.1	1650.9	1650.6	1650.3	1650.0	1649.7	1651.4
162.5°	1669.8	1669.0	1668.3	1667.5	1666.8	1666.3	1666.0	1665.7	1665.4	1665.1	1667.1
165°	1690.9	1690.0	1689.1	1688.3	1687.4	1686.9	1686.6	1686.3	1686.0	1685.7	1688.0
167.5°	1707.3	1706.2	1705.0	1703.9	1702.7	1702.2	1702.2	1702.2	1702.2	1702.2	1704.5
170°	1716.6	1715.4	1714.3	1713.2	1712.0	1711.4	1711.4	1711.4	1711.4	1711.4	1713.7
172.5°	1722.8	1721.4	1720.0	1718.6	1717.3	1716.7	1716.9	1717.2	1717.4	1717.6	1719.9
175°	1730.7	1729.3	1727.9	1726.4	1725.0	1724.4	1724.7	1725.0	1725.3	1725.6	1727.6
177.5°	1732.8	1731.6	1730.5	1729.4	1728.2	1727.8	1728.0	1728.2	1728.4	1728.7	1730.5
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7



TEST NUMBER: P332424

CATALOG NUMBER: S123RDIW-S560D1320U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	944.5	944.5	944.5	944.5	944.5	944.5	944.5	944.5
2.5°	940.8	942.3	943.8	944.4	944.1	943.8	943.6	943.3
5°	934.5	936.1	937.6	938.2	937.9	937.5	937.2	936.8
7.5°	921.4	922.2	923.1	923.2	922.6	922.1	921.5	920.9
10°	909.6	909.8	909.9	909.6	908.8	907.9	907.1	906.2
12.5°	895.0	894.9	894.8	894.2	893.2	892.2	891.3	890.3
15°	869.3	868.4	867.6	866.5	865.3	864.2	863.0	861.8
17.5°	838.6	836.8	834.9	833.2	831.4	829.6	827.8	826.1
20°	817.5	815.3	813.1	811.0	808.9	806.9	804.8	802.8
22.5°	795.0	792.2	789.5	787.1	785.2	783.3	781.4	779.5
25°	758.1	754.5	751.0	748.2	746.4	744.5	742.6	740.7
27.5°	717.9	713.0	708.0	704.1	701.2	698.4	695.5	692.6
30°	689.3	683.5	677.8	673.5	670.8	668.1	665.3	662.6
32.5°	661.3	654.9	648.6	644.0	641.2	638.3	635.4	632.6
35°	619.6	612.3	605.0	599.8	596.7	593.7	590.6	587.5
37.5°	574.9	566.6	558.3	552.3	548.5	544.7	540.9	537.1
40°	543.8	534.9	526.1	519.7	515.8	511.9	508.0	504.0
42.5°	514.0	504.3	494.6	488.0	484.5	481.0	477.5	474.0
45°	470.1	460.4	450.7	443.8	439.7	435.6	431.5	427.4
47.5°	424.7	414.2	403.6	396.5	392.9	389.2	385.6	381.9
50°	394.1	383.5	373.0	365.7	361.8	357.9	354.0	350.1
52.5°	364.5	353.5	342.5	335.3	331.8	328.3	324.8	321.3
55°	320.4	310.5	300.6	294.0	290.6	287.2	283.8	280.4
57.5°	277.0	267.7	258.4	252.3	249.4	246.5	243.6	240.7
60°	249.7	240.5	231.3	225.3	222.4	219.5	216.6	213.7
62.5°	222.6	214.0	205.3	199.5	196.5	193.4	190.4	187.4
65°	184.0	175.7	167.3	162.2	160.4	158.5	156.6	154.7
67.5°	147.2	140.9	134.7	130.6	128.6	126.6	124.6	122.6
70°	124.4	118.5	112.5	108.6	106.7	104.9	103.0	101.1
72.5°	103.9	99.1	94.2	91.4	90.6	89.8	89.0	88.2
75°	77.8	76.1	74.4	73.4	73.0	72.7	72.3	72.0
77.5°	58.7	57.8	56.8	56.2	55.9	55.5	55.2	54.8
80°	47.2	46.7	46.2	45.8	45.5	45.1	44.8	44.4
82.5°	36.2	35.7	35.2	34.9	34.8	34.8	34.7	34.6
85°	20.8	20.4	20.1	19.9	19.9	19.9	19.9	19.9
87.5°	14.3	14.4	14.5	14.5	14.5	14.5	14.5	14.5
90°	33.1	34.3	35.4	36.3	36.9	37.4	38.0	38.6
92.5°	36.6	38.4	40.2	41.3	41.7	42.0	42.3	42.7
95°	43.9	45.9	47.9	48.9	48.9	48.9	48.9	48.9
97.5°	46.0	48.3	50.5	51.8	52.1	52.4	52.7	53.0
100°	47.0	49.3	51.6	52.9	53.1	53.4	53.7	54.0
102.5°	70.4	63.3	56.3	53.0	53.5	54.0	54.5	55.0
105°	180.4	129.9	79.3	54.3	54.9	55.4	56.0	56.6
107.5°	442.0	404.9	367.8	330.2	292.1	253.9	215.8	177.7
110°	561.0	551.6	542.2	517.0	476.2	435.3	394.5	353.6





TEST NUMBER: P332424

CATALOG NUMBER: S123RDIW-S560D1320U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	645.1	645.2	645.4	641.2	632.5	623.9	615.3	606.7
115°	743.8	746.6	749.5	751.5	752.6	753.8	754.9	756.1
117.5°	833.2	835.4	837.7	839.0	839.2	839.4	839.7	839.9
120°	891.8	894.1	896.4	897.5	897.5	897.5	897.5	897.5
122.5°	949.1	950.7	952.3	953.2	953.4	953.6	953.9	954.1
125°	1029.8	1030.4	1030.9	1031.5	1032.1	1032.7	1033.2	1033.8
127.5°	1110.7	1111.6	1112.6	1112.7	1112.2	1111.6	1111.0	1110.4
130°	1159.5	1160.7	1161.8	1162.1	1161.5	1161.0	1160.4	1159.8
132.5°	1205.8	1207.0	1208.1	1208.3	1207.5	1206.7	1205.9	1205.1
135°	1276.0	1276.8	1277.7	1277.7	1276.8	1276.0	1275.1	1274.3
137.5°	1338.5	1339.8	1341.2	1341.6	1341.0	1340.5	1339.9	1339.3
140°	1378.1	1379.3	1380.4	1380.7	1380.1	1379.5	1379.0	1378.4
142.5°	1415.7	1416.6	1417.6	1417.6	1416.8	1416.0	1415.2	1414.4
145°	1468.3	1468.8	1469.4	1469.7	1469.7	1469.7	1469.7	1469.7
147.5°	1515.3	1515.9	1516.5	1516.1	1514.8	1513.5	1512.2	1510.8
150°	1544.1	1544.7	1545.3	1545.1	1544.3	1543.4	1542.6	1541.7
152.5°	1569.7	1570.8	1571.8	1571.7	1570.3	1569.0	1567.7	1566.4
155°	1605.0	1606.4	1607.9	1607.7	1606.0	1604.3	1602.6	1600.9
157.5°	1635.7	1637.4	1639.1	1638.8	1636.6	1634.4	1632.1	1629.9
160°	1653.1	1654.9	1656.6	1656.4	1654.4	1652.4	1650.4	1648.4
162.5°	1669.0	1671.0	1672.9	1673.0	1671.2	1669.5	1667.7	1665.9
165°	1690.3	1692.6	1694.9	1695.0	1693.0	1691.0	1689.0	1687.0
167.5°	1706.8	1709.0	1711.3	1711.3	1709.0	1706.8	1704.5	1702.2
170°	1716.0	1718.3	1720.6	1720.6	1718.3	1716.0	1713.7	1711.4
172.5°	1722.2	1724.5	1726.8	1726.6	1724.1	1721.6	1719.1	1716.6
175°	1729.6	1731.6	1733.6	1733.4	1731.2	1728.9	1726.6	1724.3
177.5°	1732.3	1734.2	1736.0	1735.8	1733.5	1731.2	1728.9	1726.6
180°	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7	1730.7

(END OF REPORT)