

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332418-927

Luminaire Tested: **S123RDIW-S560D1030U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332418-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S560D1030U927-4F0-1E-UDD-A  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1030 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5033.7 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.22 / 1.36  
Luminous Opening: Rectangular (W 4' x L: 0.25' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 45.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	87	80	74	69	78	72	67	63	59	55	52	46	44	42	34	33	31	26
3	79	70	63	58	71	64	58	53	52	48	44	41	38	36	31	29	27	23
4	73	62	55	49	66	57	50	45	46	42	38	37	33	31	27	25	24	20
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21	17
6	62	50	42	37	56	46	39	34	38	33	29	30	26	24	23	20	19	15
7	57	45	38	32	51	41	35	30	34	29	25	27	24	21	21	18	17	14
8	53	41	34	29	48	38	31	27	31	26	23	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	14	11
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7629	7629	7629	7629
5°	9095	7662	6748	7662
10°	11355	7618	6096	7618
15°	13329	7540	5558	7540
20°	14875	7424	5102	7424
25°	14638	7301	4822	7301
30°	10521	7188	4533	7188
35°	7025	7041	4346	7041
40°	5176	6864	4154	6864
45°	4341	6555	3962	6555
50°	3831	6149	3699	6149
55°	3359	5684	3337	5684
60°	2990	5240	3057	5240
65°	2626	4760	2845	4760
70°	2061	4337	2596	4337
75°	1817	3785	2371	3785
80°	1581	3217	2331	3217
85°	1272	2581	2470	2581



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	69.7	1.4
10°-20°	217.8	4.3
20°-30°	342.1	6.8
30°-40°	356.9	7.1
40°-50°	305.5	6.1
50°-60°	232.8	4.6
60°-70°	149.2	3.0
70°-80°	71.8	1.4
80°-90°	22.0	0.4
90°-100°	38.9	0.8
100°-110°	185.6	3.7
110°-120°	445.8	8.9
120°-130°	567.6	11.3
130°-140°	606.5	12.0
140°-150°	567.1	11.3
150°-160°	457.5	9.1
160°-170°	295.2	5.9
170°-180°	101.8	2.0
0°-30°	629.6	12.5
0°-40°	986.5	19.6
0°-60°	1524.8	30.3
0°-90°	1767.8	35.1
90°-120°	670.3	13.3
90°-150°	2411.5	47.9
90°-180°	3266.0	64.9
0°-180°	5033.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	709	709	709	709	709	
5°	842	709	624	709	842	87
15°	1196	677	499	677	1196	339
25°	1232	615	406	615	1232	530
35°	535	536	331	536	535	351
45°	285	431	260	431	285	224
55°	179	303	178	303	179	162
65°	103	187	112	187	103	101
75°	44	91	57	91	44	47
85°	10	21	20	21	10	12
90°	24	1	24	1	24	11
95°	30	49	30	49	30	25
105°	35	237	35	237	35	80
115°	468	445	468	445	468	432
125°	640	627	640	627	640	571
135°	788	780	788	780	788	608
145°	909	901	909	901	909	568
155°	991	992	991	992	991	457
165°	1044	1046	1044	1046	1044	295
175°	1067	1071	1067	1071	1067	102
180°	1071	1071	1071	1071	1071	



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	754.9	755.9	752.7	752.3	748.6	747.7	747.7	742.5	739.3	735.2	732.8
5°	841.7	846.5	844.1	838.7	829.6	827.4	821.7	812.5	802.2	789.5	783.5
7.5°	950.1	956.7	954.1	945.7	936.2	928.4	912.2	897.1	875.9	857.4	841.5
10°	1038.9	1031.9	1026.5	1018.3	1009.5	995.2	978.3	954.9	927.9	906.7	883.0
12.5°	1105.4	1104.3	1097.3	1088.9	1076.5	1063.0	1042.0	1013.6	982.2	951.5	924.5
15°	1196.1	1197.9	1193.3	1184.6	1167.0	1143.0	1111.4	1099.6	1054.7	1021.3	987.9
17.5°	1258.9	1258.5	1257.8	1245.6	1227.7	1210.6	1181.4	1150.2	1109.6	1062.6	1017.6
20°	1298.6	1295.6	1296.2	1282.5	1269.2	1249.5	1221.0	1175.8	1142.4	1088.1	1041.6
22.5°	1297.7	1297.0	1299.3	1294.7	1285.0	1269.9	1247.4	1209.3	1166.6	1111.8	1059.6
25°	1232.5	1230.1	1244.4	1248.2	1263.8	1266.5	1259.8	1238.9	1198.5	1142.1	1077.4
27.5°	1031.5	1030.2	1056.6	1089.7	1131.8	1164.4	1196.0	1211.2	1198.5	1158.1	1093.4
30°	846.5	875.0	888.4	936.4	989.8	1053.4	1109.3	1162.4	1175.4	1157.9	1104.8
32.5°	702.8	727.7	738.9	780.1	829.8	904.4	988.2	1063.3	1116.5	1130.0	1098.0
35°	534.6	535.0	560.4	578.6	624.7	701.5	782.8	883.5	983.7	1059.5	1067.5
37.5°	426.6	428.1	443.5	461.7	496.3	536.9	608.5	692.2	807.9	924.3	992.6
40°	368.4	371.1	382.6	400.5	425.4	456.1	511.9	590.7	687.2	816.8	922.7
42.5°	331.0	335.4	341.4	355.1	370.5	399.3	444.4	505.3	593.0	715.6	837.7
45°	285.2	287.6	292.2	298.6	312.5	332.6	362.9	403.9	476.7	575.3	697.6
47.5°	251.6	250.3	255.1	260.3	269.6	283.2	303.6	337.0	389.0	468.0	571.8
50°	228.8	228.5	231.8	235.8	244.5	254.6	271.2	296.4	337.7	403.2	498.2
52.5°	207.4	208.6	211.0	215.9	222.2	230.3	245.3	263.4	298.9	355.5	434.6
55°	179.0	179.9	183.2	186.0	190.5	198.8	208.2	223.3	247.6	287.0	352.3
57.5°	155.0	154.6	157.8	158.4	163.6	170.2	177.5	189.3	206.9	236.2	280.2
60°	138.9	138.1	140.8	142.9	145.6	151.1	157.2	168.7	182.7	204.2	241.9
62.5°	124.4	124.0	126.0	128.1	130.3	135.3	140.5	149.2	160.3	178.5	208.3
65°	103.1	104.1	105.0	105.9	107.1	110.1	115.0	121.0	128.7	141.4	163.0
67.5°	81.0	82.0	82.3	84.1	86.7	88.6	91.7	97.0	102.3	113.0	125.3
70°	65.5	65.2	65.5	66.5	69.8	73.1	77.1	81.0	84.4	92.0	102.3
72.5°	56.3	55.8	56.6	56.7	58.4	59.3	61.8	65.5	69.8	74.9	82.4
75°	43.7	43.7	43.7	43.7	44.9	45.6	46.4	47.4	48.9	51.3	56.7
77.5°	32.3	32.3	32.8	33.0	33.4	33.7	34.2	35.2	35.6	37.0	39.3
80°	25.5	25.8	25.5	25.8	25.8	26.4	26.7	27.6	27.9	29.5	30.3
82.5°	19.2	19.0	19.2	19.5	19.5	20.1	20.1	20.8	20.9	21.6	22.6
85°	10.3	9.7	10.3	10.0	10.6	10.0	10.3	10.9	10.9	11.2	12.4
87.5°	7.2	7.6	7.1	7.2	7.1	7.3	7.1	7.1	7.4	7.0	6.7
90°	23.8	23.5	23.1	22.8	22.4	21.9	21.2	20.5	19.8	19.1	16.8
92.5°	26.4	26.2	26.0	25.7	25.6	24.9	23.8	22.7	21.5	20.4	18.6
95°	30.3	30.3	30.3	30.3	30.3	29.6	28.4	27.2	25.9	24.6	22.7
97.5°	32.8	32.6	32.4	32.2	32.1	31.3	29.9	28.4	27.0	25.6	38.3
100°	33.4	33.3	33.0	32.9	32.7	31.9	30.5	29.1	27.6	26.2	53.9
102.5°	34.1	33.7	33.4	33.1	32.8	34.8	39.2	43.6	48.0	52.4	82.5
105°	35.0	34.6	34.3	34.0	33.6	49.0	80.3	111.7	143.0	174.3	190.2
107.5°	110.0	133.6	157.2	180.7	204.3	227.6	250.6	273.5	296.4	319.4	316.9
110°	218.8	244.1	269.3	294.7	320.0	335.5	341.4	347.2	353.0	358.9	356.9



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	375.4	380.7	386.1	391.4	396.7	399.3	399.3	399.2	399.0	398.9	397.0
115°	467.9	467.1	466.4	465.7	465.0	463.8	462.0	460.3	458.5	456.7	455.1
117.5°	519.8	519.6	519.4	519.3	519.2	518.4	517.0	515.6	514.1	512.7	511.9
120°	555.4	555.4	555.4	555.4	555.4	554.7	553.3	551.8	550.4	549.0	548.5
122.5°	590.4	590.3	590.1	589.9	589.9	589.2	588.3	587.2	586.3	585.3	584.6
125°	639.7	639.4	639.0	638.7	638.3	637.9	637.6	637.2	636.9	636.5	635.8
127.5°	687.1	687.5	687.9	688.2	688.6	688.5	687.9	687.3	686.7	686.2	685.3
130°	717.7	718.0	718.4	718.7	719.1	718.9	718.2	717.6	716.8	716.1	715.4
132.5°	745.7	746.2	746.7	747.2	747.7	747.6	746.9	746.2	745.4	744.7	744.2
135°	788.5	789.0	789.6	790.1	790.6	790.6	790.1	789.6	789.0	788.5	787.8
137.5°	828.8	829.1	829.5	829.8	830.2	830.0	829.1	828.2	827.4	826.6	826.2
140°	852.9	853.3	853.7	854.1	854.4	854.2	853.5	852.8	852.1	851.4	850.8
142.5°	875.2	875.8	876.2	876.7	877.2	877.2	876.6	876.1	875.5	874.9	874.4
145°	909.4	909.4	909.4	909.4	909.4	909.3	908.9	908.6	908.2	907.8	907.5
147.5°	934.9	935.7	936.5	937.4	938.2	938.4	938.0	937.7	937.3	937.0	936.6
150°	954.0	954.6	955.1	955.6	956.2	956.2	955.8	955.5	955.1	954.8	954.4
152.5°	969.3	970.1	970.9	971.7	972.6	972.6	972.0	971.4	970.7	970.1	969.9
155°	990.6	991.7	992.8	993.8	994.8	995.0	994.0	993.2	992.3	991.4	991.3
157.5°	1008.6	1010.0	1011.4	1012.7	1014.1	1014.2	1013.2	1012.2	1011.1	1010.0	1010.2
160°	1020.0	1021.3	1022.5	1023.7	1025.0	1025.1	1024.1	1022.9	1021.9	1020.9	1021.0
162.5°	1030.9	1032.0	1033.1	1034.2	1035.2	1035.2	1034.0	1032.8	1031.6	1030.4	1030.5
165°	1043.9	1045.1	1046.4	1047.7	1048.8	1048.8	1047.3	1045.9	1044.6	1043.1	1043.3
167.5°	1053.3	1054.7	1056.1	1057.6	1059.0	1059.0	1057.6	1056.1	1054.7	1053.3	1053.3
170°	1059.1	1060.4	1061.8	1063.3	1064.7	1064.7	1063.3	1061.8	1060.4	1059.1	1059.1
172.5°	1062.2	1063.7	1065.3	1066.9	1068.4	1068.5	1067.1	1065.7	1064.3	1062.9	1062.7
175°	1067.0	1068.4	1069.8	1071.3	1072.7	1072.8	1071.5	1070.2	1069.1	1067.8	1067.6
177.5°	1068.4	1069.8	1071.3	1072.7	1074.1	1074.2	1073.1	1072.0	1070.9	1069.7	1069.5
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	731.8	731.1	727.7	723.8	718.7	715.3	712.6	711.2	706.9	701.5	697.8
5°	777.1	767.9	758.3	746.4	735.5	724.3	717.3	709.1	699.1	687.9	679.9
7.5°	825.5	807.6	788.4	768.6	748.9	731.3	715.8	702.5	686.6	670.5	659.2
10°	862.6	836.5	809.5	781.9	756.7	733.1	714.9	697.0	677.9	659.3	645.4
12.5°	896.4	862.1	830.9	796.9	764.8	736.5	710.3	689.2	666.2	646.5	630.6
15°	939.1	903.9	866.3	814.7	771.9	736.1	704.3	676.6	648.7	624.5	609.0
17.5°	979.0	926.1	875.5	832.4	776.9	732.1	693.2	660.2	629.6	603.9	584.8
20°	995.5	944.3	889.3	834.4	779.8	729.8	684.5	648.1	616.2	587.1	569.5
22.5°	1005.4	947.4	889.5	830.5	772.5	720.5	675.8	635.7	601.2	573.5	551.8
25°	1017.1	947.8	884.2	825.9	766.8	710.3	657.2	614.7	577.4	548.0	524.9
27.5°	1024.7	943.3	868.0	803.3	743.2	687.1	638.4	593.3	555.5	524.3	499.6
30°	1026.2	939.7	855.6	785.5	724.5	673.0	621.4	578.3	538.3	505.2	482.1
32.5°	1028.1	930.7	838.9	764.5	702.0	650.9	604.2	563.0	522.0	489.4	465.9
35°	1020.1	925.7	813.5	727.9	665.4	615.9	573.8	535.8	495.5	463.9	440.0
37.5°	985.6	906.0	787.1	686.7	621.4	575.6	541.2	508.2	471.2	437.1	414.5
40°	950.9	886.6	766.8	661.8	593.5	546.4	515.5	488.5	452.7	420.8	396.6
42.5°	899.2	860.2	747.3	635.6	561.9	516.6	490.5	465.2	433.8	401.4	378.6
45°	804.4	809.5	707.6	593.8	518.2	472.7	448.1	430.6	402.7	376.0	352.6
47.5°	685.4	733.6	660.9	549.3	472.2	429.4	408.0	392.6	373.8	347.6	326.3
50°	607.8	676.6	623.5	519.4	443.3	400.8	379.6	367.2	350.8	330.1	309.8
52.5°	536.1	610.1	578.4	486.2	412.0	373.1	352.4	342.1	329.2	309.7	291.4
55°	437.2	512.1	504.9	436.0	365.0	330.1	314.3	302.9	294.0	279.5	264.9
57.5°	353.6	424.7	428.5	380.2	323.6	289.1	275.6	266.9	261.1	250.2	236.7
60°	301.0	366.2	379.0	342.5	294.0	263.6	250.3	243.4	238.8	230.0	219.7
62.5°	257.3	312.8	327.3	301.0	265.6	237.2	226.8	220.1	217.0	209.4	200.3
65°	196.9	243.0	257.0	242.4	223.9	201.1	192.7	186.9	184.2	179.9	173.3
67.5°	148.1	181.7	197.0	186.7	180.1	165.6	160.3	157.2	154.7	151.9	146.2
70°	118.9	143.9	159.6	156.9	151.4	143.9	139.9	137.8	135.3	132.9	128.0
72.5°	95.6	112.7	127.5	129.0	124.5	122.9	119.5	118.6	117.1	114.2	111.5
75°	63.5	75.3	85.6	89.5	91.3	92.8	91.3	91.0	90.7	88.3	86.7
77.5°	41.6	47.9	54.4	61.2	64.0	66.1	66.5	67.7	66.9	65.6	64.9
80°	31.8	33.4	37.9	43.7	48.2	50.1	51.3	51.9	51.6	51.3	50.1
82.5°	23.1	24.4	26.5	30.6	34.4	37.5	38.2	38.0	38.7	38.9	37.9
85°	12.4	12.8	13.4	13.9	16.1	19.4	20.4	20.9	21.5	21.5	19.7
87.5°	6.8	6.1	6.1	5.7	6.1	5.9	7.1	7.9	8.6	7.9	8.2
90°	14.5	12.2	9.9	7.8	6.1	4.4	2.5	0.8	2.5	4.4	6.1
92.5°	16.9	15.2	13.5	12.8	13.3	13.8	14.3	14.8	14.3	13.8	13.3
95°	20.8	18.9	16.9	19.6	26.8	34.1	41.3	48.6	41.3	34.1	26.8
97.5°	51.1	63.8	76.5	84.5	87.8	91.0	94.3	97.5	94.3	91.0	87.8
100°	81.4	109.0	136.6	148.6	145.0	141.6	138.0	134.4	138.0	141.6	145.0
102.5°	112.6	142.8	172.9	186.6	184.1	181.6	179.0	176.5	179.0	181.6	184.1
105°	206.0	222.0	237.9	244.9	243.0	241.0	239.1	237.1	239.1	241.0	243.0
107.5°	314.3	311.9	309.3	307.3	305.8	304.2	302.6	301.1	302.6	304.2	305.8
110°	355.0	353.0	351.1	349.4	348.0	346.6	345.2	343.7	345.2	346.6	348.0





TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	395.1	393.1	391.2	389.6	388.3	387.0	385.7	384.4	385.7	387.0	388.3
115°	453.5	451.9	450.4	449.0	448.0	446.9	445.8	444.8	445.8	446.9	448.0
117.5°	511.1	510.3	509.5	508.4	507.1	505.8	504.5	503.2	504.5	505.8	507.1
120°	548.0	547.4	546.9	545.8	544.2	542.6	541.1	539.5	541.1	542.6	544.2
122.5°	583.9	583.3	582.6	581.6	580.3	579.0	577.7	576.4	577.7	579.0	580.3
125°	635.1	634.4	633.7	632.6	631.2	629.8	628.4	627.0	628.4	629.8	631.2
127.5°	684.5	683.7	682.8	681.7	680.2	678.8	677.4	676.0	677.4	678.8	680.2
130°	714.7	714.0	713.3	712.3	710.8	709.4	708.0	706.5	708.0	709.4	710.8
132.5°	743.6	743.1	742.5	741.5	740.1	738.6	737.3	735.9	737.3	738.6	740.1
135°	787.1	786.4	785.7	784.8	783.7	782.7	781.6	780.5	781.6	782.7	783.7
137.5°	825.8	825.4	825.0	824.1	822.8	821.4	820.1	818.7	820.1	821.4	822.8
140°	850.3	849.8	849.2	848.4	847.4	846.4	845.3	844.2	845.3	846.4	847.4
142.5°	873.9	873.3	872.8	872.0	870.9	869.9	868.8	867.8	868.8	869.9	870.9
145°	907.1	906.8	906.4	905.6	904.4	903.2	901.9	900.7	901.9	903.2	904.4
147.5°	936.3	935.9	935.6	935.0	934.1	933.3	932.6	931.8	932.6	933.3	934.1
150°	954.1	953.7	953.4	952.9	952.4	951.9	951.3	950.9	951.3	951.9	952.4
152.5°	969.6	969.5	969.2	969.0	968.8	968.5	968.3	968.0	968.3	968.5	968.8
155°	991.0	990.9	990.7	990.8	991.2	991.5	991.8	992.2	991.8	991.5	991.2
157.5°	1010.3	1010.6	1010.7	1010.8	1010.9	1010.9	1011.0	1011.0	1011.0	1010.9	1010.9
160°	1021.2	1021.4	1021.5	1021.8	1021.9	1022.1	1022.2	1022.5	1022.2	1022.1	1021.9
162.5°	1030.8	1030.9	1031.1	1031.4	1031.9	1032.4	1032.8	1033.2	1032.8	1032.4	1031.9
165°	1043.5	1043.6	1043.9	1044.2	1044.7	1045.3	1045.8	1046.3	1045.8	1045.3	1044.7
167.5°	1053.3	1053.3	1053.3	1053.7	1054.4	1055.1	1055.8	1056.5	1055.8	1055.1	1054.4
170°	1059.1	1059.1	1059.1	1059.4	1060.1	1060.8	1061.5	1062.2	1061.5	1060.8	1060.1
172.5°	1062.6	1062.4	1062.3	1062.6	1063.5	1064.4	1065.2	1066.0	1065.2	1064.4	1063.5
175°	1067.5	1067.2	1067.1	1067.5	1068.3	1069.2	1070.1	1071.0	1070.1	1069.2	1068.3
177.5°	1069.4	1069.3	1069.1	1069.4	1070.2	1070.9	1071.5	1072.2	1071.5	1070.9	1070.2
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	696.6	693.5	691.3	686.4	683.3	679.9	676.5	678.7	678.4	678.2	678.2
5°	673.3	666.3	660.0	651.7	646.6	640.2	635.3	634.8	636.0	631.7	629.3
7.5°	650.1	640.6	631.5	622.5	612.9	605.2	600.5	598.3	595.2	592.6	589.8
10°	633.8	622.7	613.8	602.6	592.3	583.2	577.4	573.5	571.3	569.2	565.3
12.5°	617.1	606.1	594.8	582.2	572.4	561.8	557.5	553.1	549.0	546.6	541.2
15°	592.6	578.3	566.5	553.1	542.2	531.9	525.9	517.1	515.8	512.8	507.3
17.5°	568.0	552.5	536.2	526.3	514.0	503.3	494.0	491.1	482.4	479.1	474.4
20°	548.6	534.3	521.9	508.8	490.9	480.9	473.6	469.7	462.7	458.4	455.4
22.5°	531.9	517.3	503.0	487.7	472.9	461.8	456.4	450.3	446.5	440.5	437.2
25°	507.9	492.2	474.8	458.4	447.8	439.3	430.9	425.4	419.9	417.2	411.1
27.5°	480.1	463.7	447.5	435.1	422.0	413.6	405.9	401.1	394.5	389.9	386.6
30°	464.9	445.4	431.5	420.3	403.5	395.7	389.9	383.8	379.0	374.1	370.7
32.5°	447.1	429.4	416.1	402.3	389.4	380.9	373.4	368.0	363.9	359.3	356.0
35°	419.3	404.5	390.8	376.8	367.4	358.6	349.8	345.3	341.4	337.1	334.1
37.5°	394.2	380.3	367.3	354.1	342.5	335.3	328.2	324.7	319.4	316.6	313.5
40°	378.7	365.0	351.1	338.3	326.1	320.8	314.3	309.2	304.4	302.2	298.9
42.5°	361.7	348.0	336.3	322.5	312.6	305.1	299.3	293.7	290.0	286.9	285.0
45°	336.5	324.3	312.8	299.2	289.8	283.4	276.7	271.6	268.2	266.1	262.8
47.5°	312.0	299.9	288.2	276.3	267.2	259.9	253.3	249.6	245.3	242.6	240.3
50°	294.3	283.4	270.9	260.0	251.0	243.7	238.2	233.6	229.7	226.3	224.8
52.5°	278.1	266.4	255.6	245.5	235.9	227.6	222.7	217.9	214.9	211.0	209.3
55°	251.2	240.0	230.9	220.9	211.5	204.5	198.4	194.2	191.2	186.9	184.5
57.5°	226.0	215.9	205.1	196.5	186.7	180.9	175.8	170.0	166.4	163.0	160.7
60°	209.1	197.5	188.1	179.9	171.4	163.8	159.3	154.7	150.8	147.4	145.4
62.5°	191.3	181.3	172.4	163.4	155.7	149.0	143.8	139.9	136.5	134.4	132.2
65°	164.1	156.3	147.2	139.9	132.6	127.8	123.5	120.2	117.7	116.2	114.4
67.5°	139.2	131.5	123.6	116.4	111.5	107.8	105.0	102.2	101.0	99.0	97.8
70°	122.9	115.0	108.1	102.6	97.7	95.0	93.2	91.0	89.8	87.4	86.2
72.5°	105.2	99.5	94.4	89.9	86.0	83.6	81.3	78.7	76.7	74.1	72.8
75°	82.9	77.7	73.8	70.7	68.3	65.0	61.6	58.9	58.0	57.0	56.7
77.5°	61.3	58.1	55.2	52.7	49.7	47.2	46.5	45.9	45.7	45.2	45.2
80°	48.2	45.2	43.1	40.1	38.3	38.3	38.3	37.6	37.9	37.9	37.9
82.5°	35.9	33.0	31.9	30.8	30.5	30.7	30.7	30.8	30.7	31.1	30.9
85°	18.5	18.8	19.4	19.1	19.4	19.4	20.0	19.7	20.0	19.4	20.0
87.5°	8.4	9.5	10.2	10.9	11.6	11.8	12.2	12.4	12.8	12.9	13.0
90°	7.8	9.9	12.2	14.5	16.8	19.1	19.8	20.5	21.2	21.9	22.4
92.5°	12.8	13.5	15.2	16.9	18.6	20.4	21.5	22.7	23.8	24.9	25.6
95°	19.6	16.9	18.9	20.8	22.7	24.6	25.9	27.2	28.4	29.6	30.3
97.5°	84.5	76.5	63.8	51.1	38.3	25.6	27.0	28.4	29.9	31.3	32.1
100°	148.6	136.6	109.0	81.4	53.9	26.2	27.6	29.1	30.5	31.9	32.7
102.5°	186.6	172.9	142.8	112.6	82.5	52.4	48.0	43.6	39.2	34.8	32.8
105°	244.9	237.9	222.0	206.0	190.2	174.3	143.0	111.7	80.3	49.0	33.6
107.5°	307.3	309.3	311.9	314.3	316.9	319.4	296.4	273.5	250.6	227.6	204.3
110°	349.4	351.1	353.0	355.0	356.9	358.9	353.0	347.2	341.4	335.5	320.0



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	389.6	391.2	393.1	395.1	397.0	398.9	399.0	399.2	399.3	399.3	396.7
115°	449.0	450.4	451.9	453.5	455.1	456.7	458.5	460.3	462.0	463.8	465.0
117.5°	508.4	509.5	510.3	511.1	511.9	512.7	514.1	515.6	517.0	518.4	519.2
120°	545.8	546.9	547.4	548.0	548.5	549.0	550.4	551.8	553.3	554.7	555.4
122.5°	581.6	582.6	583.3	583.9	584.6	585.3	586.3	587.2	588.3	589.2	589.9
125°	632.6	633.7	634.4	635.1	635.8	636.5	636.9	637.2	637.6	637.9	638.3
127.5°	681.7	682.8	683.7	684.5	685.3	686.2	686.7	687.3	687.9	688.5	688.6
130°	712.3	713.3	714.0	714.7	715.4	716.1	716.8	717.6	718.2	718.9	719.1
132.5°	741.5	742.5	743.1	743.6	744.2	744.7	745.4	746.2	746.9	747.6	747.7
135°	784.8	785.7	786.4	787.1	787.8	788.5	789.0	789.6	790.1	790.6	790.6
137.5°	824.1	825.0	825.4	825.8	826.2	826.6	827.4	828.2	829.1	830.0	830.2
140°	848.4	849.2	849.8	850.3	850.8	851.4	852.1	852.8	853.5	854.2	854.4
142.5°	872.0	872.8	873.3	873.9	874.4	874.9	875.5	876.1	876.6	877.2	877.2
145°	905.6	906.4	906.8	907.1	907.5	907.8	908.2	908.6	908.9	909.3	909.4
147.5°	935.0	935.6	935.9	936.3	936.6	937.0	937.3	937.7	938.0	938.4	938.2
150°	952.9	953.4	953.7	954.1	954.4	954.8	955.1	955.5	955.8	956.2	956.2
152.5°	969.0	969.2	969.5	969.6	969.9	970.1	970.7	971.4	972.0	972.6	972.6
155°	990.8	990.7	990.9	991.0	991.3	991.4	992.3	993.2	994.0	995.0	994.8
157.5°	1010.8	1010.7	1010.6	1010.3	1010.2	1010.0	1011.1	1012.2	1013.2	1014.2	1014.1
160°	1021.8	1021.5	1021.4	1021.2	1021.0	1020.9	1021.9	1022.9	1024.1	1025.1	1025.0
162.5°	1031.4	1031.1	1030.9	1030.8	1030.5	1030.4	1031.6	1032.8	1034.0	1035.2	1035.2
165°	1044.2	1043.9	1043.6	1043.5	1043.3	1043.1	1044.6	1045.9	1047.3	1048.8	1048.8
167.5°	1053.7	1053.3	1053.3	1053.3	1053.3	1053.3	1054.7	1056.1	1057.6	1059.0	1059.0
170°	1059.4	1059.1	1059.1	1059.1	1059.1	1059.1	1060.4	1061.8	1063.3	1064.7	1064.7
172.5°	1062.6	1062.3	1062.4	1062.6	1062.7	1062.9	1064.3	1065.7	1067.1	1068.5	1068.4
175°	1067.5	1067.1	1067.2	1067.5	1067.6	1067.8	1069.1	1070.2	1071.5	1072.8	1072.7
177.5°	1069.4	1069.1	1069.3	1069.4	1069.5	1069.7	1070.9	1072.0	1073.1	1074.2	1074.1
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	675.3	675.0	675.3	674.3	675.3	675.0	675.3	678.2	678.2	678.4	678.7
5°	628.4	628.0	627.2	624.5	627.2	628.0	628.4	629.3	631.7	636.0	634.8
7.5°	587.4	587.0	584.3	584.4	584.3	587.0	587.4	589.8	592.6	595.2	598.3
10°	563.2	563.5	559.8	557.7	559.8	563.5	563.2	565.3	569.2	571.3	573.5
12.5°	539.6	538.2	535.3	532.9	535.3	538.2	539.6	541.2	546.6	549.0	553.1
15°	508.5	505.5	498.2	498.8	498.2	505.5	508.5	507.3	512.8	515.8	517.1
17.5°	471.9	469.7	469.6	465.3	469.6	469.7	471.9	474.4	479.1	482.4	491.1
20°	450.6	449.1	449.6	445.4	449.6	449.1	450.6	455.4	458.4	462.7	469.7
22.5°	433.8	432.3	429.8	428.4	429.8	432.3	433.8	437.2	440.5	446.5	450.3
25°	409.3	406.9	404.5	406.0	404.5	406.9	409.3	411.1	417.2	419.9	425.4
27.5°	384.8	382.9	380.6	380.2	380.6	382.9	384.8	386.6	389.9	394.5	401.1
30°	369.2	367.4	366.2	364.7	366.2	367.4	369.2	370.7	374.1	379.0	383.8
32.5°	353.5	353.2	350.9	350.6	350.9	353.2	353.5	356.0	359.3	363.9	368.0
35°	332.9	331.1	330.4	330.7	330.4	331.1	332.9	334.1	337.1	341.4	345.3
37.5°	313.2	310.9	309.7	308.6	309.7	310.9	313.2	313.5	316.6	319.4	324.7
40°	299.2	296.8	296.1	295.6	296.1	296.8	299.2	298.9	302.2	304.4	309.2
42.5°	283.4	282.4	282.1	281.0	282.1	282.4	283.4	285.0	286.9	290.0	293.7
45°	261.8	261.6	259.8	260.3	259.8	261.6	261.8	262.8	266.1	268.2	271.6
47.5°	239.2	237.8	236.5	237.4	236.5	237.8	239.2	240.3	242.6	245.3	249.6
50°	223.6	223.0	220.3	220.9	220.3	223.0	223.6	224.8	226.3	229.7	233.6
52.5°	208.1	205.8	204.8	204.4	204.8	205.8	208.1	209.3	211.0	214.9	217.9
55°	182.4	179.6	178.4	177.8	178.4	179.6	182.4	184.5	186.9	191.2	194.2
57.5°	157.1	156.4	155.4	156.1	155.4	156.4	157.1	160.7	163.0	166.4	170.0
60°	142.3	142.3	142.3	142.0	142.3	142.3	142.3	145.4	147.4	150.8	154.7
62.5°	130.9	130.2	129.9	130.3	129.9	130.2	130.9	132.2	134.4	136.5	139.9
65°	113.4	113.2	111.9	111.7	111.9	113.2	113.4	114.4	116.2	117.7	120.2
67.5°	97.0	95.9	95.6	95.1	95.6	95.9	97.0	97.8	99.0	101.0	102.2
70°	84.7	84.1	82.2	82.5	82.2	84.1	84.7	86.2	87.4	89.8	91.0
72.5°	71.3	70.7	70.3	69.9	70.3	70.7	71.3	72.8	74.1	76.7	78.7
75°	56.4	56.2	55.8	57.0	55.8	56.2	56.4	56.7	57.0	58.0	58.9
77.5°	45.2	45.2	45.4	44.9	45.4	45.2	45.2	45.2	45.2	45.7	45.9
80°	37.9	37.9	37.6	37.6	37.6	37.9	37.9	37.9	37.9	37.9	37.6
82.5°	30.4	30.7	30.8	30.3	30.8	30.7	30.4	30.9	31.1	30.7	30.8
85°	20.0	19.7	20.4	20.0	20.4	19.7	20.0	20.0	19.4	20.0	19.7
87.5°	13.5	13.2	13.2	13.5	13.2	13.2	13.5	13.0	12.9	12.8	12.4
90°	22.8	23.1	23.5	23.8	23.5	23.1	22.8	22.4	21.9	21.2	20.5
92.5°	25.7	26.0	26.2	26.4	26.2	26.0	25.7	25.6	24.9	23.8	22.7
95°	30.3	30.3	30.3	30.3	30.3	30.3	30.3	30.3	29.6	28.4	27.2
97.5°	32.2	32.4	32.6	32.8	32.6	32.4	32.2	32.1	31.3	29.9	28.4
100°	32.9	33.0	33.3	33.4	33.3	33.0	32.9	32.7	31.9	30.5	29.1
102.5°	33.1	33.4	33.7	34.1	33.7	33.4	33.1	32.8	34.8	39.2	43.6
105°	34.0	34.3	34.6	35.0	34.6	34.3	34.0	33.6	49.0	80.3	111.7
107.5°	180.7	157.2	133.6	110.0	133.6	157.2	180.7	204.3	227.6	250.6	273.5
110°	294.7	269.3	244.1	218.8	244.1	269.3	294.7	320.0	335.5	341.4	347.2



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	391.4	386.1	380.7	375.4	380.7	386.1	391.4	396.7	399.3	399.3	399.2
115°	465.7	466.4	467.1	467.9	467.1	466.4	465.7	465.0	463.8	462.0	460.3
117.5°	519.3	519.4	519.6	519.8	519.6	519.4	519.3	519.2	518.4	517.0	515.6
120°	555.4	555.4	555.4	555.4	555.4	555.4	555.4	555.4	554.7	553.3	551.8
122.5°	589.9	590.1	590.3	590.4	590.3	590.1	589.9	589.9	589.2	588.3	587.2
125°	638.7	639.0	639.4	639.7	639.4	639.0	638.7	638.3	637.9	637.6	637.2
127.5°	688.2	687.9	687.5	687.1	687.5	687.9	688.2	688.6	688.5	687.9	687.3
130°	718.7	718.4	718.0	717.7	718.0	718.4	718.7	719.1	718.9	718.2	717.6
132.5°	747.2	746.7	746.2	745.7	746.2	746.7	747.2	747.7	747.6	746.9	746.2
135°	790.1	789.6	789.0	788.5	789.0	789.6	790.1	790.6	790.6	790.1	789.6
137.5°	829.8	829.5	829.1	828.8	829.1	829.5	829.8	830.2	830.0	829.1	828.2
140°	854.1	853.7	853.3	852.9	853.3	853.7	854.1	854.4	854.2	853.5	852.8
142.5°	876.7	876.2	875.8	875.2	875.8	876.2	876.7	877.2	877.2	876.6	876.1
145°	909.4	909.4	909.4	909.4	909.4	909.4	909.4	909.4	909.3	908.9	908.6
147.5°	937.4	936.5	935.7	934.9	935.7	936.5	937.4	938.2	938.4	938.0	937.7
150°	955.6	955.1	954.6	954.0	954.6	955.1	955.6	956.2	956.2	955.8	955.5
152.5°	971.7	970.9	970.1	969.3	970.1	970.9	971.7	972.6	972.6	972.0	971.4
155°	993.8	992.8	991.7	990.6	991.7	992.8	993.8	994.8	995.0	994.0	993.2
157.5°	1012.7	1011.4	1010.0	1008.6	1010.0	1011.4	1012.7	1014.1	1014.2	1013.2	1012.2
160°	1023.7	1022.5	1021.3	1020.0	1021.3	1022.5	1023.7	1025.0	1025.1	1024.1	1022.9
162.5°	1034.2	1033.1	1032.0	1030.9	1032.0	1033.1	1034.2	1035.2	1035.2	1034.0	1032.8
165°	1047.7	1046.4	1045.1	1043.9	1045.1	1046.4	1047.7	1048.8	1048.8	1047.3	1045.9
167.5°	1057.6	1056.1	1054.7	1053.3	1054.7	1056.1	1057.6	1059.0	1059.0	1057.6	1056.1
170°	1063.3	1061.8	1060.4	1059.1	1060.4	1061.8	1063.3	1064.7	1064.7	1063.3	1061.8
172.5°	1066.9	1065.3	1063.7	1062.2	1063.7	1065.3	1066.9	1068.4	1068.5	1067.1	1065.7
175°	1071.3	1069.8	1068.4	1067.0	1068.4	1069.8	1071.3	1072.7	1072.8	1071.5	1070.2
177.5°	1072.7	1071.3	1069.8	1068.4	1069.8	1071.3	1072.7	1074.1	1074.2	1073.1	1072.0
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	676.5	679.9	683.3	686.4	691.3	693.5	696.6	697.8	701.5	706.9	711.2
5°	635.3	640.2	646.6	651.7	660.0	666.3	673.3	679.9	687.9	699.1	709.1
7.5°	600.5	605.2	612.9	622.5	631.5	640.6	650.1	659.2	670.5	686.6	702.5
10°	577.4	583.2	592.3	602.6	613.8	622.7	633.8	645.4	659.3	677.9	697.0
12.5°	557.5	561.8	572.4	582.2	594.8	606.1	617.1	630.6	646.5	666.2	689.2
15°	525.9	531.9	542.2	553.1	566.5	578.3	592.6	609.0	624.5	648.7	676.6
17.5°	494.0	503.3	514.0	526.3	536.2	552.5	568.0	584.8	603.9	629.6	660.2
20°	473.6	480.9	490.9	508.8	521.9	534.3	548.6	569.5	587.1	616.2	648.1
22.5°	456.4	461.8	472.9	487.7	503.0	517.3	531.9	551.8	573.5	601.2	635.7
25°	430.9	439.3	447.8	458.4	474.8	492.2	507.9	524.9	548.0	577.4	614.7
27.5°	405.9	413.6	422.0	435.1	447.5	463.7	480.1	499.6	524.3	555.5	593.3
30°	389.9	395.7	403.5	420.3	431.5	445.4	464.9	482.1	505.2	538.3	578.3
32.5°	373.4	380.9	389.4	402.3	416.1	429.4	447.1	465.9	489.4	522.0	563.0
35°	349.8	358.6	367.4	376.8	390.8	404.5	419.3	440.0	463.9	495.5	535.8
37.5°	328.2	335.3	342.5	354.1	367.3	380.3	394.2	414.5	437.1	471.2	508.2
40°	314.3	320.8	326.1	338.3	351.1	365.0	378.7	396.6	420.8	452.7	488.5
42.5°	299.3	305.1	312.6	322.5	336.3	348.0	361.7	378.6	401.4	433.8	465.2
45°	276.7	283.4	289.8	299.2	312.8	324.3	336.5	352.6	376.0	402.7	430.6
47.5°	253.3	259.9	267.2	276.3	288.2	299.9	312.0	326.3	347.6	373.8	392.6
50°	238.2	243.7	251.0	260.0	270.9	283.4	294.3	309.8	330.1	350.8	367.2
52.5°	222.7	227.6	235.9	245.5	255.6	266.4	278.1	291.4	309.7	329.2	342.1
55°	198.4	204.5	211.5	220.9	230.9	240.0	251.2	264.9	279.5	294.0	302.9
57.5°	175.8	180.9	186.7	196.5	205.1	215.9	226.0	236.7	250.2	261.1	266.9
60°	159.3	163.8	171.4	179.9	188.1	197.5	209.1	219.7	230.0	238.8	243.4
62.5°	143.8	149.0	155.7	163.4	172.4	181.3	191.3	200.3	209.4	217.0	220.1
65°	123.5	127.8	132.6	139.9	147.2	156.3	164.1	173.3	179.9	184.2	186.9
67.5°	105.0	107.8	111.5	116.4	123.6	131.5	139.2	146.2	151.9	154.7	157.2
70°	93.2	95.0	97.7	102.6	108.1	115.0	122.9	128.0	132.9	135.3	137.8
72.5°	81.3	83.6	86.0	89.9	94.4	99.5	105.2	111.5	114.2	117.1	118.6
75°	61.6	65.0	68.3	70.7	73.8	77.7	82.9	86.7	88.3	90.7	91.0
77.5°	46.5	47.2	49.7	52.7	55.2	58.1	61.3	64.9	65.6	66.9	67.7
80°	38.3	38.3	38.3	40.1	43.1	45.2	48.2	50.1	51.3	51.6	51.9
82.5°	30.7	30.7	30.5	30.8	31.9	33.0	35.9	37.9	38.9	38.7	38.0
85°	20.0	19.4	19.4	19.1	19.4	18.8	18.5	19.7	21.5	21.5	20.9
87.5°	12.2	11.8	11.6	10.9	10.2	9.5	8.4	8.2	7.9	8.6	7.9
90°	19.8	19.1	16.8	14.5	12.2	9.9	7.8	6.1	4.4	2.5	0.8
92.5°	21.5	20.4	18.6	16.9	15.2	13.5	12.8	13.3	13.8	14.3	14.8
95°	25.9	24.6	22.7	20.8	18.9	16.9	19.6	26.8	34.1	41.3	48.6
97.5°	27.0	25.6	38.3	51.1	63.8	76.5	84.5	87.8	91.0	94.3	97.5
100°	27.6	26.2	53.9	81.4	109.0	136.6	148.6	145.0	141.6	138.0	134.4
102.5°	48.0	52.4	82.5	112.6	142.8	172.9	186.6	184.1	181.6	179.0	176.5
105°	143.0	174.3	190.2	206.0	222.0	237.9	244.9	243.0	241.0	239.1	237.1
107.5°	296.4	319.4	316.9	314.3	311.9	309.3	307.3	305.8	304.2	302.6	301.1
110°	353.0	358.9	356.9	355.0	353.0	351.1	349.4	348.0	346.6	345.2	343.7



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	399.0	398.9	397.0	395.1	393.1	391.2	389.6	388.3	387.0	385.7	384.4
115°	458.5	456.7	455.1	453.5	451.9	450.4	449.0	448.0	446.9	445.8	444.8
117.5°	514.1	512.7	511.9	511.1	510.3	509.5	508.4	507.1	505.8	504.5	503.2
120°	550.4	549.0	548.5	548.0	547.4	546.9	545.8	544.2	542.6	541.1	539.5
122.5°	586.3	585.3	584.6	583.9	583.3	582.6	581.6	580.3	579.0	577.7	576.4
125°	636.9	636.5	635.8	635.1	634.4	633.7	632.6	631.2	629.8	628.4	627.0
127.5°	686.7	686.2	685.3	684.5	683.7	682.8	681.7	680.2	678.8	677.4	676.0
130°	716.8	716.1	715.4	714.7	714.0	713.3	712.3	710.8	709.4	708.0	706.5
132.5°	745.4	744.7	744.2	743.6	743.1	742.5	741.5	740.1	738.6	737.3	735.9
135°	789.0	788.5	787.8	787.1	786.4	785.7	784.8	783.7	782.7	781.6	780.5
137.5°	827.4	826.6	826.2	825.8	825.4	825.0	824.1	822.8	821.4	820.1	818.7
140°	852.1	851.4	850.8	850.3	849.8	849.2	848.4	847.4	846.4	845.3	844.2
142.5°	875.5	874.9	874.4	873.9	873.3	872.8	872.0	870.9	869.9	868.8	867.8
145°	908.2	907.8	907.5	907.1	906.8	906.4	905.6	904.4	903.2	901.9	900.7
147.5°	937.3	937.0	936.6	936.3	935.9	935.6	935.0	934.1	933.3	932.6	931.8
150°	955.1	954.8	954.4	954.1	953.7	953.4	952.9	952.4	951.9	951.3	950.9
152.5°	970.7	970.1	969.9	969.6	969.5	969.2	969.0	968.8	968.5	968.3	968.0
155°	992.3	991.4	991.3	991.0	990.9	990.7	990.8	991.2	991.5	991.8	992.2
157.5°	1011.1	1010.0	1010.2	1010.3	1010.6	1010.7	1010.8	1010.9	1010.9	1011.0	1011.0
160°	1021.9	1020.9	1021.0	1021.2	1021.4	1021.5	1021.8	1021.9	1022.1	1022.2	1022.5
162.5°	1031.6	1030.4	1030.5	1030.8	1030.9	1031.1	1031.4	1031.9	1032.4	1032.8	1033.2
165°	1044.6	1043.1	1043.3	1043.5	1043.6	1043.9	1044.2	1044.7	1045.3	1045.8	1046.3
167.5°	1054.7	1053.3	1053.3	1053.3	1053.3	1053.3	1053.7	1054.4	1055.1	1055.8	1056.5
170°	1060.4	1059.1	1059.1	1059.1	1059.1	1059.1	1059.4	1060.1	1060.8	1061.5	1062.2
172.5°	1064.3	1062.9	1062.7	1062.6	1062.4	1062.3	1062.6	1063.5	1064.4	1065.2	1066.0
175°	1069.1	1067.8	1067.6	1067.5	1067.2	1067.1	1067.5	1068.3	1069.2	1070.1	1071.0
177.5°	1070.9	1069.7	1069.5	1069.4	1069.3	1069.1	1069.4	1070.2	1070.9	1071.5	1072.2
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	712.6	715.3	718.7	723.8	727.7	731.1	731.8	732.8	735.2	739.3	742.5
5°	717.3	724.3	735.5	746.4	758.3	767.9	777.1	783.5	789.5	802.2	812.5
7.5°	715.8	731.3	748.9	768.6	788.4	807.6	825.5	841.5	857.4	875.9	897.1
10°	714.9	733.1	756.7	781.9	809.5	836.5	862.6	883.0	906.7	927.9	954.9
12.5°	710.3	736.5	764.8	796.9	830.9	862.1	896.4	924.5	951.5	982.2	1013.6
15°	704.3	736.1	771.9	814.7	866.3	903.9	939.1	987.9	1021.3	1054.7	1099.6
17.5°	693.2	732.1	776.9	832.4	875.5	926.1	979.0	1017.6	1062.6	1109.6	1150.2
20°	684.5	729.8	779.8	834.4	889.3	944.3	995.5	1041.6	1088.1	1142.4	1175.8
22.5°	675.8	720.5	772.5	830.5	889.5	947.4	1005.4	1059.6	1111.8	1166.6	1209.3
25°	657.2	710.3	766.8	825.9	884.2	947.8	1017.1	1077.4	1142.1	1198.5	1238.9
27.5°	638.4	687.1	743.2	803.3	868.0	943.3	1024.7	1093.4	1158.1	1198.5	1211.2
30°	621.4	673.0	724.5	785.5	855.6	939.7	1026.2	1104.8	1157.9	1175.4	1162.4
32.5°	604.2	650.9	702.0	764.5	838.9	930.7	1028.1	1098.0	1130.0	1116.5	1063.3
35°	573.8	615.9	665.4	727.9	813.5	925.7	1020.1	1067.5	1059.5	983.7	883.5
37.5°	541.2	575.6	621.4	686.7	787.1	906.0	985.6	992.6	924.3	807.9	692.2
40°	515.5	546.4	593.5	661.8	766.8	886.6	950.9	922.7	816.8	687.2	590.7
42.5°	490.5	516.6	561.9	635.6	747.3	860.2	899.2	837.7	715.6	593.0	505.3
45°	448.1	472.7	518.2	593.8	707.6	809.5	804.4	697.6	575.3	476.7	403.9
47.5°	408.0	429.4	472.2	549.3	660.9	733.6	685.4	571.8	468.0	389.0	337.0
50°	379.6	400.8	443.3	519.4	623.5	676.6	607.8	498.2	403.2	337.7	296.4
52.5°	352.4	373.1	412.0	486.2	578.4	610.1	536.1	434.6	355.5	298.9	263.4
55°	314.3	330.1	365.0	436.0	504.9	512.1	437.2	352.3	287.0	247.6	223.3
57.5°	275.6	289.1	323.6	380.2	428.5	424.7	353.6	280.2	236.2	206.9	189.3
60°	250.3	263.6	294.0	342.5	379.0	366.2	301.0	241.9	204.2	182.7	168.7
62.5°	226.8	237.2	265.6	301.0	327.3	312.8	257.3	208.3	178.5	160.3	149.2
65°	192.7	201.1	223.9	242.4	257.0	243.0	196.9	163.0	141.4	128.7	121.0
67.5°	160.3	165.6	180.1	186.7	197.0	181.7	148.1	125.3	113.0	102.3	97.0
70°	139.9	143.9	151.4	156.9	159.6	143.9	118.9	102.3	92.0	84.4	81.0
72.5°	119.5	122.9	124.5	129.0	127.5	112.7	95.6	82.4	74.9	69.8	65.5
75°	91.3	92.8	91.3	89.5	85.6	75.3	63.5	56.7	51.3	48.9	47.4
77.5°	66.5	66.1	64.0	61.2	54.4	47.9	41.6	39.3	37.0	35.6	35.2
80°	51.3	50.1	48.2	43.7	37.9	33.4	31.8	30.3	29.5	27.9	27.6
82.5°	38.2	37.5	34.4	30.6	26.5	24.4	23.1	22.6	21.6	20.9	20.8
85°	20.4	19.4	16.1	13.9	13.4	12.8	12.4	12.4	11.2	10.9	10.9
87.5°	7.1	5.9	6.1	5.7	6.1	6.1	6.8	6.7	7.0	7.4	7.1
90°	2.5	4.4	6.1	7.8	9.9	12.2	14.5	16.8	19.1	19.8	20.5
92.5°	14.3	13.8	13.3	12.8	13.5	15.2	16.9	18.6	20.4	21.5	22.7
95°	41.3	34.1	26.8	19.6	16.9	18.9	20.8	22.7	24.6	25.9	27.2
97.5°	94.3	91.0	87.8	84.5	76.5	63.8	51.1	38.3	25.6	27.0	28.4
100°	138.0	141.6	145.0	148.6	136.6	109.0	81.4	53.9	26.2	27.6	29.1
102.5°	179.0	181.6	184.1	186.6	172.9	142.8	112.6	82.5	52.4	48.0	43.6
105°	239.1	241.0	243.0	244.9	237.9	222.0	206.0	190.2	174.3	143.0	111.7
107.5°	302.6	304.2	305.8	307.3	309.3	311.9	314.3	316.9	319.4	296.4	273.5
110°	345.2	346.6	348.0	349.4	351.1	353.0	355.0	356.9	358.9	353.0	347.2





TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	385.7	387.0	388.3	389.6	391.2	393.1	395.1	397.0	398.9	399.0	399.2
115°	445.8	446.9	448.0	449.0	450.4	451.9	453.5	455.1	456.7	458.5	460.3
117.5°	504.5	505.8	507.1	508.4	509.5	510.3	511.1	511.9	512.7	514.1	515.6
120°	541.1	542.6	544.2	545.8	546.9	547.4	548.0	548.5	549.0	550.4	551.8
122.5°	577.7	579.0	580.3	581.6	582.6	583.3	583.9	584.6	585.3	586.3	587.2
125°	628.4	629.8	631.2	632.6	633.7	634.4	635.1	635.8	636.5	636.9	637.2
127.5°	677.4	678.8	680.2	681.7	682.8	683.7	684.5	685.3	686.2	686.7	687.3
130°	708.0	709.4	710.8	712.3	713.3	714.0	714.7	715.4	716.1	716.8	717.6
132.5°	737.3	738.6	740.1	741.5	742.5	743.1	743.6	744.2	744.7	745.4	746.2
135°	781.6	782.7	783.7	784.8	785.7	786.4	787.1	787.8	788.5	789.0	789.6
137.5°	820.1	821.4	822.8	824.1	825.0	825.4	825.8	826.2	826.6	827.4	828.2
140°	845.3	846.4	847.4	848.4	849.2	849.8	850.3	850.8	851.4	852.1	852.8
142.5°	868.8	869.9	870.9	872.0	872.8	873.3	873.9	874.4	874.9	875.5	876.1
145°	901.9	903.2	904.4	905.6	906.4	906.8	907.1	907.5	907.8	908.2	908.6
147.5°	932.6	933.3	934.1	935.0	935.6	935.9	936.3	936.6	937.0	937.3	937.7
150°	951.3	951.9	952.4	952.9	953.4	953.7	954.1	954.4	954.8	955.1	955.5
152.5°	968.3	968.5	968.8	969.0	969.2	969.5	969.6	969.9	970.1	970.7	971.4
155°	991.8	991.5	991.2	990.8	990.7	990.9	991.0	991.3	991.4	992.3	993.2
157.5°	1011.0	1010.9	1010.9	1010.8	1010.7	1010.6	1010.3	1010.2	1010.0	1011.1	1012.2
160°	1022.2	1022.1	1021.9	1021.8	1021.5	1021.4	1021.2	1021.0	1020.9	1021.9	1022.9
162.5°	1032.8	1032.4	1031.9	1031.4	1031.1	1030.9	1030.8	1030.5	1030.4	1031.6	1032.8
165°	1045.8	1045.3	1044.7	1044.2	1043.9	1043.6	1043.5	1043.3	1043.1	1044.6	1045.9
167.5°	1055.8	1055.1	1054.4	1053.7	1053.3	1053.3	1053.3	1053.3	1053.3	1054.7	1056.1
170°	1061.5	1060.8	1060.1	1059.4	1059.1	1059.1	1059.1	1059.1	1059.1	1060.4	1061.8
172.5°	1065.2	1064.4	1063.5	1062.6	1062.3	1062.4	1062.6	1062.7	1062.9	1064.3	1065.7
175°	1070.1	1069.2	1068.3	1067.5	1067.1	1067.2	1067.5	1067.6	1067.8	1069.1	1070.2
177.5°	1071.5	1070.9	1070.2	1069.4	1069.1	1069.3	1069.4	1069.5	1069.7	1070.9	1072.0
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	708.8	708.8	708.8	708.8	708.8	708.8	708.8
2.5°	747.7	747.7	748.6	752.3	752.7	755.9	754.9
5°	821.7	827.4	829.6	838.7	844.1	846.5	841.7
7.5°	912.2	928.4	936.2	945.7	954.1	956.7	950.1
10°	978.3	995.2	1009.5	1018.3	1026.5	1031.9	1038.9
12.5°	1042.0	1063.0	1076.5	1088.9	1097.3	1104.3	1105.4
15°	1111.4	1143.0	1167.0	1184.6	1193.3	1197.9	1196.1
17.5°	1181.4	1210.6	1227.7	1245.6	1257.8	1258.5	1258.9
20°	1221.0	1249.5	1269.2	1282.5	1296.2	1295.6	1298.6
22.5°	1247.4	1269.9	1285.0	1294.7	1299.3	1297.0	1297.7
25°	1259.8	1266.5	1263.8	1248.2	1244.4	1230.1	1232.5
27.5°	1196.0	1164.4	1131.8	1089.7	1056.6	1030.2	1031.5
30°	1109.3	1053.4	989.8	936.4	888.4	875.0	846.5
32.5°	988.2	904.4	829.8	780.1	738.9	727.7	702.8
35°	782.8	701.5	624.7	578.6	560.4	535.0	534.6
37.5°	608.5	536.9	496.3	461.7	443.5	428.1	426.6
40°	511.9	456.1	425.4	400.5	382.6	371.1	368.4
42.5°	444.4	399.3	370.5	355.1	341.4	335.4	331.0
45°	362.9	332.6	312.5	298.6	292.2	287.6	285.2
47.5°	303.6	283.2	269.6	260.3	255.1	250.3	251.6
50°	271.2	254.6	244.5	235.8	231.8	228.5	228.8
52.5°	245.3	230.3	222.2	215.9	211.0	208.6	207.4
55°	208.2	198.8	190.5	186.0	183.2	179.9	179.0
57.5°	177.5	170.2	163.6	158.4	157.8	154.6	155.0
60°	157.2	151.1	145.6	142.9	140.8	138.1	138.9
62.5°	140.5	135.3	130.3	128.1	126.0	124.0	124.4
65°	115.0	110.1	107.1	105.9	105.0	104.1	103.1
67.5°	91.7	88.6	86.7	84.1	82.3	82.0	81.0
70°	77.1	73.1	69.8	66.5	65.5	65.2	65.5
72.5°	61.8	59.3	58.4	56.7	56.6	55.8	56.3
75°	46.4	45.6	44.9	43.7	43.7	43.7	43.7
77.5°	34.2	33.7	33.4	33.0	32.8	32.3	32.3
80°	26.7	26.4	25.8	25.8	25.5	25.8	25.5
82.5°	20.1	20.1	19.5	19.5	19.2	19.0	19.2
85°	10.3	10.0	10.6	10.0	10.3	9.7	10.3
87.5°	7.1	7.3	7.1	7.2	7.1	7.6	7.2
90°	21.2	21.9	22.4	22.8	23.1	23.5	23.8
92.5°	23.8	24.9	25.6	25.7	26.0	26.2	26.4
95°	28.4	29.6	30.3	30.3	30.3	30.3	30.3
97.5°	29.9	31.3	32.1	32.2	32.4	32.6	32.8
100°	30.5	31.9	32.7	32.9	33.0	33.3	33.4
102.5°	39.2	34.8	32.8	33.1	33.4	33.7	34.1
105°	80.3	49.0	33.6	34.0	34.3	34.6	35.0
107.5°	250.6	227.6	204.3	180.7	157.2	133.6	110.0
110°	341.4	335.5	320.0	294.7	269.3	244.1	218.8



TEST NUMBER: P332418-927

CATALOG NUMBER: S123RDIW-S560D1030U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	399.3	399.3	396.7	391.4	386.1	380.7	375.4
115°	462.0	463.8	465.0	465.7	466.4	467.1	467.9
117.5°	517.0	518.4	519.2	519.3	519.4	519.6	519.8
120°	553.3	554.7	555.4	555.4	555.4	555.4	555.4
122.5°	588.3	589.2	589.9	589.9	590.1	590.3	590.4
125°	637.6	637.9	638.3	638.7	639.0	639.4	639.7
127.5°	687.9	688.5	688.6	688.2	687.9	687.5	687.1
130°	718.2	718.9	719.1	718.7	718.4	718.0	717.7
132.5°	746.9	747.6	747.7	747.2	746.7	746.2	745.7
135°	790.1	790.6	790.6	790.1	789.6	789.0	788.5
137.5°	829.1	830.0	830.2	829.8	829.5	829.1	828.8
140°	853.5	854.2	854.4	854.1	853.7	853.3	852.9
142.5°	876.6	877.2	877.2	876.7	876.2	875.8	875.2
145°	908.9	909.3	909.4	909.4	909.4	909.4	909.4
147.5°	938.0	938.4	938.2	937.4	936.5	935.7	934.9
150°	955.8	956.2	956.2	955.6	955.1	954.6	954.0
152.5°	972.0	972.6	972.6	971.7	970.9	970.1	969.3
155°	994.0	995.0	994.8	993.8	992.8	991.7	990.6
157.5°	1013.2	1014.2	1014.1	1012.7	1011.4	1010.0	1008.6
160°	1024.1	1025.1	1025.0	1023.7	1022.5	1021.3	1020.0
162.5°	1034.0	1035.2	1035.2	1034.2	1033.1	1032.0	1030.9
165°	1047.3	1048.8	1048.8	1047.7	1046.4	1045.1	1043.9
167.5°	1057.6	1059.0	1059.0	1057.6	1056.1	1054.7	1053.3
170°	1063.3	1064.7	1064.7	1063.3	1061.8	1060.4	1059.1
172.5°	1067.1	1068.5	1068.4	1066.9	1065.3	1063.7	1062.2
175°	1071.5	1072.8	1072.7	1071.3	1069.8	1068.4	1067.0
177.5°	1073.1	1074.2	1074.1	1072.7	1071.3	1069.8	1068.4
180°	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0	1071.0

(END OF REPORT)