

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332429-927

Luminaire Tested: **S123RDIW-S560D1535U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P332429-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S123RDIW-S560D1535U927-4F0-1E-UDD-F1  
Description: DEFINE 3 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1535 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5908.1 lumens  
Efficiency: N/A  
Efficacy: 97.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.06 / 1.22  
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 60.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P332429-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P332429-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37	29				
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25				
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	28	26	21				
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23	18				
4	71	61	53	47	63	55	48	43	43	39	35	33	30	27	23	21	20	15				
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	21	19	17	14				
6	60	48	41	35	53	44	37	32	35	30	26	27	23	21	19	17	15	12				
7	55	44	36	31	49	39	33	28	32	27	23	24	21	18	17	15	14	11				
8	51	39	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12	10				
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11	9				
10	44	33	26	21	40	30	24	20	24	20	16	19	15	13	14	11	10	8				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8054	8054	8054
5°	8084	7973	8018
10°	8039	7873	7847
15°	7952	7689	7608
20°	7834	7458	7285
25°	7712	7201	6969
30°	7549	6901	6524
35°	7384	6603	6116
40°	7231	6250	5611
45°	7030	5903	5154
50°	6807	5508	4644
55°	6583	5056	4168
60°	6374	4573	3645
65°	6105	4050	3123
70°	5766	3402	2521
75°	5273	2674	2371
80°	4705	2374	2182
85°	3977	2100	1951



TEST NUMBER: P332429-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	70.3	1.2
10°-20°	195.5	3.3
20°-30°	281.5	4.8
30°-40°	317.1	5.4
40°-50°	303.3	5.1
50°-60°	248.4	4.2
60°-70°	167.6	2.8
70°-80°	84.3	1.4
80°-90°	26.8	0.5
90°-100°	99.1	1.7
100°-110°	296.5	5.0
110°-120°	504.3	8.5
120°-130°	663.4	11.2
130°-140°	745.6	12.6
140°-150°	732.9	12.4
150°-160°	617.0	10.4
160°-170°	410.7	7.0
170°-180°	143.8	2.4
0°-30°	547.2	9.3
0°-40°	864.3	14.6
0°-60°	1416.1	24.0
0°-90°	1694.8	28.7
90°-120°	899.9	15.2
90°-150°	3041.8	51.5
90°-180°	4213.0	71.3
0°-180°	5908.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	748	748	748	748	748	
5°	748	745	738	743	742	71
15°	714	706	690	687	683	201
25°	649	633	606	594	587	298
35°	562	539	502	477	465	352
45°	462	433	388	354	339	356
55°	351	320	269	236	222	314
65°	240	206	159	130	123	237
75°	127	97	64	58	57	135
85°	32	19	17	16	16	36
90°	1	13	29	33	36	6
95°	70	79	88	93	93	79
105°	269	272	282	282	284	288
115°	508	511	509	510	509	502
125°	743	746	744	739	735	662
135°	964	971	970	965	963	743
145°	1170	1172	1175	1174	1170	730
155°	1339	1339	1340	1344	1337	616
165°	1459	1455	1455	1461	1454	411
175°	1517	1513	1512	1519	1511	144
180°	1521	1521	1521	1521	1521	



TEST NUMBER: P332429-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	750.7	750.2	749.8	749.3	748.9	748.1	746.8	745.4	744.2	742.9	744.1
5°	748.2	747.6	746.9	746.2	745.5	744.4	742.8	741.2	739.5	737.9	739.1
7.5°	741.3	740.6	739.8	739.1	738.4	737.0	734.9	732.8	730.6	728.6	729.2
10°	735.5	734.5	733.6	732.6	731.7	730.0	727.6	725.2	722.7	720.3	720.4
12.5°	727.2	726.2	725.1	724.1	723.0	721.0	718.0	715.1	712.1	709.2	709.1
15°	713.6	712.2	710.7	709.2	707.7	705.0	701.3	697.5	693.7	690.0	689.3
17.5°	696.5	694.8	693.1	691.3	689.6	686.3	681.5	676.8	671.9	667.2	665.7
20°	683.9	681.8	679.6	677.4	675.3	671.6	666.5	661.4	656.2	651.1	649.4
22.5°	669.8	667.3	664.9	662.3	659.9	655.9	650.5	645.0	639.6	634.1	631.9
25°	649.3	645.9	642.5	639.2	635.8	631.1	624.8	618.6	612.4	606.3	603.4
27.5°	624.4	620.7	617.0	613.2	609.5	604.2	597.3	590.4	583.5	576.6	572.7
30°	607.4	603.4	599.4	595.3	591.3	585.4	577.9	570.4	562.8	555.2	550.6
32.5°	590.4	585.9	581.3	576.7	572.1	565.9	557.9	549.9	541.9	533.9	528.9
35°	561.9	557.1	552.2	547.4	542.5	535.9	527.5	519.2	510.8	502.5	496.6
37.5°	533.1	527.7	522.3	516.8	511.4	504.3	495.4	486.5	477.5	468.6	462.0
40°	514.6	508.7	502.7	496.8	490.8	483.1	473.6	464.0	454.4	444.8	437.8
42.5°	493.7	487.7	481.9	475.9	470.0	462.1	452.2	442.3	432.4	422.5	414.8
45°	461.8	455.7	449.6	443.6	437.5	429.3	418.9	408.5	398.2	387.8	380.1
47.5°	429.8	423.2	416.5	409.9	403.2	394.7	384.3	373.9	363.5	353.2	344.8
50°	406.5	400.2	393.9	387.5	381.2	372.6	361.6	350.8	339.8	328.9	320.5
52.5°	385.7	378.8	371.9	365.0	358.2	349.4	338.5	327.7	316.9	306.1	297.4
55°	350.8	344.1	337.5	330.9	324.3	315.3	303.8	292.4	280.9	269.4	261.6
57.5°	318.5	311.2	304.0	296.8	289.6	280.3	268.8	257.3	245.7	234.2	226.9
60°	296.1	288.8	281.3	273.9	266.5	257.1	246.0	234.8	223.6	212.4	205.1
62.5°	273.8	266.4	259.0	251.5	244.2	234.8	223.6	212.5	201.2	190.0	183.2
65°	239.7	232.3	224.9	217.5	210.0	201.1	190.5	180.1	169.5	159.0	152.4
67.5°	205.6	198.1	190.6	183.1	175.6	166.8	156.7	146.6	136.6	126.4	121.5
70°	183.2	175.9	168.7	161.4	154.2	145.8	136.3	126.9	117.5	108.1	103.3
72.5°	160.9	153.8	146.6	139.4	132.2	124.4	115.8	107.2	98.6	90.1	86.2
75°	126.8	120.3	113.9	107.4	100.9	94.0	86.6	79.1	71.8	64.3	63.0
77.5°	95.8	89.9	84.1	78.2	72.3	67.0	62.3	57.5	52.7	47.9	47.2
80°	75.9	70.3	64.8	59.3	53.7	49.6	46.7	43.9	41.0	38.3	37.8
82.5°	57.0	52.1	47.4	42.6	37.8	34.8	33.4	32.2	30.8	29.5	29.1
85°	32.2	29.2	26.2	23.3	20.3	18.6	18.2	17.8	17.4	17.0	16.7
87.5°	11.9	11.2	10.6	9.9	9.3	9.3	10.0	10.7	11.3	12.0	12.1
90°	1.2	3.9	6.5	9.2	11.8	14.9	18.3	21.8	25.2	28.7	29.7
92.5°	28.9	30.7	32.5	34.3	36.1	38.0	40.0	41.9	43.9	45.9	46.7
95°	70.5	72.3	74.2	76.0	78.0	79.9	82.0	84.1	86.3	88.4	89.4
97.5°	125.2	126.6	127.9	129.4	130.7	132.1	133.7	135.2	136.8	138.3	139.6
100°	162.5	164.1	165.6	167.2	168.8	170.3	171.6	172.9	174.3	175.6	176.4
102.5°	205.5	206.4	207.4	208.3	209.3	210.6	212.4	214.1	215.9	217.6	218.5
105°	268.8	269.3	269.8	270.4	270.9	272.4	274.7	277.1	279.6	281.9	281.9
107.5°	342.4	342.7	343.0	343.3	343.6	344.3	345.2	346.2	347.1	348.1	349.0
110°	388.2	388.8	389.3	389.8	390.4	390.9	391.4	392.0	392.4	393.0	394.1



TEST NUMBER: P332429-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	436.0	436.3	436.7	437.0	437.3	437.5	437.6	437.7	437.8	437.9	439.2
115°	507.7	508.5	509.3	510.1	510.9	511.0	510.5	509.9	509.5	508.9	509.1
117.5°	579.9	580.4	580.9	581.5	581.9	581.9	581.2	580.5	579.8	579.2	579.1
120°	624.8	626.4	628.0	629.5	631.1	631.3	629.9	628.6	627.2	626.0	625.7
122.5°	671.6	672.7	673.9	675.1	676.3	676.5	675.8	675.1	674.5	673.8	673.0
125°	743.0	743.8	744.7	745.4	746.2	746.3	745.8	745.3	744.7	744.3	743.1
127.5°	809.0	810.6	812.4	814.0	815.8	816.3	815.7	815.2	814.6	814.0	812.5
130°	852.9	855.1	857.1	859.3	861.4	862.1	861.3	860.5	859.7	858.9	857.9
132.5°	896.9	899.0	901.1	903.2	905.4	906.2	905.5	905.0	904.4	903.8	902.5
135°	964.0	965.6	967.2	968.8	970.4	971.1	970.8	970.5	970.3	970.0	968.9
137.5°	1026.1	1027.5	1028.8	1030.2	1031.4	1032.5	1033.2	1033.8	1034.5	1035.2	1034.1
140°	1069.1	1070.5	1071.8	1073.1	1074.4	1075.2	1075.5	1075.8	1076.0	1076.3	1076.0
142.5°	1108.3	1109.6	1111.0	1112.3	1113.6	1114.5	1115.0	1115.5	1115.9	1116.4	1116.2
145°	1169.5	1170.1	1170.5	1171.1	1171.6	1172.3	1173.1	1173.9	1174.6	1175.4	1175.2
147.5°	1223.0	1223.9	1224.9	1225.9	1226.9	1227.6	1228.4	1229.2	1229.9	1230.7	1230.7
150°	1260.3	1260.8	1261.3	1261.9	1262.4	1262.9	1263.5	1264.0	1264.5	1265.0	1265.0
152.5°	1290.9	1291.6	1292.4	1293.1	1293.8	1294.3	1294.7	1295.0	1295.3	1295.6	1296.1
155°	1339.1	1339.1	1339.1	1339.1	1339.1	1339.3	1339.5	1339.7	1340.1	1340.3	1341.4
157.5°	1380.2	1379.9	1379.6	1379.3	1379.0	1378.9	1379.1	1379.3	1379.5	1379.7	1380.9
160°	1406.0	1405.5	1404.9	1404.4	1403.9	1403.6	1403.6	1403.6	1403.6	1403.6	1404.9
162.5°	1428.9	1428.2	1427.4	1426.7	1426.0	1425.7	1425.9	1426.2	1426.3	1426.6	1427.9
165°	1458.6	1457.8	1457.0	1456.2	1455.4	1455.0	1455.0	1455.0	1455.0	1455.0	1456.6
167.5°	1482.3	1481.1	1480.1	1479.0	1478.0	1477.6	1477.7	1478.0	1478.2	1478.4	1480.0
170°	1495.6	1494.5	1493.5	1492.4	1491.4	1490.8	1490.8	1490.8	1490.8	1490.8	1492.7
172.5°	1506.1	1505.1	1504.0	1502.9	1501.9	1501.3	1501.3	1501.3	1501.3	1501.3	1503.0
175°	1517.1	1516.1	1515.0	1513.9	1512.8	1512.4	1512.4	1512.4	1512.4	1512.4	1513.9
177.5°	1521.6	1520.8	1520.0	1519.1	1518.2	1517.8	1517.8	1517.8	1517.8	1517.8	1519.1
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7



TEST NUMBER: P332429-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	748.2	748.2	748.2	748.2	748.2	748.2	748.2	748.2
2.5°	745.3	746.5	747.7	748.1	747.9	747.7	747.5	747.3
5°	740.3	741.6	742.8	743.2	743.0	742.7	742.4	742.1
7.5°	729.9	730.6	731.3	731.3	730.9	730.5	730.0	729.5
10°	720.6	720.7	720.8	720.6	719.9	719.2	718.6	717.9
12.5°	709.0	708.9	708.8	708.4	707.6	706.8	706.1	705.3
15°	688.6	687.9	687.3	686.4	685.5	684.6	683.7	682.7
17.5°	664.3	662.9	661.4	660.0	658.6	657.2	655.8	654.4
20°	647.6	645.9	644.1	642.5	640.8	639.2	637.5	636.0
22.5°	629.8	627.6	625.4	623.5	622.0	620.5	619.0	617.5
25°	600.6	597.7	594.9	592.7	591.3	589.8	588.3	586.8
27.5°	568.7	564.8	560.9	557.8	555.5	553.3	551.0	548.7
30°	546.1	541.5	536.9	533.5	531.4	529.3	527.0	524.9
32.5°	523.9	518.8	513.8	510.2	507.9	505.6	503.4	501.1
35°	490.8	485.1	479.3	475.2	472.7	470.3	467.9	465.4
37.5°	455.4	448.9	442.3	437.5	434.5	431.5	428.5	425.5
40°	430.8	423.7	416.8	411.7	408.6	405.5	402.4	399.3
42.5°	407.2	399.5	391.8	386.6	383.8	381.0	378.3	375.5
45°	372.4	364.7	357.0	351.6	348.3	345.1	341.8	338.6
47.5°	336.4	328.1	319.7	314.1	311.2	308.3	305.5	302.5
50°	312.2	303.8	295.5	289.7	286.6	283.5	280.4	277.3
52.5°	288.8	280.0	271.3	265.6	262.8	260.1	257.3	254.5
55°	253.8	246.0	238.1	232.9	230.2	227.5	224.8	222.1
57.5°	219.4	212.1	204.7	199.9	197.6	195.3	193.0	190.7
60°	197.8	190.5	183.2	178.5	176.2	173.9	171.6	169.3
62.5°	176.3	169.5	162.6	158.0	155.7	153.2	150.8	148.5
65°	145.8	139.2	132.5	128.5	127.1	125.6	124.1	122.6
67.5°	116.6	111.6	106.7	103.5	101.9	100.3	98.7	97.1
70°	98.5	93.9	89.1	86.0	84.5	83.1	81.6	80.1
72.5°	82.3	78.5	74.6	72.4	71.8	71.1	70.5	69.9
75°	61.6	60.3	58.9	58.1	57.8	57.6	57.3	57.0
77.5°	46.5	45.8	45.0	44.5	44.3	44.0	43.7	43.4
80°	37.4	37.0	36.6	36.3	36.0	35.7	35.5	35.2
82.5°	28.7	28.3	27.9	27.6	27.6	27.6	27.5	27.4
85°	16.5	16.2	15.9	15.8	15.8	15.8	15.8	15.8
87.5°	12.3	12.4	12.4	12.5	12.5	12.5	12.5	12.5
90°	30.8	31.8	33.0	33.7	34.2	34.8	35.3	35.8
92.5°	47.5	48.4	49.3	49.5	49.2	48.9	48.6	48.2
95°	90.5	91.6	92.6	93.2	93.2	93.2	93.2	93.2
97.5°	140.8	142.0	143.2	143.8	143.7	143.5	143.5	143.4
100°	177.2	178.0	178.8	179.4	180.0	180.5	181.0	181.6
102.5°	219.3	220.1	220.9	221.2	221.1	220.9	220.9	220.8
105°	281.9	281.9	281.9	282.2	282.7	283.3	283.8	284.3
107.5°	349.8	350.6	351.5	351.7	351.4	351.1	350.8	350.5
110°	395.1	396.2	397.3	397.5	397.0	396.5	395.9	395.4





TEST NUMBER: P332429-927

CATALOG NUMBER: S123RDIW-S560D1535U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	440.5	441.7	443.0	443.6	443.5	443.4	443.3	443.1
115°	509.5	509.7	509.9	509.9	509.7	509.5	509.1	508.9
117.5°	579.0	579.0	578.9	578.5	577.7	577.0	576.3	575.5
120°	625.4	625.2	624.9	624.5	624.0	623.4	622.9	622.3
122.5°	672.3	671.7	671.0	670.3	669.6	668.8	668.0	667.3
125°	742.1	741.0	740.0	738.9	737.8	736.8	735.7	734.7
127.5°	811.0	809.5	808.0	806.7	805.5	804.2	803.0	801.8
130°	856.7	855.7	854.7	853.2	851.4	849.5	847.6	845.7
132.5°	901.3	900.0	898.7	897.4	896.0	894.5	893.0	891.6
135°	967.9	966.8	965.7	965.0	964.4	963.8	963.4	962.8
137.5°	1033.0	1031.9	1030.8	1029.7	1028.6	1027.7	1026.7	1025.6
140°	1075.8	1075.5	1075.2	1074.2	1072.3	1070.5	1068.6	1066.8
142.5°	1115.9	1115.6	1115.4	1114.5	1113.1	1111.7	1110.2	1108.8
145°	1174.9	1174.6	1174.4	1173.7	1172.7	1171.6	1170.5	1169.5
147.5°	1230.7	1230.7	1230.7	1229.9	1228.3	1226.7	1225.0	1223.4
150°	1265.0	1265.0	1265.0	1264.2	1262.7	1261.1	1259.5	1257.9
152.5°	1296.5	1296.9	1297.4	1296.9	1295.5	1294.1	1292.7	1291.3
155°	1342.4	1343.5	1344.6	1344.2	1342.3	1340.5	1338.6	1336.7
157.5°	1382.0	1383.1	1384.2	1384.0	1382.5	1381.0	1379.5	1378.1
160°	1406.3	1407.6	1408.9	1409.1	1408.0	1406.9	1405.9	1404.8
162.5°	1429.2	1430.5	1431.9	1431.7	1430.0	1428.3	1426.6	1424.9
165°	1458.2	1459.8	1461.3	1461.3	1459.4	1457.5	1455.6	1453.8
167.5°	1481.7	1483.4	1484.9	1484.9	1483.4	1481.7	1480.0	1478.4
170°	1494.5	1496.4	1498.3	1498.3	1496.4	1494.5	1492.7	1490.8
172.5°	1504.6	1506.3	1507.9	1507.8	1505.9	1504.1	1502.2	1500.4
175°	1515.5	1517.1	1518.7	1518.5	1516.7	1514.8	1513.0	1511.2
177.5°	1520.4	1521.6	1522.9	1522.8	1521.3	1519.8	1518.4	1516.9
180°	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7	1520.7

(END OF REPORT)